

RL78/G10

R01AN2595EJ0100

Rev.1.00

2015.11.9

Timer Array Unit

Controlling Switched-Mode Power Supply with Dual Input One-Shot Pulse Output Function

Introduction

This application note explains how to use the dual input one-shot pulse output function to control the switched-mode power supply (SMPS or flyback converter).

Target Device

RL78/G10 16-pin (Part name: R5F10Y47, R5F10Y46, R5F10Y44)

Contents

1. Basic Functions	3
1.1 Peak Current Detection	4
1.2 ZCD Signal Detection	5
2. Pin Assignment Example	6
3. Peripheral Function Settings	7
4. Flowcharts	8
4.1 Main and Peripheral Function Initialization	8
4.2 Clock Generation Circuit Initialization	9
4.3 TAU Initialization	10
4.4 12-bit Interval Timer Initialization	12
5. Switching Waveform	13
6. Sample Code	14
7. Documents for Reference	14

1. Basic Functions

The dual input one-shot pulse output function in the timer array can output a variation of one-shot pulses by changing the pin polarity of the timer output, triggering a valid edge of the timer input pin.

The following is an example of a current-controlled flyback converter using this function.




Figure 1-1 Circuit Example

The MCU detects the peak signal of the current (I_{ds}) during the ON state of switching device Q1 when the ZCD (Zero Current Detection) signal indicates the current (I_s) flowing through the transformer coil is zero. Using these two edge signals for the timer module, the MCU then controls the I_{ds} by outputting the one-shot pulse to Q1.

1.1 Peak Current Detection

Transistor Q2 is used to detect the peak current of I_{ds} . Transistor Q2's base and emitter pins are connected to both sides of shunt resistor R_s , which is connected to the Q1 source pin. The Q2 collector pin is connected to timer input pin TI03. As I_{ds} increases, the R_s end-to-end voltage reaches the V_{be} voltage of Q2 ($\approx 0.6V$). This turns Q2 ON and switches the input signal of TI03 to Low. This edge becomes the trigger to switch timer output pin TO03 to Low.

The timing of peak current detection shown in Figures 1 to 3.




Figure 1-2 Peak Current Output Detection Using External Circuit




Figure 1-3 Timing Chart (peak current detection)

1.2 ZCD Signal Detection

This application detects the zero timing of secondary-side current I_s using the winding voltage of the transformer, as shown in Figures 1 to 4. The method used to detect this zero current I_s called Zero Current Detection (ZCD). When Q1 turns OFF, the energy accumulated in the transformer is transferred to the secondary side (winding). Because I_s flows in the same direction as the diode on the secondary side, power is supplied to the output capacitor and the load. When all of the accumulated energy is transferred from the transformer, the ZCD signal goes to Low. This edge is input to timer input pin T10x and the PWM signal switches to High.

The timing of ZCD signal detection as shown in Figures 1 to 5.




Figure 1-4 ZCD Signal Detection




Figure 1-5 Timing Chart (ZCD signal detection)

2. Pin Assignment Example

Table 2-1 shows RL78/G10 pin assignments for the circuit example described above.

Table 2-1 Pin Assignment Example

Pin	Port	A/D	Comparator	SIF	Timer	External	Other	Function
1	P41				TI03	INTP2		Peak current detection
2	P40				(TI01/ TO01)	KR0	TOOL0/ (PCLBUZ0)	
3	P125					KR1	RESET	Reset
4	P137				TI00	INTP0		ZCD signal detection
5	P122					(INTP2)	X2/ EXCLK	
6	P121					(INTP3)	X1	
7							Vss	GND
8							Vdd	5V
9	P00			SO00/ TXD0		INTP1		
10	P01	ANI0		SI00/ RXD0/ SDA00		KR2		
11	P02	ANI1	VCOUT0	SCK00/ SCL00		KR3	PCLBUZ0	
12	P03	ANI2	IVCMP0		TO00	KR4/ (INTP1)		
13	P04	ANI3	IVREF0		TI01/ TO01	KR5		
14	P05	ANI4		SO01	TI02/ TO02			
15	P06	ANI5		SCLA0/ SIO1		INTP3		
16	P07	ANI6		SDAA0/ SCK01	TO03			PWM signal

3. Operation Check Conditions

The sample code contained in this application note has been checked under the conditions listed in the table below.

Table 3-1 Operation Check Conditions

Item	Description
Microcontroller used	RL78/G10 (R5F10Y47、R5F10Y46、R5F10Y44)
Operating frequency	<ul style="list-style-type: none"> High-speed on-chip oscillator (HOCO) clock : 20MHz CPU/peripheral hardware clock : 20MHz
Operating voltage	5.0V (can run on a voltage rang of 2.9Vto5.5V) SPOR detection voltage : When reset occurs:VDD \geq 2.90V (typ.) When reset occurs:VDD<2.84V (typ.)
Integrated development environment(CS+)	CS+ for CA,CX V3.00.01 from Renesas Electronics Corp.
C compiler	RA78K0R V1.71 from Renesas Electronics Corp.

4. Peripheral Function Settings

The following tables describe the peripheral function settings for RL78/G10.

Table 4-1 Peripheral Function Settings

Function	Ch	Setting
TAU	Ch0,3	<ul style="list-style-type: none"> For switching Operating mode: dual input one-shot pulse output TI00: peak current detection TI03: ZCD signal detection TO03: PWM signal output
12-bit interval timer	-	<ul style="list-style-type: none"> For main interval count (200us interval)

Table 3-2 Option Byte Setting

Address	Setting Value	Description
000C0H	1110 1110	<ul style="list-style-type: none"> Watchdog timer not used
000C1H	1111 0111	<ul style="list-style-type: none"> Uses P125 as RESET pin Generates reset: 2.84V or lower Releases reset: 2.90V or higher
000C2H	1111 1001	<ul style="list-style-type: none"> High-speed on-chip oscillator (20MHz)
000C3H	1000 0101	<ul style="list-style-type: none"> Enables on-chip debug operation

5. Flowcharts

5.1 Main and Peripheral Function Initialization

The following flowchart is an example of main processing and peripheral function initialization.




Figure 4-1 Main Processing Flow

5.2 Clock Generation Circuit Initialization

The following flowchart is an example of the clock generation circuit initialization.




Figure 4-2 Clock Generation Circuit Initialization Flowchart

5.3 TAU Initialization

The following flowchart shows the initialization of the timer array unit (TAU).




Figure 4-3 TAU Initialization Flowchart (1)




Figure 4-4 TAU Initialization Flowchart (2)

5.4 12-bit Interval Timer Initialization

The following flowchart shows the initialization of the 12-bit interval timer.




Figure 4-5 12-bit Interval Timer Initialization Flowchart

6. Switching Waveform

The following shows the switching waveform for this example.




Figure 5-1 Switching Waveform

7. Sample Code

The sample code is available on the Renesas Electronics Website.

8. Documents for Reference

RL78/G10 User's Manual: Hardware Rev.3.00 (R01UH0384E)

RL78 Family User's Manual: Software Rev.2.20 (R01US0015E)

(The latest versions of the documents are available on the Renesas Electronics Website.)

Technical Updates/Technical Brochures

(The latest versions of the documents are available on the Renesas Electronics Website.)

Website and Support

Renesas Electronics Website

- <http://www.renesas.com/index.jsp>

Inquiries

- <http://www.renesas.com/contact/>

Revision Record	RL78/G10 Timer Array Unit Controlling Switched-Mode Power Supply with Dual Input One-Shot Pulse Output Function
------------------------	---

Rev.	Date	Description	
		Page	Summary
1.00	Nov. 9. 2015	—	First edition issued

The following usage notes are applicable to all MPU/MCU products from Renesas. For detailed usage notes on the products covered by this manual, refer to the relevant sections of the manual. If the descriptions under General Precautions in the Handling of MPU/MCU Products and in the body of the manual differ from each other, the description in the body of the manual takes precedence.

1. Handling of Unused Pins

- Handle unused pins in accord with the directions given under Handling of Unused Pins in the manual.
 - The input pins of CMOS products are generally in the high-impedance state. In operation with unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible. Unused pins should be handled as described under Handling of Unused Pins in the manual.

2. Processing at Power-on

- The state of the product is undefined at the moment when power is supplied.
 - The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the moment when power is supplied.
In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the moment when power is supplied until the reset process is completed.
In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the moment when power is supplied until the power reaches the level at which resetting has been specified.

3. Prohibition of Access to Reserved Addresses

- Access to reserved addresses is prohibited.
 - The reserved addresses are provided for the possible future expansion of functions. Do not access these addresses; the correct operation of LSI is not guaranteed if they are accessed.

4. Clock Signals

- After applying a reset, only release the reset line after the operating clock signal has become stable. When switching the clock signal during program execution, wait until the target clock signal has stabilized.
 - When the clock signal is generated with an external resonator (or from an external oscillator) during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Moreover, when switching to a clock signal produced with an external resonator (or by an external oscillator) while program execution is in progress, wait until the target clock signal is stable.

5. Differences between Products

- Before changing from one product to another, i.e. to one with a different part number, confirm that the change will not lead to problems.
 - The characteristics of MPU/MCU in the same group but having different part numbers may differ because of the differences in internal memory capacity and layout pattern. When changing to products of different part numbers, implement a system-evaluation test for each of the products.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product.
 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc.
Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics.
 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics products.
 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com>" for the latest and detailed information.

Renesas Electronics America Inc.

2801 Scott Boulevard Santa Clara, CA 95050-2549, U.S.A.
Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited

9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.
Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.

Room 1709, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100191, P.R.China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.

Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, P. R. China 200333
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited

Unit 1601-1611, 16/F, Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852-2886-9022

Renesas Electronics Taiwan Co., Ltd.

13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

Renesas Electronics Singapore Pte. Ltd.

80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn Bhd.

Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.

No 777C, 100 Feet Road, HALII Stage, Indiranagar, Bangalore, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.

12F., 234 Teheran-ro, Gangnam-Gu, Seoul, 135-080, Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5141