Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.

Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anticrime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majorityowned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



2006 · February

V850 Series Development Environment

The V850 Series development environment encompasses a range of tools designed to enable smoother, faster, and more precise development of application systems that employ NEC Electronics' original V850 Series of embedded RISC microcontrollers. Each tool is provided with functions that optimize the performance of the V850 Series.

Development Environment Background

The expanded scale of hardware and software in recent application systems has brought with it an increase in the level of complexity. Successful development in today's environment means being able to **easily expand and improve functions, and efficiently raise the performance of the system.** With its V850 Series, NEC Electronics now gives developers the opportunity to achieve this. To enable the development of systems that capitalize on the excellent features of these high-performance devices, NEC Electronics provides support in the following three key areas: reduced development time, improved system performance, and coordination with partners.

INDEX	
DEVELOPMENT ENVIRONMENT TOOL CHAIN	4
In-Circuit Emulator and On-Chip Debug Emulator Environment 4 ROM Emulator and Evaluation Board Environment 5	
SOFTWARE PACKAGE	6
SP850 6 COMPILERS 7 PROJECT MANAGER (PM+) 10 DEBUGGERS 12 SIMULATORS 14 PERFORMANCE ANALYSIS TUNING TOOL 15	
AUTO VERIFICATION SYSTEM	16
IN-CIRCUIT EMULATORS	18
IECUBE SERIES 18 G1 SERIES 21 MC SERIES 23	
ON-CHIP DEBUG EMULATORS	27
MINICUBE 27 N-WIRE EMULATOR 28	
REAL-TIME OS	30
RX850, RX850 Pro 30 OSEK/VDX SPECIFICATION-COMPLIANT OS 33 TASK DEBUGGERS (RD850/RD850 Pro) 34 SYSTEM PERFORMANCE ANALYZER 35	
MIDDLEWARE	37
NETWORK LIBRARY 37 FILE SYSTEM 39 HIGH-SPEED FLOATING-POINT LIBRARY 40	
REFERENCE PLATFORM	41
SolutionGear [®] 41	
/ DEVICE DRIVER CONFIGURATION TOOL	43
Applilet 43	
FLASH MEMORY PROGRAMMER	45
PG-FP4 45	
ORDERING INFORMATION	46
SOFTWARE TOOLS 46 HARDWARE TOOLS 48 IECUBE 48 G1 EMULATOR 51 MC EMULATOR 53 MINICUBE 59 N-WIRE EMULATOR 60 FLASH MEMORY PROGRAMMER 61 COMMON INTERFACE 63	
PARTNERS	64
OS 64 Prototype Model Design Tools, Test Tools 64 Compilers, Assemblers, Integrated Development Environments 65 Middleware 66 Flash Memory Programmer 71 Emulators 72 Evaluation Board, Evaluation Kits 76	
	79
Partner Contact Information Support in Japan 79 Support Outside of Japan 81 Rental Companies 83	
SUPPORT	84
SUPPORT SYSTEM 84 DEVELOPMENT TOOLS DOWNLOAD SERVICE (ODS) 85	

DEVELOPMENT ENVIRONMENT FOR V850 SERIES (1/2)

In-Circuit Emulator and On-Chip Debug Emulator Environment





ROM Emulator and Evaluation Board Environment



APPLI:	Application Corporation
ATI:	Accelerated Technology, Inc.
Cosmo:	Cosmo, Inc.
Red Hat:	Red Hat,Inc.
GAIO:	GAIO TECHNOLOGY CO., LTD.
GHS:	Green Hills Software, Inc.
KMC:	Kyoto Microcomputer Corporation

Metrowerks Corporation Midas Lab Co., Ltd. Midas Lab: Midoriya Electric Co., Ltd. MiSPO Co.,Ltd. Wind River Systems, Inc. Personal Media Corporation **NEC Electronics Corporation**

Midoriya:

Mispo: WRS:

PMC:

Others:

our creativity

SP850

The SP850 software package combines various V850 Series development tools and software products previously sold individually.

Package Contents

- ◆ C compiler package (CA850)
- Project manager (PM+)
- Integrated debugger (ID850, ID850NW)
- System simulator (SM850, SM+)
- Performance analysis tuning tool (TW850)

- ◆ Integrated development environment from language tools to debugger and analysis tools
- Simple installation using integrated installer
- Enhanced linking functions for development tools and software products
- Optimized object debugging with compiler
- High-speed simulation of peripheral function operation
- Program performance analysis and tuning
- Management of different versions of the same tool
- ◆ Sample program for development tool operation verification (with user's manual) included
- Timely version upgrade via development tools download service (ODS) as well as version upgrade via supply media





COMPILERS

The following compilers are supported in the V850 Series.

CA850: C compiler package for V850 Series

Features

- Complies with ANSI-C standard for C language programming
- Includes powerful optimization functions
- Provides functions optimized for embedded systems
- Provides multiple utilities

Powerful Optimization Functions

The CA850 comes with "powerful optimization functions" that make the most of the device's performance features. Users can select among six optimization levels, and can even set optimization levels for individual sources.



Functions Optimized for Embedded Systems

The CA850 provides functions optimized for development of the embedded systems.

○ Functions related to size reduction of ROM/RAM used and acceleration of execution speed

- Selection of register mode (software register bank function)
 - → Setting a limit on the number of registers that can be used by the compiler (either 22 or 26 registers) reduces the interrupt overhead (saving to and restoring from registers).
- Run-time library is used for processing of function prologues and epilogues
 - → Code size is reduced by library functions that can be called both when saving to registers and when restoring from registers (slightly accelerates execution speed).
- Structure/union packing function
 - → This packing function fills holes between members of structures or unions due to alignment, which reduces code size (slightly accelerates execution speed).
- Register allocation function for external variables
 - → When in 22 or 26 register mode, the user can freely allocate external variables to any usable register and can change the memory access to the register access. This can shrink the code size while accelerating execution speed.

○ Functions implemented via C language descriptions

- Data and variables can be allocated to specified memory areas.
- → Enables allocation of data and/or variables to memory areas that can be accessed at high speed
 ♦ Interrupt/exception handler processing can be coded in C language.
- → Register save/restore processing required in assembly code can be performed automatically by compiler
- Assembly code instructions can be inserted into C language source code.
- → Useful for partial, high-speed processing, etc.
- Access to peripheral I/O register can be handled as ordinary variable access.
- → Uses "device files" that contain definitions of peripheral I/O register names, interrupt request names, on-chip memory size, and other information
- ♦ Real-time OS (RX850, RX850 Pro) tasks can be coded
 → Reduces code not required for tasks

Accessory Utilities

The CA850 provides various utilities that can be used for development of embedded systems.

○ ROMization processor (romp850)

The initial values of variables must be set before running any applications when they are declared with initial values. The romp850 utility generates these initial values and the information to be copied. This ROMization processor's functions can also be used to generate information to be copied when ROM code is deployed to RAM before executing.

○ HEX converter (hx850)

This utility converts executable object files to a hexadecimal format. The following hexadecimal formats are supported.

- Intel expanded hex format
- Motorola S type format (standard address)
- Motorola S type format (32-bit address)
- Extended Tek hex format

○ Section file generator (sf850)

This utility allocates frequently used variables (among all variables used by an application) to an internal RAM area.

○ Dump command (dump850)

The dump command displays the contents of a specified object file or archive file in an easy-to-read format.

○ Disassembler (dis850)

This utility converts text-attribute data (program code) from object files or archive files into assembly language and displays the assembly language code.

\bigcirc Cross reference tool (cxref)

This utility outputs cross reference information, tag information, call tree information, function metrics (number of lines in function, function's call frequency, etc.), and call data base (function call information).

○ Memory layout visualization tool (rammap)

This utility displays a visualization of variable allocation information.



\bigcirc Link directive generator (LDG)

This utility can be used to generate (via the GUI) "link directive files" that specify the section allocation order, addresses, etc.

Memories	Sections	Files		Symbols	Item	Value
x0000 0000 ternalROM	0×0000 0000		? ep_D		Section N Previous Start Add	None ?
98304 bytes	1040 bytes 0x0000 040f				End Address Size	? ? bytes
	+ 0x0000 0410				Access Type	Instruction
	+SCONST				Section T Align	With Initial Value 4 bytes
	201003				Input Sec	
	? bytes				Object File	
	?				Comment	
	17					
	TEXT					
	7 bytes					
	(t)					
	system 7 bytes		1			
	- Dytes					
	17					
	the second s		N.			
	.system_cmn		_			
	? bytes		11			
	7		11			
	17		1			
	.system_int		7			
	? bytes		tp_T	EXT		
	7		N-			
	+ 2		//	-		
				•		

○ Stack usage tracer (stk850)

This utility statically estimates the stack size used by sets of functions within a project. Estimations can also be performed as the real-time OS task (RX850, RX850 Pro).

ile Yiew Option Help						
TENNI InitTask	Function	Total Stack	Frame Size	Additional	File	
WCRMDTask (ext_sk) (dy_tsk) (dy_tsk) (dy_tsk) (wm_char_set (wm_char_set (wm_char_set (wm_char) (wm_ch	OutAddress	60 44	16 44	Autoria	C:VsampleVsrcWwmfuncs.c C:VsampleVsrcWwmfuncs.c	
	C:¥Program Files¥N	¥reset.s Reading ¥varfunc.s Reading ¥varfunc.s Reading ¥vmrfuncs.s Reading ¥mrfuncs.s Reading ¥def_sio.s Reading ¥def_sio.s Reading IEC Electronics Too IEC Electronics Too	mpleted. completed. g g completed. is#STK850# V2 is#STK850# V2	10 ¥dat850¥lit	bsize321xt Reading . bsize321xt Reading completed. d650porsystal Uk Reading completed.	

PROJECT MANAGER (PM+)

The project manager enables more efficient development by integrating tools such as a C compiler and debugger.

Features

- Enables editing, build, and debugging, as a series of operations
- Includes an editor function
 Includes a smart look-up function that provides a short-cut for coding function names and task names
- Menus and tool bars can be customized



Maximum Length Block/Record(b) Offset of Output Address(-d)

OK Cencel

-cpu 3101 -D C \aample\unc\link a

Edt.

Help

(0)m

cpu 3101 - Vince50

-cpu 3101 4 . Vincetto 4 C

DK Cancel

Apple



Enables management of source code and documents as well as version management using CVS. Multiple projects can be managed in the same work space.



Wizards can be used to create projects

Wizard screens provide an easier way to register target device names and required source files, to specify whether or not a real-time OS will be used, and to set startup routines or link directive files.



our creativity

DEBUGGERS

The following debuggers are available.

ID850: C source debugger for V850 Series (supporting MC series and G1 series) ID850NW: C source debugger for V850 Series (supporting the N-Wire emulator) ID850QB: C source debugger for V850 Series (supporting MINICUBE and IECUBE)

Features

- Source can be debugged.
 Source program in C and assembly language can be debugged.
- Wealth of debug functions

By using the event functions of an in-circuit emulator (IE), break, trace, and time measurement, and coverage measurement can be executed.

In addition, basic debugging such as break and run-break time measurement can be executed also for on-chip debugging (OCD) by using the event functions of the debug control unit (DCU).

- Saving debugging environments
 Debugging environments such as information on setting of breakpoints and events, downloading of files, and display status of windows can be saved as a project file.

 By loading this project file, the debugging environments can be restored.
- Function expansion by Tcl Batch processing and hook processing on the command line and creating user's original custom windows can be performed by using Tcl/Tk (Tool Command Language).
- Function expansion by TIP or ToolLink

By using a task debugger (RD) and system performance analyzer (AZ) supporting TIP (Tool Interface Protocol) or ToolLink, debugging efficiency of a user program using a real-time OS (RX) can be dramatically enhanced.

	The Source		_	1-1-1-1					15 10 R	_	_	_	_	- 0 >
ET ant	Search		Watch	Quick	Betreah	Dose	1		Behesh	DMM.	Close			
B→By crtE s →B _=crtE0000 B→By MainC →B tunc1 →B tunc2 →B tunc3 tunc3		93) 94 95 voi 96 (97 98 99 100)	TH	ACE = 0	ltimer_of ; = Øx47;	FO	-	×	Name PDL PDLL PDLH PNDL PMDLL PMDLH	Ambule R/V 16 R/V 1, R/V 1, R/V 1, R/V 1, R/V 1,	8	Value 0 4000 0 00 0 40 0 FFFF 0 FF 0 FF		1
B tunc_intervatir B intone_intervatir B intoneo	B * Ti	101 102 i 103 104 105 106 107 i 108 (109 110	nterrup	t void	intdna@ <v inttn8eq8 000064</v 				VSWC DSA0L DSA0H DDA0L DSA1L DSA1L DDA1L DDA1L	R/W 8 R/W 16 R/W 16 R/W 16 R/W 16 R/W 16 R/W 16 R/W 16 R/W 16 R/W 16		0 77 0 0D80 0 0280 0 2029 0 0280 0 4848 0 0818 0 E833 0 0048		
Timer - Timer 1	Ti	111 112 113 114 114		turr	Move Mix Add Watch Symbol Break when Aci	cess to this	: Variable	- -	DSA2L DSA2H DDA2L DDA2H DSA3L DSA3L	R/W 16 R/W 16 R/W 16 R/W 16 R/W 16 R/W 16		086F8 003D1 00000 00000 00000		-
Pass: 1 time[s] Total: 1000279360 nsec Average: 1000279360 nsec Max: 1000279360 nsec Min: 1000279360 nsec		Average: 10001 Max: 10001	940 nsec	1	Break when Wr Break when Re Clear Event ?			Delete Del	Add timer test_i *data_d		Up	?	FFFC11	
Initialize Copy Close Search <	Help Watch	20564	resh Lk	Hel I	Come Here Change PC Break Point Software Break	Point		« »	Rebesh	DMM.	Close	×		
- 000007AE - 000007B0 - 000007B2	dno0	1002 0002 85fd 5015 630f0 230f0 818f2 230f0 e1872	100	st br 1d 1d	Assemble Memory d -0x4 sp .v r1, 0x1 _intdma0- .v 0x0[sp] sr r1, 0x1 .v 0x4[sp] sr r1, 0x1	0x24 1. r1 1. 1. r1	OFFFCDCC OFFFCDCO OFFFCDCO OFFFC100 OFFFC120 OFFFC120 OFFFC130	+0 +1 +2 - 87 F4 98 49 E0 23 - 04 80 B8 - 46 91 C4 - 00 00 00 64 00 00	+3 +4 + 99 96 0 50 D3 E CA 89 9 30 25 0 00 08 0 00 00 0	5 +6 +7 A CF 41 C 8F 17 A 38 60 18 60 CC 1 FF 0F 0 00 00 0 00 00	+8 +9 86 49 DE CB 03 62 76 55 00 00 02 00	0A 81 FF 5C 6E 10	+C +D 59 53 BC 81 CF D5 BD E7 00 00 04 00 0C 00	63 4F 30 6C D7 56 00 0C



Debugger Usage Environment

		In-Circuit Emula	tor or On-Chip Debug Emulator	
Target Device	Debugger	Main Unit	Emulation Board or Option Board	Host Machine
V850ES/SG2, V850ES/SJ2	ID850QB	QB-V850ESSX2-ZZZ	_	PC 9800 series
V850E/IA3, V850E/IA4, V850ES/IK1		QB-V850EIA4-ZZZ	-	IBM PC/AT or compatible
V850ES/KE1, V850ES/KE1+, V850ES/KF1, V850ES/KF1+, V850ES/KG1, V850ES/KG1+, V850ES/KJ1, V850ES/KJ1+	•	QB-V850ESKX1H-ZZZ	-	
V850ES/FE2, V850ES/FF2, V850ES/FG2, V850ES/FJ2, μPD703229Y, μPD70F3229Y		QB-V850ESFX2-ZZZ		
V850E/ME2, V850E/MA3, V850E/IA4, V850E/SV2, V850ES/SG2, V850ES/SJ2, V850ES/FE2, V850ES/FF2, V850ES/FG2, V850ES/FJ2, μPD70F3229, V850ES/KJ1+, V850ES/KJ1		QB-V850MINI		
V850ES/SA2, V850ES/SA3	ID850	IE-V850ES-G1	IE-703204-G1-EM1	
V850ES/KF1, V850ES/KG1, V850ES/KJ1			IE-703217-G1-EM1	
V850ES/SG2, V850ES/SJ2	1		IE-703288-G1-EM1	
V850ES/PM1			IE-703228-G1-EM1	1
V850ES/FE2, V850ES/FF2, V850ES/FG2, V850ES/FJ2, μPD703229Y, μPD70F3229Y			IE-703239-G1-EM1	
V850ES/ST2			IE-703220-G1-EM1	1
V850E/SV2		IE-V850-MC-A	IE-703166-MC-EM1	1
V850E/MA1, V850E/MA2			IE-703107-MC-EM1	1
V850E/IA1		IE-V850E-MC	IE-703116-MC-EM1	
V850E/IA2			IE-703114-MC-EM1	1
V850E/MS1(5V), V850E/MS2(5V)		IE-703102-MC	IE-703102-MC-EM1	1
V850E/MS1(3.3V)			IE-703102-MC-EM1-A	1
V850/SA1	1	IE-703002-MC	IE-703017-MC-EM1	1
V850/SB1, V850/SB2	1		IE-703037-MC-EM1	1
V850/SV1	1		IE-703040-MC-EM1	1
V850/SF1	1		IE-703079-MC-EM1	1
V850/SC1, V850/SC2, V850/SC3			IE-703089-MC-EM1	
V853	1		IE-703003-MC-EM1	1
V850E/ME2	ID850NW	RTE-2000-TP	_	1
V850E/MA3	1		KIT-V850E/MA3-IE	1
NB85ET	1	IE-70000-MC-NW-A		1

Manufactured by Midas Lab Co., Ltd.

 Inquiries to:
 Naito Densei Machida Mfg. Co., Ltd.
 (Tel: 81-45-475-4191)

 CORE Corporation
 (Tel: 81-3-3795-5171)

 Application Corporation
 (Tel: 81-42-732-1377)

SIMULATORS

The following simulators are available.

	Instruction + peripheral simulator for V850ES/SG1, V850ES/SG2, and V850ES/SJ2 Instruction + peripheral simulator for V850ES/FE2, V850ES/FF2, V850ES/FG2, and V850ES/FJ2
SM+ for V850: SM850:	Instruction simulator for V850E and V850ES Series Instruction + peripheral simulator for V853, V850/SA1, V850/SB1, V850/SB2, V850/SF1, V850E/MS1, V850E/MA1, V850E/IA1, V850E/IA2, V850ES/SA2, V850ES/SA3, V850ES/KF1, V850ES/KG1, V850ES/KJ1, V850/SC1, V850/SC2, V850/SC3

Instruction + peripheral simulators: Can simulate instruction execution by the CPU and internal peripheral functions such as timers and UART.

Instruction simulators: Can simulate only instruction execution by the CPU.

Features

◆ Target-less evaluation

Microcontroller operations, including the operations of the on-chip peripheral units and interrupt servicing, in addition to the operation of the CPU, can be simulated.

Programs can be debugged in an early stage without an in-circuit emulator.

- ◆ Same operability as debuggers for V850 Series
- Various simulation functions

System debugging on PC (I/O panel window)
 Dummy target systems can be organized by placing buttons and LEDs.
 Panels having the same operability as Microsoft PowerPoint can be created.



• Monitoring I/O waveform of microcontroller (timing chart window) Waveforms can be monitored in an oscilloscope-like image.



• Simulation of serial transmission/reception (serial window) Transmits serial data to the microcontroller and displays reception of serial data from the microcontroller.





PERFORMANCE ANALYSIS TUNING TOOL

The following performance analysis tuning tool is supported by the V850 Series.

TW850: Tuning tool for V850 Series

The TW850 performance analysis tuning tool is a tuning tool for embedded software.

It enables performance estimation, performance prediction, and performance improvement through easy operation. The TW850 tool can also be used for the V850E with on-chip cache and other system LSI devices.

- Easy-to-use interface
 The wizard-type GUI allows easy specification of conditions. Moreover, profiling, performance analysis, and tuning are automatically performed.
- Profiling function Two profiling approaches are available, one in which trace data is analyzed during execution using the in-circuit emulator trace function, and another in which software analysis is performed by inserting probe code into the target program.
- Performance estimation
 Performance analysis changing the internal ROM size, instruction cache size, etc. is possible, and the analysis results can also be used for microcontroller selection.
- Analysis result output function
 - The following analysis results are output.
 - · Interfunction call relations, call count information
 - · Function execution time information
 - · Cache miss-hit information
- Performance tuning function
 - The following types of tuning can be performed.
 - · Instruction cache optimization
 - (Optimum placement of functions so as to reduce cache miss-hits)
 - · High-speed access memory allocation optimization
 - (Allocation of functions that constitute bottlenecks to high-speed access memory such as internal ROM)



The following auto verification systems are supported in the V850 Series.

XO850: Auto verification system for V850 Series

XO850 is an auto verification system for the V850 Series.

At the test process (the final process in software development), this system performs auto execution and auto evaluation using the actual target hardware, providing support for test automation.

Features

- Improved execution of tedious repetitive and regression tests
 Full testing after each software revision is tedious and time-consuming. Test automation enables regression tests to be performed more easily, for improved software quality.
- Executes tests that are too complex or too large to be executed manually.
 With the advent of ever more complex software, an increasing number of tests are endurance tests or other tests too complex for manual operation. Test scripts can be used to enable implementation of abnormality-related tests or other complex tests, and it saves time when implementing very large tests.

Facilitates reproduction of abnormalities When an abnormality is discovered, it is often difficult to remember the execution steps that preceded the abnormality. Test automation includes recording these execution steps, which facilitates and helps ensure accuracy when reproducing the abnormality.

Configuration

Tests are performed using a host machine connected to the target system.

The XO850 Test Manager, which is installed in the host machine, manages the tests by executing the tests, gathering the test results, automatically comparing the test results to the expected values, etc.







Functions

- Support for creating test scenarios
 - Auto generation of test scenarios from virtual target's operations
 - Auto generation of test scenarios from actual device's operations
- Auto execution of test scenarios
 - Enables execution of multiple test iterations or multiple consecutive test scenarios
 - Enables execution of test scenarios concurrent with condition judgments
- Auto comparison of execution results and expected values
 - When execution of test scenario ends, the pass/fail results are automatically displayed in a readable format.
 - Displays a report describing the execution conditions for all test scenarios
- Use of upstream resources
 - Verification logs from design stages can be used to make test script generation more efficient.
 - Analysis of abnormalities found during testing is facilitated by links to a status transition table.
 - Coverage can be viewed at the status transition table level, enabling confirmation of a test's coverage.

Use Conditions

Load module

The load module is generated by the V850 Series' C compiler package (CA850). The RX850 and RX850 Pro real-time operating systems for the V850 Series are also supported when the real-time OS is used.

Communication tools

One of the following is required for communications between the host machine and the target device.

- One serial communication channel for the device
- An in-circuit emulator (IE-703002-MC, IE-703102-MC, IE-V850E-MC, IE-V850E-MC-A, IE-V850ES-G1, or QB-V850ESSX2)

IECUBE SERIES

The following IECUBE series in-circuit emulators are supported in the V850 Series.

QB-V850EIA4:	In-circuit emulator for V850ES/IK1, V850E/IA3, or V850E/IA4
QB-V850ESSX2:	In-circuit emulator for V850ES/SG2 or V850ES/SJ2
QB-V850ESKX1H	: In-circuit emulator for V850ES/KE1, V850ES/KE1+, V850ES/KF1, V850ES/KF1+,
	V850ES/KG1, V850ES/KG1+, V850ES/KJ1, or V850ES/KJ1+
QB-V850ESFX2:	In-circuit emulator for V850ES/FE2, V850ES/FF2, V850ES/FG2, V850ES/FJ2, or
	μPD703229



- ◆ Low price
 - Price of 1/3 to 1/4 of the existing high-performance emulators
 - Debugger "ID850QB" and simple programmer "PG-FPL" are available as a package.
- Easy setup
 - Emulator and emulation board, which have conventionally been available separately, are combined.
 - USB (1.1/2.0) is employed for communication with the host machine.
- Many debugging functions
 - Functions equivalent to a high-performance emulator are realized (coverage and external memory emulation are optional).
 - Time measurement function as well as real-time monitor and RAM monitor functions that are frequently used are reinforced.
- Reinforced maintainability
 - Self-diagnostic function is provided to smoothly solve troubles.
- Small and lightweight
 - Palm size for easy transportation









IECUBE optional functions

The following functions are optionally available. They can be added by specifying an option when placing your order or by upgrading your IECUBE.

Memory emulation function

This function substitutes the external memory on the target system so that programs and data can be located in emulation memory and debugged.

Coverage measurement function

Percentage of executing load modules and sections can be measured.

TimeMachine[™] function

This function is supported by a Green Hills Software (GHS) debugger. Consult a GHS tool distributor for the outline and specifications of this function.

PG-FPL

The PG-FPL is a simple programmer that is supplied with IECUBE.

- Connects to a PC (via USB 1.1 or 2.0 cable), AC adapter not required.
- ◆ Write is also enabled via UART in the target device.
- Status display LEDs: power ON (green LED lit) and communication online (red LED blinking) display lamps
- Connection to target system selectable: via PG-FP4's connector or a direct connection
- ◆ Able to supply power to the target system (up to 200 mA)
- Not able to supply clock to the target system
- Evaluation programmer for development (conditionally guaranteed for use with mass production)
- Target devices: Any device supported by IECUBE (except flash memory versions that use two power supplies)





Socket for IECUBE



① Extension probe (S and T types) (option) Connecting IECUBE to target system with probe



② Exchange adapter Adapter whose pins need to be converted, depending on the product



Adapter for monitoring waveform



④ Space adapter (option) Adapter for adjusting height



to be converted, depending on the product

Adapter whose pins need

⑦ Exchange adapter

Connections

When Connecting to IECUBE						
S Type	Т Туре					
IECUBE						
1						
2	Ø					
3						
4	8					
	9					
6	0					
Target	System					

When Mounti	ng on Device				
S Type	Т Туре				
⑤(top)	10				
Device					
⑤(bottom)	_				
6	0				
Target	System				



height

 Space adapter (option)
 Adapter for adjusting

9 YQ adapter Adapter for connecting IECUBE



⑥ Target connector Connector soldered onto the target system

S-type socket

⑤ Mount adapter (option) Adapter for mounting device (cover and unit)



Mount adapter (option) Adapter for mounting onto device



① Target connector Connector to be soldered onto the target system

T-type socket

Remark The YQ adapter (T type) includes guide screws (YQGUIDE-S3).

- The exchange adapter (S type) differs according to the G1 emulator.
- A check pin adapter that can be used with both T type and S type is currently under development.
 - The following products are identical (except 64-pin products).
 - · Check pin adapter (S type) and check pin adapter for G1 emulator
- Space adapter (S type) and space adapter for G1 emulator
 Mount adapter (S type) and mount adapter for G1 emulator
 Target connector (S type) and target connector for G1 emulator
 Space adapter (T type) and YQSOCKET for MC emulator

- YQ adapter (T type) and YQPACK for MC emulator Mount adapter (T type) and HQPACK for MC emulator
- · Target connector (T type) and HQPACK for MC emulator



G1 SERIES

The following products are G1 series in-circuit emulators for V850 Series.

IE-V850ES-G1: In-circuit emulator for V850ES
IE-703204-G1-EM1: In-circuit emulator emulation board for V850ES/SA2 and V850ES/SA3
IE-703288-G1-EM1: In-circuit emulator emulation board for V850ES/SG2 and V850ES/SJ2
IE-703228-G1-EM1: In-circuit emulator emulation board for V850ES/PM1
IE-703239-G1-EM1: In-circuit emulator emulation board for V850ES/FE2, V850ES/FF2, V850ES/
FG2, V850ES/FJ2, μPD703229Y
IE-703220-G1-EM1: In-circuit emulator emulation board for V850ES/ST2



- ◆ Attains a high approximation of an actual device by integrating emulator functions on a dedicated chip.
- Provides many debugging functions such as break, trace, coverage measurement, external memory emulation, and real-time RAM monitoring.
- Extension probe supplied as standard makes connection with the target system easy.
- Internal power supply and easy-to-carry housing
- Connectable to various types of computers.



Socket for G1 Emulator



② Exchange adapter Adapter whose pins need to be converted, depending on the product



④ Check pin adapter (option) Adapter for monitoring waveform



(5) Space adapter (option) Adapter for adjusting height



Connections

When Connecting to Emulator	When Mounting on Device
Emulator	3 (top)
2	Device
4	3 (bottom)
5	1
1	Target system
Target system	



③ Mount adapter (cover and unit) Adapter for mounting onto device



① Target connector Connector to be soldered onto the target system

Remark The exchange adapter differs from the exchange adapter for IECUBE (S type). The following products are identical, although the product names are not the same (except 64-pin prod-

- ucts)
 - · Check pin adapter and check pin adapter for IECUBE (S type)
- Space adapter and space adapter for IECUBE (S type)
 Mount adapter and mount adapter for IECUBE (S type)
- Target connector and target connector for IECUBE (S type)



MC SERIES

The following products are MC series in-circuit emulators for V850 Series.

IE-703002-MC: In-circuit emulator for V85x, V850/Sxx
IE-703003-MC-EM1: In-circuit emulator option board for V853
IE-703017-MC-EM1: In-circuit emulator option board for V850/SA1
IE-703037-MC-EM1: In-circuit emulator option board for V850/SB1, V850/SB2
IE-703040-MC-EM1: In-circuit emulator option board for V850/SV1
IE-703079-MC-EM1: In-circuit emulator option board for V850/SF1
IE-703089-MC-EM1: In-circuit emulator option board for V850/SC1, V850/SC2, V850/SC3
IE-703102-MC: In-circuit emulator for V850E/MS1, V850E/MS2
IE-703102-MC-EM1: In-circuit emulator option board for V850E/MS1, V850E/MS2 (5 V type)
IE-703102-MC-EM1-A: In-circuit emulator option board for V850E/MS1 (3.3 V type)
IE-V850E-MC: In-circuit emulator for V850E (5 V type)
IE-703116-MC-EM1: In-circuit emulator option board for V850E/IA1
IE-703114-MC-EM1: In-circuit emulator option board for V850E/IA2
IE-V850E-MC-A: In-circuit emulator for V850E (3.3 V type)
IE-703166-MC-EM1: In-circuit emulator option board for V850E/SV2
IE-703107-MC-EM1: In-circuit emulator option board for V850E/MA1, V850E/MA2
IE-V850E-MC-EM1-A: In-circuit emulator core adapter for NB85E core (2.5 V type)
IE-V850E-MC-EM1-B: In-circuit emulator core adapter for NB85E core (3.3 V type)



- Integration of conventional emulator functions in a single chip enables considerable penetrability
- Rich variety of emulator functions
- High-speed operation equivalent to the target device
- Connectable to a variety of PCs







3 CSICE

Socket for emulator connection

② LSPACK^{Note} Pogo pin connector

 CSSOCKET CSP socket for connection to target system

Connections

When Connecting to Emulator	When Mounting on Device
Emulator	Cover for mounting on device
YQGUIDE	Spacer for mounting on device
3	Device
2	2
1	0
Target system	Target system

Note LSPACK is provided with the cover for mounting on a device and the spacer for mounting on a device.

Socket for MC Emulator (V850/SA1, V850E/MS1 BGA Package)



Cover for mounting on device (provided with CSPACK)

Spacer for mounting on device (provided with CSPACK)

② CSICE Socket for emulator connection (The actual color is different)

① CSPACK
 Socket for target connection

Connections

When Connecting to Emulator	When Mounting on Device
Emulator	Cover for mounting on device
YQGUIDE	Spacer for mounting on device
2	Device
1	1
Target system	Target system

Empower

your creativity

		In-Circuit Emulator					
		QB-V850XXX (IECUBE)	IE-703002-MC	IE-703102-MC	IE-V850E-MC IE-V850E-MC-A	IE-V850ES-G1	
Maximum operat	ing frequency		Ec	uivalent to target devi	ice		
Emulation momony	Internal ROM	1 MB	512 KB		1 M	1 MB	
Emulation memory capacity	Internal RAM	60 KB	28 KB 60 KB				
сараску	External memory	16 MB (optional)	1 MB 2 MB 4 MB (disabled for 8-bit bus width) (disabled for 8-bit bus width)				
Event function	Execution events	10	14				
Event function	Access events	6		8	3		
Hardware break 16 Software 2000		16	22				
		100					
	Forcible break	Enabled					
	Step execution	Enabled					
File safe brea		Enabled					
Trace function	Trace memory capacity	256K frames	32K frames				
	Trace items	Branch, access, timestamp, interpolation function	Instruction execution, timestamp, access				
	Program execution (start - end) measuring			Enabled	Enabled		
Time measuring	Inter-event measuring	Enabled (8)	Enabled (3)				
function	Display items of inter-event measuring result	Total value, pass count, maximum value, minimum value, average value	e, Total value				
	Timeout break	Enabled	Disabled				
Real-time RAM	Number of points	8	1				
monitor function	Maximum capacity	2 KB	1 KB				
	Memory capacity	Internal ROM space		1 N			
Coverage function	Execution coverage	+ any 1 MB space		Enat			
Maskable	Access coverage e pins	(optional)	Disabled Enabled Disabled RESET, WAIT, HLDRQ, NMI, STOP RESET, N		bled RESET, NMI, STC		
PC interface		USB2.0, USB1.1	PCI, PCMCIA network PCI, PCMCIA				



MINICUBE

The following products are on-chip debug emulator MINICUBE for V850 Series.

QB-V850MINI: On-chip debug emulator for V850E1 and V850ES Supported devices as of October 2005. V850E/MA3, V850E/ME2, V850E/IA4, V850E/SV2, V850E/RS1 V850ES/SG2, V850ES/SJ2, V850ES/KJ1, V850ES/KJ1+, V850ES/FE2, V850ES/FF2, V850ES/FG2, V850ES/FJ2 μPD70F3229Y

Features

- Low price
 Price 1/20 of the existing high-performance emulator and debugger "ID850QB" also available in same package
- Easy setup USB (1.1/2.0) is employed for communication with the host machine. No power supply is necessary.
- Can write to on-chip flash memory.
 Evaluation can be started right away even if a flash memory programmer is not at hand.
- Debugging in in-circuit mode Supports debugging of V850ES/KE1(+), V850ES/KF1(+), and V850ES/KG1(+) that are not equipped with a debug unit, by using the self-check board supplied as an accessory.

- Reinforced maintainability Self-diagnosis using the self-check board supplied as an accessory for smoothly solving problems
- Small and lightweight
 Pocket-size for easy transportation



System configuration

N-WIRE EMULATOR

The following product is an on-chip debug emulator N-Wire emulator for V850 Series.

IE-70000-MC-NW-A: N-Wire emulator for Nx85ET

- ◆ Ideal development environment for NB85ET and NU85ET core
- On-board debugging is possible when the target system has wiring and a connector for debugging.
- Supports high-speed operation in excess of 66 MHz
- ◆ ID850NW with identical operability to SM850 and ID850
- ◆ Includes internal ROM and RAM so user's resources are not utilized



IE-70000-MC-NW-A



On-Chip Debug Emulator Functions

		On-Chip Deb	bug Emulator	
		QB-V850MINI (MINICUBE)	IE-70000-MC-NW-A	
Maximum operating frequency		Equivalent to target device	Equivalent to target device (minimum operation frequency is 2 MHz)	
	Internal ROM	On-chip target device Flash ROM capacity	None	
Emulation memory	Internal RAM	Target device's inte	ernal RAM capacity	
capacity	External memory	None	Optional 2 MB × 2 banks	
—	Execution events		8 (2 access alternate-function pins)	
Event function	Access events	2 execution/access alternate-function pins	4 (2 execution alternate-function pins)	
	Hardware break	2	14	
	Software	2000 (only number of ROM correction	100	
Break function	break	channels of target device can be set to internal ROM)	(Setting to internal ROM is disabled)	
Dreak fullction	Forcible break	Enabled		
	Step execution	Enabled		
	File safe break	Disabled		
	Trace memory		2M frames	
	capacity			
Trace function	Trace items	No trace functions	Branch, access,	
			timestamp,	
			interpolation function	
	Program execution			
	(start - end)	(disabled for V850E/ME2, V850E/SV2)		
	measuring			
Time measuring	Inter-event measuring			
function	Display items			
	of inter-event		Disabled	
	measuring result	Disabled	Disabled	
	Timeout break	DISADIEU		
Real-time RAM	Number of points			
monitor function	nitor function Maximum capacity			
	Memory capacity	None		
Coverage function	Execution coverage			
	Access coverage			
Maskable	e pins	RESET, WAIT, H	LDRQ, NMI, STOP	
PC inter	face	USB2.0, USB1.1	PCI, PCMCIA, network	

RX850, RX850 Pro

The following real-time OSs are supported in the V850 Series.

RX850:Real-time OS for V850 SeriesRX850 Pro: Real-time OS for V850 Series

Why is a real-time OS needed?

With the recent advances in the performance and functionality of microcontrollers, not only have the systems to be developed become more complex, but also the quantity of the programs to be executed by these systems has increased. Because systems in the field of control equipment in particular are required to respond immediately to changes in external and internal events, many problems that cannot be solved by conventional interrupt servicing have arisen; hence the development of the real-time OS.

The real-time OS is designed to react promptly to event changes and interrupts and manages multiple processing programs by dividing them into task units, which are then executed in the optimal order.



Real-time OS advantages

<For designing>

- Facilitates creation of application modules
- ◆ Software development can be focused solely on the application
- Management of program in task units
- Tasks can be set individually by prescribing an inter-task communication mode

<For debugging>

- Discrete task debugging enables multiple operators to debug simultaneously
- Only inter-task communication and synchronization testing are required for integrated debugging
- <For program maintenance>
- Specification changes and function additions can be executed in task units, reducing the effect on the system as a whole
- Because the program consists of task units:
 - → The internal structure is simplified, resulting in greater program legibility
 - → The program can be reused in task units, even in other systems

The V850 Series real-time OSs have been designed as the natural successors of the 16-bit V Series and 78K Series real-time OSs. They offer the following high-performance environment.

- Compliance with industry standards (ITRON, μITRON specifications)
- Support for power management functions
- Capability to embed required functions only (selection of system calls to be used)
- Advanced task development support through task debugger (RD)
- Application operational analysis support through system performance analyzer (AZ)

Real-Time OS	Specification	Performa	ince	Description
RX850	μITRON3	[Conditions] · V853 (25 MHz) · Program: Internal ROM · Data/stack: Internal RAM • Maximum interrupt disable time • Task switching time: • Code size:	2: 7 μs 11 μs (wup_tsk) 3 to 7 KB	This OS is easy to port from the 78 K Series. It has a compact design to enable operation from the on-chip ROM and RAM of the V850.
RX850 Pro	µITRON3	[Conditions] · V850E/MA1 (50 MHz) · Program: External ROM (external bus width: · Data/stack: Internal RAM • Maximum interrupt disable time • Task switching time: • Code size:	. ,	This is the RX850 OS but with enhanced functions.



System	Call	List	(1/2)
O yotom	oun	LIUU	(<i>''_)</i>

Control Module	System Call	Description	RX850	RX850 Pro
Task management	cre_tsk	Creates a task		V
	del_tsk	Deletes a task	_	\checkmark
	sta_tsk	Activates a task	\checkmark	\checkmark
	ext_tsk	Terminates this task	\checkmark	\checkmark
	exd_tsk	Terminates and deletes this task	_	\checkmark
	ter_tsk	Forcibly terminates another task	\checkmark	\checkmark
	dis_dsp	Disables dispatch	\checkmark	\checkmark
	ena_dsp	Enables dispatch	\checkmark	\checkmark
	chg_pri	Changes the priority level of a task	\checkmark	\checkmark
	rot_rdq	Rotates a ready queue of a task	\checkmark	\checkmark
	rel_wai	Forcibly releases a task from waiting	\checkmark	\checkmark
	get_tid	Obtains the ID number of this task	\checkmark	\checkmark
	ref_tsk	Obtains task information	\checkmark	\checkmark
	vget_tid	Obtains the ID number of a task	_	\checkmark
Task-associated	sus_tsk	Places a task in the suspended state		V
synchronous	rsm_tsk	Resumes operation of a task in the suspended state	\checkmark	\checkmark
management	frsm_tsk	Forcibly resumes operation of a task in the suspended state	\checkmark	\checkmark
	slp_tsk	Places this task in the wakeup waiting state	\checkmark	\checkmark
	tslp_tsk	Places this task in wakeup waiting state (with timeout)	\checkmark	\checkmark
	wup_tsk	Wakes up a task	\checkmark	\checkmark
	can_wup	Invalidates a wakeup request	\checkmark	\checkmark
Synchronous	cre_sem	Creates a semaphore	_	√
communication	del_sem	Deletes a semaphore	—	\checkmark
management	sig_sem	Returns a resource	\checkmark	\checkmark
	wai_sem	Acquires a resource	\checkmark	\checkmark
	preq_sem	Acquires a resource (polling)	\checkmark	\checkmark
	twai_sem	Acquires a resource (with timeout)	\checkmark	\checkmark
	ref_sem	Obtains semaphore information	\checkmark	\checkmark
	vget_sid	Obtains the ID number of a semaphore	_	\checkmark
	cre_flg	Creates an event flag	_	\checkmark
	del_flg	Deletes an event flag	_	\checkmark
	set_flg	Sets a bit pattern	\checkmark	\checkmark
	clr_flg	Clears a bit pattern	\checkmark	\checkmark
	wai_flg	Checks a bit pattern	\checkmark	\checkmark
	pol_flg	Checks a bit pattern (polling)	\checkmark	\checkmark
	twai_flg	Checks a bit pattern (with timeout)	\checkmark	\checkmark
	ref_flg	Obtains event flag information	\checkmark	\checkmark
	vget_fid	Obtains the ID number of an event flag	—	\checkmark
	vset_flg1	Sets a bit pattern (1-bit event flag)	\checkmark	Note

Note System calls related to event flags are supported.

Control Module	System Call	Description	RX850	RX850 Pro
Obtains version	ins version vclr_flg1 Clears a bit pattern (1-bit event flag)		V	Note
nformation	vwai_flg1	Checks a bit pattern (1-bit event flag)		Note
	vpol_flg1	Checks a bit pattern (1-bit event flag, polling)	\checkmark	Note
	vtwai_flg1	Checks a bit pattern (1-bit event flag, with timeout)	\checkmark	Note
	vref_flg1	Obtains 1-bit event flag information	\checkmark	Note
	cre_mbx	Creates a mailbox	—	\checkmark
	del_mbx	Deletes a mailbox	—	\checkmark
	snd_msg	Sends a message	\checkmark	\checkmark
	rcv_msg	Receives a message	\checkmark	\checkmark
	prcv_msg	Receives a message (polling)	\checkmark	\checkmark
	trcv_msg	Receives a message (with timeout)		\checkmark
	ref_mbx	Obtains mailbox information		\checkmark
	vget_mid	Obtains the ID number of a mailbox	—	\checkmark
nterrupt manage-	def_int	Registers/cancels an indirectly started interrupt handler		\checkmark
ment	ret_int	Returns from a directly started interrupt handler	\checkmark	\checkmark
	ret_wup	Returns from waking up another task and a directly	\checkmark	\checkmark
		started interrupt handler		
	loc_cpu	Acknowledges a maskable interrupt and disables	\checkmark	\checkmark
		dispatch processing		
	unl_cpu	Acknowledges a maskable interrupt and enables	\checkmark	\checkmark
		dispatch processing		
	dis_int	Disables maskable interrupt acknowledgement	\checkmark	\checkmark
	ena_int	Enables maskable interrupt acknowledgement	\checkmark	\checkmark
	chg_icr	Changes the interrupt control register contents	\checkmark	\checkmark
	ref_icr	Obtains the interrupt control register contents	\checkmark	\checkmark
Memory pool	cre_mpl	Creates a variable-length memory pool	_	
nanagement	del_mpl	Deletes a variable-length memory pool	_	\checkmark
	get_blk	Obtains a variable-length memory block		\checkmark
	pget_blk	Obtains a variable-length memory block (polling)		\checkmark
	tget_blk	Obtains a variable-length memory block (with timeout)		\checkmark
	rel_blk	Releases a variable-length memory block		\checkmark
	ref_mpl	Obtains variable-length memory pool information	V	\checkmark
	vget_pid	Obtains the ID number of a variable-length memory pool		\checkmark
	get_blf	Obtains a fixed-length memory block		
	pget_blf	Obtains a fixed-length memory block (polling)	V	_
	tget_blf	Obtains a fixed-length memory block (with timeout)	V	
	rel_blf	Releases a fixed-length memory block	V	
	ref_mpf	Obtains fixed-length memory pool information	V	
Time management	set_tim	Sets the time of the system clock		V
into managomont	get_tim	Obtains the time of the system clock		V
	dly_tsk	Places the task in the time lapse waiting state	V	1
	def_cyc	Registers/cancels a cyclic handler	¥	1
	act_cyc	Deletes the active state of a cyclic handler	- \	1
	ref_cyc	Obtains cyclic handler information	V	1
System management	get_ver	Obtains cyclic handler mormation	√	<u>۷</u>
ystern management	ref_sys	Obtains version mormation	N N	N ~/
	def_svc	Registers/cancels the extended SVC handler	N	N
	viss_svc	Calls the extended SVC handler		N

Note System calls related to event flags are supported.



The following OSEK/VDX specification-compliant OS is supported by the V850 Series.

RX-OSEK850: OSEK/VDX specification-compliant OS for V850 Series

Features

Kernel

Compliant with the OSEK/VDX OS Ver. 2.0 specifications Four conformance classes (BCC1, BCC2, ECC1, and ECC2) are supported

Communication

Compliant with the OSEK/VDX COM Ver. 2.1 rev 1 specifications Three conformance classes (CCC1, CCC2, and CCC3) are supported.

Configurator

A configurator that simplifies the configuration of system information (OIL850) is provided as standard. The configuration file supports a format compliant with OIL Ver. 2.0.

- Task debugger (RD-OSEK850)
 An efficient task debugger for debugging applications that use the RX-OSEK850 is provided as standard.
- System performance analyzer (AZ-OSEK850)
 System performance analyzer for RX-OSEK850 (sold separately)
- Target devices
 V850 Series

TASK DEBUGGERS (RD850/RD850 Pro)

These RX Series dedicated task debuggers provide the functions essential for debugging applications that employ a real-time OS. The debuggers are supplied in the RX Series package as standard. The main functions of the task debuggers are shown below.

- Detailed display of OS resources such as tasks
- Display of referenced task sources

These task debuggers also enable connection with a variety of other debuggers.




SYSTEM PERFORMANCE ANALYZER

The following system performance analyzer is supported in the V850 Series.

AZ850: System performance analyzer for the V850 Series

The system performance analyzer visually displays records of executed tasks and RTOS resource access data, thereby clarifying the task load status and making it easy to determine the tuning index.

Quantitative Evaluation Index

In a system constructed using a design \rightarrow coding \rightarrow debugging process, tuning work is necessary to optimize the CPU's performance and resources, and is used to assess the system performance and analyze its operation, through which system performance and product quality can be raised.

Tuning work usually involves checking the following operations and then analyzing the system's response performance.



Response Performance Analysis

- Adequacy of access division (task run time)
- Selection of optimal scheduling (task priority level)
- Optimal resource allocation (resource utilization efficiency, resource values)

Algorithms and the system configuration concept can be changed at the design stage, based on analysis results. The tool that supports this kind of analysis and modification is the system performance analyzer (AZ).

This performance analyzer, operated in combination with one of a variety of debuggers, has the following functions.

- Detection of bugs caused by system timing misses
- Detection of problems caused by the simultaneous operation of multiple tasks
- ◆ Verification/analysis of real-time system execution performance

The system performance analyzer displays trace data visually and provides the following functions for software operation control, thus facilitating task operation analysis.

- Detection of unnecessary system processing
- Support of source analysis
- Clarification of the system tuning index

- Intertask operation check (Deadlock status, task run sequence, resource access status)
- Internal task operation check (System call/return value)
- Interrupt servicing operation check (Occurrence frequency, nesting depth, servicing time, enable/disable position)

The tools supported for this analyzer and their operating environments are shown in the table below.

Taxanat Davias	A 7	Supported Tool			
Target Device	AZ	OS	Debugger	Simulator	
V850 Series	AZ850	RX850	ID850 ^{Note}	SM850	
		RX850 Pro	ID850QB	SM+	

Note Some functions can also be executed using a partner debugger.



Execution transition status display window

This window displays the object movement versus time relationship, with time indicated by the horizontal axis and object movement by the vertical axis. Analysis of system status changes caused by task switching or interrupts/exceptions, and object accesses based on real-time OS system calls are displayed as symbols, making it easy for the user to ascertain the sequence and transition of execution. These functions enable specification of the problems for the performance analysis.

CPU utilization rate display window

This window can be used to confirm the object execution time and CPU utilization rate that guide users in the analysis of the system overhead and indicate execution performance, so that the system performance can be evaluated from the view point of the idle time and interrupt time.

Processing time pattern distribution display window

Users can analyze the causes of scheduling problems by viewing the statistical breakdown of the execution processing time, as well as the interrupt frequency and execution time maximum/average/minimum figures displayed in this window.

Trace display window

Trace data from the execution transition status can be viewed. This window can be used as a sub window of the execution transition status window so that timestamps of execution status transitions and values returned by system calls can be checked.



NETWORK LIBRARY

The following network library is supported by the V850E.

RX-NET: Network library for V850E

With the rapid spread of the Internet, network libraries are now being employed for many embedded systems such as portable information terminals. NEC Electronics has therefore provided the network library "RX-NET" for embedded systems that use the V850E.

Features

- Conforms to RFC
- Supports multi-socket interfaces
- Supports optional products such as PPP, FTP, Telnet, as well as TCP/IP basic set
- Device drivers provided Various LAN controller drivers and serial control drivers are included in the source. Since the device driver section is separate from the RX-NET library, device drivers other than those included in the package can also be imported.
- Supports NEC Electronics real-time OS (RX850 Pro)

Supported Devices

V850E (only devices enabling misalignment)

Real-Time OSs

- Target Real-Time OS
 - · RX850 Pro
- Required resources of real-time OS
 - · 2 tasks
 - · 1 cyclic startup handler

Package Contents

1. Basic set

- $\bigcirc\, {\rm TCP/IP}$ protocol stack
 - TCP, UDP, IP, ICMP, ARP
- \bigcirc LAN controller
 - · LAN91C96 (manufactured by Standard Microsystems Corporation)
 - NE2000 compatible
- \bigcirc Board support package (BSP) library
 - Includes library for driving SolutionGear-V850E/MA1^{Note}

Note Manufactured by NEC Electronics Corporation

2. Options

- PPP (Point-to-Point Protocol)
 - \bigcirc Serial controller
 - · TL16550C
- DNS (Domain Name System)
- FTP server (File Transfer Protocol)
- Telnet server
- SMTP/POP (Simple Mail Transfer Protocol/Post Office Protocol)
- DHCP (Dynamic Host Configuration Protocol)
- Web server

3. Evaluation version

Basic set + options + RX-FS850



FILE SYSTEM

The following file system is available.

RX-FS850: File system for V850E

Now that the employment of storage function in embedded devices has increased and many ordinary households have at least one PC, there has been a sharp increase in the amount of data being exchanged between embedded devices and PCs. The PC-compatible file system "RX-FS850" is designed for use with V850E.

Features

- Uses PC-compatible file system
 - \bigcirc Formats for hard disk drives
 - · FAT (FAT12, FAT16, or FAT32)
 - \cdot Supports file names up to 254 characters long (VFAT)
 - \bigcirc Formats for CD-ROM drives
 - · ISO-9660 Level 1
 - · Joliet (supports file names up to 64 characters long)
 - Supports multi-session CDs
- Designed for multi-tasking
 - O No need to set up exclusive control between tasks when issuing API
 - Includes file locking function to prevent concurrent write operations from multiple tasks to the same file
- ♦ UNIX API-compliant
- Supports hot swap
 - Enables hot swap such as for PC cards
- Auto buffering function
 - \odot I/O buffer is acquired automatically for I/O processing.
- Compact design suitable for ROM programming

Supported Devices

♦ V850E Series

Real-Time OS

Target real-time operating system
 O RX850 Pro

HIGH-SPEED FLOATING-POINT LIBRARY

The following product is offered as a high-speed floating-point library.

GOFAST: V850 Series high-speed floating-point library

This library increases the operation speed when using floating-point operations with V850 Series products that do not have an on-chip FPU.

Features

- Created based on FPT3.0 from USSOFT
- ANSI-C (JIS X 3010)-compliant

Supported Devices

♦ V850 Series

Supported Compilers

♦ GHS, GNUPro, IAR

Supported Mathematical Functions

Basic operations

· Double-precision operations dpadd, dpsub, dpmul, dpdiv Single-precision operations fpadd, fpsub, fpmul, fpdiv dptofp, litodp, dptoli, ultodp, dptoul, litofp, fptoli, ultofp, fptoul · Conversion operations lltodp, ulltodp, dptoull, dptoll, fptoll, fptoull, lltofp, ulltofp · GCC only · Compare dpcmp, fpcmp GCC runtime functions negdf2, negsf2, eqdf2, nedf2, ltdf2, ledf2, gtdf2, gedf2, eqsf2, nesf2, ltsf2, lesf2, gtsf2, gesf2 **Basic functions** · Double-precision fabs, ceil, floor, fmob, modf, frexp, ldexp, sqrt Single-precision fabsf, ceilf, floort, fmodf, modff, frexpf, ldexpf, sqrtf Transcendental functions · Double-precision asin, acos, atan, atan2, cos, cosh, exp, log, log10, pow, sin, sinh, tan, tanh Single-precision acosf, asinf, atanf, atan2f, cosf, coshf, expf, logf, log10f, powf, sinf, sinhf, tanf, tanhf Additional functions isnan, isnanf, isinf, isinff



SolutionGear®

The following products are available as RISC microcontroller reference platforms.

SG-703107-1: V850E/MA1 CPU board SG-703107-1S: V850E/MA1 CPU board (socket version) SG-703111-1: V850E/ME2 CPU board SG-MOTHER-1: Motherboard



Features

The reference platform comprises the CPU board provided for each microcontroller, and a CPU-independent motherboard.

- The reference platform sold by NEC Electronics comes in a set that includes the following.
- ◆ Binary including the rights to use the RX Series (µITRON) on the reference platform
- Binary including rights to use middleware on the reference platform
- Sample driver source code for peripheral devices incorporated on board
- Board circuit diagram

These features enable the following.

- Measuring of user program benchmarks using the actual CPU
- Evaluation of RTOS and middleware supplied by NEC Electronics
- Utilization of reference information when designing user target board
- Prototype development prior to user target board completion
- Utilization of reference information for device driver when porting RTOS to target board
- Utilization as object of comparison when doubts arise about target board operation.



By simply acquiring additional development tools, therefore, this reference platform can be used as a turnkey solution.

 Multi from Green Hills Software, Inc. or the remote monitor debugger of PARTNER from Midas Lab Co., Ltd. can be used.

Target Device

- ◆ V850E/MA1
- ◆ V850E/ME2

Features of Motherboard

- ◆ Hardware for speech I/O and other middleware
- Industry-standard (PC-compatible) PCI, ISA, PCMCIA, E-IDE, Ethernet, SIO, parallel, keyboard, mouse, and other interfaces
- Can be used with PC unit, power-supply, and peripheral equipment (ATX-compatible board size)
- Support of all CPUs in V850E (CPU independent)
- Support of partner tools such as Multi from Green Hills Software, Inc. and the PARTNER remote monitor debugger from Midas Lab Co., Ltd.

Incorporated Software

NEC Electronics provides the following RTOS and middleware on this board.

- μITRON-compliant real-time OS, RX Series (RX850 Pro)
- TCP/IP software Library (RX-NET)
- Speech recognition middleware
- Text-to-speech middleware
- JPEG middleware
- Various device drivers (samples)



Applilet

The following product is provided as a device driver configuration tool.

Applilet: Device driver configuration tool

When Applilet is used, setup source files for on-chip peripheral functions can be automatically generated following a simple selection process that does not require consulting the manual.

Operation steps

1. Set up on-chip peripheral functions

Select the target model, then enter settings as required for the peripheral functions to be used.



2. Generate code

Source files for each function are generated automatically.

3. Add or revise code as needed.

4. Build

The project files used by the Project Manager are also generated automatically. These project files are loaded before building the target object.

5. Debug

Use a debugger or simulator to perform debugging.





Features

 Conflict check among interactive type input resources

In addition to providing a digital I/O port function, ports provide various alternate functions. The conflict check function ensures that there is no overlap between ports being used by the I/O port function and ports being used by an alternate function.

C Transmit only UART transfer spend	C Receive only	(F Transmit/Receive	-	_				_
Ciockmode	Wernal clock		Digital I/O					
Inchole	10500	-	Port0 Port	1 Port2	Port3 Port4	Port5		
[#				Port8 F	Port9] Port10]	Pot11		
Internal setting Received and internal			PED	-t-	-104	and the		
Finds	and and	-	Unused	2 10	200	2		
Tamuni end element	and the second second		P61 • Unused	-	and the se	and to		
Prenty	(meet)	-		2 10	2 0.0	2		
Transference interspi		-	P62	200	200	1.11		
Proty	level1	-		2100.	200	2		
Stop bit	Detable		P63 (* Unused	-	•[du	211		
lacroDriverTool			Nº Onuied	7100	100	31	×	
F0020 Th P61 is	e following conflicts ha used as RTP110P61 as	ve been detected.You m real-time output mode	ust change the se RTP11) OK	itting in th	at module befo	re you can use it fo	r ofher purposes!	

Port aliases

The alternate functions of each port can be referenced.



♦ On-line help

Help descriptions of various functions in automatically generated source code can be referenced.





PG-FP4 (FlashP

PG-FP4

PG-FP4

The following flash memory programmer is available.

PG-FP4: Microcontroller general-purpose flash memory programmer

Features

- Supports programming of all NEC Electronics microcontrollers with on-chip flash memory
- USB support via host machine interface
- LCD panel allows checking of programmer setting information, error messages, checksum values, etc., even when used as a standalone unit
- Two user codes can be downloaded and valid code selection is supported
- Device-specific information required for programming can be freely set using parameter files
- On-board programming and programming via a program adapter are possible
- Portable A5 size
- Easily operable both as a standalone unit or on Windows 98/Me/2000/XP and Windows NT Ver. 4.0 by using a dedicated application (FlashPro4)

E FP4	
<u>File Programmer D</u> evice <u>H</u> elp	
>ver Bootloader Version V1.16 Firmware Version V1.33	Device Name: 70F3318 Status: autoconnected
Serial No.: MA1JX0037D >ctr off Parallel port in remote control mode >progarea	Parameter file Name: 70F3318.PRM Version: V1.10
Active Program Area: 0 Max. program size: 1 MByte Sautocon on AutoCon is on	Device Setting file Name: 70F3318.SET Date: Mon Aug 29 13:58:52
>crc no_store Checksum: 00000000 - 000FFFFF = 7E78ED3B >epv Blank check Chip: Not blank, Erase needed. Erase Chip: Erase OK	Download file Name: sample.hex Date: Thu Oct 09 14:08:12 Chksum: 7E78ED38 Prog Area: 0
Write Chip: 10% 20% 30% 40% 50% 60%	Connection to device Port: UART-ch0 Pulse Num: 0 Speed: 38 400 bps Vdd: 05.00 V (FP4)
70% 80% 90%	Supply Freq.: 8 000 000 Hz (Target) Multiply: 1.00
100% DK Jrite OK Set Security Flags	Range: Block/Area Address:
SEA OK	File Checksum Type: Arithmetic checksum (16 bit) Address: 00000000 - 000FFFFF Value: 528D

SOFTWARE TOOLS

Product		Target Device	Host Machine (Required OS in Parentheses)	Medium	Order Number
Software package	SP850	V850 Series	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μSAB17SP850
					μ SAB17SP850-× ^{Note 3}
			IBM PC/AT or compatible (English Windows)	CD-ROM	μSBB17SP850
					μ SBB17SP850-× ^{Note 3}
Real-time OS	RX850		IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μ SAB17RX703000-### ^{Note 1}
			IBM PC/AT or compatible (English Windows)	CD-ROM	μSBB17RX703000-### ^{Note 1}
	RX850 Pro		IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μSAB17RX703100-### ^{Note 1}
			IBM PC/AT or compatible (English Windows)	CD-ROM	μSBB17RX703100-### ^{Note 1}
Compiler ^{Note 2}	CA850		IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μ SAB17CA703000 ^{Note 4}
					μSAB17CA703000-× ^{Note 3, 4}
			IBM PC/AT or compatible (English Windows)	CD-ROM	μ SBB17CA703000 ^{Note 4}
					μSBB17CA703000-× ^{Note 3, 4}
)ebugger ^{Note 2}	ID850		IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μ SAB17ID703000 ^{Note 4}
					μ SAB17ID703000-× ^{Note 3, 4}
			IBM PC/AT or compatible (English Windows)	CD-ROM	μ SBB17ID703000 ^{Note 4}
					μSBB17ID703000-× ^{Note 3, 4}
	ID850NW		IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μ SAB17ID703000-NW ^{Note 4}
					μ SAB17ID703000-NW-× ^{Note 3, 4}
			IBM PC/AT or compatible (English Windows)	CD-ROM	μ SBB17ID703000-NW ^{Note 4}
Simulator ^{Note 2}	SM850		IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μ SAB17SM703000 ^{Note 4}
					μSAB17SM703000-× ^{Note 3, 4}
			IBM PC/AT or compatible (English Windows)	CD-ROM	μ SBB17SM703000 ^{Note 4}
			, , , ,		μSBB17SM703000-× ^{Note 3, 4}
	SM+ for V850		IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μ SAB17SM703100 ^{Note 4}
	(Core version)				μ SAB17SM703100-× ^{Note 3, 4}
			IBM PC/AT or compatible (English Windows)	CD-ROM	μ SBB17SM703100 ^{Note 4}
			, , , ,		μSBB17SM703100-× ^{Note 3, 4}
	SM+ for V850		IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μ SAB17SM703289
	(Peripheral				μ SAB17SM703289-× ^{Note 3}
	version)		IBM PC/AT or compatible (English Windows)	CD-ROM	μ SBB17SM703289
	·		,		μ SBB17SM703289-× ^{Note 3}
system performance	AZ850		IBM PC/AT or compatible (Japanese Windows)	CD-ROM	Supplied with RX850, RX850 Pro
inalyzer			,		
			IBM PC/AT or compatible (English Windows)	CD-ROM	1
Performance analysis	TW850		IBM PC/AT or compatible (Japanese Windows)	CD-ROM	Note 4
uning tool			IBM PC/AT or compatible (English Windows)	CD-ROM	-

Notes 1. ###: Number of copies licensed (precontract required)

2. The device file corresponding to the relevant product of the V850 Series is required (device files can be obtained by downloading the file using NEC Electronics' Development Tools Download service (ODS)).

3. \times : Number of licenses (5, 10, 20, or 50)

4. Supplied with SP850.

Remark Contact an NEC Electronics representative if the host machine to be used is not on the list above.



Product		Target Device	Host Machine (Required OS in Parentheses)	Medium	Order Number
Network library	RX-NET	V850E	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μ SAB17AP703100-###-B17 ^{Note}
	TCP/IP				
	RX-NET (PPP)]	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μSAB17AP703100-###-B18 ^{Note}
	RX-NET (DNS)]	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μ SAB17AP703100-###-B19 ^{Note}
	RX-NET (FTP)]	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μSAB17AP703100-###-B20 ^{Note}
	RX-NET (TELNET)	1	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μSAB17AP703100-###-B21 ^{Note}
	RX-NET (DHCP)	1	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μSAB17AP703100-###-B22 ^{Note}
	RX-NET	1	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μSAB17AP703100-###-B24 ^{Note}
	(SMTP/POP)				
	RX-NET	1	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μSAB17AP703100-###-B38 ^{Note}
	(Web server)				
	RX-NET	1	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μSAB17AP703100-###-B30 ^{Note}
	evaluation				
	version				
File system	RX-FS850	1	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μSAB17AP703100-###-B33 ^{Note}
Floating-point library	GOFAST	V850 Series	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	μSAB17AP703100-###-B34 ^{Note}
			IBM PC/AT or compatible (English Windows)		μSBB17AP703100-###-B34 ^{Note}
OSEK/VDX	RX-OSEK850	1	IBM PC/AT or compatible (Japanese Windows)	CD-ROM	TBD
specification-compliant			IBM PC/AT or compatible (English Windows)	CD-ROM	TBD
real-time OS					

Note ###: Number of copies licensed (precontract required)

Remark Contact an NEC Electronics representative if the host machine to be used is not on the list above.

HARDWARE TOOLS (IECUBE)

V850ES/KE1, V850ES/KE1+, V850ES/KF1, V850ES/KF1+, V850ES/KG1, V850ES/KG1+, V850ES/KJ1, V850ES/KJ1+, V850ES/SG2, V850ES/SJ2, V850ES/FE2, V850ES/FF2, V850ES/FG2, V850ES/FJ2, μPD703229, V850ES/IK1, V850E/IA3, V850E/IA4





				Acce	ssories	
TerretD	Deel	Outlasia N.			Socket	
Target Device	Package	Ordering Number	In-Circuit Emulator	Exchange Adapter	YQ Connector (T Type Only)	Target Connector
/850ES/KE1 (+)	_	QB-V850ESKX1H-ZZZ	QB-V850ESKX1H	_	_	_
/850ES/KF1 (+)			Including			
V850ES/KG1 (+)			· Power supply			
V850ES/KJ1 (+)			· USB cable			
V850ES/KJ1 (+)	144-pin GJ	QB-V850ESKX1H-S144GJ	· Simple	QB-144GJ-EA-02S	_	QB-144GJ-TC-01S
		QB-V850ETKX1H-T144GJ	programmer	QB-144GJ-EA-02T	QB-144GJ-YQ-01T	QB-144GJ-NQ-01T
V850ES/KG1 (+)	100-pin GC	QB-V850ESKX1H-S100GC	· Debugger	QB-100GC-EA-01S	_	QB-100GC-TC-01S
		QB-V850ESKX1H-T100GC		QB-100GC-EA-01T	QB-100GC-YQ-01T	QB-100GC-NQ-01T
	100-pin GF	QB-V850ESKX1H-S100GF		QB-100GF-EA-01S	_	QB-100GF-TC-01S
		QB-V850ESKX1H-T100GF		QB-100GF-EA-01T	QB-100GF-YQ-01T	QB-100GF-NQ-01T
/850ES/KF1 (+)	80-pin GC	QB-V850ESKX1H-S80GC		QB-80GC-EA-02S	_	QB-80GC-TC-01S
		QB-V850ESKX1H-T80GC		QB-80GC-EA-02T	QB-80GC-YQ-01T	QB-80GC-NQ-01T
	80-pin GK	QB-V850ESKX1H-S80GK		QB-80GK-EA-01S	_	QB-80GK-TC-01S
		QB-V850ESKX1H-T80GK		QB-80GK-EA-03T	QB-80GK-YQ-01T	QB-80GK-NQ-01T
V850ES/KE1 (+)	64-pin GB	QB-V850ESKX1H-S64GB	-	QB-64-EA-01S		QB-64GB-TC-01S
		QB-V850ESKX1H-T64GB		QB-64GB-EA-03T	QB-64GB-YQ-01T	QB-64GB-NQ-01T
	64-pin GK	QB-V850ESKX1H-S64GK	-	QB-64-EA-01S		QB-64GK-TC-01S
	o- pin arc	QB-V850ESKX1H-T64GK	_	QB-64GK-EA-02T	QB-64GK-YQ-01T	QB-64GK-NQ-01T
/850E/IA4		QB-V850EIA4-ZZZ	QB-V850EIA4	QD-0401(-LA-021	QD-04QI(-1Q-011	QD-04QR-NQ-011
/850E/IA3		QB-V850EIA4-ZZZ		_		_
			Including			
/850ES/IK1	100 . 00		· Power supply	00 40000 54 000		00.40000.70.040
V850E/IA4	100-pin GC	QB-V850EIA4-S100GC	· USB cable	QB-100GC-EA-02S	-	QB-100GC-TC-01S
		QB-V850EIA4-T100GC	· Simple	QB-100GC-EA-02T	QB-100GC-YQ-01T	QB-100GC-NQ-01T
	100-pin GF	QB-V850EIA4-S100GF	programmer	QB-100GF-EA-02S	—	QB-100GF-TC-01S
		QB-V850EIA4-T100GF	· Debugger	QB-100GF-EA-02T	QB-100GF-YQ-01T	QB-100GF-NQ-01T
V850E/IA3	80-pin GC	QB-V850EIA4-S80GC		QB-80GC-EA-01S		QB-80GC-TC-01S
		QB-V850EIA4-T80GC		QB-80GC-EA-03T	QB-80GC-YQ-01T	QB-80GC-NQ-01T
V850ES/IK1	64-pin GC	QB-V850EIA4-S64GC		QB-64GC-EA-01S	_	QB-64GC-TC-01S
		QB-V850EIA4-T64GC		QB-64GC-EA-02T	QB-64GC-YQ-01T	QB-64GC-NQ-01T
/850ES/SG2 /850ES/SJ2	—	QB-V850ESSX2-ZZZ	QB-V850ESSX2 Including	_	_	_
/850ES/SJ2	144-pin GJ	QB-V850ESSX2-S144GJ	· Power supply	QB-144GJ-EA-01S	_	QB-144GJ-TC-01S
		QB-V850ESSX2-T144GJ	· USB cable	QB-144GJ-EA-01T	QB-144GJ-YQ-01T	QB-144GJ-NQ-01T
/850ES/SG2	100-pin GC	QB-V850ESSX2-S100GC	· Simple	QB-100GC-EA-01S	_	QB-100GC-TC-01S
		QB-V850ESSX2-T100GC	programmer	QB-100GC-EA-01T	QB-100GC-YQ-01T	QB-100GC-NQ-01T
	100-pin GF	QB-V850ESSX2-S100GF	· Debugger	QB-100GF-EA-01S	_	QB-100GF-TC-01S
		QB-V850ESSX2-T100GF		QB-100GF-EA-01T	QB-100GF-YQ-01T	QB-100GF-NQ-01T
V850ES/FE2	_	QB-V850ESFX2-ZZZ	QB-V850ESFX2	_	_	_
V850ES/FF2			Including			
/850ES/FG2			· Power supply			
/850ES/FJ2			· USB cable			
/850ES/FJ2	144-pin GJ	QB-V850ESFX2-S144GJ	· Simple	QB-144GJ-EA-03S	_	QB-144GJ-TC-01S
	1	QB-V850ESFX2-T144GJ	programmer	QB-144GJ-EA-03T	QB-144GJ-YQ-01T	QB-144GJ-NQ-01T
/850ES/FG2	100-pin GC	QB-V850ESFX2-S100GC	· Debugger	QB-100GC-EA-01S		QB-100GC-TC-01S
		QB-V850ESFX2-T100GC		QB-100GC-EA-013	QB-100GC-YQ-01T	QB-100GC-NQ-01T
<i>и</i> PD703229	100-pin GC	QB-703229-S100GC	-	QB-100GC-EA-03S		QB-100GC-TC-01S
/850ES/FF2	80-pin GK		\neg	QB-80GK-EA-02S		
000000/FF2	oo-pin GR	QB-V850ESFX2-S80GK				QB-80GK-TC-01S
/850ES/FE2	64-pin GB	QB-V850ESFX2-T80GK QB-V850ESFX2-S64GB		QB-80GK-EA-02T QB-64GB-EA-01S	QB-80GK-YQ-01T	QB-80GK-NQ-01T QB-64GB-TC-01S
						111B-6/0-8-11-111S

Under development

Ordering	Numbe	r of Socket f	or IECUBE/0	Optional Pro	ducts					
Target Device	Package	Exchange Adapter	YQ Connector	Target Connector	Mount Adapter	Space Adapter	Check Pin Adapter (Dedicated to S Type)	Check Pin Adapter (Common to S/T Type)	Extension Probe	
V850ES/KJ1(+)	144-pin GJ	QB-144GJ-EA-02S	_	QB-144GJ-TC-01S	QB-144GJ-MA-01S	QB-144-SA-01S	QB-144-CA-01S	QB-144-CA-01	QB-144-EP-01S	
		QB-144GJ-EA-02T	QB-144GJ-YQ-01T	QB-144GJ-NQ-01T	QB-144GJ-HQ-01T	QB-144GJ-YS-01T	_			
V850ES/KG1(+)	100-pin GC	QB-100GC-EA-01S	_	QB-100GC-TC-01S	QB-100GC-MA-01S	QB-100-SA-01S	QB-100-CA-01S			
		QB-100GC-EA-01T	QB-100GC-YQ-01T	QB-100GC-NQ-01T	QB-100GC-HQ-01T	QB-100GC-YS-01T				
	100-pin GF	QB-100GF-EA-01S		QB-100GF-TC-01S	QB-100GF-MA-01S	QB-100-SA-01S	QB-100-CA-01S			
		QB-100GF-EA-01T	QB-100GF-YQ-01T	QB-100GF-NQ-01T	QB-100GF-HQ-01T	QB-100GF-YS-01T	—			
V850ES/KF1(+)	80-pin GC	QB-80GC-EA-02S	—	QB-80GC-TC-01S	QB-80GC-MA-01S	QB-80-SA-01S	QB-80-CA-01S			
		QB-80GC-EA-02T	QB-80GC-YQ-01T	QB-80GC-NQ-01T	QB-80GC-HQ-01T	QB-80GC-YS-01T	—			
	80-pin GK	QB-80GK-EA-01S	—	QB-80GK-TC-01S	QB-80GK-MA-01S	QB-80-SA-01S	QB-80-CA-01S			
		QB-80GK-EA-03T	QB-80GK-YQ-01T	QB-80GK-NQ-01T	QB-80GK-HQ-01T	QB-80GK-YS-01T	—			
V850ES/KE1(+)	64-pin GB	QB-64-EA-01S	—	QB-64GB-TC-01S	QB-64GB-MA-01S	QB-64-SA-01S	QB-64-CA-01S	-		
		QB-64GB-EA-03T	QB-64GB-YQ-01T	QB-64GB-NQ-01T	QB-64GB-HQ-01T	QB-64GB-YS-01T	_			
	64-pin GK	QB-64-EA-01S	—	QB-64GK-TC-01S	QB-64GK-MA-01S	QB-64-SA-01S	QB-64-CA-01S			
		QB-64GK-EA-02T	QB-64GK-YQ-01T	QB-64GK-NQ-01T	QB-64GK-HQ-01T	QB-64GK-YS-01T	_			
V850E/IA4	100-pin GC	QB-100GC-EA-02S	—	QB-100GC-TC-01S	QB-100GC-MA-01S	QB-100-SA-01S	QB-100-CA-01S	_		
		QB-100GC-EA-02T	QB-100GC-YQ-01T	QB-100GC-NQ-01T	QB-100GC-HQ-01T	QB-100GC-YS-01T	_			
	100-pin GF	QB-100GF-EA-02S	—	QB-100GF-TC-01S	QB-100GF-MA-02S	QB-100-SA-01S	QB-100-CA-01S			
		QB-100GF-EA-02T	QB-100GF-YQ-01T	QB-100GF-NQ-01T	QB-100GF-HQ-02T	QB-100GF-YS-01T	_			
V850E/IA3	80-pin GC	QB-80GC-EA-01S	—	QB-80GC-TC-01S	QB-80GC-MA-01S	QB-80-SA-01S	QB-80-CA-01S			
		QB-80GC-EA-03T	QB-80GC-YQ-01T	QB-80GC-NQ-01T	QB-80GC-HQ-01T	QB-80GC-YS-01T	_			
V850ES/IK1	64-pin GC	QB-64GC-EA-01S	—	QB-64GC-TC-01S	QB-64GC-MA-01S	QB-64-SA-01S	QB-64-CA-01S			
		QB-64GC-EA-02T	QB-64GC-YQ-01T	QB-64GC-NQ-01T	QB-64GC-HQ-01T	QB-64GC-YS-01T	_			
V850ES/SJ2	144-pin GJ	QB-144GJ-EA-01S	_	QB-144GJ-TC-01S	QB-144GJ-MA-01S	QB-144-SA-01S	QB-144-CA-01S			
		QB-144GJ-EA-01T	QB-144GJ-YQ-01T	QB-144GJ-NQ-01T	QB-144GJ-HQ-01T	QB-144GJ-YS-01T	_			
V850ES/SG2	100-pin GC	QB-100GC-EA-01S	_	QB-100GC-TC-01S	QB-100GC-MA-01S	QB-100-SA-01S	QB-100-CA-01S			
		QB-100GC-EA-01T	QB-100GC-YQ-01T	QB-100GC-NQ-01T	QB-100GC-HQ-01T	QB-100GC-YS-01T	_			
	100-pin GF	QB-100GF-EA-01S	_	QB-100GF-TC-01S	QB-100GF-MA-01S	QB-100-SA-01S	QB-100-CA-01S			
		QB-100GF-EA-01T	QB-100GF-YQ-01T	QB-100GF-NQ-01T	QB-100GF-HQ-01T	QB-100GF-YS-01T	_			
V850ES/FJ2	144-pin GJ	QB-144GJ-EA-03S	_	QB-144GJ-TC-01S	QB-144GJ-MA-01S	QB-144-SA-01S	QB-144-CA-01S			
		QB-144GJ-EA-03T	QB-144GJ-YQ-01T	QB-144GJ-NQ-01T	QB-144GJ-HQ-01T	QB-144GJ-YS-01T	_			
V850ES/FG2	100-pin GC	QB-100GC-EA-01S	—	QB-100GC-TC-01S	QB-100GC-MA-01S	QB-100-SA-01S	QB-100-CA-01S			
		QB-100GC-EA-01T	QB-100GC-YQ-01T			QB-100GC-YS-01T	_			
μPD703229	100-pin GC	QB-100GC-EA-03S	—	QB-100GC-TC-01S	QB-100GC-MA-01S	QB-100-SA-01S	QB-100-CA-01S			
V850ES/FF2	80-pin GK	QB-80GK-EA-02S	_	QB-80GK-TC-01S	QB-80GK-MA-01S	QB-80-SA-01S	QB-80-CA-01S			
		QB-80GK-EA-02T	QB-80GK-YQ-01T	QB-80GK-NQ-01T	QB-80GK-HQ-01T	QB-80GK-YS-01T	_			
V850ES/FE2	64-pin GB	QB-64GB-EA-01S	_	QB-64GB-TC-01S	QB-64GB-MA-01S	QB-64-SA-01S	QB-64-CA-01S			
	1 . .	QB-64GB-EA-02T	QB-64GB-YQ-01T	QB-64GB-NQ-01T	QB-64GB-HQ-01T	QB-64GB-YS-01T	_			

Under development

Socket required for connecting target system

Optional socket for use according to purpose

Mount adapter:	Adapter for mounting device
Space adapter:	Adapter for adjusting height
Check pin adapter:	Adapter for monitoring signal
Extension probe:	Probe for extending connection between IECUBE and target system



V850ES/KF1, V850ES/KG1, V850ES/KJ1, V850ES/SA2, V850ES/SA3, V850ES/SG2, V850ES/SJ2, V850ES/FE2, V850ES/FF2, V850ES/FG2, V850ES/FJ2, V850ES/PM1, μ PD703229Y, V850ES/ST2



(1) In-circuit emulator (main unit)

- (2) Emulation board (connected inside main unit)
- ③ Emulation probe
- 4 Conversion adapter/conversion socket
- 5 PC interface cable (included with 1)
- $\overline{\mathbb{6}}$ Power cable (included with 1)

our creativity

Empower

T	In-Circui	t Emulator	Conversion Adapter/			Power
Target Device	Main Unit	Emulation Board	Conversion Socket	Emulation Probe	PC Interface Board	Supply
V850ES/SA2	IE-V850ES-G1	IE-703204-G1-EM1	NQPACK100SD	SWEX-100SD-1	IE-70000-CD-IF-A	Included
100-pin TQFP			YQPACK100SD	(coaxial cable)	IE-70000-PCI-IF-A	with
14 × 14 mm			HQPACK100SD			main unit
			YQSOCKET100SDN			
			YQGUIDE			
V850ES/SA3			CSICE121A1312N03	SWEX-120SE-1		
121-pin FBGA			LSPACK121A1312N01	(coaxial cable)		
12 × 12 mm			CSSOCKET121A1312N01		_	
V850ES/SG2		IE-703288-G1-EM1	EV-703288GC100	Included with		
100-pin LQFP				emulation board		
14 × 14 mm	-			-		
V850ES/SG2			EV-703288GF100			
100-pin QFP						
14 × 20 mm	-		FV 7020800 1144	-		
V850ES/SJ2			EV-703288GJ144			
144-pin LQFP 20 × 20 mm						
20 x 20 mm V850ES/FE2		IE-703239-G1-EM1	EV-703239GB64	-		
64-pin TQFP						
$10 \times 10 \text{ mm}$						
V850ES/FF2			EV-703239GK80	-		
80-pin TQFP						
12 × 12 mm						
V850ES/FG2			EV-703239GC100			
100-pin LQFP						
14 × 14 mm						
V850ES/FJ2			EV-703239GJ144			
144-pin LQFP						
20 × 20 mm						
μPD703229Y			EV-703239GC100			
100-pin LQFP						
14 × 14 mm			FV/ 70000000100	-		
V850ES/ST2		IE-703220-G1-EM1	EV-703220GC120			
120-pin TQFP						
14 × 14 mm V850ES/ST2			EV-703220GJ144	-		
144-pin LQFP			Lv-10022000144			
$20 \times 20 \text{ mm}$						
V850ES/PM1	-	IE-703228-G1-EM1	NQPACK100SD	Use of emulation probe is	-	
100-pin LQFP		(Includes A/D BOARD,	YQPACK100SD	not possible.		
$14 \times 14 \text{ mm}$		flat cable,	HQPACK100SD	Connect to target system		
		NQPACK100SD,	YQSOCKET100SDN	via a flat cable and A/D		
		YQPACK100SD,	YQGUIDE	BOARD.		
		HQPACK100SD,				
		YQSOCKET100SDN,				
		and YQGUIDE)				

Manufactured by Tokyo Eletech Corporation

Inquiries to: Daimaru Kogyo Ltd. Tokyo Electronics Department (Tel: 81-3-3820-7112) Application Corporation (Tel: 81-42-732-1377)

HARDWARE TOOLS (MC EMULATOR 1/3)



Empor

eativitu

Target Device		t Emulator	Conversion Adapter/	Extension Probe	PC Interface Board	Power Supply
raiger bevice	Main Unit	Option Board	Conversion Socket	(Option)		r ower ouppry
V850E/MA1	IE-V850E-MC-A	IE-703107-MC-EM1	NQPACK144SD	SC-144SDN	IE-70000-PCI-IF-A	IE-70000-MC-PS-B
144-pin LQFP	/ Includes PC	/Includes NQPACK144SD,	YQPACK144SD	(flexible cable)	IE-70000-CD-IF-A	(Includes AC100
0.5 mm pitch	interface cable	YQPACK144SD,	HQPACK144SD	SWEX-144SD-1		to 240 V power cable /
	and external	HQPACK144SD,	YQSOCKET144SDN	(coaxial cable)		
	logic probe /	\and YQGUIDE	YQGUIDE			
V850E/MA1			CSSOKET161A1413N01NNote 1	—		
161-pin FBGA			(for target board)			
13 × 13 mm			CSSOKET161A1413N01S1			
			(fastener)			
			LSPACK161A1413NO1			
			CSICE161A1413NO2		_	
V850E/MA2			VP-V850E/MA1-MA2Note 2	SC-100SDN		
100-pin LQFP			NQPACK100SD	(flexible cable)		
0.5 mm pitch			YQPACK100SD	SWEX-100SD-1		
			HQPACK100SD	(coaxial cable)		
			YQSOCKET100SDN			
			YQGUIDE		_	
V850E/SV2		IE-703166-MC-EM1	BSSOCKET257B2014N01	SWEX-260AXK		
257-pin FBGA			(for target board)	(coaxial cable)		
			CSSOCKET257B2014N01			
			(fastener, option)			
			LSPACK257B2014N01			
			(for mounting device)			
			CSICE257B2014N01			
			(for emulator connection)		-	
NB85E ^{Note 3}		IE-V850E-MC-EM1-A	_	—		
(2.5 V)			-			
NB85E ^{Note 4}		IE-V850E-MC-EM1-B				
(3.3 V)						

Notes 1. Type without target socket guides

In the case of the type with guides, remove the N from the end of the order number.

- **2.** NQPACK100SD, YQPACK100SD, HQPQACK100SD, and YQGUIDE are included.
- **3.** For connection to the UDL board, use 2529-1357-50-1902 (manufactured by Sumitomo 3M, Ltd.) (included with the product).
- 4. For connection to the UDL board, use XH3A-0141-A (manufactured by Omron Corporation) (included with the product).

Target Device	In-Circuit Main Unit	Emulator Option Board	Conversion Adapter/ Conversion Socket	Extension Probe (Option)	PC Interface Board	Power Supply
V850E/IA1	IE-V850E-MC	IE-703116-MC-EM1	NQPACK144SD	SC-144SDN	IE-70000-PCI-IF-A	IE-70000-MC-PS-B
144-pin LQFP	/ Includes PC	/ Includes NQPACK144SD, \	YQPACK144SD	(flexible cable)	IE-70000-CD-IF-A	(Includes AC100
0.5 mm pitch	interface cable	YQPACK144SD,	HQPACK144SD	SWEX-144SD-1		to 240 V power cable
	and external	HQPACK144SD,	YQSOCKET144SDN	(coaxial cable)		
	logic probe	and YQGUIDE	YQGUIDE			
V850E/IA2		IE-703114-MC-EM1	NQPACK100SD	SC-100SDN		
100-pin LQFP		/ Includes NQPACK100SD, \	YQPACK100SD	(flexible cable)		
0.5 mm pitch		YQPACK100SD,	HQPACK100SD	SWEX-100SD-1		
		HQPACK100SD,	YQSOCKET100SDN	(coaxial cable)		
		and YQGUIDE	YQGUIDE			
V850E/IA2			NEXB-2R100SD/RB			
100-pin QFP			NQPACK100RB			
0.65 mm pitch			YQPACK100RB			
			HQPACK100RB			
			YQSOCKET100RBN			
			YQGUIDE			
Inquirie	Applicatio		``	el: 81-3-3820-7 el: 81-42-732-13	,	
		sei Machida Mfg. Co.		el: 81-45-475-4	191)	





Empowe

creativity

Target Device		Emulator	Conversion Adapter/	Extension Probe	PC Interface Board	Power Supply
raiger Berlee	Main Unit	Option Board	Conversion Socket	(Option)	1 o intollado Board	i onor euppry
V850E/MS1	IE-703102-MC	IE-703102-MC-EM1	NQPACK144SD	SC-144SDN	IE-70000-PCI-IF-A	IE-70000-MC-PS-B
(5 V)	Includes PC		YQPACK144SD	(flexible cable)	IE-70000-CD-IF-A	(Includes AC100
144-pin LQFP	interface cable,		HQPACK144SD	SWEX-144SD-1		to 240 V power cable
0.5 mm pitch	external logic		YQSOCKET144SDN	(coaxial cable)		
	probe,		YQGUIDE			
V850E/MS1	NQPACK144SD,		CSPACK157A1614N01			
(5 V)	YQPACK144SD,		CSICE157A1614N01			
157-pin FBGA	HQPACK144SD,					
14 × 14 mm	and YQGUIDE.				-	
V850E/MS2			VP-V850E/MS1-MS2 ^{Note}	SC-100SDN		
(5 V)				(flexible cable)		
100-pin LQFP			NQPACK100SD	SWEX-100SD-1		
14 × 14 mm			YQPACK100SD	(coaxial cable)		
0.5 mm pitch			HQPACK100SD			
			YQSOCKET100SDN			
			YQGUIDE		-	
V850E/MS1		IE-703102-MC-EM1-A	NQPACK144SD	SC-144SDN		
(3 V)			YQPACK144SD	(flexible cable)		
144-pin LQFP			HQPACK144SD	SWEX-144SD-1		
0.5 mm pitch			YQSOCKET144SDN	(coaxial cable)		
10505/100			YQGUIDE	4		
V850E/MS1			CSPACK157A1614N01			
(3 V)			CSICE157A1614N01			
157-pin FBGA						
14 × 14 mm						

Manufactured by Tokyo Eletech

Inquiries to: Daimaru Kogyo, Ltd. Tokyo Electronics Department (Tel: 81-3-3820-7112) Application Corporation (Tel: 81-42-732-1377)

Manufactured by Naito Densei Machida Mfg. Co., Ltd. Inquiries to: Naito Densei Machida Mfg. Co., Ltd.

(Tel: 81-45-475-4191)

HARDWARE TOOLS (MC EMULATOR 3/3)



Target DeviceIn Orical EnrollationOption BoardConversion SocketPC Interface BoardPower SV853IE-703002-MCIE-703003-MC-EM1NQPACK100SDSC-100SDNIE-70000-CD-IF-AIE-70000-CD-IF-AIE-70000-M100-pin LQFP 0.5 mm pitch/Includes PC interface cable, external logic(Includes (NQPACK100SD)NQPACK100SDSC-100SDNIE-70000-PCI-IF-AIE-70000-PCI-IF-AIE-70000-PCI-IF-AIE-70000-PCI-IF-AIC-7000-PCI-IF-AIC-7000-PCI-IF-AIC-70000-PCI-IF-AIC-7000-PCI-IF-A<	C-PS-B C100
100-pin LQFP (Includes PC interface cable, (Includes NQPACK100SD YQPACK100SD HQPACK100SD (flexible cable) SWEX-100SD-1 IE-70000-PCI-IF-A (Includes A to 240 V pc	C100
0.5 mm pitch interface cable, NQPACK100SD HQPACK100SD SWEX-100SD-1 (to 240 V pr	
	wer cable
external logic YQSOCKET100SDN (coaxial cable)	
probe, YQGUIDE	
NQPACK100SD,	
YQPACK100SD,	
HQPACK100SD,	
YQSOCKET100SD	
and YQGUIDE	

Empow

creativity

	In-Circuit	t Emulator	Conversion Adapter/	Extension Probe		
Target Device	Main Unit	Option Board	Conversion Socket	(Option)	PC Interface Board	Power Supply
V850/SA1	IE-703002-MC	IE-703017-MC-EM1	NQPACK100SD	SC-100SDN	IE-70000-CD-IF-A	IE-70000-MC-PS-B
100-pin LQFP	Includes PC	/ Includes	YQPACK100SD	(flexible cable)	IE-70000-PCI-IF-A	/ Includes AC100
0.5 mm pitch	interface cable,	NQPACK100SD and	HQPACK100SD	SWEX-100SD-1		to 240 V power cable
	external logic	crystal oscillator	YQSOCKET100SDN	(coaxial cable)		
	probe,	(20 MHz)	YQGUIDE	, ,		
V850/SA1	NQPACK100SD,		CSPACK121A1312N02	SC-100SDN		
121-pin	YQPACK100SD,		CSICE121A1312N02	(flexible cable)		
FPBGA	HQPACK100SD,			SWEX-100SD-1		
	YQSOCKET100SD,			(coaxial cable)		
V850/SB1,	and YQGUIDE	IE-703037-MC-EM1	NQPACK100SD	SC-100SDN		
SB2			YQPACK100SD	(flexible cable)		
100-pin LQFP			HQPACK100SD	SWEX-100SD-1		
0.5 mm pitch			YQSOCKET100SDN	(coaxial cable)		
1/252/05/			YQGUIDE	00.00000	-	
V850/SB1,			NEXB-100SD/RB ^{Note 1}	SC-100SDN		
SB2 100-pin LQFP			NQPACK100RB YQPACK100RB	(flexible cable) SWEX-100SD-1		
100-pin LQFP $14 \times 20 \text{ mm}$			HQPACK100RB	(coaxial cable)		
0.65 mm pitch			YQSOCKET100RBN			
0.00 mm piton			YQGUIDE			
V850/SV1		IE-703040-MC-EM1	NQPACK176SD	SC-176SDN	-	
176-pin LQFP		/ Includes	YQPACK176SD	(flexible cable)		
0.5 mm pitch		NQPACK176SD,	HQPACK176SD	(
·		YQPACK176SD,	YQSOCKET176SDN			
		YQGUIDE, and crystal	YQGUIDE			
		oscillator (20 MHz)				
V850/SV1			EXC-180A/SV1	-		
180-pin FBGA			CSSOCKET180A1513N01NNote 2			
			(for target board)			
			CSSOCKET180A1513N01S1			
			(fastener)			
			LSPACK180A1513N01		-	
V850/SF1		IE-703079-MC-EM1	NQPACK100SD YQPACK100SD	SWEX-100SD-1		
100-pin QFP			HQPACK100SD	(coaxial cable)		
0.5 mm pitch			YQSOCKET100SDN			
			YQGUIDE			
V850/SF1			SWEX-100SD/	_	4	
100-pin LQFP			GF-N17D			
14 × 20 mm			(coaxial cable)			
0.65 mm pitch			NQPACK100RB			
			YQPACK100RB			
			HQPACK100RB			
			YQSOCKET100RBN			
			YQGUIDE			
V850/SC1,		IE-703089-MC-EM1	NQPACK144SD	SWEX-144SD-1		
V850/SC2,		Includes	YQPACK144SD	(coaxial cable)		
V850/SC3,		NQPACK144SD,	HQPACK144SD			
144-pin LQFP		YQPACK144SD,	YQSOCKET144SDN			
14 × 14 mm		HQPACK144SD,	YQGUIDE			
0.5 mm pitch		\and YQGUIDE				

Notes 1. The following conversion sockets are included.

NQPACK100RB, YQPACK100RB, HQPACK100RB, YQGUIDE

 Type without target socket guides In the case of the type with guides, remove the N from the end of the order number.

Manufactured by Tokyo Eletech

Inquiries to: Daimaru Kogyo, Ltd. Tokyo Electronics Department (Tel: 81-3-3820-7112) Application Corporation (Tel: 81-42-732-1377)



V850E/MA3, V850E/ME2, V850E/IA4, V850E/SV2, V850E/RS1, V850ES/SG2, V850ES/SJ2, V850ES/KJ1, V850ES/KJ1+, V850ES/FE2, V850ES/FF2, V850ES/FG2, V850ES/FJ2, μPD70F3229Y



- 1 On-chip debug emulator (MINICUBE)
- ② OCD cable (Supplied with ①)
- 3 USB interface cable (Supplied with 1)
- (4) KEL adapter (Supplied with (1))
- (5) KEL connector (Supplied with (1))

On-Chip Debug Emulator	OCD Cable USB Cable	Adapter	Target Connector for OCB
QB-V850MINI Supplied with B-136 8		B-136	8830E-026-170S
	QB-V850MINI	(Supplied with QB-V850MINI)	(26-pin KEL connector straight version)
			(Supplied with QB-V850MINI)
			8830E-026-170L
			(26-pin KEL connector right-angle version)
		B-137 (Straight version)	2-767004-2
		B-137A (Right-angle version)	(38-pin MICTOR connector straight version)
		B-140	XF2E-1515-1
		(One XF2E-1515-1 supplied)	(15-pin XF2E connector)
		SICA2012P	SICA2P20S05
		(One SICA2P20S supplied)	(Five 20-pin SICA connector set)
		Unnecessary	HIF3FC-20PA-2.54DS
			(20-pin 2.54 mm pitch recommended general-purpose connector right-angle version)
			HIF3FC-20PA-2.54DSA
			(20-pin 2.54 mm pitch recommended general-purpose connector straight version)

Remark A debugger (ID850QB) is supplied with IE-V850E1-CD-NW.

- Manufactured by Lightwell
 - Inquiries to: Lightwell Co., Ltd. (Tel: 81-3-3392-3331)
- Manufactured by KEL
- Inquiries to: KEL Corporation (Tel: 81-42-374-5800)
- Manufactured by Tyco Electronics AMP K.K.
- Inquiries to: Tyco Electronics AMP K.K. (Tel: 81-44-844-8013)
- Manufactured by OMRON Corporation
- Inquiries to: OMRON Corporation (URL: http://www.omron.com/)
- Manufactured by Tokyo Eletech
- Inquiries to: Daimaru Kogyo, Ltd. Tokyo Electronics Department (Tel: 81-3-3820-7112) Application Corporation (Tel: 81-42-732-1377)
- Manufactured by HIROSE ELECTRIC CO.,LTD. Inquiries to: HIROSE ELECTRIC CO.,LTD. (URL: http://www.hirose.com/index.html)

HARDWARE TOOLS (N-WIRE EMULATOR)





HARDWARE TOOLS (FLASH MEMORY PROGRAMMER)



Product	Target Device	Order Number	Remarks
Flash programmer	All products (except V852)	PG-FP4	Flash memory programmer
		FL-PR4	
Program adapter	V850/SA1 (121-pin FBGA)	FA-121FPBGA	Flash program adapter for 121-pin FBGA (121S1-YJC)
		FA-121F1-EA6-A	Flash program adapter for 121-pin FBGA (121F1-EA6)
	V853 (121-pin FBGA)	FA-121F1-EA6-A	Flash program adapter for 121-pin FBGA (121F1-EA6)
	V850E/MS1 (157-pin FBGA)	FA-157FPBGA	Flash program adapter for 157-pin FBGA (157F1-FA1)
	V850E/MA1 (161-pin FBGA)	FA-161F1-EN4-A	Flash program adapter for 161-pin FBGA (161F1-EN4)
	V853, V850/SA1, V850E/IA2,	FA-100GC-8EU-A	Flash program adapter for 100-pin LQFP
	V850/SB1, V850/SB2, V850/SF1,		(100GC-8EU, 100GC-8EA)
	V850ES/KG1, V850ES/KG1+,		
	V850ES/SG2, V850ES/PM1,		
	V850E/IA4, µPD70F3229Y,		
	V850ES/FG2 (100-pin LQFP)		
	V850E/MS1, V850E/MA1,	FA-144GJ-UEN-A	Flash program adapter for 144-pin LQFP
	V850E/IA1, V850ES/KJ1,		(144GJ-8EU,144GJ-UEN)
	V850ES/KJ1+, V850ES/SJ2,		
	V850ES/FJ2 (144-pin LQFP) ,		
	V850/SC1, V850/SC2, V850/SC3		
	V850/SB1, V850/SB2	FA-100GF-3BA-A	Flash program adapter for 100-pin QFP
	V850/SF1, V850ES/SG2,		(100GF-3BA, 100GF-JBT)
	V850E/IA4, V850ES/KG1+		
	(100-pin QFP)		
	V850/SV1 (176-pin LQFP)	FA-176GM-UEU	Flash program adapter for 176-pin LQFP (176GM-UEU)
	V850ES/SA2 (100-pin TQFP)	FA-100GC-YEU-A	Flash program adapter for 100-pin TQFP (100GC-YEU)
	V850ES/SA3 (121-pin FBGA)	FA-121F1-EA6-A	121-pin FBGA (121F1-EA6) program adapter with
			connector for single-power-supply flash memory
	V850ES/KF1, V850E/IA3	FA-80GC-8BT-A	Flash program adapter for 80-pin QFP (80GC-8BT)
	(80-pin QFP)		
	V850ES/KF1, V850ES/KF1+,	FA-80GK-9EU-A	Flash program adapter for 80-pin TQFP (80GK-9EU)
	V850ES/FF2 (80-pin TQFP)		
	V850ES/KJ1 (144-pin LQFP)	FA-144GJ-UEN-A	Flash program adapter for 144-pin LQFP (144GJ-UEN)
	V850E/SV2 (257-pin FBGA)	FA-257F1-FA5-A	Flash program adapter for 257-pin FBGA (257F1-FA5)
	V850ES/KE1+,	FA-64GB-8EU-A	Flash program adapter for 64-pin QFP
	V850ES/FE2 (64-pin QFP)		(64GB-8EU, 64GB-YEU)
	V850ES/KE1+ (64-pin TQFP)	FA-64GK-9ET-A	Flash program adapter for 64-pin TQFP (64GK-9ET)

Manufactured by Naito Densei Machida Mfg. Co., Ltd. Inquiries to: Naito Densei Machida Mfg. Co., Ltd. (Tel: 81-45-475-4191)





Empower your creativity

PARTNERS

NEC Electronics works together with partners who provide various types of development tools for the V850 Series to support our customers' system building requirements. By passing on to these partners the hardware and software information we develop, they can tailor product development to our customers' needs.

os **TOPPERS-Pro Nucleus Plus** [Manufacturer/Marketer] Accelerated Technology [Manufacturer/Marketer] AI Corporation Mentor Graphics Division of Mentor [Features] • Conforms to μ ITRON V4. Graphics Japan Co., Ltd. • Dynamic loading of remote link loader method [Features] ◆ A real-time operating system with a proven track record throughout ◆ TCP/IP protocol stack and file system integrated the world. Includes source code, making royalties unnecessary. ◆ Scalable: From 4 KB to 45 KB depending on which functions are reauired Descriptions in ANSI C Short interrupt latency • Expandable: New service calls can be prepared by combining existing service calls ◆ Configurable: Unused service calls can easily be excluded Dynamic creation of all Nucleus PLUS resources Intertask communication: Mailboxes, queues, pipes, task synchronization, counting semaphores, events, UNIX-like signal handler One-shot timer and multiple-shot timer • Memory management: Support of fixed length and variable length (malloc) Nucleus PLUS components can be allocated to any memory area ◆ Advanced Interrupt Management Mechanism (AIMM) ThreadX/ThreadX µITRON [Manufacturer] Express Logic, Inc. [Marketer] Grape Systems Inc. [Features] Supplies ANSI C source code without royalties NORTi Professional Compact code size (4 KB min.) [Manufacturer/Marketer] MiSPO Co., Ltd. ♦ Usable as OS conforming to µITRON [Features] • Easy integration and development with Green Hills MULTI (kernel-aware Complies with both μITRON 4.0 and 3.0 specifications, enables mixdebug function) ing of new and old system calls ♦ High-speed response (2.9 μs, context switch@33 MHz) ◆ Full-fledged TCP/IP protocol stack is a standard-equipped feature Easy-to-understand API and flexible memory configuration Simple, royalty-free licensing similar to compiler Quick technical support in Japanese • Provides various protocols, file systems, and wireless LAN drivers

- Wealth of middleware (such as FileX, NetX, and PegX)
- ◆ NetX is supplied with high-end protocol of TCP/IP (such as DHCP, FTP, HTTP, PPP, Telnet, SNMP v1/v2/v3, TFTP, DNS, IGMP, and ICMP)

Prototype Model Design Tools, Test Tools (1/2)

ProtoBuilder

[Manufacturer/Marketer] GAIO TECHNOLOGY CO., LTD. [Features]

- Easy-to-operate product specification creation tool that does not require programming skill
- Smoothes communication between specification creator and software developer, so that "going back" of development because of insufficient specification can be eliminated
- Automatically creates specification based on status transition from a prototype model created.
- Read-only tool that can be distributed to other departments, cooperative companies, and foreign branch offices

Prototype Model Design Tools, Test Tools (2/2)

TestRT

[Manufacturer/Marketer] IBM Japan, Ltd. [Features]

Integrated dynamic test tool

- This is an optimum test tool for customers with strict test requirements such as in the aerospace, military, and automotive fields.
- Supports all test processes from unit testing to system testing, displaying application execution results as sequence diagrams that include time stamps. Also simultaneously displays test-related information including high-level coverage/memory error/bottleneck measuring and detection.
- Realizes linkage with IBM's configuration/fault management tools and other companies' products (MATLAB, Simulink, CodeComposerStudio).
- A dedicated editor for easy customization of target and compilation environments is included as standard.



your creativity

Compilers, Assemblers, Integrated Development Environments (1/2)

IAR Embedded Workbench (EW)

[Manufacturer] IAR Systems AB [Marketer] IAR Systems Company [Features]

♦ No. 1 in Europe

- Industry's top-level compiler that generates compact code
- Many include files that can be used immediately, various templates, and sample files supplied as standard
- Supports various RTOSs.



XASS-V Series

[Manufacturer/Marketer] GAIO TECHNOLOGY CO., LTD. [Features]

- Supplies seamless integrated development environment
- Easy modifying and building program and starting debugger with editor, compiler, and assembler under management of integrated development environment
- Low-cost monthly rental available
- Supports in-circuit emulators and RTOSs of many manufacturers

code | lab Debug

[Manufacturer/Marketer] Accelerated Technology

Mentor Graphics Division of Mentor Graphics Japan Co., Ltd.

[Features]

- Automatic trace function
- Kernel-aware debugging
- Configurable display windows for sources, memories, variables, registers, etc.
- Easy-to-use button bar interface learnable in a short time
- Complex breakpoints
- Consistent file viewer
- Stop watch for timing function
- ◆ Source file tracking
- ◆ Advanced dvnamic file exchange
- ◆ Advanced DLL interface

code | lab EDE

[Manufacturer/Marketer] Accelerated Technology Mentor Graphics Division of Mentor

Graphics Japan Co., Ltd.

[Features]

- Complete embedded development environment that speeds up development, compilation, building, and debugging
- ♦ Microsoft[®] Visual Studio[™]
- System construction possible using any commercially available tools
- Error display in window for quick editing
- Ships with settings completed to allow faster development
- Simple access to cross-development debugger
- Existing build system commands (make files, batch files, etc.) can be easily applied to code I lab EDE projects.

ZIPC

[Manufacturer/Marketer] Cats, Inc.

[Features]

- ◆ Japan's first CASE tool for embedded system development, using status transition table designing technique
- Designing with status transition table and dynamic verification at design (model) level. Improves productivity and product quality by early discovery and solution of problems in upstream process
- Dynamic verification at design (model) level including operation of RX850
- Automatic generation of ANSI C codes that can operate in accordance with design from design (model) that was proved to be "correct" by dynamic verification
- Debugging while checking both the target code and design (model) through coordination with ID850 and SM850
 Model-based dynamic verification log can be used as a test script of automatic verification system "XO850".



	eveCCC
 DE MULTI TimeMachine C++/EC++/C cross compiler Manufacturer] Green Hills Software, Inc. Marketer] Advanced Data Controls Corporation Features] MULTI Based on integrated GUI, GHS's MULTI provides a high-performance, easy-to-use integrated development environment. It provides a total support from programming to debugging and maintaining, helping shorten the development period and improve the performance and quality of the application program. TimeMachine By reversely executing a program based on trace data, complicated problems of real-time interferences with the application are made clear. Realizes execution analysis, such as profile, without extra codes for measurement. Compiler Conforms to ANCI/ISO9899. Also supports Japanese Automotive C and MISRA-C. Optimization can be set in function units, such as loop optimization and in-line optimization, as well as specification by purpose, such as emphasizing speed and size. 	 exeGCC [Manufacturer] Kyoto Microcomputer Corporation [Marketer] Kyoto Microcomputer Corporation Naito Densei Machida Mfg. Co., Ltd. Application Corporation NEC Micro Systems, Ltd. [Target devices] V850E1 core, V850E2 core, NU85E core, V850ES/ST2 [Features] Supports GNU C version 3.0. Supports C++. Also supplies EC++ library suitable for embedding. Porting optimized for Windows environment By optimizing and porting GNU C/C++ that runs in UNIX environment to Win32 of Windows, short compile time is realized and environment setting by GUI is provided. Original embedded library Develops new total library including a library conforming to ANSI C and a floating-point emulator library and supplies high operation per- formances. Supports Japanese. Comments and character strings in Japanese can be used.
 Can generate more efficient codes by expanding the bit manipulation instructions of the V850. 	 GNUPro™ [Manufacturer] Red Hat, Inc. [Marketer] Red Hat, Inc. [Features] Package including GNU assembler (gas), C/C++ compiler (gcc/g++), debugger (gdb), simulator and other utilities GNUPro is provided in accordance with the GNU General Public License (GPL). Supports available for GNU Pro for remuneration

IAR visualSTATE (graphical design tool)

[Manufacturer] Sweden IAR Systems AB

[Marketer] IAR Systems Company

[Target devices] All devices (no device dependency)

[Features]

Development tool that dramatically improves productivity, reliability, and maintainability of

- embedded software with the following functions
- ◆ Graphical design tool
- Prototyping tool
- Automatic/manual test tool
 Automatic and a second sec
- ◆ C/C++ code generation
- Graphical debugging with actual target
- Automatic document creation





Middleware (2/6)

NetFront[™], Compact NetFront[®], JV-Lite[®]2 [Manufacturer/Marketer] ACCESS Co., Ltd. [Features]

NetFront

- ◆ Internet module set including embedded web browsers such as for TVs and PDAs, Internet mail, TCP/IP modules, and a variety of drivers
- The browser includes a 300 KB kernel, complies with HTML 3.2, and provides support for frames. Parts of HTML 4.0 are also supported
- ◆ TCP/IP protocol stack AVE-TCPv6.0 for IPv6 is included as standard. Compact NetFront
- HTML browser optimized for mobile devices with small monochrome liquid crystal displays such as cellular phones, PHS, PDAs, and pagers
- ◆ HTML 4.0 subset functions are available with 150 KB of RAM and 300 KB of ROM

JV-Lite2

- ◆ Java VM (Virtual Machine) for embedded systems. Entirely compatible with Embedded Java[™], Personal Java[™] and J2ME CLDC1.0 + Profiles
- ◆ The virtual machine and class library are ROMable and available with 500 KB of ROM and 500 KB of RAM
- ◆ Can be provided as a plug-in of the Net Front browser or as a discrete JV-Lite2 unit

Nucleus FILE

[Manufacturer/Marketer] Accelerated Technology Mentor Graphics Division of Mentor Graphics Japan Co., Ltd.

[Features]

- ◆ FAT12/16/32 support including long file name handling
- ◆ Royalties unnecessary as C source code is included
- ♦ Reentrant file access
- ◆ ROM programming supported
- Support of multiple floppy discs and fixed discs
- File system format functions provided
- RAM disc driver provided free of charge
- Transparent CPU byte allocation
- Simple device driver interface
- ◆ Nucleus PLUS integration complete

Nucleus NET

[Manufacturer/Marketer] Accelerated Technology Mentor Graphics Division of Mentor Graphics Japan Co., Ltd.

[Features]

- ◆ Fully functional TCP/IP protocol stack
- Source code provided, no royalties
- Optimized for real-time applications
- ◆ Full integration with Nucleus PLUS for optimal performance
- Scalable configurations: IP, IP+UDP, IP+UDP+TCP
- Sockets API
- Compact (small footprint)
- ◆ RAW IP, IP Multicasting, IP Forwarding
- Ethernet drivers and serial driver templates
- ♦ PPP available
- Reentrant and ROMable
- ◆ Multiple protocols supported over same network device
- First class support and training

Nucleus WebServ

[Manufacturer/Marketer] Accelerated Technology Mentor Graphics Division of Mentor

Graphics Japan Co., Ltd.

[Features]

- Fully functional server in a tiny package
- ♦ HTTP 1.0/1.1 Support
- Dynamic Web page content (Allows Monitoring)
- Forms support (Allows Configuration)
- Content Independent (Supports Java Applets, Images, etc.)
- ◆ CGI (plug-in) support
- ◆ Server Side Include support (SSI)
- File upload (online document update)
- Flexible page storage (in memory or on disk)
- ◆ Supports multiple concurrent requests
- Basic authentication
- DES authentication
- Document compression

JAVA platform for embedded computing JBlend™ [Manufacturer/Marketer] Aplix Corporation

[Features]

- ◆ Java execution environment optimized for embedded application
- Practical performance with fewer resources
- Supports Java specifications (profile/extension) based on JavaME.
- Quickly supports new Java specification and manufacturer's original specification by sophisticated modularization and standardization.
- Existing software resources can be used as is, so that mounting on the OS/CPU you use is possible.
- ◆ Plans to participate in "platformOViA" partner program (as of July 2005).

Mobile PictDirect (MoPiD™)

[Manufacturer/Marketer] Aplix Corporation eSol Co., Ltd.

[Features]

- Realizes image printing by directly connecting a cellular phone and a printer.
- Conforms to PictBridge standard that has become widespread in the field of direct printing.
- Printer supporting PictBridge can be used regardless of the manufacturer and model.
- ◆ Can also be used from applications for printing.
- Requests for porting and customization can also be supported. The number of development processes can be decreased.

Middleware	(3/6)
------------	-------

Embedded software products [Marketer] AI Corporation

[Features]

[Manufacturer] Datalight

- FlashFX
- Driver for sector emulation with flash memory as disc drive
- Reliance
 ♦ File system supporting power failure

[Manufacturer] EBSnet, Inc.

RTFiles

- File system compatible with MS-Windows/power failure (Fail-safe function) support function
- UPnP SDK
- Conforms to UPnP Device Architecture version 1.0.

[Manufacturer] Extended Systems

- XTNDAccess Blue SDK
- Bluetooth protocol stack/Supporting CAN CCAP for automobile/Supporting many new protocols
- XTNDAccess Data Sync SDK
- Data synchronization/Conforming to OMA standard

[Manufacturer] Interpeak

- IPNET/IPLITE/IPSec
- ♦ IPv4/v6 dual stack

[Manufacturer] Mimer Information Technology AB Mimer SQL Mobile

SQL database engine for embedded system

[Manufacturer] Swell Software, Inc.

PEG

• GUI library for embedded system and GUI development environment

[Manufacturer] AINIX Corporation

- ImageStar QR/e
- Image processing & decoding of QR code (model 2) symbol

[Manufacturer] AI Corporation

Resizeable

- Scalable font engine for embedded system/Japanese Rodan (gothic) supplied
- SDIO card driver
- Control driver of SD memory card and SDIO card having SD expansion function
- Small media driver (SD/SDIO/MemoryStick/CF/MMC)
- Control driver of various flash media

Grousenet UPnP

[Manufacturer] SEC Corporation [Marketer] NEC Engineering, Ltd.

[Features]

- Conforming to UPnP Device Architecture Version 1.0
- Addressing, discovery, description, control, event, and presentation functions
- Supports μ ITRON as OS.
- ◆ Debug function
- Sample application also in package
- Source code supplied

Cantata++

[Manufacturer] Information Processing Ltd., England [Marketer] AI Corporation

[Features]

- ◆ Cantata++ is a standalone, combined test support tool.
- Standalone, combined test: Supporting host environment and target environment
- ◆ Test coverage analysis: Statement, branch, MC/DC, entry point, call return metric
- \blacklozenge GUI: Graphical analysis of test result and test creation with wizard
- Wrap, stub function: Simulating and controlling behavior of external functions



KASAGO TCP/IP (IPv4)-based development kit [Manufacturer/Marketer] Elmic Wescom, Inc.

[Features]

- High-speed TCP/IP protocol stack dedicated to embedded applications
- Support of ZERO Copy function
- ◆ Compact code size of about 100 KB
- ◆ Independent of CPU, OS, and compiler
- Supplied in source code conforming to ANSI C
- BSD4.4 socket I/F supported
- ◆ Wealth of optional software products such as PPP, SNMP, HTTPD, POP3&SMTP, and SIP

KASAGO IPv6 (IPv4/IPv6 Dual)-based development kit [Manufacturer/Marketer] Elmic Wescom, Inc. [Features]

[Features

- High-speed TCP/IP protocol stack supporting IPv6 and dedicated to embedded applications
- ◆ IPv6 Ready Logo Phase-2 approved
- Support of ZERO Copy function
- Compact code size of about 150 KB (IPv4/IPv6 Dual)
- Independent of CPU, OS, and compiler
- Supplied in source code conforming to ANSI C
- Many optional software products such as IPsec, SNMP, HTTPD, POP3&SMTP, and SIP





Middleware (4/6)

Coverage master winAMS

[Manufacturer/Marketer] GAIO TECHNOLOGY CO., LTD. [Features]

- Environment automating single module (function) test of software
- Comprehensively executes single test to improve module quality.
- Automatically executes and judges I/O test of any module.
- Automatic coverage test for obtaining quantitative data of coverage rate of module test



CasePlayer2

[Manufacturer/Marketer] GAIO TECHNOLOGY CO., LTD. [Features]

- Analyzes source code in C and assembler to automatically create various documents such as flowcharts and variable lists.
- Visualizes information of source code to accurately analyze existing software resources in a short time.
- Can also clarify source code review in a short time.



Fusion WebPilot

[Manufacturer] Unicoi Systems Inc.

[Marketer] Grape Systems Inc.

[Features]

- Communications middleware for various embedded applications
- Supplies royalty-free ANSI C source code
- ◆ Core WEB browser with small footprints
- Can be transplanted to all platforms.
- Conforming to HTTP 1.0, 1.1, and completely supporting cookies
- Supporting Japanese, GIF, GIF89a (animation GIF), JPEG, and BMP (non-compression)
- Supporting JavaScript (option)

No.1 System Simulator

[Manufacturer/Marketer] GAIO TECHNOLOGY CO., LTD. [Features]

- Next-generation simulation environment improving quality of embedded software
- Easily reproducing exception operations, interrupts, and timing events that are difficult to reproduce in verification using an actual machine, dramatically improving software quality
- Necessary simulation is automatically synthesized by only connecting model components on GUIs and thus can be organized in a short time.



Middleware series for embedded application (GRAPEWARE)

[Manufacturer/Marketer] Grape Systems Inc.

[Features] GR-USB series

- USB protocol stack for embedded applications
- Supplies royalty-free ANSI C source code.
- Supporting various real-time OSs, such as μITRON, NORTi, and ThreadX
- ◆ GR-USB/HOST, GR-USB/HOST II (host protocol stack)
- ◆ GR-USB/OTG (On-The-Go specification protocol stack)
- ◆ GR-USB/DEVICE (device protocol stack)
- ◆ GR-USB/FILE (USB mass storage integrated kit)
- Many class drivers
- New porting and development upon request possible
- GR-FILE
- ◆ FAT file system for embedded application (supporting FAT 12/16/32)
- ◆ Supplies royalty-free ANSI C source code.
- Supplies standard I/O interface in C compatible with POSIX.
- Consecutive direct I/O or cache method can be selected in accordance with file characteristics
- Designing independent of OS
- Function to set format/partition of file system
- Supplies sample format code dedicated to SD cards
- Supporting long file names and Shift JIS file names
- Supporting simultaneous multi-task accesses
- Supporting illegal plugging in and out of media

Middleware (5/6)

Cente middleware series

[Manufacturer/Marketer] Data Technology Co., Ltd. [Features]

- Middleware package for μ ITRON kernel
- Supplies 100% source code without project license and royalties.
- Flexible technical service (porting customization)
- Common modules available (ctkernel, shell, ctlib, crypto, Cente)

CentelPv6

- IPv4/IPv6 dual stack
- Expands API of ITRON TCP/IP specification to IPv6.

CentelPSec

- Usable in both IPv4/IPv6 environments
- ◆ Encryption algorithm: NULL, DES-CBC, 3DES-CBC, AES (RIJNDAEL)
- ◆ Authentication algorithm: MD5, SHA-1

CenteTCP/IPv4

◆ API of ITRON TCP/IP specification and original DD (DeviceDriverinterface) Cente HTTPd/c

- ◆ Both WEB server and client available
- ◆ Conforms to HTTP 1.0/1.1 (supported method: GET/HEAD/POST)
- Cente SMTP/POP
- ◆ Transmission/reception of E-mail by SMTP/POP3
- ◆ File data can be attached (CenteFileSystem is necessary).
- Cente PPP
- Supporting authentication of PAP/CHAP/MS-CHAPv2
- Supporting IP address setting with IPCP

Cente SNMP

◆ MIB, MIB-II provided as standard

Original MIB can be defined.

Cente SSL

- ♦ SSL library usable with CenteTCP/IPv4, CenteIPv6
- Cente 802.11g PRISM
- ◆ Supporting PRISMGT chip set
- Cente 802.11b PRISM
- ◆ Supporting PRISM2.0/2.5/3.0 chip set
- Cente USB 1.1 Device
- Transfer method: Control transfer/bulk transfer supported
- ◆ USB device driver sample for Windows supplied
- Cente Filesystem
- ◆ Protects recording data from power failure as much as possible.
- Supporting FAT12/16/32, VFAT, and hierarchical directory

Cente SD Card Driver

- Can organize/read/write FAT file system to SD memory card via SD memory card controller LSI.
- ◆ Fully supports SD memory card control commands.
- Cente SmartMedia Driver
- Conforms to SSFDC forum specifications and can organize/read/write FAT file system to commercially available SmartMedia.
- Supports SmartMedia standard control function commands.
- Cente NANDFLASH Driver
- ◆ Can organize/read/write FAT file system to on-board NANDEEPROM.

matrixQUEST series

[Manufacturer/Marketer] TEPCO UQUEST, LTD. [Features]

matrixUSB (USB host driver)

- Supports high-speed operation and OTG
- Supports various controllers and classes
- matrixDPS (PictBridge software)
- Provided for printers and digital cameras respectively
- Tested for logo recognition via supplied sample application
- Emulation function enables development of applications without actual devices

matrixNET (TCP/IP dual stack)

- ◆ Full scratch IPv4/v6 dual stack
- ◆ IPsec/IKE is provided as standard
- matrixWLAN (wireless LAN driver)
- Supports Conexant's PRISM2/3 and Atheros's AR500x chips
- ◆ Supports WPA
- ◆ Can be provided with matrixNET
- matrixFS (various file systems)
- Products that supports FAT12/16/32, VFAT, ISO9660, and UDF file systems are provided
- ◆ Supports Japanese file names
- Provides cache library common to various file systems
- matrixXML/XHTML Browser
- Compact browser for viewing XHTML Basic content
- Lightweight and fast by using SAX Parser and minimum required CSS Parser (Level 1 subset)
- Can be combined with matrixNET and matrixFS

EmbeddedWare series

- [Manufacturer/Marketer] Nissin Systems, Co., Ltd.
- ◆ USNetPlus (super small embedded TCP/IP stack)
- ◆ USFilesPlus (super small embedded FAT file system)
- EW-SSL (super small embedded SSL)
- ◆ EW-SSH (super small embedded SSH)

[Manufacturer] Pocket Soft, Inc.

[Marketer] MONET

- EW-RTPatch (differential upgrading)
- [Features]
- USNet Plus (embedded TCP/IP stack)
- ◆ Supporting radio LAN802.11b
- USFilesPlus (embedded FAT file system)
- Supporting SD memory card
- EW-SSL (super small embedded SSL)
- ◆ Supporting SSL Ver3
- EW-SSH (super small embedded SSH)
- Supporting SSH Ver2
- EW-RTPatch (differential upgrading)
- High-speed, safe upgrading of differential/compression/authentication


Middleware (6/6)

CANopen Master source code

CANopen Slave source code

[Marketer] Vector Informatik GmbH

Vector Japan Co., Ltd.

[Target devices] V850ES

- [Features]
- Protocol stack widely employed in Europe, especially in Germany where CANopen was originated
- Embedded source code for developing CANopen Master or slave device
- ◆ Operation confirmed, including driver for on-chip CAN controller of V850
- Can be customized by user in accordance with user device specifications.
- Development efficiency can be further enhanced by also using development support tools such as CANerator and CANoe.

SYSTEM COMPONENT for ECHONET

[Manufacturer/Marketer] YASUKAWA INFORMATION SYSTEMS Corporation [Features]

- ◆ Easily realizes Echonet (home network) system development.
- ◆ Can freely combine various components of Echonet middleware layer.
- Lightweight suitable for embedded system
- Can also support application development for various Echonet systems.

Flash Memory Programmer (1/2)

Stick Writer SW-850SX2

[Manufacturer/Marketer] Application Corporation [Target devices] V850/SG2

[Features]

- ◆ Compact size directly connectable to USB connector
- No external power supply needed
- Operable with only target power supply
- ◆ Operable with USB bus power
- Operable in standalone mode
- Easy operation guided by Japanese messages
- Error log storage function helping you to analyze write errors

Programming system Y1000-8

[Manufacturer/Marketer] Wave Technology Co., Ltd. [Target devices] V850E/MA1, V850/SV1, V850/SB1 (70F3032A, 70F3033A), V850/SB2 (70F3035A, 70F3037A),

V850E/IA1 (70F3116)

[Features]

- Gang programmer enabling simultaneous programming and verification of up to 8 devices
- Enables reading of master data directly from floppy disk to internal memory
- Data dump display and editing functions
- Master data storable on internal hard disk
- Emphasizes simple and effortless operation via touch panel and workability via PASS/FAIL display, checksum display, and task count display supporting sockets



Flash Gang Forward FL-G01

[Manufacturer] Hong Kong Forward Electric Co., Ltd. [Marketer] Application Corporation [Target devices] V850/SA1, V850/SB1, V850/SF1, V850E/MA1, V850E/MA3, V850ES/KG1

- ◆ USB (V1.1) supported as host machine interface
- ◆ Can also operate in standalone mode by using compact flash.
- Up to eight programs can be written simultaneously (eight optional adapter boards are necessary).
- ◆ Low price





Flash Memory Programmer (2/2)

FlashPRO IV FL-PR4

[Manufacturer/Marketer] Naito Densei Machida Mfg. Co., Ltd. [Features]

- Supports programming of all NEC Electronics microcontrollers with on-chip flash memory
- ◆ USB support via host machine interface
- ◆ LCD panel allows checking of programmer setting information, error messages, checksum values, etc., even when used as a standalone unit.
- Two user codes can be downloaded and valid code selection is supported.
- Device-specific information required for programming can be freely set using parameter files.
- On-board programming and programming via a program adapter are possible.
- Portable A5 size
- Easily operable both as a standalone unit or on Windows 95/98/Me/2000/XP and Windows NT 4.0 by using dedicated application (FlashPro4)

NET IMPRESS series

[Manufacturer/Marketer] Yokogawa Digital Computer Corporation

[Target devices] V850E/IA1 (µPD70F3116), V850/SB1 (µPD70F3030B, µPD70F3032A, µPD70F3032B, µPD70F3033, µPD70F3033A, µPD70F3033B), V850/SB2 (µPD70F3037A), V850/SA1 (µPD70F3017A), V850/SC3 (µPD70F3089Y), V853 (µPD70F3003A, µPD70F3025A), V850E/MS1 (µPD70F3102A), V850E/MA1 (µPD70F3107), V850E/IA2 (µPD70F3114), V850ES/KF1 (µPD70F3210), V850ES/SA2 (µPD70F3201), V850ES/SA3 (µPD70F3204), V850ES/SG2 (µPD70F3261, µPD70F3263, µPD70F3271, µPD70F3273, μPD70F3281, μPD70F3283), V850ES/SJ2 (μPD70F3264, μPD70F3266, μPD70F3274, μPD70F3276, μPD70F3284, μPD70F3286, μPD70F3288), V850ES/FE2 (μPD70F3231), V850ES/FF2 (μPD70F3232, μPD70F3233), V850ES/FG2 (µPD70F3234, µPD70F3235, µPD70F3236), V850ES/FJ2 (µPD70F3237, µPD70F3238, µPD70F3239)

[Features]

- Enables programming with various manufacturers' microcontrollers (various programming specifications) with on-chip flash memory solder-mounted onto the user system
- ◆ General-purpose keys on one control module Supports parameter changes for microcontrollers in same series Supports licensing of definitions from microcontrollers in different series
- Able to operate via a host machine or as a stand-alone device
- ◆ Full lineup of software available as free downloads
- ◆ Flash programming using CAN interface, widely employed in automobiles, is possible (C"arNETIMPRESS).



C"arNETIMPRESS

Emulators (1/5)

TimeMachine, SuperTrece Probe

[Manufacturer] Green Hills Software, Inc. [Marketer] Advanced Data Controls Corporation

[Target devices] V850E, V850ES

[Features] TimeMachine

- ◆ Clarifies complicated problems of real-time interference with applications by reversely executing programs based on trace data.
- ◆ Realizes execution analysis, such as profiles, without extra codes for measurement.

SuperTrace Probe

- ◆ Trace buffer of up to 1 GB that can completely collect data with a clock exceeding 300 MHz (however, up to 160 MHz if IECUBE is used)
- Can easily realize execution analysis of program subject to several 100 millions or more of trace frames when used with TimeMachine.
- TimeMachine and SuperTrace Probe in V850 environment requires IECUBE supporting options.





Emulators (2/5)

PARTNER-Jet

[Manufacturer] Kyoto Microcomputer Corporation [Marketer] Kyoto Microcomputer Corporation Naito Densei Machida Mfg. Co., Ltd. Application Corporation NEC Micro Systems, Ltd. [Target devices] V850E/MA1, V850E/MA2, NU85E core (may be added at any time)

[Features]

- ◆ Super high-speed download
- Via JTAG: With V850E/ME2 connected: 2.8 MB/s, JTCK = 51.344 MHz With ROM emulation probe: 10 MB/s
- ◆ Host interface of all models supports USB 2.0/1.1. Model30 also supports LAN (100Base-TX/10Base-T).
- ◆ High-capacity trace memory (up to 18 Mb, Model30)
- Supporting high-speed trace clock (200 MHz)
- Option supporting high-capacity emulation memory (Model20/30) High capacity (4 MB to 64 MB), high access speed: 30 ns
- Low price

From 198,000 yen (207,900 yen, including consumption tax)



UniSTAC II

[Manufacturer/Marketer] Sophia Systems Co., Ltd. [Features]

- ◆ Supporting N-Wire interface
- Downloading to flash memory
- Hardware break settable
- ◆ Software break (without limit) settable
- Branch trace function (256K steps)
- ◆ Debugger WATCHPOINT supporting C/C++ language supplied as standard
- Host connection with USB/LAN



PARTNER-ET II

[Manufacturer] Kyoto Microcomputer Corporation

- [Marketer] Kyoto Microcomputer Corporation Naito Densei Machida Mfg. Co., Ltd.
 - Application Corporation
 - NEC Micro Systems, Ltd.

[Target devices] V850 core, processor incorporating V850E core [Features]

- Debug tool of ROM in-circuit type enabling debugging with microcontroller without N-Wire function
- Tracing program executed on emulation memory
- Super high downloading speed of 4 MB/s
- Supporting network interface of 100Base-TX/10Base-T
- Hardware break and profile functions provided
- ◆ Available option of on-chip debugging by N-Wire connection



ND-V850ES Series

[Manufacturer/Marketer] Naito Densei Machida Mfg. Co., Ltd. [Target devices] V850ES/KF1, V850ES/KG1, V850ES/KJ1, V850ES/SG2 (under development),

V850ES/SJ2 (under development)

- Low price (sold as a set of hardware + debugger)
- Simple-connection USB interface
- ◆ High-performance debugger supporting NEC Electronics development environment
- Realizes manipulatability equivalent to NEC Electronics ID debugger
- ◆ High device equivalence by using NEC Electronics dedicated in-circuit-emulator chipset
- Provides real-time trace/real-time RAM monitor function
- Supports NEC Electronics compiler/project manager
- Space-saving type that can be used lying down or standing up
- ◆ Lineup of low-price, high-flexibility dedicated probes (NP-CX Series: Sold separately)



Emulators (3/5)	
 ND-V850 Series, ND-V850E Series Manufacturer/Marketer] Naito Densei Machida Mfg. Co., Ltd. Target devices] V850/SB1, V850/SB2, V850/SA1, V850E/MA1, V850E/IA1 Features] Low price (sold as a set of hardware + debugger) On-chip host interface (LPT port) High-performance debugger supporting NEC Electronics development environment Realizes manipulatability equivalent to NEC Electronics ID debugger High device equivalence by using NEC Electronics dedicated in-circuit-emulator chipset Provides real-time trace/real-time RAM monitor function Supports NEC Electronics compiler/project manager Space-saving type which can be used lying down or standing up 	
RTE Series Manufacturer] Midas Lab, Co., Ltd CORE Corporation Target devices] N-Wire-supporting micronontrolles in the V853, V853A, V850/SA1, V850/SB1, V850/SB2, V850E2/ME3, V850E/IA1, Nx85ET, NA85E2, AS85EP2, V850ES/E/E2 Series Features] TTE-V850x-IE series Vill ICE series of in-circuit type emphasizing reduction in size and weight as dedicated emulator 0 GHS's "MULTI" and Midas Lab's "Partner" can be used as debuggers. Peleases all resources of processor and supports all operation modes. Provided with emulation memory as standard Releases all resources of processor and supports all operation modules and realizes a high degree of reedom and expandability of component configuration Equipped with high-speed JTAG circuit (66 MHz min.) Supporting high-speed N-Trace (333 MHz to 400 MHz) High-capacity trace memories (36 Mb to 144 Mb) Many options • High-capacity, high-speed emulation memory (35 ns, 64 bits, 128 MB) • Envolation memory supporting high-speed synchronous flash • Probe supporting 48-bit width N-Trace • External bus trace unit (various [/Fs) • High-speed download probe (bus connection type) • Low voltage (1.2 V min.) • LAWUSB-IF equipped as standard (100 Mbps/480 Mbps) • Many debuggers usable • High-speed f	

Emulators (4/5)

Code Debugger for V850

[Manufacturer/Marketer] BITRAN CORPORATION [Target devices] V850E/ME2, V850ES/SG2, V850E/MA3, Nx85ET [Features]

- ◆ Low-cost emulator that supports N-Wire interface
- ◆ Enables support using only one code debugger in a CPU or Nx85ET core equipped with the V850E1 or V850ES DCU (Debug Control Unit)
- ◆ Complies with LAN and USB2.0 host interfaces as standard
- Supports NEC Electronics compilers as well as various compilers made by other manufacturers
- Supports programming to internal or external flash memory (over 800 models)

EMUSE-G II

[Manufacturer] CATS, Inc. [Marketer] Midoriya Electric Co., Ltd.

[Features]

- ◆ Address/data bus monitoring with ROMprobe alone
- Also usable as logic analyzer
- High-capacity emulation memory (8 MB)
- High-speed downloading (about 75 times that of vsEMUSE, 1 MB/5 s)
- ◆ Supporting GHS's MULTI



our creativity

advicePOCKET

[Manufacturer/Marketer] Yokogawa Digital Computer Corporation [Target devices] V850E/ME2, V850E/MA3, V850E2/ME3 [Features]

- ◆ Easy connection supporting N-Wire interface
- Power supply-less operation supporting USB Vbus (JTAG model)
- Branch PC trace/data trace by N-Wire
- Maximum frequency: 100 MHz (trace model)
- * Support depends on MPU.
- Can write external flash memory.
- Can write on-chip flash memory (V850E/MA3)
- Debugger: microVIEW-PLUS dedicated to advicePOCKET supplied as standard



advice PLUS

[Manufacturer/Marketer] Yokogawa Digital Computer Corporation [Target devices] V850ES/KF1, V850ES/KG1, V850ES/KJ1: (Full-ICE) NU85ET, NB85ET, NA85E2, V850E/ME2, V850E2/ME3: (OCD tool)

- Option module support enables selection of only necessary functions
- Supports large-capacity emulation memory
- ◆ Supports trace analysis function of up to 32K samples
- Supports a range of measuring functions
 Profile measuring, two-point execution time measuring, coverage measuring
 * Option module used depending on device.
- Enables writing to external flash memory (OCD tool)
- Supports N-Wire interface (OCD tool)
- ◆ Debugger: Supports microVIEW-PLUS



Emulators (5/5)

MJX330, MJX440, SSX850

[Manufacturer/Marketer] ZAX Division, Lightwell Co., Ltd.

[Target devices] V850/SA1, V850/SB1, V850E/MA1, V850E/MA2, V850E/IA1, V850E/IA2, V850E/IA2, V850E/ME2, NB85E

[Features]

MJX330 for NB85E

- ◆ Card-type JTAG interface debugger
- ◆ Supported devices: V850E/ME2, NB85E
- ◆ Lightweight and compact JTAG emulator of PC card type with excellent portability
- ◆ JTAG emulator with high cost effectiveness, reducing cost while supporting JTAG debug function
- Supports integrated development environment MULTI of Green Hills Software.
- Writing to external general-purpose flash is supported.
- High-speed downloading (440 KB/s max.)

MJX440 for V850E/ME2

- ◆ High-performance JTAG interface debugger
- ◆ Supported devices: V850E/ME2, NB85E
- ◆ High-speed download: 440 KB/s
- Conforms to GHS integrated development environment MULTI
- ◆ ROM emulation function
- ◆ Real-time trace function
- \blacklozenge Supports PC operating on Windows 98/ME, Windows NT 4.0/2000, and Windows XP
- SSX850 Series
- ◆ Low-cost V850 in-circuit emulator
- ◆ Supported devices: V850/SA1, V850/SB1, V850E/MA1, V850E/MA2, V850E/IA1, V850E/IA2
- ◆ Conforms to GHS integrated development environment MULTI
- Real-time trace function
- On-chip flash memory programmer
- ◆ Supports PC operating on Windows 98/ME, Windows NT 4.0/2000, and Windows XP







Evaluation Board, Evaluation Kits (1/3)

TK-850 Series

[Manufacturer/Marketer] Application Corporation [Target devices] V850ES/SG2, V850/KJ1+ [Features]

- Various software products necessary for development also supplied
 Low price
- Easy-to-use, as tutorial and sample programs available
- ◆ Compact, name card-size



TK-850/SG2+NET

[Manufacturer/Marketer] Application Corporation [Target devices] V850/SG2 [Features]

TCP/IP stack that can operate only with internal memory of V850

- Necessary items (AC adapter, serial cable, and Ethernet cross cable) in package
- Not only TCP/IP but also HTTP protocol, mail protocol (POP3, SMTP), and sampling application using these are stored in ROM.
- C compiler, debugger, and flash programmer are also packed as development environments.

Evaluation Board, Evaluation Kits (2/3)

CEB-V8xx

[Manufacturer/Marketer] Cosmo Co., Ltd.

[Target devices] V850E/MA1, V850E/MA3, V850E/IA1, V850/SA1, V850/SB1, V850ES/SJ2, V850ES/FJ2 [Features]

- V850E/MA1, V850/SA1, and V850/SB1 include evaluation board, PARTNER monitor-debugger, and GNU compiler exeGCC evaluation versions in a single low-price package
- V850E/MA3, V850E/IA1, V850ES/SJ2, and V850ES/FJ2 include evaluation board and NEC Electronics development tool in a single low-price package
- ◆ RISC chip performance can be experienced by a simple serial PC connection
- ◆ Compact board design measuring just 137 × 86 mm (V850E/MA1, V850/SA1, V850/SB1), 140 × 85 mm (V850E/MA3), *φ*150 mm (V850E/IA1), 150 × 125 mm (V850ES/SJ2, V850ES/FJ2)
- External fetchability of CPU signals facilitates expansion
- ◆ Includes connector for writing to CPU's on-chip flash memory

KBCR-CB2

[Manufacturer] Shikino High-Tech Co., Ltd. [Marketer] Shikino High-Tech Co., Ltd., ZENIC, Inc. [Target devices] V850E/MA1, V850E/ME2 [Features]

The KBCR-CB2 image processing evaluation kit is a reference board that includes full-motion capture, sensing, and compression processing functions as well as multiple communication ports. This product not only facilitates the development of various surveillance

camera systems but is also a useful evaluation kit for developing image processing system algorithms.

 Various image processing functions such as object sensing and color sensing for sensing functions, and JPEG for image compression functions (ZENIC's ZEN3001F image processing LSI for sensor cameras is used for image processing)

- ◆ Camera inputs include CMOS digital and NTSC inputs, enabling up to 4 channels of multi image control
- Uses Ethernet (or optional wireless LAN) as network interface, and also includes serial communication port and extended bus
- ◆ Real-time OS complies with µITRON 4.0 specification and TCP/IP is implemented (uses MiSPO's NORTi)

μ T-Engine/V850E-MA3 development kit

[Manufacturer/Marketer] Personal Media Corporation [Target devices] V850E/MA3

[Features]

- Kit based on μ T-Engine specification promoted by T-Engine project
- All software necessary for program development, such as driver, sample application, and development environment, as well as real-time OS "PMC T-Kernel" that makes the best use of 20 years of experience of Tron project, are supplied. Some source codes are also supplied.
- Detailed technical information related to hardware and circuit diagrams also attached





our creativity

RTE Series

[Manufacturer] Midas Lab, Co., Ltd [Marketer] Naito Densei Machida Mfg. Co., Ltd. CORE Corporation

[Target devices] V853, V850E/MS1, V850E/MA1, V850E/ME2, V850E2/ ME3, V850ES/SA3

- ♦ Monitor support for MULTI from GHS and NEC Electronics' PARTNER
- ◆ High-speed program transfer via PC bus connection (except CB se-
- ries) • Connectable via serial communication (RS-232-C)



Evaluation Board, Evaluation Kits (3/3)

Giraffe

[Manufacturer/Marketer] Mikasa Shoji Co., Ltd [Target devices] V850E/ME2

[Features]

- Supports LAN, compact flash memory card, and USB based on the high-speed (operating frequency: higher than100 MHz) RISC microcontroller (V850E/ME2), and realizes a very adaptable platform.
- ◆ Optional 5.5 inch color LCD board selectable
- Enables development specialized for audio/visual functions which features A/V I/ O connecting NTSC video encoder/decoder and audio ADC/DAC.





GT200 series

[Manufacturer/Marketer] Yokogawa Digital Computer Corporation [Target devices] V850E/IA1

- Starter kit evaluating FlexRay next-generation automobile LAN mounting V850E/ IA1
- ◆ Robert Bosch GmbH's IP (FPGA version) as FlexRay controller
- Philips' FlexRay driver mounted on physical layer
- Enables establishing an appropriate environment for FlexRay system introduction instruction and waveform monitoring of communication operation and output signals.





Partner Contact Information - Support in Japan (1/2)					
Contact		TEL	FAX		
IAR Systems Company		81-3-5298-4800	81-3-5298-4801		
E-mail: info@iarsys.co.jp					
URL: http://www.iarsys.co.jp					
ACCESS Co., Ltd. E-mail: adinfo@access.co.jp		81-3-3233-0200	81-3-3233-0222		
URL: http://www.access.co.jp/					
Advanced Data Controls Corporation		81-3-3576-5351	81-3-3576-1772		
E-mail: sales@adac.co.jp					
URL: http://www.adac.co.jp/ Application Corporation		81-42-732-1377	81-42-732-1378		
E-mail: info@apply.co.jp		01-42-752-1577	01-42-732-1370		
URL: http://www.apply.co.jp/					
Aplix Corporation		81-3-3207-6575	81-3-3204-6450		
E-mail: http://www.aplixcorp.com/en/contact/index.html					
URL: http://www.aplix.co.jp/ Wave Technology Co., Ltd.		81-3-5304-1885	81-3-5304-1886		
E-mail: sales@y1000.com		010004-1000	010000-1000		
URL: http://www.y1000.com/					
Al Corporation		81-3-3493-7981	81-3-3493-7993		
E-mail: sales@aicp.co.jp					
URL: http://www.aicp.co.jp/ NEC Micro Systems, Ltd.		81-44-722-8194	81-44-733-9054		
E-mail: si-info@nms.necel.com					
URL: http://www.nms.necel.com					
NEC Engineering, Ltd.	81-4-7185-7707	81-4-7185-7881			
E-mail: dsi-sales@nece.jp.nec.com URL: http://www.nec-eng.com/pro/grousenet/					
Elmic Wescom, Inc.		81-120-045-690	81-45-650-1021		
E-mail: info@elwsc.co.jp	81-45-664-5171				
URL: http://www.elwsc.co.jp/					
GAIO TECHNOLOGY CO., LTD.	81-3-3662-3041	81-3-3662-3043			
E-mail: info@gaio.co.jp URL: http://www.gaio.co.jp/					
CATS, Inc.		81-45-473-2816	81-45-473-2673		
E-mail: info@zipc.com					
URL: http://www.zipc.com/					
Kyoto Microcomputer Corporation E-mail: jp-info@kmckk.co.jp	Head office	81-75-335-1050	81-75-335-1051		
URL: http://www.kmckk.co.jp/	Tokyo office	81-3-5157-4530	81-3-5157-4531		
Grape Systems, Inc.		81-45-222-3761	81-45-222-3760		
E-mail: middle@info.grape.co.jp (Middleware)					
threadx@info.grape.co.jp (OS) URL: http://www.grape.co.jp/					
C-ICE Sales Division, CORE Corporation		81-3-3795-5171	81-3-3795-5170		
URL: http://www.core.co.jp/					
Cosmo Co., Ltd.		81-3-3449-2194	81-3-3449-2197		
URL: http://www.cosmo.co.jp/ Shikino High-Tech Co.,Ltd.	81-6-6221-0850	81-6-6221-0859			
E-mail: sales@po.shikino.co.jp	01-0-0221-0000	01-0-0221-0000			
URL: http://www.shikino.co.jp/oosaka/index.html					
ZENIC Inc. 81-77-543-2101 81-77-543-9431					
E-mail: mailto:support@zenic.co.jp URL: http://www.zenic.co.jp/j1/pro_zen3001f.htm					
Marketing Group, Planning Division, Sophia Systems Co., Ltd.		81-44-989-7245	81-44-989-7005		
E-mail: market@sophia-systems.co.jp					
URL: http://www.sophia-systems.co.jp/					
Data Technology Inc.		81-42-523-1177	81-42-523-7070		
E-mail: sales@cente.jp URL: http://www.cente.jp					
]		

Partner Contact Information - Support in Japa			
Contact	TEL	FAX	
Tokyo Eletech Corporation	81-3-5295-1661	81-3-5295-1663	
E-mail: info@tetc.co.jp			
URL: http://www.tetc.co.jp/	04.0.0500.5551		
TEPCO UQUEST, LTD.		81-3-3580-5501	81-3-3580-5509
E-mail: sales@uquest.co.jp			
URL: http://www.uquest.co.jp Naito Densei Machida Mfg. Co., Ltd.		81-45-475-4191	81-45-475-4091
E-mail: info@ndk-m.co.jp		01-40-470-4191	01-40-470-4091
URL: http://www.ndk-m.co.jp/asmis/			
	stern Japan	81-3-5807-5931	81-3-3839-0112
E-mail: mid-sales@co-nss.co.in			
URL: http://www.co-nss.co.jp/	estern Japan	81-75-344-7881	81-75-344-7887
IBM Japan, Ltd.		81-3-5642-9100	81-3-5642-9120
E-mail: RATLASK@jp.ibm.com			
URL: http://www.ibm.com/jp/software/rational/			
Personal Media, Inc.		81-3-5475-2185	81-3-5475-2186
E-mail: te-sales@personal-media.co.jp			
URL: http://www.personal-media.co.jp/te			
ICE Division, BITRAN CORPORATION		81-48-556-9881	81-48-556-9591
E-mail: ice-sales@bitran.co.jp			
URL: http://www.bitran.co.jp/ice/			
Open Network Division, Vector Japan Co., Ltd.		81-3-5769-6974	81-3-5769-6975
E-mail: mailto:CANopen@vector-japan.co.jp			
URL: http://www.vector-japan.co.jp/products/canopen.html			
Sales Division, Vector Japan Co., Ltd.		81-3-5769-6980	81-3-5769-6975
E-mail: mailto:sales@vector-japan.co.jp			
URL: http://www.vector-japan.co.jp/			
Midas Lab, Co., Ltd.		81-3-3357-2589	81-3-3357-8029
E-mail: support@midas.co.jp			
URL: http://www.midas.co.jp	04 0 00 40 0770	04.0.0040.0750	
Sales Engineering Division, Mikasa Shoji Co.,Ltd	81-6-6946-3773	81-6-6946-3753	
E-mail: info-d1@mikasa.co.jp			
URL: http://www.mikasa.jp/		01.0.5007.0014	01.0.5007.0010
System Engineering Center, Midoriya Electric Co., Ltd.	81-3-5907-2814	81-3-5907-2819	
E-mail: emuse_support@sec.midoriya.co.jp			
URL: http://www.midoriya.co.jp/		81-44-829-3381	81-44-829-3382
MiSPO, Inc.		01-44-029-3301	01-44-029-3302
E-mail: sales@mispo.co.jp			
URL: http://www.mispo.co.jp/ Accelerated Technology Mentor Graphics Division, Mentor Graphics Japan Co., Ltd.		81-3-5488-3041	81-3-5488-3032
E-mail: jpn info@acceleratedtechnology.com		01-3-3400-3041	01-3-3400-3032
URL: http://www.acceleratedtechnology.jp/ YASKAWA INFORMATION SYSTEMS Corporation		81-44-952-8918	81-44-952-8921
E-mail: echonet@ysknet.co.jp			
URL: http://www.ysknet.co.jp/product/johokaden/echonet			
advice Division, Yokogawa Digital Computer Corporation		81-42-333-6222	81-42-352-6107
E-mail: info-advice@yokogawa-digital.com			
URL: http://www.yokogawa-digital.com/			
Instruments Business Division, Yokogawa Digital Computer Corporation		81-42-333-6224	81-42-352-6109
E-mail: info-impress@yokogawa-digital.com			
URL: http://www.yokogawa-digital.com/			
Automotive Instruments Business Division, Yokogawa Digital Computer Corporation	81-42-333-6239	81-42-352-6106	
E-mail: info-mvi@yokogawa-digital.com			
URL: http://www.yokogawa-digital.com/			
ZAXTEX Division, Lightwell Co., Ltd.		81-3-3392-3331	81-3-3393-3878
E-mail: zaxsales@lightwell.co.jp			
URL: http://www.lightwell.co.jp/zax/			
Red Hat, Inc.		81-3-6406-9900	81-3-6406-9901
E-mail: embedded-jp@redhat.com			
URL: http://www.jp.redhat.com/			



Company Name (Japanese) Accelerated Technology Japan Embedded Systems Division of Mentor Graphics Japan Co., Ltd. Al Corporation Aplix Corporation CORE Corporation Express Logic,Inc	Area Worldwide U.S.A. Europe, Middle East, Africa Asia Pacific Other countries U.S.A. Japan Worldwide	Company Name (Spot) Accelerated Technology, Embedded Systems Division of Mentor Graphics info@acceleratedtechnology.com http://www.acceleratedtechnology.com/ATI/contact.php http://www.mentor.com/embedded AI Corporation sales@aicp.co.jp Aplix Corporation of America www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ Aplix Europe GmbH www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/n/contact/general/ http://www.aplix.co.jp/ CORE Corporation MICROTEK INTERNATIONAL, INC. Grape Systems Inc.	TEL 1-251-208-3400 Toll-free: 800-468-6853 (US only) 81-3-3493-7981 1-415-558-8800 49-89-2420759-0 886-2-2776-1680 81-3-3795-5171 1-310-687-5826	FAX 1-251-208-7074 1-251-208-7074 81-3-3493-7993 1-415-558-8822 49-89-2420759-5 886-2-2776-1380 81-3-3795-5170
Embedded Systems Division of Mentor Graphics Japan Co., Ltd. Al Corporation Aplix Corporation	Worldwide U.S.A. Europe, Middle East, Africa Asia Pacific Other countries U.S.A. Japan	Embedded Systems Division of Mentor Graphics info@acceleratedtechnology.com http://www.acceleratedtechnology.com/ATI/contact.php http://www.mentor.com/embedded AI Corporation sales@aicp.co.jp Aplix Corporation of America www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ Aplix Europe GmbH www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/ncontact/general/ http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/ncontact/general/ http://www.aplix.co.jp/ MICROTEK INTERNATIONAL, INC.	Toll-free: 800-468-6853 (US only) 81-3-3493-7981 1-415-558-8800 49-89-2420759-0 886-2-2776-1680 881-3-3795-5171	81-3-3493-7993 1-415-558-8822 49-89-2420759-5 886-2-2776-1380
Mentor Graphics Japan Co., Ltd. AI Corporation Aplix Corporation CORE Corporation	U.S.A. Europe, Middle East, Africa Asia Pacific Other countries U.S.A. Japan	Graphicsinfo@acceleratedtechnology.comhttp://www.acceleratedtechnology.com/ATI/contact.phphttp://www.mentor.com/embeddedAl Corporationsales@aicp.co.jpAplix Corporation of Americawww.aplix.co.jp/en/contact/general/index.htmlhttp://www.aplix.co.jp/Aplix Europe GmbHwww.aplix.co.jp/en/contact/general/index.htmlhttp://www.aplix.co.jp/iaSolution Inc.index.htmlwww.aplix.co.jp/CORE CorporationMICROTEK INTERNATIONAL, INC.	800-468-6853 (US only) 81-3-3493-7981 1-415-558-8800 49-89-2420759-0 886-2-2776-1680 81-3-3795-5171	49-89-2420759-5 886-2-2776-1380
Al Corporation Aplix Corporation	U.S.A. Europe, Middle East, Africa Asia Pacific Other countries U.S.A. Japan	info@acceleratedtechnology.com http://www.acceleratedtechnology.com/ATI/contact.php http://www.mentor.com/embedded AI Corporation sales@aicp.co.jp Aplix Corporation of America www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ Aplix Europe GmbH www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/ CORE Corporation MICROTEK INTERNATIONAL, INC.	(US only) 81-3-3493-7981 1-415-558-8800 49-89-2420759-0 886-2-2776-1680 81-3-3795-5171	49-89-2420759-5 886-2-2776-1380
Aplix Corporation	U.S.A. Europe, Middle East, Africa Asia Pacific Other countries U.S.A. Japan	http://www.acceleratedtechnology.com/ATI/contact.php http://www.mentor.com/embedded AI Corporation sales@aicp.co.jp Aplix Corporation of America www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ Aplix Europe GmbH www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/ CORE Corporation MICROTEK INTERNATIONAL, INC.	81-3-3493-7981 1-415-558-8800 49-89-2420759-0 886-2-2776-1680 81-3-3795-5171	49-89-2420759-5 886-2-2776-1380
Aplix Corporation	U.S.A. Europe, Middle East, Africa Asia Pacific Other countries U.S.A. Japan	http://www.mentor.com/embedded All Corporation sales@aicp.co.jp Aplix Corporation of America www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ Aplix Europe GmbH www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/ncontact/general/ http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/ncontact/general/ http://www.aplix.co.jp/ GORE Corporation MICROTEK INTERNATIONAL, INC.	1-415-558-8800 49-89-2420759-0 886-2-2776-1680 81-3-3795-5171	49-89-2420759-5 886-2-2776-1380
Aplix Corporation	U.S.A. Europe, Middle East, Africa Asia Pacific Other countries U.S.A. Japan	Al Corporation sales@aicp.co.jp Aplix Corporation of America www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ Aplix Europe GmbH www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/, www.iasolution.net/ CORE Corporation MICROTEK INTERNATIONAL, INC.	1-415-558-8800 49-89-2420759-0 886-2-2776-1680 81-3-3795-5171	49-89-2420759-5 886-2-2776-1380
Aplix Corporation	U.S.A. Europe, Middle East, Africa Asia Pacific Other countries U.S.A. Japan	sales@aicp.co.jp Aplix Corporation of America www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ Aplix Europe GmbH www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/, www.iasolution.net/ CORE Corporation MICROTEK INTERNATIONAL, INC.	1-415-558-8800 49-89-2420759-0 886-2-2776-1680 81-3-3795-5171	49-89-2420759-5 886-2-2776-1380
CORE Corporation	Europe, Middle East, Africa Asia Pacific Other countries U.S.A. Japan	Aplix Corporation of America www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ Aplix Europe GmbH www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/, www.iasolution.net/ CORE Corporation MICROTEK INTERNATIONAL, INC.	49-89-2420759-0 886-2-2776-1680 81-3-3795-5171	49-89-2420759-5 886-2-2776-1380
CORE Corporation	Europe, Middle East, Africa Asia Pacific Other countries U.S.A. Japan	www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ Aplix Europe GmbH www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/, www.iasolution.net/ CORE Corporation MICROTEK INTERNATIONAL, INC.	49-89-2420759-0 886-2-2776-1680 81-3-3795-5171	49-89-2420759-5 886-2-2776-1380
	Middle East, Africa Asia Pacific Other countries U.S.A. Japan	http://www.aplix.co.jp/ Aplix Europe GmbH www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/ CORE Corporation MICROTEK INTERNATIONAL, INC.	886-2-2776-1680 81-3-3795-5171	886-2-2776-1380
	Middle East, Africa Asia Pacific Other countries U.S.A. Japan	Aplix Europe GmbH www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/, www.iasolution.net/ CORE Corporation MICROTEK INTERNATIONAL, INC.	886-2-2776-1680 81-3-3795-5171	886-2-2776-1380
	Middle East, Africa Asia Pacific Other countries U.S.A. Japan	www.aplix.co.jp/en/contact/general/index.html http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/, www.iasolution.net/ CORE Corporation MICROTEK INTERNATIONAL, INC.	886-2-2776-1680 81-3-3795-5171	886-2-2776-1380
	Africa Asia Pacific Other countries U.S.A. Japan	http://www.aplix.co.jp/ iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/, www.iasolution.net/ CORE Corporation MICROTEK INTERNATIONAL, INC.	81-3-3795-5171	
	Asia Pacific Other countries U.S.A. Japan	iaSolution Inc.index.html www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/, www.iasolution.net/ CORE Corporation MICROTEK INTERNATIONAL, INC.	81-3-3795-5171	
	Other countries U.S.A. Japan	www.aplix.co.jp/en/contact/general/ http://www.aplix.co.jp/, www.iasolution.net/ CORE Corporation MICROTEK INTERNATIONAL, INC.	81-3-3795-5171	
	U.S.A. Japan	http://www.aplix.co.jp/, www.iasolution.net/ CORE Corporation MICROTEK INTERNATIONAL, INC.		81 2 2705 5170
	U.S.A. Japan	CORE Corporation MICROTEK INTERNATIONAL, INC.		91 2 2705 5170
	U.S.A. Japan	MICROTEK INTERNATIONAL, INC.		91 2 2705 5170
Express Logic,Inc	Japan	,	1-310-687-5826	01-0-0/90-01/0
Express Logic,Inc		Grape Systems Inc.	1 010-007-0020	1-310-687-5954
	Worldwide		81-45-323-6541	81-45-323-6546
		Express Logic,Inc	1-858-613-6640	1-858-613-6646
		info@expresslogic.com		
		http://www.expresslogic.com		
GAIO TECHNOLOGY CO., LTD.	Worldwide	GAIO TECHNOLOGY CO., LTD.	81-3-3662-3041	81-3-3662-3043
		info@gaio.co.jp		
		http://www.gaio.com		
Advanced Data Controls Corp.	Japan, Asia	Advanced Data Controls Corp.	81-3-3576-5351	81-3-3576-1772
Advanced Data Controls Corp.	Japan, Asia	sales@adac.co.jp	01-0-0070-0001	01-0-0070-1172
		http://www.adac.co.jp	1 005 005 0044	1 005 005 0040
	U.S.A.	Green Hills Software, Inc.	1-805-965-6044	1-805-965-6343
		sales@ghs.com		
		http://www.ghs.com		
	Europe	http://www.ghs.com		
Hewlett-Packard Company	Worldwide	http://www.tmo.hp.com/tmo/		
IAR Systems	Sweden	IAR Systems AB	46-18-16-78-00	46-18-16-78-38
		info@iar.se		
		http://www.iar.com		
	U.S.A.(West)	IAR Systems Software Inc.	1-650-287-4250	1-650-287-4253
		info@iar.com		
		http://www.iar.com		
	U.S.A.(East)	IAR Systems Software Inc.	1-508-485-2692	1-508-485-9126
		info@iar.com		
		http://www.iar.com		
	China	IAR Systems AB	86-21-6267-0236	86-21-6267-5980
		info@iar.se		
		http://www.iar.com		
	United Kingdom	IAR Systems Ltd.	44-0-1604-250-440	44-0-1604-250-330
	Sinceringdom	info@iarsys.co.uk		
		http://www.iar.com		
	Germany	IAR Systems AG	49-89-88-98-90-0	49-89-88-98-90-90
	Germany		-+3-02-00-20-20-70-0	43-03-00-30-30-30
		info@iar.de		
		http://www.iar.com	00.0.404.07.07	
	Belgium	IAR Systems AB	32-2-401-87-89	32-2-401-68-68
		info@iar.se		
		http://www.iar.com		
	Denmark	IAR Systems A/S	45-8734-1100	45-8734-1190
		info@iar.dk		
		http://www.iar.com		
	Brazil	IAR Systems Software Inc.	55-19-3251-1763	55-19-3251-1763
		info@iar.com		
		http://www.iar.com		

Partner Contact	Information	- Support Outside of Japan	(2/3)	
Company Name (Japanese)	Area	Company Name (Spot)	TEL	FAX
BM Japan, Ltd.	Japan	IBM Japan, Ltd.	81-3-5642-9100	81-3-5642-9120
	Worldwide	International Business Machines Corporation	1-800-728-1212	1-781-676-2410
		ratlinfo@us.ibm.com		
		http://www.rational.com/products/testrt		
Kyoto Microcomputer Co., Ltd.	Worldwide	en-info@kmckk.co.jp	81-75-335-1050	81-75-335-1051
yoto microcomputer co., Eta.	Wondwide	http://www.kmckk.co.jp/eng/index.html		
ightwell Co.,Ltd.	Worldwide	ZAXSales@lightwell.co.jp	81-3-3392-3331	81-3-3393-3878
lightweir Co., Ltd.	Wondwide		01-0-0092-0001	01-0-0090-0070
) A (= u = h = u = i = l =	http://www.lightwell.co.jp/ZAX	01.0.0040.0770	01.0.0040.0750
/IKASA SHOJI Co.,Ltd.	Worldwide	info-d1@mikasa.co.jp	81-6-6946-3773	81-6-6946-3753
		http://www.mikasa.jp/		
Naito Densei Machida Seisakusho	Japan	Naito Densei Machida Mfg. Co., Ltd.	_	81-45-475-4091
Red Hat, Inc.	Worldwide	Red Had, Inc.	1-919-754-3700	1-919-754-3701
		http://www.redhat.com/		
Sophia Systems Co., Ltd.	United States,	Enable Engineering Co., Inc	1-650-375-0409	1-650-375-8666
	Canada	sales@eecosales.com		
	Israel	Sightsys	972-3-922-2771	972-3-922-2059
		dani@sightsys.co.il		
		http://www.sightsys.co.il		
	United Kingdom	Direct Insight	44-0-1280-700262	44-0-1280-700577
	guon	sales@directinsight.co.uk		
		http://www.directinsight.co.uk		
	France	Antycip	33-1-39-61-14-14	33-1-30-76-29-73
	France		33-1-39-01-14-14	33-1-30-70-29-73
		akkouche@antycip.com		
		http://www.antycip.com		
	Eastern Europe	Eastern Trade Embedded Systems	49-0-8233-78-09-26	49-0-8233-78-09-27
		Trading and Consulting		
		info@easterntrade.de		
		http://www.easterntrade.de		
	Singapore,	FLASH Technology	065-6749-6168	065-6749-6138
	Malasia	flashsgp@pacific.net.sg		
		http://www.flashtech.com.sg		
	Taiwan	SuperLink Technology	886-2-2698-3456	886-2-2698-3535
		sulin@superlink.com.tw		
		http://www.superlink.com.tw		
	India	Trident Infosol	91-80-2224-5037	91-80-2229-1566
		rameshwarbandi@vsnl.net	51 00 2224 0001	01 00 2220 1000
		http://www.tridentinfosol.com		
	China,	Emdoor Electronic & Technology Co, Ltd.	Shenzhen Office(HQ)	Shenzhen Office(HQ)
	Hong Kong	info@emdoor.com	86-755-83474893,	86-755-83474895
		http://www.emdoor.com	86-755-83474896,	
			86-755-83474892	
			Beijing Office	Beijing Office
			86-10-62376767,	86-10-62376767
			86-10-62375506	
			Shanghai Office	Shanghai Office
			86-21-62650520,	86-21-62650520
			86-21-62643621	
			Hong Kong Office	
			852-25780383	-
	Korea	MDS Technology	82-2-2106-6000	82-2-2106-6004
	Korea	0,7	02-2-2100-0000	02-2-2100-0004
		hyungkwan@hkmds.com		
		http://www.mdstec.com		
okyo Eletech Corporation	Japan	Tokyo Eletech Corporation	81-3-5295-1663	81-3-5295-1663
	U.S.A.	DAIMARU NEW YORK CORPORATION	1-212-681-9371	1-212-681-8951
	U.S.A.	OESS SANJOSE OFFICE	1-408-437-5490	1-408-437-5493
	Europe	OESS Gmbh	06106-75013	06106-72719
	Asia	DAIMARU KOGYO, LTD.HONG KONG OFFICE	852-2893-	852-2893-5853
			9457/9108	
	Asia	DAIMARU KOGYO, LTD.TAIPEI OFFICE	886-2-2776-	886-2-2771-3023
	1.000		1	300 2 211 1 0020



		- Support Outside of Japa				
Company Name (Japanese)	Area	Company Name (Spot)	TEL	FAX		
'ector Japan	Germany	Vector Informatik	49-711-80670-0	49-711-80670-111		
		sales@vector-informatik.com				
		http://www.vector-informatik.de				
	U.S.A.	Vector CANtech	1-248-449-9290	1-248-449-9704		
		sales@vector-cantech.com				
		http://www.vector-cantech.com				
	Japan	Vector Japan	81-3-5769-6980	81-3-5769-6975		
		sales@vector-japan.co.jp				
		http://www.vector-japan.co.jp				
	France	Vector France	33-1-4231-4000	33-1-4231-4009		
		information@vector-france.com				
		http://www.vector-france.com				
	Sweden	Vector Scandinavia	46-31-83-40-80	46-31-83-40-99		
		sales@vecscan.com				
		http://www.vecscan.com				
Nave Technology Co., Ltd.	Worldwide	http://www.y1000.com/en/	81-3-5304-1885	81-3-5304-1886		
ASKAWA INFORMATION	Worldwide	echonet@ysknet.co.jp	81-44-952-8918	81-44-952-8921		
SYSTEMS Corporation		http://www.ysknet.co.jp/product/johokaden/echo	net			
okogawa Digital Computer	U.S.A.	U.S.A. Yokogawa Corporation of America				
Corporation		[Pacific Time Zone]				
		shotaro.saito@us.yokogawa.com	1-408-392-1364	1-408-392-0541		
		[Eastern Time Zone]				
		bob.timms@us.yokogawa.com	1-770-594-0399,	1-770-594-0336		
			Ext. 5126			
		http://www.advice-PLUS.com/				
	Germany	Hitex Development Tools GmbH	49-721-9628-0	49-721-9628-149		
		info@hitex.de				
		http://www.hitex.de/				
	Europe	Ashling Microsystems Limited	44-1256-811998	44-1256-811761		
		advice@ashling.com				
		http://www.ashling.com/				
	Korea	KM Data Inc.	82-2-3281-0333	82-2-3281-3117		
		kmdata@kmd.co.kr				
		http://www.kmdata.co.kr/				
	China	Yokogawa Shanghai Trading Co., Ltd.	86-10-6588-3555	86-10-6588-7025		
		meng_fanpu@ysh.com.cn				
		http://www.yokogawa.com/cn-ysh/				
	Singapore	Unidux Electronics Limited	65-6569-3611	65-6566-9271		
	State t	sales@unidux.com.sg				
		http://www.unidux.com.sg/				
	Other countries	Yokogawa Digital Computer Corporation	81-42-333-6222	81-42-333-6107		
		info-ovs@vokogawa-digital.com				
		http://www.yokogawa-digital.com/en/				

Rental Companies

The above tools (hardware only) are leased out by the following companies. Please contact these companies for further details.

Contact	URL
Orix Rentec	http://www.orixrentec.co.jp
Showa High-Tec Rent	http://www.shiret.co.jp
Yokogawa Rent-A-Lease	http://www.yrl.com

SUPPORT SYSTEM

Purchasing Products

Please contact an NEC Electronics distributor or sales representative regarding the purchase of NEC Electronics products. Customers will receive shipment of products after the distributor or NEC Electronics sales office has submitted their order form.

Note that a precontract is required for real-time OS and middleware (RX-NET, RX-FS, GOFAST) products to be embedded in the customer's system. The procedure for purchasing NEC Electronics products is outlined below.

Purchasing procedure for products requiring precontract

Preparation of purchase order form	A precontract is required when purchasing real-time OS products. Customers are therefore requested to fill out a purchase order form and submit it to an NEC Electronics sales representative.
About 1 week	
Signing of contract	A contract will be ready for signing about 1 week following submission of the order form. Please confirm that the contents are correct before signing the contract.
•	
Submission of order	After the contract has been signed, the NEC Electronics sales division will submit the order form.
About 2 weeks	
Product shipment	NEC Electronics operates on a production-on-demand system, so customers should expect ship- ment about 2 weeks after their order is received.

Supply format

Software from NEC Electronics includes only those objects necessary for operation. In the case of real-time OS and middleware products, however, due to the nature of the software, source code is supplied along with the execution objects.

After-sales support

Free upgrades

Provided the customer has completed and returned the User Registration Card included with the product's guarantee card, free upgrades are available online for the period of one-year following purchase. Once this period expires, an upgrade fee will be required.

Inquiries regarding product usage and bugs

Please direct any inquiries to an NEC Electronics distributor, sales division, or use the technical hotline.

Range of support

NEC Electronics provides support for all products that have been used in accordance with the stated methods. Note that real-time OS source code products fall outside NEC Electronics' support range.

Seminars

NEC Electronics provides a wide variety of forums for exploring the V850 Series development environment, ranging from seminars to introduce potential new customers to NEC Electronics products, to training sessions for those customers seeking to improve their knowledge and technical skills. All those interested are warmly invited to attend. The following seminars have been organized to assist customers in understanding and using the V850 Series development environment.

Seminar Name	Length	Description		
V800 Series C Compiler	2 days	A seminar that combines lecturing and hands-on training (using the V850 Series) to give		

Basics and Application	2 dayo	customers an understanding of the basic coding techniques used in software development.
Real-Time OS for V850 Series Basics	2 days	A seminar to give customers detailed descriptions of and hands-on experience in using the functions of a real-time OS (RX850 Pro). Aim: To master RX850 Pro functions, operations, and system call usage.
Real-Time OS for V850 Series Application	2 days	A seminar to give an understanding and practical knowledge of development using the V850E and an evaluation board (SolutionGear) through hands-on practice.

To find out more about these seminars, please refer to the separate introductory pamphlet. Those interested in NEC Electronics' "onsite seminars" held at the customer's location are requested to contact an NEC Electronics for details such as date and content.

DEVELOPMENT TOOLS DOWNLOAD SERVICE (ODS)

Service Outline

- 1. Development tool software for the V850 Series can be downloaded.
- 2. Technical information (version, technical documentation, etc.) pertaining to development tool software for the V850 Series can be viewed.
- 3. Version upgrade information is distributed by e-mail to registered users.

For more information, see

http://www.necel.com/micro/ods/eng/ods_readme_e.pdf



The ODS top screen can be jumped to from the NEC Electronics Microcomputer website (http://www.necel.com/micro/index_e.html) by clicking [Development Tools Download]. (Refer to above figure.)

ODS top screen

vour creativity



The sought after development tool can be looked for by device series or by development tool.

Screen when C Compiler has been selected

INCLEMENTING Monosel Internet Lighters INCLEMENTING INCLEMENTING Address Internet INCLEMENTING <

Technical information such as the development tool software version, release date, size, and attached documents can be viewed. (Example: CA703000).

NEC Electronics Microcomputer website: http://www.necel.com/micro/index_e.html

SolutionGear is a registered trademark of NEC Electronics Corporation. Green Hills Software, MULTI, and TimeMachine are trademarks of Green Hills Software, Inc. NORTi is a registered trademark of MiSPO Co., Ltd. WATCHPOINT is a trademark of Sophia Systems Co., Ltd. UNIX is a registered trademark licensed by X/Open Company Limited in the United States and/or other countries. CodeWarrior is a registered trademark of Metrowerks Corporation. PC/AT is a trademark of International Business Machines Corporation. Microsoft, MS-DOS, Windows, Windows NT, Visual Basic, and Visual Studio are either trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries. SPARCstation is a trademark of SPARC International, Inc. JBlend and microJBlend are trademarks of Aplix Corporation. GNUPro is a registered trademark of Red Hat, Inc. GOFAST, USNET, and USFiles are trademarks of United States Software Corp. Java and all trademarks and logos related to Java are either trademarks or registered trademarks of Sun Microsystems, Inc. in the United States and/or other countries. ZIPC is a registered trademark of CATS, Inc. TRON stands for The Realtime Operating system Nucleus. ITRON is an abbreviation of Industrial TRON. µITRON is an abbreviation of "Micro Industrial TRON". TRON, ITRON, and μ ITRON do not refer to specific products or product groups. JTRON stands for Java technology on ITRON.

The names of other products are the trademarks of each company.

- The information in this document is current as of August, 2005. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC Electronics data sheets or data books, etc., for the most up-to-date specifications of NEC Electronics products. Not all products and/or types are available in every country. Please check with an NEC Electronics sales representative for availability and additional information.
- No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Electronics. NEC Electronics assumes no responsibility for any errors that may appear in this document.
- NEC Electronics does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC Electronics products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Electronics or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of a customer's equipment shall be done under the full responsibility of the customer. NEC Electronics assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC Electronics endeavors to enhance the quality, reliability and safety of NEC Electronics products, customers agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize risks of damage to property or injury (including death) to persons arising from defects in NEC Electronics products, customers must incorporate sufficient safety measures in their design, such as redundancy, fire-containment and anti-failure features.
- NEC Electronics products are classified into the following three quality grades: "Standard", "Special" and "Specific".

The "Specific" quality grade applies only to NEC Electronics products developed based on a customerdesignated "quality assurance program" for a specific application. The recommended applications of an NEC Electronics product depend on its quality grade, as indicated below. Customers must check the quality grade of each NEC Electronics product before using it in a particular application.

- "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots.
- "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support).
- "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.

The quality grade of NEC Electronics products is "Standard" unless otherwise expressly specified in NEC Electronics data sheets or data books, etc. If customers wish to use NEC Electronics products in applications not intended by NEC Electronics, they must contact an NEC Electronics sales representative in advance to determine NEC Electronics' willingness to support a given application.

(Note)

- (1) "NEC Electronics" as used in this statement means NEC Electronics Corporation and also includes its majority-owned subsidiaries.
- (2) "NEC Electronics products" means any product developed or manufactured by or for NEC Electronics (as defined above).

For further information, please contact:

NEC Electronics Corporation

1753, Shimonumabe, Nakahara-ku, Kawasaki, Kanagawa 211-8668, Japan Tel: 044-435-5111 http://www.necel.com/

[America]

NEC Electronics America, Inc.

2880 Scott Blvd. Santa Clara, CA 95050-2554, U.S.A. Tel: 408-588-6000 800-366-9782 http://www.am.necel.com/

[Europe]

NEC Electronics (Europe) GmbH Arcadiastrasse 10

40472 Düsseldorf, Germany Tel: 0211-65030 http://www.eu.necel.com/

Hanover Office

Podbielskistrasse 166 B 30177 Hannover Tel: 0 511 33 40 2-0

Munich Office Werner-Eckert-Strasse 9 81829 München

Tel: 0 89 92 10 03-0

Stuttgart Office

Industriestrasse 3 70565 Stuttgart Tel: 0 711 99 01 0-0

United Kingdom Branch

Cygnus House, Sunrise Parkway Linford Wood, Milton Keynes MK14 6NP, U.K. Tel: 01908-691-133

Succursale Française

9, rue Paul Dautier, B.P. 52180 78142 Velizy-Villacoublay Cédex France Tel: 01-3067-5800

Sucursal en España

Juan Esplandiu, 15 28007 Madrid, Spain Tel: 091-504-2787

Tyskland Filial

Täby Centrum Entrance S (7th floor) 18322 Täby, Sweden Tel: 08 638 72 00

Filiale Italiana

Via Fabio Filzi, 25/A 20124 Milano, Italy Tel: 02-667541

Branch The Netherlands

Limburglaan 5 5616 HR Eindhoven The Netherlands Tel: 040 265 40 10

Document No. U15763EJ5V0PF00 (5th edition) Date Published February 2006 N CP(K)

[Asia & Oceania]

NEC Electronics (China) Co., Ltd 7th Floor, Quantum Plaza, No. 27 ZhiChunLu Haidian District, Beijing 100083, P.R.China TEL: 010-8235-1155 http://www.cn.necel.com/

NEC Electronics Shanghai Ltd.

Room 2509-2510, Bank of China Tower, 200 Yincheng Road Central, Pudong New Area, Shanghai P.R. China P.C:200120 Tel: 021-5888-5400 http://www.cn.necel.com/

NEC Electronics Hong Kong Ltd.

12/F., Cityplaza 4, 12 Taikoo Wan Road, Hong Kong Tel: 2886-9318 http://www.hk.necel.com/

Seoul Branch

11F., Samik Lavied'or Bldg., 720-2, Yeoksam-Dong, Kangnam-Ku, Seoul, 135-080, Korea Tel: 02-558-3737

NEC Electronics Taiwan Ltd.

7F, No. 363 Fu Shing North Road Taipei, Taiwan, R. O. C. Tel: 02-2719-2377

NEC Electronics Singapore Pte. Ltd.

238A Thomson Road, #12-08 Novena Square, Singapore 307684 Tel: 6253-8311 http://www.sg.necel.com/