

DA14531

Ultra-Low Power Bluetooth 5.1 SoC

The DA14531 is an ultra-low power SoC integrating a 2.4 GHz transceiver and an Arm® Cortex®-M0+ microcontroller with a RAM of 48 kB and a One-Time Programmable (OTP) memory of 32 kB. It can be used as a standalone application processor or as a data pump in hosted systems.

The radio transceiver, the baseband processor, and the qualified Bluetooth® low energy stack are fully compliant with the Bluetooth® Low Energy 5.1 standard.

The DA14531 has dedicated hardware for the Link Layer implementation of Bluetooth® LE and interface controllers for enhanced connectivity capabilities.

The Bluetooth® LE firmware includes the L2CAP service layer protocols, Security Manager (SM), Attribute Protocol (ATT), the Generic Attribute Profile (GATT), and the Generic Access Profile (GAP). All profiles published by the Bluetooth® SIG as well as custom profiles are supported.

The DA14531-01 is optimized for peripheral only applications, provides around 25 % additional user RAM for a typical Bluetooth[®] LE application compared to the DA14531-00 and is pin-to-pin compatible.

The device is suitable for disposables, wireless sensor nodes, beacons, proximity tags, and trackers, smart HID devices (stylus, keyboards, mice, and trackpads), toys, and medical and industrial applications.

Key Features

- Compatible with Bluetooth® v5.1, ETSI EN 300 328 and EN 300 440 Class 2 (Europe), FCC CFR47 Part 15 (US) and ARIB STD-T66 (Japan)
- Supports up to three Bluetooth® LE connections
- Typical cold boot to radioactive 35 ms
- Processing power
 - 16 MHz 32-bit Arm Cortex-M0+ with SWD interface
 - 18300 EEMBC IoTMark-Bluetooth LE[®] score
 - Dedicated Link Layer and AES-128 Encryption Processor
 - Software-based True Random Number Generator (TRNG)
- Memories
 - 32 kB One-Time-Programmable (OTP)
 - 48 kB Retainable System RAM
 - 144 kB ROM
- Power management
 - Integrated Buck/Boost DCDC converter
 - Buck: $1.8 \text{ V} \leq \text{V}_{\text{BAT HIGH}} \leq 3.6 \text{ V}$
 - Boost: 1.1 V ≤ V_{BAT_LOW} ≤ 1.65 V
 - Clock-less hibernation mode: Buck 270 nA, Boost 240 nA
 - Built-in temperature sensor for die temperature monitoring

- Clocks
 - 32 MHz crystal and 32 MHz RC osc.
 - 32 kHz crystal and 32/512 kHz RC osc.
 - 15 kHz RCX as crystal replacement
- Programmable Reset Circuitry
- 2× General purpose Timers with capture and PWM capabilities
- Digital interfaces
 - GPIOs: 6 (WLCSP17), 12 (FCGQFN24)
 - 2× UARTs (one with flow control)
 - SPI Master/Slave up to 32 MHz (Master)
 - I2C bus at 100 kHz and 400 kHz
 - 3-axis capable Quadrature Decoder
 - Keyboard controller
- Analog interfaces
 - 4-channel 10-bit ADC
- Radio transceiver
 - Fully integrated 2.4 GHz CMOS transceiver
 - · Single wire antenna
 - TX: 3.5 mA, RX: 2.2 mA (system currents with DCDC, VBAT_HIGH = 3 V and 0 dBm)
 - Programmable transmit output power from -19.5 dBm to +2.5 dBm
 - -94 dBm receiver sensitivity

- Packages:
 - WLCSP 17 balls, 1.7 × 2.05, 0.5 mm pitch
 - FCGQFN 24 pins, 2.2 × 3, 0.4 mm pitch
- Variant:
 - 531-00: LE central and peripheral
 - 531-01: LE peripheral only

Applications

- Medical applications
- Disposables
- Beacons
- Proximity tags and trackers
- Wireless sensor nodes
 - · Fitness trackers
 - Consumer health
- Smartwatches
- Human interface devices (HID)
 - Stylus pens
 - Keyboards
 - Mouse devices
 - Trackpads
- Toys
- Industrial appliances

Key Benefits

- Lowest power consumption
- Smallest system size
- Lowest system cost

System Diagram



Figure 1. System diagram

Contents

Key	Key Features1						
App	olicatio	ns			2		
Key	Bene	fits			2		
Sys	tem D	iagram			3		
Cor	ntents				4		
Fig	ures				10		
Tab	les				12		
1.	Block	k Diagra	m		22		
2.	DA14	1531-0x	Product Var	riants	23		
3.	Pack	ages an	d Pinout		24		
	3.1	WLCSF	P17		24		
	3.2	FCGQF	N24		28		
4.	Spec	ification	s		32		
	4.1	Absolut	e Maximum	Ratings	34		
	4.2	Recomi	mended Ope	erating Conditions	34		
	4.3	DC Cha	aracteristics.		35		
	4.4	Timing	Characterist	ics	37		
	4.5	RCX O	scillator		37		
	4.6	XTAL32	2MHz Oscilla	ator	38		
	4.7	XTAL32kHz Oscillator					
	4.8	RC32MHz Oscillator					
	4.9	DC-DC	39				
	4.10	0 LDO_LOW Characteristics					
	4.11	Digital I	41				
	4.12	Power (42				
	4.13	GP AD	43				
	4.14	Temper	ature Senso	or	44		
	4.15	Radio			45		
5.	Syste	em Over	view		49		
	5.1	Internal	Blocks		49		
	5.2	Power I	Managemen ^a	t Unit	50		
		5.2.1	Introduction	n	50		
		5.2.2	Architectur	re	50		
			5.2.2.1	Digital Power Domains	52		
			5.2.2.2	Power Modes	53		
			5.2.2.3	DD Level in Hibernation	55		
			5.2.2.4	Retainable Registers	55		
		5.2.3	Programm	ing	56		
			5.2.3.1	Buck Configuration	56		
			5.2.3.2	Boost Configuration	56		
			5.2.3.3	Bypass Configuration	57		

	5.3	Hardwa	are FSM (Power-Up, Wake-Up, and Go-to-Sleep)	58			
		5.3.1	Power-Up/Wake-Up in Buck Configuration	58			
		5.3.2	Power-Up/Wake-Up in Boost Configuration	60			
		5.3.3	Go-to-Sleep and Refresh Bandgap	61			
	5.4	OTP M	emory Layout	61			
		5.4.1	OTP Header	62			
		5.4.2	Configuration Script	64			
	5.5	BootRO	DM Sequence	65			
6.	Rese	et		68			
	6.1	1 Introduction					
	6.2	Architecture					
		6.2.1	POR, Hardware, and Software Reset	68			
		6.2.2	POR Functionality	69			
			6.2.2.1 POR Timer Clock	70			
			6.2.2.2 RST Pad	70			
			6.2.2.3 POR from GPIO	70			
		6.2.3	POR Timing Diagram	70			
		6.2.4	POR Considerations	70			
	6.3	Program	mming	71			
7.	Arm	m [®] Cortex-M0+					
	7.1	Introduction					
	7.2	Archite	cture	73			
		7.2.1	Interrupts	73			
		7.2.2	System Timer (SysTick)	74			
		7.2.3	Wake-Up Interrupt Controller	75			
	7.3	Program	mming	75			
8.							
	8.1	Introduction					
	8.2		cture				
	8.3	Programming					
9.)				
10.		•	troller				
			ction				
	10.2	Archite	cture				
		10.2.1					
11.			ration				
	11.1		Гree				
			General Clock Constraints				
	11.2	-	Oscillators				
		11.2.1	Frequency Control (32 MHz Crystal)				
		11.2.2	Automated Trimming and Settling Notification				
	11.3		cillators				
		11.3.1	Frequency Calibration	85			

12.	ОТР	Controll	er		86
	12.1	Introduc	tion		86
	12.2	Archited	ture		86
		12.2.1	OTP Acce	ssing Considerations	87
	12.3	Progran	nming		87
13.	DMA	Control	er		89
	13.1	Introduc	tion		89
	13.2	Architec	ture		89
		13.2.1	DMA Perip	pherals	89
		13.2.2	Input/Outp	ut Multiplexer	90
		13.2.3	DMA Char	nnel Operation	90
		13.2.4	DMA Arbit	ration	91
		13.2.5	Freezing [DMA Channels	92
	13.3	Progran	nming		92
		13.3.1	Memory to	Memory Transfers	92
		13.3.2	Peripheral	to Memory Transfers	92
14.	I2C II	nterface			94
	14.1	Introduc	tion		94
	14.2	Architec	ture		94
		14.2.1	I2C Bus T	erms	95
			14.2.1.1	Bus Transfer Terms	95
		14.2.2	I2C Behav	ior	96
			14.2.2.1	START and STOP Generation	96
			14.2.2.2	Combined Formats	
		14.2.3	I2C Protoc	cols	97
			14.2.3.1	START and STOP Conditions	97
			14.2.3.2	Addressing Slave Protocol	
			14.2.3.3	7-bit Address Format	97
			14.2.3.4	10-bit Address Format	97
			14.2.3.5	Transmitting and Receiving Protocols	98
		14.2.4	-	aster Arbitration	
		14.2.5	•	chronization	
		•	•		
15.					
	15.1	5.1 Introduction			
	15.2				
		15.2.1	•	232) Serial Protocol	
		15.2.2	·	port	
		15.2.3	•		
		15.2.4	ŭ	able THRE Interrupt	
		15.2.5		egisters	
		15.2.6		t Mode	
	15.3	Progran	nming		108

16.	SPI II	nterface		109	
	16.1	6.1 Introduction			
	16.2	Archited	cture	110	
		16.2.1	SPI Timing	110	
	16.3	Progran	nming	111	
		16.3.1	Master Mode	111	
		16.3.2	Slave Mode	111	
17.	Quad	Irature D	ecoder	113	
	17.1	Introduc	ction	113	
	17.2	Archited	cture	113	
	17.3	Progran	nming	114	
18.	Cloc	kless Wa	ake-up Controller	116	
	18.1	Introduc	etion	116	
	18.2	Archited	cture	116	
	18.3	Progran	nming	116	
19.		•	e-up Controller		
	19.1	Introduc	etion	118	
	19.2	Archited	sture	118	
	19.3	Progran	nming	119	
20.					
	20.1	.1 Introduction			
	20.2	2 Architecture			
	20.3	0.3 Programming		122	
		20.3.1	Timer Functionality		
		20.3.2	PWM Generation		
21.	Time	r 1			
			etion		
			cture		
			nming		
		21.3.1	Timer Functionality		
		21.3.2	Capture Functionality		
		21.3.3	Frequency Measuring Functionality		
22.	Time		, , , , , , , , , , , , , , , , , , ,		
	22.1		etion		
	22.2		sture		
			nming		
		22.3.1	PWM Generation		
		22.3.2	Freeze Functionality		
23.	Watc	_	ner		
	23.1	_	tion		
	_	2 Architecture			
			nming		
24.		•	Sensor		

	24.1	Introdu	ction		132
	24.2	Archite	cture		132
		24.2.1	Programm	ning	133
			24.2.1.1	Absolute Temperature	133
			24.2.1.2	Relative Temperature	134
25.	Keyb	oard Co	ontroller		135
	25.1	Introdu	ction		135
	25.2	Archite	cture		135
		25.2.1	Keyboard	Scanner	135
		25.2.2	GPIO Inte	errupt Generator	136
	25.3	Progra	mming		137
		25.3.1	Keyboard	Scanner	137
		25.3.2	GPIO Inte	errupts	137
26.	Input	/Output	Ports		138
	26.1	Introdu	ction		138
	26.2	Archite	cture		138
		26.2.1	Programm	nable Pin Assignment	138
			26.2.1.1	Priority	138
			26.2.1.2	Direction Control	139
		26.2.2	General P	Purpose Port Registers	139
			26.2.2.1	Port Data Register	
			26.2.2.2	Port Set Data Output Register	139
			26.2.2.3	Port Reset Data Output Register	
		26.2.3	Fixed Ass	ignment Functionality	
		26.2.4		GPIO Pads	
		26.2.5		rength	
27.	Gene	ral Purp	•		
		-			
	27.2				
	27.3	Input C	hannels		143
		27.3.1	Operating	Modes	143
			27.3.1.1	Enabling the ADC	144
			27.3.1.2	Manual Mode	145
			27.3.1.3	Continuous Mode	145
		27.3.2	Conversio	on Modes	145
			27.3.2.1	AD Conversion	
			27.3.2.2	Averaging	
			27.3.2.3	Chopper Mode	
		27.3.3	Additional	Settings	
		27.3.4		Effects	
		27.3.5		libration	
		27.3.6		e Adjustment	
		27.3.7		Mode Adjustment	

		27.3.8	Input Imped	dance, Inductance, and Input Settling	148	
	27.4	Prograr	nming		148	
28.	Real	Time Cl	ock (RTC)		150	
	28.1	Introduc	ction		150	
	28.2	Archited	cture		150	
	28.3	Prograr	nming		151	
29.	Powe	ər			152	
	29.1	DCDC	Converter		152	
	29.2	LDOs			154	
	29.3	POR C	rcuit		154	
30.	Blue	tooth® L	E Core		155	
	30.1	Archited	cture		155	
		30.1.1	Exchange I	Memory	155	
	30.2	Prograr	nming		156	
		30.2.1	Wake-Up II	RQ	156	
		30.2.2	Switch from	n Bluetooth® LE Active Mode to Bluetooth® LE Deep Sleep Mode	156	
		30.2.3	Switch from	n Bluetooth [®] LE Deep Sleep Mode to Bluetooth [®] LE Active Mode	157	
			30.2.3.1	Switching at an Anchor Point	157	
			30.2.3.2	Switching Due to an External Event	158	
31.	Radi	0			160	
	31.1	Introduc	ction		160	
	31.2	Archited	cture		160	
		31.2.1	Receiver		160	
		31.2.2	Synthesize	r	160	
		31.2.3	Transmitter	٢	161	
		31.2.4	RFIO		161	
		31.2.5	Biasing		161	
		31.2.6	RF Monitor	ing	161	
32.	Regi	sters			162	
	32.1	Analog	Miscellaneou	us Registers	162	
	32.2	Bluetoo	th [®] LE Core	Registers	164	
	32.3	Clock G	eneration ar	nd Reset Registers	189	
	32.4	DCDC	Converter Re	egisters	204	
	32.5	DMA C	ontroller Reg	isters	206	
	32.6	General Purpose ADC Registers				
	32.7	General Purpose I/O Registers				
	32.8	2.8 General Purpose Registers				
	32.9	32.9 I2C Interface Registers				
	32.10) Keyboa	rd Registers		248	
	32.11	Miscella	aneous Regis	sters	252	
	32.12	OTP Co	ontroller Regi	sters	256	
	32.13	3 Quadra	ture Decodei	r Registers	261	
	32.14	Real Ti	me Clock Re	gisters	263	

	32.15 SPI Interface Registers	270
	32.16 Timer and Triple PWM Registers	274
	32.17 Timer1 Registers	278
	32.18 UART Interface Registers	
	32.19 Chip Version Registers	
	32.20 Wake-Up Registers	
	32.21 Watchdog Registers	
33.		
	4. Package Information	
•	34.1 Moisture Sensitivity Level (MSL)	
	34.2 WLCSP Handling	
	34.3 Soldering Information	
	•	
	34.4 Package Outline Drawings	
	5. Revision History	
Fi	igures	
Fia	gure 1. System diagram	3
_	gure 2. DA14531 block diagram	
-	gure 3. WLCSP17 ball assignment (top view)	
_	gure 4. FCGQFN24 pin assignment (top view)	
	gure 5. Boost configuration system diagram	
Figu	gure 6. Buck configuration system diagram	33
Figu	gure 7. Power management unit: buck configuration	51
Figu	gure 8. Power management unit: boost configuration	51
Figu	gure 9. Power management unit: bypass configuration	52
Figu	gure 10. Digital power domains	52
Figu	gure 11. Power-up/Wake-up/Sleep FSM diagram	58
Figu	gure 12. Power-up (Buck)	59
Figu	gure 13. Wake-up from Hibernation (Buck)	59
Figu	gure 14. Wake-Up (Buck)	59
_	gure 15. Power-up (Boost)	
_	gure 16. Wake-up from Hibernation (Boost)	
	gure 17. Wake-up from Extended/Deep Sleep (Boost)	
_	gure 18. Go-to-Sleep and bandgap refresh	
_	gure 19. OTP layout scheme	
_	gure 20. BootROM sequence	
-	gure 21. Reset block diagram	
_	gure 22. POR timing diagram	
-	gure 23. Arm [®] Cortex-M0+ block diagram	
_	gure 24. AMBA Bus architecture and power domains	
_	gure 25. Memory controller block diagram	
-	gure 26. Clock tree diagram	
-	gure 27. Crystal oscillator circuits	
_	gure 28. XTAL32MHz oscillator frequency trimming	
-	gure 29. Automated mechanism for XTAL32M trim and settling	
Fia	gure 30. OTP controller block diagram	86

Figure 31.	DMA controller block diagram	89
Figure 32.	DMA channel diagram	91
Figure 33.	I2C controller block diagram	94
Figure 34.	Master/Slave and Transmitter/Receiver Relationships	95
Figure 35.	Data transfer on the I2C bus	96
Figure 36.	START and STOP conditions	97
Figure 37.	7-bit address format	97
Figure 38.	10-bit address format	98
Figure 39.	Master-transmitter protocol	99
Figure 40.	Master-receiver protocol	99
Figure 41.	START BYTE transfer	100
Figure 42.	Multiple master arbitration	101
Figure 43.	Multiple Master clock synchronization	101
-	UART block diagram	
Figure 45.	Serial data format	104
Figure 46.	Receiver serial data sampling points	104
Figure 47.	Flowchart of interrupt generation for programmable THRE Interrupt mode	107
Figure 48.	Flowchart of interrupt generation when not in programmable THRE Interrupt mode	107
-	SPI block diagram	
Figure 50.	SPI Slave mode timing (CPOL = 0, CPHA = 0)	110
Figure 51.	Quadrature decoder block diagram	113
Figure 52.	Moving forward on Axis X	113
Figure 53.	Moving backwards on Axis X	114
Figure 54.	Digital filtering and edge detection circuit	114
-	Clockless wake-up controller circuit	
Figure 56.	Clocked wake-up controller block diagram	118
Figure 57.	Event counter state machine for the wake-up interrupt generator	119
Figure 58.	Timer 0 block diagram	120
_	Timer 0 PWM mode	
_	Timer 1 block diagram	124
Figure 61.	Timer 2 block diagram	127
_	Timer 2 timing diagram	
-	Watchdog timer block diagram	
Figure 64.	Temperature sensor behavior	132
_	Keyboard controller block diagram	
-	Keyboard scanner state machine	
-	GPIO interrupt generator state machine	
-	Port P0 with programmable pin assignment and driving strength	
•	Type A GPIO pad - GPIO with Schmitt trigger on input	
•	Type B GPIO pad - GPIO with Schmitt trigger and RC Filter on Input	
_	Block diagram of GPADC	
Figure 72.	GPADC operation flow diagram	144
Figure 73.	Real time clock block diagram	150
•	DCDC block diagram - buck configuration	
_	DCDC block diagram - boost configuration	
Figure 76.	DCDC efficiency in buck configuration	153
•	DCDC efficiency in boost configuration	
Figure 78.	Bluetooth® LE core block diagram	155

Figure 79. Entering Bluetooth® LE Deep Sleep mode	157
Figure 80. Exit Bluetooth LE Deep Sleep mode at predetermined time (zoom in)	
Figure 81. Exit Bluetooth LE Deep Sleep mode after predetermined time (zoom in)	
Figure 82. Exit Bluetooth LE Deep Sleep mode at predetermined time (zoom out)	158
Figure 83. Exit Bluetooth LE Deep Sleep mode due to external event	159
Figure 84. Bluetooth [®] radio block diagram	160
Figure 85. WLCSP17 package outline drawing	333
Figure 86. FCGQFN24 package outline drawing	334
Tables	
Table 1: DA14531-0x Product Variants Differentiation	23
Table 2: DA14531 WLCSP17 Ball Description	25
Table 3: DA14531 FCGQFN24 Pin Description	28
Table 4: Absolute maximum ratings	34
Table 5: Recommended operating conditions	34
Table 6: DC characteristics	35
Table 7: Timing characteristics	37
Table 8: RCX Oscillator - Timing characteristics	37
Table 9: XTAL32MHz Oscillator - Recommended operating conditions	38
Table 10: XTAL oscillator 32kHz - Recommended operating conditions	38
Table 11: XTAL oscillator 32kHz - Timing characteristics	39
Table 12: RC32MHz Oscillaor - Timing characteristics	39
Table 13: DCDC Converter - Recommended operating conditions	39
Table 14: DCDC Converter - DC characteristics	40
Table 15: LDO_LOW - Recommended operating conditions	40
Table 16: LDO_LOW - DC characteristics	40
Table 17: Digital Pad - Recommended operating conditions	41
Table 18: Digital Pad - DC characteristics	42
Table 19: Digital Pad with LPF - DC characteristics	42
Table 20: Digital Pad with LPF - Recommended operating conditions	42
Table 21: POR VBAT_LOW - DC characteristics	42
Table 22: POR VBAT_HIGH - DC characteristics	
Table 23: GP ADC - Recommended operating conditions	
Table 24: GP ADC - DC characteristics	43
Table 25: GP ADC - Electrical performance	44
Table 26: Temperature Sensor - DC characteristics	44
Table 27: BLE 1Mb/s specifications - Recommended operating conditions	45
Table 28: BLE 1Mb/s specifications - AC characteristics	
Table 29: BLE 1Mb/s specifications - Timing characteristics	47
Table 30: BLE 1Mb/s specifications - DC characteristics	
Table 31: Power Domains Description	52
Table 32: Power Modes, Digital Power Domains, Clocks, and Wake-up Triggers	
Table 33: Power Rails Drivers and Voltages	
Table 34: VDD_Clamp Recommended Settings over Temperature and Load	
Table 35: Retainable Registers	
Table 36: OTP Header	
Table 37: CS Commands and Description	64

Table 38: CS Example	65
Table 39: Booting Sequence Steps	67
Table 40: Reset Signals and Registers	69
Table 41: Interrupt List	73
Table 42: Arm Documents List	75
Table 43: Memory Map	78
Table 44: Generated Clocks Description	82
Table 45: DMA Served Peripherals	89
Table 46: I2C Definition of Bits in First Byte in 10-bit Address Format	98
Table 47: UART Baud Rate Generation	105
Table 48: UART Interrupt Priorities	105
Table 49: SPI Modes Configuration and SCK States	110
Table 50: SPI Timing Parameters	
Table 51: Fixed Assignment of Specific Signals	139
Table 52: ADC Input Channels	143
Table 53: GPADC External Input Channels and Voltage Range	
Table 54: ADC_LDO Start-Up Delay	145
Table 55: ADC Sampling Time Constant (TADC_SMPL)	
Table 56: ENOB in Oversampling Mode	
Table 57: GPADC Calibration Procedure for Single-Ended and Differential Modes	
Table 58: Common Mode Adjustment	
Table 59: Register map ANAMISC	
Table 60: CLK_REF_SEL_REG (0x50001600)	
Table 61: CLK_REF_CNT_REG (0x50001602)	
Table 62: CLK_REF_VAL_L_REG (0x50001604)	
Table 63: CLK_REF_VAL_H_REG (0x50001606)	
Table 64: Register map BLE	
Table 65: BLE_RWBLECNTL_REG (0x4000000)	
Table 66: BLE VERSION REG (0x40000004)	
Table 67: BLE_RWBLECONF_REG (0x40000008)	
Table 68: BLE_INTCNTL_REG (0x4000000C)	168
Table 69: BLE_INTSTAT_REG (0x40000010)	
Table 70: BLE_INTRAWSTAT_REG (0x40000014)	
Table 71: BLE_INTACK_REG (0x40000018)	
Table 72: BLE_BASETIMECNT_REG (0x4000001C)	
Table 73: BLE_FINETIMECNT_REG (0x40000020)	
Table 74: BLE_BDADDRL_REG (0x40000024)	
Table 75: BLE_BDADDRU_REG (0x40000028)	
Table 76: BLE_CURRENTRXDESCPTR_REG (0x4000002C)	
Table 77: BLE_DEEPSLCNTL_REG (0x40000030)	
Table 78: BLE_DEEPSLWKUP_REG (0x40000034)	
Table 79: BLE_DEEPSLSTAT_REG (0x40000038)	
Table 80: BLE_ENBPRESET_REG (0x4000003C)	
Table 81: BLE_FINECNTCORR_REG (0x40000040)	
Table 82: BLE_BASETIMECNTCORR_REG (0x40000044)	
Table 83: BLE_DIAGCNTL_REG (0x40000050)	
Table 84: BLE_DIAGSTAT_REG (0x40000054)	
Table 85: BLE_DEBUGADDMAX_REG (0x40000054)	
14510 00. DEE_DEDOORDDINAN_NEO (0X+0000000)	170

Table 86: BLE_DEBUGADDMIN_REG (0x4000005C)	176
Table 87: BLE_ERRORTYPESTAT_REG (0x40000060)	176
Table 88: BLE_SWPROFILING_REG (0x40000064)	178
Table 89: BLE_RADIOCNTL1_REG (0x40000074)	178
Table 90: BLE_RADIOPWRUPDN_REG (0x40000080)	179
Table 91: BLE_ADVCHMAP_REG (0x40000090)	
Table 92: BLE_ADVTIM_REG (0x400000A0)	
Table 93: BLE_ACTSCANSTAT_REG (0x400000A4)	179
Table 94: BLE_WLPUBADDPTR_REG (0x400000B0)	180
Table 95: BLE_WLPRIVADDPTR_REG (0x400000B4)	
Table 96: BLE_WLNBDEV_REG (0x400000B8)	180
Table 97: BLE_AESCNTL_REG (0x400000C0)	180
Table 98: BLE_AESKEY31_0_REG (0x400000C4)	180
Table 99: BLE_AESKEY63_32_REG (0x400000C8)	180
Table 100: BLE_AESKEY95_64_REG (0x400000CC)	180
Table 101: BLE_AESKEY127_96_REG (0x400000D0)	181
Table 102: BLE_AESPTR_REG (0x400000D4)	181
Table 103: BLE_TXMICVAL_REG (0x400000D8)	181
Table 104: BLE_RXMICVAL_REG (0x400000DC)	181
Table 105: BLE_RFTESTCNTL_REG (0x400000E0)	181
Table 106: BLE_RFTESTTXSTAT_REG (0x400000E4)	182
Table 107: BLE_RFTESTRXSTAT_REG (0x400000E8)	
Table 108: BLE_TIMGENCNTL_REG (0x400000F0)	
Table 109: BLE_GROSSTIMTGT_REG (0x400000F4)	
Table 110: BLE_FINETIMTGT_REG (0x400000F8)	
Table 111: BLE_SAMPLECLK_REG (0x400000FC)	
Table 112: BLE_COEXIFCNTL0_REG (0x40000100)	
Table 113: BLE_COEXIFCNTL1_REG (0x40000104)	
Table 114: BLE_BLEMPRIO0_REG (0x40000108)	
Table 115: BLE_BLEMPRIO1_REG (0x4000010C)	
Table 116: BLE_CNTL2_REG (0x40000200)	
Table 117: BLE EM BASE REG (0x40000208)	
Table 118: BLE_DIAGCNTL2_REG (0x4000020C)	
Table 119: BLE_DIAGCNTL3_REG (0x40000210)	
Table 120: Register map CRG	
Table 121: CLK_AMBA_REG (0x50000000)	
Table 122: CLK_FREQ_TRIM_REG (0x50000002)	
Table 123: CLK_PER_REG (0x50000004)	
Table 124: CLK_RADIO_REG (0x50000008)	
Table 125: CLK_CTRL_REG (0x5000000A)	
Table 126: PMU_CTRL_REG (0x50000010)	
Table 127: SYS_CTRL_REG (0x50000012)	
Table 128: SYS_STAT_REG (0x50000014)	
Table 129: TRIM_CTRL_REG (0x50000014)	
Table 130: RAM_PWR_CTRL_REG (0x50000018)	
Table 131: CLK_RC32K_REG (0x50000010)	
Table 131: CLK_KC32K_KEG (0x30000020)	
Table 132: CLK_ATAL32K_REG (0x500000022)	
TADIO 100. OLIN_INOUZIVI_INEO (UNUUUUUUUUUUUUUUUUUUUUUUUUUUUUUUUUUUU	

Table 134: CLK_RCX_REG (0x50000026)	107
Table 135: BANDGAP_REG (0x50000028)	
_ ,	
Table 136: ANA_STATUS_REG (0x5000002A)	
Table 137: XTAL32M_START_REG (0x50000030)	
Table 138: XTAL32M_TRSTAT_REG (0x50000032)	
Table 139: XTALRDY_CTRL_REG (0x50000034)	
Table 140: XTAL32M_CTRL0_REG (0x50000038)	
Table 141: POR_PIN_REG (0x50000040)	
Table 142: POR_TIMER_REG (0x50000042)	
Table 143: PMU_SLEEP_REG (0x50000050)	
Table 144: POWER_CTRL_REG (0x50000052)	
Table 145: POWER_LEVEL_REG (0x50000054)	
Table 146: Register map CRG_TIM	
Table 147: CLK_RTCDIV_REG (0x5000424C)	202
Table 148: Register map DCDC	204
Table 149: DCDC_CTRL_REG (0x50000080)	204
Table 150: Register map DMA	206
Table 151: DMA0_A_STARTL_REG (0x50003600)	207
Table 152: DMA0_A_STARTH_REG (0x50003602)	207
Table 153: DMA0_B_STARTL_REG (0x50003604)	
Table 154: DMA0_B_STARTH_REG (0x50003606)	
Table 155: DMA0_INT_REG (0x50003608)	
Table 156: DMA0_LEN_REG (0x5000360A)	
Table 157: DMA0_CTRL_REG (0x5000360C)	
Table 158: DMA0_IDX_REG (0x5000360E)	
Table 159: DMA1_A_STARTL_REG (0x50003610)	
Table 160: DMA1_A_STARTH_REG (0x50003612)	
Table 161: DMA1_B_STARTL_REG (0x50003614)	
Table 161: DMA1_B_STARTH_REG (0x50003616)	
Table 163: DMA1_INT_REG (0x50003618)	
Table 164: DMA1_LEN_REG (0x5000361A)	
Table 165: DMA1_CTRL_REG (0x5000361C)	
Table 166: DMA1_IDX_REG (0x5000361E)	
Table 167: DMA2_A_STARTL_REG (0x50003620)	
Table 168: DMA2_A_STARTH_REG (0x50003622)	
Table 169: DMA2_B_STARTL_REG (0x50003624)	
Table 170: DMA2_B_STARTH_REG (0x50003626)	
Table 171: DMA2_INT_REG (0x50003628)	
Table 172: DMA2_LEN_REG (0x5000362A)	
Table 173: DMA2_CTRL_REG (0x5000362C)	
Table 174: DMA2_IDX_REG (0x5000362E)	214
Table 175: DMA3_A_STARTL_REG (0x50003630)	214
Table 176: DMA3_A_STARTH_REG (0x50003632)	214
Table 177: DMA3_B_STARTL_REG (0x50003634)	214
Table 178: DMA3_B_STARTH_REG (0x50003636)	214
Table 179: DMA3_INT_REG (0x50003638)	
Table 180: DMA3_LEN_REG (0x5000363A)	
Table 181: DMA3_CTRL_REG (0x5000363C)	

Table 182: DMA3_IDX_REG (0x5000363E)	216
Table 183: DMA_REQ_MUX_REG (0x50003680)	216
Table 184: DMA_INT_STATUS_REG (0x50003682)	217
Table 185: DMA_CLEAR_INT_REG (0x50003684)	217
Table 186: Register map GPADC	218
Table 187: GP_ADC_CTRL_REG (0x50001500)	218
Table 188: GP_ADC_CTRL2_REG (0x50001502)	219
Table 189: GP_ADC_CTRL3_REG (0x50001504)	220
Table 190: GP_ADC_SEL_REG (0x50001506)	221
Table 191: GP_ADC_OFFP_REG (0x50001508)	221
Table 192: GP_ADC_OFFN_REG (0x5000150A)	221
Table 193: GP_ADC_TRIM_REG (0x5000150C)	221
Table 194: GP_ADC_CLEAR_INT_REG (0x5000150E)	222
Table 195: GP_ADC_RESULT_REG (0x50001510)	222
Table 196: Register map GPIO	222
Table 197: P0_DATA_REG (0x50003000)	223
Table 198: P0_SET_DATA_REG (0x50003002)	223
Table 199: P0_RESET_DATA_REG (0x50003004)	223
Table 200: P00_MODE_REG (0x50003006)	223
Table 201: P01_MODE_REG (0x50003008)	224
Table 202: P02_MODE_REG (0x5000300A)	224
Table 203: P03_MODE_REG (0x5000300C)	225
Table 204: P04_MODE_REG (0x5000300E)	225
Table 205: P05_MODE_REG (0x50003010)	225
Table 206: P06_MODE_REG (0x50003012)	225
Table 207: P07_MODE_REG (0x50003014)	226
Table 208: P08_MODE_REG (0x50003016)	226
Table 209: P09_MODE_REG (0x50003018)	226
Table 210: P010_MODE_REG (0x5000301A)	226
Table 211: P011_MODE_REG (0x5000301C)	227
Table 212: PAD_WEAK_CTRL_REG (0x5000301E)	227
Table 213: Register map GPREG	228
Table 214: SET_FREEZE_REG (0x50003300)	228
Table 215: RESET_FREEZE_REG (0x50003302)	228
Table 216: DEBUG_REG (0x50003304)	229
Table 217: GP_STATUS_REG (0x50003306)	229
Table 218: GP_CONTROL_REG (0x50003308)	229
Table 219: BLE_TIMER_REG (0x5000330A)	230
Table 220: Register map I2C	231
Table 221: I2C_CON_REG (0x50001300)	232
Table 222: I2C_TAR_REG (0x50001304)	
Table 223: I2C_SAR_REG (0x50001308)	233
Table 224: I2C_DATA_CMD_REG (0x50001310)	
Table 225: I2C_SS_SCL_HCNT_REG (0x50001314)	
Table 226: I2C_SS_SCL_LCNT_REG (0x50001318)	
Table 227: I2C_FS_SCL_HCNT_REG (0x5000131C)	
Table 228: I2C_FS_SCL_LCNT_REG (0x50001320)	
Table 229: I2C_INTR_STAT_REG (0x5000132C)	

Table 230: I2C_INTR_MASK_REG (0x50001330)	237
Table 231: I2C_RAW_INTR_STAT_REG (0x50001334)	238
Table 232: I2C_RX_TL_REG (0x50001338)	240
Table 233: I2C_TX_TL_REG (0x5000133C)	240
Table 234: I2C_CLR_INTR_REG (0x50001340)	240
Table 235: I2C_CLR_RX_UNDER_REG (0x50001344)	240
Table 236: I2C_CLR_RX_OVER_REG (0x50001348)	240
Table 237: I2C_CLR_TX_OVER_REG (0x5000134C)	241
Table 238: I2C_CLR_RD_REQ_REG (0x50001350)	241
Table 239: I2C_CLR_TX_ABRT_REG (0x50001354)	241
Table 240: I2C_CLR_RX_DONE_REG (0x50001358)	241
Table 241: I2C_CLR_ACTIVITY_REG (0x5000135C)	242
Table 242: I2C_CLR_STOP_DET_REG (0x50001360)	242
Table 243: I2C_CLR_START_DET_REG (0x50001364)	242
Table 244: I2C_CLR_GEN_CALL_REG (0x50001368)	242
Table 245: I2C_ENABLE_REG (0x5000136C)	242
Table 246: I2C_STATUS_REG (0x50001370)	243
Table 247: I2C_TXFLR_REG (0x50001374)	244
Table 248: I2C_RXFLR_REG (0x50001378)	
Table 249: I2C_SDA_HOLD_REG (0x5000137C)	
Table 250: I2C_TX_ABRT_SOURCE_REG (0x50001380)	
Table 251: I2C_DMA_CR_REG (0x50001388)	
Table 252: I2C_DMA_TDLR_REG (0x5000138C)	
Table 253: I2C_DMA_RDLR_REG (0x50001390)	
Table 254: I2C_SDA_SETUP_REG (0x50001394)	
Table 255: I2C_ACK_GENERAL_CALL_REG (0x50001398)	
Table 256: I2C_ENABLE_STATUS_REG (0x5000139C)	
Table 257: I2C_IC_FS_SPKLEN_REG (0x500013A0)	
Table 258: Register map KBRD	
Table 259: GPIO_IRQ0_IN_SEL_REG (0x50001400)	
Table 260: GPIO_IRQ1_IN_SEL_REG (0x50001402)	
Table 261: GPIO_IRQ2_IN_SEL_REG (0x50001404)	
Table 262: GPIO_IRQ3_IN_SEL_REG (0x50001406)	
Table 263: GPIO_IRQ4_IN_SEL_REG (0x50001408)	
Table 264: GPIO_DEBOUNCE_REG (0x5000140C)	
Table 265: GPIO_RESET_IRQ_REG (0x5000140E)	
Table 266: GPIO_INT_LEVEL_CTRL_REG (0x50001410)	
Table 267: KBRD_IRQ_IN_SEL0_REG (0x50001412)	
Table 268: KBRD_CTRL_REG (0x50001414)	
Table 269: Register map CRG_AON	
Table 270: HWR_CTRL_REG (0x50000300)	
Table 271: RESET_STAT_REG (0x50000304)	
Table 272: RAM_LPMX_REG (0x50000308)	
Table 273: PAD_LATCH_REG (0x5000030C)	
Table 274: HIBERN_CTRL_REG (0x50000310)	
Table 274: TIBERIN_CTRL_REG (0x50000310)	
Table 276: GP_DATA_REG (0x500000324)	
Table 277: Register map OTPC	
Table 211. Register map 011 0	ZJU

Table 278: OTPC_MODE_REG (0x07F40000)	256
Table 279: OTPC_STAT_REG (0x07F40004)	
Table 280: OTPC_PADDR_REG (0x07F40008)	
Table 281: OTPC_PWORD_REG (0x07F4000C)	
Table 282: OTPC_TIM1_REG (0x07F40010)	258
Table 283: OTPC_TIM2_REG (0x07F40014)	259
Table 284: OTPC_AHBADR_REG (0x07F40018)	
Table 285: OTPC_CELADR_REG (0x07F4001C)	260
Table 286: OTPC_NWORDS_REG (0x07F40020)	261
Table 287: Register map QDEC	261
Table 288: QDEC_CTRL_REG (0x50000200)	261
Table 289: QDEC_XCNT_REG (0x50000202)	261
Table 290: QDEC_YCNT_REG (0x50000204)	262
Table 291: QDEC_CLOCKDIV_REG (0x50000206)	262
Table 292: QDEC_CTRL2_REG (0x50000208)	262
Table 293: QDEC_ZCNT_REG (0x5000020A)	263
Table 294: QDEC_EVENT_CNT_REG (0x5000020C)	263
Table 295: Register map RTC	263
Table 296: RTC_CONTROL_REG (0x50004100)	264
Table 297: RTC_HOUR_MODE_REG (0x50004104)	264
Table 298: RTC_TIME_REG (0x50004108)	264
Table 299: RTC_CALENDAR_REG (0x5000410C)	265
Table 300: RTC_TIME_ALARM_REG (0x50004110)	265
Table 301: RTC_CALENDAR_ALARM_REG (0x50004114)	266
Table 302: RTC_ALARM_ENABLE_REG (0x50004118)	266
Table 303: RTC_EVENT_FLAGS_REG (0x5000411C)	267
Table 304: RTC_INTERRUPT_ENABLE_REG (0x50004120)	267
Table 305: RTC_INTERRUPT_DISABLE_REG (0x50004124)	268
Table 306: RTC_INTERRUPT_MASK_REG (0x50004128)	268
Table 307: RTC_STATUS_REG (0x5000412C)	269
Table 308: RTC_KEEP_RTC_REG (0x50004130)	269
Table 309: Register map SPI	270
Table 310: SPI_CTRL_REG (0x50001200)	270
Table 311: SPI_CONFIG_REG (0x50001204)	271
Table 312: SPI_CLOCK_REG (0x50001208)	271
Table 313: SPI_FIFO_CONFIG_REG (0x5000120C)	271
Table 314: SPI_IRQ_MASK_REG (0x50001210)	272
Table 315: SPI_STATUS_REG (0x50001214)	272
Table 316: SPI_FIFO_STATUS_REG (0x50001218)	272
Table 317: SPI_FIFO_READ_REG (0x5000121C)	273
Table 318: SPI_FIFO_WRITE_REG (0x50001220)	273
Table 319: SPI_CS_CONFIG_REG (0x50001224)	273
Table 320: SPI_FIFO_HIGH_REG (0x50001228)	273
Table 321: SPI_TXBUFFER_FORCE_L_REG (0x5000122C)	273
Table 322: SPI_TXBUFFER_FORCE_H_REG (0x50001230)	274
Table 323: Register map Timer+3PWM	274
Table 324: TIMER0_CTRL_REG (0x50003400)	274
Table 325: TIMER0_ON_REG (0x50003402)	275

Table 326: TIMER0_RELOAD_M_REG (0x50003404)	275
Table 327: TIMER0_RELOAD_N_REG (0x50003406)	275
Table 328: TRIPLE_PWM_FREQUENCY (0x50003408)	275
Table 329: PWM2_START_CYCLE (0x5000340A)	275
Table 330: PWM3_START_CYCLE (0x5000340C)	276
Table 331: PWM4_START_CYCLE (0x5000340E)	276
Table 332: PWM5_START_CYCLE (0x50003410)	276
Table 333: PWM6_START_CYCLE (0x50003412)	276
Table 334: PWM7_START_CYCLE (0x50003414)	276
Table 335: PWM2_END_CYCLE (0x50003416)	
Table 336: PWM3_END_CYCLE (0x50003418)	276
Table 337: PWM4_END_CYCLE (0x5000341A)	277
Table 338: PWM5_END_CYCLE (0x5000341C)	
Table 339: PWM6_END_CYCLE (0x5000341E)	
Table 340: PWM7_END_CYCLE (0x50003420)	
Table 341: TRIPLE_PWM_CTRL_REG (0x50003422)	
Table 342: Register map Timer1	
Table 343: TIMER1_CTRL_REG (0x50004000)	
Table 344: TIMER1 CAPTURE REG (0x50004004)	
Table 345: TIMER1 STATUS REG (0x50004008)	
Table 346: TIMER1_CAPCNT1_VALUE_REG (0x5000400C)	
Table 347: TIMER1_CAPCNT2_VALUE_REG (0x50004010)	
Table 348: TIMER1_CLR_EVENT_REG (0x50004014)	
Table 349: Register map UART	
Table 350: UART_RBR_THR_DLL_REG (0x50001000)	
Table 351: UART_IER_DLH_REG (0x50001004)	
Table 352: UART_IIR_FCR_REG (0x50001008)	
Table 353: UART_LCR_REG (0x5000100C)	
Table 354: UART_MCR_REG (0x50001010)	
Table 355: UART_LSR_REG (0x50001014)	
Table 356: UART MSR REG (0x50001018)	
Table 357: UART_SCR_REG (0x5000101C)	
Table 358: UART_SRBR_STHR0_REG (0x50001030)	
Table 359: UART_SRBR_STHR1_REG (0x50001034)	
Table 360: UART_SRBR_STHR2_REG (0x50001038)	
Table 361: UART_SRBR_STHR3_REG (0x5000103C)	
Table 362: UART_SRBR_STHR4_REG (0x50001040)	
Table 363: UART_SRBR_STHR5_REG (0x50001044)	
Table 364: UART_SRBR_STHR6_REG (0x50001048)	
Table 365: UART_SRBR_STHR7_REG (0x5000104C)	
Table 366: UART_SRBR_STHR8_REG (0x50001050)	
Table 367: UART_SRBR_STHR9_REG (0x50001054)	
Table 368: UART_SRBR_STHR10_REG (0x50001058)	
Table 369: UART_SRBR_STHR11_REG (0x5000105C)	
Table 370: UART_SRBR_STHR12_REG (0x50001060)	
Table 371: UART_SRBR_STHR13_REG (0x50001064)	
Table 372: UART_SRBR_STHR14_REG (0x50001068)	
Table 373: UART_SRBR_STHR15_REG (0x5000106C)	

Table 374: UART_FAR_REG (0x50001070)	301
Table 375: UART_USR_REG (0x5000107C)	301
Table 376: UART_TFL_REG (0x50001080)	302
Table 377: UART_RFL_REG (0x50001084)	302
Table 378: UART_SRR_REG (0x50001088)	303
Table 379: UART_SRTS_REG (0x5000108C)	303
Table 380: UART_SBCR_REG (0x50001090)	303
Table 381: UART_SDMAM_REG (0x50001094)	304
Table 382: UART_SFE_REG (0x50001098)	304
Table 383: UART_SRT_REG (0x5000109C)	304
Table 384: UART_STET_REG (0x500010A0)	305
Table 385: UART_HTX_REG (0x500010A4)	305
Table 386: UART_DMASA_REG (0x500010A8)	305
Table 387: UART_DLF_REG (0x500010C0)	306
Table 388: UART_UCV_REG (0x500010F8)	306
Table 389: UART_UCV_HIGH_REG (0x500010FA)	306
Table 390: UART_CTR_REG (0x500010FC)	
Table 391: UART_CTR_HIGH_REG (0x500010FE)	306
Table 392: UART2_RBR_THR_DLL_REG (0x50001100)	306
Table 393: UART2_IER_DLH_REG (0x50001104)	307
Table 394: UART2_IIR_FCR_REG (0x50001108)	308
Table 395: UART2_LCR_REG (0x5000110C)	
Table 396: UART2_MCR_REG (0x50001110)	311
Table 397: UART2_LSR_REG (0x50001114)	311
Table 398: UART2_SCR_REG (0x5000111C)	313
Table 399: UART2_SRBR_STHR0_REG (0x50001130)	
Table 400: UART2_SRBR_STHR1_REG (0x50001134)	
Table 401: UART2_SRBR_STHR2_REG (0x50001138)	
Table 402: UART2_SRBR_STHR3_REG (0x5000113C)	
Table 403: UART2_SRBR_STHR4_REG (0x50001140)	
Table 404: UART2_SRBR_STHR5_REG (0x50001144)	
Table 405: UART2_SRBR_STHR6_REG (0x50001148)	
Table 406: UART2_SRBR_STHR7_REG (0x5000114C)	
Table 407: UART2_SRBR_STHR8_REG (0x50001150)	
Table 408: UART2_SRBR_STHR9_REG (0x50001154)	
Table 409: UART2_SRBR_STHR10_REG (0x50001158)	
Table 410: UART2_SRBR_STHR11_REG (0x5000115C)	
Table 411: UART2_SRBR_STHR12_REG (0x50001160)	
Table 412: UART2 SRBR STHR13 REG (0x50001164)	
Table 413: UART2_SRBR_STHR14_REG (0x50001168)	
Table 414: UART2_SRBR_STHR15_REG (0x5000116C)	
Table 415: UART2_FAR_REG (0x50001170)	
Table 416: UART2_USR_REG (0x5000117C)	
Table 417: UART2_TFL_REG (0x50001180)	
Table 418: UART2_RFL_REG (0x50001184)	
Table 419: UART2_SRR_REG (0x50001188)	
Table 420: UART2_SBCR_REG (0x50001190)	
Table 421: UART2_SDMAM_REG (0x50001194)	

Table 422: UART2_SFE_REG (0x50001198)	325
Table 423: UART2_SRT_REG (0x5000119C)	325
Table 424: UART2_STET_REG (0x500011A0)	325
Table 425: UART2_HTX_REG (0x500011A4)	326
Table 426: UART2_DMASA_REG (0x500011A8)	326
Table 427: UART2_DLF_REG (0x500011C0)	326
Table 428: UART2_UCV_REG (0x500011F8)	326
Table 429: UART2_UCV_HIGH_REG (0x500011FA)	326
Table 430: UART2_CTR_REG (0x500011FC)	326
Table 431: UART2_CTR_HIGH_REG (0x500011FE)	327
Table 432: Register map Version	327
Table 433: CHIP_ID1_REG (0x50003200)	327
Table 434: CHIP_ID2_REG (0x50003204)	327
Table 435: CHIP_ID3_REG (0x50003208)	327
Table 436: CHIP_ID4_REG (0x5000320C)	327
Table 437: Register map WKUP	327
Table 438: WKUP_CTRL_REG (0x50000100)	328
Table 439: WKUP_COMPARE_REG (0x50000102)	328
Table 440: WKUP_IRQ_STATUS_REG (0x50000104)	328
Table 441: WKUP_COUNTER_REG (0x50000106)	329
Table 442: WKUP_SELECT_GPIO_REG (0x50000108)	329
Table 443: WKUP2_SELECT_GPIO_REG (0x5000010A)	329
Table 444: WKUP_POL_GPIO_REG (0x5000010C)	329
Table 445: WKUP2_POL_GPIO_REG (0x5000010E)	329
Table 446: Register map WDOG	329
Table 447: WATCHDOG_REG (0x50003100)	330
Table 448: WATCHDOG_CTRL_REG (0x50003102)	330
Table 449: Ordering Information (Samples)	331
Table 450: Ordering Information (Production)	331
Table 451: MSL Classification	

1. Block Diagram




Figure 2. DA14531 block diagram

2. DA14531-0x Product Variants

Table 1 presents the differentiation among the variants of the DA14531-0x.

Table 1: DA14531-0x Product Variants Differentiation

Features	DA14531-00	DA14531-01
LE Central support	✓	×
LE Observer support	✓	×
Generation of Private addresses support	✓	×
LL 2/5 Resolution of Private addresses support	✓	×
Compatible with SDK 6.0.16 or lower	✓	×
Rest of features	✓	✓

3. Packages and Pinout

The DA14531 comes in two packages:

- A Wafer Level Chip Scale Package (WLCSP) with 17 balls
- A Quad Flat No Leads Package (FCGQFN) with 24 pins

The actual pin/ball assignment is depicted in the following sections.

3.1 WLCSP17




Figure 3. WLCSP17 ball assignment (top view)

Table 2: DA14531 WLCSP17 Ball Description

Ball no.	Pin name	Туре	Reset state	Description
Gene	eral Purpose I/Os	(Note 3)		
F4	P0_0	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power-down.
	RST	DIO (Type B)		RST active high hardware reset (default).
E5	P0_1	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.
	ADC0	Al		INPUT. Analog to Digital Converter input 0.
	SWDIO	DIO		INPUT/OUTPUT. JTAG Data input/output. Bidirectional data and control communication.
C5	P0_2	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.
	ADC1	Al		INPUT. Analog to Digital Converter input 1.
	SWCLK	DIO		INPUT JTAG clock signal (by default).
B4	P0_3	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down. Check GP_DATA_REG[P03_P04_FILT_DIS] for correct pad filter settings.
	XTAL32kp	Al		INPUT. Analog input of the XTAL32K crystal oscillator.
		DI		INPUT. Digital input for an external clock (square wave).
A5	P0_4	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down. Check GP_DATA_REG[P03_P04_FILT_DIS] for correct pad filter settings.
	XTAL32km	AO		OUTPUT. Analog output of the XTAL32K crystal oscillator.
D4	P0_5	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.
	SWDIO	DIO		INPUT/OUTPUT. JTAG Data input/output. Bidirectional data and control communication (by default).
Debu	ıg Interface			
E5 D4	SWDIO	DIO	I-PD	INPUT/OUTPUT. JTAG Data input/output. Bidirectional data and control communication. Mapped on P0_1 or P0_5 (P0_5 by default).

Ball no.	Pin name	Туре	Reset state	Description
C5	SWCLK	DIO	I-PD	INPUT JTAG clock signal. Mapped on P0_2 (by default).
Clock	(S		•	
D2	XTAL32Mp	AI		INPUT. Crystal input for the 32 MHz XTAL.
E1	XTAL32Mm	AO		OUTPUT. Crystal output for the 32 MHz XTAL.
B4	XTAL32kp	Al		INPUT. Crystal input for the 32.768 kHz XTAL. Mapped on P0_3.
A5	XTAL32km	AO		OUTPUT. Crystal output for the 32.768 kHz XTAL. Mapped on P0_4.
Quad	rature Decoder			
	QD_CHA_X	DI		INPUT. Channel A for the X axis. Mapped on Px ports.
	QD_CHB_X	DI		INPUT. Channel B for the X axis. Mapped on Px ports.
	QD_CHA_Y	DI		INPUT. Channel A for the Y axis. Mapped on Px ports.
	QD_CHB_Y	DI		INPUT. Channel B for the Y axis. Mapped on Px ports.
	QD_CHA_Z	DI		INPUT. Channel A for the Z axis. Mapped on Px ports.
	QD_CHB_Z	DI		INPUT. Channel B for the Z axis. Mapped on Px ports.
SPI B	us Interface			
	SPI_CLK	DO		INPUT/OUTPUT. SPI Clock. Mapped on Px ports.
	SPI_DI	DI		INPUT. SPI Data input. Mapped on Px ports (Note 1).
	SPI_DO	DO		OUTPUT. SPI Data output. Mapped on Px ports (Note 2).
	SPI_EN	DI/DO		INPUT/OUTPUT. SPI Clock enable. Mapped on Px ports.
I2C B	us Interface			
	SDA	DIO/DIOD		INPUT/OUTPUT. I2C bus data with open drain port. Mapped on Px ports. The mapped Px pin is automatically configured with a pull-up resistor (25 k Ω) when pin x is mapped to the I2C_SDA PID function.
	SCL	DIO/DIOD		INPUT/OUTPUT. I2C bus Clock with open drain port. In open drain mode, SCL is monitored to support bit stretching by a slave. Mapped on Px ports. The mapped Px pin is automatically configured with a pull-up resistor (25 k Ω) when pin x is mapped to the I2C_SCL PID function.
UAR1	Interface	<u> </u>		
	UTX	DO		OUTPUT. UART transmit data. Mapped on Px ports.
	URX	DI		INPUT. UART receive data. Mapped on Px ports.
	URTS	DO		OUTPUT. UART Request to Send. Mapped on Px ports.
	UCTS	DI		INPUT. UART Clear to Send. Mapped on Px ports.
	UTX2	DO		OUTPUT. UART2 transmit data. Mapped on Px ports.
	URX2	DI		INPUT. UART2 receive data. Mapped on Px ports.
ADC	IO Channels			
E5	ADC0	Al		INPUT. Analog to Digital Converter input 0. Mapped on P0_1.
E5	ADC0	Al		INPUT. Analog to Digital Converter input 0. Mapped on Po

Ball no.	Pin name	Туре	Reset state	Description
C5	ADC1	Al		INPUT. Analog to Digital Converter input 1. Mapped on P0_2.
Radio	Transceiver			
A1	RFIOp	AIO		RF input/output. Impedance 50 Ω.
А3	RFIOm	AIO		RF ground.
C3	GND_RF1	AIO		RF ground.
C1	GND_RF2	AIO		RF ground.
Misce	ellaneous			
F4	RST	DIO		INPUT. Reset signal (active high). Mapped on P0_0 (by default).
G3	LX	AIO		INPUT/OUTPUT. Connection for the external DC-DC converter inductor.
Powe	er and Ground			
E3	VSS	AIO		Digital ground.
G5	Vват_ніgh	AIO		INPUT/OUTPUT. Battery connection or DCDC output in BUCK/BOOST mode, respectively. IO-supply.
G1	V _{BAT_LOW}	AIO		INPUT/OUTPUT. Battery connection or DCDC output in BOOST/BUCK mode, respectively. System supply.
F2	GND_DCDC	AIO		DCDC ground

Note 1 Data input only. MOSI in SPI slave mode and MISO in SPI master mode.

Note 2 Data output only. MISO in SPI slave mode and MOSI in SPI master mode.

Note 3 The differences between Type A and Type B GPIO pads are presented in Types of GPIO Pads.

3.2 FCGQFN24




Figure 4. FCGQFN24 pin assignment (top view)

Table 3: DA14531 FCGQFN24 Pin Description

Pin no.	Pin name	Туре	Reset state	Description			
Gene	General Purpose I/Os (Note 3)						
10	P0_0	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.			
	RST	DIO (Type B)		RST active high hardware reset (default).			
11	P0_1	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.			
	ADC0	Al		INPUT. Analog to Digital Converter input 0.			
12	P0_2	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or			

Pin no.	Pin name	Туре	Reset state	Description
				alternate function nodes. Contains a state retention mechanism during power down.
	ADC1	Al		INPUT. Analog to Digital Converter input 1.
	SWCLK	DIO		INPUT JTAG clock signal (by default).
13	P0_3	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down. Check GP_DATA_REG[P03_P04_FILT_DIS] for correct pad filter settings.
	XTAL32kp	Al		INPUT. Analog input of the XTAL32K crystal oscillator.
		DI		INPUT. Digital input for an external clock (square wave).
14	P0_4	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down. Check GP_DATA_REG[P03_P04_FILT_DIS] for correct pad filter settings.
	XTAL32km	AO		OUTPUT. Analog output of the XTAL32K crystal oscillator.
24	P0_5	DIO (Type B)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.
22	P0_6	DIO (Type A)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.
	ADC2	Al		INPUT. Analog to Digital Converter input 2.
15	P0_7	DIO (Type A)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.
	ADC3	AI		INPUT. Analog to Digital Converter input 3.
17	P0_8	DIO (Type A)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.
16	P0_9	DIO (Type A)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.
9	P0_10	DIO (Type A)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.
	SWDIO	DIO		INPUT/OUTPUT. JTAG Data input/output. Bidirectional data and control communication (by default).

Pin no.	Pin name	Туре	Reset state	Description
8	P0_11	DIO (Type A)	I-PD	INPUT/OUTPUT with selectable pull-up/down resistors. Pull-down enabled during and after reset. General purpose I/O port bit or alternate function nodes. Contains a state retention mechanism during power down.
Debu	ıg Interface	•		
9	SWDIO	DIO	I-PD	INPUT/OUTPUT. JTAG Data input/output. Bidirectional data and control communication. Mapped on P0_10 (by default).
12	SWCLK	DIO	I-PD	INPUT JTAG clock signal. Mapped on P0_2 (by default).
Cloc	ks	•		
3	XTAL32Mp	Al		INPUT. Crystal input for the 32 MHz XTAL.
4	XTAL32Mm	AO		OUTPUT. Crystal output for the 32 MHz XTAL.
13	XTAL32kp	Al		INPUT. Crystal input for the 32.768 kHz XTAL. Mapped on P0_3.
14	XTAL32km	AO		OUTPUT. Crystal output for the 32.768 kHz XTAL. Mapped on P0_4.
Quac	drature Decoder		•	
	QD_CHA_X	DI		INPUT. Channel A for the X axis. Mapped on Px ports.
	QD_CHB_X	DI		INPUT. Channel B for the X axis. Mapped on Px ports.
	QD_CHA_Y	DI		INPUT. Channel A for the Y axis. Mapped on Px ports.
	QD_CHB_Y	DI		INPUT. Channel B for the Y axis. Mapped on Px ports.
	QD_CHA_Z	DI		INPUT. Channel A for the Z axis. Mapped on Px ports.
	QD_CHB_Z	DI		INPUT. Channel B for the Z axis. Mapped on Px ports.
SPI E	Bus Interface	•		
	SPI_CLK	DO		INPUT/OUTPUT. SPI Clock. Mapped on Px ports.
	SPI_DI	DI		INPUT. SPI Data input. Mapped on Px ports (Note 1).
	SPI_DO	DO		OUTPUT. SPI Data output. Mapped on Px ports (Note 2).
	SPI_EN	DI/DO		INPUT/OUTPUT. SPI Clock enable. Mapped on Px ports.
I2C E	Bus Interface			
	SDA	DIO/DIOD		INPUT/OUTPUT. I2C bus Data with open drain port. Mapped on Px ports. The mapped Px pin is automatically configured with a pull-up resistor (25 k Ω) when pin x is mapped to the I2C_SDA PID function.
	SCL	DIO/DIOD		INPUT/OUTPUT. I2C bus Clock with open drain port. In open drain mode, SCL is monitored to support bit stretching by a slave. Mapped on Px ports. The mapped Px pin is automatically configured with a pull-up resistor (25 k Ω) when pin x is mapped to the I2C_SCL PID function.
UAR	T Interface			
	UTX	DO		OUTPUT. UART transmit data. Mapped on Px ports.
	URX	DI		INPUT. UART receive data. Mapped on Px ports.
	URTS	DO		OUTPUT. UART Request to Send. Mapped on Px ports.

Pin no.	Pin name	Туре	Reset state	Description
	UCTS	DI		INPUT. UART Clear to Send. Mapped on Px ports.
	UTX2	DO		OUTPUT. UART2 transmit data. Mapped on Px ports.
	URX2	DI		INPUT. UART2 receive data. Mapped on Px ports.
ADC	IO Channels			
11	ADC0	AI		INPUT. Analog to Digital Converter input 0. Mapped on P0_1.
12	ADC1	AI		INPUT. Analog to Digital Converter input 1. Mapped on P0_2.
22	ADC2	AI		INPUT. Analog to Digital Converter input 2. Mapped on P0_6.
15	ADC3	AI		INPUT. Analog to Digital Converter input 3. Mapped on P0_7.
Radi	o Transceiver			
1	RFIOp	AIO		RF input/output. Impedance 50 Ω.
18	RFIOm	AIO		RF ground.
19	GND_RF1	AIO		RF ground.
2	GND_RF2	AIO		RF ground.
Misc	ellaneous			
10	RST	DIO		INPUT. Reset signal (active high). Mapped on P0_0 (by default).
6	LX	AIO		INPUT/OUTPUT. Connection for the external DC-DC converter inductor.
Pow	er and Ground			
23	vss	AIO		Digital ground.
20	GND	AIO		Analog ground.
7	V _{BAT_} HIGH	AIO		INPUT/OUTPUT. Battery connection or DCDC output in BUCK/BOOST mode, respectively. IO supply.
5	V _{BAT_LOW}	AIO		INPUT/OUTPUT. Battery connection or DCDC output in BOOST/BUCK mode, respectively. System supply.
21	GND_DCDC	AIO		DCDC ground.

Note 1 Data input only. MOSI in SPI slave mode and MISO in SPI master mode.

Note 2 Data output only. MISO in SPI slave mode and MOSI in SPI master mode.

Note 3 The differences between Type A and Type B GPIO pads are presented in Types of GPIO Pads.

4. Specifications

All MIN/MAX specification limits are guaranteed by design, production testing and/or statistical characterization. Typical values are based on characterization results at default measurement conditions and are informative only.

Default measurement conditions (unless otherwise specified): V_{BAT_HIGH} = 3.0 V (buck mode), V_{BAT_LOW} = 1.5 V (boost mode), T_A = 25 °C. All radio measurements are performed with standard RF measurement equipment providing a source/load impedance of 50 Ω . All listed currents involving any radio operation have been conducted without the external CLC filter.

Due to the voltage dependent capacitance of MLCC capacitors the specified capacitor values at V_{BAT_HIGH} and V_{BAT_LOW} are effective capacitances.




Figure 5. Boost configuration system diagram




Figure 6. Buck configuration system diagram

4.1 Absolute Maximum Ratings

Table 4: Absolute maximum ratings

Parameter	Description	Conditions	Min	Max	Unit
V _{BAT_LIM_LO}	Limiting supply voltage	Battery voltage in boost configuration, supply voltage in buck configuration	-0.2	3.6	V
V _{BAT_LIM_} HIG	Limiting supply voltage	Battery voltage in buck configuration, supply voltage in boost configuration	-0.2	3.6	V
VPIN_LIM_defa	Limiting voltage on a pin		-0.2	3.6	V
V _{ESD_HBM_FC} GQFN24	Electrostatic discharge voltage (Human Body Model)	RFIOm and RFIOp pins only up to 2.5 kV		4	kV
VESD_HBM_W LCSP17	Electrostatic discharge voltage (Human Body Model)			2	kV
VESD_CDM_F CGQFN24	Electrostatic discharge voltage (Charged Device Model)			500	V
VESD_CDM_W LCSP17	Electrostatic discharge voltage (Charged Device Model)			500	V
T _{STG}	Storage temperature		-50	150	°C

4.2 Recommended Operating Conditions

Table 5: Recommended operating conditions

Parameter	Description	Conditions	Min	Тур	Max	Unit
IL_VBAT_HIGH_ BOOTING	Maximum external DC load current on V _{BAT_HIGH} rail during booting in boost mode	Boost mode booting sequence active			50	μA
VBAT_BYPASS	Supply voltage.Battery voltage.	For OTP functionality refer to VBAT_HIGH_OTP_Program/Read. Minimum boot voltage is 1.8 V	1.1		3.3	V
VBAT_HIGH_BO	DCDC output	For OTP functionality refer to VBAT_HIGH_OTP_Program/Read	1.8		3.3	V
VBAT_HIGH_BU	Supply voltage.Battery voltage.	For OTP functionality refer to VBAT_HIGH_OTP_Program/Read	1.8		3.6	V
V _{BAT_LOW_BO}	Supply voltage.Battery voltage.		1.1		1.6	V
VBAT_LOW_BU	DCDC or LDO_LOW output		1.1		3.3	V
VBAT_HIGH_OT P_Program	Voltage range for OTP programming	Required temperature for programming: -40 °C to 85 °C	2.25		3.6	V
VBAT_HIGH_OT P_Read	Voltage range for OTP reading		1.62		3.6	V

Parameter	Description	Conditions	Min	Тур	Max	Unit
V _{PIN_default}	Voltage on a pin		-0.2		VBAT_ HIGH+ 0.2	٧
TA	Ambient temperature		-40		85	°C

4.3 DC Characteristics

Table 6: DC characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
IBAT_HIGH_HIBE RN_0kB	Battery supply current	Hibernation mode, no RAM retained, no oscillator running; LDO_RET_TRIM = 0xE Note 1		270		nA
IBAT_HIGH_HIBE RN_48kB	Battery supply current	Hibernation mode, 48 kB RAM retained, no oscillator running; LDO_RET_TRIM = 0xD		750		nA
I _{BAT_LOW_HIBE}	Battery supply current	Hibernation mode, no RAM retained, no oscillator running; LDO_RET_TRIM = 0xE Note 2		240		nA
IBAT_LOW_HIBE RN_0kB_5DEG	Battery supply current	Hibernation mode at 5 °C, 0kB RAM retained, no oscillator running; LDO_RET_TRIM = 0xE		150		nA
I _{BAT_LOW_HIBE}	Battery supply current	Hibernation mode, 48 kB RAM retained, no oscillator running; LDO_RET_TRIM = 0xD		700		nA
IBAT_LOW_DP_ SLP_0kB	Battery supply current	Deep-sleep with 0 kB RAM retained, running on RCX; LDO_RET_TRIM = 0xF		0.9		μΑ
IBAT_LOW_EX_S LP_20kB	Battery supply current	Extended-sleep with 20 kB RAM retained, running on RCX; LDO_RET_TRIM = 0xF		1.2		μΑ
IBAT_LOW_EX_S LP_48kB	Battery supply current	Extended-sleep with 48 kB RAM retained, running on RCX; LDO_RET_TRIM = 0xF		1.6		μΑ
BAT_HIGH_DP_ SLP_0kB	Battery supply current	Deep-sleep with no RAM retained, running on RCX; LDO_RET_TRIM = 0xF		1		μΑ
BAT_HIGH_EX_ SLP_20kB	Battery supply current	Extended-sleep mode with 20 kB RAM retained, running on RCX; LDO_RET_TRIM = 0xF		1.2		μΑ
BAT_HIGH_EX_ SLP_48kB	Battery supply current	Extended-sleep mode with 48 kB RAM retained, running on RCX; LDO_RET_TRIM = 0xF		1.6		μΑ

Parameter	Description	Conditions	Min	Тур	Max	Unit
IBAT_LOW_ACT_ RX	Battery supply current	Application with Receiver Active, CPU idle at 16 MHz, DCDC off		5		mA
IBAT_LOW_ACT_ TX	Battery supply current	Application with Pout = 0 dBm, Power setting 9, Transmit continuous unmodulated output power, CPU idle at 16 MHz, DCDC off		8		mA
IBAT_HIGH_ACT _RX	Battery supply current	Application with Receiver Active, CPU idle at 16 MHz, DCDC on		2.2		mA
BAT_HIGH_ACT _TX	Battery supply current	Application with Pout = 0 dBm,Power setting 9, Transmit continuous unmodulated output power, CPU idle at 16 MHz, DCDC on		3.5		mA
BAT_LOW_RUN _16MHz	Battery supply current	CPU executing code from RAM running on XTAL32M oscillator at 16 MHz, DCDC off		830		μА
BAT_HIGH_RUN _16MHz	Battery supply current	CPU executing code from RAM running on XTAL32M oscillator at 16 MHz		380		μА
BAT_HIGH_IDLE _16MHz	Battery supply current	CPU in Wait-for-Interrupt (WFI) state running on XTAL32M oscillator at 16 MHz		230		μА
BAT_LOW_IDLE	Battery supply current	CPU in Wait-for-Interrupt (WFI) state running on XTAL32M oscillator at 16 MHz, DCDC off		460		μА
BAT_HIGH_RST	Battery supply current	Reset pin asserted, buck configuration, V _{BAT_HIGH} = 3.0 V, at 25 °C		200		μA
IBAT_LOW_RST	Battery supply current	Reset pin asserted, boost configuration, V _{BAT_LOW} = 1.5 V, at 25 °C		200		μΑ

Note 1 IBAT_HIGH is Buck configuration at VBAT = 3 V, at 25 °C

Note 2 I_{BAT_LOW} is Boost configuration at VBAT = 1.5 V, at 25 °C

4.4 Timing Characteristics

Table 7: Timing characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
tsta_hiber	Start-up time	Time from hibernation to the first executed code instruction. Applies to both buck or boost modes, excludes capacitors charging time. Assumes VBAT_LOW=VBAT_HIGH with use of the resistive switch so no charging of the respective rail is needed.		0.2	0.4	ms
tsta_slp_buck	Start-up time	Time from GPIO toggle to the first executed code instruction. Applicable for both deep and extended sleep mode. Application in buck configuration at 3 V battery voltage, excluding capacitor charging.	0.86		1.2	ms
tsta_slp_boost	Start-up time	Time from GPIO toggle to the first executed code instruction. Applicable for both deep and extended sleep mode. Application in boost configuration at 1.5 V battery voltage, excluding capacitor charging.	0.83		1.1	ms

4.5 RCX Oscillator

Table 8: RCX Oscillator - Timing characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
Δf _{RC}	RCX oscillator frequency drift	100 ms time slot		100	500	ppm
Δf _{RC} /ΔV_vba T_HIGH	Supply voltage dependency (VBAT_HIGH)		-500	80	500	ppm/V
$\Delta f_{RC}/\Delta V_{_{_{_{_{_{_{_{_{_{_{_{_{_{_{_{_{_{_{$	Supply voltage dependency (VBAT_LOW)		-500	200	3000	ppm/V
f _{RCX}	RCX oscillator frequency	at target fixed trim setting	13	15	17	kHz
$\Delta f_{RC}/\Delta T_{_1}$	Temperature dependency	Temperature range -40 °C to 85 °C, RCX_BIAS at preferred value	-125		125	ppm/de g
$\Delta f_{RC}/\Delta T_{_2}$	Temperature dependency	Temperature range -40 °C to 105 °C, RCX_BIAS at preferred value	-200		200	ppm/de g

4.6 XTAL32MHz Oscillator

Table 9: XTAL32MHz Oscillator - Recommended operating conditions

Parameter	Description	Conditions	Min	Тур	Max	Unit
P _{DRV_MAX}	Maximum drive power	Note 1			100	μW
VCLK_EXT	External clock voltage	In case of external clock source on XTAL32Mp (XTAL32Mm floating or connected to mid-level 0.6 V)		0.9		V
Φ N_EXT_32M	Phase noise	f _C = 50 kHz; in case of external clock source			-130	dBc/Hz
Δfxtal_trim	Crystal frequency trim			2		ppm
f _{XTAL_32M}	Crystal oscillator frequency			32		MHz
Δf _{XTAL}	Crystal frequency tolerance	After optional trimming; including aging and temperature drift Note 2	-20		20	ppm
Δfxtal_unt	Crystal frequency tolerance	Untrimmed; including aging and temperature drift Note 3	-40		40	ppm
ESR_1pF	Equivalent series resistance	C ₀ <1pF			200	Ω
ESR_3pF	Equivalent series resistance	C ₀ <3pF			80	Ω
ESR_5pF	Equivalent series resistance	C ₀ <5pF			50	Ω
CL	Load capacitance	No external capacitors are required	4	6	8	pF

Note 1 Select a crystal which can handle a drive level of at least this specification.

4.7 XTAL32kHz Oscillator

Table 10: XTAL oscillator 32kHz - Recommended operating conditions

Parameter	Description	Conditions	Min	Тур	Max	Unit
fclk_ext	External clock frequency	at pin 32KXTAL1/P0_3 in GPIO mode	10		100	kHz
f _{XTAL}	Crystal oscillator frequency		30	32.768	35	kHz
ESR	Equivalent series resistance				100	kΩ
CL	Load capacitance	No external capacitors are required for a 6 pF or 7 pF crystal	6	7	9	pF
C ₀	Shunt capacitance			1	2	pF

Note 2 Using the internal varicaps a wide range of crystals can be trimmed to the required tolerance.

Note 3 Maximum allowed frequency tolerance for compensation by the internal varicap trimming mechanism.

Parameter	Description	Conditions	Min	Тур	Max	Unit
Δf_{XTAL}	Crystal frequency tolerance (including aging)	Timing accuracy is dominated by crystal accuracy. A much smaller value is preferred.	-250		250	ppm
P _{DRV_MAX}	Maximum drive power	Note 1	0.1			μW

Note 1 Select a crystal that can handle a drive level of at least this specification.

Table 11: XTAL oscillator 32kHz - Timing characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
tsta_xtal	Crystal oscillator start-up time	Typical application, time until 1000 clocks are detected		100	300	ms

4.8 RC32MHz Oscillator

Table 12: RC32MHz Oscillaor - Timing characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
frc32M_TRIMME	RC oscillator frequency	at target trimming	29	30.5	31.5	MHz

4.9 DC-DC Converter

Table 13: DCDC Converter - Recommended operating conditions

Parameter	Description	Conditions	Min	Тур	Max	Unit
Соит	External capacitor	Effective value at DC output voltage	1			μF
L _{EXT}	External inductor		2	2.2	2.4	μH
V _{BAT_HIGH}	Operational supply voltage, applied to V _{BAT_HIGH}	POWER_LEVEL_REG[DCDC _LEVEL] = 0x0	1.8		3.6	V
V _{BAT_LOW}	Operational supply voltage, applied to V _{BAT_LOW}	POWER_LEVEL_REG[DCDC _LEVEL] = 0x1	1.1		1.65	V
IL_VBAT_HIGH_1 V8	Load current on V _{BAT_HIGH} in BOOST mode	V _{OUT} = 1.8 V Note 1			20	mA
IL_VBAT_HIGH_2 V5	Load current on V _{BAT_HIGH} in BOOST mode	V _{OUT} = 2.5 V Note 1			10	mA
IL_VBAT_HIGH_3 V0	Load current on V _{BAT_HIGH} in BOOST mode	V _{OUT} = 3.0 V Note 1			10	mA

Note 1 IL_VBAT_HIGH_BOOTING is applicable during booting

Table 14: DCDC Converter - DC characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
Vo_BUCK_1V1	DC output voltage	DCDC_LEVEL = 0x0 DCDC_TRIM = 0x3	1.075	1.1	1.125	V
Vo_BOOST_1V8	DC output voltage	DCDC_LEVEL = 0x1 DCDC_TRIM = 0x3	1.75	1.8	1.85	V
Vo_BOOST_2V5	DC output voltage	DCDC_LEVEL = 0x2 DCDC_TRIM = 0x3	2.425	2.5	2.575	V
Vo_BOOST_3V0	DC output voltage	DCDC_LEVEL = 0x3 DCDC_TRIM = 0x3	2.9	3	3.1	V
ηсопу_виск	Conversion efficiency	V _{BAT} = 3.0 V V _{OUT} = 1.1 V I _{LOAD} = 10 mA	80	85	90	%
П СОNV_ВООЅТ	Conversion efficiency	V _{BAT} = 1.5 V V _{OUT} = 1.8 V I _{LOAD} = 10 mA	85	90	95	%
V _{RPL_BUCK}	Ripple voltage	V _{BAT} = 3.0 V V _{OUT} = 1.1 V I _{LOAD} = 1 - 20 mA C _{EXT} = 1 μF	5	15	25	mV
Vrpl_boost	Ripple voltage	V _{BAT} = 1.5 V V _{OUT} = 1.8 V I _{LOAD} = 1 - 20 mA C _{EXT} = 1 μF	5	20	35	mV
I _{Q_} vbat_high	Quiescent current BUCK mode	V _{BAT_HIGH} = 3.0 V No load on V _{BAT_LOW}			40	μΑ
I _{Q_VBAT_LOW}	Quiescent current BOOST mode	V _{BAT_LOW} = 1.5 V No load on V _{BAT_HIGH}			75	μΑ

4.10 LDO_LOW Characteristics

Table 15: LDO_LOW - Recommended operating conditions

Parameter	Description	Conditions	Min	Тур	Max	Unit
Соит	Output capacitance		1		10	μF

Table 16: LDO_LOW - DC characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
Vo_active	Output voltage	Active mode (high current) POWER_LEVEL_REG[LDO_L OW_TRIM] = 0x3 (default) ILOAD = 1 mA	1.067	1.1	1.133	V

Parameter	Description	Conditions	Min	Тур	Max	Unit
Vo_sleep	Output voltage	Sleep mode (low current) POWER_LEVEL_REG[LDO_L OW_TRIM] = 0x3 (default) ILOAD = 100 µA	1.056	1.1	1.144	V
Vo_trim_0	Trim step, delta from 1.1 V nominal value	POWER_LEVEL_REG[LDO_L OW_TRIM] = 0x0		-75		mV
Vo_trim_1	Trim step, delta from 1.1 V nominal value	POWER_LEVEL_REG[LDO_L OW_TRIM] = 0x1		-50		mV
V _{O_TRIM_2}	Trim step, delta from 1.1 V nominal value	POWER_LEVEL_REG[LDO_L OW_TRIM] = 0x2		-25		mV
Vo_trim_3	Trim step, delta from 1.1 V nominal value	POWER_LEVEL_REG[LDO_L OW_TRIM] = 0x3		0		mV
Vo_trim_4	Trim step, delta from 1.1 V nominal value	POWER_LEVEL_REG[LDO_L OW_TRIM] = 0x4		25		mV
Vo_trim_5	Trim step, delta from 1.1 V nominal value	POWER_LEVEL_REG[LDO_L OW_TRIM] = 0x5		50		mV
V _{O_TRIM_6}	Trim step, delta from 1.1 V nominal value	POWER_LEVEL_REG[LDO_L OW_TRIM] = 0x6		75		mV
Vo_trim_7	Trim step, delta from 1.1 V nominal value	POWER_LEVEL_REG[LDO_L OW_TRIM] = 0x7		100		mV
IQ_ACTIVE	Quiescent current	No load		12		μΑ
I _{Q_SLEEP}	Quiescent current	No load		40		nA
Ron_sw_High	On resistance of the high Ohmic switch between V _{BAT_HIGH} and V _{BAT_LOW} rail	Buck mode, V _{BAT_HIGH} = 1.62 V, V _{BAT_LOW} = 1.1 V		250		Ω
Ron_sw_low	On resistance of the low Ohmic switch between V _{BAT_HIGH} and V _{BAT_LOW} rail	Buck mode, V _{BAT_HIGH} = 1.62 V, V _{BAT_LOW} = 1.1 V		10		Ω
Ron_sw_low_ BOOST	On resistance of the low Ohmic switch between V _{BAT_HIGH} and V _{BAT_LOW} rail	Boost mode, V _{BAT_LOW} = 1.1 V		10		Ω

4.11 Digital I/O Characteristics

Table 17: Digital Pad - Recommended operating conditions

Parameter	Description	Conditions	Min	Тур	Max	Unit
I _{L_HIDRV}	Driving current - high mode			3.5		mA
I _{L_LODRV}	Driving current - low mode			0.35		mA
VIH	HIGH level input voltage	V _{DD} = 0.9 V	0.7*VD D			V
V _{IL}	LOW level input voltage	V _{DD} = 0.9 V			0.3*VD D	V

Table 18: Digital Pad - DC characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
I _{IH}	HIGH level input current	V _I =V _{BAT_HIGH} = 3.0 V	-10		10	μΑ
I _{IL}	LOW level input current	V _I =V _{SS} = 0 V	-10		10	μA
I _{IH_PD}	HIGH level input current	V _I =V _{BAT_HIGH} = 3.0 V	60		180	μA
I _{IL_PU}	LOW level input current	V _I =V _{SS} = 0 V, V _{BAT_HIGH} = 3.0 V	-180		-60	μΑ
Vон	HIGH level output voltage	I _O = 3.5 mA, V _{BAT_HIGH} = 1.7 V	0.8*VB AT_HI GH			V
V _{OL}	LOW level output voltage	I _O = 3.5 mA, V _{BAT_HIGH} = 1.7 V			0.2*VB AT_HI GH	V
Voh_Lowdrv	HIGH level output voltage	I _O = 0.3 mA, V _{BAT_HIGH} = 1.7 V	0.8*VB AT_HI GH			V
Vol_lowdrv	LOW level output voltage	I _O = 0.3 mA, V _{BAT_HIGH} = 1.7 V			0.2*VB AT_HI GH	V
C _{IN}	Input capacitance			0.75		рF

Table 19: Digital Pad with LPF - DC characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
Cin	Input capacitance	Note 1 Note 2		3.85		pF

Note 1 Digital pad characteristics are equal to the standard GPIO pads unless overruled or added in this table.

Table 20: Digital Pad with LPF - Recommended operating conditions

Parameter	Description	Conditions	Min	Тур	Max	Unit
I _{L_HIDRV}	Driving current - high mode			3.5		mA
I _{L_LODRV}	Driving current - low mode			0.35		mA

4.12 Power On Reset

Table 21: POR VBAT_LOW - DC characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
V _{TH_H}	POR VBAT_LOW reset release voltage			1.05	1.1	>
V _{TH_L}	POR VBAT_LOW reset activation voltage		0.95	1		٧

Note 2 P0_3 and P0_4 are type B pads with selectable filter via GP_DATA_REG[P03_P04_FILT_DIS], C_{IN} is equal to a Type A pad both with filter enabled or disabled.

Table 22: POR VBAT_HIGH - DC characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
V _{ТН_} н	POR VBAT_HIGH reset release voltage			1.75	1.8	V
V _{TH_L}	POR VBAT_HIGH reset activation voltage		1.62	1.66		V

4.13 **GP ADC**

Table 23: GP ADC - Recommended operating conditions

Parameter	Description	Conditions	Min	Тур	Max	Unit
N _{BIT_ADC}	Number of bits (resolution)			10		bit

Table 24: GP ADC - DC characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
E _G	ADC gain error without software correction (single-ended)	Trimmed bandgap	-3		3	%
Eg_cor	ADC gain error after software correction (single-ended)	Trimmed bandgap & Gain Error + Offset correction applied	-1		1	%
E _{OFS}	ADC offset error without software correction (single-ended)	Trimmed bandgap, no chopping	-40		40	LSB
Eofs_cor	ADC offset error after software correction (single-ended)	Trimmed bandgap, chopping enabled & Gain Error + Offset correction applied	-4		4	LSB
E _{G_DIF}	ADC gain error without software correction (differential)	Trimmed bandgap	-3		3	%
E _{G_DIF_COR}	ADC gain error after software correction (differential)	Trimmed bandgap & Gain Error + Offset correction applied	-1		1	%
E _{OFS_DIF}	ADC offset error without software correction (differential)	Trimmed bandgap, no chopping	-20		20	LSB
Eofs_dif_cor	ADC offset error after software correction (differential)	Trimmed bandgap, chopping enabled & Gain Error + Offset correction applied	-4		4	LSB
E _{G_ATTNX}	ADC gain error after software correction (including attenuator)	Trimmed bandgap & GPADC Gain Error + Offset correction applied	-4		4	%
E _{OFS_ATTNX}	ADC offset error after software correction (including attenuator)	Trimmed bandgap, chopping enabled & GPADC Gain Error + Offset correction applied	-16		16	LSB
E _{G_OFFSH}	ADC gain error after software correction (including offset shifter)	Trimmed bandgap & Offset Shifter Gain Error + Offset correction applied	-1		1	%

Parameter	Description	Conditions	Min	Тур	Max	Unit
Eofs_offsh	ADC offset error after software correction (including offset shifter)	Trimmed bandgap, chopping enabled & Offset Shifter Gain Error + Offset correction applied	-4		4	LSB
INL	Integral non-linearity	Note 1	-2		2	LSB
DNL	Differential non-linearity		-2		2	LSB
ENOB	Effective Number Of Bits	no averaging, no chopping, Single-Ended: V _{IN,PP} = 800mV		9		bit
ENOB _{AVG128}	Effective Number Of Bits	128x averaging, Single- Ended: V _{IN,PP} = 800mV		11		bit

Note 1 INL is the deviation of a code from a straight line passing through the actual endpoints of the transfer curve.

Table 25: GP ADC - Electrical performance

Parameter	Description	Conditions	Min	Тур	Max	Unit
tconv_adc	Conversion time of the ADC			125	500	ns

4.14 Temperature Sensor

Table 26: Temperature Sensor - DC characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
T _{SENSE_RANG} E	Temperature sensor range		-40		105	°C
Tsense_acc_o TP_csp	Applies to the CSP package. Absolute accuracy of temperature sensor using calibration value from OTP (single point calibration at 25 °C). Formula: Tx = 25 °C + (ADCx - ADCotp_CAL_25c) / (TCsense * 64) (64 is used to correct 16b to 10b ADC values)	Tambient = 25°C, Vbat_low = 1.1 V	-4		4	°C
Tsense_acc_o tp_qfn	Applies to the QFN package. Absolute accuracy of temperature sensor using calibration value from OTP (single point calibration at 25 °C). Formula: Tx = 25 °C + (ADCx - ADCotp_CAL_25c) / (TCsense * 64) (64 is used to correct 16b to 10b ADC values)	Tambient = 25°C, Vbat_low = 1.1 V		±4		°C
TC _{SENSE}	Temperature coefficient of the internal temperature sensor	Reading via GP_ADC (10-bit result)	1.15	1.45	1.75	LSB/°C

4.15 Radio

Table 27: BLE 1Mb/s specifications - Recommended operating conditions

Parameter	Description	Conditions	Min	Тур	Max	Unit
foper	Operating frequency		2400		2483.5	MHz
Nch	Number of channels			40		1
fсн	Channel frequency	K = 0 to 39		2402+K *2		MHz

Table 28: BLE 1Mb/s specifications - AC characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
Psens_clean	Sensitivity level	Dirty Transmitter disabled; DC-DC converter disabled; PER = 30.8 % Note 1		-94		dBm
Psens_epkt	Sensitivity level	Extended packet size (255 octets) Note 1		-90.5		dBm
Psens	Sensitivity level	Normal Operating Conditions; DC-DC converter disabled; PER = 30.8 % Note 1		-93		dBm
Psens_eoc	Sensitivity level	Extreme Operating Conditions; DC-DC converter enabled; PER = 30.8% ; -40 °C \leq T _A \leq +85 °C Note 1			-90	dBm
Psens_epkt_c	Sensitivity level	Dirty Transmitter disabled; DC-DC converter disabled; Extended packet size (255 octets) Note 1		-91.5		dBm
P _{I_MAX}	Maximum input power level	DC-DC converter disabled; PER = 30.8 % Note 1	0			dBm
PINT_IMD	Intermodulation distortion interferer power level	worst-case interferer level @ f_1 , f_2 with $2*f_1 - f_2 = f_0$, $ f_1 - f_2 = n$ MHz and $n = 3, 4, 5$; $p_{WANTED} = -64$ dBm @ f_0 ; PER = 30.8 % Note 1	-35	-20.5		dBm
CIR ₀	Carrier to interferer ratio	n = 0; interferer @ f ₁ = f ₀ + n*1 MHz; Note 1		7.5	21	dB

Parameter	Description	Conditions	Min	Тур	Max	Unit
CIR ₁	Carrier to interferer ratio	$n = \pm 1$; interferer @ $f_1 = f_0 + n*1$ MHz; Note 1		-1.5	15	dB
CIR _{P2}	Carrier to interferer ratio	n = +2 (image frequency); interferer @ $f_1 = f_0 + n*1$ MHz; Note 1		-27	-9	dB
CIR _{M2}	Carrier to interferer ratio	n = -2; interferer @ f ₁ = f ₀ + n*1 MHz; Note 1		-31	-17	dB
CIR _{P3}	Carrier to interferer ratio	n = +3 (image frequency + 1 MHz); interferer @ $f_1 = f_0 + n*1$ MHz; Note 1		-37.5	-15	dB
CIR _{M3}	Carrier to interferer ratio	n = -3; interferer @ $f_1 = f_0 +$ n*1 MHz; Note 1		-43	-27	dB
CIR ₄	Carrier to interferer ratio	n ≥ 4 (any other BLE channel); interferer @ f ₁ = f ₀ + n*1 MHz; Note 1		-41.5	-27	dB
P _{BL_I}	Blocker power level	30 MHz \leq f _{BL} \leq 2000 MHz; P _{WANTED} = -67 dBm Note 1	-17	5		dBm
P _{BL_II}	Blocker power level Note 2	2003 MHz ≤ f _{BL} ≤ 2399 MHz; P _{WANTED} = -67 dBm Note 1	-17	0		dBm
P _{BL_III}	Blocker power level	2484 MHz \leq f _{BL} \leq 2997 MHz; P _{WANTED} = -67 dBm Note 1	-17	0		dBm
P _{BL_IV}	Blocker power level	3000 MHz ≤ f _{BL} ≤ 12.75 GHz; P _{WANTED} = -67 dBm Note 1	-17	5		dBm
Lacc_rssi	Level accuracy	Tolerance at 5 % to 95 % confidence interval of P _{RF} : when RXRSSI[7:0] = <i>X</i> , 50 < <i>X</i> < 175; burst mode, 1500 packets		0	3	dB
Lres_rssi	Level resolution	Gradient of monotonous range for RXRSSI[7:0] = <i>X</i> , 50 < <i>X</i> < 175; burst mode, 1500 packets		0.5		dB/LSB
ACP _{2M}	Adjacent channel power level	f _{OFS} = 2 MHz; Note 1		-53		dBm

Parameter	Description	Conditions	Min	Тур	Max	Unit
ACP _{2M_EOC}	Adjacent channel power level	Extreme Operating Conditions; $f_{OFS} = 2$ MHz; -40 °C $\leq T_A \leq +85$ °C Note 1		-53	-47	dBm
ACP _{3M}	Adjacent channel power level	f _{OFS} ≥ 3 MHz; Note 1		-57		dBm
АСРзм_ЕОС	Adjacent channel power level	Extreme Operating Conditions; foFs ≥ 3 MHz; -40 °C ≤ TA ≤ +85 °C Note 1		-57	-47	dBm
P _{O_12}	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 12		2.5		dBm
Po_11	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 11		1.5		dBm
Po_10	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 10		1		dBm
P _{O_09}	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 9		0		dBm
Po_08	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 8		-1		dBm
P _{O_07}	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 7		-2		dBm
P _{O_06}	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 6		-3.5		dBm
P _{O_05}	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 5		-5		dBm
P _{O_04}	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 4		-7		dBm
P _{O_03}	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 3		-10		dBm
P _{O_02}	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 2		-13.5		dBm
Po_01	Output power level	RF_ATTR_REG[PA_POWER _SETTING]= 1		-19.5		dBm

Note 1 Measured according to Bluetooth® Low Energy Test Specification RF-PHY.TS/5.1.0

Table 29: BLE 1Mb/s specifications - Timing characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
thold	Hold time of radio Ido's	Temperature from -40 °C to 55 °C	500			ms

Note 2 Frequencies close to the ISM band can show slightly worse performance

Parameter	Description	Conditions	Min	Тур	Max	Unit
thold_eoc	Hold time of the radio Ido's	Temperature from -40 °C to 85 °C	10			ms

Table 30: BLE 1Mb/s specifications - DC characteristics

Parameter	Description	Conditions	Min	Тур	Max	Unit
I _{BAT_RF_RX}	Current at V _{BAT_LOW} = 1.1 V	Radio receiver and synthesizer active; T _A = 25 °C		4.3		mA
IBAT_RF_TX_12	Current at V _{BAT_LOW} = 1.1 V	Radio transmitter and synthesizer active; power setting = 12; P _{OUT} = 2.5 dBm; T _A = 25 °C		7.9		mA
I _{BAT_RF_TX_9}	Current at V _{BAT_LOW} = 1.1 V	Radio transmitter and synthesizer active; power setting = 9; P _{OUT} = 0 dBm; T _A = 25 °C		6.9		mA
lbat_rf_tx_6	Current at V _{BAT_LOW} = 1.1 V	Radio transmitter and synthesizer active; power setting = 6; P _{OUT} = -3.5 dBm; T _A = 25 °C		5.7		mA

5. System Overview

5.1 Internal Blocks

The DA14531 contains the following blocks:

Arm® Cortex-M0+ CPU with Wake-up Interrupt Controller (WIC). This processor provides 0.9 dMIPS/MHz and is used for assisting the Bluetooth® LE protocol implementation, for providing processing power for calculations or data fetches required by applications, and for housekeeping, including controlling the power scheme of the system.

BLE core. This is the baseband hardware accelerator for the Bluetooth® LE protocol.

ROM. This 144-kB ROM contains the Bluetooth® LE protocol stack and the boot code sequence.

OTP. This 32-kB OTP memory array is used to store application code and Bluetooth[®] LE profiles. It also contains the system configuration and calibration data.

System SRAM (SysRAM). This 48-kB SysRAM is primarily used to mirror the program code from the OTP when the system wakes/powers up. It also serves as a Data RAM for intermediate variables and various data that the protocol requires. It can be used as an extra memory space for the Bluetooth[®] LE TX and RX data structures (Exchange RAM). The SysRAM cells can not only be retained during sleep modes but also be completely switched off during active mode if not needed.

UART and UART2. The serial interface of the UART implements hardware flow control while UART2 does not. Both UARTs feature FIFOs with depths of 16 bytes each.

SPI. This is the serial peripheral interface (SPI) with master/slave capability and it has separate FIFOs for RX and TX of two 16-bit words each.

I2C. This Master/Slave I2C interface is used for sensors and/or host Micro-Controllers Units (MCUs) communication. It comprises a 32-place 9-bit deep FIFO.

General Purpose (GP) ADC. This 10-bit analog-to-digital converter (ADC) has four external input channels (GPIOs) and internal channels for reading die temperature, the battery voltage, and other internal analog nodes.

Radio Transceiver. This block implements the RF part of the Bluetooth LE protocol.

Clock Generator. This block is responsible for clocking the system. It contains two XTAL oscillators, one running at 32 MHz (XTAL32M) and used for the active mode of the system and the other running at 32.768 kHz (XTAL32K) and used for the sleep modes of the system. There are also three RC oscillators available: a 32 MHz oscillator (RC32M) with low precision (> 500 ppm), a 32 kHz oscillator (RC32K) with low precision (> 500 ppm), and a ~15 kHz oscillator (RCX) with high precision (< 500 ppm). The RCX oscillator can be used as a sleep clock to replace the XTAL32K oscillator to further improve the power dissipation of the system while reducing the bill of materials. The RC32M oscillator is used to provide a clock to mirror the OTP code into the SysRAM while the XTAL32M oscillator is settling directly after power/wake up. This clock is also used to run the Booter at power-up. An external digital clock can be used as a sleep clock to replace the XTAL32K or the RCX oscillator.

Timers. This block contains three timers:

- A 16-bit general purpose timer (Timer0) with two pulse width modulation (PWM) signals (PWM1 is inverted to PWM0)
- An 11-bit timer (Timer1) with two capture channels
- A 14-bit timer (Timer2) that controls six PWM signals that all have the same frequency, but each has a configurable duty cycle

Real Time Clock (RTC). This hardware controller supports the complete time of day clock: 12/24 hours, minutes, seconds, milliseconds, and hundredths of a millisecond. It includes a configurable alarm function and can be programmed to generate an interrupt on any event, like a rollover of the month, day, hour, minute, second, or hundredths of a millisecond.

Wake-Up Timer. This timer captures external events and it can be used on any of the GPIO ports as a wake-up trigger based on a programmable number of external events.

Quadrature Decoder. This block decodes the pulse trains from a rotary encoder to provide the step and the direction of a movement of an external device. Three axes (X, Y, and Z) are supported. The block also supports an edge counting mode which enables counting positive or negative edges on the selected GPIOs.

Keyboard Controller. This circuit enables the reading and debouncing of a programmable number of GPIOs and generates an interrupt upon a configurable action.

AHB/APB Bus. This block implements the AMBA Lite version of the AHB and APB specifications.

Power Management. This sophisticated power management circuit is equipped with a Buck/Boost DC-DC converter and several low-dropout regulators (LDOs) that can be turned on/off via software.

A more detailed description of each component of the DA14531 is presented in the following sections.

5.2 Power Management Unit

5.2.1 Introduction

The DA14531 has an integrated power management unit (PMU) which comprises a VDD_Clamp, a POR circuitry, a DCDC converter, and various LDOs. The system diagram of the integrated PMU is shown in Figure 7.

Features

- Boost, Buck, and DCDC bypass configurations
- Single inductance DCDC converter configured for Boost or Buck configuration
- Programmable DCDC converter outputs
- Active and sleep mode LDOs
- Low BOM and use of small external components

5.2.2 Architecture

The PMU integrates two externally decoupled power rails: V_{BAT_HIGH} and V_{BAT_LOW}, and one internal V_{DD} power rail. There are three main power configurations: Buck, Boost, and Bypass. The integrated PMU configures itself automatically to the appropriate mode depending on how the battery is initially connected to the application.

- VBAT_HIGH: voltage range of 1.8 V 3.6 V. This power rail is used for the blocks which require a higher supply voltage. The OTP and the GPIOs are connected to this power rail. VBAT_HIGH is protected by the POR circuit POR HIGH, which generates a POR when the voltage drops below the threshold voltage.
- V_{BAT_LOW}: the main system supply and most internal blocks are powered from this rail. Its functional range is from 1.1 V to 3.3 V. When used in Boost configuration, its default voltage range is from 1.1 V to 1.65 V, and within this range, the DCDC converter can provide a supply at V_{BAT_HIGH} in the range of 1.8 V to 3.0 V (see Section 5.2.3.2). V_{BAT_LOW} is protected with the POR circuit POR_LOW which generates an HW reset when the voltage drops below the threshold voltage.
- The internal V_{DD} power rail supplies the digital power domains (see Section 5.2.2.1 for the details) The VDD Clamp and RC32k blocks are supplied by the highest of V_{BAT HIGH} and V_{BAT LOW}.

In the Buck configuration (Figure 7), the battery is connected to V_{BAT_HIGH} . The voltage on V_{BAT_LOW} is generated from V_{BAT_HIGH} . In Boost configuration (Figure 8), the battery is connected to V_{BAT_LOW} . The voltage on V_{BAT_HIGH} is generated from V_{BAT_LOW} . The different power modes of the system are explained in Section 5.2.2.2.




Figure 7. Power management unit: buck configuration




Figure 8. Power management unit: boost configuration

In bypass configuration (Figure 9), the DCDC is bypassed, and the battery is connected to both V_{BAT_LOW} and V_{BAT_HIGH} . In this mode, an external inductor is omitted resulting to lower BOM. GPIOs supply follows the battery voltage in this configuration. The minimum cold boot voltage is 1.8 V. After cold boot and providing that no OTP or GPIO (at a specific voltage level) is needed, POR HIGH can be disabled and then V_{BAT_BYPASS} can go down to 1.1 V.

VBAT_LOW is limited to a max of 3.3 V, the battery/supply voltage shall not exceed that level in the bypass configuration. If an application requires supply levels up to 3.6 V and the choice is made to omit the DCDC converter (reduced BOM at the cost of higher current consumption), it is recommended to use the "Buck Configuration" and enable LDO_LOW to power the VBAT_LOW rail (instead of via DCDC converter).




Figure 9. Power management unit: bypass configuration

5.2.2.1 Digital Power Domains

The DA14531 supports a number of digital power domains that can be turned on and off by software (Figure 10). Some of the blocks contain registers that can retain their values even if the digital power domain where they reside is powered off. RAM cells can retain their contents independently from the digital power domains state.




Figure 10. Digital power domains

The list of blocks residing in each one of the digital power domains is presented in Table 31.

Table 31: Power Domains Description

Domain name	Description
PD_AON	Always powered domain. It contains a Clock-less Wake Up controller and the pad-ring.
PD_SLP	Sleep power domain. It comprises the Arm/WIC, the Bluetooth® LE Timer, the PMU/Clock Generation, the Clocked Wakeup Controller, the Quadrature Decoder, and various registers required for the Wake-Up sequence.

Domain name	Description
PD_SYS	System Power Domain. It comprises the AHB bus, the OTP cell and controllers, the ROM, the System RAM, the Watchdog, the SW Timer, and the GPIO port multiplexing.
PD_TIM	Timer Power Domain. It comprises the RTC and the Timer1. These two blocks can be active during sleep modes.
PD_RAD	Radio Power Domain. It comprises the Bluetooth® LE Core and the digital PHY of the Radio.

5.2.2.2 Power Modes

There are five different power modes in the DA14531:

- Active mode: System is active and operates at full speed
- **Sleep mode:** No power gating has been programmed. The Cortex CPU is idle, waiting for an interrupt. PD_SYS is on. PD_TIM and PD_RAD depend on the programmed enabled value
- Extended Sleep mode: PD_AON, PD_SLP, and conditionally PD_TIM are active. RAM is expected to be retained for
 - Keeping a Bluetooth® LE connection alive (stack variables or Bluetooth® LE data)
 - Potentially keep the application code and it can be omitted if the OTP is instructed to automatically get mirrored into RAM upon every wake-up
- Deep Sleep mode: Shipping clocked mode with all domains disabled. RAM may or may not be retained. RTC operation is programmable
- Hibernation mode: Shipping clock-less mode with all domains disabled. RAM may or may not be retained.
 No clock is running

A summary of the power modes, the digital power domains, as well as the clocks and wake-up capabilities are explained in Table 32.

Table 32: Power Modes, Digital Power Domains, Clocks, and Wake-up Triggers

Power mode	Digital power domains	LDOs, DCDC converter, and VDD level	Clock availability	RAM	Wake up from
Active or Sleep (WFI)	PD_AON = ON PD_SLP = ON PD_SYS = ON PD_TIM = OPTIONAL PD_RAD = OPT	VDD = 0.9 V DCDC = ON (Buck or Boost) LDO_LOW = OFF LDO_CORE = ON, Active (0.9 V) VDD_Clamp = OFF LDO_RADIO = Programmable	All	SysRAM1 = ON (Application) SysRAM2 = optionally retained SysRAM3 = ON (Stack Data)	
Extended Sleep (with or without OTP)	PD_AON = ON PD_SLP = ON PD_SYS = OFF PD_TIM = OPTIONAL PD_RAD = OFF	VDD = 0.75 V DCDC = OFF LDO_LOW = ON, in Buck mode. LDO_CORE = ON, in retain mode (0.75 V) VDD_Clamp = OFF LDO_RADIO = OFF	RCX or XTAL32K	SysRAMx = optionally retained (typically only SysRAM1 is retained)	 from any GPIOs RTC alarm Timer1 Bluetooth® LE sleep timer
Deep Sleep	PD_AON = ON PD_SLP = ON PD_SYS = OFF PD_TIM = OPTIONAL PD_RAD = OFF	VDD = 0.75 V DCDC = OFF LDO_LOW = ON, in Buck mode LDO_CORE = ON, in retain mode (0.75 V) VDD_Clamp = OFF LDO_RADIO = OFF	RCX or XTAL32K	SysRAMx = optionally retained (Typically OFF)	from any GPIOsRTC alarmTimer1
Hibernation	PD_AON = ON PD_SLP = OFF PD_SYS = OFF PD_TIM = OFF PD_RAD = OFF	VDD = ~0.75 V DCDC = OFF LDO_LOW = OFF LDO_CORE = OFF VDD_Clamp = ~0.75 V LDO_RADIO = OFF	No Clocks	SysRAMx = optionally retained	Wake up from P0_1, P0_2, P0_3, P0_4, P0_5

Table 33 shows the typical rail voltages and their drivers present during various PMU modes.

Table 33: Power Rails Drivers and Voltages

Configurations	Mode	V _{BAT_HIGH}	V _{BAT_LOW}	V _{DD}
	Active	Battery (3.6 V – 1.8 V)	DCDC out (1.1 V)	LDO_CORE (0.9 V)
Buck	Deep or Extended Sleep		LDO_LOW (1.1 V)	LDO_CORE in retain mode (0.75 V)

Configurations	Mode	V _{BAT_HIGH}	V _{BAT_LOW}	V _{DD}
	Hibernation		0 V (none)	VDD_Clamp (~0.75 V)
	Active	DCDC out (3 V - 1.8 V)		LDO_CORE 0.9 V
Boost	Deep or Extended Sleep	Parasitic diodes in DCDC or clamp (V _{BAT_LOW}) (Note 1)	Battery (1.5V – 1.1 V)	LDO_CORE in retain mode (0.75 V)
	Hibernation	Parasitic diodes in DCDC or clamp (VBAT_LOW) (Note 1)		VDD_Clamp (~0.75 V)
	Active			LDO_CORE (0.9 V)
Bypass	Deep or Extended Sleep	Battery (3.3 V – 1.1 V)	Battery (3.3 V – 1.1 V)	LDO_CORE in retain mode (0.75 V)
	Hibernation			VDD_Clamp (~0.75 V)

Note 1 Parasitic diodes in DCDC and LDO_LOW circuits prevent V_{BAT_HIGH} from dropping to 0 V. V_{BAT_HIGH} can also be programmed to be clamped to V_{BAT_LOW}.

5.2.2.3 DD Level in Hibernation

While in Hibernation, the Always On domain (PD_AON) is supplied by a clamp. Since the reference is not enabled, the actual voltage supplied by the clamp is depending on the load and temperature. To ensure proper operation of the PD_AON across the application operating temperature range and load, it is recommended to configure the voltage level of the VDD_Clamp using POWER_AON_CTRL_REG[LDO_RET_TRIM] according to Table 34.

Table 34: VDD_Clamp Recommended Settings over Temperature and Load

Temperature range	0 kB retained RAM	48 kB retained RAM
-40 °C to +40 °C	0xE	0xD
-40 °C to +60 °C	0xD	0xC
-40 °C to +85 °C	0xB	0xA

5.2.2.4 Retainable Registers

When the system enters one of the sleep modes, some registers need to retain their values even though their power domain might be shut down. These special retainable registers and their power domains are described in Table 35.

Table 35: Retainable Registers

Power domains	Retainable registers			
	OTPC_MODE_REG			
	OTPC_TIM1_REG			
	OTPC_TIM2_REG			
PD_SYS	OTPC_AHBADR_REG			
	OTPC_CELADR_REG			
	OTPC_NWORDS_REG			
	DEBUG_REG			
	BLE_CNTL2_REG			
	RF_ADCI_DC_OFFSET_REG			
PD_RAD	RF_ADCQ_DC_OFFSET_REG			
	RF_DC_OFFSET_RESULT_REG			

Power domains	Retainable registers
	RF_DC_OFFSET_FULL_RES_REG
	RF_DC_OFFSET_MPAR_RES0/1/2/3_REG

5.2.3 Programming

5.2.3.1 Buck Configuration

In Buck configuration (Figure 7), the voltage on V_{BAT_LOW} and V_{DD} is generated from V_{BAT_HIGH} in the following ways:

Hibernation Mode

In hibernation mode, the V_{BAT LOW} rail is not powered and the digital core V_{DD} is supplied by the VDD clamp.

The VDD clamp is supplied automatically by selecting the highest of V_{BAT_HIGH} and V_{BAT_LOW}. Since in Buck configuration the V_{BAT_HIGH} rail is always the highest supply on the chip, it is safe to disable this automatic supply selection. Setting POWER_AON_CTRL_REG[CMP_VCONT_SLP_DISABLE] = 0x1 forces the clamp to use V_{BAT_HIGH} as supply and reduces the hibernation current by approximately 40 nA.

Extended Sleep and Deep Sleep Modes

In the extended sleep mode or deep sleep mode, the V_{BAT_LOW} rail is supplied from LDO_LOW which is in a retention low power mode. The digital core V_{DD} is powered from LDO_CORE, retention mode. To configure this mode the following settings must be applied:

- POWER CTRL REG[LDO LOW CTRL REG] = 0x3
- POWER_CTRL_REG[LDO_CORE_RET_ENABLE] = 0x1

Active and Sleep Modes

The V_{BAT_LOW} rail is powered by LDO_LOW or by the DCDC converter. To enable the DCDC converter the following settings must be applied:

- POWER LEVEL REG[DCDC LEVEL] = 0x0
- DCDC CTRL REG[DCDC ENABLE] = 0x1

The DCDC converter is automatically disabled and re-enabled when PD_SYS is powered down and powered up again. Therefore, to use the DCDC converter to power V_{BAT_LOW} rail, LDO_LOW has to be turned off again after the system wakes up by setting the register:

• POWER CTRL REG[LDO LOW CTRL REG] = 0x1

Register settings when the V_{BAT LOW} rail is powered by LDO LOW:

POWER_CTRL_REG[LDO_LOW_CTRL_REG] = 0x3

5.2.3.2 Boost Configuration

NOTE

In the Boost configuration, several diodes between V_{BAT_HIGH} and V_{BAT_LOW} can prevent V_{BAT_HIGH} from dropping more than a few hundred millivolts below V_{BAT_LOW} .

During boot, external circuits connected to the V_{BAT_HIGH} rail must be disabled. To guarantee a smooth start-up, a user must keep the total load of VBAT_HIGH to less than 50 μ A.

In Boost configuration (Figure 8), voltages on V_{BAT_HIGH} and V_{DD} are generated from V_{BAT_LOW} as explained below:

Hibernation Mode

Hibernation mode is generally a state in which the device stays longer. It is recommended to force the VBAT_HL_RES switch on to reduce the power consumption from the comparator. When the VBAT_HL_RES switch is on, VBAT_HIGH is connected to VBAT_LOW. The register setting is:

• POWER AON CTRL REG[VBAT HL CONNECT RES CTRL] = 0x1

In the hibernation mode of the Boost configuration, the digital core V_{DD} is powered from VDD Clamp.

Extended Sleep and Deep Sleep Modes

The digital core V_{DD} is supplied by LDO_CORE switched to retention mode. The reference voltage for this LDO is generated by periodically enabling and sampling the bandgap (see Section 5.3.3 for details). V_{BAT_HIGH} rail can be supplied by the following options:

- Diodes controlled: VBAT_HIGH is connected to VBAT_LOW via diodes. This option is useful for short sleep durations, typically below a second. When no significant load is present on VBAT_HIGH, it will not drop below VBAT_LOW during the sleep interval. This is the reset setting.
- Software controlled: VBAT_HIGH and VBAT_LOW are connected via VBAT_HL_RES. In typical use cases, this
 setting is energy efficient for sleep durations longer than one second. This mode requires the following
 register settings:
 - o POWER CTRL REG[LDO CORE RET ENABLE] = 0x1
 - o POWER_AON_CTRL_REG[VBAT_HL_CONNECT_RES_CTRL] = 0x2
- Hardware controlled: For short sleep durations, typically under one second, in combination with increased load conditions that can discharge V_{BAT_HIGH} to the level of V_{BAT_LOW} during the sleep interval, it is recommended to use the HW-controlled V_{BAT_HIGH} connection, in which the two rails are connected as soon as V_{BAT_HIGH} drops to the same level of V_{BAT_LOW} (*/- 50 mV). This mode requires the following register settings:
 - o POWER_AON_CTRL_REG[LDO_CORE_RET_ENABLE] = 0x1
 - POWER_CTRL_REG[CMP_VBAT_HIGH_OK_ENABLE] = 0x1
 - o POWER AON CTRL REGIVBAT HL CONNECT RES CTRL] = 0x3

Active and Sleep Modes

In these modes, the V_{BAT_HIGH} rail is normally powered by the DCDC converter at 1.8 V. This level can be changed to 2.5 V or 3.0 V by configuring POWER_LEVEL_REG[DCDC_LEVEL].

Since the Boost converter is only needed to generate 1.8 V allowing for accessing to the OTP cell and supply the GPIOs, it is possible to disable it when access to the OTP is not required and no GPIOs are being driven. In this mode the VBAT_HL_SW should be activated to clamp VBAT_HIGH at VBAT_LOW, allowing some load on VBAT_HIGH and GPIO operation at a reduced speed and voltage. Note that this mode rapidly discharges VBAT_HIGH from the boosted voltage down to the VBAT_LOW level. Also, the POR_HIGH block has to be masked or disabled to avoid resets:

- if it is masked, the POR HIGH status remains available, but it will not generate a reset
- if it is disabled, the status becomes unavailable as well

The following settings are required to enter this mode of operation:

- POWER_CTRL_REG[POR_VBAT_HIGH_DISABLE] = 0x1 (Disable) or
- POWER AON CTRL REGIPOR VBAT HIGH RST MASK] = 0x1 (Mask)
- DCDC_CTRL_REG[DCDC_ENABLE] = 0x0
- POWER_CTRL_REG[VBAT_HL_CONNECT] = 0x1

5.2.3.3 Bypass Configuration

In the bypass configuration, the V_{BAT_HIGH} and V_{BAT_LOW} rails are shorted on the PCB. This configuration is detected by the chip as a boost configuration, but since the boost converter is not able to generate a voltage on V_{BAT_HIGH} , the initial voltage has to be above 1.75 V to allow the OTP to be read and mirrored.

The software can disable the DCDC converter and LDO_LOW to reduce quiescent current and avoid unnecessary switching of the DCDC converter. The following register settings are required to accomplish this:

- DCDC_CTRL_REG[DCDC_ENABLE] = 0x0
- POWER_CTRL_REG[LDO_LOW_CTRL_REG] = 0x1

If the voltage drops below 1.75 V, POR_HIGH must be masked to prevent unnecessary resets. The OTP reads cannot be performed after this point. Masking POR_HIGH is done by the following setting:

■ POWER AON CTRL REG[POR VBAT HIGH RST MASK] = 0x1

When POR_HIGH is masked, its status remains available, but it will not generate a reset. POR_HIGH can be also disabled by the following setting:

■ POWER CTRL REG[POR VBAT HIGH DISABLE] = 0x1

When POR HIGH is disabled, its status becomes unavailable.

5.3 Hardware FSM (Power-Up, Wake-Up, and Go-to-Sleep)

The hardware Finite State Machine (FSM) responsible for the power-up, wake-up, and go-to-sleep processes of the system is presented in Figure 11.




Figure 11. Power-up/Wake-up/Sleep FSM diagram

The details of the power-up, wake-up, and sleep sequences of the FSM for the different modes are described in the following sections.

In Boost configuration the DCDC is enabled by the Booter during power up. After waking up, if the DCDC was left enabled, it will be started by the HW FSM. In Buck configuration, upon a wake-up, the DCDC is enabled by programming DCDC_CTRL_REG[DCDC_ENABLE]. If DCDC_ENABLE is kept asserted before the system goes to sleep, the DCDC will be started by the HW FSM upon waking up. If DCDC_ENABLE is cleared before the system goes to sleep, the DCDC can only be started by SW asserting this bit after a wake-up. When the system is allowed to go to sleep, the HW FSM is activated and the DCDC controller is automatically turned off.

5.3.1 Power-Up/Wake-Up in Buck Configuration

At the beginning of a power-up (cold boot), the PMU detects whether the system is in a Buck or a Boost configuration, and this decision is retained from that point on. The power-up (cold boot) sequence of the Buck configuration is shown in Figure 12. When the system is at the start of the Buck configuration path, then V_{BAT_HIGH} rail has a stable supply already and "boost_mode = 0" (which means buck is identified) has been set.

To start the system, it is required that the V_{BAT_LOW} rail is also brought up to an acceptable level, which is done by HW, enabling the resistive switch VBAT_HL_RES and monitoring POR_LOW. The rising voltage of the V_{BAT_LOW}

rail will eventually trigger POR_LOW to "ok" after that, the bandgap will be enabled. The HW FSM runs at 32 kHz from the RC32K oscillator at this time, and it will dynamically change to 512 kHz in one clock cycle after the switch is enabled. The HW FSM will continue working at 512 kHz. When the reference voltage from the bandgap is stable, LDO_LOW is enabled. After a stable 1.1 V is generated, LDO_CORE is enabled to generate a stable V_{DD} of 0.9 V. After this, the main system clock, RC32MHz, is enabled. All conditions are now in place to release the system reset so that the Booter can start running. An indicative time needed to power up the system in Buck configuration up until the application SW starts running, is around 2.5 ms. The time required to charge V_{BAT_LOW} and V_{BAT_HIGH} depends on the external capacitor values on these rails.




Figure 12. Power-up (Buck)

In hibernation, the resistive switch VBAT_HL_RES can be closed to pre-charge V_{BAT_LOW} to the level of V_{BAT_HIGH} by programming POWER_AON_CTRL_REG[VBAT_HL_CONNECT_RES_CTRL]. Therefore, during the wake-up sequence from the hibernation mode, step "Charge V_{BAT_LOW} " can be omitted (Figure 13) via POWER_AON_CTRL_REG[CHARGE_VBAT_DISABLE]. All other steps are the same as in the power-up cold-boot sequence. The total time needed to wake up the system from hibernation up until booter software starts running is around 185 μ s.




Figure 13. Wake-up from Hibernation (Buck)

The wake-up sequence from the clocked, extended sleep, or deep sleep mode using an external GPIO toggle is shown in Figure 14. The difference between the power-up and wake-up sequence in the Buck configuration is that the V_{BAT_LOW} rail is already charged via the switch VBAT_HL_RES in the wake-up sequence as shown in Figure 11. Therefore, when the system wakes up from a deep sleep or an extended deep sleep, the bandgap will be enabled within one 32 kHz clock cycle after the wake-up signal is triggered. After the bandgap is enabled, LDO_LOW and LDO_CORE will be enabled one after the other. The total time which is needed to wake up the system until the software starts running is around 800 µs. If RAM has been retained, running software means application, if not then the Booter will be started.




Figure 14. Wake-Up (Buck)

A GPIO trigger will have to go through the wake-up controller first, which requires 7 RCX clock cycles before it is allowed to trigger the PMU and have the state machine running. Even after all power rails are done, switching the system clock from RCX into RC32M (so software starts running) takes 3.5 RCX clock cycles (indicated in state = RUNNING:SWITCH) in Figure 14.

If the system wakes up from an internal timer running at the RCX clock, then the WokenUp signal will be asserted 6 RCX clock cycles after the timer generates the interrupt (for example, ~400 μs).

5.3.2 Power-Up/Wake-Up in Boost Configuration

At the beginning of a power-up (cold boot), the PMU detects whether the system is in a Buck or a Boost configuration, and this decision is retained in the system. The power-up (cold boot) sequence of the Boost configuration is shown in Figure 15. When the system is at the start of the Boost configuration path, then VBAT_LOW has a stable supply already and "boost_mode = 1" (which means boost is identified) has been set.

Because the supply on the V_{BAT_LOW} rail is already on an acceptable level, the bandgap will be enabled in the first step and LDO_CORE in the second step. After this, the resistive switch VBAT_HL_RES is closed to bring V_{BAT_HIGH} up to the same level as V_{BAT_LOW} . This is needed for the DCDC converter to start since its drivers run on the V_{BAT_HIGH} rail. When the V_{BAT_HIGH} rail is stable, the system reset can be released for the Booter to start running. The DCDC will be enabled during the first actions in the Booter (Section 5.5). An indicative time that is needed to power up the system in Boost configuration up until software starts running is around 1.2 ms. The time required to charge V_{BAT_HIGH} depends on the external capacitor values on this rail.




Figure 15. Power-up (Boost)

In hibernation, the resistive switch VBAT_HL_RES can be closed to pre-charge V_{BAT_HIGH} to the level of V_{BAT_LOW} by programming POWER_AON_CTRL_REG[VBAT_HL_CONNECT_RES_CTRL]. Therefore, during the wake-up sequence from the hibernation mode, step "Charge V_{BAT_HIGH} " can be omitted (Figure 16) via POWER_AON_CTRL_REG[CHARGE_VBAT_DISABLE]. All other steps are the same as in the power-up cold-boot sequence. The total time needed to wake up the system from hibernation up until booter software starts running is around 180 μ s.




Figure 16. Wake-up from Hibernation (Boost)

In the wake-up sequence from deep or extended sleep using a GPIO toggle, the step Charge V_{BAT_HIGH} lasts minimum 4 clock cycles (Figure 17). This time is sufficient to quickly re-charge V_{BAT_HIGH} under the condition that the leakage current and the sleep interval are sufficiently low and the V_{BAT_HIGH} voltage does not drop below V_{BAT_LOW} . The state Charge V_{BAT_HIGH} can be omitted by using the resistive paths. The total time which is needed to power up the system until the software starts running is around 865 μ s. If RAM has been retained, running software means application, if not then the Booter will be started.




Figure 17. Wake-up from Extended/Deep Sleep (Boost)

A GPIO trigger will have to go through the wake-up controller first, which requires 7 RCX clock cycles before it can trigger the PMU and have the state machine running. Even after all power rails are done, switching the system clock from RCX into RC32M (so software starts running) takes 3.5 RCX clock cycles (indicated in state = RUNNING:SWITCH) in Figure 17.

If the system wakes up from an internal timer running at the RCX clock, then the WokenUp signal will be asserted 6 RCX clock cycles after the timer generates the interrupt (for example, ~400 μs).

5.3.3 Go-to-Sleep and Refresh Bandgap

The system can enter a sleep state, either sleep Buck or sleep Boost, depending on the status of the boost_mode bit. The sleep state disables the power-consuming blocks and triggers the "hold mode" for the bandgap referenced voltages. After a certain amount of time (sleep refresh counter), these "hold" voltages need to be refreshed. The lower loop of the FSM in Figure 11 enables the bandgap, refreshes the voltages, checks for BOD events via the POR circuits and if ok, resets the refresh timer and goes back to sleep. This is an autonomous cycle led by hardware until the system is woken up by a wake-up event. The refresh timer can be configured by setting the PMU_SLEEP_REG [BG_REFRESH_INTERVAL] bit field (1 LSB = 64 × 32 kHz clock cycles). The go-to-sleep and the bandgap refresh sequence are shown in Figure 18.




Figure 18. Go-to-Sleep and bandgap refresh

5.4 OTP Memory Layout

The OTP memory has to be programmed according to a specific layout, which structures information to be easily accessible from the BootROM code as well as the actual application. An overview of the layout scheme is presented in Figure 19.




Figure 19. OTP layout scheme

The OTP memory is a matrix of 8Kx32-bit words. The contents are described below:

- Interrupt Vectors: they are the vectors of the interrupt service routines and always reside at the address 0x0. This is part of the application (customer) code. The size of this vector list is 32 words
- **Customer Code:** it contains the applications and the profiles that a customer has developed. The size is known and fixed before the mass production and the programming of the OTP
- Configuration Script (Section 5.4.2): it is used to program registers with values that are defined during production testing, to store a trim value for the application software, and to define the UART time-out timer during booting. It is executed by the Booter to prepare and initialize the system before the CPU starts running the application code. Available size is 60 words
- **OTP Header:** it contains various information about the configuration of the system and the Bluetooth[®] LEspecific data. The size of the header is 16 words

5.4.1 OTP Header

The OTP header breakdown is presented in Table 36.

Table 36: OTP Header

	Words		Programmed during	
Address	Address Words (32-bit) Description		Chip test	Product manufacturing
7F87FC0	1	Application Programmed Flag #1 0x1234A5A5 = Application is in OTP		Yes
7F87FC4	1	Application Programmed Flag #2 0xA5A51234 = Application is in OTP		Yes

	Words		Prograi	Programmed during	
Address	(32-bit)	Description	Chip test	Product manufacturing	
7F87FC8	1	Boot-specific configuration: Bits[7:0]: OxAA = Boot from SPI port at a specific location OxFF = Normal sequence Bits[15:8] = Wake up Command opcode Bits[23:16] = SPI_DIV Bits[31:24]: Ox00 = Two-wire UART (P0_0/P0_1) Ox01 = One-wire UART (P0_3) Ox02 = One-wire UART (P0_5) Default (all other values) = Two-wire UART (P0_0/P0_1)		Yes	
7F87FCC	1	Boot-specific port mapping: Bits[7:4] = SPI_CLK, Port number Bits[3:0] = SPI_CLK, Pin number Bits[15:12] = SPI_EN, Port number Bits[11:8] = SPI_EN, Pin number Bits[23:20] = SPI_DO, Port number Bits[19:16] = SPI_DO, Pin number Bits[31:28] = SPI_DI, Port number Bits[27:24] = SPI_DI, Pin number		Yes	
Device and Package Flag Bits[7:0]: 0xFF = WLCSP with 0x66 = WLCSP with 0xAA = FCGQFN24 Bits[15:8]: 0xFF = 531 0x30 = 530 Others = Reserved		 0xFF = WLCSP with P0_5 0x66 = WLCSP without P0_5 0xAA = FCGQFN24 Bits[15:8]: 0xFF = 531 0x30 = 530 	Yes		
7F87FD4	2	Bluetooth Device Address (64-bit word). It is handled as a string of bytes.		Yes	
7F87FDC	1	OTP DMA length (number of 32-bit words).		Yes	
7F87FE0	1	Position: Bits[7:0] = X coord Bits[15:8] = Y coord Bits[23:16] = Wafer # Bits[31:24] = LOT #	Yes		
Tester: Bits[7:0] = Tester_Site 7F87FE4 1 Bits[15:8] = Tester_ID (LSB) Bits[23:16] = Tester_ID (MSB) Bits[31:24] = Reserved		Yes			

	Words	Description	Programmed during	
Address	(32-bit)		Chip test	Product manufacturing
7F87FE8	1	TimeStamp: Bits[7:0] = TS_Byte0 Bits[15:8] = TS_Byte1 Bits[23:16] = TS_Byte2 Bits[31:24] =TS_Byte3	Yes	
7F87FEC	5	Reserved for Future Needs		

The Device and Package Flag reflects what the current device (DA14531) is and which package is used. Default (unprogrammed) values are 0xFFFFFFFF.

Boot-specific mapping value is used to define a specific configuration for the SPI interface when used for booting from an external device (either an MCU or a FLASH). Byte0 is the flag to instruct the BootROM to use the specific SPI pin mapping and skip the rest of the serial peripheral interfaces. The BootROM takes care of waking up an external flash when the flash memory is in a deep power-down state.

Byte1 is used for the Wake-up Command opcode that the flash memory responds to. If Byte0 is left unprogrammed, BootROM will send the "0xAB" opcode by default. Furthermore, the BootROM can wake up the external flash by toggling the CS pin.

Two more flags indicate whether the application code has indeed been programmed (burned) into the OTP. Both flags are read by the BootROM software designating that the system is in the Normal mode and not in the Development mode (Section 5.5).

5.4.2 Configuration Script

The Configuration Script (CS) is a table of 32-bit entries and is 60 words deep, so in total, the CS can utilize 240 bytes of space.

The CS is used to program registers with values that are defined during production testing, to store a trim value for the application software, and to define the UART time-out timer during booting. It is executed by the Booter to prepare and initialize the system before the CPU starts running the application code.

The format of the commands in the CS is presented in Table 37.

Table 37: CS Commands and Description

#	Command type	Description	
1	Start Command	One 32-bit word containing 0xA5A5A5A5 to signal a valid CS is in place.	
2	Register Configuration	 One 32-bit word containing an address of an existing register One 32-bit word containing the data value of the register 	
3	SDK Value	One 32-bit word which is equal to 0x9000YYXX indicating that the next word is a value stored during production testing. More specifically: 9: it indicates that the following word(s) are not to be stored to registers but will be used by the SDK SW YY: it indicates that YY amount of words follow XX: it is an increasing value and can be used for indexing by the SW application. If YY > 1, XX will not be increased for the words that belong to the same value One or more 32-bit words can represent one value.	
4	SWD mode	One 32-bit word which is equal to 0x70000000. It prevents the JTAG from being enabled at the end of the Booter and the Booter will not enter the endless while (1) loop. Instead, it will continue to rescan all peripherals in the development mode path.	
5	UART STX timeout value	One 32-bit word which is equal to $0x8XXXXXXXX$. The XXXXXXX is used to program the selected STX timeout in multiples of 100 μ s. So, for example, $0x800000028$ is $40 \times 100 \ \mu$ S = 4 ms.	
6	SPI Clock value	0xA0000000 This value overwrites the default 2-MHz clock speed of the SPI boot path and sets it to 32 MHz.	

The Booter stops processing the CS once it encounters an empty OTP value (0xFFFFFFF). This way, no more processing time is spent checking the rest and it is possible to add new entries later, for example, to patch/update previous entries.

An example describing the format of the configuration script is presented in Table 38.

Table 38: CS Example

Words	Even words	Odd words	Description
0-1	0xA5A5A5A5	0x80000028	Start command of the CS Script, followed by STX timeout value of 4 ms (40 × 100 μ s)
2-3	<address></address>	<value></value>	Booter automatically writes the <value> to the <address></address></value>
4-5	0x90000301	<value></value>	Three calibration values stored during production testing. SDK should know what this is for.
6-7	<value></value>	<value></value>	
8-9	<address></address>	<value></value>	Booter automatically write the <value> to the <address></address></value>
10-11	<address></address>	<value></value>	Booter automatically write the <value> to <address></address></value>
12-13	0x90000402	<value1></value1>	Four calibration values stored during production testing. SDK should know what this is for.
14-15	<value2></value2>	<value3></value3>	Calibration value stored during production testing. SDK should know what this is for.
16-17	<value4></value4>	0x70000000	Disable SWD
18-19	0xFFFFFFF	(don't care)	Booter stops running the CS after an empty entry, so anything after this is "don't care".

5.5 BootROM Sequence

The booting process of DA14531 is presented in Figure 20. The Booter is always executed when a POR or an HW Reset occurs, or the RESET_ON_WAKEUP feature is configured.

The booter will start executing with the RC32M clock, to speed up its execution. Then the Booter checks whether the system is in the Boost configuration or not. The configuration (Buck or Boost) has been already decided by the HW and should be readable by SW at the ANA_STATUS_REG[BOOST_SELECTED] bit field. To access the OTP, V_{BAT_HIGH} needs to be set at \geq 1.8 V. In the Boost configuration the DCDC is enabled to boost V_{BAT_HIGH} at 1.8 V and BOOST_VBAT_OK = 1 confirms that the voltage at the DCDC is stable. After the OTP is operational, the Booter initializes the UART baud rate at 115.2 kHz, and the CS (Section 5.4.2) is enabled to be executed.

After the CS has been executed, the Booter has to decide whether the device is in Development or Normal mode by reading the two words indicated as application flags in the OTP. The OTP image is copied into RAM starting at address 0x0 by the Booter.

In Development mode, the "Boot from Specific" flag will be evaluated. If the flag is programmed, new pin locations for booting from an external SPI slave to make DA14531 an SPI Master will be set. The "Boot from Specific" flag addresses mostly the QFN package allowing for booting from a different pin configuration than the default one so that the system can boot from an external FLASH using the development mode. The details of the configuration are presented in Section 5.4.1. If this path is entered, the system will always try to boot from UART so that the SPI Flash can be updated if needed. Any of the three UART configurations specified in Table 39 can be selected by writing bits [31:24] at the "Boot specific config" field in the OTP header. If booting from SPI Flash fails, the Booter will jump back to the normal scan sequence of the peripheral devices.

If the "Boot from Specific" flag is not programmed, the system should continue with scanning the different serial interfaces to identify whether a device is connected to it. After OTP is disabled, six steps as described in Table 39 are performed. Before using the UART, the XTAL32M clock needs to be enabled. All the boot steps are protected by a timeout.




Figure 20. BootROM sequence

The one-wire UART boot capability is introduced due to the limited amount of GPIOs in the WLCSP package. The one-wire UART boot leaves four GPIOs for the application and one GPIO for programming/debugging. Since the booting from the UART protocol is a half-duplex, a single GPIO is used in DA14531 for the external UART. The protocol is the same as for a two-wire UART booting except that the Booter SW needs to change the pin direction before sending or receiving information.

Table 39: Booting Sequence Steps

	Step 1: Boot from External SPI Master	Step 2: Boot from 1-wire UART (First Option)	Step 3: Boot from 1-wire UART (Second Option)	Step 4: Boot from 2-wire UART	Step 5: Boot from External SPI Slave	Step 6: Boot from I2C
P0_0/RS T	MISO			Тх	MOSI	
P0_1	MOSI			Rx	scs	
P0_2						
P0_3	SCS		RxTx		MISO	SDA
P0_4	SCK				SCK	SCL
P0_5		RxTx (Default)				
P0_6						
P0_7						
P0_8						
P0_9						
P0_10						
P0_11						

If no bootable devices are found on any of the serial interfaces, the Booter can do two things, depending on what is stored in the CS. If the "Debugger disable" (0x70000000) command is stored there, the Booter will start scanning for peripherals again. Otherwise, it enters the endless loop with the debugger (JTAG) being enabled. The debugger can be connected to P0_5 in the WLCSP17 package or P0_10 in the FCGQFN24 package.

After the BootROM sequence has been completed, the default system clock is RC32M, regardless of which boot path has been chosen and all GPIOs are set back to their default reset values.

6. Reset

6.1 Introduction

The DA14531 comprises a reset (RST) pad which is active high. It contains an RC filter with a resistor of 465 k Ω and a capacitor of 3.5 pF to suppress spikes. It also contains a 25 k Ω pull-down resistor. This pad should be driven externally by a field-effect transistor (FET) or a single button connected to VBAT. The typical latency of the RST pad is in the range of 2 μ s.

Features

- RC spike filter on RST to suppress external spikes (465 kΩ, 3.5 pF)
- Three different reset lines (software, hardware, and POR)
- Latching the cause of a reset operation (RESET_STAT_REG)
- Configurable POR circuitry




Figure 21. Reset block diagram

6.2 Architecture

6.2.1 POR, Hardware, and Software Reset

There are three main reset signals in the DA14531:

- The Power-On Reset (POR): it is optionally triggered by a GPIO set as the POR source with a selectable polarity and/or the RST pad (P0_0) after a programmable time delay
- The hardware reset: it is optionally triggered by the RST pad (P0_0) when it becomes active for a short period of time (less than the programmable delay for POR)
- The SW reset: it is triggered by writing the SYS CTRL REG[SW RESET] bit

The POR signal is generated:

- Internally and releases the system's flip flops as soon as the VDD, VBAT_HIGH, and VBAT_LOW voltages crossed
 the specified thresholds
- Externally by a POR source (RST pad multiplexed on a GPIO or P0 0 configured as RST pin)

The HW reset can also be automatically activated when the system wakes up from the Extended or Deep Sleep mode by programming the bit PMU_CTRL_REG[RESET_ON_WAKEUP]. The POR and the HW reset basically run the cold start-up sequence and the BootROM code is executed.

The software reset is the logical OR of a signal from the Cortex CPU (triggered by writing SCB->AIRCR = 0x05FA0004) and the SYS_CTRL_REG[SW_RESET] bit. It is mainly used to reboot the system after the base address has been remapped.

The block diagram of the reset block is depicted in Figure 21.

Certain registers are reset by POR only, or by POR and the hardware reset signal but not by the software reset. These registers are listed in Table 40.

Table 40: Reset Signals and Registers

Reset by POR Only	Reset by POR or hardware reset	Reset by POR, hardware reset, or software reset
BANDGAP_REG	BLE_CNTL2_REG	The rest of the Register File
POR_PIN_REG	CLK_AMBA_REG[OTP_ENABLE]	
POR_TIMER_REG	CLK_FREQ_TRIM_REG	
HWR_CTRL_REG	CLK_RADIO_REG	
RESET_STAT_REG[PORESET_STAT]	CLK_CTRL_REG	
PAD_LATCH_REG	PMU_CTRL_REG	
POWER_AON_CTARL_REG	SYS_CTRL_REG	
GP_DATA_REG	TRIM_CTRL_REG	
TEST_VDD_REG	RAM_PWR_CTRL_REG	
	CLK_RC32K_REG	
	CLK_XTAL32K_REG	
	CLK_RC32M_REG	
	CLK_RCX_REG	
	XTALRDY_CTRL_REG	
	XTAL32M_CTRL0_REG	
	PMU_SLEEP_REG	
	POWER_CTRL_REG	
	POWER_LEVEL_REG	
	DCDC_CTRL_REG	
	RAM_LPMX_REG	
	HIBERN_CTRL_REG	
	CLK_RTCDIV_REG	
	RTC_CONTROL_REG	
	RTC_KEEP_RTC_REG	
	OTPC_*_REG	
	QDEC_*_REG	
	All RF calibration registers	

6.2.2 POR Functionality

The POR functionality is available by two sources:

- RST Pad: the RST pad is always capable of producing a POR
- GPIO Pin: a GPIO can be selected by the user application to act as a POR source

The time needed for a GPIO pin selected for the POR to be active is stored in the POR_TIMER_REG. The register field POR_TIME is a 7-bit field that holds the time factor by which the total time for POR is calculated. The maximum value of the field is 0x7F. The total time for POR is calculated by the following formula:

Total time =
$$POR_TIME \times 4096 \times RC32k$$
 clock period (1)

where RC32k clock period = 31.25 µs at 25°C.

The maximum time for which a POR can be performed is ~16.2 seconds at 25°C.

The RC32k clock frequency depends on temperature, so based on the temperature span of -10°C to 50°C, the clock frequency range is calculated to be 25 kHz to 39 kHz. Then,

 $T_{PORcold} = 13 s$

 $T_{PORhot} = 20.8 s$

6.2.2.1 POR Timer Clock

The POR timer is clocked by the RC32k clock. If an SW application disables the RC32k, the HW takes care of enabling the RC32k clock when a POR source (the RST pad or a selected GPIO pin) is asserted. It should be noted that if the POR is generated from the RST pad, the RC32k operates with the reset (default) trimming value. If a GPIO pin is used as the POR source, the RC32k clock is trimmed. The timing difference between both cases is expected to be minor.

6.2.2.2 RST Pad

The RST pad will produce an HW reset if the pin active time is less than the programmed value in the POR_TIMER_REG register or a POR if the pin active time is greater than or equal to that value. Reset pad is always Active High.

6.2.2.3 POR from GPIO

When a GPIO is used as a POR source, the selected pin retains its capability to act as GPIO. The POR_PIN_REG[PIN_SELECT] field holds the required GPIO pin number. If the value of the PIN_SELECT field equals 0, the POR triggered by GPIO functionality is disabled. The polarity of the pin can be configured by the POR_PIN_REG [POR_POLARITY] bit, where 0 means Active Low and 1 means Active High.

6.2.3 POR Timing Diagram

The operation of the POR triggered by both the RST pad and a selected GPIO pin is depicted in Figure 22.




Figure 22. POR timing diagram

6.2.4 POR Considerations

When a POR source (the RST pad or a selected GPIO pin) is asserted, the POR timer starts to count. When the POR source is released before the timer has expired, the POR timer will be reset to 0. If a POR source is asserted while there is already an asserted POR, and the first POR is released after the second POR is asserted, and the total time of the two asserted sources is larger than or equal to the POR_TIME, POR will occur.

It should also be noted that the POR timer triggered by the RST pad can only expire once. After the POR timer has expired, the RST pad has to be released so the timer can be reloaded. There is no such limitation when a GPIO is used as the POR source.

The POR_PIN_REG[PIN_SELECT] field cannot survive any reset (POR, HW reset, or SW reset), therefore, users must take special care on setting up the GPIO POR source right after a reset. This also applies to the POR_TIMER_REG[POR_TIME] field after a POR.

Be aware that, if a GPIO is used as a POR source, the dynamic current of the system increases due to the dynamic current consumed by the RC32k oscillator. This increase is calculated to be from 100 nA to 120 nA and it is also present during the sleep time period. POR from the RST pad does not add this dynamic current consumption.

6.3 Programming

To configure the functionality of triggering a POR by a GPIO pin, follow the steps below:

- 1. Select a GPIO to be set as the POR source by programming POR_PIN_REG[POR_PIN_SELECT].
- 2. Set up the input polarity of the GPIO that causes POR by programming POR PIN REG[POR PIN POLARITY].
- 3. Configure the time for the POR to happen by programming POR_TIMER_REG[POR_TIME]. The default time is around three seconds.

NOTE

To set up the time when the RST pad produces a POR, just set the POR TIMER REG register.

7. Arm® Cortex-M0+

7.1 Introduction

The Arm® Cortex-M0+ processor is a 32-bit Reduced Instruction Set Computing (RISC) processor with a von Neumann architecture (single bus interface). It uses an instruction set called Thumb, which was first supported in the ARM7TDMI processor, but it also uses several newer instructions from the Armv6 architecture and a few instructions from the Thumb-2 technology. Thumb-2 technology extends the previous Thumb instruction set to allow all operations to be carried out in one CPU state. The instruction set in Thumb-2 includes both 16-bit and 32-bit instructions; most instructions generated by the C compiler use the 16-bit instructions, and the 32-bit instructions are used when the 16-bit version cannot carry out the required operations. This results in high code density and avoids the overhead of switching between two instruction sets.

In total, the Cortex-M0+ processor supports only 56 base instructions, although some instructions can have more than one form. Although the instruction set is small, the Cortex-M0+ processor is highly capable because the Thumb instruction set is highly optimized.

Academically, the Cortex-M0+ processor is classified as load-store architecture, as it has separate instructions for reading and writing to memory, and instructions for arithmetic or logical operations that use registers. It has a two-stage pipeline (fetch+predecode and decode+execute) as opposed to its predecessor (Cortex-M0) that has a three-stage pipeline (fetch, decode, and execute).

A simplified block diagram of the Cortex-M0+ is shown in Figure 23.




Figure 23. Arm® Cortex-M0+ block diagram

Features

- Thumb instruction set: highly efficient, of high code density, and able to execute all Thumb and Thumb-2 instructions
- High performance: up to 0.9 DMIPS/MHz (Dhrystone 2.1) with fast multiplier
- Built-in Nested Vectored Interrupt Controller (NVIC): this makes interrupt configuration and coding of exception handlers easy. When an interrupt request is taken, the corresponding interrupt handler is executed automatically without the need to determine the exception vector in software
- Interrupts can have four different programmable priority levels and the NVIC automatically handles nested interrupts
- The design is configured to respond to exceptions (for example, interrupts) as soon as possible (minimum 15 clock cycles)
- Non maskable interrupt (NMI) input for safety critical systems

- Easy to use and C friendly. There are only two modes, Thread mode and Handler mode. The whole application, including exception handlers, can be written in C without any assemblers
- Built-in System Tick timer for OS support. A 24-bit timer with a dedicated exception type is included in the architecture, which the OS can use as a tick timer or as a general timer in other applications without an OS
- SuperVisor Call (SVC) instruction with a dedicated SVC exception and Pendable SuperVisor service (PendSV) to support various operations in an embedded OS
- Architecturally defined sleep modes and instructions to enter sleep. The sleep features allow power
 consumption to be reduced dramatically. Defining sleep modes as an architectural feature makes porting of
 software easier because the sleep modes are entered by specific instructions rather than implementation
 defined control registers
- Fault handling exception to catch various sources of errors in the system
- Support for 21 interrupts
- Little endian memory support
- Wake-up Interrupt Controller (WIC) to allow the processor to be powered down during sleep, while interrupt sources are still allowed to wake up the system
- Halt mode debug allows the processor activity to stop completely so that register values can be accessed and modified. No overhead in code size and stack memory size
- CoreSight technology allows memories and peripherals to be accessed from the debugger without halting the processor
- Supports Serial Wire Debug (SWD) connections. The SWD protocol can handle the same debug features as the JTAG, but it only requires two wires and is already supported by a number of debug solutions from various tools vendors
- Four (4) hardware breakpoints and two (2) watch points
- Breakpoint instruction support for an unlimited number of software breakpoints
- Programmer's model similar to the ARM7TDMI processor. Most existing Thumb code for the ARM7TDMI processor can be reused. This also makes it easy for ARM7TDMI users, as there is no need to learn a new instruction set.

7.2 Architecture

7.2.1 Interrupts

This section lists all 21 interrupt lines, except the NMI interrupt, and describes their sources and functionality. The overview of the interrupts is illustrated in Table 41.

Table 41: Interrupt List

IRQ number (Inherent Priority)	IRQ name	Description
0	BLE_WAKEUP_LP_IRQn	Wake up the system from Low Power (Extended Sleep) interrupt from BLE.
1	BLE_GEN_IRQn	Bluetooth® LE Interrupt. Sources: ■ BLE_FINETGTIM_IRQn: Fine Target Timer interrupt generated when Fine Target timer expires. The timer resolution is 625 µs base time reference ■ BLE_GROSSTGTIM_IRQn: Gross Target Timer interrupt generated when Gross Target timer expired. The timer resolution is 16 times 625 µs base time reference ■ BLE_CSCNT_IRQn: 625 µs base time reference interrupt, available in active modes ■ BLE_SLP_IRQn: End of Sleep mode interrupt ■ BLE_ERROR_IRQn: Error interrupt, generated when undesired behavior or bad programming occurs in the BLE Core

IRQ number (Inherent Priority)	IRQ name	Description
		 BLE_RX_IRQn: Receipt interrupt at the end of each received packets
		 BLE_EVENT_IRQn: End of Advertising/Scanning/Connection events interrupt
		 BLE_CRYPT_IRQn: Encryption/Decryption interrupt, generated when AES and/or CCM processing is finished
		 BLE_SW_IRQn: SW triggered interrupt, generated on SW request
2	UART_IRQn	UART interrupt.
3	UART2_IRQn	UART2 interrupt.
4	I2C_IRQn	I2C interrupt.
5	SPI_IRQn	SPI interrupt.
6	ADC_IRQn	Analog-Digital Converter interrupt.
7	KEYBRD_IRQn	Keyboard interrupt.
8	BLE_RF_DIAG_IRQn	Baseband or Radio Diagnostics Interrupt. Triggered by internal events of the Radio or Baseband selected by the BLE_RF_DIAGIRQ_REG. For Debug purposes only.
9	RF_CAL_IRQn	RF Calibration Interrupt.
10	GPIO0_IRQn	GPIO interrupt through debounce.
11	GPIO1_IRQn	GPIO interrupt through debounce.
12	GPIO2_IRQn	GPIO interrupt through debounce.
13	GPIO3_IRQn	GPIO interrupt through debounce.
14	GPIO4_IRQn	GPIO interrupt through debounce.
15	SWTIM_IRQn	Timer0/2 interrupt.
16	WKUP_QUADEC_IRQn	Combines the Wake-up Capture Timer interrupt, the GPIO interrupt, and the QuadDecoder interrupt.
17	TIM1_IRQn	Timer1 interrupt.
18	RTC_IRQn	Real Time Clock interrupt.
19	DMA_IRQn	DMA interrupt.
20	XTAL32RDY_IRQn	XTAL32M settling ready interrupt.

Interrupt priorities are programmable by the Arm Cortex-M0+. The lower the priority number, the higher the priority level. The priority level is stored in a byte-wide register, which is set to 0x0 at reset. Interrupts with the same priority level follow a fixed priority order using the interrupt number listed in Table 41 (a lower interrupt number has a higher priority level).

To access the Cortex-M0+ NVIC registers, the Cortex Microcontroller Software Interface Standard (CMSIS) functions can be used. The input parameter IRQn of the CMSIS NVIC access functions is the IRQ number. This can be the IRQ number or (more conveniently) the corresponding IRQ name listed in Table 41. For example, the corresponding interrupt handler name in the vector table for IRQ#15 is SPI_Handler. For more information on the Arm Cortex-M0+ interrupts and the corresponding CMSIS functions, see *section 4.2 Nested Vectored Interrupt Controller* in the

Cortex-M0+ Devices Generic User Guide.

The Watchdog interrupt is connected to the NMI input of the processor.

7.2.2 System Timer (SysTick)

The Cortex-M0+ System Timer (SysTick) can be configured for using two different clocks. The SysTick Control & Status (STCSR) register specifies which clock should be used by the counter.

- STCSR[CLKSOURCE] = 0: use the (fixed) external reference clock STCLKEN of 1 MHz
- STCSR[CLKSOURCE] = 1: use the (HCLK_DIV dependent) processor clock SCLK (for example, 2, 4, 8, or 16 MHz)

The default SysTick Timer configuration uses the (fixed) external reference clock STCLKEN (STCSR[CLKSOURCE] = 0). When necessary, higher clock frequencies can be used with STCSR[CLKSOURCE] = 1, but the software should take the HCLK_DIV dependent core clock SCLK into account about the timing.

7.2.3 Wake-Up Interrupt Controller

The Wake-up Interrupt Controller (WIC) is a peripheral that can detect an interrupt and wake the processor from Extended Sleep mode. The WIC is enabled only when the SLEEPDEEP bit in the system control register is set to 1 (see *System Control Register* in the *Cortex-M0+ Technical Reference Manual*).

The WIC is not programmable and does not have any registers or user interface. It operates entirely from hardware signals. When the WIC is enabled and the processor enters Extended Sleep mode, the power management unit in the system can power down most of the Cortex-M0+ processor. This has the side effect of stopping the SysTick timer. When the WIC receives an interrupt, it takes a number of clock cycles to wake up the processor and restore its state before it can process the interrupt. This means the interrupt latency is increased in Extended Sleep mode.

7.3 Programming

For more information on the Arm Cortex-M0+, see the documents listed in Table 42.

Table 42: Arm Documents List

	Document title	Arm document number	
1	Cortex-M0+ Devices Generic User Guide	Arm DUI 0662B (available on the website)	
2	Cortex-M0+ Technical Reference Manual, r0p1	Arm DDI 0484C (available on the website)	
3	Armv6-M Architecture Reference Manual	Arm DDI 0419C (can be downloaded by registered customers)	

8. AMBA Bus

8.1 Introduction

The DA14531 is based on the AMBA 2.0 AHB and APB components. The AHB is an AMBA Lite version which requires a single master on the system, but there is arbitration between the Arm Cortex-M0+ CPU and the Direct Memory Access (DMA) engine. There are two APB bridges, one for APB16 and the other for APB32, implementing three different decoded slaves which are grouped according to the power domain structure of the chip.

The AMBA bus organization is presented in Figure 24.




Figure 24. AMBA Bus architecture and power domains

8.2 Architecture

Since the DA14531 consists of several different power domains that are digitally controlled and can be shut down completely, various slave resources, especially on the APB bus, are grouped together to reduce signal isolation requirements. On the AHB Lite bus, the CPU or the DMA can be the master, while OTP, Bluetooth[®] LE Core, Memory and ROM controllers are slaves.

The Always On power domain (PD_AON) contains only the clock-less wake-up controller and the start-up hardware FSM responsible for the activation of the power devices within the system.

The sleep power domain (PD_SLP) contains the clock tree, the Bluetooth® LE Timer, the Clocked Wake-up Controller, and the Quadrature Decoder. These blocks are supposed to trigger or to capture wake-up events while the system is in any of the clocked sleep modes.

The timers power domain (PD_TIM) contains special purpose timers that might or might not be crucial for an application: a full featured Real Time Clock (RTC) engine and Timer1. The registers of these blocks are 32-bit wide, hence they are connected to the APB32 bus.

The APB16 bus connects to the radio power domain (PD_RAD), which consists of the Radio control unit and the Bluetooth[®] LE controller, and to the peripheral blocks which are all part of the same power domain as the CPU (PD_SYS).

8.3 Programming

Since the AMBA Bus only acknowledges a single master at a time, a programmable arbitration is implemented to decide whether the Arm Cortex-M0+ or the DMA is the master. The priority can be configured in the GP_CONTROL_REG[CPU_DMA_BUS_PRIO] with the CPU having the highest priority by default.

9. Memory Map

Table 43: Memory Map

Address	Description	Power domain			
0x00000000	Boot/BLE ROM/OTP/RAM				
0x04000000	Remapped address space based on SYS_CTRL_REG[REMAP_ADR0].				
0x04000000	RESERVED				
0x07F00000					
0x07F00000	Boot/BLE ROM				
0x07F24000	Contains Boot ROM code and BLE protocol related code.				
0x07F24000	RESERVED				
0x07F40000					
0x07F40000	OTP-Regs	PD_SYS			
0x07F40100	Contains the control registers of the OTP Subsystem.				
0x07F40100	RESERVED				
0x07F80000					
0x07F80000	OTP				
0x07F88000	Contains the OTP cell actual memory space.	1			
0x07F88000	RESERVED				
0x07F C0000	Out to the PAM	1			
0x07FC0000	System RAM 49 kB. Contains application and data for the application stock and been				
0x07FCC000	48 kB. Contains application code, data for the application, stack, and heap. SysRAM1 (16 kB): 0x07FC0000 to 0x07FC3FFF				
	SysRAM2 (12 kB): 0x07FC4000 to 0x07FC6FFF				
	SysRAM3 (20 kB): 0x07FC7000 to 0x07FCBFFF				
0x07FD8000	RESERVED				
0x40000000					
0x40000000	AHB/BLE-Regs	PD_RAD			
0x40001000	Contains the control registers of the BLE Link Layer Processor.				
0x40001000	AHB/Radio	PD_RAD			
0x40004000					
0x40004000	RESERVED				
0x50000000					
0x50000000	APB16/PMU-CRG	PD_SLP			
0x50000100	Contains the control registers of the Power Management Unit and the Clock Generator.				
0x50000100	APB16/wake-up	PD_SLP			
0x50000200	Contains the registers of the clocked and clock-less wake-up controllers.				
0x50000200	APB16/Quadrature Decoder	PD_SLP			
0x50000300	Contains Logic that implements a step counter for X and Y axis from a rotary encoder.				
0x50000300	RESERVED				
0x50001000					
0x50001000	APB16/UART PD_SYS				
0x50001100	Contains the control registers of the UART.				
0x50001100	APB16/UART2	PD_SYS			

Address	Description	Power domain
0x50001200	Contains the control registers of the UART2.	
0x50001200	APB16/SPI	PD_SYS
0x50001300	Contains the control registers of the SPI interface.	
0x50001300	APB16/I2C	PD_SYS
0x50001400	Contains the control registers of the I2C interface.	
0x50001400	APB16/Kbrd	PD_SYS
0x50001500	Contains the registers of the Keyboard controller.	
0x50001500	APB16/ADC	PD_SYS
0x50001600	Contains the registers of the 4-channel ADC.	
0x50001600	APB16/AnaMisc	PD_SYS
0x50001700	Contains registers for various analog blocks.	
0x50001700	RESERVED	
0x50003000		
0x50003000	APB16/Ports	PD_SYS
0x50003100	Contains the mode and direction registers of the GPIOs.	
0x50003100	APB16/Watchdog	PD_SYS
0x50003200	Contains the control registers of the Watchdog timer.	
0x50003200	APB16/Version	PD_SYS
0x50003300	Contains the version/revision of the chip.	
0x50003300	APB16/Gen Purpose	PD_SYS
0x50003400	Contains general purpose control registers.	
0x50003400	APB16/Timer	PD_SYS
0x50003500	Contains the control registers of Timer0 and Timer2.	
0x50003500	APB16/RF Monitor	PD_SYS
0x50003600	Contains the control registers of the RFMON.	
0x50003600	APB16/DMA	PD_SYS
0x50003700	Contains the control registers of the DMA.	
0x50003700	RESERVED	
0x50004000		
0x50004000	APB32/Timer1	PD_TIM
0x50004100	Contains the control registers of Timer1.	
0x50004100	APB32/RTC	PD_TIM
0x50004200	Contains the control registers of the Real Time Clock.	
0x50004200	RESERVED	
0xE0000000		
0xE0000000	Internal Private Bus	PD_SYS
0xE0100000	Contains various registers of the Arm Cortex-M0+.	

10. Memory Controller

10.1 Introduction

The Memory Controller of DA14531 is responsible for the interface between the memory cells and the masters of the system that request access. It comprises two arbiters which use a fixed priority level scheme to allow parallelization between the three main masters of the RAM. The memory controller also provides the actual physical sequence of the RAM cells in a continuous memory space to enable the activation of the required amount of SysRAM only to save power.

The block diagram is presented in Figure 25.

Features

- Three different capacities for the RAM cells with retention capability (12 kB, 16 kB, and 20 kB)
- Arbitration among the AHB masters (CPU or DMAs), OTP, and the BLE core
- Transparently interfaces the AHB busses to memory signaling
- Fixed arbitration algorithm with time sharing




Figure 25. Memory controller block diagram

10.2 Architecture

The Memory Controller contains two Arbiters which connect to the following busses via a Mux-Demux:

- Bluetooth® LE Mem I/F: this is a memory interface directly from the Bluetooth® 5.1 Core to the RAM used as an exchange memory (TX/RX descriptors and others). This interface always operates at 16 MHz
- System Mem I/F: This is a memory interface directly from the OTP memory to the RAM used for copying data after power-up/wake-up

10.2.1 Arbitration

The arbitration is a mixture of the highest priority and a fair use policy. If more than one master request access to cells which reside under the same arbiter, time division is employed. This is to make sure none of the busses can stall the others for a long period. The OTP and Bluetooth[®] LE accesses are handled as very critical and therefore they have the highest priority.

11. Clock Generation

11.1 Clock Tree

The generation of the system's clocks is described in detail in Figure 26.




Figure 26. Clock tree diagram

Figure 26 shows the possible clock sources as well as all different divisions and multiplexing paths towards the generation of each block's clock. Furthermore, the required registers that have to be programmed are also shown in Figure 26.

Internal clock sources of DA14531 are the RC32M, RC32K/512K, and RCX oscillators. External clock sources of DA14531 are the 32 MHz crystal oscillator (the pins XTAL32Mp and XTAL32Mm), the 32.768 kHz crystal

oscillator (the pins XTAL32kp and XTAL32km mapped on P0_3 and P0_4, respectively), or an external digital clock (the pin P0_3).

There are two main clock lines which are of interest:

- Ip_clk: this is the low power clock used for the sleep modes and can only be either the RCX, the RC32K, the XTAL32K, or an externally supplied digital clock
- sys_clk: this is the system clock used for the AMBA clock (hclk), which runs the CPU, the memories, and the bus. This clock source can be one of the oscillators or an externally supplied digital clock

The clock names depicted in Figure 26 are explained in Table 44.

Table 44: Generated Clocks Description

Clock Name	Description		
wakeupct_clk	Clocked wake-up controller clock.		
apb_clk	AMBA APB interface clock.		
otp_clk	OTP controller clock.		
hclk	AMBA AHB interface clock.		
ble_hclk	AMBA AHB clock for the BLE core.		
wdog_clk	Watchdog clock.		
pmu_rc_clk	Clock for the PMU and analog start-up FSM.		
icp_clk_512_c (512KHz)	Clock for the Charge pump in the LDO_CORE.		
gen_por_timer	Clock for the POR_FORCE Timer.		
spi_clk	Clock for the SPI controller. This clock is further divided by 2, 4, 8, or 14 as defined by SPI_CTRL_REG[SPI_CLK].		
spi_fast_clk	Fast 32 MHz clock for the SPI controller.		
i2c_clk	Clock for the I2C controller. This clock is further divided to provide 100 kHz or 400 kHz as defined by I2C_CON_REG[I2C_SPEED].		
uart_clk	Clock for the UART.		
uart2_clk	Clock for the UART2.		
quad_clk	Clock for the quadrature decoders.		
rfcu_clk	Clock for the RF control unit of the Radio.		
tmr0_clk, tmr2_clk	Timer0/2 clocks.		
tmr1_clk	Timer1 clock.		
tmr0_on_clk	Timer0 ON counter clock.		
rtc_clk	Clock for Real Time Clock (RTC).		
gp_adc_clk	General Purpose ADC conversion clock.		
ble_crypt_clk	Clock for the Crypto block of the Bluetooth® LE core.		
ble_master1_clk	Internal clock for the Bluetooth® LE core.		
ble_master2_clk	Internal clock for the Bluetooth® LE core.		
arb_clk	Clock for the memory controller arbiter.		
ble_lp_clk	Bluetooth® LE core low power clock.		
pll	PLL clock.		

11.1.1 General Clock Constraints

There are certain constraints on various clocks regarding their frequency relations or the effectiveness. This section summarizes these rules:

- The minimum of the AMBA clock (hclk) should be 8 MHz when Bluetooth® LE is utilized. This is also the clock of the Cortex CPU and ensures the required MIPS for handling the Bluetooth® LE Protocol
- The AMBA clock (hclk) should always be greater or equal to the ble_*_clks. This is required for the proper operation of the Bluetooth[®] LE protocol. For example, hclk at 16 MHz and Bluetooth[®] LE clocks at 8 MHz is an acceptable combination but not the other way around

11.2 Crystal Oscillators

The Digital Controlled XTAL Oscillators (DXCO) are designed for low power consumption and high stability. There are two such crystal oscillators in the system, one at 32 MHz (XTAL32M) and the other at 32.768 kHz (XTAL32K). The XTAL32K has no trimming capabilities and is used as the clock of the Deep Sleep/Extended Sleep modes. The XTAL32M can be trimmed.

The principal schematic of the two oscillators is shown in Figure 27. No external components to the DA14531 are required other than the crystal itself. If the crystal has a case connection, it is advised to connect the case to ground.




Figure 27. Crystal oscillator circuits

11.2.1 Frequency Control (32 MHz Crystal)

The 8-bit register CLK_FREQ_TRIM_REG controls the trimming of the 32 MHz crystal oscillator. The frequency is trimmed by two on-chip variable capacitor banks. Both capacitor banks are controlled by the same register.

The capacitance of both variable capacitor banks varies from the minimum to the maximum value in 256 equal steps. With CLK_FREQ_TRIM_REG[XTAL32M_TRIM] = 0x00, the minimum capacitance and thus the maximum frequency are selected. With CLK_FREQ_TRIM_REG[XTAL32M_TRIM] = 0xFF, the maximum capacitance and thus the minimum frequency are selected.

The five least significant bits of CLK_FREQ_TRIM_REG register (XTAL32M_TRIM<4:0>) directly control five binary weighted capacitors (Figure 28). The three most significant bits of CLK_FREQ_TRIM_REG register (XTAL32M_TRIM<7:5>) are binary to the thermometer decoded. Each of the seven outputs of the decoder controls a capacitor, of which the value is 32 times the value of the smallest capacitor.




Figure 28. XTAL32MHz oscillator frequency trimming

11.2.2 Automated Trimming and Settling Notification

There is provision in the DA14531 for automating the actual trimming of the 32 MHz crystal oscillator. This is a special hardware block that realizes the XTAL trimming in a single step. Notification about the XTAL oscillator being settled after applying the trim value is also provided in form of an interrupt, namely, the XTAL32RDY_IRQn line. The automated mechanism for applying the trim value and signaling that the oscillator is settled is described in Figure 29.

The XTAL32RDY_IRQn is always triggered as soon as an internal counter reaches the value programmed at XTALRDY_CTRL_REG. This counter runs on the RC32M clock if the system is powering up, or on a selected low power clock if the system is waking up. The enabling of the XTAL32M is always done by HW. There are two sections until the interrupt notifies the software that the XTAL32M can be used:

- The start-up section, where the XTAL32M oscillator is slowly converging towards the initial frequency of the crystal. This section ends with the application of the trim value to achieve a <50 ppm, 32 MHz clock
- The settling section, where the XTAL32M oscillator settles to the preferred frequency after the application of the trim value which is done automatically by HW

There are two ways of deciding when the start-up section ends and when the trim values are supposed to be applied. This decision is controlled by TRIM CTRL REG[XTAL TRIM SELECT] bit field:

- Counter Mode: trim value stored in the CLK_FREQ_REG is applied as soon as an internal counter reaches
 the value XTAL COUNT N-1. This is the default mode
- Current Mode: trim value is applied as soon as the current drops

The different modes are illustrated in Figure 29.




Figure 29. Automated mechanism for XTAL32M trim and settling

In both modes mentioned above, trimming is done by HW. In the current mode, upon assertion of XTAL32M_TRIM_READY, the interrupt counter value is stored in a shadow register XTALRDY_STAT_REG to enable SW understanding when the start-up section is finished.

The settling section usually takes no more than five to 10 clock cycles. Using the explanation above, fine tuning and reducing the XTAL32M latency is feasible. One feature of the XTAL32_CLK_CNT is that it asserts an observable signal (SYS_STAT_REG[XTAL32_SETTLE_READY]) as soon as the counter reaches a pre-defined threshold programmed at TRIM_CTRL_REG[XTAL_SETTLE_N]. This allows the SW to have an indication of the status of the clock by adjusting the threshold accordingly.

11.3 RC Oscillators

There are three RC oscillators in the DA14531:

- One providing 32 MHz (RC32M)
- One providing 32 kHz and 512 kHz (RC32K/512K)
- One providing a frequency of 15 kHz (RCX)

The RC32M is powered by V_{BAT_LOW} which is available during Active or Sleep mode. The output clock is slower than 32 MHz if untrimmed and it is used to clock the CPU and the digital part of the chip during power-up or wake-up, while the XTAL32M oscillator is settling.

The simple RC oscillator (RC32K/512K) operates on VDD and provides 32 kHz or 512 kHz. The main usage of the RC32K/512K oscillator is for internal clocking during power-up or start-up. It clocks the HW FSM which brings up the power management system of the chip. In the power-up or start-up sequence, the clock dynamically changes from 32 kHz to 512 kHz to speed up the sequence. The enhanced RC oscillator (RCX) provides a stable 15 kHz frequency and operates on VBAT LOW which is available during Active or Sleep mode.

The RCX oscillator can be used to replace the 32.768 kHz crystal, since it has a precision of < 500 ppm, while its output frequency needs to be recalibrated over temperature.

Using the RCX requires the following registers to be set:

- Set GP_DATA_REG = 0x20 after the system wakes up
- RCX calibration (the calibration is optional, please see Section 11.3.1 for the RCX calibration)
- Go to sleep: set GP_DATA_REG = 0x40 after the sleep procedure is handled

The procedure is also implemented as a part of the SDK.

11.3.1 Frequency Calibration

The output frequency of the 32 kHz crystal oscillator and the three RC-oscillators can be measured relative to the 32/2 (16) MHz crystal oscillator using the on-chip reference counter.

The measurement procedure is as follows:

- 1. REF CNT VAL = N (the larger number N is, the more accurate and longer the calibration will be)
- 2. CLK_REF_SEL_REG = 0x0000 (RC32K) or CLK_REF_SEL_REG = 0x0001 (RC32M) or CLK_REF_SEL_REG = 0x0002 (XTAL32K) or CLK_REF_SEL_REG = 0x0003 (RCX)
- 3. Start the calibration: CLK_REF_SEL_REG[REF_CAL_START] = 1
- 4. Wait until CLK_REF_SEL_REG[REF_CAL_START] = 0
- 5. Read CLK REF VAL H REG and CLK REF VAL L REG = M (32-bit values)
- 6. Frequency = $(N/M) \times 32/2 \text{ MHz}$

If the RCX is used as a sleep clock, the frequency calibration should be implemented on each active time of a connection interval to guarantee a correct operation.

12. OTP Controller

12.1 Introduction

The OTP controller realizes all functions of the OTP macro cell in an automated and transparent way. The controller facilitates all data transfers (reading and programming), comprises a DMA engine which connects to the AHB bus as a master, and has the highest priority to copy code from OTP into SysRAM in mirrored mode. Figure 30 shows the block diagram.

Features

- Implements all timing constraints for any access to the physical OTP cell
- Automatic single Error Code Correction (ECC) 6 bits (implemented in the OTP cell)
- 32-bit read in a single read access from the OTP cell
- Single word buffer for programming. No burst programming supported
- Empty words are 0xFFFFFFF. Zeros are programmed per 32-bit word
- Embedded DMA engine for fast mirroring of the OTP contents into the SysRAM
- Embedded DMA supports reading in bursts of 4 × 32-bit words
- Transparent random address access to the OTP memory cells via the AHB slave memory interface
- Hardwired handshaking with the PMU to realize the mirroring procedure




Figure 30. OTP controller block diagram

12.2 Architecture

The OTP controller block includes the OTP macro cell and pure digital logic implementing the controlling functions. The OTP memory communicates with the controller through a proprietary interface.

The internal organization of the OTP cell is 32-bit data and 6-bit ECC for each of the 8192 addressable positions. The six bits of the ECC are only accessible within the OTP cell. The ECC is generated by the OTP cell during the programming and is used again by the OTP cell in a transparent way during reading.

The AHB master interface is controlled by a DMA engine with an internal FIFO of eight 32-bit words. The DMA engine supports AHB reads and writes. The AHB address where memory access should begin is programmed into the DMA engine at OTPC_AHBADR_REG[OTPC_AHBADR]. The number of the 32-bit words of a transfer minus 1 must be specified in OTPC_NWORDS_REG[OTP_NWORDS].

The DMA engine internally supports the following burst types:

- Eight words incremental burst (INCR8)
- Four words incremental burst (INCR4)
- Unspecified incremental burst (INCR) with a length different from 1, 4, or 8

Single word access (SINGLE)

The slave block combines two AHB slave interfaces: one is for the registers and can be read from/written to, and the other is for the contents of the OTP memory and is read-only.

The OTP controller configures the OTP cell to be in one of the following modes:

- Deep Stand-by Mode (DSTBY). In this mode, the required power supplies are applied to the OTP cell, while
 the internal LDO of the OTP cell is inactive.
- Stand-by Mode (STBY). In this mode, the OTP cell is disabled by deactivating the chip select signal. The OTP cell is powered and the internal LDO is enabled. The power consumption of the OTP cell in this mode is not the minimum possible but is less than in an active mode (RD, PROG, PVFY, RINI, AREAD). This is the state from which any active mode of operation can be transitioned into with the least delay.
- **Read Mode (RD).** When this mode is used, the contents of the OTP cell can be read at the respective AHB address space. This mode can also be used to execute software in place (XIP). A read request is translated by the OTP controller into the corresponding control sequence for the OTP cell to retrieve the requested data.
- Programming Mode (PROG). The PROG mode provides the functionality to program a 32-bit word into an OTP position. The OTP cell expands the 32-bit word by calculating and automatically appending a 6-bit checksum (ECC). Please note that there is no way to access these extra six bits of the ECC information. Programming is performed only for bits equal to 0. Bits equal to 1 are bypassed to save programming time. Because the ECC value is unknown to the controller, there are always six extra programming pulses applied to the ECC bits. Programming is done by issuing a programming request stored in the Programming Buffer (PBUF). PBUF consists of two configuration registers storing the 32-bit data value and the 13-bit address in the OTP cell where the value should be programmed. A new request can only be stored in PBUF when the previous one is served. A status bit indicates whether this has already been done, therefore programming should be monitored by SW before a new programming request is issued.
- Programming Verification Mode (PVFY). The PVFY mode forces the OTP cell to enter a special margin read mode. This mode is used to verify the content of the OTP positions that have been programmed using the PROG mode and to verify that the programmed data is retrieved correctly under all corner cases. When this mode is used, the contents of the OTP cell can be read at the respective AHB address space. The CPU must read all OTP positions that have been programmed by accessing the corresponding addresses and verify that all the retrieved words are equal to the expected values.
- Read Initial State Mode (RINI). The RINI mode implements a production test of the initial margin read, which should be performed in the OTP cell, before the first programming is applied. This test verifies that the OTP cell is empty (all the bits are equal to 1). The OTP controller will send the required control sequence to the OTP cell to enable the test mode. Then the CPU should read all the content of the OTP cell at the respective AHB address space and verify that all the retrieved words are equal to 0xFFFFFFF. The RINI mode should be used after the PROG mode to verify the content of the OTP positions that have been programmed and specify the bits that remain un-programmed. This verification is required to ensure that the programming process has not affected the un-programmed bits. This specific read mode is a margin read, which means that it is not an equivalent to the normal read and should only be used for verification.
- Automatic Read Mode (AREAD). This mode is used to mirror large parts of the OTP cell into RAM through the AHB master interface and the integrated DMA controller.

Transitioning from one mode to another automatically steps through the STBY mode.

12.2.1 OTP Accessing Considerations

Access to the OTP memory (read/write) can only be performed at certain voltage ranges. Users are responsible for meeting these conditions while accessing the OTP. The recommended operation conditions of the OTP memory can be found under Recommended Operating Conditions section.

12.3 Programming

To configure the OTP controller, follow the sequence of steps below:

- 1. Enable clock for the OTP controller by setting the CLK_AMBA_REG[OTP_ENABLE] bit.
- 2. Put the OTP in STBY mode (OTPC MODE REGIOTPC MODE MODE] = 0x1).
- 3. Wait for OTP mode to change (OTPC STAT REG[OTPC STAT MRDY] = 1).

- 4. Set OTP speed by writing OTPC_TIM1_REG and OTPC_TIM2_REG if the system clock speed is to be reduced. These numbers basically generate asynchronous timing signals towards the OTP cell that comply to the default internal 16 MHz bus speed.
- 5. Perform an OTP access:
 - a. Programming:
 - Set up OTP write mode (OTPC_MODE_REG[OTPC_MODE_MODE] = 0x3).
 - ii. Wait for OTP mode to change (OTPC_STAT_REG[OTPC_STAT_MRDY] = 1).
 - iii. Check OTPC_STAT_REG[OTPC_STAT_PBUF_EMPTY] = 1
 - iv. Write the data to be programmed to OTPC PWORD REG.
 - v. Write the address to which the data is to be programmed to OTPC_PADDR_REG.
 - vi. Wait until the programming is finished (OTPC_STAT_REG[OTPC_STAT_PRDY] = 1).
 - vii. Switch to OTP verify mode (OTPC MODE REG[OTPC MODE MODE] = 0x4).
 - viii. Wait for OTP mode to change (OTPC_STAT_REG[OTPC_STAT_MRDY] = 1).
 - ix. Read back and compare the data written.
 - x. Put the OTP in STBY mode (OTPC_MODE_REG[OTPC_MODE_MODE] = 0x1).
 - xi. Wait for OTP mode to change (OTPC_STAT_REG[OTPC_STAT_MRDY] = 1).
 - b. Reading:
 - i. Set up OTP read mode (OTPC MODE REG[OTPC MODE MODE] = 0x2).
 - ii. Wait for OTP mode to change (OTPC_STAT_REG[OTPC_STAT_MRDY] = 1).
 - iii. Read the OTP word.
 - iv. Put the OTP in STBY mode (OTPC MODE REG[OTPC MODE MODE] = 0x1).
 - v. Wait for OTP mode to change (OTPC_STAT_REG[OTPC_STAT_MRDY] = 1).

13. DMA Controller

13.1 Introduction

The 4-channel direct memory access (DMA) controller transfers data of eight bits, 16 bits, or 32 bits between the on-chip supported peripherals (SPI, UART, UART2, I2C, and ADC) and the on-chip RAM and supports regular memory-to-memory transfers. The DMA also supports a programmable interrupt generation to generate an interrupt after a certain number of transfers to off load the Cortex interrupt rate. The on-chip peripheral requests are multiplexed on the two available channel pairs to increase the DMA utilization. A block diagram of the controller is shown on Figure 27.

Features

- Four channels with an optional peripheral trigger
- Full 32-bit source and destination pointers
- Flexible interrupt generation
- Programmable length
- Flexible peripheral request per channel
- Option to initialize memory (DMA INIT)
- Programmable edge-sensitive request support (recommended when writing to UART/UART2 and I2C)




Figure 31. DMA controller block diagram

13.2 Architecture

13.2.1 DMA Peripherals

By default, the DMA assumes memory-to-memory transactions. Each DMA channel can also be connected with the hand-shaking signals or other request signals of the corresponding peripherals (Table 45).

Table 45: DMA Served Peripherals

Name	Direction	
SPI	RX/TX	
UART	RX/TX	
UART2	RX/TX	

Name	Direction	
12C	RX/TX	
GP-ADC	RX	

13.2.2 Input/Output Multiplexer

The multiplexing of peripheral requests is controlled by DMA_REQ_MUX_REG. Thus, if DMA_REQ_MUX_REG[DMAxy_SEL] is set to a certain (non-reserved) value, the TX/RX request from the corresponding peripheral will be routed to DMA channels y (TX request) and x (RX request), respectively. Similarly, an acknowledging de-multiplexing mechanism is applied.

When two or more bit-fields (peripheral selectors) of DMA_REQ_MUX_REG have the same value, the lesser significant selector will be given priority (see also the register's description).

13.2.3 DMA Channel Operation

A DMA channel is switched on with bit DMA_ON. This bit is automatically reset if the DMA channel's transfer is finished. The DMA channels can either be triggered by SW or by a peripheral DMA request. If DREQ_MODE is 0, a DMA channel is immediately triggered.

If DREQ_MODE is 1, a DMA channel can be triggered by a HW request coming from a selected peripheral. All DMA channels support either level (default) or edge-sensitive requests via the bit-field REQ_SENSE of DMAx_CTRL_REG (x = 0, 1, 2, 3). If this bit-field is set (recommended for Memory-to-UART/UART2 and Memory-to-I2C transfers), the channel detects a positive edge on the request signal of the selected peripheral in order to start up a new transfer cycle. The edge-sensitive requests can be used globally, if desired, for all the peripherals interfacing with the DMA.

When DMA starts, data is transferred from address DMAx_A_START_REG to address DMAx_B_START_REG for a length of DMAx_LEN_REG, which can be eight, 16, or 32 bits wide. The address increment is realized with an internal 16-bit counter DMAx_IDX_REG, which is set to 0 when the DMA transfer starts and is compared with the DMAx_LEN_REG after each transfer. The register value is multiplied by the values of the automatic increment of source address (AINC), the automatic increment of destination address (BINC), and bus transfer width (BW) before it is added to DMAx_A_START_REG and DMAx_B_START_REG. AINC or BINC must be 0 for register access.

If at the end of a DMA cycle, the DMA start condition is still true, the DMA continues. The DMA stops if DREQ_MODE is low or if DMAx_LEN_REG is equal to the internal index register. This condition also clears the DMA_ON bit if DREQ_MODE is 0 or if DREQ_MODE is set to 1 and CIRCULAR bit is not set.

If a hand shaking is attached to the specific DMA channel at the end of a DMA cycle, the channel will be blocked for as long as the peripheral is not ready for the next transaction.

If the bit CIRCULAR is set to 1, the DMA controller automatically resets the internal index registers and continues from its starting address without intervention of the Arm Cortex-M0+. If the DMA controller is started with DREQ MODE = 0, the DMA will always stop, regardless of the state of CIRCULAR.




Figure 32. DMA channel diagram

Each DMA channel can generate an interrupt if the index counter DMAx_IDX_REG reaches the value of the channel's interrupt transfer length register, DMAx_INT_REG. After the transfer and before DMAx_IDX_REG is incremented, the interrupt is generated.

For example, if $DMA_x_INT_REG = 0$ and $DMA_x_LEN_REG = 0$, there will be one transfer and an interrupt.

13.2.4 DMA Arbitration

The priority level of a DMA channel can be set with bits DMA_PRIO[2-0]. These bits determine which DMA channel will be activated if more than one DMA channel requests DMA. If two or more channels have the same priority, an inherent priority applies (see register description).

With DREQ_MODE = 0, a DMA can be interrupted by a channel with a higher priority if the DMA_IDLE bit is set.

When DMA_INIT is set, however, the DMA channel currently performing the transfer locks the bus and cannot be interrupted by any other channels until the transfer is completed, regardless of whether DMA_IDLE is set. The purpose of DMA_INIT is to initialize a specific memory block with a certain value without any interruption from other active DMA channels that may request the bus at the same time. Consequently, DMA_INIT should be used only for memory initialization. When the DMA transfers data to/from peripherals, DMA_INIT should be set to 0.

NOTE

When DMA INIT is enabled, AINC must be set to 0 and BINC to 1.

Memory initialization could also be performed by simply setting AINC to 0 and BINC to 1 without enabling the DMA_INIT, provided that the source address of the memory will not change during the transfer. However, it is not guaranteed that the

NOTE

DMA transfer is not interrupted by other channels of a higher priority, when they request access to the bus at the same time.

13.2.5 Freezing DMA Channels

Each channel of the DMA controller can be temporarily disabled by writing a 1 to bit 4 SET_FREEZE_REG[FRZ_DMA] to freeze all channels.

To enable a frozen channel again, write a 1 to bit 4 RESET_FREEZE_REG[FRZ_DMA].

There is no HW protection from erroneous programming of the DMA registers.

The on-going Memory-to-Memory transfers (DREQ_MODE = 0) cannot be interrupted, therefore the corresponding DMA channels are frozen after a Memory-to-Memory transfer is completed.

13.3 Programming

13.3.1 Memory to Memory Transfers

- 1. Set the length of data to be transferred (DMAx_LEN_REG).
- 2. Set the source address (DMAx A START REG).
- 3. Set the destination address (DMAx_B_START_REG).
- 4. Configure the number of transfers until an interrupt is generated (DMAx INT REG).
- 5. Configure transfer options:
 - a. DMAx_CTRL_REG[AINC]: Automatic increment of source address.
 - b. DMAx_CTRL_REG[BINC]: Automatic increment of destination address.
 - c. DMAx_CTRL_REG[BW]: Bus transfer width.
 - d. DMAx_CTRL_REG[IRQ_ENABLE]: Enable the DMA interrupt generation for this channel.
- 6. Start the DMA transfer by setting the DMAx_CTRL_REG[DMA_ON] bit.
- 7. Wait until the transfer is finished (DMAx CTRL REG[DMA ON] = 0).
- 8. Clear the IRQ status bit for channel x in DMA_INT_STATUS_REG.

13.3.2 Peripheral to Memory Transfers

- 1. Set the length of data to be transferred (DMAx_LEN_REG).
- Set the source address (DMAx_A_START_REG) to the peripheral Rx register (for example, I2C_DATA_CMD_REG).
- 3. Set the destination address (DMAx_B_START_REG). This should point to a buffer in memory (for example, SYSRAM).
- 4. Configure the number of transfers until an interrupt is generated (DMAx INT REG).
- 5. Map the peripheral to the selected channels pair (DMA_REQ_MUX_REG[DMAxy_SEL]).
- 6. Configure transfer options:
 - a. DMAx CTRL REG[AINC]: Disable automatic increment of source address.
 - b. DMAx_CTRL_REG[BINC]: Automatic increment of destination address.
 - c. DMAx_CTRL_REG[BW]: Bus transfer width.
 - d. DMAx CTRL REG[DREQ MODE]: Enable triggering by peripheral DMA request.
 - e. DMAx_CTRL_REG[DMA_PRIO]: Set the channel's priority.
 - f. DMAx CTRL REG[IRQ ENABLE]: Enable the DMA interrupt generation for this channel.
 - g. DMAx_CTRL_REG[REQ_SENSE]: Enable edge-sensitive requests for this channel. This is recommended for Memory-to-UART/UART2/I2C transfers but can also be used globally for all the supported peripherals and for both directions (TX/RX).
- 7. Start the DMA transfer by setting the DMAx CTRL REG[DMA ON] bit.

- 8. Enable peripheral's DMA request (for example, I2C_DMA_CR_REG[TDMAE]).
- 9. Clear the IRQ status bit for channel x in DMA_INT_STATUS_REG.

14. I2C Interface

14.1 Introduction

The I2C Interface is a programmable control bus that provides support for the communications link between Integrated Circuits in a system. It is a simple two-wire bus with a software-defined protocol for system control, which is used in temperature sensors and voltage level translators to EEPROMs, general-purpose I/O, and A/D and D/A converters.

Features

- Two-wire I2C serial interface consisting of a serial data line (SDA) and a serial clock (SCL)
- Two speeds are supported:
 - Standard mode (0 to 100 kbit/s)
 - Fast mode (≤ 400 kbit/s)
- Clock synchronization
- 32 locations deep transmit/receive FIFOs (32× 8-bit RX and 32× 10-bit TX)
- Master transmit and Master receive operation
- Slave transmit and Slave receive operation
- 7-bit or 10-bit addressing
- 7-bit or 10-bit combined format transfers
- Bulk transmit mode
- Default slave address of 0x055
- Interrupt or polled-mode operation
- Handles bit and byte waiting at both bus speeds
- Programmable SDA hold time
- DMA support




Figure 33. I2C controller block diagram

14.2 Architecture

The I2C Controller block diagram is shown in Figure 33. It contains the following sub-blocks:

- AMBA Bus Interface Unit: it accesses the register file via the APB interface
- Register File: it contains configuration registers and is the interface with software
- Master State Machine: it generates the I2C protocol for the master transfers
- Slave State Machine: it generates the I2C protocol for the slave transfers
- Clock Generator: it calculates the required time to do the following:

- · Generate the SCL clock when configured as a master
- · Check for bus idle
- · Generate a START and a STOP
- · Set up the data and hold the data
- RX Shift: it takes data into the design and extracts it in byte format
- TX Shift: it presents data supplied by CPU for transfer on the I2C bus
- RX Filter: it detects the events in the bus, for example, start, stop, and arbitration lost
- Toggle: it generates pulses on both sides and toggles to transfer signals across clock domains
- Synchronizer: it transfers signals from one clock domain to another
- Interrupt Controller: it generates the raw interrupt and interrupt flags, allowing them to be set and cleared.
- RX FIFO/TX FIFO: it holds the RX FIFO and TX FIFO register banks and controllers along with their status levels.

14.2.1 I2C Bus Terms

The following terms relate to what the role of the I2C device is and how it interacts with other I2C devices on the bus.

- Transmitter is the device that sends data to the bus. A transmitter can either initiate the data transmission to the bus (a master-transmitter) or respond to a request from the master to send data back (a slave-transmitter)
- **Receiver** is the device that receives data from the bus. A receiver can either receive data on its own request (a master-receiver) or respond to a request from the master to receive data (a slave-receiver)
- Master is the component that initializes a transfer (START command), generates the clock (SCL) signal, and terminates the transfer (STOP command). A master can be either a transmitter or a receiver
- Slave is the device addressed by the master. A slave can be either a receiver or a transmitter These concepts are illustrated in Figure 34.




Figure 34. Master/Slave and Transmitter/Receiver Relationships

- Multi-master means the ability for more than one master to co-exist on the bus at the same time without collision or data loss
- Arbitration is the predefined procedure that authorizes only one master at a time to take control of the bus. For more information, refer to Section 14.2.4
- Synchronization is the predefined procedure that synchronizes the clock signals provided by two or more masters. For more information, see Section 14.2.5
- SDA is the data signal line (Serial Data)
- SCL is the clock signal line (Serial Clock)

14.2.1.1 Bus Transfer Terms

The following terms are specific to data transfers that occur to/from the I2C bus.

 START (RESTART). Data transfer begins with a START or RESTART condition. The level of the SDA data line changes from high to low, while the SCL clock line remains high. When this occurs, the bus becomes busy STOP. Data transfer is terminated by a STOP condition. This occurs when the level of the SDA data line changes from low to high, while the SCL clock line remains high. When the data transfer has been terminated, the bus is free or idle again. The bus stays busy if a RESTART is generated instead of a STOP condition

NOTE

START and RESTART conditions are functionally identical.

14.2.2 I2C Behavior

The I2C can only be controlled via SW to be an I2C master, communicating with other I2C slaves. The master is responsible for generating the clock and controlling the transfer of data. The I2C protocol also allows multiple masters to reside on the I2C bus and uses an arbitration procedure to determine the bus ownership. A slave is responsible for either transmitting or receiving data to/from the master. The acknowledgment of data is sent by the device that is receiving data, which can be either a master or a slave.

Each slave has a unique address that is determined by the system designer. When a master wants to communicate with a slave, the master transmits a START/RESTART condition that is then followed by the slave's address and a control bit (R/W) to determine whether the master wants to transmit data or receive data from the slave. The slave then sends an acknowledge pulse (ACK) after the address.

If a master-transmitter writes to a slave-receiver, the receiver gets one byte of data. This transaction continues until the master terminates the transmission with a STOP condition. If a master-receiver reads from a slave-transmitter, the slave transmits a byte of data to the master, and the master then acknowledges the transaction with an ACK pulse. This transaction continues until the master terminates the transmission by not acknowledging (NACK) the transaction after the last byte is received, and then the master issues a STOP condition or addresses another slave after issuing a RESTART condition. This behavior is illustrated in Figure 35.




Figure 35. Data transfer on the I2C bus

The I2C is a synchronous serial interface. The SDA line is a bidirectional signal and changes only when the SCL line is low, except for STOP, START, and RESTART conditions. The output drivers are open-drain or open-collector to perform wire-AND functions on the bus. The maximum number of devices on the bus is limited only by the maximum capacitance specification of 400 pF. Data is transmitted in byte packages.

14.2.2.1 START and STOP Generation

When operating as an I2C master, putting data into the transmit FIFO causes the I2C Controller to generate a START condition on the I2C bus. Allowing the transmit FIFO to empty causes the I2C Controller to generate a STOP condition on the I2C bus.

When operating as a slave, the I2C Controller does not generate START or STOP conditions, as per the protocol. However, if a read request is made to the I2C Controller, it holds the SCL line low until read data has been supplied to it. This stalls the I2C bus until read data is provided to the slave I2C Controller, or the I2C Controller slave is disabled by writing a 0 to I2C ENABLE.

14.2.2.2 Combined Formats

The I2C Controller supports transactions in a read and write combined format in both 7-bit and 10-bit addressing modes.

The I2C Controller does not support mixed address and mixed address format, that is, a 7-bit address transaction followed by a 10-bit address transaction or vice versa.

To initiate combined format transfers, I2C_CON_REG[I2C_RESTART_EN] should be set to 1. With this value set and the I2C Controller operating as a master, when an I2C transfer is completed, the I2C Controller checks the transmit FIFO and executes the next transfer. If the direction of the new transfer differs from the previous

one, the combined format is used to issue the transfer. If the transmit FIFO is empty when the current I2C transfer completes, a STOP is issued, and the next transfer is issued after a START condition.

14.2.3 I2C Protocols

The I2C Controller has the following protocols:

- START and STOP Conditions
- Addressing Slave Protocol
- Transmitting and Receiving Protocols
- START BYTE Transfer Protocol

14.2.3.1 START and STOP Conditions

When the bus is idle, both SCL and SDA signals are pulled high through external pull-up resistors on the bus. When a master wants to start a transmission on the bus, it issues a START condition. This is defined to be a high-to-low transition of the SDA signal while SCL is 1. When the master wants to terminate the transmission, it issues a STOP condition. This is defined to be a low-to-high transition of the SDA line while SCL is 1. Figure 36 shows the timing of the START and STOP conditions. When data is being transmitted on the bus, the SDA line must be stable when SCL is 1.




Figure 36. START and STOP conditions

NOTE

The signal transitions for the START/STOP conditions (Figure 36) reflect those observed at the output signals of the master driving the I2C bus. Be careful with observing the SDA/SCL signals at the input signals of the slave(s), because unequal line delays may result in an incorrect SDA/SCL timing relationship.

14.2.3.2 Addressing Slave Protocol

There are two address formats: 7-bit address format and 10-bit address format.

14.2.3.3 7-bit Address Format

In the 7-bit address format, the first seven bits (bits 7:1) of the first byte set the slave address and the LSB bit (bit 0) is the R/W bit (Figure 37). When bit 0 (R/W) is set to 0, the master writes to the slave. When bit 0 (R/W) is set to 1, the master reads from the slave.




Figure 37. 7-bit address format

14.2.3.4 10-bit Address Format

In the 10-bit address format, two bytes are transferred to set the 10-bit address. The transfer of the first byte contains the following bit definition: the first five bits (bits 7:3) notify the slaves that this is a 10-bit transfer, the next two bits (bits 2:1) set the slaves address bits 9:8, and the LSB bit (bit 0) is the R/W bit. The second byte transferred sets bits 7:0 of the slave address. Figure 38 shows the 10-bit address format and Table 46 defines the special purpose and the reserved first byte addresses.




Figure 38. 10-bit address format

Table 46: I2C Definition of Bits in First Byte in 10-bit Address Format

Slave address	R/W Bits	Description	
0000 000	0	General Call Address. I2C Controller places the data in the receive buffer and issua General Call interrupt.	
0000 000	1	START byte. For more details, refer to "START BYTE Transfer Protocol".	
0000 001	Х	CBUS address. I2C Controller ignores these accesses.	
0000 010	Х	Reserved.	
0000 011	Х	Reserved.	
0000 1XX	Х	Reserved	
1111 1XX	Х	Reserved.	
1111 0XX	Х	10-bit slave addressing.	

The I2C Controller does not restrict users from using these reserved addresses. However, if these reserved addresses are used, incompatibilities with other I2C components may occur.

14.2.3.5 Transmitting and Receiving Protocols

A master can initiate data transmission and reception to/from the bus, acting as either a master-transmitter or master-receiver. A slave responds to requests from a master to either transmit data or receive data to/from the bus, acting as either a slave-transmitter or slave-receiver.

14.2.3.5.1 Master-Transmitter and Slave-Receiver

All data is transmitted in byte format with no limit on the number of bytes transferred per data transfer. After a master sends a slave address and an R/W bit or a master transmits a byte of data to a slave, the slave-receiver must respond with an acknowledge signal (ACK). When a slave-receiver does not respond with an ACK signal, the master aborts the transfer by issuing a STOP condition. The slave must leave the SDA line high so that the master can abort the transfer.

If a master-transmitter is transmitting data as shown in Figure 39, the slave-receiver responds to the master-transmitter with an ACK signal after every byte of data is received.




Figure 39. Master-transmitter protocol

14.2.3.5.2 Master-Receiver and Slave-Transmitter

If a master is receiving data as shown in Figure 40, the master responds to the slave-transmitter with an ACK signal after a byte of data has been received except for the last byte. This is the way the master-receiver notifies the slave-transmitter that this is the last byte. The slave-transmitter relinquishes the SDA line after detecting the No Acknowledge (NACK) so that the master can issue a STOP condition.

When a master does not want to relinquish the bus with a STOP condition, the master can issue a RESTART condition. This is identical to a START condition except it occurs after the ACK signal. The master can then communicate with the same slave or a different slave.




Figure 40. Master-receiver protocol

14.2.3.5.3 START BYTE Transfer Protocol

The START BYTE transfer protocol is set up for systems that do not have an on-board dedicated I2C hardware module. When the I2C Controller is addressed as a slave, it always samples the I2C bus at the highest speed supported so that it never requires a START BYTE transfer. However, when I2C Controller is a master, it supports the generation of START BYTE transfers at the beginning of every transfer in case a slave device requires it. This protocol consists of seven zeros followed by a 1 being transmitted (Figure 41). This allows the processor that is polling the bus to under-sample the address phase until 0 is detected. Once the microcontroller detects a 0, it switches from the under-sampling rate to the correct rate of the master.

Figure 41. START BYTE transfer

The START BYTE procedure is as follows:

- 1. Master generates a START condition.
- Master transmits the START byte (0000 0001).
- 3. Master transmits the ACK clock pulse. (Present only to conform with the byte handling format used on the bus)
- 4. No slave sets the ACK signal to 0.
- 5. Master generates a RESTART (R) condition.

A hardware receiver does not respond to the START BYTE because it is a reserved address and gets reset after the RESTART condition is generated.

14.2.4 Multiple Master Arbitration

The I2C Controller allows multiple masters to reside on the same bus. There is an arbitration procedure if two masters on the same I2C bus try to control the bus at the same time by generating a START condition simultaneously. Once a master (for example, a microcontroller) has control of the bus, no other master can take control until the first master sends a STOP condition and places the bus in an idle state.

Arbitration takes place on the SDA line while the SCL line is 1. The master which transmits a 1 while the other master transmits a 0 loses the arbitration and turns off its data output stage. The master that has lost the arbitration can continue to generate clocks until the end of the byte transfer. If both masters are addressing the same slave device, the arbitration could go into the data phase. Figure 42 illustrates the timing of an arbitration between two masters on the bus.

Control of the bus is determined by the address or master code and data sent by the competing masters, so there is no central master or any order of priority on the bus.

Arbitration is not allowed between the following conditions:

- A RESTART condition and a data bit
- A STOP condition and a data bit
- A RESTART condition and a STOP condition

Slaves are not involved in the arbitration process.




Figure 42. Multiple master arbitration

14.2.5 Clock Synchronization

All masters generate their own clock to transfer messages. Data is only valid during the HIGH period of the SCL clock. When two or more masters try to transfer information on the bus at the same time, they must synchronize the SCL clock. Clock synchronization is performed using the wired-AND connection to the SCL signal. When the master transitions the SCL clock to 0, the master starts counting the LOW period of the SCL clock and transitions the SCL clock signal to 1 at the beginning of the next clock period. However, if another master is holding the SCL line to 0, the first master goes into a HIGH wait state until the SCL clock line transitions to 1.

All masters then count out their HIGH time and the master with the shortest HIGH time transitions the SCL line to 0. The masters then count out their LOW time and the one with the longest LOW time forces the other master into a HIGH wait state. Therefore, a synchronized SCL clock is generated, which is illustrated in Figure 43. Optionally, slaves may hold the SCL line LOW to slow down the timing on the I2C bus.




Figure 43. Multiple Master clock synchronization

14.3 Programming

To configure and use the I2C Controller, follow the simple sequence of steps below:

- 1. Set up the GPIOs to be used for the I2C interface (P0x MODE REG[PID] = 9 or 10).
- 2. Enable the clock for the I2C Controller (CLK_PER_REG[I2C_ENABLE] = 0x1).
- 3. Disable the I2C Controller (I2C ENABLE REG = 0).
- 4. Configure the I2C clock frequency:

- a. Standard mode (100 kbit/s): I2C_CON_REG[I2C_SPEED] = 1.
- b. Full speed mode (400 kbit/s): I2C_CON_REG[I2C_SPEED] = 2.
- 5. Setup the I2C Controller as:
 - a. Master: I2C_CON_REG[I2C_MASTER_MODE] = 1 and I2C_CON_REG[I2C_SLAVE_DISABLE] = 1.
 - b. Slave: I2C_CON_REG[I2C_MASTER_MODE] = 0 and I2C_CON_REG[I2C_SLAVE_DISABLE] = 0.
- 6. Choose whether the controller starts its transfers in the 7-bit or 10-bit addressing format when acting as a master (I2C_CON_REG[I2C_10BITADDR_MASTER]) or whether the controller responds to the 7-bit or 10-bit addresses when acting as a slave (I2C_CON_REG[I2C_10BITADDR_SLAVE]).
- 7. Set target slave address in:
 - a. Master mode (I2C_TAR_REG[IC_TAR] = 0x55 (default)).
 - b. Slave mode (I2C SAR REG[IC SAR] = 0x55 (default)).
- 8. Set the threshold levels on RX and TX FIFO (I2C RX TL REG and I2C TX TL REG).
- 9. Enable the required interrupts (I2C_INTR_MASK_REG).
- 10. Enable the I2C Controller (I2C ENABLE REG = 0x1).
- 11. Read a byte:
 - a. Prepare to transmit the read command byte (I2C_DATA_CMD_REG[I2C_CMD] = 1).
 - b. Wait until TX FIFO is empty (I2C STATUS REG[TFE] = 1).
 - Wait until master has finished reading the byte from the slave device (I2C STATUS REG[MST ACTIVITY] = 0).
- 12. Write a byte:
 - a. Prepare to transmit the write command byte (I2C_DATA_CMD_REG[I2C_CMD] = 0 and I2C_DATA_CMD_REG[I2C_DAT] = command byte).
 - b. Wait until TX FIFO is empty (I2C STATUS REG[TFE] = 1).
 - Wait until master has finished reading the response byte from the slave device (I2C_STATUS_REG[MST_ACTIVITY] = 0). End of List 0.

15. UART

15.1 Introduction

The DA14531 contains two instances of the UART block, that is, UART and UART2.

The UART is compliant to the industry-standard 16550 and is used for serial communication with a peripheral. Data is written from a master (CPU) over the APB bus to the UART and it is converted to the serial form and transmitted to the destination device. Serial data is also received by the UART and stored for the master (CPU) to read back.

There is also DMA support on the UART block, thus the internal FIFOs can be used. Only UART supports the hardware flow control signals (RTS and CTS) and the 9-bit mode.




Figure 44. UART block diagram

Features

- 16-byte transmit and receive FIFOs
- Hardware flow control (CTS/RTS) (UART only)
- Shadow registers to reduce software overhead and a software programmable reset is included
- Transmitter Holding Register Empty (THRE) interrupt mode
- Functionality based on the 16550 industry standard:
 - Programmable character properties, such as number of data bits per character (5-8) (optional)

- Parity bit (with odd or even select) and number of stop bits (1, 1.5, or 2)
- · Line break generation and detection
- · Prioritized interrupt identification
- Programmable serial data baud rate

15.2 Architecture

15.2.1 UART (RS232) Serial Protocol

Because the serial communication between the UART and the selected device is asynchronous, additional bits (start and stop) are added to the serial data to indicate the beginning and end. Utilizing these bits allows two devices to be synchronized. This structure of serial data accompanied by the start and stop bits is referred to as a character (Figure 45).




Figure 45. Serial data format

An additional parity bit may be added to the serial character. This bit appears after the last data bit and before the stop bit(s) in the character structure to provide the UART with the ability to perform simple error checking on the received data.

The UART Line Control Register (UART_LCR_REG) is used to control the serial character characteristics. The individual bits of the data word are sent after the start bit, starting with the least-significant bit (LSB). These are followed by the optional parity bit and then by the stop bit(s), which can be of 1, 1.5, or 2 bits.

All the bits in the transmission (except the half stop bit when the 1.5 stop bits are used) are transmitted for the same time duration. This is referred to as a Bit Period or Bit Time. One Bit Time equals to 16 baud clocks. To ensure stability on the line, the receiver samples the serial input data at approximately the mid-point of the Bit Time once the start bit has been detected. As the exact number of baud clocks that each bit has been transmitted for is known, the mid-point for sampling is every 16 baud clocks after the mid-point sample of the start bit. Figure 46 shows the sampling points of the first couple of bits in a serial character.




Figure 46. Receiver serial data sampling points

As part of the 16550 standards, an optional baud clock reference output signal (baudout_n) is supplied to provide timing information to the receiving devices that require it. The baud rate of the UART is controlled by the serial clock (*sclk* or *pclk* in a single clock implementation) and the Divisor Latch Register (DLH and DLL) in the following equation:

baud rate = (serial clock frequency)/
$$(16 \times \text{divisor})$$
 (2)

where the divisor is a 16-bit integer value plus 4-bit fractional value. The divisor range is 0 to 65535,9375 with steps of 1/16. Divisor High 8-bit integer part is in the DLH register. Divisor Low 8-bit integer part is in the DLF register. Divisor 4-bit fractional port is in the DLF register.

The registers settings for the common baud rate values are presented in Table 47.

Table 47: UART Baud Rate Generation

Baud rate	Divider	Divisor latch	DLH Reg	DLL Reg	DLF Reg	Actual BR	Error (%)
1200	833,333	833,3125	3	65	5	1200,03	0,00
2400	416,667	416,6875	1	160	11	2399,88	0,00
4800	208,333	208,3125	0	208	5	4800,48	0,01
9600	104,167	104,1875	0	104	3	9598,08	0,02
19200	52,083	52,0625	0	52	1	19207,68	0,04
38400	26,042	26,0625	0	26	1	38369,30	0,08
57600	17,361	17,375	0	17	6	57553,96	0,08
115200	8,681	8,6875	0	8	11	115107,91	0,08
230400	4,340	4,3125	0	4	5	231884,06	0,64
460800	2,170	2,1875	0	2	3	457142,86	0,79
921600	1,085	1,0625	0	1	1	941176,47	2,12
1000000	1	1	0	1	0	1000000	0,00

15.2.2 Clock Support

The UART has two system clocks (*pclk* and *sclk*). Having a second asynchronous serial clock (sclk) allows for accurate serial baud rate settings and meeting APB bus interface requirements.

With the two-clock design, a synchronization module is implemented to synchronize all controls and data across the two system clock boundaries.

Although a serial clock faster than four-times the *pclk* does not leave enough time for a complete incoming character to be received and pushed into the receiver FIFO, in most cases the *pclk* signal is faster than the serial clock and this should never be an issue.

The serial clock modules must have time to see new register values and reset their respective state machines. This total time is guaranteed to be no more than eight clock cycles of the slower of the two system clocks. Therefore, no data should be transmitted or received before this maximum time expires after the initial configuration of the UART.

15.2.3 Interrupts

The assertion of the UART interrupt (UART_INT) occurs whenever one of the several prioritized interrupt types are enabled and active. The following interrupt types can be enabled with the IER register:

- Receiver Error
- Receiver Data Available
- Character Timeout (in FIFO mode only)
- Transmitter Holding Register Empty at/below threshold (in Programmable THRE interrupt mode)

When an interrupt occurs, the master accesses the UART_IIR_REG to determine the source of the interrupt before dealing with it accordingly. These interrupt types are described in more detail in Table 48.

Table 48: UART Interrupt Priorities

Interrupt ID	Interrupt set and reset functions				
Bits [3-0]	Priority	Interrupt type	Interrupt source	Interrupt reset control	
0001	-	None			
0110	Highest	Receiver Line status	Overrun/parity/framing errors or break interrupt	Reading the line status register	
0100	1	Receiver Data Available	Receiver data available (non- FIFO mode or FIFOs disabled) or	Reading the receiver buffer register (non-FIFO mode or FIFOs disabled) or the FIFO	

Interrupt ID	Interrupt set and reset functions					
Bits [3-0]	Priority	Interrupt type	Interrupt source	Interrupt reset control		
			RCVR FIFO trigger level reached (FIFO mode and FIFOs enabled)	drops below the trigger level (FIFO mode and FIFOs enabled)		
1100	2	Character timeout indication	No characters in or out of the RCVR FIFO during the last four-character times and there is at least one character in it during this time.	Reading the receiver buffer register		
0010	3	Transmitter holding register empty	Transmitter holding register empty (Prog. THRE Mode disabled) or XMIT FIFO at or below threshold (Prog. THRE Mode enabled).	Reading the IIR register to check whether there is an interrupt and what its source is; or, writing into THR (FIFOs or THRE Mode not selected or disabled) or XMIT FIFO above threshold (FIFOs and THRE Mode selected and enabled).		
0000	4	Reserved				
0111	Lowest	Reserved	-	-		

15.2.4 Programmable THRE Interrupt

The UART can be configured to have a Programmable THRE Interrupt mode available to increase system performance.

When Programmable THRE Interrupt mode is selected, it can be enabled via the Interrupt Enable Register (IER[7]). When FIFOs and the THRE Mode are implemented and enabled, THRE Interrupts are active at and below a programmed transmitter FIFO empty threshold level, as shown in the flowchart in Figure 47. Figure 48 shows the programmed transmitter FIFO empty threshold level, where THRE Interrupts are active when the FIFO is empty. In this case the programmable THRE interrupt mode is disabled.

This threshold level is programmed into FCR[5:4]. The available empty thresholds are: empty, 2, ¼, and ½. See UART_FCR_REG for threshold setting details. Selection of the best threshold value depends on the system's ability to begin a new transmission sequence in a timely manner. However, one of these thresholds should prove optimum in increasing system performance by preventing the transmitter FIFO from running empty.

In addition to the interrupt change, Line Status Register (LSR[5]) also switches its function from indicating transmitter FIFO empty to FIFO full. This allows software to fill the FIFO in each transmit sequence by polling LSR[5] before writing another character. Instead of waiting until the FIFO is completely empty, the flow becomes "fill transmitter FIFO whenever an interrupt occurs and there is data to transmit". Waiting until the FIFO is empty causes a performance hit whenever the system is too busy to respond immediately.

Even if everything else is selected and enabled, if the FIFOs are disabled via FCR[0], the Programmable THRE Interrupt mode is also disabled. When not selected or disabled, THRE interrupts and LSR[5] function normally (both reflecting an empty THR or FIFO). The flowchart of THRE interrupt generation when not in programmable THRE interrupt mode is shown in Figure 48.




Figure 47. Flowchart of interrupt generation for programmable THRE Interrupt mode




Figure 48. Flowchart of interrupt generation when not in programmable THRE Interrupt mode

15.2.5 Shadow Registers

The shadow registers shadow some of the existing register bits that are regularly modified by software. These can be used to reduce the software overhead that is introduced by having to perform read-modify-writes.

- UART_SRBR_REG support a host burst mode where the host increments its address but still accesses the same receive buffer register
- UART_STHR support a host burst mode where the host increments its address but still accesses the same transmit holding register
- UART SFE REG accesses the FCR[0] register without accessing the other UART FCR REG bits
- UART_SRT_REG accesses the FCR[7-6] register without accessing the other UART_FCR_REG bits
- UART STER REG accesses the FCR[5-4] register without accessing the other UART FCR REG bits

15.2.6 Direct Test Mode

The on-chip UARTs can be used for the Direct Test Mode required for the final product PHY layer testing. It can be done either over the HCl layer, which engages a full CTS/RTS UART, or by using a 2-wire UART directly as described in the *Bluetooth Low Energy Specification (Volume 6. Part F)*.

15.3 Programming

To configure and use the UART controllers, follow the simple sequence of steps below:

- 1. Set up the GPIOs to be used for the UART interface (P0x MODE REG[PID] = 1 to 4 and/or 19-20).
- 2. Enable the selected UART by setting the CLK_PER_REG[UARTx_ENABLE] bit.
- Enable access to Divisor Latch Registers (DLL and DLH) by setting the UARTx_LCR_REG[UART_DLAB] bit
- 4. Set the desired baud rate. To calculate the registers values for the desired baud rate, use the following equation:

Divisor =
$$UART CLK/(16 \times Baud rate)$$
 (3)

- a. UARTx_IER_DLH_REG: High byte of the Divisor integer part.
- b. UARTx RBR THR DLL REG: Low byte of the Divisor integer part.
- c. UARTx_DLF_REG: The fractional part of the Divisor.
- 5. Configure the break control bit, parity, number of stop bits, and data length (UARTx_LCR_REG).
- 6. Enable and configure the FIFO (UARTx IIR FCR REG).
- 7. Configure the generated interrupts, if needed (UARTx IER DLH REG).
- 8. Send a byte:
 - a. Check if Transmit Hold Register (THR) is empty (UARTx LSR REG[UART THRE]).
 - b. Load the byte to THR (UARTx RBR THR DLL REG).
 - c. Check if the byte has been transmitted (UARTx_LSR_REG[UART_TEMT]).
- 9. Receive a byte:
 - a. Wait until serial data is ready (UARTx LSR REG[UART DR]).
 - b. Read the incoming byte from the THR (UARTx_RBR_THR_DLL_REG).

16. SPI Interface

16.1 Introduction

This controller implements the Serial Peripheral Interface (SPI™)¹ for master and slave modes. The serial interface can transmit and receive from four bits to up to 32 bits in master/slave mode. The controller comprises separate TX and RX FIFOs and DMA handshake support. Slave mode clock speed is independent from the system clock speed. Moreover, master's clock speed can be as fast as the system's clock speed. The controller can generate an interrupt upon data threshold reached in the TX or RX FIFOs.

Features

- Slave and master mode
- From 4-bit to up to 32-bit operation
- SPI Master clock line speed up to 32 MHz, SPI Slave clock line speed up to 16 MHz
- SPI mode 0, 1, 2, and 3 support (clock edge and phase)
- Built-in separate 8-bit wide and 4-byte deep RX/TX FIFOs for continuous SPI bursts
- Maskable interrupt generation based on TX or RX FIFO thresholds
- DMA support




Figure 49. SPI block diagram

¹ SPI is a trademark of Motorola, Inc.

16.2 Architecture

The SPI controller is an APB peripheral operating on the apb clk clock. It contains a front end which is clocked by the spi clk clock and is responsible for the serialization/deserialization of the data in the RX and TX streams.

Two separate FIFOs, each of eight bits wide and four bytes deep, are used to store data for RX and TX streams. Since a SPI word can be configured to be from four bits to up to 32 bits, one to four FIFO positions can be written/read at the same time. FIFOs contain logic implementing programmable thresholds comparison.

The SPI controller supports DMA requests and interrupt generation based on the FIFO thresholds. If enabled, a DMA request and/or interrupt will be asserted with whether TX FIFO level is low or RX FIFO level is high.

The SPI interface supports all four modes of operation and the corresponding polarity (CPOL) and phase (CPHA) of the SPI clock (SPI CLK) are defined in Table 49.

SPI Mode	CPOL	СНРА	TX SPI_CLK	RX SPI_CLK	Idle SPI_CLK
0	0	0	Falling edge	Rising edge	Low
1	0	1	Rising edge	Falling edge	Low

0

1

Table 49: SPI Modes Configuration and SCK States

1

1

To read from or to write to an external single byte FLASH device in the SPI master mode, a byte swap mechanism is implemented to allow for a proper placement of the bytes in a 16-bit word for the DMA to write to/read from the internal RAM. More specifically, when the SPI controller is configured as a master with DMA support and a 16-bit word width so that the bus utilization is increased compared to reading from an 8-bit device, the byte swap mechanism brings the least significant byte read and place it in the most significant byte in the 16bit word. The controller automatically swaps the bytes to allow for placing the first byte read in the least significant byte of the 16-bit word. This feature is programmable via SPI CTRL REG[SPI SWAP BYTES].

Rising edge

Falling edge

Falling edge

Rising edge

The SPI controller can operate at the highest speed (32 MHz on the SPI CLK line) in a special master mode. The clock of the controller is then either the XTAL32M or the RC32M and can be used for fast booting from external FLASH devices that support this frequency.

16.2.1 SPI Timing

2

3

The timing of the SPI interface when the SPI controller is in slave mode is presented in Figure 50.




Figure 50. SPI Slave mode timing (CPOL = 0, CPHA = 0)

Table 50: SPI Timing Parameters

Parameter	Description	Тур	Unit
tckper	spi_clk clock period	60	ns
tcsst	CS active time before the first edge of spi_clk	1 spi_clk cycle	
tcshold	tcshold CS non-active time after the last edge of spi_clk		
t _{MOST}	Master input data latching setup time	(spi_clk/2) - 5	ns

High

High

Parameter	Description	Тур	Unit
tmohold	Master input data hold time	0	ns
tsodel	Slave output data delay	25	ns

16.3 Programming

16.3.1 Master Mode

To configure the SPI controller in master mode, follow the steps below:

- 1. Set the appropriate GPIO ports in SPI clock mode (output), SPI Chip Select mode (output), SPI Data Out mode (output), and SPI Data In mode (input).
- 2. Enable SPI clock by setting CLK PER REG[SPI ENABLE] = 1.
- 3. Reset SPI FIFO by setting SPI_CTRL_REG[SPI_FIFO_RESET] = 1.
- Set the SPI clock mode (synchronous or asynchronous with APB clock) by programming SPI_CLOCK_REG[SPI_MASTER_CLK_MODE].
- 5. Set the SPI clock frequency by programming SPI_CLOCK_REG[SPI_CLK_DIV]. If SPI_CLK_DIV is not 0x7F, SPI_CLK = module_clk/2 × (SPI_CLK_DIV + 1). If SPI_CLK_DIV = 0x7F, SPI_CLK = module_clk.
- 6. Set the SPI mode (CPOL or CPHA) by programming SPI_CONFIG_REG[SPI_MODE].
- 7. Set the SPI controller in master mode by setting SPI CONFIG REG[SPI SLAVE EN] = 0.
- 8. Define the SPI word length (from 4-bit to 32-bit) by programming SPI CONFIG REG[SPI WORD LENGTH]. SPI WORD LENGTH = word length 1.

To read/write the following sequence should be performed:

- 1. If a slave device is slow and does not give the data at the correct clock edge, configure the SPI module to capture data at the next clock edge by setting SPI_CTRL_REG[SPI_CAPTURE_AT_NEXT_EDGE] = 1. Otherwise, set SPI_CTRL_REG[SPI_CAPTURE_AT_NEXT_EDGE] = 0.
- 2. Release FIFO reset by setting SPI_CTRL_REG[SPI_FIFO_RESET] = 0.
- 3. Enable SPI TX path by setting SPI CTRL REG[SPI TX EN] = 1.
- 4. Enable SPI RX path by setting SPI_CTRL_REG[SPI_RX_EN] = 1.
- 5. Enable the SPI chip select by programming the SPI_CS_CONFIG_REG[SPI_CS_SELECT] = 1 or 2. This option allows the master to select the slave that is connected to the GPIO that has the function of SPI_CS0 or SPI_CS1.
- 6. Enable the SPI controller by setting SPI_CTRL_REG[SPI_EN] = 1.
- 7. Write to TX FIFO by programming SPI_FIFO_WRITE_REG[SPI_FIFO_WRITE]. Write access is permitted only when SPI_FIFO_STATUS_REG[SPI_TX_FIFO_FULL] = 0.
- 8. Read from RX FIFO by programming SPI_FIFO_READ_REG[SPI_FIFO_READ]. Read is permitted only when SPI_FIFO_STATUS_REG[SPI_RX_FIFO_EMPTY] = 0.
- 9. To disable the SPI chip select, set SPI_CS_CONFIG_REG[SPI_CS_SELECT] = 0 to deselect the slave and set SPI_CTRL_REG[SPI_FIFO_RESET] = 1 to reset the SPI FIFO.

16.3.2 Slave Mode

- 1. Set the appropriate GPIO ports in SPI clock mode (input), SPI Chip Select mode (input), SPI Data Out mode (output), and SPI Data In mode (input).
- 2. Enable SPI clock by setting CLK PER REG[SPI ENABLE] = 1.
- 3. Reset SPI FIFO by setting SPI CTRL REG[SPI FIFO RESET] = 1.
- 4. Set the SPI mode (CPOL or CPHA) by programming SPI_CONFIG_REG[SPI_MODE].
- 5. Set the SPI module in slave controller by setting SPI_CONFIG_REG[SPI_SLAVE_EN] = 1.
- Define the SPI word length (from 4-bit to 32-bit) by programming SPI_CONFIG_REG[SPI_WORD_LENGTH]. SPI_WORD_LENGTH = word length - 1.

To read/write the following sequence has to be performed:

- 1. Set SPI FIFO in normal operation by setting SPI_CTRL_REG[SPI_FIFO_RESET] = 0.
- 2. Enable SPI TX path by setting SPI_CTRL_REG[SPI_TX_EN] = 1.
- 3. Enable SPI RX path by setting SPI_CTRL_REG[SPI_RX_EN] = 1.
- 4. Enable the SPI controller by setting SPI_CTRL_REG[SPI_EN] = 1.
- 5. Write the first data byte directly to TX buffer by programming the SPI_TXBUFFER_FORCE_L_REG[SPI_TXBUFFER_FORCE_L].
- Write the rest of the data to TX FIFO by programming SPI_FIFO_WRITE_REG[SPI_FIFO_WRITE]. Write access is permitted only if SPI_FIFO_STATUS_REG[SPI_TX_FIFO_FULL] = 0.
- 7. Read from RX FIFO by programming SPI_FIFO_READ_REG[SPI_FIFO_READ]. Read is permitted only if SPI_FIFO_STATUS_REG[SPI_RX_FIFO_EMPTY] = 0.

17. Quadrature Decoder

17.1 Introduction

The DA14531 has an integrated Quadrature decoder that can automatically decode the signals for the X, Y, and Z axes of a HID input device, reporting step count and direction. It can also be programmed to simply count rising/falling edges on any of the channel pairs. This block can be used to wake up the chip as soon as there is a movement from the connected external device. The block diagram of the quadrature decoder is presented in Figure 51.

Features

- Three 16-bit signed counters that provide the step count and direction on each of the axes (X, Y, and Z) and one 8-bit counter counting the overall edges from all the three counters
- Programmable system clock sampling at a maximum of 16 MHz
- APB interface for control and programming
- Programmable source from the GPIOs
- Digital filter on the channel inputs to avoid spikes




Figure 51. Quadrature decoder block diagram

17.2 Architecture

Channels are expected to provide a pulse train with 90 degrees rotation as displayed in Figure 52 and Figure 53.




Figure 52. Moving forward on Axis X




Figure 53. Moving backwards on Axis X

Depending on whether channel A or channel B is leading in phase, the quadrature decoding block calculates the direction on the related axis. Furthermore, the signed counter value represents the number of steps moved.

Users can choose which GPIOs to use for the channels by programming the QDEC_CTRL2_REG register. The block supports two modes of operation: quadrature counting and edges counting. The quadrature counting mode reads the patterns of successive pulses as in Figure 52 and Figure 53, while the edges counting mode simply counts all positive and negative edges on any of the two channels of a pair.

NOTE

If two edges happen at the same time, the counter will only count one.

The digital filter eliminates the spikes shorter than three clock periods. It is followed by an edge detection circuitry and they are shown in Figure 54.




Figure 54. Digital filtering and edge detection circuit

A counter for its dedicated axis holds the movement events of the channels. When a channel is disabled, the counter is reset. The counters are accessible via the APB bus.

The QDEC_EVENT_CNT gathers all edges on all channels regardless of the mode of operation. If two edges happen at the same time, this counter will only be increased by one.

The quadrature decoder operates on the system clock. The QDEC_CLOCKDIV register defines the number of clock cycles during which the decoding logic samples the data on the channel inputs. The division is automatically disabled when the lp_clk is used as the system clock.

17.3 Programming

To program the quadrature decoder for actual quadrature counting or edge counting, follow the simple sequence of steps below:

- 1. Configure the clock frequency by configuring the QDEC_CLOCKDIV register. The value in this register will be dividing the sys_clk. However, if sys_clk = lp_clk, this divider is completely bypassed.
- 2. Define which pin pairs represent the different channels for the X, Y, and Z axes or the GPIOs from which the edges are counted. Configure such information at QDEC_CHX_PORT_SEL, QDEC_CHY_PORT_SEL, and QDEC_CHZ_PORT_SEL registers.
- Configure the interrupt threshold upon which an interrupt will be generated at QDEC_CTRL_REG[QDEC_IRQ_THRES]. Note that the interrupt threshold is based on the value of QDEC_EVENT_CNT_REG which keeps on counting after the interrupt is generated.

- 4. Define the mode of operation by configuring the respective QDEC_CHx_EVENT_MODE field in the QDEC_CTRL2_REG.
- 5. Enable the clock of the block by writing at CLK PER REG[QUAD ENABLE].
- 6. Wait for the interrupt and then read X, Y, and Z values at QDEC_XCNT_REG, QDEC_YCNT_REG, and QDEC_ZCNT_REG (in the quadrature counting case) or the QDEC_EVENT_CNT_REG (in the edges counting case).
- 7. Clear the interrupt (by writing at QDEC_CTRL_REG[QDEC_IRQ_STATUS]) and the edge counter (by writing at QDEC_CTRL_REG[QDEC_EVENT_CNT_CLR) if needed.

18. Clockless Wake-up Controller

18.1 Introduction

The Clockless Wake-up Controller implements a circuit that enables the RC32K clock which in turn triggers the HW Startup FSM to allow the system to be woken up by an external event (a GPIO toggle). This controller is only used when the system is in hibernation mode, that is, when all clocks are stopped.

Features

- Wake up the system from specific GPIOs (P0 1, P0 2, P0 3, P0 4, and P0 5)
- Configurable polarity of the GPIO signals (single configuration for all GPIOs)
- Special RC filtered inputs feeding the wakeup control circuit (Type B pads)
- Always powered




Figure 55. Clockless wake-up controller circuit

18.2 Architecture

The Clockless Wake-up Controller automatically enables the RC32K oscillator when a toggle is identified in one of the five specific GPlOs (P0_1, P0_2, P0_3, P0_4, and P0_5). These GPlO signals are connected to the Type B pads, which provide two outputs to the digital domain. One output goes through a Schmitt trigger and the other one goes through an RC filter with a cutoff frequency of 100 kHz and a Schmitt trigger. The output going through the RC filter and a Schmitt trigger feeds the clockless wakeup controller circuitry. Hence, any spikes larger than 100 kHz will be filtered out without waking up the system.

The triggering GPIO can be defined by means of a masking register. If no GPIO is masked out, any toggle in any of these GPIOs will create an edge which serves as a clock for a Flip-Flop to lock and enable the oscillator. The polarity of the edge is also programmable, but it is common for the GPIOs and not a dedicated bit per GPIO.

Note that, if two opposite edges occur exactly at the same time on two GPIOs that are allowed to wake up the system, the XOR output will not change its value and no wake up occurs. However, even if the GPIO signal events have a couple of ns difference, the circuit will still understand it and the clock is started.

18.3 Programming

To program the clockless wakeup controller before setting the system into hibernation mode, follow the simple sequence of steps below:

 Define which pins are allowed to wake up the system from hibernation by configuring the HIBERN_CTRL_REG[HIBERN_WKUP_MASK].

- 2. Define the polarity of the waking up events at HIBERN_CTRL_REG[HIBERN_WKUP_POLARITY]. This should be done by reading the value of the unmasked GPIOs and programming the polarity register with their XOR'ed state.
- 3. Enable the hibernation mode by programming the HIBERN_CTRL_REG[HIBERNATION_ENABLE] bit field. Note that this action stops all clocks when the system drops to sleep.
- 4. Allow RAM to be retained by programming the RAM_PWR_CTRL_REG accordingly.
- 5. Define where address 0 is to be mapped at SYS_CTRL_REG[REMAP_ADR0] so that the CPU can execute code right after waking up. If RAM is retained, REMAP_ADR0 should point to 0x2 or 0x3.
- 6. Clear RESET STAT REG. Clear this register means that the system wakes up from the hibernation mode.
- 7. Put the system to sleep by executing the WFI command with the SCR bit set.

19. Clocked Wake-up Controller

19.1 Introduction

The Clocked Wake-up Controller can be programmed to wake up the DA14531 from deep sleep mode and extended sleep mode upon a pre-programmed number of GPIO events on a maximum of two pins in parallel. This wakeup controller resides in the PD SLP power domain and operates on the LP CLK.

The block diagram illustrating the wakeup function is shown in Figure 56.

Features

- Monitors GPIO state changes
- Implements debouncing time from 0 ms up to 63 ms on two GPIOs in parallel
- Accumulates external events and compares the number to a programmed value
- Generates an interrupt to the CPU's WIC




Figure 56. Clocked wake-up controller block diagram

19.2 Architecture

The controller comprises two identical circuits that implement the edge detection, debouncing, and event counting before generating a wakeup interrupt towards the CPU.

A LOW to HIGH level transition on the selected input port sets internal signal "key_hit" to 1, while WKUP_POL_GPIO_REG[y] = 0. This signal triggers the event counter state machine as shown in Figure 57. The debounce counter is loaded with the value of WKUP_CTRL_REG[WKUP_DEB_VALUE]. The timer counts down every 1 ms. The signal state is constantly monitored. If the debounce counter reaches 0, it means that the key hit signal state has been stable over the amount of clock cycles counted by the debounce counter.




Figure 57. Event counter state machine for the wake-up interrupt generator

The event counter is edge sensitive. After an active edge is detected, a reverse edge must be detected first before the event counter goes back to the IDLE state and from there starts waiting for a new active edge.

If the event counter is equal to the value set in the WKUP_COMPARE_REG register, the counter will be reset and an interrupt will be generated, if the interrupt generation has been enabled by WKUP_ENABLE_IRQ and WKUP2_ENABLE_IRQ in the WKUP_CTRL_REG.

NOTE

There is only one register for both circuits that contains the number of events before an interrupt is issued.

The interrupt can be cleared by writing a value to the register WKUP_RESET_IRQ_REG. The event counter can be reset by writing a value to the register WKUP_RESET_CNTR_REG. The value of the event counter can be read at any time by reading register WKUP_COUNTER_REG.

Any of the GPIO inputs can be selected to generate an event by programming the corresponding WKUP/WKUP2_SELECT_GPIO_REG register. When both WKUP/WKUP2_SELECT_GPIO_REG registers are configured to generate a wakeup interrupt, a toggle on any GPIO will wake up the system.

The input signal edge can be selected by programming the WKUP/WKUP2_POL_GPIO_REG registers.

NOTE

A minimum of 2 low power clocks pulse is required on a GPIO in order to be correctly identified as a wake-up edge trigger

19.3 Programming

To configure the clocked wakeup controller, follow the simple sequence of steps below:

- 1. Define the polarity of the triggering GPIOs at WKUP/WKUP2_POL_GPIO_REG.
- 2. Configure the debouncing counters by programming WKUP_CTRL_REG[WKUP_DEB_VALUE] with the amount of time (ms) during which the signal should be re-sampled before its state is decided. Note that there is a single bit field for debouncing counters.
- 3. Define the number of events that are needed to trigger the wakeup interrupt by programming the WKUP_COMPARE_REG. Note there is only one register for both circuits.
- 4. Allow the interrupt generation by configuring the WKUP_ENABLE_IRQ and WKUP2_ENABLE_IRQ bit fields, respectively, in the WKUP_CTRL_REG.
- 5. Define which GPIOs are allowed to trigger a wakeup event at WKUP/WKUP2 SELECT GPIO REG.
- 6. Set the system to deep sleep mode or extended sleep mode by executing the WFI command with the SCR bit set.

20. Timer 0

20.1 Introduction

Timer 0 is a 16-bit general purpose software programmable timer, which has the ability of generating Pulse Width Modulated (PWM) signals PWM0 and PWM1. It also generates the SWTIM_IRQ interrupt to the Arm Cortex-M0+. It can be configured in various modes regarding output frequency, duty cycle, and the modulation of the PWM signals. Figure 58 shows the block diagram of Timer 0.

Features

- 16-bit general purpose timer
- Ability to generate two PWM signals (PWM0 and PWM1)
- Programmable output frequency (f) with N = 0 to (2¹⁶-1) and M = 0 to (2¹⁶-1)

$$f = \frac{(16, 8, 4, 2 MHz \text{ or } 32 \text{ kHz})}{(M+1) + (N+1)}$$

Programmable duty cycle (δ):

$$\delta = \frac{M+1}{(M+1)+(N+1)} \times 100 \%$$

Separately programmable interrupt timer:

$$T = \frac{(16, 8, 4, 2 MHz \text{ or } 32 \text{ kHz})}{(ON+1)}$$




Figure 58. Timer 0 block diagram

20.2 Architecture

The 16-bit Timer 0 consists of two counters, that is, T0-counter and ON-counter, and three registers, that is, TIMER0_RELOAD_M_REG, TIMER0_RELOAD_N_REG, and TIMER0_ON_REG. Upon reset, the counter and register values are 0x0000. Timer 0 generates a PWM signal PWM0, of which the frequency and duty cycle are determined by the contents of the TIMER0_RELOAD_N_REG and the TIMER0_RELOAD_M_REG registers. The PWM1 signal is the inverted version of PWM0.

Timer 0 can run at five different clocks: 16 MHz, 8 MHz, 4 MHz, 2 MHz, or 32 kHz. The 32 kHz clock is selected by default with bit TIM0_CLK_SEL in the TIMER0_CTRL_REG register. This slow clock has no enabling bit. The other four options can be selected by setting the TIM0_CLK_SEL bit and the TMR_ENABLE bit in the CLK_PER_REG (by default the TMR_ENABLE bit is disabled). This register also controls the four higher clock frequency on which Timer 0 runs via the TMR_DIV bits. An extra clock divider is available and can be activated via bit TIM0_CLK_DIV of the timer control register TIMER0_CTRL_REG. This clock divider is only used for the ON-counter and always divides the clock for the ON-counter by 10.

NOTE

If the LP clock is selected as system clock, the CLK_AMBA_REG[HCLK] bit field should always be 0 to ensure the proper operation of the timer.

Timer 0 operates in PWM mode. The signals PWM0 and PWM1 can be mapped to any GPIOs.

Timer 0 PWM Mode

If bit TIM0_CTRL in the TIMER0_CTRL_REG is set, Timer 0 will start running. SWTIM_IRQ will be generated and the T0-counter will load its start value from the TIMER0_RELOAD_M_REG register and will decrement on each clock cycle. The ON-counter also loads its start value from the TIMER0_ON_REG register and decrements with the selected clock.


When the T0-counter reaches zero, the internal signal T0-toggle will be toggled to select the TIMER0_RELOAD_N_REG whose value will be loaded in the T0-counter. Each time the T0-counter reaches zero, it is alternately reloaded with the values of the M0- and N0-shadow registers. PWM0 will be high when the M0-value decrements and low when the N0-value decrements. For PWM1 the opposite is applicable since it is inverted. If bit PWM_MODE in the TIMER0_CTRL_REG register is set, the PWM signals are not HIGH during the "high time" but output a clock in that stage. The frequency is based on the clock settings defined in the CLK_PER_REG register (also when the 32-kHz clock is used), but the selected clock frequency is divided by two to get a 50 % duty cycle.

If the ON-counter reaches zero, it will remain zero until the T0-counter also reaches zero, while decrementing the value loaded from the TIMER0_RELOAD_N_REG register (PWM0 is low). The counter will then generate an interrupt (SWTIM_IRQ). The ON-counter will be reloaded with the value of the TIMER0_ON_REG register. The T0-counter as well as the M0-shadow register will be loaded with the value of the TIMER0_RELOAD_M_REG register. At the same time, the N0-shadow register will be loaded with the value of TIMER0_RELOAD_N_REG register. Both counters will be decremented on the next clock again and the sequence will be repeated.

NOTE

It is possible to generate interrupts at a high rate by selecting a high clock frequency and low counter values. This could result in missed interrupt events.

During the time when the ON-counter is non-zero, new values for the ON-register, M0-register, and N0-register can be written, but they are not used by the T0-counter until a full cycle is finished. More specifically, the newly written values in the TIMER0_RELOAD_M_REG and TIMER0_RELOAD_N_REG registers are only stored into the shadow registers when the ON-counter and the T0-counter have both reached zero and the T0-counter is decrementing the value loaded from the TIMER0_RELOAD_N_REG register (Figure 59).



TIM0580-01

Figure 59. Timer 0 PWM mode

At start-up both counters and the PWM0 signal are LOW, so at start-up an interrupt is also generated. If Timer 0 is disabled, all flip-flops, counters, and outputs are in reset state except the ON-register, the TIMER0 RELOAD N REG register, and the TIMER0 RELOAD M REG register.

The timer input registers, that is, ON-register, TIMERO_RELOAD_N_REG, and TIMERO_RELOAD_M_REG can be written, and the counter registers ON-counter and T0-counter can be read. When reading from the address of the ON-register, the value of the ON-counter is returned. Reading from the address of either the TIMERO_RELOAD_N_REG or the TIMERO_RELOAD_M_REG register returns the value of the T0-counter.

It is possible to freeze Timer 0 with bit FRZ_SWTIM of the register SET_FREEZE_REG. When the timer is frozen, the timer counters are not decremented. This will freeze all the timer registers at their last value. The timer will continue its operation again when bit FRZ_SWTIM is cleared via register RESET_FREEZE_REG.

20.3 Programming

When LP clock is selected as system clock, CLK AMBA REG[HCLK DIV] should be set to 0.

When LP clock is selected as Timer clock, CLK_PER_REG[TMR_DIV] should be set to 0

20.3.1 Timer Functionality

Timer 0 supports the functionality of a timer for generating interrupts after specific time intervals. To configure the timer operation, follow the steps below:

- Select the timer clock by programming TIMER0_CTRL_REG[TIM0_CLK_SEL]. The system or the LP clock can be selected using this option.
- 2. Select the clock division scaler by programming CLK_PER_REG[TMR_DIV]. Note that this setting only applies to the system clock.
- Define whether Timer 0 will use the clock frequency as is or divided by 10 by programming TIMERO CLK REG[TIMO CLK DIV].
- 4. Enable Timer 0 clock by programming CLK PER REG[TMR ENABLE].
- For 16-bit counting, program TIMER0_ON_REG with the expired time in timer 0 clock cycles TIMER0_RELOAD_M_REG and TIMER0_RELOAD_N_REG must be set to 0.
- For 17-bit counting, load 65535 to TIMER0_RELOAD_M_REG and the rest to TIMER0_RELOAD_N_REG. TIMER0 ON REG must be set to 0.
- 7. Enable Timer 0 by programming TIMER0 CTRL REG[TIM0 CTRL].

20.3.2 PWM Generation

Timer 0 also supports PWM generation. To configure the PWM generation functionality, follow the steps below:

1. Select the timer clock by programming TIMER0_CTRL_REG[TIM0_CLK_SEL]. The system or the LP clock can be selected by this option.

- 2. Select the clock division scaler by programming CLK_PER_REG[TMR_DIV]. Note that this setting only applies to the system clock.
- 3. Select the PWM mode by programming the TIMERO_CTRL_REG[PWM_MODE]. There are two modes supported. In the first one, the PWM signals are '1' during high time. In the second one, the PWM signals send out the (fast) clock divided by two during high time, so the clock frequency will be in the range of 1 to 8 MHz.
- 4. Enable Timer 0 clock by programming CLK_PER_REG[TMR_ENABLE].
- 5. Load the "high" value of the duty cycle in TIMER0_RELOAD_M_REG and the "low" value of the duty cycle in TIMER0_RELOAD_N_REG.
- 6. Set the desired GPIOs in PWM0/PWM1 and output mode.
- 7. Enable Timer 0 by programming TIMER0_CTRL_REG[TIM0_CTRL].

21. Timer 1

21.1 Introduction

Timer 1 is an 11-bit timer that can count up or down. It supports a free-running mode with an interrupt generated when zero is reached (also by wrapping around). It can be configured to use the system clock (sys_clk) or the LP clock (lp_clk) as the clock source. It supports capturing events on two GPIO channels when the number of clock cycles between these events is known. It can also generate an interrupt after a programmable number of clock cycles after an event. Figure 60 shows the block diagram of Timer 1.

Features

- 11-bit up/down counter with free running mode
- Selectable system or LP clock as source
- Two channels for capture input triggered by GPIOs
- Capture capability from two GPIO events with programmable polarity
- Programmable number of events between the two GPIOs for capturing
- Timer 1 or RTC snapshot on capture events
- Interrupt generation




Figure 60. Timer 1 block diagram

21.2 Architecture

Timer 1 is placed in the PD_TIM power domain which can be kept powered even when the system power domain (containing the CPU) is shut down.

The main operation of Timer 1 is to count up or down, generating an interrupt when it reaches the maximum/minimum value or the threshold that has been programed as the reload value.

Moreover, Timer 1 comes with a sense block that allows for sensing positive or negative edges on two GPIOs (configurable). The sense block operates in two modes:

- Counting mode: Timer1 will generate an interrupt upon a configurable amount of edges on a GPIO has been detected. The number of clock cycles was counted between timer start and captured the N events is stored to CAPCNTx_VALUE register. When timer detects the first N-events, automatically starts to detect the next N-events until timer is disabled
- Capture mode: Timer 1 saves a snapshot of either its own counter (11 bits) or the RTC port (22 bits) after an edge on a GPIO has been detected. If there is a pending interrupt, a new snapshot is not saved and the TIMER1_STATUS_REG[TIMER1_INx_OVRFLW] bit is set. This bit is cleared together with the TIMER1_STATUS_REG[TIMER1_Inx_EVENT] bit

The same GPIO can be used for both modes.

If Timer 1 is used in the counting mode, it can measure the frequency applied to a GPIO port (see Section 21.3.3).

21.3 Programming

When LP clock is selected as system clock, CLK AMBA REG[HCLK DIV] should be set to 0.

21.3.1 Timer Functionality

Timer 1 supports the functionality of a timer for generating interrupts after specific time intervals. To configure the timer functionality, follow the steps below:

1. Select the timer clock by programming TIMER1_CTRL_REG[TIMER1_USE_SYS_CLK]. The system or the LP clock can be selected by this option.

NOTE

If the LP clock is selected as system clock, the CLK_AMBA_REG[HCLK] bit field should always be 0 to ensure the proper operation of the timer.

- Enable or disable the free run mode by programming TIMER1_CTRL_REG[TIMER1_FREE_RUN_MODE_EN]. The free run mode can only be used when Timer 1 counts up.
- 3. Enable Timer 1 interrupt by programming TIMER1 CTRL REG[TIMER1 IRQ EN].
- 4. Set Timer 1 to count up or down by programming TIMER1 CTRL REG[TIMER1 COUNT DOWN EN].
- 5. Specify the reload value by programming TIMER1_CTRL_REG[TIMER1_RELOAD].
- 6. Enable the Timer 1 clock by programming TIMER1_CTRL_REG[TIMER1_CLK_EN].
- 7. Enable Timer 1 by programming TIMER1_CTRL_REG[TIMER1_ENABLE].

21.3.2 Capture Functionality

Timer 1 can capture a snapshot of the value of RTC or Timer1 counts after a GPIO edge is detected. To configure the capture functionality, follow the steps below:

- Depending on the source of the snapshot value, configure and enable RTC or Timer 1 or both in the capture mode.
- 2. Set the edge type (rising or falling edge) by programming TIMER1_CAPTURE_REG[TIMER1_IN1_EVENT_FALL_EN] or TIMER1_CAPTURE_REG[TIMER1_IN2_EVENT_FALL_EN], depending on the channel that is used.
- 3. Set the timer in capture mode by setting TIMER1_CAPTURE_REG[TIMER1_IN1_COUNT_EN]=0 or TIMER1_CAPTURE_REG[TIMER1_IN2_COUNT_EN]=0, depending on the channel that is used.
- 4. Enable capture interrupt by setting TIMER1_CAPTURE_REG[TIMER1_IN1_IRQ_EN] = 1 or TIMER1_CAPTURE_REG[TIMER1_IN2_IRQ_EN] = 1, depending on the channel that is used.
- Set the source of the snapshot value (RTC or Timer 1 count) by setting TIMER1_CAPTURE_REG[TIMER1_IN1_STAMP_TYPE] or TIMER1_CAPTURE_REG[TIMER1_IN2_STAMP_TYPE], depending on the channel that is used.
- Set the GPIO that will be used to trigger the capture by setting TIMER1_CAPTURE_REG[TIMER1_GPIO1_CONF] or TIMER1_CAPTURE_REG[TIMER1_GPIO1_CONF], depending on the channel that is used.
 Note that the values from 1 to 12 define the P0 pins from 0 to 11.
- 7. When an interrupt is generated, the capture value will be saved in TIMER1_CAPCNT1_VALUE_REG[TIMER1_CAPCNT1_VALUE] or TIMER1_CAPCNT2_VALUE_REG[TIMER1_CAPCNT2_VALUE], depending on the channel that is used.
- 8. Write 1 to TIMER1 CLR EVENT REGITIMER CLR Inx EVENT] to clear the event.

21.3.3 Frequency Measuring Functionality

Timer 1 can measure the frequency applied to a GPIO port. To configure the frequency measure functionality, follow the steps below:

- 1. Configure and enable Timer 1 in count up free mode using the system clock.
- 2. Set Timer 1 in count mode by setting TIMER1_CAPTURE_REG[TIMER1_IN1_COUNT_EN] = 1 or TIMER1 CAPTURE REG[TIMER1 IN2 COUNT EN] = 1, depending on the channel that is used.
- Enable capture interrupt by setting TIMER1_CAPTURE_REG[TIMER1_IN1_IRQ_EN] = 1 or TIMER1_CAPTURE_REG[TIMER1_IN2_IRQ_EN] = 1, depending on the channel that is used.
- 4. Set the rising edge by programming TIMER1_CAPTURE_REG[TIMER1_IN1_EVENT_FALL_EN] = 0 or TIMER1_CAPTURE_REG[TIMER1_IN2_EVENT_FALL_EN] = 0, depending on the channel that is used.
- Set the number of periods plus one, in which Timer 1 counts, by setting
 TIMER1_CAPTURE_REG[TIMER1_IN1_PERIOD_MAX] or
 TIMER1_CAPTURE_REG[TIMER1_IN2_PERIOD_MAX], depending on the channel that is used.
- 6. Set the GPIO that will be used to trigger the capture by setting TIMER1_CAPTURE_REG[TIMER1_GPIO1_CONF] or TIMER1_CAPTURE_REG[TIMER1_GPIO1_CONF], depending on the channel that is used.

 Note that the values from 1 to 12 define the P0 pins from 0 to 11.
- 7. After the interrupt is triggered, read the value in TIMER1_CAPCNT1_VALUE_REG[TIMER1_CAPCNT1_VALUE] or TIMER1_CAPCNT2_VALUE_REG[TIMER1_CAPCNT2_VALUE], depending on the channel that is used. This value indicates the number of cycles that has passed during the period defined in step 5.
- 8. To calculate the frequency applied to the GPIO, divide the number of periods (step 5) by the cycles (step 7) and multiply the result with the frequency of Timer 1 clock.
- 9. Write 1 to TIMER1_CLR_EVENT_REG[TIMER_CLR_Inx_EVENT] to clear the event.

22. Timer 2

22.1 Introduction

Timer 2 is basically a PWM generator. It has six PWM outputs. The block diagram is shown in Figure 61.




Figure 61. Timer 2 block diagram

Features

- 14-bit general purpose timer
- Ability to generate six PWM signals (PWM2, PWM3, PWM4, PWM5, PWM6, and PWM7,)
- Input clock frequency (f_{IN}) with N = 1, 2, 4, or 8 and sys_clk = 16 MHz or 32 kHz:

$$f_{IN} = \frac{sys_clk}{N}$$

■ Programmable output frequency (fout):

$$f_{OUT} = \left(\frac{f_{IN}}{2}\right) \text{ to } \left(\frac{f_{IN}}{2^{14} - 1}\right)$$

- Six outputs with a programmable duty cycle from 0 % to 100 %
- Used for white LED intensity (on/off) control or motor control

22.2 Architecture

Timer 2 is clocked with the system clock divided by TMR_DIV (1, 2, 4, or 8) and can be enabled with TRIPLE_PWM_CTRL_REG[TRIPLE_PWM_ENABLE].

TRIPLE_PWM_FREQUENCY determines the output frequency of the PWM outputs.

NOTE

There is a single frequency register for all six PWM outputs.

DUTY_CNTR is an up-counter counting from 0 up to TRIPLE_PWM_FREQUENCY.

If DUTY_CNTR is equal to the value stored in the respective PWMn_END_CYCLE register, it resets the PWMn output to 0.

If DUTY_CNTR is equal to the value stored in the respective PWMn_START_CYCLE register, it sets the PWMn output to 1.

Note that the value of PWMn_END_CYCLE and PWMn_START_CYCLE must be less than or equal to TRIPLE PWM FREQUENCY.

The Timer 2 is enabled/disabled by programming the TRIPLE_PWM_CTRL_REG[TRIPLE_PWM_EN] bit.

The timing diagram of Timer 2 is shown in Figure 62.

Freeze function

During RF activity it may be desirable to temporarily suppress the PWM switching noise. This can be done by setting TRIPLE_PWM_CTRL_REG[HW_PAUSE_EN] = 1. The effect is that whenever there is a transmission or a reception process from the Radio, DUTY_CNTR is frozen and PWMx output is switched to 0 to disable the selected PWMn. As soon as the Radio is idle, that is, RX_EN or TX_EN signals are zero, DUTY_CNTR resumes counting and finalizes the remaining part of the PWM duty cycle.

TRIPLE_PWM_CTRL_REG[SW_PAUSE_EN] can be set to 0 to disable the automatic, hardware driven freeze function of the duty counter and keep the duty cycle constant.

Note that the RX_EN and TX_EN signals are not software driven but controlled by the Bluetooth® LE core hardware.




Figure 62. Timer 2 timing diagram

22.3 Programming

When LP clock is selected as system clock, CLK_AMBA_REG[HCLK_DIV] should be set to 0.

When LP clock is selected as Timer clock, CLK_PER_REG[TMR_DIV] should be set to 0

22.3.1 PWM Generation

Timer 2 only supports PWM generation and does not support a normal, interrupt generating, timer functionality as the previous timers do. To configure the PWM generation functionality, follow the steps below:

- Select the clock source for Timer 2 by programming TRIPLE_PWM_CTRL_REG[TRIPLE_PWM_CLK_SEL].
 System clock or LP clock can be selected. Please note that if the (fast) system clock is selected, the division scaler is the same as the one for Timer 0.
- 2. Define the GPIOs to which the PWM signals are mapped by programming the respective PID number.
- 3. Define the frequency of Timer 2 that feeds the PWM waveforms by programming the TRIPLE_PWM_FREQUENCY with a value that conforms to the following equation. For example, if Timer 2 clock is 32000 Hz (lp_clk) and the required frequency for the PWM is 16 kHz, this register should be written with 0x1.

Timer2_clk_freq_Hz/Required_freq_Hz
$$-1$$
 (4)

NOTE

There is a single frequency register for all six PWM outputs.

- 4. Define the duty cycle of each PWM signal. Program the start and end cycle of the pulse at PWMx_START_CYCLE and PWMx_END_CYCLE, respectively. The available amount of cycles is depicted in the contents of TRIPLE_PWM_FREQUENCY register. For example, if the TRIPLE_PWM_FREQUENCY has a value of 0x8 and the START/END_CYCLE bit fields have a value of 3 and 5, respectively, the PWM signals will rise after three Timer 2 clock cycles and fall after five clock cycles. Every PWM signal has its own register to configure its duty cycle.
- 5. Enable the PWM signals by programming TRIPLE_PWM_CTRL_REG[TRIPLE_PWM_ENABLE] = 1.

22.3.2 Freeze Functionality

There is provision to allow hardware to pause PWM signals while RF is active. This can be done by programming TRIPLE_PWM_CTRL_REG[HW_PAUSE_EN] = 1. It can also be done via SW control by programming TRIPLE_PWM_CTRL_REG[SW_PAUSE_EN] = 1.

23. Watchdog Timer

23.1 Introduction

The Watchdog Timer is an 8-bit timer with a sign bit that can be used to detect an unexpected execution sequence caused by a software run-away and can generate a full system reset (WDOG reset) or a Non-Maskable Interrupt (NMI). Figure 63 shows the block diagram of the Watchdog Timer.

Features

- 8-bit down counter with a sign bit, clocked with a 10.24 ms clock for a maximum 2.6 s time-out
- Non-Maskable Interrupt (NMI) or WDOG reset
- Optional automatic WDOG reset if NMI handler fails to update the Watchdog register
- Non-maskable Watchdog freeze of the Cortex-M0+ Debug module when the Cortex-M0+ is halted in Debug state. Maskable Watchdog freeze by user program




Figure 63. Watchdog timer block diagram

23.2 Architecture

The 8-bit watchdog timer is decremented by 1 every 10.24 ms. The timer value can be accessed through the WATCHDOG_REG register which is set to 255 (FF₁₆) at reset. This results in a maximum watchdog time-out of \sim 2.6 s. During write access, the WATCHDOG_REG[WDOG_WEN] bit must be 0. This provides extra filtering for a software run-away by writing ones to all the bits in the WATCHDOG_REG. If the watchdog timer reaches 0, its value will get a negative value by setting bit 8. The counter sequence becomes 1, 0, 1FF₁₆ (-1), 1FE₁₆(-2), till 1F0₁₆ (-16).

If WATCHDOG_CTRL_REG[NMI_RST] = 0, the watchdog timer will generate an NMI when it reaches 0 and a WDOG reset when it becomes less or equal to -16 (1F0 $_{16}$). The NMI handler must write a value that is larger than -16 to the WATCHDOG_REG to prevent the generation of a WDOG reset when the watchdog timer reaches the value -16 after 16 × 10.24 = 163.8 ms.

If WATCHDOG_CTRL_REG[NMI_RST] = 1, the watchdog timer generates a WDOG reset when it becomes less than or equal to 0.

The WDOG reset is one of the system (SYS) reset sources and resets almost the whole device, including resetting the WATCHDOG_REG register to 255. See Section 6.2.1 for an overview of the complete reset circuit and conditions.

For debugging purposes, the Cortex-M0+ Debug module can always freeze the watchdog by setting the DHCSR[DBGKEY | C_HALT | C_DEBUGEN] control bits (reflected by the status bit S_HALT, see Table 42). This is automatically done by the debugging tool, for example, during step-by-step debugging. Note that this bit also freezes the Wake-up Timer, the Software Timer, and the BLE master clock. For additional information see

the DEBUG_REG[DEBUGS_FREEZE_EN] mask register. The C_DEBUGEN bit cannot be accessed by the user software so that freezing the watchdog is prevented.

In addition to the S_HALT bit, the watchdog timer can also be frozen if NMI_RST = 0 and SET_FREEZE_REG[FRZ_WDOG] is set to 1. The watchdog timer resumes counting when RESET_FREEZE_REG[FRZ_WDOG] is set to 1. The WATCHDOG_CTRL_REG[NMI_RST] bit can only be set by software and will only be reset on a SYS reset. Note that if the system is not remapped, that is, the SysRAM is at address 0x07FC0000, a watchdog fire will trigger the BootROM code to be executed again.

23.3 Programming

To program the Watchdog Timer, follow the simple sequence of steps below:

- 1. Freeze watchdog by setting the SET_FREEZE_REG[FRZ_WDOG] bit (optional).
- 2. Select NMI and reset events (WATCHDOG CTRL REG[NMI RST]).
- 3. Enable writing of the watchdog timer (WATCHDOG_REG[WDOG_WEN] = 0]).
- 4. Write the reload value of the watchdog timer (WATCHDOG_REG[WDOG_VAL], see the register description).
- 5. Resume watchdog (RESET_FREEZE_REG[FRZ _WDOG] = 1), if frozen.

24. Temperature Sensor

24.1 Introduction

The DA14531 features a built-in temperature sensor.

Features

- Temperature range -40 °C to 105 °C
- Absolute accuracy after one-point calibration +/- 4 °C (assuming 25 °C reference temperature)
- 25°C single point calibration reference value provided in OTP memory

24.2 Architecture

The temperature sensor can be read out via the GP_ADC.

Figure 64 illustrates the relationship between the actual ambient temperature and the calculated temperature from the GP_ADC readout, including possible inaccuracies in T_{SENSE_ACC_OTP} (offset) and TC_{SENSE} (angle).




Figure 64. Temperature sensor behavior

The recommended formula for single point calibrated temperature reading is as follows:

$$T_x = 25 + (ADC_x - ADC_{OTP_CAL_25C})/(TC_{SENSE} \times 64)$$

Where:

- T_x = calculated single point calibrated die temperature in [°C]
- ADC_x = 16-bit GP ADC VAL readout (converted to decimal) at temperature T_x
- ADC_{OTP_CAL_25C} = 25 °C OTP calibration value recorded during production testing (based on the 16-bit readout)
- TC_{SENSE} = temperature coefficient in [LSB/°C], typical value is 1.45 LSB/°C
- 25 = reference base value in [°C]
- 64 = correction for 16-bit to 10-bit ADC values

For uncalibrated temperature sensor measurements, ADC_{OTP_CAL25C} can be replaced by the default value using the formula below:

$$T_x = 25 + (ADC_x - 30272)/(TC_{SENSE} \times 64)$$

Note that this is not recommended since it can result in large offsets.

NOTE

While measuring and/or calibration, the system's power dissipation should be kept the same, otherwise, the measurement is affected by the internal thermal gradient.

24.2.1 Programming

There is a certain programming sequence required to read the temperature sensor. There are two reading options available:

- absolute temperature (single-point calibration)
- relative temperature

24.2.1.1 Absolute Temperature

A calibration value at 25 °C is stored in OTP for absolute temperature measurements. When the calibration value from OTP is used, the default GP ADC offset calibration settings should be used.

- To enable OTP in normal read mode:
 - CLK_AMBA_REG[OTP_ENABLE] = 1
 - OTPC MODE REG[OTPC MODE MODE] = 2
- To read the calibration value at 25°C:
 - Read ADC_{OTP CAL 25C}: the content of ADC_{OTP CAL 25C} is at the address 0x7F87F28 of the OTP
- To disable OTP:
 - OTPC MODE REG[OTPC MODE MODE] = 0
 - CLK_AMBA_REG[OTP_ENABLE] = 0
- To read back the offset calibration:
 - Offp = GP ADC OFFP REG[GP ADC OFFP]
 - Offn = GP_ADC_OFFN_REG[GP_ADC_OFFN]

(Store the data if the original values are needed later for the application)

- To overwrite the defaults (the settings during factory calibration) with the ADC offset values
 - GP ADC OFFP REGIGP ADC OFFP1 = 200
 - GP_ADC_OFFN_REG[GP_ADC_OFFN] = 200
- To enable the temperature sensor:
 - GP ADC CTRL REG[DIE TEMP EN] = 1
- Wait 25 µs for the temperature sensor to start up
- To set the advised ADC settings:
 - GP_ADC_TRIM_REG[GP_ADC_LDO_LEVEL] = 4

- GP ADC CTRL REG[GP ADC CHOP] = 1
- GP_ADC_CTRL_REG[GP_ADC_SE] = 1
- GP_ADC_CTRL_REG[GP_ADC_EN] = 1
- GP_ADC_CTRL2_REG[GP_ADC_I20U] = 1
- GP ADC SEL REG[GP ADC SEL P] = 4
- GP_ADC_CTRL2_REG[GP_ADC_STORE_DEL] = 0
- To set sample time and averaging of the ADC sampling
 - GP_ADC_CTRL2_REG[GP_ADC_SMPL_TIME] = F
 - GP_ADC_CTRL2_REG[GP_ADC_CONV_NRS] = 6
- To perform ADC conversion:
 - GP_ADC_CTRL_REG[GP_ADC_START] = 1
- To wait for the conversion to finish, read the register
 - GP_ADC_RESULT_REG[GP_ADC_VAL]
- To write back the original offset values
 - GP ADC OFFP REG[GP ADC OFFP] = Offp
 - GP ADC OFFN REG[GP ADC OFFN] = Offn

(Restore the original data if needed by the application)

24.2.1.2 Relative Temperature

For relative temperature measurements, the single-point calibration is not needed. The programming sequence is presented below.

- To enable GP_ADC:
 - GP ADC CTRL REG[DIE TEMP EN] = 1
- Wait 25 µs for the temperature sensor to start up
- To set the advised ADC settings:
 - GP_ADC_TRIM_REG[GP_ADC_LDO_LEVEL] = 4
 - GP_ADC_CTRL_REG[GP_ADC_CHOP] = 1
 - GP ADC CTRL REG[GP ADC SE] = 1
 - GP_ADC_CTRL_REG[GP_ADC_EN] = 1
 - GP_ADC_CTRL2_REG[GP_ADC_I20U] = 1
 - GP ADC SEL REG[GP ADC SEL P] = 4
 - GP_ADC_CTRL2_REG[GP_ADC_STORE_DEL] = 0
- To set sample time and averaging of the ADC sampling
 - GP_ADC_CTRL2_REG[GP_ADC_SMPL_TIME] = F
 - GP ADC CTRL2 REG[GP ADC CONV NRS] = 6
- To perform ADC conversion:
 - GP_ADC_CTRL_REG[GP_ADC_START] = 1
- To wait for the conversion to finish, read the register
 - GP_ADC_RESULT_REG[GP_ADC_VAL]

25. Keyboard Controller

25.1 Introduction

The Keyboard controller can be used for debouncing the incoming GPIO signals when implementing a keyboard scanning engine. It generates an interrupt to the CPU (KEYBR IRQ).

In parallel, five extra interrupt lines can be triggered by a state change on up to 12 selectable GPIOs (GPIO_IRQx).

Features

- Monitors the 12 available GPIOs (6 in the WLCSP17 package and 12 in the FCGQFN24 package)
- Generates a keyboard interrupt on key press or key release
- Implements debouncing time from 0 up to 63 ms.
- Supports five separate interrupt generation lines from GPIO toggling

The block diagram of the Keyboard Controller is presented in the Figure 65.




Figure 65. Keyboard controller block diagram

25.2 Architecture

25.2.1 Keyboard Scanner

A HIGH-to-LOW transition on one of the GPIO inputs sets the internal signal "key_hit" to 1, while KBRD_IRQ_IN_SEL0_REG[KBRD_LEVEL] = 0 and KBRD_IRQ_IN_SELx_REG[KBRD_Pyy_EN] = 1. This signal triggers the state machine of the keyboard interface shown in Figure 66. The debounce timer is loaded with the value of GPIO_DEBOUNCE_REG[DEB_VALUE]. The timer counts down every 1 ms. When the timer reaches 0 and the "key_hit" signal is still 1, the timer is loaded with the value of KBRD_IRQ_IN_SEL0_REG[KEY_REPEAT], generating a repeating sequence of interrupts every time when the timer reaches 0.

When the key is released (key_hit = 0) and the bit KBRD_REL (key release) is set to 1, a new debounce sequence is started and a KEYBR IRQ interrupt is generated after the debounce time.

The debounce timer can be disabled with GPIO_DEBOUNCE_REG[DEB_ENABLE_KBRD] = 0. The key repeat function can be disabled by setting KEY_REPEAT to 0.

The level for generating an interrupt is programmable via bit KBRD_IRQ_IN_SEL0_REG[KBRD_LEVEL]. The key release function can be disabled by setting bit KBRD_IRQ_IN_SEL0_REG[KBRD_REL] to 0. The inputs for

the keyboard interface can be selected by setting the corresponding bits KBRD_IRQ_IN_SEL0_REG[KBRD_Pxx_EN] to 1.

The keyboard interrupt service routine can distinguish which input has caused the interrupt by reading the Px DATA REG registers.




Figure 66. Keyboard scanner state machine

25.2.2 GPIO Interrupt Generator

Five identical GPIO interrupt generators support the generation of up to five interrupts (GPIO0_IRQ to GPIO4_IRQ). One of the GPIO inputs can be selected to generate an interrupt by programming the corresponding GPIO_IRQx_IN_SEL_REG register. The input level can be selected by GPIO_INT_LEVEL_CTRL_REG[INPUT_LEVELx].

A LOW-to-HIGH level transition on one of the GPIO inputs sets the internal signal "key_hit" to 1, while the bit INPUT_LEVELx = 0. This signal triggers the state machine of the GPIO Interrupt Generator shown in Figure 67. The debounce timer is loaded with the value of GPIO_DEBOUNCE_REG[DEB_VALUE]. The timer counts down every 1 ms. If the timer reaches 0 and the "key_hit" signal is still 1, an interrupt will be generated. The debounce timer for each interrupt can be disabled with GPIO_DEBOUNCE_REG[DEB_ENABLEx].

The interrupt flag remains set until it is reset by writing to the corresponding bit in the GPIO_RESET_IRQ_REG register. If the GPIO interrupt is edge sensitive selected with bit GPIO_INT_LEVEL_CTRL_REG[EDGE_LEVELNx], the state machine will progress to the state WAIT_FOR_RELEASE when the interrupt is reset. It will progress to the IDLE state only after the non-active edge is detected.

To detect both signal edges, the edge polarity INPUT_LEVELx must be inverted in the WAIT_FOR_RELEASE state. This will result in "key_hit" = 0 and will advance the state machine to the IDLE state, allowing the next inverted edge to be detected.




Figure 67. GPIO interrupt generator state machine

25.3 Programming

To configure and use the Keyboard controller, follow the steps under each subsection.

25.3.1 Keyboard Scanner

- 1. Enable a keyboard interrupt for the P0_x by setting the KBRD_IRQ_IN_SEL0_REG[KBRD_Px_EN] bit.
- 2. Select the logic level by which the interrupt is generated (KBRD_CTRL_REG[KBRD_LEVEL]).
- 3. Select whether a key release also generates an interrupt (KBRD_CTRL_REG[KBRD_REL]).
- Select whether repeated interrupts will be generated when a key is held pressed (KBRD_CTRL_REG[KEY_REPEAT]).
- 5. Set up the debounce time for each key stroke (GPIO_DEBOUNCE_REG[DEB_VALUE]).
- 6. Enable the debounce timer (GPIO_DEBOUNCE_REG[DEB_ENABLE_KBRD]).

25.3.2 GPIO Interrupts

- 1. Enable a GPIO interrupt for the P0 x by setting the GPIO IRQx IN SEL REG[KBRD IRQ0 SEL] bit.
- 2. Select the logic level by which the interrupt is generated (GPIO_INT_LEVEL_CTRL_REG[INPUT_LEVELx]).
- Select whether a key release is needed for an interrupt to be generated after a generated IRQ is cleared (GPIO_INT_LEVEL_CTRL_REG[EDGE_LEVELNx]).
- 4. Set up the debounce time for GPIO trigger (GPIO DEBOUNCE REG[DEB VALUE]).
- 5. Enable the debounce timer for the selected IRQ (GPIO_DEBOUNCE_REG[DEB_ENABLEx]).

26. Input/Output Ports

26.1 Introduction

The DA14531 has an I/O pin assignment that can be configured by the SW and is organized into the Port 0. Pins from P0_0 to P0_5 are available for input/output on the WLCSP17 package, whereas the full Port 0 (P0_0 to P0_11) is available on the FCGQFN24 package. Figure 68 shows the block diagram of the IO and its programmability options.

Features

- Six GPIOs on WLCSP17 and 12 GPIOs on FCGQFN24 (including RST, SW_CLK, SWDIO, XTAL32Km, and XTAL32Kp)
- Fully programmable pin assignment
- Selectable 25 kΩ pull-up and pull-down resistors per pin
- Programmable driving strength outputs
- Fixed assignment for analog pin ADC[3:0]
- Pins can retain their last state when system enters a Sleep mode




Figure 68. Port P0 with programmable pin assignment and driving strength

26.2 Architecture

26.2.1 Programmable Pin Assignment

The Programmable Pin Assignment (PPA) provides a multiplexing function to the I/O pins of on-chip peripherals. Any peripheral input or output signal can be freely mapped to any I/O port bit by setting Pxy_MODE_REG[4-0]:

```
0x00 to 0x1F: Peripheral IO ID (PID)
```

Refer to the registers of Px_MODE_REG (x = 00, 01, 02, to 11) for an overview of the available PIDs. The analog ADC has a fixed pin assignment so that the interference with the digital domain is limited. The SWD interface (JTAG) is mapped on $P0_5$ (or $P0_1$ or $P0_10$, see Section 3) for the SWDIO and on $P0_2$ for the SWCLK.

26.2.1.1 Priority

The firmware can assign the same peripheral output to more than one pin. It is the users' responsibility to make a unique assignment.

If more than one input signal is assigned to a peripheral input, the left most pin in the lowest port pin number has priority.

26.2.1.2 Direction Control

The port direction is controlled by setting Pxy_MODE_REG[9-8] to:

- 00 = Input, no resistors selected
- 01 = Input, pull-up resistors selected
- 10 = Input, pull-down resistors selected
- 11 = Output, no resistors selected

In output mode and analog mode, the pull-up/down resistors are automatically disabled.

26.2.2 General Purpose Port Registers

The general-purpose ports are selected with PID = 0. The port function is accessible through registers:

- Px DATA REG: Port data input/output register
- Px_SET_OUTPUT_DATA_REG: Port set output register
- Px_RESET_OUTPUT_DATA_REG: Port reset output register

26.2.2.1 Port Data Register

The registers input Px DATA REG and output Px DATA REG are mapped on the same address.

The data input register (Px_DATA_REG) is a read-only register that returns the current state on each port pin, even if the output direction is selected, regardless of the programmed PID, unless the analog function is selected (in this case it reads 0). The Cortex CPU can read this register at any time, even when the pin is configured as an output.

The data output register (Px_DATA_REG) holds the data to be driven on the output port pins. In this configuration, writing to this register changes the output value.

26.2.2.2 Port Set Data Output Register

Writing a 1 in the set data output register (Px_SET_DATA_REG) sets the corresponding output pin. Writing a 0 is ignored.

26.2.2.3 Port Reset Data Output Register

Writing a 1 in the reset data output register (Px_RESET_DATA_REG) resets the corresponding output pin. Writing a 0 is ignored.

26.2.3 Fixed Assignment Functionality

Certain signals have a fixed mapping on specific general purpose IOs. This assignment is illustrated in Table 51.

Table 51: Fixed Assignment of Specific Signals

GPIO	Reset/SWD (Note 1)	QUADRATURE DECODER (Note 2)	ADC (Note 3)
P0_0	RST	CH6_A	
P0_1	SWDIO (alternative)	CH1_A	ADC_0
P0_2	SWCLK	CH1_B	ADC_1
P0_3		CH2_A	
P0_4		CH2_B	
P0_5	SWDIO	CH3_A	
P0_6		CH3_B	ADC_2
P0_7		CH4_A	ADC_3
P0_8		CH6_B	
P0_9		CH5_A	

GPIO	Reset/SWD (Note 1)	QUADRATURE DECODER (Note 2)	ADC (Note 3)
P0_10	SWDIO (alternative)	CH5_B	
P0_11		CH4_B	

- Note 1 The SWD signal mapping is defined by SYS_CTRL_REG[DEBUGGER_ENABLE]. However, these signals are mapped on the ports by default. The alternative SWD mapping is selected by the SYS_CTRL_REG[DEBUGGER_ENABLE] bit field. The RST default functionality can be disable by the HWR_CTRL_REG[DISABLE_HWR] bit.
- Note 2 The mapping of the quadrature decoder signals on the respective pins is overruled by the QDEC CTRL2 REG[CHx PORT SEL] register.
- Note 3 The ADC function can be selected by the PID bit field on the respective Px port.

26.2.4 Types of GPIO Pads

There are two different types for the GPIO pads, namely, type A and type B. Their block diagrams are presented in Figure 69 and Figure 70.




Figure 69. Type A GPIO pad - GPIO with Schmitt trigger on input




Figure 70. Type B GPIO pad - GPIO with Schmitt trigger and RC Filter on Input

Red signals are latched when the system enters a Sleep mode.

26.2.5 Driving Strength

Pads can be configured regarding their driving capability using PAD_WEAK_CTRL_REG. There are only 2 levels available for the load that the pad can support, namely normal = 3.5 mA typical, and reduced = 0.35 mA typical.

27. General Purpose ADC

27.1 Introduction

The DA14531 is equipped with a high-speed ultra-low-power 10-bit general purpose Analog-to-Digital Converter (GPADC). It can operate in unipolar (single ended) mode as well as in bipolar (differential) mode. The ADC has its own voltage regulator (LDO) of 0.9 V, which represents the full-scale reference voltage. Figure 71 shows the block diagram of the GPADC.

Features

- 10-bit dynamic ADC with 125 ns typical conversion time
- Maximum sampling rate 1 Msample/s
- 128× averaging; conversion time 1 ms, up to 11b ENOB
- Ultra-low power (20 µA typical supply current at 100 ksample/s)
- Four single-ended or two differential external input channels (GPIOs)
- Battery, DCDC outputs, and the internal V_{DD} monitoring channels
- Chopper function
- Offset adjust
- Common-mode input level adjust
- Configurable attenuator: 1×, 2×, 3× and 4×
- Input shifter




Figure 71. Block diagram of GPADC

27.2 Architecture

The ADC architecture shown in Figure 71 has the following sub-blocks:

Analog to Digital converter (ADC)

- ADC analog part internally clocked with 100 MHz
- o ADC logic part clocked with the ADC CLK which is the 16 MHz system clock (sys clk)
- 0.9 V LDO for the ADC supply with a high PSRR enabled with GP_ADC_CTRL_REG[GP_ADC_EN]
- Configurable attenuator with 1×, 2×, 3×, and 4× attenuation controlled by GP_ADC_CTRL2_REG[GP_ADC_ATTN]
- Input shifter which shifts the battery voltage range from 0.85 V to 1.75 V (with a common mode adjustment) to the ADC input range from 0 V to 0.9 V controlled by GP_ADC_CTRL2_REG[GP_ADC_OFFS_SH_EN] and GP_ADC_CTRL2_REG[GP_ADC_OFFS_CM]
- APB Bus interface clocked with the APB clock. Control and status registers are available through registers GP_ADC_*
- Maskable Interrupt (ADC IRQ) and DMA request (ADC DMA REQ)
- ADC input channel selector. Up to four GPIO ports, the battery and DCDC output (V_{BAT_HIGH} and V_{BAT_LOW}), the internal V_{DD}, and the analog ground level (AVS) can be measured.

27.3 Input Channels

Table 52 summarizes the ADC input channels. The GPIO signals at the channels [3:0] can be monitored both single-ended and differentially. The signals at the 4-7 inputs can be monitored single-ended or differentially with respect to the GPIOs.

Table 52: ADC Input Channels

Channel	Signal	Description
3:0	GPIO [P0_1, P0_,2, P0_6, P0_7]	General Purpose Inputs
4	Temperature Sensor	Temperature Sensor
5	V _{BAT_} HIGH	V _{BAT_HIGH} rail
6	V _{BAT_LOW}	V _{BAT_LOW} rail
7	V _{DD}	V _{DD} rail for the digital power domain

Table 53 summarizes the voltage ranges which can be handled with the single-ended or differential operation for different attenuation values. The single-ended/differential mode is controlled by the bit GP_ADC_CTRL_REG[GP_ADC_SE], and the attenuation is handled by the bit GP_ADC_CTRL2_REG[GP_ADC_ATTN].

Table 53: GPADC External Input Channels and Voltage Range

GP_ADC_ATTN	GP_ADC_SE	Input scale	Input limits
0 (4 x)	0	-0.9 V to +0.9 V	-1 V to +1 V
0 (1 ×)	1	0 V to +0.9 V	-0.1 V to 1V
4 (0)	0	-1.8 V to +1.8 V	-1.9 V to +1.9 V
1 (2 ×)	1	0 V to +1.8 V	-0.1 V to 1.9 V
0 (0)	0	-2.7 V to +2.7 V	-2.8 V to +2.8 V
2 (3 ×)	1	0 V to +2.7 V	-0.1 V to 2.8 V
2 (4)	0	-3.6 V to +3.6 V	-3.45 V to +3.45 V
3 (4 ×)	1	0 V to +3.6 V	-0.1 V to 3.45 V

27.3.1 Operating Modes

The GPADC operation flow diagram is shown in Figure 72.




Figure 72. GPADC operation flow diagram

27.3.1.1 Enabling the ADC

Enabling/disabling of the ADC is triggered by configuring bit GP_ADC_CTRL_REG[GP_ADC_EN]. When the bit is set to 1, first the LDO is enabled. Then after the delay value set in

GP_ADC_CTRL3_REG[GP_ADC_EN_DEL] (typically 16 μs to account for the LDO settling time), the ADC will be enabled, and an AD conversion can be started. See Table 54 for recommended values.

Table 54: ADC_LDO Start-Up Delay

f _{ADC_CLK}	GP_ADC_EN_DEL	TADC_EN_DEL	
16 MHz	0x40	16 µs	

Formula:

This value must be rounded up to the nearest integer.

The GPADC is a dynamic ADC and consumes no static power, except for the **ADC_LDO** which consumes approximately 20 µA. Therefore, GP_ADC_EN must be set to 0 if the ADC is not used.

27.3.1.2 Manual Mode

An AD conversion can be started by setting GP_ADC_START to 1. While a conversion is active, GP_ADC_START remains 1. When a conversion is finished, the hardware sets GP_ADC_START to 0 and GP_ADC_INT to 1 (interrupt), and GP_ADC_RESULT_REG contains the valid ADC value. While a conversion is active, writing 1 to GP_ADC_START will not start a new conversion. SW should always check that bit GP_ADC_START = 0 before starting a new conversion.

27.3.1.3 Continuous Mode

Setting GP_ADC_CTRL_REG[GP_ADC_CONT] to 1 enables the continuous mode, which automatically starts a new AD conversion when the current conversion has been completed. The GP_ADC_START bit is only needed once to trigger the first conversion. As long as the continuous mode is active, GP_ADC_RESULT_REG always contains the latest ADC value.

To correctly terminate the continuous mode, it is required to disable the GP_ADC_CONT bit first and then wait until the GP_ADC_START bit is cleared to 0, so the ADC is in a defined state.

NOTE

Before making any changes to the ADC settings, users must disable the continuous mode by setting bit GP_ADC_CONT to 0 and waiting until bit GP_ADC_START = 0.

At full speed the ADC consumes approximately 50 to 60 μ A. If the data rate is less than 100 ksample/s, the current consumption will be in the order of 25 μ A.

The time interval between two successive AD conversions is programmable with GP_ADC_CTRL3_REG[GP_ADC_INTERVAL] in steps of 1.024 ms. If GP_ADC_INTERVAL = 0, the conversion will restart immediately. If GP_ADC_INTERVAL is not zero, the ADC first synchronizes to the delay clock before starting the conversion. This can take up to 1 ms.

27.3.2 Conversion Modes

27.3.2.1 AD Conversion

Each AD conversion has three phases:

- Sampling
- Conversion
- Storage

The AD conversion starts with the sampling phase. This phase ends after the time set in GP_ADC_CTRL2_REG[GP_ADC_SMPL_TIME] and triggers the conversion phase. If GP_ADC_CTRL2_REG[GP_ADC_STORE_DEL] = 0, handshaking is used, that is, the ADC result is stored when a conversion is finished. Otherwise, a fixed (programmable) delay is used, and the result is stored regardless of whether the conversion is finished or not.

The total conversion time of an AD conversion depends on various settings. In short, it is as follows.

$$T_{ADC} = \frac{N_{CONV} \cdot \left(N_{CYCL_SMPL} + N_{CYLC_STORE}\right)}{f_{ADC_CLK}} \tag{5}$$

Where

July 10, 2025

- N_{CONV} = the number of conversions. This is related to the value programmed in GP_ADC_CTRL2_REG[GP_ADC_CONV_NRS], following 2^{GP_ADC_CONV_NRS}. When GP_ADC_CTRL_REG[GP_ADC_CHOP] is set, the minimum value for N_{CONV} is always 2.
- N_{CYLC_SMPL} = the number of ADC_CLK cycles used for sampling, which is 8 × GP_ADC_CTRL2_REG[GP_ADC_SMPL_TIME].
- NCYCL_STORE = the number of ADC_CLK cycles until the result is stored. When GP_ADC_CTRL2_REG[GP_ADC_STORE_DEL] = 0, handshaking is used. With handshaking, the number of ADC_CLK cycles is typically three. This value may spread from sample to sample and over temperature, otherwise the number of ADC_CLK cycles is GP_ADC_CTRL2_REG[GP_ADC_STORE_DEL] + 1.

27.3.2.1.1 Sampling Phase

The sampling time can be programmed via GP_ADC_CTRL2_REG[GP_ADC_SMPL_TIME] and depends on the sampling time constant in combination with the desired sampling accuracy. This sampling time constant, T_{ADC_SMPL} (Table 55), then depends on the output impedance of the source, the internal resistive dividers, and the internal sampling capacitor. And the number of required time constants is given by the natural logarithm of the desired accuracy, that is, $I_{C}N_{BIT}$. For N_{BIT} = 10-bit accuracy, 7-time constants are required.

Table 55: ADC Sampling Time Constant (TADC_SMPL)

ADC Input	TADC_SMPL
GPADC0, GPADC1 (GP ADC ATTN = 0)	R _{OUT} × 0.5 pF (Differential Input)
GI ABOU, GI ABOT (GI _ABO_ATTIV = 0)	R _{OUT} × 1 pF (Single-Ended Input)
GPADC0, GPADC1 (GP ADC ATTN = 1)	(R _{OUT} + 120 kΩ) × 0.5 pF (Differential Input)
GFADCO, GFADCT (GF_ADC_ATTN = 1)	$(R_{OUT} + 120 \text{ k}\Omega) \times 1 \text{ pF (Single-Ended Input)}$

Formula:

GP ADC SMPL TIME = In(2^NBIT) × TADC SMPL × fADC CLK / 8

This value must be rounded up to the nearest integer.

27.3.2.1.2 Conversion and Storage Phase

One AD conversion typically takes around 125 ns with a 100 MHz clock. The result can be stored either by handshaking or after a fixed number of cycles (programmable).

Handshake mode (GP_ADC_STORE_DEL = 0):

In handshake mode the conversion result is available in GP_ADC_RESULT_REG after two sampling ADC_CLK cycles plus two conversion ADC_CLK cycles plus two ADC_CLK cycles for synchronization.

Fixed delay mode (GP ADC STORE DEL > 0):

In fixed delay mode the conversion result is available in GP_ADC_RESULT_REG after the programmed storage delay, regardless of whether the conversion is ready or not. Note that when the delay is too short (that is, the conversion is not finished in the allocated time), the old (previous) ADC result is stored.

27.3.2.2 Averaging

In order to reduce noise and improve performance, multiple samples can be averaged out (assuming the time average of noise equals zero). This is handled by HW and can be controlled by setting GP_ADC_CTRL2_REG[GP_ADC_CONV_NRS] to a non-zero value. The actual number of the consecutive samples taken is by 2^{GP_ADC_CONV_NRS}.

Because the internal noise also acts as a form of dither, the actual accuracy can be improved. Therefore, the ADC result is not truncated to 10-bit but stored as 16-bit left aligned, and truncation is left for the user. The expected Effective Number of Bits (ENOB) is shown in Table 56.

Table 56: ENOB in Oversampling Mode

GP_ADC_CONV_NRS	ENOB (Left Aligned) in GP_ADC_RESULT_REG
0	> 9
1	> 9
2	> 9

GP_ADC_CONV_NRS	ENOB (Left Aligned) in GP_ADC_RESULT_REG
3	> 10
4	> 10
5	> 10
6	> 11
7	> 11

27.3.2.3 Chopper Mode

Inherently, the ADC has a DC offset (E_{OFS}). When GP_ADC_CTRL_REG[GP_ADC_CHOP] is set to 1, the hardware triggers two consecutive AD conversions and flips the sign of the offset in-between. Summing the two samples effectively cancels out the inherent ADC offset. This method also smooths other non-ideal effects and is recommended for DC and the slowly changing signals.

When combined with averaging, every other AD conversion is taken with opposite sign. Without averaging two AD conversions are always triggered.

Note that a DC offset causes saturation effects at zero scale or full scale. When chopping is used without offset calibration, non-linear behavior is introduced towards zero scale and full scale.

27.3.3 Additional Settings

The hardware also supports pre-ADC attenuation via GP_ADC_CTRL2_REG[GP_ADC_ATTN]:

- Setting 0 disables the attenuator
- Setting 1 scales the input range by a factor of two
- Setting 2 scales the input range by a factor of three
- Setting 3 scales the input range by a factor of four

With bit $GP_ADC_CTRL_REG[GP_ADC_MUTE] = 1$, the input is connected to $0.5 \times ADC$ reference. So, the ideal ADC result should be 511.5. Any deviation from this is the ADC offset.

With bit GP_ADC_CTRL_REG[GP_ADC_SIGN] = 1, the sign of the offset is inverted. When chopper is used, the hardware alternates GP_ADC_SIGN = 0 and 1. This bit is typically only used for the offset calibration routine described in Section 27.3.5 and has no specific use to the end user.

27.3.4 Non-Ideal Effects

Besides Differential Non-Linearity (DNL) and Integral Non-Linearity (INL), each ADC has a gain error (linear) and an offset error (linear). The gain error (E_G) of the GPADC affects the effective input range. The offset error (E_{OFS}) causes the effective input scale to become non-centered. The offset error can be reduced by chopping and/or by offset calibration.

The ADC result will also include some noise. If the input signal itself is noise free (inductive effects included), the average noise level will be ±1 LSB. Reducing noise effects can be done by taking more samples and calculating the average value. This can be done by programming GP_ADC_CTRL2_REG[GP_ADC_CONV_NRS] to a non-zero value.

With a "perfect" input signal (for example, if a filter capacitor is placed close to the input pin), most of the noise comes from the low-power voltage regulator (LDO) of the ADC. Since the DA14531 is targeted for ultra-compact applications, there is no pin available to add a capacitor at this voltage regulator output.

The dynamic current of the ADC causes extra noise at the regulator output. This noise can be reduced by setting bits $GP_ADC_CTRL2_REG[GP_ADC_I20U]$. Bit GP_ADC_I20U enables a constant 20 μ A load current at the regulator output so that the current will not drop to zero. This, obviously, increases power consumption by 20 μ A.

27.3.5 Offset Calibration

A relative high offset error (E_{OFS} , up to 30 mV, so approximately 30 LSB) is caused by a very small dynamic comparator. This offset error can be cancelled with the chopping function, but it still causes unwanted saturation effects at zero scale or full scale. With GP_ADC_OFFP_REG and GP_ADC_OFFN_REG, the offset error can be compensated in the ADC network itself. To calibrate the ADC, follow the steps in Table 57. In this routine, 0x200 is the target mid-scale of the ADC.

Table 57: GPADC Calibration Procedure for Single-Ended and Differential Modes

Step	Single-Ended Mode (GP_ADC_SE = 1)	Differential Mode (GP_ADC_SE = 0)	
1	Set GP_ADC_OFFP = GP_ADC_OFFN = 0x200; GP_ADC_MUTE = 0x1; GP_ADC_SIGN = 0x0.	Set GP_ADC_OFFP = GP_ADC_OFFN = 0x200; GP_ADC_MUTE = 0x1; GP_ADC_SIGN = 0x0.	
2	Start conversion.	Start conversion.	
3	adc_off_p = GP_ADC_RESULT - 0x200	adc_off_p = GP_ADC_RESULT - 0x200	
4	Set GP_ADC_SIGN = 0x1.	Set GP_ADC_SIGN = 0x1.	
5	Start conversion.	Start conversion.	
6	adc_off_n = GP_ADC_RESULT - 0x200	adc_off_n = GP_ADC_RESULT - 0x200	
7	GP_ADC_OFFP = 0x200 - 2 × adc_off_p	GP_ADC_OFFP = 0x200 - adc_off_p	
	GP_ADC_OFFN = 0x200 - 2 × adc_off_n	GP_ADC_OFFN = 0x200 - adc_off_n	

To increase the accuracy, it is recommended to set the GP_ADC_CTRL2_REG[GP_ADC_SMPL_TIME] = 2 or 3 and GP_ADC_CTRL2_REG[GP_ADC_CONV_NRS] = 3 or 4 prior to this routine.

It is recommended to implement the above calibration routine during the initialization phase of DA14531. To verify the calibration results, check whether the GP_ADC_RESULT value is close to 0x200 while bit GP_ADC_CTRL_REG[GP_ADC_MUTE] = 1.

27.3.6 Zero-Scale Adjustment

The GP_ADC_OFFP and GP_ADC_OFFN registers can also be used to set the zero-scale or full-scale input level at a certain target value. For instance, they can be used to calibrate GP_ADC_RESULT to 0x000 at an input voltage of exactly 0.0 V, or to calibrate the zero scale of a sensor.

27.3.7 Common Mode Adjustment

The common mode level of the differential signal must be 0.45 V = Full Scale/2 (or 1.35 V with GP_ADC_ATTN = 2, that is, 3× attenuation). If the common mode input level of 0.45 V cannot be achieved, the common mode level of the GPADC can be adjusted via GP_ADC_OFFP_REG and GP_ADC_OFFN_REG according to Table 58. The GPADC can tolerate a common mode margin of up to 50 mV.

Table 58: Common Mode Adjustment

CM Voltage (V _{ccm})	GP_ADC_OFFP = GP_ADC_OFFN
0.225 V	0x300
0.450 V	0x200
0.675 V	0x100

Any other common mode levels between 0.0 V and 0.9 V can be calculated from Table 58. Offset calibration can be combined with common mode adjustment by replacing the 0x200 value in the offset calibration routine with the value required to get the appropriate common mode level.

27.3.8 Input Impedance, Inductance, and Input Settling

The GPADC has no input buffer stage. During the sampling phase, a capacitor of 0.5 pF in differential mode or 1 pF in single-ended mode is switched to the input line(s). The pre-charge of this capacitor is at midscale level, so the input impedance is infinite.

During the sampling phase, a certain settling time is required. A 10-bit accuracy requires at least seven-time constants TADC_SMPL, determined by the output impedance of the input signal source, the internal resistive dividers, and the 0.5 pF or 1 pF sampling capacitor. See Table 55.

The inductance from the signal source to the ADC input pin must be very small. Otherwise filter capacitors are required from the input pins to ground (single-ended mode) or from pin to pin (differential mode).

27.4 Programming

To program and use the GPADC, follow the simple sequence of steps below:

- 1. Enable the GPADC by setting the GP ADC CTRL REG[GP ADC EN] bit.
- 2. Set up the GPIO input (P0_x_MODE_REG[PID] = 15).
- 3. Select the input channel (GP_ADC_SEL_REG).
- 4. Select the sampling mode (differential or single ended) by writing the GP_ADC_CTRL_REG[GP_ADC_SE] bit.
- 5. Select between the manual mode and the continuous mode of sampling (GP ADC CTRL REG[GP ADC CONT].
- 6. Set up extra options (see GP_ADC_CTRLx_REG description)
- 7. Start the conversion by setting GP ADC CTRL REG[GP ADC START] bit.
- 8. Wait for GP_ADC_CTRL_REG[GP_ADC_START] to become 0 or interrupt being triggered (when used).
- 9. Clear the ADC interrupt by writing any value to GP_ADC_CLEAR_INT_REG.
- 10. Get the ADC result from the GP_ADC_RESULT_REG.

28. Real Time Clock (RTC)

28.1 Introduction

The DA14531 is equipped with a Real Time Clock (RTC) which provides the complete clock and calendar information with automatic time units adjustment and easy configuration.

Features

- Complete time of day clock: 12/24 hour, hours, minutes, seconds, and hundredths of a second
- Calendar function: day of week, date of month, month, year, century, leap year compensation, and year 2000 compliant
- Alarm function: month, date, hour, minute, second, and hundredths of a second
- Event interrupt on any calendar or time unit
- Available during sleep if the power domain PD_TIM is kept alive
- Granularity of 10 ms (RTC_CLK)
- Provides 22 LSB to Timer 1 upon a capture trigger




Figure 73. Real time clock block diagram

28.2 Architecture

Figure 73 shows the architecture of the RTC.

The RTC supports a year range from 1900 to 2999 as well as full month, date, minute, second, and hundredth of second ranges. It also supports hour ranges of 0 to 23 (24-hour format) or 1 to 12 with a.m./p.m. flag (12-hour format).

Alarms can be generated in two ways, as a one-time alarm or as a recurring alarm. In addition to alarms, the RTC can detect when a particular event occurs. Each field of the calendar and time counter can generate an event when it rolls over. For example, an event can be generated every new month, new week, new day, new half day (12-hour mode), new minute, or new second. Both alarms and events can generate an interrupt. All the interrupts can be set, enabled, disabled, or masked at any time.

The LSB (22) of the port showing a full of 32-bit information on the current time is latched by Timer 1 (TIMER1_CAPCNT1/2_VALUE_REG) if instructed by Timer 1 configuration. This allows for storing an RTC based snapshot upon an event on a GPIO.

28.3 Programming

To configure the RTC, follow the simple sequence of steps below:

- 1. Configure the 100 Hz RTC granularity if needed:
 - Based on the selected LP clock (for example, 32768 kHz), set the CLK_RTCDIV_REG[RTC_DIV_INT] = 327 (= 0x147).
 - This values should be equal to the integer divisor part of the formula F_{LP} CLK/100 = **327**.680.
 - b. Based on the selected LP clock (for example, 32768 kHz), set the CLK_RTCDIV_REG[RTC_DIV_FRAC] = 680 (= 0x2A8). This values should be equal to the fractional divisor part of the formula F_{LP} CLK/100 = 327.680.
 - c. To achieve a better accuracy of the divisor, configure the denominator for the fractional division accordingly (CLK_RTCDIV_REG[RTC_DIV_DENOM]).
 - d. Enable the 100 Hz RTC granularity by setting the CLK_RTCDIV_REG [RTC_DIV_ENABLE] bit.
- 2. Enable the time functionality by clearing the RTC CONTROL REG[RTC TIME DISABLE].
- 3. Enable the calendar functionality by clearing the RTC_CONTROL_REG[RTC_CAL_DISABLE].
- 4. Choose between 12-hour or 24-hour mode (RTC_HOUR_MODE_REG[RTC_HMS]).
- 5. Configure the time (RTC TIME REG).
- 6. Configure the date (RTC_CALENDAR_REG).
- 7. Set up a time alarm if needed (RTC ALARM ENABLE REG).
- 8. Set up a calendar alarm if needed (RTC CALENDAR ALARM REG).
- 9. Enable the configured alarms (RTC_ALARM_ENABLE_REG[RTC_ALARM_xxxx_EN]).
- 10. Configure the interrupt generation when an alarm happens (RTC_INTERRUPT_ENABLE_REG). Disable the interrupt generation with RTC_INTERRUPT_DISABLE_REG.
- 11. Configure the event flag generation when an alarm happens (RTC_EVENT_FLAGS_REG).
- 12. Define whether a software reset resets the RTC (RTC_KEEP_RTC_REG[RTC_KEEP]).

29. Power

As discussed in Section 4.2, the integrated power management unit (PMU) comprises the DCDC converter and various LDOs, the V_{DD} Clamp, and the POR circuitry. The details of these blocks are discussed in the following sections.

29.1 DCDC Converter

The DA14531 can be configured in three configurations: buck, boost, and DCDC bypass. The integrated part of the DCDC is the same for all three configurations, that is, the black building blocks in Figure 74 and Figure 75. The buck configuration and the boost configuration are configured on the PCB, distinguished with the red external components in Figure 74 and Figure 75, respectively. In the bypass configuration the V_{BAT_HIGH} and V_{BAT_LOW} rails are connected, so the DCDC is bypassed.




Figure 74. DCDC block diagram - buck configuration




Figure 75. DCDC block diagram - boost configuration

- In buck configuration the battery is connected to VBAT HIGH, and DCDC supplies power to VBAT LOW rail
- In boost configuration the battery is connected to V_{BAT_LOW}, and DCDC supplies power to V_{BAT_HIGH} rail
- In DCDC bypass configuration V_{BAT_HIGH} is connected to V_{BAT_LOW} and the battery is connected to both rails. The DCDC level can be programmed by POWER_LEVEL_REG[DCDC_LEVEL] and a fine trimming is available by POWER_LEVEL_REG[DCDC_TRIM].

When the system is allowed to go to sleep, the HW FSM is activated and the DCDC controller is automatically turned off. Upon a wakeup, the DCDC will be enabled by programming DCDC_CTRL_REG[DCDC_ENABLE]. If DCDC_ENABLE is kept set before the system goes to sleep, the DCDC will be started by the hardware FSM

while waking up. If DCDC_ENABLE is reset before the system goes to sleep, the DCDC can only be started by SW setting this bit after wakeup.

For Buck configuration, a typical DCDC efficiency at 25° C as a function of the load current for different battery voltages ($V_{BAT} = V_{BAT_HIGH}$) is shown in Figure 76.




Figure 76. DCDC efficiency in buck configuration

For Boost configuration, a typical DCDC efficiency at 25°C as a function of the load current for different battery voltages ($V_{BAT} = V_{BAT LOW}$) is shown in Figure 77.




Figure 77. DCDC efficiency in boost configuration

29.2 LDOs

Several LDOs are used in the DA14531 to provide a stable power supply to the rails and the building blocks.

- V_{DD}_Clamp generates a trimmable ~0.75 V V_{DD} supply voltage for the AON (always on) DCORE power domain from V_{BAT_HIGH} or V_{BAT_LOW} when the system is in the hibernation mode
- LDO_LOW provides power to the V_{BAT_LOW} rail in the buck configuration with a typical output voltage of 1.1 V. This LDO is used during start-up and can also be used after start-up. Alternatively, it can be disabled and the V_{BAT_LOW} rail can be supplied by the DCDC converter. The LDO has a low power setting which is used to maintain the V_{BAT_LOW} rail during sleep mode. See Section 4.2.3 for more details.
- LDO_CORE supplies the internal V_{DD} from V_{BAT_LOW}. In the active mode it generates 0.9 V and in the sleep mode 0.75 V
- LDOs for the RF and the analog building blocks generate 0.9 V when the particular blocks are active. When the blocks are switched off, the LDOs are disabled.

29.3 POR Circuit

The POR_LOW circuit issues a POR when the VBAT_LOW voltage is below the threshold voltage V_{IL} for more than 50 µs. The POR is cleared when the battery voltage is above V_{IH} for at least 25 µs. The threshold levels of the POR circuit are summarized in Section 3.12.

The POR_HIGH circuit issues a POR when the VBAT_HIGH voltage is below the V_{IL} for more than 50 μ s. The POR is cleared when the battery voltage is above V_{IH} for at least 25 μ s. The threshold levels of the POR circuit are summarized in Section 3.12.

30. Bluetooth® LE Core

The Bluetooth® Low Energy (BLE) core used in the DA14531 is a qualified Bluetooth® 5.1 baseband controller compatible with the Bluetooth® LE specification and it is in charge of packet encoding/decoding and frame scheduling.

The block diagram of Bluetooth® LE core is presented in Figure 78.

Features

- Compliant with Bluetooth® Core Specification, v5.1, Bluetooth® SIG
 - · Dual topology
 - · Low duty cycle advertising
 - L2CAP connection-oriented channels
- All device classes support (Broadcaster, Central, Observer, and Peripheral)
- All packet types (Advertising, Data, and Control)
- Dedicated Encryption (AES/CCM)
- Bit stream processing (CRC and Whitening)
- FDMA/TDMA/events formatting and synchronization
- Frequency hopping calculation
- Operating clock 16 MHz or 8 MHz
- Low power modes supporting 32.0 kHz, 32.768 kHz, or 15 kHz
- Supports powerdown of the baseband during the protocol's idle periods




Figure 78. Bluetooth® LE core block diagram

30.1 Architecture

30.1.1 Exchange Memory

The Bluetooth® LE Core requires access to a memory space named "Exchange Memory" to store control structures and frame buffers. The access to Exchange Memory is performed via the AHB Master interface. The base address of the Exchange Memory is programmable by means of the BLE_EM_BASE register.

30.2 Programming

30.2.1 Wake-Up IRQ

Once the Bluetooth® LE core switches to "BLE Deep Sleep mode", the only way to correctly exit from this state is by generating initially the BLE_WAKEUP_LP_IRQ and consecutively the BLE_SLP_IRQ. This sequence must be followed regardless of the cause of the termination of the "BLE Deep Sleep mode", that is, regardless of whether the BLE Timer has expired or BLE Timer is stopped due to the assertion of BLE WAKEUP REQ.

The assertion and de-assertion of BLE_WAKEUP_LP_IRQ is fully controlled via the BLE_ENBPRESET_REG bit fields. A detailed description is as follows:

- TWIRQ_SET: it defines the number of "ble_lp_clk" cycles before the expiration of the Bluetooth® LE Timer when the BLE_WAKEUP_LP_IRQ must be asserted. It is recommended to select a TWIRQ_SET value larger than the amount of time that is required to finish trimming the XTAL 32 MHz (refer to XTAL32M_TRIM_READY) plus the execution time of the IRQ Handler. If the programmed value of TWIRQ_SET is less than the minimum recommended value, the system will wake up but the actual BLE sleep duration (refer to BLE_DEEPSLSTAT_REG) will be larger than the programmed sleep duration (refer to BLE_DEEPSLWKUP_REG)
- TWIRQ_RESET: it defines the number of "ble_lp_clk" cycles before the expiration of the sleep period when the BLE_WAKEUP_LP_IRQ will be de-asserted. It is recommended to always set its value to "1"
- TWEXT: it determines the high period of BLE_WAKEUP_LP_IRQ, if an external wake-up event (refer to GP_CONTROL_REG[BLE_WAKEUP_REQ]) occurs. Its minimum value is "TWIRQ_RESET + X", where X is the number of "ble_lp_clk" clock cycles that BLE_WAKEUP_LP_IRQ will be held high. The recommended value is "TWIRQ_RESET + 1". Note that as soon as GP_CONTROL_REG[BLE_WAKEUP_REQ] is set to "1", the BLE_WAKEUP_LP_IRQ will be asserted
- Minimum Bluetooth® LE Sleep Duration: The minimum value of BLE_DEEPSLWKUP_REG[DEEPSLTIME] bit, measured in "ble_lp_clk" cycles, is the higher value between (a) "TWIRQ_SET + 1" and (b) the SW execution time from setting BLE_DEEPSLCNTL_REG[DEEP_SLEEP_ON] up to preparing CPU to accept the BLE_WAKEUP_LP_IRQ (for example, to call the Cortex instruction WFI). If the programmed DEEPSLTIME is less than the minimum value of BLE_DEEPSLWKUP_REG[DEEPSLTIME], the BLE_WAKEUP_LP_IRQ Handler may execute sooner than the call of the Cortex WFI instruction in the example and cause SW instability

30.2.2 Switch from Bluetooth® LE Active Mode to Bluetooth® LE Deep Sleep Mode

Software can set the Bluetooth[®] LE core into the "BLE Deep Sleep mode" by first programming the timing of BLE_WAKEUP_LP_IRQ generation, then programming the desired sleep duration at BLE_DEEPSLWKUP_REG, and finally set the register bit BLE_DEEPSLCNTL_REG[DEEP_SLEEP_ON].

During the "Bluetooth LE Deep Sleep mode", the BluetoothLE Core switches to the "ble_lp_clk" (15 kHz, 32.0 kHz, or 32.768 kHz) in order to maintain its internal 625 µs timing reference. SW must poll the state of BLE_CNTL2_REG[RADIO_PWRDN_ALLOW] to detect the completion of this mode transition. Once the "ble_lp_clk" is used for base time reference, SW must disable the Bluetooth® LE clocks ("ble_master1_clk", "ble master2 clk", and "ble crypt clk") by setting the CLK_RADIO_REG[BLE_ENABLE] register bit to "0".

Finally, software can optionally power down the Radio Subsystem by using the PMU CTRL REG[RADIO SLEEP] and the Peripheral and System power domains as well.

Figure 79 presents the waveforms when the Bluetooth® LE Deep Sleep mode is entered. In this case, as soon as the SW detects that RADIO_PWRDOWN_ALLOW is "1", it sets the PMU_CTRL_REG[RADIO_SLEEP] to power down the Radio Subsystem. In Figure 79, Figure 80, Figure 81, Figure 82, and Figure 83, the corresponding Bluetooth® LE Core signals are marked with red while Radio Subsystem is in power-down state and they remain red-marked during the period when RADIO_SLEEP is set.




Figure 79. Entering Bluetooth® LE Deep Sleep mode

30.2.3 Switch from Bluetooth® LE Deep Sleep Mode to Bluetooth® LE Active Mode

There are two possibilities for the Bluetooth® LE Core to terminate the Bluetooth® LE Deep Sleep mode:

- Termination at the end of a predetermined time
- Termination on SW wake-up request due to an external event

30.2.3.1 Switching at an Anchor Point

Figure 82 shows a typical BLE deep sleep phase that is terminated at a predetermined time. After a configurable time before the scheduled wake-up time (configured via BLE_ENBPRESET_REG register bit fields), the BLE Timer asserts the BLE_WAKEUP_LP_IRQ to wake up the CPU (powering up the System Power Domain). The BLE_WAKEUP_LP_IRQ Interrupt Handler will prepare the code environment and the XTAL32M oscillator stabilization (refer to SYS_STAT_REG[XTAL32_SETTLED]) and will decide when the BLE Core is ready to exit the BLE Deep Sleep mode.

Once the SW decides that the BLE Core can wake up, it must enable the BLE clocks (via CLK_RADIO_REG[BLE_ENABLE]) and power up the Radio Power Domain (refer to PMU_CTRL_REG[RADIO_SLEEP] and SYS_STAT_REG[RAD_IS_UP]).

After the sleep period is expired (as specified in BLE_DEEPSLWKUP_REG[DEEPSLTIME]), the BLE Timer will not exit the BLE Deep Sleep mode until it detects that the BLE Core is powered up. That means, if the SW requires more time to power up the BLE Core, the final sleep duration (provided by BLE_DEEPSLSTAT_REG) will be longer than the preprogrammed value.

When the BLE Timer is expired, BLE clocks are enabled, and the BLE Core (Radio Subsystem) is powered up, the BLE Core exists the "BLE Core Deep Sleep mode" and asserts the BLE_SLP_IRQ.




Figure 80. Exit Bluetooth LE Deep Sleep mode at predetermined time (zoom in)




Figure 81. Exit Bluetooth LE Deep Sleep mode after predetermined time (zoom in)



Figure 82. Exit Bluetooth LE Deep Sleep mode at predetermined time (zoom out)

30.2.3.2 Switching Due to an External Event

Figure 83 shows a wakeup from a BLE deep sleep period forced by the assertion of register bit GP_CONTROL_REG[BLE_WAKEUP_REQ].

Assume that the system is in Extended Sleep state with all power domains switched off and both the wake-up timer and wake-up controller programmed appropriately. Then assume that an event is detected at one of the GPIOs, causing the System Power Domain to wake up due to WKUP_QUADDEC_IRQ. In that case, the software decides to wake up the Bluetooth LE core, then it sets the GP_CONTROL_REG[BLE_WAKEUP_REQ] to 1 to force the wake-up sequence.

In Figure 83 the BLE_WAKEUP_REQ is raised by the software as soon as possible, causing BLE_WAKEUP_LP_IRQ Handler to be executed as soon as possible. It is also possible to raise BLE_WAKEUP_REQ after the detection of XTAL32_TRIM_READY, causing both BLE_WAKEUP_LP_IRQ and BLE_SLP_IRQ Handlers to be executed sequentially. The decision depends on the SW structure and the application.




Figure 83. Exit Bluetooth LE Deep Sleep mode due to external event

As soon as the bit field BLE_WAKEUP_REQ is set to 1, the BLE_WAKEUP_LP_IRQ is asserted. In that case, the high period of BLE_WAKEUP_LP_IRQ is controlled via TWEXT. The recommended value of TWEXT is "TWIRQ_RESET + 1", meaning that BLE_WAKEUP_LP_IRQ will remain high for one "ble_lp_clk" period.

If the BLE_WAKEUP_REQ is high, entering the sleep mode is prohibited. Please note that BLE_WAKEUP_REQ event can be disabled by setting BLE_DEEPSLCNTL_REG[EXTWKUPDSB].

31. Radio

31.1 Introduction

The Radio Transceiver implements the RF part of the Bluetooth® LE protocol. Together with the Bluetooth® 5.1 PHY layer, it provides up to 93 dB RF link budget for a reliable wireless communication. All RF blocks are supplied by on-chip low-drop out-regulators (LDOs). The bias scheme is programmable per block and optimized for minimum power consumption. The radio block diagram is given in Figure 84. It comprises the Receiver, Transmitter, Synthesizer, Rx/Tx combiner block, and Biasing LDOs.

Features

- Single ended RFIO interface, 50 Ω matched
- Alignment free operation
- -90 dBm receiver sensitivity
- Configurable transmit output power from -19.5 dBm up to +2.5 dBm
- Ultra-low power consumption
- Fast frequency tuning minimizes overhead




Figure 84. Bluetooth® radio block diagram

31.2 Architecture

31.2.1 Receiver

The RX frontend consists of a selective matching network, a low noise amplifier (LNA), and an image rejection down conversion mixer. The intermediate frequency (IF) part of the receiver comprises a filter with a programmable gain. The LNA and IF Filter gains are controlled by the Automatic Gain Control (AGC). This provides the necessary signal conditioning prior to digitalization. The digital demodulator block (DEM) provides a synchronous bit stream.

31.2.2 Synthesizer

The RF Synthesizer generates the quadrature LO signal for the mixer, but also generates the modulated TX output signal. The Digitally Controlled Oscillator (DCO) runs at twice the required frequency and a dedicated

divide-by-2 circuit generates the 2.4 GHz signals in the required phase relations. The reference frequency is the 32 MHz crystal clock. The modulation of the TX frequency is performed by 2-point modulation.

31.2.3 Transmitter

The RF power amplifier (RFPA) is an extremely efficient Class-D structure, providing typically the power ranging from -19.5 dBm to +2.5 dBm to the antenna. It is fed by the DCO's divide-by-2 circuit and delivers its TX power to the antenna pin through the combined RX/TX matching circuit.

31.2.4 RFIO

The RX/TX combiner block is a unique feature of the DA14531. It makes sure that the received power is applied to the LNA with minimum losses towards the RFPA. In TX mode, the LNA poses a minimal load for the RFPA and its input pins are protected from the RFPA. In both modes, the single ended RFIO port is matched to a resistor of 50 Ω to provide the simplest possible interfacing to the antenna on the printed circuit board.

31.2.5 Biasing

All RF blocks are supplied by on-chip LDOs. The bias scheme is programmable and optimized for minimum power consumption.

31.2.6 RF Monitoring

The Radio is equipped with a monitoring block whose responsibility is to acquire the data provided by the RF Unit and other analog resources, to combine them in words of 32 bits (when necessary), and to store them in system's memory. Data can be the output of the Demodulator (I and Q) or be provided by the GPADC. With the monitoring block, production tests of the corresponding block can be achieved.

32. Registers

This section contains a detailed view of the DA14531 registers. It is organized as follows: an overview table is presented initially, which depicts all register names, addresses, and descriptions. A detailed bit level description of each register follows.

The register file of the Arm Cortex-M0+ can be found in the following documents available on the website:

Devices Generic User Guide:

https://developer.arm.com/docs/238818831/10/getting-started-with-cortex-m0-cortex-m0-cortex-m3-and-cortex-m4-full-licensee-bundles

Technical Reference Manual:

https://developer.arm.com/docs/ddi0484/c/preface

These documents contain the register descriptions for the Nested Vectored Interrupt Controller (NVIC), the System Control Block (SCB), and the System Timer (SysTick).

32.1 Analog Miscellaneous Registers

Table 59: Register map ANAMISC

Address	Register	Description
0x50001600	CLK_REF_SEL_REG	Select clock for oscillator calibration
0x50001602	CLK_REF_CNT_REG	Count value for oscillator calibration
0x50001604	CLK_REF_VAL_L_REG	XTAL32M reference cycles, lower 16 bits
0x50001606	CLK_REF_VAL_H_REG	XTAL32M reference cycles, higher 16 bits

Table 60: CLK_REF_SEL_REG (0x50001600)

Bit	Mode	Symbol/Description	Reset
3	R/W EXT_CNT_EN_SEL		0x0
		Enable XTAL_CNT counter by the REF_CLK selected by REF_CLK_SEL. Enable XTAL_CNT counter from an external input.	
2	R/W	REF_CAL_START	0x0
		Writing 1 starts a calibration of the clock selected by CLK_REF_SEL_REG[REF_CLK_SEL]. This bit is cleared when calibration is finished, and CLK_REF_VAL is ready.	
1:0	R/W	REF_CLK_SEL	0x0
		Select clock input for calibration: 0x0: RC32K 0x1: RC32M 0x2: XTAL32K 0x3: RCX	

Table 61: CLK_REF_CNT_REG (0x50001602)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	REF_CNT_VAL	0x0
		Indicates the calibration time, with a decrement counter to 1.	

Table 62: CLK_REF_VAL_L_REG (0x50001604)

Bit	Mode	Symbol/Description	Reset
15:0	R	XTAL_CNT_VAL	0x0
		Returns the number of the DIVN clock cycles counted during the calibration time, defined with REF_CNT_VAL	

Table 63: CLK_REF_VAL_H_REG (0x50001606)

Bit	Mode	Symbol/Description	Reset
15:0	R	XTAL_CNT_VAL	0x0
		Returns the number of the DIVN clock cycles counted during the calibration time, defined with REF_CNT_VAL	

32.2 Bluetooth® LE Core Registers

Table 64: Register map BLE

Address	Register	Description
0x40000000	BLE_RWBLECNTL_REG	Bluetooth LE Control register
0x40000004	BLE_VERSION_REG	Version register
0x40000008	BLE_RWBLECONF_REG	Configuration register
0x400000c	BLE_INTCNTL_REG	Interrupt controller register
0x40000010	BLE_INTSTAT_REG	Interrupt status register
0x40000014	BLE_INTRAWSTAT_RE G	Interrupt raw status register
0x40000018	BLE_INTACK_REG	Interrupt acknowledge register
0x4000001c	BLE_BASETIMECNT_RE G	Base time reference counter
0x40000020	BLE_FINETIMECNT_RE G	Fine time reference counter
0x40000024	BLE_BDADDRL_REG	Bluetooth LE device address LSB register
0x40000028	BLE_BDADDRU_REG	Bluetooth LE device address MSB register
0x4000002c	BLE_CURRENTRXDESC PTR_REG	RX Descriptor Pointer for the Receive Buffer Chained List
0x40000030	BLE_DEEPSLCNTL_RE G	Deep-Sleep control register
0x40000034	BLE_DEEPSLWKUP_RE G	Time (measured in Low Power clock cycles) in Deep Sleep mode before waking up the device
0x40000038	BLE_DEEPSLSTAT_RE G	Duration of the last deep sleep phase register
0x4000003c	BLE_ENBPRESET_REG	Time in low power oscillator cycles register
0x40000040	BLE_FINECNTCORR_R EG	Phase correction value register
0x40000044	BLE_BASETIMECNTCO RR_REG	Base Time Counter
0x40000050	BLE_DIAGCNTL_REG	Diagnostics Register
0x40000054	BLE_DIAGSTAT_REG	Debug use only
0x40000058	BLE_DEBUGADDMAX_R EG	Upper limit for the memory zone
0x4000005c	BLE_DEBUGADDMIN_R EG	Lower limit for the memory zone
0x40000060	BLE_ERRORTYPESTAT _REG	Error Type Status registers
0x40000064	BLE_SWPROFILING_RE G	Software Profiling register
0x40000074	BLE_RADIOCNTL1_REG	Radio interface control register
0x40000080	BLE_RADIOPWRUPDN_ REG	RX/TX powerup/down phase register
0x40000090	BLE_ADVCHMAP_REG	Advertising Channel Map
0x400000a0	BLE_ADVTIM_REG	Advertising Packet Interval

Address	Register	Description
0x400000a4	BLE_ACTSCANSTAT_R EG	Active scan register
0x400000b0	BLE_WLPUBADDPTR_R EG	Start address of public devices list
0x400000b4	BLE_WLPRIVADDPTR_ REG	Start address of private devices list
0x400000b8	BLE_WLNBDEV_REG	Devices in white list
0x400000c0	BLE_AESCNTL_REG	Start AES register
0x400000c4	BLE_AESKEY31_0_REG	AES encryption key
0x400000c8	BLE_AESKEY63_32_RE G	AES encryption key
0x400000cc	BLE_AESKEY95_64_RE G	AES encryption key
0x400000d0	BLE_AESKEY127_96_R EG	AES encryption key
0x400000d4	BLE_AESPTR_REG	Pointer to the block to encrypt/decrypt
0x400000d8	BLE_TXMICVAL_REG	AES/CCM plain MIC value
0x400000dc	BLE_RXMICVAL_REG	AES/CCM plain MIC value
0x400000e0	BLE_RFTESTCNTL_RE G	RF Testing Register
0x400000e4	BLE_RFTESTTXSTAT_R EG	RF Testing Register
0x400000e8	BLE_RFTESTRXSTAT_R EG	RF Testing Register
0x400000f0	BLE_TIMGENCNTL_RE G	Timing Generator Register
0x400000f4	BLE_GROSSTIMTGT_R EG	Gross Timer Target value
0x400000f8	BLE_FINETIMTGT_REG	Fine Timer Target value
0x400000fc	BLE_SAMPLECLK_REG	Samples the Base Time Counter
0x40000100	BLE_COEXIFCNTL0_RE G	Coexistence interface Control 0 Register
0x40000104	BLE_COEXIFCNTL1_RE G	Coexistence interface Control 1 Register
0x40000108	BLE_BLEMPRIO0_REG	Coexistence interface Priority 0 Register
0x4000010c	BLE_BLEMPRIO1_REG	Coexistence interface Priority 1 Register
0x40000200	BLE_CNTL2_REG	Bluetooth LE Control Register 2
0x40000208	BLE_EM_BASE_REG	Exchange Memory Base Register
0x4000020c	BLE_DIAGCNTL2_REG	Debug use only
0x40000210	BLE_DIAGCNTL3_REG	Debug use only

Table 65: BLE_RWBLECNTL_REG (0x40000000)

Bit	Mode	Symbol/Description	Reset
31	R0/W	MASTER_SOFT_RST	0x0

Bit	Mode	Symbol/Description	Reset
		Reset the complete Bluetooth LE Core except registers and timing generator, when written with 1. Resets at 0 when action is performed. No action happens if it is written with 0.	
30	R0/W	MASTER_TGSOFT_RST	0x0
		Reset the timing generator, when written with 1. Resets at 0 when action is performed. No action happens if it is written with 0.	
29	R/W	REG_SOFT_RST	0x0
		Reset the complete register block, when written with 1. Resets at 0 when action is performed. No action happens if it is written with 0.	
		Note that INT STAT is not cleared, so you should also write to BLE_INTACK_REG after the software reset.	
28	R0/W	SWINT_REQ	0x0
		Forces the generation of ble_sw_irq when written with 1, and proper masking is set. Resets at 0 when action is performed. No action happens if it is written with 0.	
26	R0/W	RFTEST_ABORT	0x0
		Abort the current RF Testing defined as per CS-FORMAT when written with 1. Resets at 0 when action is performed. No action happens if it is written with 0.	
		Note that when RFTEST_ABORT is requested:	
		1) In case of infinite TX, the Packet Controller FSM stops at the end of the current byte in process, and processes accordingly the packet CRC.	
		2) In case of Infinite RX, the Packet Controller FSM either stops as the end of the current Packet reception (if Access address has been detected), or simply stop the processing switching off the RF.	
25	R0/W	ADVERT_ABORT	0x0
		Abort the current Advertising event when written with 1. Resets at 0 when action is performed. No action happens if it is written with 0.	
24	R0/W	SCAN_ABORT	0x0
		Abort the current scan window when written with 1. Resets at 0 when action is performed. No action happens if it is written with 0.	
22	R/W	MD_DSB	0x0
		0: Normal operation of MD bits management	
		1: Allow a single TX/RX exchange whatever the MD bits are	
		- value forced by software from TX Descriptor	
		- value just saved in RX Descriptor during reception	
21	R/W	SN_DSB	0x0
		0: Normal operation of Sequence number	
		1: Sequence Number Management disabled	
		- value forced by software from TX Descriptor	
		- value ignored in RX, where no SN error reported	
20	R/W	NESN_DSB	0x0
		0: Normal operation of Acknowledge	
		1: Acknowledge scheme disabled	
		- value forced by software from TX Descriptor	
		- value ignored in RX, where no NESN error reported	
19	R/W	CRYPT_DSB	0x0
		Normal operation. Encryption/Decryption enabled Encryption/Decryption disabled	

Bit	Mode	Symbol/Description	Reset
		Note that if CS-CRYPT_EN is set, then MIC is generated, and only data encryption is disabled, meaning data sent are plain data.	
18	R/W	WHIT_DSB	0x0
		Normal operation. Whitening enabled Whitening disabled	
17	R/W	CRC_DSB	0x0
		0: Normal operation. CRC removed from data stream.1: CRC stripping disabled on RX packets, CRC replaced by 0x000 in TX.	
16	R/W	HOP_REMAP_DSB	0x0
		Normal operation. Frequency Hopping Remapping algorithm enabled Frequency Hopping Remapping algorithm disabled	
13:12	R/W	-	0x0
		Reserved	
9	R/W	ADVERTFILT_EN	0x0
		Advertising Channels Error Filtering Enable control 0: Bluetooth LE Core reports all errors to RW-Bluetooth LE Software 1: Bluetooth LE Core reports only correctly received packet, without error to RW-Bluetooth LE Software	
8	R/W	RWBLE_EN	0x0
		Disable Bluetooth LE Core Exchange Table pre-fetch mechanism Enable Bluetooth LE Core Exchange table pre-fetch mechanism	
7:4	R/W	RXWINSZDEF	0x0
		Default RX Window size in µs. Used when device: - is master connected - performs its second receipt. 0 is not a valid value. Recommended value is 10 (in decimal).	
2:0	R/W	SYNCERR	0x0
		Indicates the maximum number of errors allowed to recognize the synchronization word	

Table 66: BLE_VERSION_REG (0x40000004)

Bit	Mode	Symbol/Description	Reset
31:24	R	TYP	0x7
		Bluetooth LE Core Type	
23:16	R	REL	0x1
		Bluetooth LE Core version Major release number	
15:8	R	UPG	0x0
		Bluetooth LE Core Upgrade number	
7:0	R	BUILD	0x0
		Bluetooth LE Core Build number	

Table 67: BLE_RWBLECONF_REG (0x40000008)

Bit	Mode	Symbol/Description	Reset
29:24	R	ADD_WIDTH	0xF
		Value of the RW_BLE_ADDRESS_WIDTH parameter concerted into binary	
22:16	R	RFIF	0x2
		Radio Interface ID	
13:8	R	CLK_SEL	0x0
		Operating Frequency (in MHz)	
6	R	DECIPHER	0x0
		0: AES deciphering not present	
5	R	DMMODE	0x0
		0: Bluetooth LE Core is used as a standalone Bluetooth LE device	
4	R	INTMODE	0x1
		1: Interrupts are trigger level generated, stays active at 1 till acknowledgement	
3	R	COEX	0x1
		1: WLAN Coexistence mechanism present	
2	R	USEDBG	0x1
		1: Diagnostic port instantiated	
1	R	USECRYPT	0x1
		1: AES-CCM Encryption block present	
0	R	BUSWIDTH	0x1
		Processor bus width:	
		1: 32 bits	

Table 68: BLE_INTCNTL_REG (0x4000000C)

Bit	Mode	Symbol/Description	Reset
15	R/W	CSCNTDEVMSK	0x1
		CSCNT interrupt mask during event. This bit allows to enable CSCNT interrupt generation during events (advertising, scanning, initiating, and connection)	
		0: CSCNT Interrupt not generated during events	
		1: CSCNT Interrupt generated during events	
14:10	R	-	0x0
		Reserved	
9	R/W	SWINTMSK	0x0
		Software triggered interrupt Mask	
		0: Interrupt not generated	
		1: Interrupt generated	
8	R/W	EVENTAPFAINTMSK	0x1
		End of event/anticipated pre-fetch abort interrupt Mask	
		0: Interrupt not generated	
		1: Interrupt generated	
7	R/W	FINETGTIMINTMSK	0x0
		Fine Target Timer Mask	

Bit	Mode	Symbol/Description	Reset
		0: Interrupt not generated	
		1: Interrupt generated	
6	R/W	GROSSTGTIMINTMSK	0x0
		Gross Target Timer Mask	
		0: Interrupt not generated	
		1: Interrupt generated	
5	R/W	ERRORINTMSK	0x0
		Error Interrupt Mask	
		0: Interrupt not generated	
		1: Interrupt generated	
4	R/W	CRYPTINTMSK	0x1
		Encryption engine Interrupt Mask	
		0: Interrupt not generated	
		1: Interrupt generated	
3	R/W	EVENTINTMSK	0x1
		End of event Interrupt Mask	
		0: Interrupt not generated	
		1: Interrupt generated	
2	R/W	SLPINTMSK	0x1
		Sleep Mode Interrupt Mask	
		0: Interrupt not generated	
		1: Interrupt generated	
1	R/W	RXINTMSK	0x1
		RX Interrupt Mask	
		0: Interrupt not generated	
		1: Interrupt generated	
0	R/W	CSCNTINTMSK	0x1
		625 μs Base Time Interrupt Mask	
		0: Interrupt not generated	
		1: Interrupt generated	

Table 69: BLE_INTSTAT_REG (0x40000010)

Bit	Mode	Symbol/Description	Reset
9	R	SWINTSTAT	0x0
		Software triggered interrupt status	
		0: No software triggered interrupt	
		1: A software triggered interrupt is pending	
8	R	EVENTAPFAINTSTAT	0x0
		End of event/Anticipated Pre-Fetch Abort interrupt status	
		0: No End of Event interrupt	
		1: An End of Event interrupt is pending	
7	R	FINETGTIMINTSTAT	0x0
		Masked Fine Target Timer Error interrupt status	
		0: No Fine Target Timer interrupt	

Bit	Mode	Symbol/Description	Reset
		1: A Fine Target Timer interrupt is pending	
6	R	GROSSTGTIMINTSTAT	0x0
		Masked Gross Target Timer interrupt status	
		0: No Gross Target Timer interrupt	
		1: A Gross Target Timer interrupt is pending	
5	R	ERRORINTSTAT	0x0
		Masked Error interrupt status	
		0: No Error interrupt	
		1: An Error interrupt is pending	
4	R	CRYPTINTSTAT	0x0
		Masked Encryption engine interrupt status	
		0: No Encryption/Decryption interrupt	
		1: An Encryption/Decryption interrupt is pending	
3	R	EVENTINTSTAT	0x0
		Masked End of Event interrupt status	
		0: No End of Advertising/Scanning/Connection interrupt	
		1: An End of Advertising/Scanning/Connection interrupt is pending	
2	R	SLPINTSTAT	0x0
		Masked Sleep interrupt status	
		0: No End of Sleep Mode interrupt	
		1: An End of Sleep Mode interrupt is pending	
1	R	RXINTSTAT	0x0
		Masked Packet Reception interrupt status	
		0: No RX interrupt	
		1: An RX interrupt is pending	
0	R	CSCNTINTSTAT	0x0
		Masked 625 µs base time reference interrupt status	
		0: No 625 μs Base Time interrupt	
		1: A 625 µs Base Time interrupt is pending	

Table 70: BLE_INTRAWSTAT_REG (0x40000014)

Bit	Mode	Symbol/Description	Reset
9	R	SWINTRAWSTAT	0x0
		Software triggered interrupt raw status 0: No software triggered interrupt 1: A software triggered interrupt is pending	
8	R	EVENTAPFAINTRAWSTAT End of event/Anticipated Pre-Fetch Abort interrupt raw status 0: No End of Event interrupt 1: An End of Event interrupt is pending	0x0
7	R	FINETGTIMINTRAWSTAT Fine Target Timer Error interrupt raw status 0: No Fine Target Timer interrupt 1: A Fine Target Timer interrupt is pending	0x0

Bit	Mode	Symbol/Description	Reset
6	R	GROSSTGTIMINTRAWSTAT	0x0
		Gross Target Timer interrupt raw status	
		0: No Gross Target Timer interrupt	
		1: A Gross Target Timer interrupt is pending	
5	R	ERRORINTRAWSTAT	0x0
		Error interrupt raw status	
		0: No Error interrupt	
		1: An Error interrupt is pending	
4	R	CRYPTINTRAWSTAT	0x0
		Encryption engine interrupt raw status	
		0: No Encryption/Decryption interrupt	
		1: An Encryption/Decryption interrupt is pending	
3	R	EVENTINTRAWSTAT	0x0
		End of Event interrupt raw status	
		0: No End of Advertising/Scanning/Connection interrupt	
		1: An End of Advertising/Scanning/Connection interrupt is pending	
2	R	SLPINTRAWSTAT	0x0
		Sleep interrupt raw status	
		0: No End of Sleep Mode interrupt	
		1: An End of Sleep Mode interrupt is pending	
1	R	RXINTRAWSTAT	0x0
		Packet Reception interrupt raw status	
		0: No RX interrupt	
		1: An RX interrupt is pending	
0	R	CSCNTINTRAWSTAT	0x0
		625 μs base time reference interrupt raw status	
		0: No 625 μs Base Time interrupt	
		1: A 625 µs Base Time interrupt is pending	

Table 71: BLE_INTACK_REG (0x40000018)

Bit	Mode	Symbol/Description	Reset
9	R0/W	SWINTACK	0x0
		Software triggered interrupt acknowledgement bit. Software writing 1 acknowledges the software triggered interrupt. This bit resets SWINTSTAT and SWINTRAWSTAT flags. Resets at 0 when action is performed.	
8	R0/W	EVENTAPFAINTACK	0x0
		End of event/Anticipated Pre-Fetch Abort interrupt acknowledgement bit. Software writing 1 acknowledges the End of event/Anticipated Pre-Fetch Abort interrupt. This bit resets EVENTAPFAINTSTAT and EVENTAPFAINTRAWSTAT flags. Resets at 0 when action is performed.	
7	R0/W	FINETGTIMINTACK	0x0
		Fine Target Timer interrupt acknowledgement bit.	

Bit	Mode	Symbol/Description	Reset
		Software writing 1 acknowledges the Fine Timer interrupt. This bit resets FINETGTIMINTSTAT and FINETGTIMINTRAWSTAT flags.	
		Resets at 0 when action is performed.	
6	R0/W	GROSSTGTIMINTACK	0x0
		Gross Target Timer interrupt acknowledgement bit.	
		Software writing 1 acknowledges the Gross Timer interrupt. This bit resets GROSSTGTIMINTSTAT and GROSSTGTIMINTRAWSTAT flags.	
		Resets at 0 when action is performed.	
5	R0/W	ERRORINTACK	0x0
		Error interrupt acknowledgement bit.	
		Software writing 1 acknowledges the Error interrupt. This bit resets ERRORINTSTAT and ERRORINTRAWSTAT flags.	
		Resets at 0 when action is performed.	
4	R0/W	CRYPTINTACK	0x0
		Encryption engine interrupt acknowledgement bit.	
		Software writing 1 acknowledges the Encryption engine interrupt. This bit resets CRYPTINTSTAT and CRYPTINTRAWSTAT flags.	
		Resets at 0 when action is performed.	
3	R0/W	EVENTINTACK	0x0
		End of Event interrupt acknowledgment bit.	
		Software writing 1 acknowledges the End of Advertising/Scanning/Connection interrupt. This bit resets SLPINTSTAT and SLPINTRAWSTAT flags.	
		Resets at 0 when action is performed.	
2	R0/W	SLPINTACK	0x0
		End of Deep Sleep interrupt acknowledgment bit.	
		Software writing 1 acknowledges the End of Sleep Mode interrupt. This bit resets SLPINTSTAT and SLPINTRAWSTAT flags.	
		Resets at 0 when action is performed.	
1	R0/W	RXINTACK	0x0
		Packet Reception interrupt acknowledgment bit.	
		Software writing 1 acknowledges the RX interrupt. This bit resets RXINTSTAT and RXINTRAWSTAT flags.	
		Resets at 0 when action is performed.	
0	R0/W	CSCNTINTACK	0x0
		625 µs base time reference interrupt acknowledgment bit.	
		Software writing 1 acknowledges the CLKN interrupt. This bit resets CLKINTSTAT and CLKINTRAWSTAT flags.	
		Resets at 0 when action is performed.	

Table 72: BLE_BASETIMECNT_REG (0x4000001C)

Bit	Mode	Symbol/Description	Reset
26:0	R	BASETIMECNT	0x0
		Value of the 625 µs base time reference counter. Updated each time SAMPCLK is written. Used by the software to synchronize with the hardware.	

Table 73: BLE_FINETIMECNT_REG (0x40000020)

Bit	Mode	Symbol/Description	Reset
9:0	R	FINECNT	0x0
		Value of the current μs fine time reference counter. Updated each time SAMPCLK is written. Used by the software to synchronize with the hardware, and obtain a more precise sleep duration.	

Table 74: BLE_BDADDRL_REG (0x40000024)

Bit	Mode	Symbol/Description	Reset
31:0	R/W	BDADDRL	0x0
		Bluetooth Low Energy Device Address. LSB part.	

Table 75: BLE_BDADDRU_REG (0x40000028)

Bit	Mode	Symbol/Description	Reset
16	R/W	PRIV_NPUB	0x0
		Bluetooth Low Energy Device Address privacy indicator 0: Public Bluetooth Device Address 1: Private Bluetooth Device Address	
15:0	R/W	BDADDRU	0x0
		Bluetooth Low Energy Device Address. MSB part.	

Table 76: BLE_CURRENTRXDESCPTR_REG (0x4000002C)

Bit	Mode	Symbol/Description	Reset
31:16	R/W	ETPTR	0x0
		Exchange Table Pointer that determines the starting point of the Exchange Table.	
14:0	R/W	CURRENTRXDESCPTR	0x0
		RX Descriptor Pointer that determines the starting point of the Receive Buffer Chained List.	

Table 77: BLE_DEEPSLCNTL_REG (0x40000030)

Bit	Mode	Symbol/Description	Reset
31	R/W	EXTWKUPDSB	0x0
		External Wake-Up disable	
		0: RW-BLE Core can be woken by external wake-up	
		1: RW-BLE Core cannot be woken up by external wake-up	
15	R	DEEP_SLEEP_STAT	0x0
		Indicator of current Deep Sleep clock mux status:	
		0: RW-Bluetooth LE Core is not yet in Deep Sleep mode	
		1: RW-Bluetooth LE Core is in Deep Sleep mode (only low_power_clk is running)	
4	R/W	SOFT_WAKEUP_REQ	0x0
		Wake Up Request from Bluetooth LE Software. Applies when system is in Deep Sleep mode. It wakes up the Bluetooth LE Core when written with 1. Resets at 0 when action is performed. No action happens if it is written with 0.	
3	R0/W	DEEP_SLEEP_CORR_EN	0x0

Bit	Mode	Symbol/Description	Reset
		625 µs base time reference integer and fractional part correction. Applies when system has been woken-up from Deep Sleep mode. It enables Fine Counter and Base Time counter when written with 1. Resets at 0 when action is performed. No action happens if it is written with 0.	
2	R0/W	DEEP_SLEEP_ON	0x0
		0: Bluetooth LE Core in normal Active mode	
		1: Request RW-Bluettoh LE Core to switch in Deep Sleep mode	
		This bit is reset on DEEP_SLEEP_STAT falling edge	
1:0	R/W	DEEP_SLEEP_IRQ_EN	0x0
		Always set to 3 when DEEP_SLEEP_ON is set to 1.	
		It controls the generation of BLE_WAKEUP_LP_IRQ.	

Table 78: BLE_DEEPSLWKUP_REG (0x40000034)

Bit	Mode	Symbol/Description	Reset
31:0	R/W	DEEPSLTIME	0x0
		Determines the time in low_power_clk clock cycles to spend in Deep Sleep mode before waking up the device. This ensures a maximum of 37 hours and 16 mn sleep mode capabilities at 32 kHz. This ensures a maximum of 36 hours and 16 mn sleep mode capabilities at 32.768 kHz.	

Table 79: BLE_DEEPSLSTAT_REG (0x40000038)

Bit	Mode	Symbol/Description	Reset
31:0	R	DEEPSLDUR	0x0
		Actual duration of the last deep sleep phase measured in low_power_clk clock cycle. DEEPSLDUR is set to zero at the beginning of the deep sleep phase, and is incremented at each low_power_clk clock cycle until the end of the deep sleep phase.	

Table 80: BLE_ENBPRESET_REG (0x4000003C)

Bit	Mode	Symbol/Description	Reset
31:21	R/W	TWEXT	0x0
		Minimum and recommended value is "TWIRQ_RESET + 1".	
		In the case of wake-up due to an external wake-up request, TWEXT specifies the time delay in low power oscillator cycles to deassert BLE_WAKEUP_LP_IRQ.	
		See also GP_CONTROL_REG[BLE_WAKEUP_REQ].	
		Range is [064 ms] for 32 kHz; [062.5 ms] for 32.768 kHz	
20:10	R/W	TWIRQ_SET	0x0
		Minimum value is "TWIRQ_RESET + 1".	
		Time in low power oscillator cycles to set BLE_WAKEUP_LP_IRQ before the Bluetooth LE sleep timer expiration.	
		See also BLE_DEEPSLWKUP_REG[DEEPSLTIME].	
		Range is [064 ms] for 32 kHz; [062.5 ms] for 32.768 kHz	
9:0	R/W	TWIRQ_RESET	0x0
		Recommended value is 1.	
		Time in low power oscillator cycles to reset BLE_WAKEUP_LP_IRQ before the Bluetooth LE sleep timer expiration.	

Bit	Mode	Symbol/Description	Reset
		See also BLE_DEEPSLWKUP_REG[DEEPSLTIME].	
		Range is [032 ms] for 32 kHz; [031.25 ms] for 32.768 kHz.	

Table 81: BLE_FINECNTCORR_REG (0x40000040)

Bit	Mode	Symbol/Description	Reset
9:0	R/W	FINECNTCORR	0x0
		Phase correction value for the 625 µs reference counter (Fine Counter) in µs	

Table 82: BLE_BASETIMECNTCORR_REG (0x40000044)

Bit	Mode	Symbol/Description	Reset
26:0	R/W	BASETIMECNTCORR	0x0
		Base Time Counter correction value	

Table 83: BLE_DIAGCNTL_REG (0x40000050)

Bit	Mode	Symbol/Description	Reset
31	R/W	DIAG3_EN	0x0
		0: Disable diagnostic port 0 output. All outputs are set to 0x0.	
		1: Enable diagnostic port 0 output.	
29:24	R/W	DIAG3	0x0
		Only relevant when DIAG3_EN = 1.	
		Selection of the outputs that must be driven to the diagnostic port BLE_DIAG3.	
23	R/W	DIAG2_EN	0x0
		0: Disable diagnostic port 0 output. All outputs are set to 0x0.	
		1: Enable diagnostic port 0 output.	
21:16	R/W	DIAG2	0x0
		Only relevant when DIAG2_EN = 1.	
		Selection of the outputs that must be driven to the diagnostic port BLE_DIAG2.	
15	R/W	DIAG1_EN	0x0
		0: Disable diagnostic port 0 output. All outputs are set to 0x0.	
		1: Enable diagnostic port 0 output.	
13:8	R/W	DIAG1	0x0
		Only relevant when DIAG1_EN = 1.	
		Selection of the outputs that must be driven to the diagnostic port BLE_DIAG1.	
7	R/W	DIAG0_EN	0x0
		0: Disable diagnostic port 0 output. All outputs are set to 0x0.	
		1: Enable diagnostic port 0 output.	
5:0	R/W	DIAG0	0x0
		Only relevant when DIAG0_EN = 1.	
		Selection of the outputs that must be driven to the diagnostic port BLE_DIAG0.	

Table 84: BLE_DIAGSTAT_REG (0x40000054)

Bit	Mode	Symbol/Description	Reset
31:24	R	DIAG3STAT	0x0
		Directly connected to ble_dbg3[7:0] output. Debug use only.	
23:16	R	DIAG2STAT	0x0
		Directly connected to ble_dbg2[7:0] output. Debug use only.	
15:8	R	DIAG1STAT	0x0
		Directly connected to ble_dbg1[7:0] output. Debug use only.	
7:0	R	DIAG0STAT	0x0
		Directly connected to ble_dbg0[7:0] output. Debug use only.	

Table 85: BLE_DEBUGADDMAX_REG (0x40000058)

Bit	Mode	Symbol/Description	Reset
31:16	R/W	REG_ADDMAX	0x0
		Upper limit for the Register zone indicated by the reg_inzone flag.	
15:0	R/W	EM_ADDMAX	0x0
		Upper limit for the Exchange Memory zone indicated by the em_inzone flag.	

Table 86: BLE_DEBUGADDMIN_REG (0x4000005C)

Bit	Mode	Symbol/Description	Reset
31:16	R/W	REG_ADDMIN	0x0
		Lower limit for the Register zone indicated by the reg_inzone flag.	
15:0	R/W	EM_ADDMIN	0x0
		Lower limit for the Exchange Memory zone indicated by the em_inzone flag.	

Table 87: BLE_ERRORTYPESTAT_REG (0x40000060)

Bit	Mode	Symbol/Description	Reset
17	R	CONCEVTIRQ_ERROR	0x0
		Indicates whether two consecutive and concurrent ble_event_irq have been generated, and not acknowledged in time by the Bluetooth LE Software.	
		0: No error	
		1: Error occurred	
16	R	RXDATA_PTR_ERROR	0x0
		Indicates whether RX data buffer pointer value programmed is null: this is a major programming failure.	
		0: No error	
		1: Error occurred	
15	R	TXDATA_PTR_ERROR	0x0
		Indicates whether TX data buffer pointer value programmed is null during Advertising/Scanning/Initiating events, or during Master/Slave connections with non-null packet length: this is a major programming failure.	
		0: No error	
		1: Error occurred	

Bit	Mode	Symbol/Description	Reset
14	R	RXDESC_EMPTY_ERROR	0x0
		Indicates whether RX Descriptor pointer value programmed in register is null: this is a major programming failure. 0: No error	
		1: Error occurred	
13	R	TXDESC_EMPTY_ERROR	0x0
		Indicates whether TX Descriptor pointer value programmed in Control Structure is null during Advertising/Scanning/Initiating events: this is a major programming failure.	
		0: No error	
		1: Error occurred	
12	R	CSFORMAT_ERROR	0x0
		Indicates whether CS-FORMAT has been programmed with an invalid value: this is a major software programming failure.	
		0: No error	
		1: Error occurred	
11	R	LLCHMAP_ERROR	0x0
		Indicates Link Layer Channel Map error, happens when actual number of CS- LLCHMAP bit set to one is different from CS-NBCHGOOD at the beginning of Frequency Hopping process	
		0: No error	
		1: Error occurred	
10	R	ADV_UNDERRUN	0x0
		Indicates Advertising Interval Under run, occurs if time between two consecutive Advertising packet (in Advertising mode) is lower than the expected value.	
		0: No error	
		1: Error occurred	
9	R	IFS_UNDERRUN	0x0
		Indicates Inter Frame Space Under run, occurs if IFS time is not enough to update and read Control Structure/Descriptors, and/or White List parsing is not finished and/or Decryption time is too long to be finished on time	
		0: No error	
		1: Error occurred	
8	R	WHITELIST_ERROR	0x0
		Indicates White List Timeout error, occurs if White List parsing is not finished on time	
		0: No error	
		1: Error occurred	
7	R	EVT_CNTL_APFM_ERROR	0x0
		Indicates Anticipated Pre-Fetch Mechanism error: happens when two consecutive events are programmed, and when the first event is not completely finished while second pre-fetch instant is reached.	
		0: No error	
		1: Error occurred	
6	R	EVT_SCHDL_APFM_ERROR	0x0
		Indicates Anticipated Pre-Fetch Mechanism error: happens when two consecutive events are programmed, and when the first event is not completely finished while second pre-fetch instant is reached.	

Bit	Mode	Symbol/Description	Reset
		0: No error	
		1: Error occurred	
5	R	EVT_SCHDL_ENTRY_ERROR	0x0
		Indicates Event Scheduler faced Invalid timing programing on two consecutive ET entries (for example, first one with 624 s offset and second one with no offset) 0: No error 1: Error occurred	
4	R	EVT_SCHDL_EMACC_ERROR	0x0
		Indicates Event Scheduler Exchange Memory access error, happens when Exchange Memory accesses are not served in time, and blocks the Exchange Table entry read 0: No error 1: Error occurred	
3	R	RADIO_EMACC_ERROR	0x0
		Indicates Radio Controller Exchange Memory access error, happens when Exchange Memory accesses are not served in time and data are corrupted. 0: No error 1: Error occurred	
2	R	PKTCNTL_EMACC_ERROR	0x0
		Indicates Packet Controller Exchange Memory access error, happens when Exchange Memory accesses are not served in time and TX/RX data are corrupted 0: No error 1: Error occurred	
1	R	RXCRYPT_ERROR	0x0
•		Indicates real time decryption error, happens when AES-CCM decryption is too slow compared to Packet Controller requests. A 16-bytes block has to be decrypted prior the next block is received by the Packet Controller 0: No error 1: Error occurred	
0	R	TXCRYPT_ERROR	0x0
		Indicates Real Time encryption error, happens when AES-CCM encryption is too slow compared to Packet Controller requests. A 16-bytes block has to be encrypted and prepared on Packet Controller request, and needs to be ready before the Packet Controller has to send ti	
		0: No error	
		1: Error occurred	

Table 88: BLE_SWPROFILING_REG (0x40000064)

Bit	Mode	Symbol/Description	Reset
31:0	R/W	SWPROFVAL	0x0
		Software Profiling register: used by Bluetooth LE Software for profiling purpose: this value is copied on Diagnostic port.	OXO

Table 89: BLE_RADIOCNTL1_REG (0x40000074)

Bit	Mode	Symbol/Description	Reset
31:21	-	-	0x0

Bit	Mode	Symbol/Description	Reset
		Reserved	
20:16	R/W	XRFSEL	0x0
		Extended radio selection field, Must be set to "2".	

Table 90: BLE_RADIOPWRUPDN_REG (0x40000080)

Bit	Mode	Symbol/Description	Reset
30:24	R/W	RTRIP_DELAY	0x0
		Defines round trip delay value. This value corresponds to the addition of data latency in TX and data latency in RX. The value is in μ s.	
23:16	R/W	RXPWRUP	0xD2
		This register holds the length in μs of the RX powerup phase for the current radio device. The default value is 210 μs (reset value). Operating range depends on the selected radio.	
11:8	R/W	TXPWRDN	0x3
		This register extends the length in μs of the TX powerdown phase for the current radio device. The default value is 3 μs (reset value). Operating range depends on the selected radio.	
7:0	R/W	TXPWRUP	0xD2
		This register holds the length in μs of the TX powerup phase for the current radio device. The default value is 210 μs (reset value). Operating range depends on the selected radio.	

Table 91: BLE_ADVCHMAP_REG (0x40000090)

Bit	Mode	Symbol/Description	Reset
2:0	R/W	ADVCHMAP	0x7
		Advertising Channel Map, defined as per the advertising connection settings. Contains advertising channels index 37 to 39. If ADVCHMAP[i] equals:	
		0: Do not use data channel i+37	
		1: Use data channel i+37	

Table 92: BLE_ADVTIM_REG (0x400000A0)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	ADVINT	0x0
		Advertising Packet Interval defines the time interval in between two ADV_xxx packet sent. Value is in µs.	
		Value to program depends on the used Advertising Packet type and the device filtering policy.	

Table 93: BLE_ACTSCANSTAT_REG (0x400000A4)

Bit	Mode	Symbol/Description	Reset
24:16	R	BACKOFF	0x1
		Active scan mode back-off counter initialization value.	
8:0	R	UPPERLIMIT	0x1
		Active scan mode upper limit counter value.	

Table 94: BLE_WLPUBADDPTR_REG (0x400000B0)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	WLPUBADDPTR	0x0
		Start address pointer of the public devices whitelist.	

Table 95: BLE_WLPRIVADDPTR_REG (0x400000B4)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	WLPRIVADDPTR	0x0
		Start address pointer of the private devices whitelist.	

Table 96: BLE_WLNBDEV_REG (0x400000B8)

Bit	Mode	Symbol/Description	Reset
15:8	R/W	NBPRIVDEV	0x0
		Number of private devices in the whitelist.	
7:0	R/W	NBPUBDEV	0x0
		Number of public devices in the whitelist.	

Table 97: BLE_AESCNTL_REG (0x400000C0)

Bit	Mode	Symbol/Description	Reset
1	R/W	AES_MODE	0x0
		0: Cipher mode	
		1: Decipher mode	
0	R0/W	AES_START	0x0
		Writing 1 starts AES-128 ciphering/deciphering process.	
		This bit is reset when the process is finished (ble_crypt_irq interrupt occurs, even masked).	

Table 98: BLE_AESKEY31_0_REG (0x400000C4)

Bit	Mode	Symbol/Description	Reset
31:0	R/W	AESKEY31_0	0x0
		AES encryption 128-bit key. Bit 31 down to 0	

Table 99: BLE_AESKEY63_32_REG (0x400000C8)

Bit	Mode	Symbol/Description	Reset
31:0	R/W	AESKEY63_32	0x0
		AES encryption 128-bit key. Bit 63 down to 32	

Table 100: BLE_AESKEY95_64_REG (0x400000CC)

Bit	Mode	Symbol/Description	Reset
31:0	R/W	AESKEY95_64	0x0

Bit	Mode	Symbol/Description	Reset
		AES encryption 128-bit key. Bit 95 down to 64	

Table 101: BLE_AESKEY127_96_REG (0x400000D0)

Bit	Mode	Symbol/Description	Reset
31:0	R/W	AESKEY127_96	0x0
		AES encryption 128-bit key. Bit 127 down to 96	

Table 102: BLE_AESPTR_REG (0x400000D4)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	AESPTR	0x0
		Pointer to the memory zone where the block to cipher/decipher using AES-128 is stored.	

Table 103: BLE_TXMICVAL_REG (0x400000D8)

Bit	Mode	Symbol/Description	Reset
31:0	R	TXMICVAL	0x0
		AES-CCM plain MIC value. Valid on when MIC has been calculated (in TX).	

Table 104: BLE_RXMICVAL_REG (0x400000DC)

Bit	Mode	Symbol/Description	Reset
31:0	R	RXMICVAL	0x0
		AES-CCM plain MIC value. Valid on when MIC has been extracted from RX packet.	

Table 105: BLE_RFTESTCNTL_REG (0x400000E0)

Bit	Mode	Symbol/Description	Reset
31	R/W	INFINITERX	0x0
		Applicable in RF Test Mode only	
		0: Normal mode of operation	
		1: Infinite RX window	
27	R/W	RXPKTCNTEN	0x0
		Applicable in RF Test Mode only	
		0: RX packet count disabled	
		1: RX packet count enabled, and reported in CS-RXCCMPKTCNT and BLE_RFTESTRXSTAT_REG[RXPKTCNT] on RF abort command	
15	R/W	INFINITETX	0x0
		Applicable in RF Test Mode only	
		0: Normal mode of operation	
		1: Infinite TX packet/Normal start of a packet but endless payload	
14	R/W	TXLENGTHSRC	0x0
		Applicable only in TX/RX RF Test mode	

Mode	Symbol/Description	Reset
	0: Normal mode of operation: TxDESC-TXADVLEN controls the TX packet payload size	
	Uses BLE_RFTESTCNTL_REG[TXLENGTH] packet length (can support up to 512 bytes transmit)	
R/W	PRBSTYPE	0x0
	Applicable only in TX/RX RF Test mode 0: TX Packet Payload are PRBS15 type 1: TX Packet Payload are PRBS15 type	
R/W	TXPLDSRC	0x0
	Applicable only in TX/RX RF Test mode 0: TX Packet Payload source is the Control Structure 1: TX Packet Payload are PRBS generator	
R/W	TXPKTCNTEN Applicable in RF Test mode only 0: TX packet count disabled 1: TX packet count enabled, and reported in CS-TXCCMPKTCNT and	0x0
R/W	TXLENGTH	0x0
	Applicable only for TX/RX RF Test mode, and valid when BLE_RFTESTCNTL_REG[TXLENGTHSRC] = 1	
	R/W R/W	0: Normal mode of operation: TxDESC-TXADVLEN controls the TX packet payload size 1: Uses BLE_RFTESTCNTL_REG[TXLENGTH] packet length (can support up to 512 bytes transmit) R/W PRBSTYPE Applicable only in TX/RX RF Test mode 0: TX Packet Payload are PRBS9 type 1: TX Packet Payload are PRBS15 type R/W TXPLDSRC Applicable only in TX/RX RF Test mode 0: TX Packet Payload source is the Control Structure 1: TX Packet Payload are PRBS generator R/W TXPKTCNTEN Applicable in RF Test mode only 0: TX packet count disabled 1: TX packet count enabled, and reported in CS-TXCCMPKTCNT and BLE_RFTESTTXSTAT_REG[TXPKTCNT] on RF abort command R/W TXLENGTH Applicable only for TX/RX RF Test mode, and valid when

Table 106: BLE_RFTESTTXSTAT_REG (0x400000E4)

Bit	Mode	Symbol/Description	Reset
31:0	R	TXPKTCNT	0x0
		Reports number of transmitted packet during Test modes. Value is valid if BLE_RFTESTCNTL_REG[TXPKTCNTEN] is set.	

Table 107: BLE_RFTESTRXSTAT_REG (0x400000E8)

Bit	Mode	Symbol/Description	Reset
31:0	R	RXPKTCNT	0x0
		Reports number of correctly received packet during Test Modes (no sync error, no CRC error).	
		Value is valid if BLE_RFTESTCNTL_REG[RXPKTCNTEN] is set	

Table 108: BLE_TIMGENCNTL_REG (0x400000F0)

Bit	Mode	Symbol/Description	Reset
31	R/W	APFM_EN	0x1
		Controls the Anticipated pre-Fetch Abort mechanism 0: Disabled 1: Enabled	
25:16	R/W	PREFETCHABORT_TIME	0x1FE
		Defines the instant in μ s at which immediate abort is required after anticipated prefetch abort.	

Bit	Mode	Symbol/Description	Reset
8:0	R/W	PREFETCH_TIME	0x96
		Defines Exchange Table pre-fetch instant in µs	

Table 109: BLE_GROSSTIMTGT_REG (0x400000F4)

Bit	Mode	Symbol/Description	Reset
22:0	R/W	GROSSTARGET	0x0
		Gross Timer Target value on which a ble_grosstgtim_irq must be generated. This timer has a precision of 10 ms: interrupt is generated only when GROSSTARGET[22:0] = BASETIMECNT[26:4] and BASETIMECNT[3:0] = 0.	

Table 110: BLE_FINETIMTGT_REG (0x400000F8)

Bit	Mode	Symbol/Description	Reset
26:0	R/W	FINETARGET	0x0
		Fine Timer Target value on which a ble_finetgtim_irq must be generated. This timer has a precision of 625 μs: interrupt is generated only when FINETARGET = BASETIMECNT	

Table 111: BLE_SAMPLECLK_REG (0x400000FC)

Bit	Mode	Symbol/Description	Reset
31:1	-	-	0x0
		Reserved	
0	R0/W	SAMP	0x0
		Writing a 1 samples the Base Time Counter value in BASETIMECNT register. Resets at 0 when action is performed.	

Table 112: BLE_COEXIFCNTL0_REG (0x40000100)

Bit	Mode	Symbol/Description	Reset
21:20	R/W	WLCRXPRIOMODE	0x0
		Defines Bluetooth Low Energy packet ble_rx mode behavior. 00: RX indication excluding RX Powerup delay (starts when correlator is enabled) 01: RX indication including RX Powerup delay 10: RX High priority indicator 11: n/a	
17:16	R/W	WLCTXPRIOMODE Defines Bluetooth Low Energy packet ble_tx mode behavior 00: TX indication excluding TX Powerup delay 01: TX indication including TX Powerup delay 10: TX High priority indicator 11: n/a	0x0
7:6	R/W	WLANTXMSK Determines how wlan_tx impact Bluetooth LE TX and RX 00: wlan_tx has no impact (default mode) 01: wlan_tx can stop Bluetooth LE TX, no impact on Bluetooth LE RX	0x0

Bit	Mode	Symbol/Description	Reset
		10: wlan_tx can stop Bluetooth LE RX, no impact on Bluetooth LE TX	
		11: wlan_tx can stop both Bluetooth LE TX and Bluetooth LE RX	
5:4	R/W	WLANRXMSK	0x1
		Determines how wlan_rx impact Bluetooth LE TX and RX	
		00: wlan_rx has no impact	
		01: wlan_rx can stop Bluetooth LE TX, no impact on Bluetooth LE RX (default mode)	
		10: wlan_rx can stop Bluetooth LE RX, no impact on Bluetooth LE TX	
		11: wlan_rx can stop both Bluetooth LE TX and Bluetooth LE RX	
1	R/W	SYNCGEN_EN	0x0
		Determines whether ble_sync is generated or not.	
		0: ble_sync pulse not generated	
		1: ble_sync pulse generated	
0	R/W	COEX_EN	0x0
		Enable/Disable control of the MWS/WLAN Coexistence control	
		0: Coexistence interface disabled	
		1: Coexistence interface enabled	

Table 113: BLE_COEXIFCNTL1_REG (0x40000104)

Bit	Mode	Symbol/Description	Reset
28:24	R/W	WLCPRXTHR	0x0
		Applies on ble_rx if WLCRXPRIOMODE equals 10	
		Determines the threshold for RX priority setting.	
		If ble_pti[3:0] output value is greater than WLCPRXTHR, then RX Bluetooth Low Energy priority is considered as high, and must be provided to the WLAN coexistence interface.	
20:16	R/W	WLCPTXTHR	0x0
		Applies on ble_tx if WLCTXPRIOMODE equals 10	
		Determines the threshold for priority setting.	
		If ble_pti[3:0] output value is greater than WLCPTXTHR, then TX Bluetooth Low Energy priority is considered as high, and must be provided to the WLAN coexistence interface.	
14:8	R/W	WLCPDURATION	0x0
		Applies on ble_tx if WLCTXPRIOMODE equals 10.	
		Applies on ble_rx if WLCRXPRIOMODE equals 10.	
		Determines how many s the priority information must be maintained.	
		Note that if WLCPDURATION = 0x00, then TX/RX priority levels are maintained till TX/RX EN are deasserted.	
6:0	R/W	WLCPDELAY	0x0
		Applies on ble_tx if WLCTXPRIOMODE equals 10.	
		Applies on ble_rx if WLCRXPRIOMODE equals 10.	
		Determines the delay (in μs) in TX/RX enables rises the time Bluetooth Low energy TX/RX priority has to be provided.	

Table 114: BLE_BLEMPRIOO_REG (0x40000108)

Bit	Mode	Symbol/Description	Reset
31:28	R/W	BLEM7	0x3
		Set Priority value for Passive Scanning	
27:24	R/W	BLEM6	0x4
		Set Priority value for Non-Connectable Advertising	
23:20	R/W	BLEM5	0x8
		Set Priority value for Connectable Advertising BLE message	
19:16	R/W	BLEM4	0x9
		Set Priority value for Active Scanning Bluetooth LE message	
15:12	R/W	BLEM3	0xA
		Set Priority value for Initiating (Scanning) Bluetooth LE message	
11:8	R/W	BLEM2	0xD
		Set Priority value for Data Channel transmission Bluetooth LE message	
7:4	R/W	BLEM1	0xE
		Set Priority value for LLCP Bluetooth LE message	
3:0	R/W	BLEM0	0xF
		Set Priority value for Initiating (Connection Request Response) Bluetooth LE message	

Table 115: BLE_BLEMPRIO1_REG (0x4000010C)

Bit	Mode	Symbol/Description	Reset
31:28	R/W	BLEMDEFAULT	0x3
		Set the default priority value for other Bluetooth LE messages than those defined above.	

Table 116: BLE_CNTL2_REG (0x40000200)

Bit	Mode	Symbol/Description	Reset
31:25	R	-	0x0
		Reserved	
24	R/W	BLE_PHY_ERR_MSK_N	0x0
23	R/W	BLE_ARP_ERR_MSK_N	0x0
		When cleared to "0", then it masks the BLE_ARP_ERR_STAT to not trigger the BLE_ERROR_IRQ.	
22	RW1C	BLE_ARP_PHY_ERR_STAT	0x0
		When set to "1", then an error occurred in Bluetooth LE ARP subblock and the BLE_GEN_IRQ is asserted.	
		It is set if ARP_ERROR or PHY_ERROR is asserted and if BLE_ARP_ERR_MSK is set to "1".	
		Writing the value "1" acknowledges and clears this field.	
21	R/W	BLE_RSSI_SEL	0x0
		0: (default) Select Peak-hold RSSI value during the SYNC_FOUND event:	

Bit	Mode	Symbol/Description	Reset
		CS->RXRSSI[7:0] = RF_RSSI_RESULT_REG->RSSI_LATCHED_RD[9:2].	
		1: Select the Average RSSI value during the SYNC_FOUND event:	
		CS->RXRSSI[7:0] = RF_RSSI_RESULT_REG->RSSI_AVG_RD[9:2].	
20	R	WAKEUPLPSTAT	0x0
		The status of the BLE_WAKEUP_LP_IRQ. The Interrupt Service Routine of BLE_WAKEUP_LP_IRQ should return only when the WAKEUPLPSTAT is cleared.	
		Note that BLE_WAKEUP_LP_IRQ is automatically acknowledged after the powerup of the Radio Subsystem, plus one Low Power Clock period.	
19	R/W	SW_RPL_SPI	0x0
		Keep to 0.	
18	R/W	BB_ONLY	0x0
		Keep to 0.	
17	R/W	BLE_PTI_SOURCE_SEL	0x0
		0: Provide to COEX block the PTI value indicated by the Control Structure. Recommended value is "0".	
		1: Provide to COEX block the PTI value generated dynamically by the Bluetooth LE core, which is based on the PTI of the Control Structure.	
16:15	R	-	0x0
		Reserved	
14:9	R/W	BLE_CLK_SEL	0x0
		Bluetooth LE Clock Select.	
		Specifies the Bluetooth LE master clock absolute frequency in MHz.	
		Typical values are 16 and 8.	
		Value depends on the selected XTAL frequency and the value of CLK_RADIO_REG[BLE_DIV] bitfield. For example, if XTAL oscillates at 16 MHz and CLK_RADIO_REG[BLE_DIV] = 1 (divide by 2), then Bluetooth LE master clock frequency is 8 MHz and BLE_CLK_SEL should be set to value 8.	
		The selected Bluetooth LE master clock frequency (affected by BLE_DIV and BLE_CLK_SEL) must be modified and set only during the initialization time, that is before setting BLE_RWBLECNTL_REG[RWBLE_EN] to 1.	
		Also see BLE_RWBLECONF_REG[CLK_SEL].	
8	R	RADIO_PWRDN_ALLOW	0x0
		This active high signal indicates when it is allowed for the Bluetooth LE core (embedded in the Radio sub-system power domain) to be powered down.	
		After the assertion of the BLE_DEEPSLCNTL_REG[DEEP_SLEEP_ON], a hardware sequence based on the Low Power clock causes the assertion of RADIO_PWRDN_ALLOW. The RADIO_PWRDN_ALLOW is cleared to "0" when the Bluetooth LE core exits from the SLEEP state, when the BLE_SLP_IRQ is asserted.	
7	R	MON_LP_CLK	0x0
		The software can only write a "0" to this bit.	
		Whenever a positive edge of the low power clock used by the Bluetooth LE Timers is detected, then the hardware automatically sets this bit to "1". This functionality does not work if Bluetooth LE Timer is in RESET state (see CLK_RADIO_REG[BLE_LP_RESET]).	
		This bit can be used for software synchronization, to debug the low power clock, and so on.	
6	R	BLE_CLK_STAT	0x0
		0: Bluetooth LE uses low power clock	

Bit	Mode	Symbol/Description	Reset
		1: Bluetooth LE uses master clock	
5:4	R/W	-	0x0
		Reserved	
3	R/W	BLE_DIAG_OVR	0x0
		1: Overrule BLE_DIAG.	
		0: BLE_DIAG is not overruled.	
2	R/W	EMACCERRMSK	0x1
		Exchange Memory Access Error Mask:	
		When cleared to "0", the EM_ACC_ERR does not cause the BLE_ERROR_IRQ interrupt.	
		When set to "1", BLE_ERROR_IRQ is generated as long as EM_ACC_ERR is "1".	
1	R0/W	EMACCERRACK	0x0
		Exchange Memory Access Error Acknowledge.	
		When the software writes a "1" to this bit, then the EMACCERRSTAT bit is cleared.	
		When the software writes "0", it has no effect.	
		The read value is always "0".	
0	R	EMACCERRSTAT	0x0
		Exchange Memory Access Error Status:	
		The bit is read-only and can be cleared only by writing a "1" at EMACCERRACK bitfield.	
		This bit is set to "1" by the hardware when the controller accesses an EM page that is not mapped according to the EM_MAPPING value.	
		When this bit is "1", then BLE_ERROR_IRQ is asserted as long as EMACCERRMSK is "1".	

Table 117: BLE_EM_BASE_REG (0x40000208)

Bit	Mode	Symbol/Description	Reset
31:17	R	-	0x0
		Reserved	
16:10	R/W	BLE_EM_BASE_16_10	0x0
		The physical address on the system memory map of the base of the Exchange Memory.	
9:0	R	-	0x0
		Reserved	

Table 118: BLE_DIAGCNTL2_REG (0x4000020C)

Bit	Mode	Symbol/Description	Reset
31	R/W	DIAG7_EN	0x0
		Disable diagnostic port 0 output. All outputs are set to 0x0. Enable diagnostic port 0 output.	
30	R	-	0x0
		Reserved	
29:24	R/W	DIAG7	0x0

Bit	Mode	Symbol/Description	Reset
		Only relevant when DIAG7_EN = 1. Selection of the outputs that must be driven to the diagnostic port BLE_DIAG7.	
23	R/W	DIAG6_EN	0x0
		O: Disable diagnostic port 0 output. All outputs are set to 0x0. 1: Enable diagnostic port 0 output.	
22	R	-	0x0
		Reserved	
21:16	R/W	DIAG6	0x0
		Only relevant when DIAG6_EN = 1. Selection of the outputs that must be driven to the diagnostic port BLE_DIAG6.	
15	R/W	DIAG5_EN	0x0
		0: Disable diagnostic port 0 output. All outputs are set to 0x0.1: Enable diagnostic port 0 output.	
14	R	-	0x0
		Reserved	
13:8	R/W	DIAG5	0x0
		Only relevant when DIAG5_EN = 1. Selection of the outputs that must be driven to the diagnostic port BLE_DIAG5.	
7	R/W	DIAG4_EN	0x0
		0: Disable diagnostic port 0 output. All outputs are set to 0x0.1: Enable diagnostic port 0 output.	
6	R	-	0x0
		Reserved	
5:0	R/W	DIAG4	0x0
		Only relevant when DIAG4_EN = 1. Selection of the outputs that must be driven to the diagnostic port BLE_DIAG4.	

Table 119: BLE_DIAGCNTL3_REG (0x40000210)

Bit	Mode	Symbol/Description	Reset
31	R/W	DIAG7_INV	0x0
		If set, then the specific diagnostic bit is inverted.	
30:28	R/W	DIAG7_BIT	0x0
		Selects which bit from the DIAG7 word is forwarded to bit 7 of the Bluetooth LE Dlagnostic Port.	
27	R/W	DIAG6_INV	0x0
		If set, then the specific diagnostic bit is inverted.	
26:24	R/W	DIAG6_BIT	0x0
		Selects which bit from the DIAG6 word is forwarded to bit 6 of the Bluetooth LE Dlagnostic Port.	
23	R/W	DIAG5_INV	0x0
		If set, then the specific diagnostic bit is inverted.	
22:20	R/W	DIAG5_BIT	0x0

Bit	Mode	Symbol/Description	Reset
		Selects which bit from the DIAG5 word is forwarded to bit 5 of the Bluetooth LE DIagnostic Port.	
19	R/W	DIAG4_INV	0x0
		If set, then the specific diagnostic bit is inverted.	
18:16	R/W	DIAG4_BIT	0x0
		Selects which bit from the DIAG4 word is forwarded to bit 4 of the Bluetooth LE Dlagnostic Port.	
15	R/W	DIAG3_INV	0x0
		If set, then the specific diagnostic bit is inverted.	
14:12	R/W	DIAG3_BIT	0x0
		Selects which bit from the DIAG3 word is forwarded to bit 3 of the Bluetooth LE Dlagnostic Port.	
11	R/W	DIAG2_INV	0x0
		If set, then the specific diagnostic bit is inverted.	
10:8	R/W	DIAG2_BIT	0x0
		Selects which bit from the DIAG2 word is forwarded to bit 2 of the Bluetooth LE Dlagnostic Port.	
7	R/W	DIAG1_INV	0x0
		If set, then the specific diagnostic bit is inverted.	
6:4	R/W	DIAG1_BIT	0x0
		Selects which bit from the DIAG1 word is forwarded to bit 1 of the Bluetooth LE Dlagnostic Port.	
3	R/W	DIAG0_INV	0x0
		If set, then the specific diagnostic bit is inverted.	
2:0	R/W	DIAG0_BIT	0x0
		Selects which bit from the DIAG0 word is forwarded to bit 0 of the Bluetooth LE DIagnostic Port.	

32.3 Clock Generation and Reset Registers

Table 120: Register map CRG

Address	Register	Description
0x50000000	CLK_AMBA_REG	HCLK, PCLK, divider and clock gates
0x50000002	CLK_FREQ_TRIM_REG	Xtal frequency trimming register
0x50000004	CLK_PER_REG	Peripheral divider register
0x50000008	CLK_RADIO_REG	Radio PLL control register
0x5000000a	CLK_CTRL_REG	Clock control register
0x50000010	PMU_CTRL_REG	Power Management Unit control register
0x50000012	SYS_CTRL_REG	System Control register
0x50000014	SYS_STAT_REG	System status register
0x50000016	TRIM_CTRL_REG	Control trimming of the XTAL32M
0x50000018	RAM_PWR_CTRL_REG	Control power state of System RAMS
0x50000020	CLK_RC32K_REG	32 kHz RC oscillator register

Address	Register	Description
0x50000022	CLK_XTAL32K_REG	32 kHz XTAL oscillator register
0x50000024	CLK_RC32M_REG	Fast RC control register
0x50000026	CLK_RCX_REG	RCX-oscillator control register
0x50000028	BANDGAP_REG	Bandgap trimming
0x5000002a	ANA_STATUS_REG	Status bit of analog (power management) circuits
0x50000030	XTAL32M_START_REG	Trim values for XTAL32M
0x50000032	XTAL32M_TRSTAT_REG	Read back value of current XTAL trimming
0x50000034	XTALRDY_CTRL_REG	Control register for XTALRDY IRQ
0x50000038	XTAL32M_CTRL0_REG	Control bits for XTAL32M
0x50000040	POR_PIN_REG	Selects a GPIO pin for POR generation
0x50000042	POR_TIMER_REG	Time for POR to happen
0x50000050	PMU_SLEEP_REG	Bandgap refresh interval during sleep
0x50000052	POWER_CTRL_REG	Power management control
0x50000054	POWER_LEVEL_REG	Power management level and trim settings

Table 121: CLK_AMBA_REG (0x50000000)

Bit	Mode	Symbol/Description	Reset
7	R/W	OTP_ENABLE	0x0
		Clock enable for OTP controller	
6	R/W	-	0x0
		Reserved	
5:4	R/W	PCLK_DIV	0x0
		APB interface clock (PCLK). Divider is cascaded with HCLK_DIV. PCLK is HCLK divided by:	
		0x0: divide by 1	
		0x1: divide by 2	
		0x2: divide by 4	
		0x3: divide by 8	
3:2	R/W	-	0x0
		Reserved	
1:0	R/W	HCLK_DIV	0x0
		AHB interface and microprocessor clock (HCLK). HCLK is source clock divided by: 0x0: divide by 1	
		0x1: divide by 2	
		0x2: divide by 4	
		0x3: divide by 8	

Table 122: CLK_FREQ_TRIM_REG (0x50000002)

Bit	Mode	Symbol/Description	Reset
7:0	R/W	XTAL32M_TRIM	0x80
		XTAL frequency fine trimming register.	
		0x00: Highest frequency	

Bit	Mode	Symbol/Description	Reset
		0xFF: Lowest frequency	

Table 123: CLK_PER_REG (0x50000004)

Bit	Mode	Symbol/Description	Reset
11	R/W	QUAD_ENABLE	0x1
		Enable the Quadrature clock	
10	R/W	SPI_ENABLE	0x0
		Enable SPI clock	
9:8	R/W	-	0x0
		Reserved	
7	R/W	UART1_ENABLE	0x0
		Enable UART1 clock	
6	R/W	UART2_ENABLE	0x0
		Enable UART2 clock	
5	R/W	I2C_ENABLE	0x0
		Enable I2C clock	
4	R/W	WAKEUPCT_ENABLE	0x0
		Enable Wakeup CaptureTimer clock	
3	R/W	TMR_ENABLE	0x0
		Enable TIMER0 and TIMER2 clock	
2	R/W	-	0x0
		Reserved	
1:0	R/W	TMR_DIV	0x0
		Division factor for TIMER0	
		0x0: divide by 1	
		0x1: divide by 2	
		0x2: divide by 4	
		0x3: divide by 8	

Table 124: CLK_RADIO_REG (0x50000008)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7	R/W	BLE_ENABLE	0x0
		Enable the BLE core clocks	
6	R/W	BLE_LP_RESET	0x1
		Reset for the BLE LP timer	
5:4	R/W	BLE_DIV	0x0
		Division factor for BLE core blocks	
		0x0: divide by 1	
		0x1: divide by 2	
		0x2: divide by 4	

Bit	Mode	Symbol/Description	Reset
		0x3: divide by 8	
		The programmed frequency should not be lower than 8 MHz and not faster than the programmed CPU clock frequency. Also see BLE_CNTL2_REG[BLE_CLK_SEL].	
3	R/W	RFCU_ENABLE	0x0
		Enable the RF control Unit clock	
2	R/W	-	0x0
		Reserved	
1:0	R/W	-	0x0
		Reserved	

Table 125: CLK_CTRL_REG (0x5000000A)

Bit	Mode	Symbol/Description	Reset
7	R	RUNNING_AT_XTAL32M	0x0
		Indicates that the XTAL32M clock is used as clock, and may not be switched off	
6	R	RUNNING_AT_RC32M	0x1
		Indicates that the RC32M clock is used as clock	
5	R	RUNNING_AT_LP_CLK	0x0
		Indicates that either the LP_CLK is being used as system clock	
4:3	R/W	LP_CLK_SEL	0x0
		Sets the clock source of the LowerPower clock 0x0: RC32K 0x1: RCX 0x2: XTAL32K through the oscillator with an external Crystal. 0x3: XTAL32K through an external square wave generator (set PID of P0[3] to FUNC_GPIO) Change this setting before using this clock, and while RUNNING_AT_LP_CLK ==	
2	R/W	N XTAL32M_DISABLE Setting this bit instantaneously disables the 32 MHz crystal oscillator. Also, after sleep/wakeup cycle, the oscillator will not be enabled. This bit may not be set to '1' when "RUNNING_AT_XTAL32M is '1' to prevent deadlock. After resetting this bit, wait for XTAL32M_SETTLED or XTAL32M_TRIM_READY to become '1' before switching to XTAL32M clock source.	
1:0	R/W	SYS_CLK_SEL	0x1
		Selects the clock source. 0x0: XTAL32M (check the XTAL32M_SETTLED and XTAL32M_TRIM_READY bits!!) 0x1: RC32M 0x2/0x3: LP CLK	

Table 126: PMU_CTRL_REG (0x50000010)

Bit	Mode	Symbol/Description	Reset
6	R/W	MAP_BANDGAP_EN	0x0

Bit	Mode	Symbol/Description	Reset
		Enable wake-up diagnostics mapping. When set, these functions are mapped (set direction to output)	
		P0[2]: BANDGAP_ENABLE	
		P0[1]: Power WOKENUP	
		Note: P0[2] assigned also to SWD_CLK, thus the debugger must be detached before entering into sleep mode with MAP_BANDGAP_EN=1. Also see SYS_STAT_REG->DBG_IS_UP.	
5:4	R/W	OTP_COPY_DIV	0x0
		Sets the HCLK division during OTP mirroring	
3	R/W	-	0x0
		Reserved	
2	R/W	RADIO_SLEEP	0x1
		Put the digital part of the radio in powerdown	
1	R/W	TIM_SLEEP	0x1
		Put PD_TIM in powerdown	
0	R/W	RESET_ON_WAKEUP	0x0
		Perform a Hardware Reset after waking up. Booter will be started.	

Table 127: SYS_CTRL_REG (0x50000012)

Bit	Mode	Symbol/Description	Reset
15	W	SW_RESET	0x0
		Writing a '1' to this bit will reset the device, except for: SYS_CTRL_REG CLK_FREQ_TRIM_REG	
10	R/W	TIMEOUT_DISABLE	0x0
		Disables timeout in Power statemachine. By default, the statemachine continues if after 2 ms the blocks are not started up. This can be read back from ANA_STATUS_REG.	
9	R/W	-	0x0
		Reserved	
8:7	R/W	DEBUGGER_ENABLE	0x0
		Enable the debugger. This bit is set by the booter according to the OTP header. If not set, the SWDIO and SW_CLK can be used as GPIO ports. 0x0: no debugger enabled. 0x1: SW_CLK = P0[2], SW_DIO=P0[5]	
		0x2: SW_CLK = P0[2], SW_DIO=P0[1]	
		0x3: SW_CLK = P0[2], SW_DIO=P0[10]	
6	R/W	OTPC_RESET_REQ	0x0
		Reset request for the OTP controller.	
5	R/W	-	0x1
		Reserved	
4	R/W	OTP_COPY	0x0
		Enables OTP to SysRAM copy action after waking up PD_SYS	

Bit	Mode	Symbol/Description	Reset
3	R/W	-	0x0
		Reserved	
2	R/W	DEV_PHASE	0x0
		Sets the development phase mode.	
		If this bit is set, in combination with the OTP_COPY bit, the OTP DMA will emulate the OTP mirroring to System RAM.	
		No actual writing to RAM is done, but the exact same amount of time is spend as if the mirroring would take place. This is to mimic the behavior as if the System Code is already in OTP, and the mirroring takes place after waking up, but the (development) code still resides in an external source.	
		If this bit is set to 0 and OTP_COPY = 1, then the OTP DMA will actually do the OTP mirroring at wake-up.	
1:0	R/W	REMAP_ADR0	0x0
		Controls which memory is located at address 0x0000 for execution. 0x0: ROM 0x1: OTP	
		0x2: RAM (SysRAM1)	
		0x3: RAM (SysRAM3, 28 kB offset) This bitfield only takes affect after a Software Reset.	

Table 128: SYS_STAT_REG (0x50000014)

Bit	Mode	Symbol/Description	Reset
7	R	XTAL32M_SETTLED	0x0
		Indicates that XTAL32M has had its settle time, as defined by TRIM_CTRL_REG[XTAL_SETTLE_N]	
6	R	XTAL32M_TRIM_READY	0x1
		Indicates that XTAL trimming mechanism is ready, that is the trimming equals CLK_FREQ_TRIM_REG.	
5	R	-	0x0
		Reserved	
4	R	DBG_IS_UP	0x0
		Indicates that the SW debugger is attached and in connection with the Cortex	
3	R	TIM_IS_UP	0x0
		Indicates that PD_TIM is functional	
2	R	TIM_IS_DOWN	0x1
		Indicates that PD_TIM is in power down	
1	R	RAD_IS_UP	0x0
		Indicates that PD_RAD is functional	
0	R	RAD_IS_DOWN	0x1
		Indicates that PD_RAD is in power down	

Table 129: TRIM_CTRL_REG (0x50000016)

Bit	Mode	Symbol/Description	Reset
13:8	R/W	XTAL_SETTLE_N	0x3F
		Designates that the XTAL can be safely used as the CPU clock. When XTAL_CLK_CNT reases this value, the signal XTAL32M_SETTLED bit in the SYS_STAT_REG will be set. Counts in steps of 64 XTAL clock-cycles.	
7:6	R/W	XTAL_TRIM_SELECT	0x0
		Select which source controls the XTAL trimming	
		0b00: xtal counter. Starts XTAL32M_START_REG[XTAL32M_START] after COUNT_N * 32 xtal pulses trim is changed to CLK_FREQ_TRIM_REG[XTAL32M_TRIM].	
		0b01: xtal OK filter. Starts with CLK_FREQ_TRIM_REG[XTAL32M_START], when xtal amplitude is ramping is changed to CLK_FREQ_TRIM_REG[XTAL32M_TRIM].	
		0b10: statically forced off. Only uses CLK_FREQ_TRIM_REG[XTAL32M_TRIM].	
		0b11: xtal OK filter, 2 stage. Starts with CLK_FREQ_TRIM_REG[XTAL32M_START] switches to CLK_FREQ_TRIM_REG[XTAL32M_RAMP] after timeout (32 μs), and switches to CLK_FREQ_TRIM_REG[XTAL32M_TRIM] when xtal amplitude is ramping up.	
5:0	R/W	XTAL_COUNT_N	0x22
		Defines the number of XTAL cycles to be counted, before the XTAL trimming is applied, in steps of 64 cycles. 0x01: 64	
		0x02: 128	
		0x3f: 4032	

Table 130: RAM_PWR_CTRL_REG (0x50000018)

Bit	Mode	Symbol/Description	Reset
5:4	R/W	RAM3_PWR_CTRL	0x0
		See description of RAM1_PWR_CTRL	
3:2	R/W	RAM2_PWR_CTRL	0x0
		See description of RAM1_PWR_CTRL	
1:0	R/W	RAM1_PWR_CTRL	0x0
		Power state control of the individual RAMs. May only change when the memory isn't accessed.	
		When in Active or Sleep mode:	
		0x0: Normal operation	
		0x1: Normal operation	
		0x2: Retained (no access possible)	
		0x3: Off (memory content corrupted)	
		When in Extended Sleep, Deep Sleep or Hibernation mode	
		0x0: Retained	
		0x1: Off (memory content corrupted)	
		0x2: Retained	
		0x3: Off (memory content corrupted)	

Table 131: CLK_RC32K_REG (0x50000020)

Bit	Mode	Symbol/Description	Reset
4:1	R/W	RC32K_TRIM	0x7
		0000 = lowest frequency	
		0111 = default	
		1111 = highest frequency	
0	R/W	RC32K_DISABLE	0x0
		Instantly disables the 32 kHz RC oscillator	
		Sleep cycles cannot happen with this clock disabled	

Table 132: CLK_XTAL32K_REG (0x50000022)

Bit	Mode	Symbol/Description	Reset
8	R/W		0x0
		Reserved	
7	R/W	XTAL32K_DISABLE_AMPREG	0x0
		Setting this bit disables the amplitude regulation of the XTAL32kHz oscillator. Set this bit to '1' for an external clock to XTAL32Kp Keep this bit '0' with a crystal between XTAL32Kp and XTAL32Km	
6:3	R/W	XTAL32K_CUR	0x5
		Bias current for the 32 kHz XTAL oscillator. 0000 is minimum, 1111 is maximum, 0011 is default. For each application there is an optimal setting for which the start-up behavior is optimal	
2:1	R/W	XTAL32K_RBIAS	0x3
		Setting for the bias resistor. 00 is maximum, 11 is minimum. Prefered setting will be provided by Dialog	
0	R/W	XTAL32K_ENABLE	0x0
		Enables the 32 kHz XTAL oscillator.	
		Also set GP_DATA_REG[P03_P04_FILT_DIS] = 1 for lowest current consumption.	

Table 133: CLK_RC32M_REG (0x50000024)

Bit	Mode	Symbol/Description	Reset
10:7	R/W	RC32M_COSC	0xF
		C-adjust of RC-oscillator	
		A higher value of COSC results in a lower frequency	
6:5	R/W	RC32M_RANGE	0x0
		Coarse adjust	
		A higher value of RANGE results in a higher frequency, values 2 and 3 are equal	
4:1	R/W	RC32M_BIAS	0x7
		Bias adjustment	
0	R/W	RC32M_DISABLE	0x0
		Instantly disables the 32 MHz RC oscillator	
		Disabling of the oscillator during sleep happens automatically.	

Table 134: CLK_RCX_REG (0x50000026)

Bit	Mode	Symbol/Description	Reset
11:8	R/W	RCX_BIAS	0xA
		LDO bias current.	
		0x0: minimum	
		0xF: maximum	
7	R/W	RCX_C0	0x1
		Add unit capacitance to RC-time delay	
6:2	R/W	RCX_CADJUST	0x1F
		Adjust capacitance part of RC-time delay.	
		0x00: minimum capacitance	
		0x1F: maximum capacitance	
1	R/W	RCX_RADJUST	0x0
		Adjust resistance part of RC-time delay. Lower resistance increases power consumption.	
		0x0: maximum resistance	
		0x1: minimum resistance	
0	R/W	RCX_ENABLE	0x0
		Enable the RCX oscillator	

Table 135: BANDGAP_REG (0x50000028)

Bit	Mode	Symbol/Description	Reset
9:5	R/W	BGR_ITRIM	0x0
		Trim setting for bandgap bias current	
		10000 -> -25%	
		11111 -> ~0%	
		00000 -> ~0% (typ)	
		01111 -> +32%	
4:0	R/W	BGR_TRIM	0x0
		Trim setting for bandgap voltage	
		10000 -> -6.4%	
		11111 -> ~0%	
		00000 -> ~0% (typ)	
		01111 -> +5.8%	

Table 136: ANA_STATUS_REG (0x5000002A)

Bit	Mode	Symbol/Description	Reset
12	R	CLKLESS_WAKEUP_STAT	0x0
		Indicates the output of the Clockless wake-up XOR tree. If this signal is "0", the chip will wake up.	

Mode	Symbol/Description	Reset
	Use the HIBERN_WKUP_POLARITY bit to set the value to "1" before going into hibernation mode.	
R	-	0x0
	Reserved	
R	LDO_GPADC_OK	0x0
	Indicates that LDO_GPADC output is OK	
R	LDO_XTAL_OK	0x0
	Indicates that LDO_XTAL output is OK	
R	BOOST_SELECTED	0x0
	0: Buck mode detected 1: Boost mode detected	
R	POR_VBAT_HIGH	0x0
	Output of V _{BAT_HIGH} supply rail voltage monitoring circuit. 0: Voltage level on V _{BAT_HIGH} is lower than POR VBAT_HIGH threshold V _{TH_L} (rail not ok, will result in reset if not masked) 1: Voltage level on V _{BAT_HIGH} is higher than POR VBAT_HIGH threshold V _{TH_H} (rail ok, reset released)	
R	POR_VBAT_LOW	0x0
	Output of V _{BAT_LOW} supply rail voltage monitoring circuit. 0: Voltage level on V _{BAT_LOW} is lower than POR VBAT_LOW threshold V _{TH_L} (rail not ok, will result in reset if not masked) 1: Voltage level on V _{BAT_LOW} is higher than POR VBAT_LOW threshold V _{TH_H} (rail ok, reset released)	
R	BANDGAP_OK	0x0
	Indicates that BANDGAP is OK	
R	COMP_VBAT_HIGH_NOK	0x0
	Indicates that V _{BAT_HIGH} < V _{BAT_LOW} -50 mV	
R	COMP_VBAT_HIGH_OK	0x0
	Indicates that V _{BAT_HIGH} > V _{BAT_LOW} +50 mV	
R	DCDC_OK	0x0
	Indicates that V _{BAT_LOW} (buck mode) or V _{BAT_HIGH} (boost mode) is OK	
R	LDO_LOW_OK	0x0
	Indicates that LDO_LOW output is OK (only valid for high current mode)	
R	LDO_CORE_OK Indicates that LDO_CORE output is OK	0x0
	R R R R R R R R R	Use the HIBERN_WKUP_POLARITY bit to set the value to "1" before going into hibernation mode. R R Reserved R LDO_GPADC_OK Indicates that LDO_GPADC output is OK R LDO_XTAL_OK Indicates that LDO_XTAL output is OK R BOOST_SELECTED 0: Buck mode detected 1: Boost mode detected 1: Boost mode detected 1: Boost mode detected 0: Voltage level on VBAT_HIGH SUPPly rail voltage monitoring circuit. 0: Voltage level on VBAT_HIGH SUPPly rail solwer than POR VBAT_HIGH threshold VTH_L (rail not ok, will result in reset if not masked) 1: Voltage level on VBAT_HIGH is higher than POR VBAT_HIGH threshold VTH_H (rail ok, reset released) R POR_VBAT_LOW Output of VBAT_LOW solver than POR VBAT_LOW threshold VTH_L (rail not ok, will result in reset if not masked) 1: Voltage level on VBAT_LOW is lower than POR VBAT_LOW threshold VTH_L (rail not ok, will result in reset if not masked) 1: Voltage level on VBAT_LOW is higher than POR VBAT_LOW threshold VTH_H (rail ok, reset released) R BANDGAP_OK Indicates that BANDGAP is OK R COMP_VBAT_HIGH_NOK Indicates that VBAT_HIGH < VBAT_LOW +50 mV R COMP_VBAT_HIGH_OK Indicates that VBAT_HIGH > VBAT_LOW +50 mV R DCDC_OK Indicates that VBAT_HIGH > VBAT_LOW +50 mV R LDO_COMP_OK Indicates that LDO_LOW output is OK (only valid for high current mode) R LDO_CORE_OK

Table 137: XTAL32M_START_REG (0x50000030)

Bit	Mode	Symbol/Description	Reset
15:8	R/W	XTAL32M_RAMP	0x0
		Xtal frequency trimming register. 0x00 : highest frequency 0xFF :lowest frequency	
7:0	R/W	XTAL32M_START	0xAA

Bit	Mode	Symbol/Description	Reset
		Xtal frequency trimming register.	
		0x0 = highest frequency	
		0xF = lowest frequency	

Table 138: XTAL32M_TRSTAT_REG (0x50000032)

Bit	Mode	Symbol/Description	Reset
7:0	R	XTAL32M_TRSTAT	0x0
		Reads value of the current XTAL trimming	

Table 139: XTALRDY_CTRL_REG (0x50000034)

Bit	Mode	Symbol/Description	Reset
7:0	R/W	XTALRDY_CNT	0x0
		Number of 32 kHz cycles between the crystal is enabled, and the XTALRDY_IRQ is fired. 0x00: no interrupt	

Table 140: XTAL32M_CTRL0_REG (0x50000038)

Bit	Mode	Symbol/Description	Reset
9:8	R/W	-	0x0
		Reserved	
7:5	R/W	CORE_AMPL_TRIM	0x0
		Core amplitude trimming	
4:2	R/W	CORE_CUR_SET	0x5
		Core current trim setting	
1	R/W	CORE_AMPL_REG_NULLBIAS	0x0
		Keep bias in ampl detector alive, even when there is a large drive	
0	R/W	DCBLOCK_ENABLE	0x1
		Enable dcblock/high pass filter circuit	

Table 141: POR_PIN_REG (0x50000040)

Bit	Mode	Symbol/Description	Reset
7	R/W	POR_PIN_POLARITY	0x0
		O: Active Low 1: Active High Note: This applies only for the GPIO pin. Reset pad has a fixed polarity	
6:4	R/W	-	0x0
		Reserved	
3:0	R/W	POR_PIN_SELECT	0x0
		Selects the GPIO which is used for POR generation. 0x0: GPIO pin POReset disabled 0x1: P0_0	

Bit	Mode	Symbol/Description	Reset
		0x2: P0_1	
		0xB: P0_10	
		0xC: P0_11	
		0xD - 0xF: reserved	

Table 142: POR_TIMER_REG (0x50000042)

Bit	Mode	Symbol/Description	Reset
6:0	R/W	POR_TIME	0x18
		Time for the POReset to happen.	
		Formula:	
		Time = POR_TIME x 4096 x RC32k clock period	
		Default value: ~3 seconds	
		When set to 0x00, the POR TIMER is disabled.	

Table 143: PMU_SLEEP_REG (0x50000050)

Bit	Mode	Symbol/Description	Reset
11:0	R/W	BG_REFRESH_INTERVAL	0x80
		Defines the refresh interval of reference voltages (bandgap activation and sampling), in units of 2 ms.	

Table 144: POWER_CTRL_REG (0x50000052)

Bit	Mode	Symbol/Description	Reset
15	R/W	VBAT_HL_CONNECT_MODE	0x0
		Sets the control mode fo the switch between VBAT_HIGH and VBAT_LOW 0: Manual (default)	
14	R/W	1: Automatic (boost mode only) POR_VBAT_HIGH_HYST_DIS	0x1
••		0: Hysteresis enabled 1: Hysteresis disabled	OX I
13	R/W	POR_VBAT_HIGH_HYST_SEL	0x0
		0: Low level selected 1: High level selected	
12	R/W	POR_VBAT_HIGH_DISABLE	0x0
		Disable por_vbat_high circuit	
11	R/W	POR_VBAT_LOW_HYST_DIS	0x0
		0: Hysteresis enabled 1: Hysteresis disabled	
10	R/W	POR_VBAT_LOW_HYST_SEL	0x0
		0: Low level selected 1: High level selected	
9	R/W	POR_VBAT_LOW_DISABLE	0x0
		Disable por_vbat_low circuit	

Bit	Mode	Symbol/Description	Reset
8	R/W	CP_DISABLE	0x0
		Disables LDO_CORE charge-pump circuit	
7	R/W	LDO_VREF_HOLD_FORCE	0x0
		Forces LDO references in HOLD mode	
6:5	R/W	LDO_LOW_CTRL_REG	0x0
		00: High-current mode in active, LDO_LOW OFF in sleep	
		01: LDO_LOW OFF	
		10: Low-current mode in active, Low-current mode in sleep	
		11: High-current mode in active, Low-current mode in sleep	
4	R/W	LDO_CORE_DISABLE	0x0
		Disables LDO_CORE	
3	R/W	LDO_CORE_RET_ENABLE	0x0
		LDO_CORE_RETENTION	
		0: Disabled	
		1: Enabled	
2	R/W	VBAT_HL_CONNECT	0x0
		Switch between V _{BAT_HIGH} and V _{BAT_LOW}	
		0: Open	
		1: Closed	
1	R/W	CMP_VBAT_HIGH_OK_ENABLE	0x0
		Enable cmp_vbat_high_ok	
0	R/W	CMP_VBAT_HIGH_NOK_ENABLE	0x0
		Enable cmp_vbat_high_nok	

Table 145: POWER_LEVEL_REG (0x50000054)

Bit	Mode	Symbol/Description	Reset
13:11	R/W	DCDC_TRIM	0x3
		Delta from DCDC_LEVEL nominal value	
		000: -75 mV	
		001: -50 mV	
		010: -25 mV	
		011: 0 (default)	
		100: +25 mV	
		101: +50 mV	
		110: +75 mV	
		111: +100 mV	
10:9	R/W	DCDC_LEVEL	0x1
		00: 1.1 V	
		01: 1.8 V (default)	
		10: 2.5 V	
		11: 3.0 V	
8:7	R/W	-	0x0

Bit	Mode	Symbol/Description	Reset
		Reserved	
6:4	R/W	LDO_XTAL_TRIM	0x3
		Delta from 0.9 V nominal value	
		000: -75 mV	
		001: -50 mV	
		010: -25 mV	
		011: 0 (default)	
		100: +25 mV	
		101: +50 mV	
		110: +75 mV	
		111: +100 mV	
3:1	R/W	LDO_LOW_TRIM	0x7
		Delta from 1.1 V nominal value	
		000: -75 mV	
		001: -50 mV	
		010: -25 mV	
		011: 0 (default)	
		100: +25 mV	
		101: +50 mV	
		110: +75 mV	
		111: +100 mV (coldboot)	
0	R/W	-	0x0
		Reserved	

Table 146: Register map CRG_TIM

Address	Register	Description
0x5000424c	CLK_RTCDIV_REG	Divisor for RTC 100 Hz clock

Table 147: CLK_RTCDIV_REG (0x5000424C)

Bit	Mode	Symbol/Description	Reset
21	R/W	RTC_RESET_REQ	0x0
		Reset request for the RTC module.	
20	R/W	RTC_DIV_ENABLE	0x0
		Enable for the 100-Hz generation for the RTC block.	
19	R/W	RTC_DIV_DENOM	0x0
		Selects the denominator for the fractional division:	
		0b0: 1000	
		0b1: 1024	
18:10	R/W	RTC_DIV_INT	0x147
		Integer divisor part for RTC 100-Hz generation.	
9:0	R/W	RTC_DIV_FRAC	0x2A8
		Fractional divisor part for RTC 100 Hz generation.	

Ultra-Low Power Bluetooth 5.1 SoC

Bit	Mode	Symbol/Description	Reset
		If RTC_DIV_DENOM = 1, <rtc_div_frac> out of 1024 cycles divides by <rtc_div_int+1>, the rest is <rtc_div_int>.</rtc_div_int></rtc_div_int+1></rtc_div_frac>	
		If RTC_DIV_DENOM = 0, <rtc_div_frac> out of 1000 cycles divides by <rtc_div_int+1>, the rest is <rtc_div_int>.</rtc_div_int></rtc_div_int+1></rtc_div_frac>	

32.4 DCDC Converter Registers

Table 148: Register map DCDC

Address	Register	Description
0x50000080	DCDC_CTRL_REG	

Table 149: DCDC_CTRL_REG (0x50000080)

Bit	Mode	Symbol/Description	Reset
15:12	R/W	DCDC_ILIM_MAX	0x8
		Maximum value for automatic inductor peak current limit control.	
		0x0: 6 mA	
		0x1: 12 mA	
		0x2: 18 mA	
		0x3: 24 mA	
		0x4: 30 mA	
		0x5: 36 mA	
		0x6: 42 mA	
		0x7: 48 mA	
		0x8: 54 mA (default, limits inrush current)	
		0x9: 60 mA	
		0xA: 66 mA	
		0xB: 72 mA	
		0xC: 78 mA	
		0xD: 84 mA	
		0xE: 90 mA	
		0xF: 96 mA (set as default for low-ohmic batteries)	
11:8	R/W	DCDC_ILIM_MIN	0x4
		Minimum value for automatic inductor peak current limit control.	
		0x0: 6 mA	
		0x1: 12 mA	
		0x2: 18 mA	
		0x3: 24 mA	
		0x4: 30 mA (default)	
		0x5: 36 mA	
		0x6: 42 mA	
		0x7: 48 mA	
		0x8: 54 mA	
		0x9: 60 mA	
		0xA: 66 mA	
		0xB: 72 mA	
		0xC: 78 mA	
		0xD: 84 mA	
		0xE: 90 mA	
		0xF: 96 mA	
7:6	R/W	DCDC_OK_CLR_CNT	0x2
		Number of subsequent V_NOK events needed to reset VDCD_OK.	
		0x0: 2	

Ultra-Low Power Bluetooth 5.1 SoC

Bit	Mode	Symbol/Description	Reset
		0x1: 4	
		0x2: 8 (deafult)	
		0x3: 15	
5:3	R/W	DCDC_TIMEOUT	0x4
		Switch timeout, go to next state if either switch is active for longer than this setting.	
		0x0: Disabled	
		0x1: 0.25 μs	
		0x2: 0.50 μs	
		0x3: 0.75 μs	
		0x4: 1.00 μs (default)	
		0x5: 1.25 μs	
		0x6: 1.50 μs	
		0x7: 1.75 μs	
2:1	R/W	DCDC_CLK_DIV	0x1
		Idle clock divider, sets rate at which the output is monitored when the converter is idle.	
		0x0: Divide by 4	
		0x1: Divide by 8	
		0x2: Divide by 16	
		0x3: Divide by 32	
0	R/W	DCDC_ENABLE	0x0
		Enables hardware control of the DCDC converter.	
		0: DCDC converter disabled	
		1: DCDC converter under hardware control	

32.5 DMA Controller Registers

Table 150: Register map DMA

Address	Register	Description
0x50003600	DMA0_A_STARTL_REG	Start address Low A of DMA channel 0
0x50003602	DMA0_A_STARTH_REG	Start address High A of DMA channel 0
0x50003604	DMA0_B_STARTL_REG	Start address Low B of DMA channel 0
0x50003606	DMA0_B_STARTH_REG	Start address High B of DMA channel 0
0x50003608	DMA0_INT_REG	DMA receive interrupt register channel 0
0x5000360a	DMA0_LEN_REG	DMA receive length register channel 0
0x5000360c	DMA0_CTRL_REG	Control register for the DMA channel 0
0x5000360e	DMA0_IDX_REG	Index value of DMA channel 0
0x50003610	DMA1_A_STARTL_REG	Start address Low A of DMA channel 1
0x50003612	DMA1_A_STARTH_REG	Start address High A of DMA channel 1
0x50003614	DMA1_B_STARTL_REG	Start address Low B of DMA channel 1
0x50003616	DMA1_B_STARTH_REG	Start address High B of DMA channel 1
0x50003618	DMA1_INT_REG	DMA receive interrupt register channel 1
0x5000361a	DMA1_LEN_REG	DMA receive length register channel 1
0x5000361c	DMA1_CTRL_REG	Control register for the DMA channel 1
0x5000361e	DMA1_IDX_REG	Index value of DMA channel 1
0x50003620	DMA2_A_STARTL_REG	Start address Low A of DMA channel 2
0x50003622	DMA2_A_STARTH_REG	Start address High A of DMA channel 2
0x50003624	DMA2_B_STARTL_REG	Start address Low B of DMA channel 2
0x50003626	DMA2_B_STARTH_REG	Start address High B of DMA channel 2
0x50003628	DMA2_INT_REG	DMA receive interrupt register channel 2
0x5000362a	DMA2_LEN_REG	DMA receive length register channel 2
0x5000362c	DMA2_CTRL_REG	Control register for the DMA channel 2
0x5000362e	DMA2_IDX_REG	Index value of DMA channel 2
0x50003630	DMA3_A_STARTL_REG	Start address Low A of DMA channel 3
0x50003632	DMA3_A_STARTH_REG	Start address High A of DMA channel 3
0x50003634	DMA3_B_STARTL_REG	Start address Low B of DMA channel 3
0x50003636	DMA3_B_STARTH_REG	Start address High B of DMA channel 3
0x50003638	DMA3_INT_REG	DMA receive interrupt register channel 3
0x5000363a	DMA3_LEN_REG	DMA receive length register channel 3
0x5000363c	DMA3_CTRL_REG	Control register for the DMA channel 3
0x5000363e	DMA3_IDX_REG	Index value of DMA channel 3
0x50003680	DMA_REQ_MUX_REG	DMA channel assignments
0x50003682	DMA_INT_STATUS_REG	DMA interrupt status register
0x50003684	DMA_CLEAR_INT_REG	DMA clear interrupt register

Table 151: DMA0_A_STARTL_REG (0x50003600)

Bit	Mode	Symbol/Description	
15:0	R/W	DMA0_A_STARTL	0x0
		Source start address, lower 16 bits	

Table 152: DMA0_A_STARTH_REG (0x50003602)

Bit	Mode	Symbol/Description	
15:0	R/W	DMA0_A_STARTH	0x0
		Source start address, upper 16 bits	

Table 153: DMA0_B_STARTL_REG (0x50003604)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA0_B_STARTL	0x0
		Destination start address, lower 16 bits	

Table 154: DMA0_B_STARTH_REG (0x50003606)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA0_B_STARTH	0x0
		Destination start address, upper 16 bits	

Table 155: DMA0_INT_REG (0x50003608)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA0_INT	0x0
		Number of transfers until an interrupt is generated. The interrupt is generated after a transfer, if DMAx_INT_REG is equal to DMAx_IDX_REG and before DMAx_IDX_REG is incremented. The bit field IRQ_ENABLE of DMAx_CTRL_REG must be set to 1 to let the controller generate the interrupt.	

Table 156: DMA0_LEN_REG (0x5000360A)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA0_LEN	0x0
		DMA channel's transfer length. DMAx_LEN of value 0, 1, 2, results into an actual transfer length of 1, 2, 3,	

Table 157: DMA0_CTRL_REG (0x5000360C)

Bit	Mode	Symbol/Description	Reset
15:14	R	-	0x0
		Reserved	
13	R/W	REQ_SENSE	0x0
		0 = DMA operates with level-sensitive peripheral requests (default) 1 = DMA operates with (positive) edge-sensitive peripheral requests	
12	R/W	DMA_INIT	0x0

Bit	Mode	Symbol/Description	Reset
		0 = DMA performs copy A1 to B1, A2 to B2, and so on	
		1 = DMA performs copy of A1 to B1, B2, and so on	
		This feature is useful for memory initialization to any value. Thus, BINC must be set to 1, while AINC is don't care, as only one fetch from A is done. This process cannot be interrupted by other DMA channels. It is also noted that DMA_INIT should not be used when DREQ_MODE = 1.	
11	R/W	DMA_IDLE	0x0
		0 = Blocking mode, the DMA performs a fast back-to-back copy, disabling bus access for any bus master with lower priority.	
		1 = Interrupting mode, the DMA inserts a wait cycle after each store allowing the CPU to steal cycles or cache to perform a burst read. If DREQ_MODE = 1, DMA_IDLE is don't care.	
10:8	R/W	DMA_PRIO	0x0
		The priority level determines which DMA channel is granted access for transferring data, in case more than one channel is active and request the bus at the same time. The greater the value, the higher the priority. In specific: 000 = lowest priority	
		111 = highest priority	
		If different channels with equal priority level values request the bus at the same time, an inherent priority mechanism is applied. According to this mechanism, if, for example, both the DMA0 and DMA1 channels have the same priority level, then DMA0 is first granted access to the bus.	
7	R/W	CIRCULAR	0x0
		0 = Normal mode. The DMA channel stops after having completed the transfer of length determined by DMAx_LEN_REG. DMA_ON automatically deasserts when the transfer is completed.	
		1 = Circular mode (applicable only if DREQ_MODE = 1). In this mode, DMA_ON never deasserts, as the DMA channel automatically resets DMAx_IDX_REG and starts a new transfer.	
6	R/W	AINC	0x0
		Enable increment of source address.	
		0 = Do not increment (source address stays the same during the transfer)	
		1 = Increment according to the value of BW bit field (by 1, when BW = 00; by 2, when BW = 01; by 4, when BW = 10)	
5	R/W	BINC	0x0
		Enable increment of destination address.	
		0 = Do not increment (destination address stays the same during the transfer)	
		1 = Increment according to the value of BW bit field (by 1, when BW = 00; by 2, when BW = 01; by 4, when BW = 10)	
4	R/W	DREQ_MODE	0x0
		0 = DMA channel starts immediately	
		1 = DMA channel must be triggered by peripheral DMA request (see also the description of DMA_REQ_MUX_REG)	
3	R/W	IRQ_ENABLE	0x0
		0 = Disable interrupt on this channel	
		1 = Enable interrupt on this channel	
2:1	R/W	BW	0x0
		Bus transfer width:	
		00 = 1 byte (suggested for peripherals like UART and 8-bit SPI)	

Bit	Mode	Symbol/Description	Reset
		01 = 2 bytes (suggested for peripherals like I2C and 16-bit SPI)	
		10 = 4 bytes (suggested for Memory-to-Memory transfers)	
		11 = Reserved	
0	R/W	DMA_ON	0x0
		0 = DMA channel is off, clocks are disabled	
		1 = DMA channel is enabled. This bit is automatically cleared after the completion of a transfer, if circular mode is not enabled. In circular mode, this bit stays set.	

Table 158: DMA0_IDX_REG (0x5000360E)

Bit	Mode	Symbol/Description	Reset
15:0	R	DMA0_IDX	0x0
		This (read-only) register determines the data items currently fetched by the DMA channel, during an ongoing transfer. When the transfer is completed, the register is automatically reset to 0.	
		The DMA channel uses this register to form the source/destination address of the next DMA cycle, considering also AINC/BINC and BW.	

Table 159: DMA1_A_STARTL_REG (0x50003610)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA1_A_STARTL	0x0
		Source start address, lower 16 bits	

Table 160: DMA1_A_STARTH_REG (0x50003612)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA1_A_STARTH	0x0
		Source start address, upper 16 bits	

Table 161: DMA1_B_STARTL_REG (0x50003614)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA1_B_STARTL	0x0
		Destination start address, lower 16 bits	

Table 162: DMA1_B_STARTH_REG (0x50003616)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA1_B_STARTH	0x0
		Destination start address, upper 16 bits	

Table 163: DMA1_INT_REG (0x50003618)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA1_INT	0x0
		Number of transfers until an interrupt is generated. The interrupt is generated after a transfer, if DMAx_INT_REG is equal to DMAx_IDX_REG and before	

Bit	Mode	Symbol/Description	Reset
		DMAx_IDX_REG is incremented. The bit field IRQ_ENABLE of DMAx_CTRL_REG must be set to 1 to let the controller generate the interrupt.	

Table 164: DMA1_LEN_REG (0x5000361A)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA1_LEN	0x0
		DMA channel's transfer length. DMAx_LEN of value 0, 1, 2, results into an actual transfer length of 1, 2, 3,	

Table 165: DMA1_CTRL_REG (0x5000361C)

Bit	Mode	Symbol/Description	Reset
15:14	R	-	0x0
		Reserved	
13	R/W	REQ_SENSE	0x0
		0 = DMA operates with level-sensitive peripheral requests (default)	
		1 = DMA operates with (positive) edge-sensitive peripheral requests	
12	R/W	DMA_INIT	0x0
		0 = DMA performs copy A1 to B1, A2 to B2, and so on	
		1 = DMA performs copy of A1 to B1, B2, and so on	
		This feature is useful for memory initialization to any value. Thus, BINC must be set to 1, while AINC is don't care, as only one fetch from A is done. This process cannot be interrupted by other DMA channels. It is also noted that DMA_INIT should not be used when DREQ_MODE = 1.	
11	R/W	DMA_IDLE	0x0
		0 = Blocking mode, the DMA performs a fast back-to-back copy, disabling bus access for any bus master with lower priority.	
		1 = Interrupting mode, the DMA inserts a wait cycle after each store allowing the CPU to steal cycles or cache to perform a burst read. If DREQ_MODE= 1, DMA_IDLE is don't care.	
10:8	R/W	DMA_PRIO	0x0
		The priority level determines which DMA channel is granted access for transferring data, in case more than one channel is active and request the bus at the same time. The greater the value, the higher the priority. In specific:	
		000 = lowest priority	
		111 = highest priority	
		If different channels with equal priority level values request the bus at the same time, an inherent priority mechanism is applied. According to this mechanism, if, for example, both the DMA0 and DMA1 channels have the same priority level, then DMA0 is first granted access to the bus.	
7	R/W	CIRCULAR	0x0
		0 = Normal mode. The DMA channel stops after having completed the transfer of length determined by DMAx_LEN_REG. DMA_ON automatically deasserts when the transfer is completed.	
		1 = Circular mode (applicable only if DREQ_MODE = 1). In this mode, DMA_ON never deasserts, as the DMA channel automatically resets DMAx_IDX_REG and starts a new transfer.	
6	R/W	AINC	0x0

Bit	Mode	Symbol/Description	Reset
		Enable increment of source address. 0 = Do not increment (source address stays the same during the transfer) 1 = Increment according to the value of BW bit field (by 1, when BW = 00; by 2, when BW = 01; by 4, when BW = 10)	
5	R/W	BINC	0x0
		Enable increment of destination address. 0 = Do not increment (destination address stays the same during the transfer) 1 = Increment according to the value of BW bit field (by 1, when BW = 00; by 2, when BW = 01; by 4, when BW = 10)	
4	R/W	DREQ_MODE 0 = DMA channel starts immediately 1 = DMA channel must be triggered by peripheral DMA request (see also the description of DMA_REQ_MUX_REG)	0x0
3	R/W	IRQ_ENABLE 0 = disable interrupt on this channel 1 = enable interrupt on this channel	0x0
2:1	R/W	BW Bus transfer width: 00 = 1 byte (suggested for peripherals like UART and 8-bit SPI) 01 = 2 bytes (suggested for peripherals like I2C and 16-bit SPI) 10 = 4 bytes (suggested for Memory-to-Memory transfers) 11 = Reserved	0x0
0	R/W	DMA_ON 0 = DMA channel is off, clocks are disabled 1 = DMA channel is enabled. This bit is automatically cleared after the completion of a transfer, if circular mode is not enabled. In circular mode, this bit stays set.	0x0

Table 166: DMA1_IDX_REG (0x5000361E)

Bit	Mode	Symbol/Description	Reset
15:0	R	DMA1_IDX	0x0
		This (read-only) register determines the data items currently fetched by the DMA channel, during an ongoing transfer. When the transfer is completed, the register is automatically reset to 0.	
		The DMA channel uses this register to form the source/destination address of the next DMA cycle, considering also AINC/BINC and BW.	

Table 167: DMA2_A_STARTL_REG (0x50003620)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA2_A_STARTL	0x0
		Source start address, lower 16 bits	

Table 168: DMA2_A_STARTH_REG (0x50003622)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA2_A_STARTH	0x0

Bit	Mode	Symbol/Description	Reset
		Source start address, upper 16 bits	

Table 169: DMA2_B_STARTL_REG (0x50003624)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA2_B_STARTL	0x0
		Destination start address, lower 16 bits	

Table 170: DMA2_B_STARTH_REG (0x50003626)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA2_B_STARTH	0x0
		Destination start address, upper 16 bits	

Table 171: DMA2_INT_REG (0x50003628)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA2_INT	0x0
		Number of transfers until an interrupt is generated. The interrupt is generated after a transfer, if DMAx_INT_REG is equal to DMAx_IDX_REG and before DMAx_IDX_REG is incremented. The bit field IRQ_ENABLE of DMAx_CTRL_REG must be set to 1 to let the controller generate the interrupt.	

Table 172: DMA2_LEN_REG (0x5000362A)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA2_LEN	0x0
		DMA channel's transfer length. DMAx_LEN of value 0, 1, 2, results into an actual transfer length of 1, 2, 3,	

Table 173: DMA2_CTRL_REG (0x5000362C)

Bit	Mode	Symbol/Description	Reset
15:14	R	-	0x0
		Reserved	
13	R/W	REQ_SENSE	0x0
		0 = DMA operates with level-sensitive peripheral requests (default)	
		1 = DMA operates with (positive) edge-sensitive peripheral requests	
12	R/W	DMA_INIT	0x0
		0 = DMA performs copy A1 to B1, A2 to B2, and so on	
		1 = DMA performs copy of A1 to B1, B2, and so on	
		This feature is useful for memory initialization to any value. Thus, BINC must be set to 1, while AINC is don't care, as only one fetch from A is done. This process cannot be interrupted by other DMA channels. It is also noted that DMA_INIT should not be used when DREQ_MODE = 1.	
11	R/W	DMA_IDLE	0x0
		0 = Blocking mode, the DMA performs a fast back-to-back copy, disabling bus access for any bus master with lower priority.	

Bit	Mode	Symbol/Description	Reset
		1 = Interrupting mode, the DMA inserts a wait cycle after each store allowing the CPU to steal cycles or cache to perform a burst read. If DREQ_MODE = 1, DMA_IDLE is don't care.	
10:8	R/W	DMA_PRIO	0x0
		The priority level determines which DMA channel is granted access for transferring data, in case more than one channel is active and request the bus at the same time. The greater the value, the higher the priority. In specific:	
		000 = lowest priority	
		111 = highest priority	
		If different channels with equal priority level values request the bus at the same time, an inherent priority mechanism is applied. According to this mechanism, if, for example, both the DMA0 and DMA1 channels have the same priority level, then DMA0 is first granted access to the bus.	
7	R/W	CIRCULAR	0x0
		0 = Normal mode. The DMA channel stops after having completed the transfer of length determined by DMAx_LEN_REG. DMA_ON automatically deasserts when the transfer is completed.	
		1 = Circular mode (applicable only if DREQ_MODE = 1). In this mode, DMA_ON never deasserts, as the DMA channel automatically resets DMAx_IDX_REG and starts a new transfer.	
6	R/W	AINC	0x0
		Enable increment of destination address.	
		0 = Do not increment (destination address stays the same during the transfer)	
		1 = Increment according to the value of BW bit field (by 1, when BW = 00; by 2, when BW = 01; by 4, when BW = 10)	
5	R/W	BINC	0x0
		Enable increment of destination address 0 = Do not increment	
		1 = Increment according to the value of BW	
4	R/W	DREQ_MODE	0x0
		0 = DMA channel starts immediately	
		1 = DMA channel must be triggered by peripheral DMA request (see also the description of DMA_REQ_MUX_REG)	
3	R/W	IRQ_ENABLE	0x0
		0 = Disable interrupt on this channel	
		1 = Enable interrupt on this channel	
2:1	R/W	BW	0x0
		Bus transfer width:	
		00 = 1 byte (suggested for peripherals like UART and 8-bit SPI)	
		01 = 2 bytes (suggested for peripherals like I2C and 16-bit SPI)	
		10 = 4 bytes (suggested for Memory-to-Memory transfers)	
^	D.044	11 = Reserved	0.0
0	R/W	DMA_ON	0x0
		0 = DMA channel is off, clocks are disabled	
		1 = DMA channel is enabled. This bit is automatically cleared after the completion of a transfer, if circular mode is not enabled. In circular mode, this bit stays set.	

Table 174: DMA2_IDX_REG (0x5000362E)

Bit	Mode	Symbol/Description	Reset
15:0	R	DMA2_IDX	0x0
		This (read-only) register determines the data items currently fetched by the DMA channel, during an ongoing transfer. When the transfer is completed, the register is automatically reset to 0.	
		The DMA channel uses this register to form the source/destination address of the next DMA cycle, considering also AINC/BINC and BW.	

Table 175: DMA3_A_STARTL_REG (0x50003630)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA3_A_STARTL	0x0
		Source start address, lower 16 bits	

Table 176: DMA3_A_STARTH_REG (0x50003632)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA3_A_STARTH	0x0
		Source start address, upper 16 bits	

Table 177: DMA3_B_STARTL_REG (0x50003634)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA3_B_STARTL	0x0
		Destination start address, lower 16 bits	

Table 178: DMA3_B_STARTH_REG (0x50003636)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA3_B_STARTH	0x0
		Destination start address, upper 16 bits	

Table 179: DMA3_INT_REG (0x50003638)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA3_INT	0x0
		Number of transfers until an interrupt is generated. The interrupt is generated after a transfer, if DMAx_INT_REG is equal to DMAx_IDX_REG and before DMAx_IDX_REG is incremented. The bit field IRQ_ENABLE of DMAx_CTRL_REG must be set to 1 to let the controller generate the interrupt.	

Table 180: DMA3_LEN_REG (0x5000363A)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	DMA3_LEN	0x0
		DMA channel's transfer length. DMAx_LEN of value 0, 1, 2, results into an actual transfer length of 1, 2, 3,	

Table 181: DMA3_CTRL_REG (0x5000363C)

Bit	Mode	Symbol/Description	Reset
15:14	R	-	0x0
		Reserved	
13	R/W	REQ_SENSE	0x0
		0 = DMA operates with level-sensitive peripheral requests (default)	
		1 = DMA operates with (positive) edge-sensitive peripheral requests	
12	R/W	DMA_INIT	0x0
		0 = DMA performs copy A1 to B1, A2 to B2, and so on	
		1 = DMA performs copy of A1 to B1, B2, and so on	
		This feature is useful for memory initialization to any value. Thus, BINC must be set to 1, while AINC is don't care, as only one fetch from A is done. This process cannot be interrupted by other DMA channels. It is also noted that DMA_INIT should not be used when DREQ_MODE = 1.	
11	R/W	DMA_IDLE	0x0
		0 = Blocking mode, the DMA performs a fast back-to-back copy, disabling bus access for any bus master with lower priority.	
		1 = Interrupting mode, the DMA inserts a wait cycle after each store allowing the CPU to steal cycles or cache to perform a burst read. If DREQ_MODE = 1, DMA_IDLE is don't care.	
10:8	R/W	DMA_PRIO	0x0
		The priority level determines which DMA channel is granted access for transferring data, in case more than one channel is active and request the bus at the same time. The greater the value, the higher the priority. In specific:	
		000 = lowest priority	
		111 = highest priority	
		If different channels with equal priority level values request the bus at the same time, an inherent priority mechanism is applied. According to this mechanism, if, for example, both the DMA0 and DMA1 channels have the same priority level, then DMA0 is first granted access to the bus.	
7	R/W	CIRCULAR	0x0
		0 = Normal mode. The DMA channel stops after having completed the transfer of length determined by DMAx_LEN_REG. DMA_ON automatically deasserts when the transfer is completed.	
		1 = Circular mode (applicable only if DREQ_MODE = 1). In this mode, DMA_ON never deasserts, as the DMA channel automatically resets DMAx_IDX_REG and starts a new transfer.	
6	R/W	AINC	0x0
		Enable increment of source address.	
		0 = Do not increment (source address stays the same during the transfer)	
		1 = Increment according to the value of BW bit field (by 1, when BW = 00; by 2, when BW = 01; by 4, when BW = 10)	
5	R/W	BINC	0x0
		Enable increment of destination address.	
		0 = Do not increment (destination address stays the same during the transfer)	
		1 = Increment according to the value of BW bit field (by 1, when BW = 00; by 2, when BW = 01; by 4, when BW = 10)	
4	R/W	DREQ_MODE	0x0
		0 = DMA channel starts immediately	

Bit	Mode	Symbol/Description	Reset
		1 = DMA channel must be triggered by peripheral DMA request (see also the description of DMA_REQ_MUX_REG)	
3	R/W	IRQ_ENABLE	0x0
		0 = Disable interrupt on this channel	
		1 = Enable interrupt on this channel	
2:1	R/W	BW	0x0
		Bus transfer width:	
		00 = 1 byte (suggested for peripherals like UART and 8-bit SPI)	
		01 = 2 bytes (suggested for peripherals like I2C and 16-bit SPI)	
		10 = 4 bytes (suggested for Memory-to-Memory transfers)	
		11 = Reserved	
0	R/W	DMA_ON	0x0
		0 = DMA channel is off, clocks are disabled	
		1 = DMA channel is enabled. This bit is automatically cleared after the completion of a transfer, if circular mode is not enabled. In circular mode, this bit stays set.	

Table 182: DMA3_IDX_REG (0x5000363E)

Bit	Mode	Symbol/Description	Reset
15:0	R	DMA3_IDX	0x0
		This (read-only) register determines the data items currently fetched by the DMA channel, during an ongoing transfer. When the transfer is completed, the register is automatically reset to 0.	
		The DMA channel uses this register to form the source/destination address of the next DMA cycle, considering also AINC/BINC and BW.	

Table 183: DMA_REQ_MUX_REG (0x50003680)

Bit	Mode	Symbol/Description	Reset
15:12	R/W	-	0xF
		Reserved	
11:8	R/W	-	0xF
		Reserved	
7:4	R/W	DMA23_SEL	0xF
		Select which combination of peripherals are mapped on the DMA channels. The peripherals are mapped as pairs on two channels.	
		Hence, the first DMA request (peripheral-to-memory) is mapped on channel 2 and the second (memory-to-peripheral) on channel 3.	
		See also the description of DMA01_SEL bit field of this register for the supported peripherals.	
3:0	R/W	DMA01_SEL	0xF
		Select which combination of peripherals are mapped on the DMA channels. The peripherals are mapped as pairs on two channels.	
		Hence, the first DMA request (peripheral-to-memory) is mapped on channel 0 and the second (memory-to-peripheral) on channel 1.	
		0x0: SPI_rx/SPI_tx	
		0x1: Reserved	
		0x2: UART_rx/UART_tx	

Bit	Mode	Symbol/Description	Reset
		0x3: UART2_rx/UART2_tx	
		0x4: I2C_rx/I2C_tx	
		0x5: GP_ADC (RX only)	
		0x6-0xE: Reserved	
		0xF: None	
		Note: If any of the two available peripheral selector fields (DMA01_SEL, DMA23_SEL) have the same value, the lesser significant selector has higher priority and controls the DMA acknowledge. Hence, if DMA01_SEL = DMA23_SEL, the channels 0 and 1 generate the DMA acknowledge signals for the selected peripheral. Consequently, it is suggested to assign the intended peripheral value to a unique selector field.	

Table 184: DMA_INT_STATUS_REG (0x50003682)

Bit	Mode	Symbol/Description	Reset
15:8	R	-	0x0
		Reserved	
7	R	-	0x0
		Reserved	
6	R	-	0x0
		Reserved	
5	R	-	0x0
		Reserved	
4	R	-	0x0
		Reserved	
3	R	DMA_IRQ_CH3	0x0
		0: IRQ on channel 3 is not set	
		1: IRQ on channel 3 is set	
2	R	DMA_IRQ_CH2	0x0
		0: IRQ on channel 2 is not set	
		1: IRQ on channel 2 is set	
1	R	DMA_IRQ_CH1	0x0
		0: IRQ on channel 1 is not set	
		1: IRQ on channel 1 is set	
0	R	DMA_IRQ_CH0	0x0
		0: IRQ on channel 0 is not set	
		1: IRQ on channel 0 is set	

Table 185: DMA_CLEAR_INT_REG (0x50003684)

Bit	Mode	Symbol/Description	Reset
15:8	R	-	0x0
		Reserved	
7	R	-	0x0
		Reserved	

Bit	Mode	Symbol/Description	Reset
6	R	-	0x0
		Reserved	
5	R	-	0x0
		Reserved	
4	R	-	0x0
		Reserved	
3	R0/W	DMA_RST_IRQ_CH3	0x0
		Writing 1 resets the status bit of DMA_INT_STATUS_REG for channel 3; writing 0 has no effect.	
2	R0/W	DMA_RST_IRQ_CH2	0x0
		Writing 1 resets the status bit of DMA_INT_STATUS_REG for channel 2; writing 0 has no effect.	
1	R0/W	DMA_RST_IRQ_CH1	0x0
		Writing 1 resets the status bit of DMA_INT_STATUS_REG for channel 1; writing 0 has no effect.	
0	R0/W	DMA_RST_IRQ_CH0	0x0
		Writing 1 resets the status bit of DMA_INT_STATUS_REG for channel 0; writing 0 has no effect.	

32.6 General Purpose ADC Registers

Table 186: Register map GPADC

Address	Register	Description
0x50001500	GP_ADC_CTRL_REG	General Purpose ADC Control Register
0x50001502	GP_ADC_CTRL2_REG	General Purpose ADC Second Control Register
0x50001504	GP_ADC_CTRL3_REG	General Purpose ADC Third Control Register
0x50001506	GP_ADC_SEL_REG	General Purpose ADC Input Selection Register
0x50001508	GP_ADC_OFFP_REG	General Purpose ADC Positive Offset Register
0x5000150a	GP_ADC_OFFN_REG	General Purpose ADC Negative Offset Register
0x5000150c	GP_ADC_TRIM_REG	General Purpose ADC Trim Register
0x5000150e	GP_ADC_CLEAR_INT_R EG	General Purpose ADC Clear Interrupt Register
0x50001510	GP_ADC_RESULT_REG	General Purpose ADC Result Register

Table 187: GP_ADC_CTRL_REG (0x50001500)

Bit	Mode	Symbol/Description	Reset
12	R/W	DIE_TEMP_EN	0x0
		Enables the die-temperature sensor. Output can be measured on GPADC input 4.	
11	R/W	-	0x0
		Reserved	
10	R/W	GP_ADC_LDO_HOLD	0x0
		0: GPADC LDO tracking bandgap reference	
		1: GPADC LDO hold sampled bandgap reference	

Bit	Mode	Symbol/Description	Reset
9	R/W	GP_ADC_CHOP	0x0
		0: Chopper mode off	
		1: Chopper mode enabled. Takes two samples with opposite GP_ADC_SIGN to cancel the internal offset voltage of the ADC; Highly recommended for DC-measurements.	
8	R/W	GP_ADC_SIGN	0x0
		Default Conversion with opposite sign at input and output to cancel out the internal offset of the ADC and low-frequency	
7	R/W	GP_ADC_MUTE	0x0
		0: Normal operation	
		1: Mute ADC input. Takes sample at mid-scale (to dertermine the internal offset and/or noise of the ADC with regards to VDD_REF which is also sampled by the ADC).	
6	R/W	GP_ADC_SE	0x0
		0: Differential mode 1: Single ended mode	
5	R/W	GP_ADC_MINT	0x0
		0: Disable (mask) GP_ADC_INT. 1: Enable GP_ADC_INT to ICU.	
4	R	GP_ADC_INT	0x0
		1: AD conversion ready and has generated an interrupt. Must be cleared by writing any value to GP_ADC_CLEAR_INT_REG.	
3	R/W	GP_ADC_DMA_EN	0x0
		DMA functionality disabled DMA functionality enabled	
2	R/W	GP_ADC_CONT	0x0
		0: Manual ADC mode, a single result will be generated after setting the GP_ADC_START bit.	
		1: Continuous ADC mode, new ADC results will be constantly stored in GP_ADC_RESULT_REG. Still GP_ADC_START has to be set to start the execution. The time between conversions is configurable with GP_ADC_INTERVAL.	
1	R/W	GP_ADC_START	0x0
		O: ADC conversion ready. 1: If a 1 is written, the ADC starts a conversion. After the conversion this bit will be set to 0 and the GP_ADC_INT bit will be set. It is not allowed to write this bit while it is not (yet) zero.	
0	R/W	GP_ADC_EN	0x0
		0: LDO is off and ADC is disabled	
		1: LDO is turned on and afterwards the ADC is enabled.	

Table 188: GP_ADC_CTRL2_REG (0x50001502)

Bit	Mode	Symbol/Description	Reset
15:13	R/W	GP_ADC_STORE_DEL	0x0
		0: Data is stored after handshake synchronisation	

Bit	Mode	Symbol/Description	Reset
		1: Data is stored 2 ADC_CLK cycles after internal start trigger	
		7: Data is stored 8 ADC_CLK cycles after internal start trigger	
12:9	R/W	GP_ADC_SMPL_TIME	0x1
		0: The sample time (switch is closed) is two ADC_CLK cycles	
		1: The sample time is 1*8 ADC_CLK cycles	
		2: The sample time is 2*8 ADC_CLK cycles	
		15: The sample time is 15*8 ADC_CLK cycles	
8:6	R/W	GP_ADC_CONV_NRS	0x0
		0: 1 sample is taken or 2 in case ADC_CHOP is active.	
		1: 2 samples are taken.	
		2: 4 samples are taken.	
		7: 128 samples are taken.	
5:4	R/W	GP_ADC_OFFS_SH_CM	0x1
		Common mode adjust for offset shifter. Input range is CM +/- 450 mV.	
		0: CM = 1.25 V (Input range 0.80 - 1.70)	
		1: CM = 1.30 V (Input range 0.85 - 1.75) (default)	
		2: CM = 1.35 V (Input range 0.90 - 1.80)	
		3: CM = 1.40 V (input range 0.95 - 1.85)	
3	R/W	GP_ADC_OFFS_SH_EN	0x0
		0: Disable input shifter	
		1: Enable input shifter (900 mV - 1800 mV shifted to 0 mV - 900 mV)	
2	R/W	GP_ADC_I20U	0x0
		1: Adds 20 uA constant load current at the ADC LDO to minimize ripple on the reference voltage of the ADC.	
1:0	R/W	GP_ADC_ATTN	0x0
		0: No attenuator (input voltages up to 0.9 V allowed)	
		1: Enabling 2x attenuator (input voltages up to 1.8 V allowed)	
		2: Enabling 3x attenuator (input voltages up to 2.7 V allowed)	
		3: Enabling 4x attenuator (input voltages up to 3.6 V allowed)	
		Enabling the attenuator requires a longer sampling time.	

Table 189: GP_ADC_CTRL3_REG (0x50001504)

Bit	Mode	Symbol/Description	Reset
15:8	R/W	GP_ADC_INTERVAL	0x0
		Defines the interval between two ADC conversions in case GP_ADC_CONT is set. 0: No extra delay between two conversions. 1: 1.024 ms interval between two conversions. 2: 2.048 ms interval between two conversions. 255: 261.12 ms interval between two conversions.	
7:0	R/W	GP_ADC_EN_DEL Defines the delay for enabling the ADC after enabling the LDO. 0: Not allowed 1: 4x ADC_CLK period. n: n*4x ADC_CLK period.	0x40

Table 190: GP_ADC_SEL_REG (0x50001506)

Bit	Mode	Symbol/Description	Reset
7	R/W	-	0x0
		Reserved	
6:4	R/W	GP_ADC_SEL_P	0x0
		ADC positive input selection.	
		0: ADC0 (P0[1])	
		1: ADC1 (P0[2])	
		2: ADC2 (P0[6])	
		3: ADC3 (P0[7])	
		4: Temperature Sensor	
		5: VBAT_HIGH	
		6: VBAT_LOW	
		7: VDDD	
3	R/W	-	0x0
		Reserved	
2:0	R/W	GP_ADC_SEL_N	0x0
		ADC negative input selection. Differential only (GP_ADC_SE=0).	
		0: ADC0 (P0[1])	
		1: ADC1 (P0[2])	
		2: ADC2 (P0[6])	
		3: ADC3 (P0[7])	
		All other combinations are reserved.	

Table 191: GP_ADC_OFFP_REG (0x50001508)

Bit	Mode	Symbol/Description	Reset
9:0	R/W	GP_ADC_OFFP	0x200
		Offset adjust of the "positive" array of ADC-network (effective if "GP_ADC_SE=0", or "GP_ADC_SE=1 AND GP_ADC_SIGN=0 OR GP_ADC_CHOP=1")	

Table 192: GP_ADC_OFFN_REG (0x5000150A)

Bit	Mode	Symbol/Description	
9:0	R/W	GP_ADC_OFFN	
		Offset adjust of the "negative" array of ADC-network (effective if "GP_ADC_SE=0", or "GP_ADC_SE=1 AND GP_ADC_SIGN=1 OR GP_ADC_CHOP=1")	

Table 193: GP_ADC_TRIM_REG (0x5000150C)

Bit	Mode	Symbol/Description		
6:4	R/W	GP_ADC_LDO_LEVEL	0x3	
	GPADC LDO level			
	0: 825 mV			
		1: 850 mV		
	2: 875 mV			
		3: 900 mV (reset)		
		4: 925 mV (default)		

Bit	Mode	Symbol/Description			
		5: 950 mV 6: 975 mV 7:1000 mV			
3:0	R/W	GP_ADC_OFFS_SH_VREF			
		Offset Shifter common-mode reference fine trimming: 2 mV/LSB			
		Default = mid-scale at 1000			

Table 194: GP_ADC_CLEAR_INT_REG (0x5000150E)

Bit	Mode	Symbol/Description		
15:0	R0/W	GP_ADC_CLR_INT	0x0	
		Writing any value to this register clears the ADC_INT interrupt. Reading returns 0.		

Table 195: **GP_ADC_RESULT_REG** (0x50001510)

Bit	Mode	Symbol/Description	
15:0	R	GP_ADC_VAL	
		Returns the 10 up to 16 bits linear value of the last AD conversion. The upper 10 bits are always valid, the lower 6 bits are only valid in case oversampling has been applied. Two samples result in one extra bit and 64 samples result in six extra bits.	

32.7 General Purpose I/O Registers

Table 196: Register map GPIO

Address	Register	Description
0x50003000	P0_DATA_REG	P0 Data input/output Register
0x50003002	P0_SET_DATA_REG	P0 Set port pins Register
0x50003004	P0_RESET_DATA_REG	P0 Reset port pins Register
0x50003006	P00_MODE_REG	P00 Mode Register
0x50003008	P01_MODE_REG	P01 Mode Register
0x5000300A	P02_MODE_REG	P02 Mode Register
0x5000300C	P03_MODE_REG	P03 Mode Register
0x5000300E	P04_MODE_REG	P04 Mode Register
0x50003010	P05_MODE_REG	P05 Mode Register
0x50003012	P06_MODE_REG	P06 Mode Register
0x50003014	P07_MODE_REG	P07 Mode Register
0x50003016	P08_MODE_REG	P08 Mode Register
0x50003018	P09_MODE_REG	P09 Mode Register
0x5000301A	P010_MODE_REG	P010 Mode Register
0x5000301C	P011_MODE_REG	P011 Mode Register
0x5000301E	PAD_WEAK_CTRL_REG	Pad driving strength control Register

Table 197: P0_DATA_REG (0x50003000)

Bit	Mode	Symbol	Description	Reset
15:12	-	-	Reserved	0x0
11:0	R/W	P0_DATA	Sets P0 output register when written ; Returns the value of P0 port when read	0x0

Table 198: P0_SET_DATA_REG (0x50003002)

Bit	Mode	Symbol	Description	Reset
15:12	-	-	Reserved	0x0
11:0	R0/W	P0_SET	Writing a 1 to P0[x] sets P0[x] to 1.	0x0
			Writing 0 is discarded, reading returns 0	

Table 199: P0_RESET_DATA_REG (0x50003004)

Bit	Mode	Symbol	Description	Reset
15:12	-	-	Reserved	0x0
11:0	R0/W	P0_RESET	Writing a 1 to P0[x] sets P0[x] to 0	0x0
			Writing 0 is discarded, reading returns 0	

Table 200: P00_MODE_REG (0x50003006)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected	0x2
			01 = Input, pull-up selected	
			10 = Input, pull-down selected	
			11 = Output, no resistors selected	
			In ADC mode, these bits are don't care	
7:5	-	-	Reserved	0x0
4:0	R/W	PID	Function of port	0x0
			0 = GPIO (pin direction determined by "PUPD" field)	
			1 = UART1_RX	
			2 = UART1_TX	
			3 = UART2_RX	
			4 = UART2_TX	
			5 = SYS_CLK	
			6 = LP_CLK	
			7 = Reserved	
			8 = Reserved	
			9 = I2C_SCL	
			10 = I2C_SDA	
			11 = PWM5	
			12 = PWM6	
			13 = PWM7	
			14 = Reserved	
			15 = ADC (only for P0_1, P0_2, P0_6 and P0_7)	

Bit	Mode	Symbol	Description	Reset
			16 = PWM0	
			17 = PWM1	
			18 = BLE_DIAG (signals mapped to P0[3:0] are also mapped to P0[11:8])	
			19 = UART1_CTSN	
			20 = UART1_RTSN	
			21 = Reserved	
			22 = Reserved	
			23 = PWM2	
			24 = PWM3	
			25 = PWM4	
			26 = SPI_DI	
			27 = SPI_DO	
			28 = SPI_CLK	
			29 = SPI_CSN0	
			30 = SPI_CSN1	
			31 = Reserved	
			Note: When a certain input function (like SPI_DI) is selected on more than 1 pins, the pin of the lowest index has the highest priority.	

Table 201: P01_MODE_REG (0x50003008)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected	0x2
			01 = Input, pull-up selected	
			10 = Input, pull-down selected	
			11 = Output, no resistors selected	
			In ADC mode, these bits are don't care	
7:5	-	-	Reserved	0x0
4:0	R/W	PID	See P00_MODE_REG[PID]	0x0

Table 202: P02_MODE_REG (0x5000300A)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected 01 = Input, pull-up selected 10 = Input, pull-down selected 11 = Output, no resistors selected In ADC mode, these bits are don't care	0x2
7:5	-	-	Reserved	0x0
4:0	R/W	PID	See P00_MODE_REG[PID]	0x0

Table 203: P03_MODE_REG (0x5000300C)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected	0x2
			01 = Input, pull-up selected	
			10 = Input, pull-down selected	
			11 = Output, no resistors selected	
			In ADC mode, these bits are don't care	
7:5	-	-	Reserved	0x0
4:0	R/W	PID	See P00_MODE_REG[PID]	0x0

Table 204: P04_MODE_REG (0x5000300E)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected 01 = Input, pull-up selected 10 = Input, pull-down selected 11 = Output, no resistors selected	0x2
7:5	-	-	Reserved	0x0
4:0	R/W	PID	See P00_MODE_REG[PID]	0x0

Table 205: P05_MODE_REG (0x50003010)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected	0x2
			01 = Input, pull-up selected	
			10 = Input, pull-down selected	
			11 = Output, no resistors selected	
7:5	-	-	Reserved	0x0
4:0	R/W	PID	See P00_MODE_REG[PID]	0x0

Table 206: P06_MODE_REG (0x50003012)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected 01 = Input, pull-up selected 10 = Input, pull-down selected 11 = Output, no resistors selected	0x2
7:5	-	-	Reserved	0x0
4:0	R/W	PID	See P00_MODE_REG[PID]	0x0

Table 207: P07_MODE_REG (0x50003014)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected	0x2
			01 = Input, pull-up selected	
			10 = Input, pull-down selected	
			11 = Output, no resistors selected	
7:5	-	-	Reserved	0x0
4:0	R/W	PID	See P00_MODE_REG[PID]	0x0

Table 208: P08_MODE_REG (0x50003016)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected	0x2
			01 = Input, pull-up selected	
			10 = Input, pull-down selected	
			11 = Output, no resistors selected	
7:5	-	-	Reserved	0x0
4:0	R/W	PID	See P00_MODE_REG[PID]	0x0

Table 209: P09_MODE_REG (0x50003018)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected 01 = Input, pull-up selected 10 = Input, pull-down selected 11 = Output, no resistors selected	0x2
7:5	-	-	Reserved	0x0
4:0	R/W	PID	See P00_MODE_REG[PID]	0x0

Table 210: P010_MODE_REG (0x5000301A)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected	0x2
			01 = Input, pull-up selected	
			10 = Input, pull-down selected	
			11 = Output, no resistors selected	
7:5	-	-	Reserved	0x0
4:0	R/W	PID	See P00_MODE_REG[PID]	0x0

Table 211: P011_MODE_REG (0x5000301C)

Bit	Mode	Symbol	Description	Reset
15:10	-	-	Reserved	0x0
9:8	R/W	PUPD	00 = Input, no resistors selected	0x2
			01 = Input, pull-up selected	
			10 = Input, pull-down selected	
			11 = Output, no resistors selected	
7:5	-	-	Reserved	0x0
4:0	R/W	PID	See P00_MODE_REG[PID]	0x0

Table 212: PAD_WEAK_CTRL_REG (0x5000301E)

Bit	Mode	Symbol	Description	Reset
15:12	-	-	Reserved	0x0
11:0	R/W	PAD_LOW_DRV	0 = Normal operation	0x0
			1 = Reduces the driving strength of P0_x pad.	
			Bit x controls the driving strength of P0_x, x=0, 1,, 11.	

32.8 General Purpose Registers

Table 213: Register map GPREG

Address	Register	Description
0x50003300	SET_FREEZE_REG	Controls freezing of various timers/counters.
0x50003302	RESET_FREEZE_REG	Controls unfreezing of various timers/counters.
0x50003304	DEBUG_REG	Various debug information register.
0x50003306	GP_STATUS_REG	General purpose system status register.
0x50003308	GP_CONTROL_REG	General purpose system control register.
0x5000330a	BLE_TIMER_REG	BLE FINECNT sampled value while in deep sleep state.

Table 214: SET_FREEZE_REG (0x50003300)

Bit	Mode	Symbol/Description	Reset
15:5	-	-	0x0
		Reserved	
4	R/W	FRZ_DMA	0x0
		If 1, the DMA is frozen, 0 is discarded.	
3	R/W	FRZ_WDOG	0x0
		If 1, the watchdog timer is frozen, 0 is discarded. WATCHDOG_CTRL_REG[NMI_RST] must be 0 to allow the freeze function.	
2	R/W	FRZ_BLETIM	0x0
		If 1, the BLE master clock is frozen, 0 is discarded.	
1	R/W	FRZ_SWTIM	0x0
		If 1, the SW Timer (TIMER0) is frozen, 0 is discarded.	
0	R/W	FRZ_WKUPTIM	0x0
		If 1, the Wake Up Timer is frozen, 0 is discarded.	

Table 215: RESET_FREEZE_REG (0x50003302)

Bit	Mode	Symbol/Description	Reset
15:5	-		0x0
		Reserved	
4	R/W	FRZ_DMA	0x0
		If 1, the DMA continues, 0 is discarded.	
3	R/W	FRZ_WDOG	0x0
		If 1, the watchdog timer continues, 0 is discarded.	
2	R/W	FRZ_BLETIM	0x0
		If 1, the the BLE master clock continues, 0 is discarded.	
1	R/W	FRZ_SWTIM	0x0
		If 1, the SW Timer (TIMER0) continues, 0 is discarded.	
0	R/W	FRZ_WKUPTIM	0x0
		If 1, the Wake Up Timer continues, 0 is discarded.	

Table 216: DEBUG_REG (0x50003304)

Bit	Mode	Symbol/Description	Reset
15:1	R/W	-	0x0
		Reserved	
0	R/W	DEBUGS_FREEZE_EN	0x1
		Default 1, freezing of the on-chip timers is enabled when the Cortex is halted in DEBUG State.	
		If 0, freezing of the on-chip timers is depending on FREEZE_REG when the Cortex is halted in DEBUG State except the watchdog timer. The watchdog timer is always frozen when the Cortex is halted in DEBUG State.	

Table 217: **GP_STATUS_REG** (0x50003306)

Bit	Mode	Symbol/Description	Reset
15:2	-	-	0x0
		Reserved	
1	R/W	-	0x0
		Reserved	
0	R/W	CAL_PHASE	0x0
		If 1, it designates that the chip is in Calibration Phase that is the OTP has been initially programmed but no Calibration has occured.	

Table 218: GP_CONTROL_REG (0x50003308)

Bit	Mode	Symbol/Description	Reset
15:7	-	-	0x0
		Reserved	
6:5	R/W	BLE_TIMER_DATA_CTRL	0x0
		See BLE_TIMER_REG.	
4	R/W	CPU_DMA_BUS_PRIO	0x0
		Controls the CPU DMA system bus priority:	
		If 0, the CPU has highest priority.	
		If 1, the DMA has highest priority.	
3	-	-	0x0
		Reserved	
2	R	BLE_WAKEUP_LP_IRQ	0x0
		The current value of the BLE_WAKEUP_LP_IRQ interrupt request.	
1	-	-	0x0
		Reserved	
0	R/W	BLE_WAKEUP_REQ	0x0
		If 1, the BLE wakes up. Must be kept high at least for 1 low power clock period. If the BLE is in deep sleep state, then by setting this bit it will cause the wake-up LP IRQ to be asserted with a delay of 3 to 4 low power cycles.	

Table 219: BLE_TIMER_REG (0x5000330A)

Bit	Mode	Symbol/Description	Reset
15:10	-	-	0x0
		Reserved	
9:0	R/W	BLE_TIMER_DATA	0x0
		Operation depends on GP_CONTROL_REG->BLE_TIMER_DATA_CTRL. If BLE_TIMER_DATA_CTRL = 0 then:	
		This register is located at the Always On Power Domain and it holds the automatically sampled value of the BLE FINECNT timer	
		The HW automatically samples the value into this register during the sequence of "BLE Sleep On" and restores automatically the value during the BLE Wake up sequence.	
		The Software may read and modify the value while the BLE is in Sleep state. While the BLE is awake, the value of the register has no meaning, while changing the value by writing another one will have no effect in the operation of the BLE core.	
		There is a constraint when the SW performs an write-read sequence where it has to inject a one cycle delay in between (e.g. write-NOP-read) in order to read back the correct value.	
		If BLE_TIMER_DATA_CTRL is non 0 then write operations have the same effect as when BLE_TIMER_DATA_CTRL=0, while for read operations:	
		BLE_TIMER_DATA_CTRL= 1: then reading BLE_TIMER_REG returns "deepsldur[9:0]".	
		BLE_TIMER_DATA_CTRL= 2: then reading BLE_TIMER_REG returns "deepsltime_samp[9:0]".	
		BLE_TIMER_DATA_CTRL= 3: then reading BLE_TIMER_REG returns "{deep_stat_monitor, deepsltime_samp[18:10]}.	

32.9 I2C Interface Registers

Table 220: Register map I2C

Address	Register	Description
0x50001300	I2C_CON_REG	I2C Control Register
0x50001304	I2C_TAR_REG	I2C Target Address Register
0x50001308	I2C_SAR_REG	I2C Slave Address Register
0x50001310	I2C_DATA_CMD_REG	I2C RX/TX Data Buffer and Command Register
0x50001314	I2C_SS_SCL_HCNT_RE G	Standard Speed I2C Clock SCL High Count Register
0x50001318	I2C_SS_SCL_LCNT_RE G	Standard Speed I2C Clock SCL Low Count Register
0x5000131c	I2C_FS_SCL_HCNT_RE G	Fast Speed I2C Clock SCL High Count Register
0x50001320	I2C_FS_SCL_LCNT_RE G	Fast Speed I2C Clock SCL Low Count Register
0x5000132c	I2C_INTR_STAT_REG	I2C Interrupt Status Register
0x50001330	I2C_INTR_MASK_REG	I2C Interrupt Mask Register
0x50001334	I2C_RAW_INTR_STAT_ REG	I2C Raw Interrupt Status Register
0x50001338	I2C_RX_TL_REG	I2C Receive FIFO Threshold Register
0x5000133c	I2C_TX_TL_REG	I2C Transmit FIFO Threshold Register
0x50001340	I2C_CLR_INTR_REG	Clear Combined and Individual Interrupt Register
0x50001344	I2C_CLR_RX_UNDER_R EG	Clear RX_UNDER Interrupt Register
0x50001348	I2C_CLR_RX_OVER_RE G	Clear RX_OVER Interrupt Register
0x5000134c	I2C_CLR_TX_OVER_RE G	Clear TX_OVER Interrupt Register
0x50001350	I2C_CLR_RD_REQ_REG	Clear RD_REQ Interrupt Register
0x50001354	I2C_CLR_TX_ABRT_RE G	Clear TX_ABRT Interrupt Register
0x50001358	I2C_CLR_RX_DONE_RE G	Clear RX_DONE Interrupt Register
0x5000135c	I2C_CLR_ACTIVITY_RE G	Clear ACTIVITY Interrupt Register
0x50001360	I2C_CLR_STOP_DET_R EG	Clear STOP_DET Interrupt Register
0x50001364	I2C_CLR_START_DET_ REG	Clear START_DET Interrupt Register
0x50001368	I2C_CLR_GEN_CALL_R EG	Clear GEN_CALL Interrupt Register
0x5000136c	I2C_ENABLE_REG	I2C Enable Register
0x50001370	I2C_STATUS_REG	I2C Status Register
0x50001374	I2C_TXFLR_REG	I2C Transmit FIFO Level Register
0x50001378	I2C_RXFLR_REG	I2C Receive FIFO Level Register
0x5000137c	I2C_SDA_HOLD_REG	I2C SDA Hold Time Length Register

Address	Register	Description
0x50001380	I2C_TX_ABRT_SOURCE _REG	I2C Transmit Abort Source Register
0x50001388	I2C_DMA_CR_REG	DMA Control Register
0x5000138c	I2C_DMA_TDLR_REG	DMA Transmit Data Level Register
0x50001390	I2C_DMA_RDLR_REG	I2C Receive Data Level Register
0x50001394	I2C_SDA_SETUP_REG	I2C SDA Setup Register
0x50001398	I2C_ACK_GENERAL_CA LL_REG	I2C ACK General Call Register
0x5000139c	I2C_ENABLE_STATUS_ REG	I2C Enable Status Register
0x500013a0	I2C_IC_FS_SPKLEN_RE G	I2C SS and FS spike suppression limit Size

Table 221: I2C_CON_REG (0x50001300)

Bit	Mode	Symbol/Description	Reset
15:7	-	-	0x0
		Reserved	
6	R/W	I2C_SLAVE_DISABLE	0x1
		Slave enabled or disabled after reset is applied, which means software does not have to configure the slave.	
		0 = Slave is enabled	
		1 = Slave is disabled	
		Software should ensure that if this bit is written with "0", then bit 0 should also be written with "0".	
5	R/W	I2C_RESTART_EN	0x1
		Determines whether RESTART conditions may be sent when acting as a master 0 = Disable	
		1 = Enable	
4	R/W	I2C_10BITADDR_MASTER	0x1
		Controls whether the controller starts its transfers in 7- or 10-bit addressing mode when acting as a master.	
		0 = 7-bit addressing	
		1 = 10-bit addressing	
3	R/W	I2C_10BITADDR_SLAVE	0x1
		When acting as a slave, this bit controls whether the controller responds to 7- or 10-bit addresses.	
		0 = 7-bit addressing	
		1 = 10-bit addressing	
2:1	R/W	I2C_SPEED	0x2
		These bits control at which speed the controller operates.	
		1 = Standard mode (100 kbit/s)	
		2 = Fast mode (400 kbit/s)	
		Note: The actuall speed depends on the pcb traces capacitance as well as on the values of the external pull-up resistorts. For an exact speed match, trimming might be required, by adjusting the values of I2C_SS_SCL_HCNT_REG, I2C_SS_SCL_LCNT_REG, I2C_FS_SCL_LCNT_REG	

Bit	Mode	Symbol/Description	Reset
		registers. The reset values of those registers were calculated with the assumption of 4.3 k Ω external pull-up resistors.	
0	R/W	I2C_MASTER_MODE	0x1
		This bit controls whether the controller master is enabled.	
		0 = Master disabled	
		1 = Master enabled	
		Software should ensure that if this bit is written with "1", then bit 6 should also be written with "1".	

Table 222: I2C_TAR_REG (0x50001304)

Bit	Mode	Symbol/Description	Reset
15:12	-	-	0x0
		Reserved	
11	R/W	SPECIAL	0x0
		This bit indicates whether software performs a General Call or START BYTE command.	
		0: Ignore bit 10 GC_OR_START and use IC_TAR normally	
		1: Perform special I2C command as specified in GC_OR_START bit	
10	R/W	GC_OR_START	0x0
		If bit 11 (SPECIAL) is set to 1, then this bit indicates whether a General Call or START byte command is to be performed by the controller.	
		0: General Call Address - after issuing a General Call, only writes may be performed. Attempting to issue a read command results in setting bit 6 (TX_ABRT) of the IC_RAW_INTR_STAT register. The controller remains in General Call mode until the SPECIAL bit value (bit 11) is cleared.	
		1: START BYTE	
9:0	R/W	IC_TAR	0x55
		This is the target address for any master transaction. When transmitting a General Call, these bits are ignored. To generate a START BYTE, the CPU needs to write only once into these bits.	
		Note: If the IC_TAR and IC_SAR are the same, loopback exists but the FIFOs are shared between master and slave, so full loopback is not feasible. Only one direction loopback mode is supported (simplex), not duplex. A master cannot transmit to itself; it can transmit to only a slave.	

Table 223: I2C_SAR_REG (0x50001308)

Bit	Mode	Symbol/Description	Reset
15:10	-	-	0x0
		Reserved	
9:0	R/W	IC_SAR	0x55
		The IC_SAR holds the slave address when the I2C is operating as a slave. For 7-bit addressing, only IC_SAR[6:0] is used. This register can be written only when the I2C interface is disabled, which corresponds to the IC_ENABLE register being set to 0. Writes at other times have no effect.	

Table 224: I2C_DATA_CMD_REG (0x50001310)

Bit	Mode	Symbol/Description	Reset
15:11	-		0x0
		Reserved	
10	R/W	I2C_RESTART	0x0
		This bit controls whether a RESTART is issued before the byte is sent or received. If IC_RESTART_EN is 1, a RESTART is issued before the data is sent/received (according to the value of CMD), regardless of whether or not the transfer direction is changing from the previous command; if IC_RESTART_EN is 0, a STOP followed by a START is issued instead. If IC_RESTART_EN is 1, a RESTART is issued only if the transfer direction is changing from the previous command; if IC_RESTART_EN is 0, a STOP followed by a START is issued instead. Reset value: 0x0	
9	R/W	I2C_STOP	0x0
		This bit controls whether a STOP is issued after the byte is sent or received. STOP is issued after this byte, regardless of whether or not the TX FIFO is empty. If the TX FIFO is not empty, the master immediately tries to start a new transfer by issuing a START and arbitrating for the bus. STOP is not issued after this byte, regardless of whether or not the TX FIFO is empty. If the TX FIFO is not empty, the master continues the current transfer by sending/receiving data bytes according to the value of the CMD bit. If the TX FIFO is empty, the master holds the SCL line low and stalls the bus until a new command is available in the TX FIFO. Reset value: 0x0	
8	R/W	I2C_CMD	0x0
		This bit controls whether a read or a write is performed. This bit does not control the direction when the I2C Ctrl acts as a slave. It controls only the direction when it acts as a master.	
		1 = Read	
		When a command is entered in the TX FIFO, this bit distinguishes the write and read commands. In slave-receiver mode, this bit is a "don't care" because writes to this register are not required. In slave-transmitter mode, a "0" indicates that CPU data is to be transmitted and as DAT or IC_DATA_CMD[7:0]. When programming this bit, you should remember the following: attempting to perform a read operation after a General Call command has been sent results in a TX_ABRT interrupt (bit 6 of the I2C_RAW_INTR_STAT_REG), unless bit 11 (SPECIAL) in the I2C_TAR register has been cleared.	
		If a "1" is written to this bit after receiving a RD_REQ interrupt, then a TX_ABRT interrupt occurs.	
		NOTE: It is possible that while attempting a master I2C read transfer on the controller, a RD_REQ interrupt may have occurred simultaneously due to a remote I2C master addressing the controller. In this type of scenario, it ignores the I2C_DATA_CMD write, generates a TX_ABRT interrupt, and waits to service the RD_REQ interrupt	
7:0	R/W	DAT	0x0
		This register contains the data to be transmitted or received on the I2C bus. If you are writing to this register and want to perform a read, bits 7:0 (DAT) are ignored by the controller. However, when you read this register, these bits return the value of data received on the controller's interface.	

Table 225: I2C_SS_SCL_HCNT_REG (0x50001314)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	IC_SS_SCL_HCNT	0x48

Bit	Mode	Symbol/Description	Reset
		This register must be set before any I2C bus transaction can take place to ensure proper I/O timing. This register sets the SCL clock high-period count for standard speed. This register can be written only when the I2C interface is disabled which corresponds to the IC_ENABLE register being set to 0. Writes at other times have no effect.	
		The minimum valid value is 6; hardware prevents values less than this being written, and if attempted results in 6 being set.	
		NOTE: This register must not be programmed to a value higher than 65525, because the controller uses a 16-bit counter to flag an I2C bus idle condition when this counter reaches a value of IC_SS_SCL_HCNT + 10.	

Table 226: I2C_SS_SCL_LCNT_REG (0x50001318)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	IC_SS_SCL_LCNT	0x4F
		This register must be set before any I2C bus transaction can take place to ensure proper I/O timing. This register sets the SCL clock low period count for standard speed.	
		This register can be written only when the I2C interface is disabled which corresponds to the I2C_ENABLE register being set to 0. Writes at other times have no effect.	
		The minimum valid value is 8; hardware prevents values less than this being written, and if attempted, results in 8 being set.	

Table 227: I2C_FS_SCL_HCNT_REG (0x5000131C)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	IC_FS_SCL_HCNT	0x8
		This register must be set before any I2C bus transaction can take place to ensure proper I/O timing. This register sets the SCL clock high-period count for fast speed. It is used in high-speed mode to send the Master Code and START BYTE or General CALL. This register can be written only when the I2C interface is disabled, which corresponds to the I2C_ENABLE register being set to 0. Writes at other times have no effect.	
		The minimum valid value is 6; hardware prevents values less than this being written, and if attempted results in 6 being set.	

Table 228: I2C_FS_SCL_LCNT_REG (0x50001320)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	IC_FS_SCL_LCNT	0x17
		This register must be set before any I2C bus transaction can take place to ensure proper I/O timing. This register sets the SCL clock low-period count for fast speed. It is used in high-speed mode to send the Master Code and START BYTE or General CALL. This register can be written only when the I2C interface is disabled, which corresponds to the I2C_ENABLE register being set to 0. Writes at other times have no effect.	
		The minimum valid value is 8; hardware prevents values less than this being written, and if attempted results in 8 being set. For designs with APB_DATA_WIDTH = 8 the order of programming is important to ensure the correct operation of the controller. The lower byte must be programmed first. Then the upper byte is programmed.	

Table 229: I2C_INTR_STAT_REG (0x5000132C)

Bit	Mode	Symbol/Description	Reset
15:12	-	-	0x0
		Reserved	
11	R	R_GEN_CALL	0x0
		Set only when a General Call address is received and it is acknowledged. It stays set until it is cleared either by disabling controller or when the CPU reads bit 0 of the I2C_CLR_GEN_CALL register. The controller stores the received data in the RX buffer.	
10	R	R_START_DET	0x0
		Indicates whether a START or RESTART condition has occurred on the I2C interface regardless of whether controller is operating in Slave or Master mode.	
9	R	R_STOP_DET	0x0
		Indicates whether a STOP condition has occurred on the I2C interface regardless of whether controller is operating in Slave or Master mode.	
8	R	R_ACTIVITY	0x0
		This bit captures I2C Ctrl activity and stays set until it is cleared. There are four ways to clear it: => Disabling the I2C Ctrl => Reading the IC_CLR_ACTIVITY register	
		=> Reading the IC_CLR_INTR register	
		=> System reset	
		When this bit is set, it stays set unless one of the four methods is used to clear it. Even if the controller module is idle, this bit remains set until cleared, indicating that there was activity on the bus.	
7	R	R_RX_DONE	0x0
		When the controller is acting as a slave-transmitter, this bit is set to 1 if the master does not acknowledge a transmitted byte. This occurs on the last byte of the transmission, indicating that the transmission is done.	
6	R	R_TX_ABRT	0x0
		This bit indicates if the controller, as an I2C transmitter, is unable to complete the intended actions on the contents of the transmit FIFO. This situation can occur both as an I2C master or an I2C slave, and is referred to as a "transmit abort". When this bit is set to 1, the I2C_TX_ABRT_SOURCE register indicates the reason why the transmit abort takes place.	
		NOTE: The controller flushes/resets/empties the TX FIFO whenever this bit is set. The TX FIFO remains in this flushed state until the register I2C_CLR_TX_ABRT is read. When this read is performed, the TX FIFO is then ready to accept more data bytes from the APB interface.	
5	R	R_RD_REQ	0x0
		This bit is set to 1 when the controller is acting as a slave and another I2C master is attempting to read data from the controller. The controller holds the I2C bus in a wait state (SCL = 0) until this interrupt is serviced, which means that the slave has been addressed by a remote master that is asking for data to be transferred. The processor must respond to this interrupt and then write the requested data to the I2C_DATA_CMD register. This bit is set to 0 just after the processor reads the I2C_CLR_RD_REQ register.	
4	R	R_TX_EMPTY	0x0
		This bit is set to 1 when the transmit buffer is at or below the threshold value set in the I2C_TX_TL register. It is automatically cleared by hardware when the buffer level goes above the threshold. When the IC_ENABLE bit 0 is 0, the TX FIFO is	

Bit	Mode	Symbol/Description	Reset
		flushed and held in reset. There the TX FIFO looks like it has no data within it, so this bit is set to 1, provided there is activity in the master or slave state machines. When there is no longer activity, then with ic_en = 0, this bit is set to 0.	
3	R	R_TX_OVER	0x0
		Set during transmit if the transmit buffer is filled to 32 and the processor attempts to issue another I2C command by writing to the IC_DATA_CMD register. When the module is disabled, this bit keeps its level until the master or slave state machines go into idle, and when ic_en goes to 0, this interrupt is cleared.	
2	R	R_RX_FULL	0x0
		Set when the receive buffer reaches or goes above the RX_TL threshold in the I2C_RX_TL register. It is automatically cleared by hardware when buffer level goes below the threshold. If the module is disabled (I2C_ENABLE[0] = 0), the RX FIFO is flushed and held in reset; therefore, the RX FIFO is not full. So this bit is cleared when the I2C_ENABLE bit 0 is programmed with a 0, regardless of the activity that continues.	
1	R	R_RX_OVER	0x0
		Set if the receive buffer is completely filled to 32 and an additional byte is received from an external I2C device. The controller acknowledges this, but any data bytes received after the FIFO is full are lost. If the module is disabled (I2C_ENABLE[0] = 0), this bit keeps its level until the master or slave state machines go into idle, and when ic_en goes to 0, this interrupt is cleared.	
0	R	R_RX_UNDER	0x0
		Set if the processor attempts to read the receive buffer when it is empty by reading from the IC_DATA_CMD register. If the module is disabled (I2C_ENABLE[0] = 0), this bit keeps its level until the master or slave state machines go into idle, and when ic_en goes to 0, this interrupt is cleared.	

Table 230: I2C_INTR_MASK_REG (0x50001330)

Bit	Mode	Symbol/Description	Reset
15:12	-		0x0
		Reserved	
11	R/W	M_GEN_CALL	0x1
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	
10	R/W	M_START_DET	0x0
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	
9	R/W	M_STOP_DET	0x0
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	
8	R/W	M_ACTIVITY	0x0
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	
7	R/W	M_RX_DONE	0x1
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	
6	R/W	M_TX_ABRT	0x1

Bit	Mode	Symbol/Description	Reset
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	
5	R/W	M_RD_REQ	0x1
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	
4	R/W	M_TX_EMPTY	0x1
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	
3	R/W	M_TX_OVER	0x1
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	
2	R/W	M_RX_FULL	0x1
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	
1	R/W	M_RX_OVER	0x1
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	
0	R/W	M_RX_UNDER	0x1
		These bits mask their corresponding interrupt status bits in the I2C_INTR_STAT register.	

Table 231: I2C_RAW_INTR_STAT_REG (0x50001334)

Bit	Mode	Symbol/Description	Reset
15:12	-	-	0x0
		Reserved	
11	R	GEN_CALL	0x0
		Set only when a General Call address is received and it is acknowledged. It stays set until it is cleared either by disabling controller or when the CPU reads bit 0 of the I2C_CLR_GEN_CALL register. I2C Ctrl stores the received data in the RX buffer.	
10	R	START_DET	0x0
		Indicates whether a START or RESTART condition has occurred on the I2C interface regardless of whether controller is operating in Slave or Master mode.	
9	R	STOP_DET	0x0
		Indicates whether a STOP condition has occurred on the I2C interface regardless of whether controller is operating in slave or master mode.	
8	R	ACTIVITY	0x0
		This bit captures I2C Ctrl activity and stays set until it is cleared. There are four ways to clear it:	
		=> Disabling the I2C Ctrl	
		=> Reading the IC_CLR_ACTIVITY register	
		=> Reading the IC_CLR_INTR register	
		=> System reset	
		When this bit is set, it stays set unless one of the four methods is used to clear it. Even if the controller module is idle, this bit remains set until cleared, indicating that there was activity on the bus.	

Bit	Mode	Symbol/Description	Reset
7	R	RX_DONE	0x0
		When the controller is acting as a slave-transmitter, this bit is set to 1 if the master does not acknowledge a transmitted byte. This occurs on the last byte of the transmission, indicating that the transmission is done.	
6	R	TX_ABRT	0x0
		This bit indicates if the controller, as an I2C transmitter, is unable to complete the intended actions on the contents of the transmit FIFO. This situation can occur both as an I2C master or an I2C slave, and is referred to as a "transmit abort".	
		When this bit is set to 1, the I2C_TX_ABRT_SOURCE register indicates the reason why the transmit abort takes place.	
		NOTE: The controller flushes/resets/empties the TX FIFO whenever this bit is set. The TX FIFO remains in this flushed state until the register I2C_CLR_TX_ABRT is read. When this read is performed, the TX FIFO is then ready to accept more data bytes from the APB interface.	
5	R	RD_REQ	0x0
		This bit is set to 1 when I2C Ctrl is acting as a slave and another I2C master is attempting to read data from the controller. The controller holds the I2C bus in a wait state (SCL = 0) until this interrupt is serviced, which means that the slave has been addressed by a remote master that is asking for data to be transferred. The processor must respond to this interrupt and then write the requested data to the I2C_DATA_CMD register. This bit is set to 0 just after the processor reads the I2C_CLR_RD_REQ register	
4	R	TX_EMPTY	0x0
		This bit is set to 1 when the transmit buffer is at or below the threshold value set in the I2C_TX_TL register. It is automatically cleared by hardware when the buffer level goes above the threshold. When the IC_ENABLE bit 0 is 0, the TX FIFO is flushed and held in reset. There the TX FIFO looks like it has no data within it, so this bit is set to 1, provided there is activity in the master or slave state machines. When there is no longer activity, then with ic_en=0, this bit is set to 0.	
3	R	TX_OVER	0x0
		Set during transmit if the transmit buffer is filled to 32 and the processor attempts to issue another I2C command by writing to the IC_DATA_CMD register. When the module is disabled, this bit keeps its level until the master or slave state machines go into idle, and when ic_en goes to 0, this interrupt is cleared	
2	R	RX_FULL	0x0
		Set when the receive buffer reaches or goes above the RX_TL threshold in the I2C_RX_TL register. It is automatically cleared by hardware when buffer level goes below the threshold. If the module is disabled (I2C_ENABLE[0] = 0), the RX FIFO is flushed and held in reset; therefore the RX FIFO is not full. So this bit is cleared when the I2C_ENABLE bit 0 is programmed with a 0, regardless of the activity that continues.	
1	R	RX_OVER	0x0
		Set if the receive buffer is completely filled to 32 and an additional byte is received from an external I2C device. The controller acknowledges this, but any data bytes received after the FIFO is full are lost. If the module is disabled (I2C_ENABLE[0] = 0), this bit keeps its level until the master or slave state machines go into idle, and when ic_en goes to 0, this interrupt is cleared.	
0	R	RX_UNDER	0x0
		Set if the processor attempts to read the receive buffer when it is empty by reading from the IC_DATA_CMD register. If the module is disabled (I2C_ENABLE[0]=0), this bit keeps its level until the master or slave state machines go into idle, and when ic_en goes to 0, this interrupt is cleared.	

Table 232: I2C_RX_TL_REG (0x50001338)

Bit	Mode	Symbol/Description	Reset
15:5	-	-	0x0
		Reserved	
4:0	R/W	RX_TL	0x0
		Receive FIFO Threshold Level Controls the level of entries (or above) that triggers the RX_FULL interrupt (bit 2 in I2C_RAW_INTR_STAT register). The valid range is 0-31, with the additional restriction that hardware does not allow this value to be set to a value larger than the depth of the buffer. If an attempt is made to do that, the actual value set is the maximum depth of the buffer. A value of 0 sets the threshold for 1 entry, and a value of 31 sets the threshold for 32 entries.	

Table 233: I2C_TX_TL_REG (0x5000133C)

Bit	Mode	Symbol/Description	Reset
15:5	-	-	0x0
		Reserved	
4:0	R/W	RX_TL	0x0
		Transmit FIFO Threshold Level Controls the level of entries (or below) that trigger the TX_EMPTY interrupt (bit 4 in I2C_RAW_INTR_STAT register). The valid range is 0-31, with the additional restriction that it may not be set to the value larger than the depth of the buffer. If an attempt is made to do that, the actual value set is the maximum depth of the buffer. A value of 0 sets the threshold for 0 entries, and a value of 31 sets the threshold for 32 entries.	

Table 234: I2C_CLR_INTR_REG (0x50001340)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R	CLR_INTR	0x0
		Read this register to clear the combined interrupt, all individual interrupts, and the I2C_TX_ABRT_SOURCE register. This bit does not clear hardware clearable interrupts but software clearable interrupts. Refer to Bit 9 of the I2C_TX_ABRT_SOURCE register for an exception to clearing I2C_TX_ABRT_SOURCE	

Table 235: I2C_CLR_RX_UNDER_REG (0x50001344)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R	CLR_RX_UNDER	0x0
		Read this register to clear the RX_UNDER interrupt (bit 0) of the I2C_RAW_INTR_STAT register.	

Table 236: I2C_CLR_RX_OVER_REG (0x50001348)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0

Bit	Mode	Symbol/Description	Reset
		Reserved	
0	R	CLR_RX_OVER	0x0
		Read this register to clear the RX_OVER interrupt (bit 1) of the I2C_RAW_INTR_STAT register.	

Table 237: I2C_CLR_TX_OVER_REG (0x5000134C)

Bit	Mode	Symbol/Description	Reset
15:1	-		0x0
		Reserved	
0	R	CLR_TX_OVER	0x0
		Read this register to clear the TX_OVER interrupt (bit 3) of the I2C_RAW_INTR_STAT register.	

Table 238: I2C_CLR_RD_REQ_REG (0x50001350)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R	CLR_RD_REQ	0x0
		Read this register to clear the RD_REQ interrupt (bit 5) of the I2C_RAW_INTR_STAT register.	

Table 239: I2C_CLR_TX_ABRT_REG (0x50001354)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R	CLR_TX_ABRT	0x0
		Read this register to clear the TX_ABRT interrupt (bit 6) of the IC_RAW_INTR_STAT register, and the I2C_TX_ABRT_SOURCE register. This also releases the TX FIFO from the flushed/reset state, allowing more writes to the TX FIFO. See Bit 9 of the I2C_TX_ABRT_SOURCE register for an exception to clearing IC_TX_ABRT_SOURCE.	

Table 240: I2C_CLR_RX_DONE_REG (0x50001358)

Bit	Mode	Symbol/Description	Reset
15:1	-		0x0
		Reserved	
0	R	CLR_RX_DONE	0x0
		Read this register to clear the RX_DONE interrupt (bit 7) of the I2C_RAW_INTR_STAT register.	

Table 241: I2C_CLR_ACTIVITY_REG (0x5000135C)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R	CLR_ACTIVITY	0x0
		Reading this register clears the ACTIVITY interrupt if the I2C is not active anymore. If the I2C module is still active on the bus, the ACTIVITY interrupt bit continues to be set. It is automatically cleared by hardware if the module is disabled and if there is no further activity on the bus. The value read from this register to get status of the ACTIVITY interrupt (bit 8) of the IC_RAW_INTR_STAT register.	

Table 242: I2C_CLR_STOP_DET_REG (0x50001360)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R	CLR_STOP_DET	0x0
		Read this register to clear the STOP_DET interrupt (bit 9) of the IC_RAW_INTR_STAT register. Reset value: 0x0	

Table 243: I2C_CLR_START_DET_REG (0x50001364)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R	CLR_START_DET	0x0
		Read this register to clear the START_DET interrupt (bit 10) of the IC_RAW_INTR_STAT register.	

Table 244: I2C_CLR_GEN_CALL_REG (0x50001368)

Bit	Mode	Symbol/Description	Reset
15:1	-		0x0
		Reserved	
0	R	CLR_GEN_CALL	0x0
		Read this register to clear the GEN_CALL interrupt (bit 11) of the I2C_RAW_INTR_STAT register.	

Table 245: I2C_ENABLE_REG (0x5000136C)

Bit	Mode	Symbol/Description	Reset
15:2	-	-	0x0
		Reserved	
1	R/W	I2C_ABORT	0x0
		0 = ABORT not initiated or ABORT done	
		1 = ABORT operation in progress	

Bit	Mode	Symbol/Description	Reset
		The software can abort the I2C transfer in Master mode by setting this bit. The software can set this bit only when ENABLE is already set; otherwise, the controller ignores any write to ABORT bit. The software cannot clear the ABORT bit when set. In response to an ABORT, the controller issues a STOP and flushes the TX FIFO after completing the current transfer, then sets the TX_ABORT interrupt after the abort operation. The ABORT bit is cleared automatically after the abort operation.	
0	R/W	CTRL_ENABLE	0x0
		Controls whether the controller is enabled.	
		0: Disables the controller (TX and RX FIFOs are held in an erased state)	
		1: Enables the controller	
		Software can disable the controller while it is active. However, it is important that care be taken to ensure that the controller is disabled properly. When the controller is disabled, the following occurs:	
		* The TX FIFO and RX FIFO get flushed.	
		* Status bits in the IC_INTR_STAT register are still active until the controller goes into IDLE state.	
		If the module is transmitting, it stops as well as deletes the contents of the transmit buffer after the current transfer is complete. If the module is receiving, the controller stops the current transfer at the end of the current byte and does not acknowledge the transfer.	
		There is a two ic_clk delay when enabling or disabling the controller.	

Table 246: I2C_STATUS_REG (0x50001370)

Bit	Mode	Symbol/Description	Reset
15:7	-	-	0x0
		Reserved	
6	R	SLV_ACTIVITY	0x0
		Slave FSM Activity Status. When the Slave Finite State Machine (FSM) is not in the IDLE state, this bit is set.	
		0: Slave FSM is in IDLE state so the Slave part of the controller is not Active	
		1: Slave FSM is not in IDLE state so the Slave part of the controller is Active	
5	R	MST_ACTIVITY	0x0
		Master FSM Activity Status. When the Master Finite State Machine (FSM) is not in the IDLE state, this bit is set.	
		0: Master FSM is in IDLE state so the Master part of the controller is not Active	
		1: Master FSM is not in IDLE state so the Master part of the controller is Active	
4	R	RFF	0x0
		Receive FIFO Completely Full. When the receive FIFO is completely full, this bit is set. When the receive FIFO contains one or more empty location, this bit is cleared.	
		0: Receive FIFO is not full	
		1: Receive FIFO is full	
3	R	RFNE	0x0
		Receive FIFO Not Empty. This bit is set when the receive FIFO contains one or more entries; it is cleared when the receive FIFO is empty.	
		0: Receive FIFO is empty	
		1: Receive FIFO is not empty	
2	R	TFE	0x1

Bit	Mode	Symbol/Description	Reset
		Transmit FIFO Completely Empty. When the transmit FIFO is completely empty, this bit is set. When it contains one or more valid entries, this bit is cleared. This bit field does not request an interrupt.	
		0: Transmit FIFO is not empty	
		1: Transmit FIFO is empty	
1	R	TFNF	0x1
		Transmit FIFO Not Full. Set when the transmit FIFO contains one or more empty locations, and is cleared when the FIFO is full.	
		0: Transmit FIFO is full	
		1: Transmit FIFO is not full	
0	R	I2C_ACTIVITY	0x0
		I2C Activity Status.	

Table 247: I2C_TXFLR_REG (0x50001374)

Bit	Mode	Symbol/Description	Reset
15:6	-		0x0
		Reserved	
5:0	R	TXFLR	0x0
		Transmit FIFO Level. Contains the number of valid data entries in the transmit FIFO. Size is constrained by the TXFLR value	

Table 248: I2C_RXFLR_REG (0x50001378)

Bit	Mode	Symbol/Description	Reset
15:6	-		0x0
		Reserved	
5:0	R	RXFLR	0x0
		Receive FIFO Level. Contains the number of valid data entries in the receive FIFO. Size is constrained by the RXFLR value.	

Table 249: I2C_SDA_HOLD_REG (0x5000137C)

Bi	it	Mode	Symbol/Description	Reset
15	5:0	R/W	IC_SDA_HOLD	0x1
			SDA Hold time	

Table 250: I2C_TX_ABRT_SOURCE_REG (0x50001380)

Bit	Mode	Symbol/Description	Reset
15	R	ABRT_SLVRD_INTX	0x0
		When the processor side responds to Slave mode request for data to be transmitted to a remote master and user writes 1 in CMD (bit 8) of 2IC_DATA_CMD register.	
14	R	ABRT_SLV_ARBLOST	0x0
		Slave lost the bus while transmitting data to a remote master. I2C_TX_ABRT_SOURCE[12] is set at the same time. Note: Even though the slave never "owns" the bus, something could go wrong on the bus. This is a fail safe.	

Bit	Mode	Symbol/Description	Reset
		check. For instance, during a data transmission at the low-to-high transition of SCL, if what is on the data bus is not what is supposed to be transmitted, then the controller no longer owns the bus.	
13	R	ABRT_SLVFLUSH_TXFIFO	0x0
		1: Slave has received a read command and some data exists in the TX FIFO so the slave issues a TX_ABRT interrupt to flush old data in TX FIFO.	
12	R	ARB_LOST	0x0
		1: Master has lost arbitration, or if I2C_TX_ABRT_SOURCE[14] is also set, then the slave transmitter has lost arbitration. Note: I2C can be both master and slave at the same time.	
11	R	ABRT_MASTER_DIS	0x0
		1: User tries to initiate a Master operation with the Master mode disabled.	
10	R	ABRT_10B_RD_NORSTRT	0x0
		1: The restart is disabled (IC_RESTART_EN bit (I2C_CON[5]) = 0) and the master sends a read command in 10-bit addressing mode.	
9	R	ABRT_SBYTE_NORSTRT	0x0
		To clear Bit 9, the source of the ABRT_SBYTE_NORSTRT must be fixed first; restart must be enabled (I2C_CON[5]=1), the SPECIAL bit must be cleared (I2C_TAR[11]), or the GC_OR_START bit must be cleared (I2C_TAR[10]). When the source of the ABRT_SBYTE_NORSTRT is fixed, then this bit can be cleared in the same manner as other bits in this register. If the source of the ABRT_SBYTE_NORSTRT is not fixed before attempting to clear this bit, bit 9 clears for one cycle and then gets re-asserted. 1: The restart is disabled (IC_RESTART_EN bit (I2C_CON[5]) = 0) and the user is trying to send a START Byte.	
8	R	ABRT_HS_NORSTRT	0x0
		1: The restart is disabled (IC_RESTART_EN bit (I2C_CON[5]) = 0) and the user is trying to use the master to transfer data in High Speed mode.	
7	R	ABRT_SBYTE_ACKDET	0x0
		1: Master has sent a START Byte and the START Byte was acknowledged (wrong behavior).	
6	R	ABRT_HS_ACKDET	0x0
		1: Master is in High Speed mode and the High Speed Master code was acknowledged (wrong behavior).	
5	R	ABRT_GCALL_READ	0x0
		1: The controller in master mode sent a General Call but the user programmed the byte following the General Call to be a read from the bus (IC_DATA_CMD[9] is set to 1).	
4	R	ABRT_GCALL_NOACK	0x0
		1: The controller in master mode sent a General Call and no slave on the bus acknowledged the General Call.	
3	R	ABRT_TXDATA_NOACK	0x0
		1: This is a master-mode only bit. Master has received an acknowledgement for the address, but when it sent data byte(s) following the address, it did not receive an acknowledgement from the remote slave(s).	
2	R	ABRT_10ADDR2_NOACK	0x0
		1: Master is in 10-bit address mode and the second address byte of the 10-bit address was not acknowledged by any slave.	
1	R	ABRT_10ADDR1_NOACK	0x0

Bit	Mode	Symbol/Description	Reset
		Master is in 10-bit address mode and the first 10-bit address byte was not acknowledged by any slave.	
0	R	ABRT_7B_ADDR_NOACK	0x0
		1: Master is in 7-bit addressing mode and the address sent was not acknowledged by any slave.	

Table 251: I2C_DMA_CR_REG (0x50001388)

Bit	Mode	Symbol/Description	Reset
1	R/W	TDMAE	0x0
	Transmit DMA Enable. This bit enables/disables the transmit FIFO DMA channel. 0 = Transmit DMA disabled 1 = Transmit DMA enabled		
0	R/W RDMAE		0x0
		Receive DMA Enable. This bit enables/disables the receive FIFO DMA channel. 0 = Receive DMA disabled 1 = Receive DMA enabled	

Table 252: I2C_DMA_TDLR_REG (0x5000138C)

Bit	Mode	Symbol/Description	Reset
4:0	R/W	DMATDL	0x0
		Transmit Data Level. This bit field controls the level at which a DMA request is made by the transmit logic. It is equal to the watermark level; that is, the dma_tx_req signal is generated when the number of valid data entries in the transmit FIFO is equal to or below this field value, and TDMAE = 1.	

Table 253: I2C_DMA_RDLR_REG (0x50001390)

Bit	Mode	Symbol/Description	Reset
4:0 R/W DMARDL		DMARDL	0x0
		Receive Data Level. This bit field controls the level at which a DMA request is made by the receive logic. The watermark level = DMARDL+1; that is, dma_rx_req is generated when the number of valid data entries in the receive FIFO is equal to or more than this field value + 1, and RDMAE =1. For instance, when DMARDL is 0, then dma_rx_req is asserted when 1 or more data entries are present in the receive FIFO.	

Table 254: I2C_SDA_SETUP_REG (0x50001394)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SDA_SETUP	0x64
		SDA Setup.	
		This register controls the amount of time delay (number of I2C clock periods) between the rising edge of SCL and SDA changing by holding SCL low when I2C block services a read request while operating as a slave-transmitter. The relevant I2C requirement is tSU:DAT (note 4) as detailed in the I2C Bus Specification. This register must be programmed with a value equal to or greater than 2.	

Bit	Mode	Symbol/Description	Reset
		It is recommended that if the required delay is 1000 ns, then for an I2C frequency of 10 MHz, IC_SDA_SETUP should be programmed to a value of 11. Writes to this register succeed only when IC_ENABLE[0] = 0.	

Table 255: I2C_ACK_GENERAL_CALL_REG (0x50001398)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	
		Reserved	
0	R/W ACK_GEN_CALL		0x0
		ACK General Call. When set to 1, I2C Ctrl responds with a ACK (by asserting ic_data_oe) when it receives a General Call. When set to 0, the controller does not generate General Call interrupts.	

Table 256: I2C_ENABLE_STATUS_REG (0x5000139C)

Bit	Mode	Symbol/Description	Reset
15:3	-	-	0x0
		Reserved	
2	R	SLV_RX_DATA_LOST	0x0
		Slave Received Data Lost. This bit indicates if a Slave-Receiver operation has been aborted with at least one data byte received from an I2C transfer due to the setting of IC_ENABLE from 1 to 0. When read as 1, the controller is deemed to have been actively engaged in an aborted I2C transfer (with matching address) and the data phase of the I2C transfer has been entered, even though a data byte has been responded with a NACK.	
		NOTE: If the remote I2C master terminates the transfer with a STOP condition before the controller has a chance to NACK a transfer, and IC_ENABLE has been set to 0, then this bit is also set to 1.	
		When read as 0, the controller is deemed to have been disabled without being actively involved in the data phase of a Slave-Receiver transfer.	
		NOTE: The CPU can safely read this bit when IC_EN (bit 0) is read as 0.	
1	R	SLV_DISABLED_WHILE_BUSY	0x0
		Slave Disabled While Busy (Transmit, Receive). This bit indicates if a potential or active Slave operation has been aborted due to the setting of the IC_ENABLE register from 1 to 0. This bit is set when the CPU writes a 0 to the IC_ENABLE register while:	
		(a) I2C Ctrl is receiving the address byte of the Slave-Transmitter operation from a remote master; OR,	
		(b) address and data bytes of the Slave-Receiver operation from a remote master. When read as 1, the controller is deemed to have forced a NACK during any part of an I2C transfer, irrespective of whether the I2C address matches the slave address set in I2C Ctrl (IC_SAR register) OR if the transfer is completed before IC_ENABLE is set to 0 but has not taken effect.	
		NOTE: If the remote I2C master terminates the transfer with a STOP condition before the the controller has a chance to NACK a transfer, and IC_ENABLE has been set to 0, then this bit is also set to 1.	
		When read as 0, the controller is deemed to have been disabled when there is master activity, or when the I2C bus is idle.	
		NOTE: The CPU can safely read this bit when IC_EN (bit 0) is read as 0.	
0	R	IC_EN	0x0

Bit	Mode	Symbol/Description	Reset
		ic_en Status. This bit always reflects the value driven on the output port ic_en. When read as 1, the controller is deemed to be in an enabled state.	
		When read as 0, the controller is deemed completely inactive.	
		NOTE: The CPU can safely read this bit anytime. When this bit is read as 0, the CPU can safely read SLV_RX_DATA_LOST (bit 2) and SLV_DISABLED_WHILE_BUSY (bit 1).	

Table 257: I2C_IC_FS_SPKLEN_REG (0x500013A0)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	IC_FS_SPKLEN	0x1
		This register must be set before any I2C bus transaction can take place to ensure stable operation. This register sets the duration, measured in ic_clk cycles, of the longest spike in the SCL or SDA lines that are filtered out by the spike suppression logic. This register can be written only when the I2C interface is disabled which corresponds to the IC_ENABLE register being set to 0. Writes at other times have no effect. The minimum valid value is 1; hardware prevents values less than this being written, and if attempted results in 1 being set.	

32.10 Keyboard Registers

Table 258: Register map KBRD

Address	Register	Description
0x50001400	GPIO_IRQ0_IN_SEL_RE G	GPIO interrupt selection for GPIO_IRQ0
0x50001402	GPIO_IRQ1_IN_SEL_RE G	GPIO interrupt selection for GPIO_IRQ1
0x50001404	GPIO_IRQ2_IN_SEL_RE G	GPIO interrupt selection for GPIO_IRQ2
0x50001406	GPIO_IRQ3_IN_SEL_RE G	GPIO interrupt selection for GPIO_IRQ3
0x50001408	GPIO_IRQ4_IN_SEL_RE G	GPIO interrupt selection for GPIO_IRQ4
0x5000140c	GPIO_DEBOUNCE_REG	Debounce counter value for GPIO inputs
0x5000140e	GPIO_RESET_IRQ_REG	GPIO interrupt reset register
0x50001410	GPIO_INT_LEVEL_CTRL _REG	High or low level select for GPIO interrupts
0x50001412	KBRD_IRQ_IN_SEL0_RE G	GPIO interrupt selection for KBRD_IRQ for P0
0x50001414	KBRD_CTRL_REG	GPIO KBRD control register

Table 259: GPIO_IRQ0_IN_SEL_REG (0x50001400)

Bit	Mode	Symbol/Description	Reset
15:6	-	-	0x0
		Reserved	

Bit	Mode	Symbol/Description	Reset
3:0	R/W	KBRD_IRQ0_SEL	0x0
		Input selection that can generate a GPIO interrupt	
		1: P0[0] is selected	
		2: P0[1] is selected	
		3: P0[2] is selected	
		4: P0[3] is selected	
		5: P0[4] is selected	
		6: P0[5] is selected	
		7: P0[6] is selected	
		8: P0[7] is selected	
		9: P0[8] is selected	
		10: P0[9] is selected	
		11: P0[10] is selected	
		12: P0[11] is selected	
		all others: no input selected	

Table 260: GPIO_IRQ1_IN_SEL_REG (0x50001402)

Bit	Mode	Symbol/Description	Reset
15:6	-	-	0x0
		Reserved	
3:0	R/W	KBRD_IRQ1_SEL	0x0
		See KBRD_IRQ0_SEL	

Table 261: GPIO_IRQ2_IN_SEL_REG (0x50001404)

Bit	Mode	Symbol/Description	Reset
15:6	-	-	0x0
		Reserved	
3:0	R/W	KBRD_IRQ2_SEL	0x0
		See KBRD_IRQ0_SEL	

Table 262: GPIO_IRQ3_IN_SEL_REG (0x50001406)

Bit	Mode	Symbol/Description	Reset
15:6	-	-	0x0
		Reserved	
3:0	R/W	KBRD_IRQ3_SEL	0x0
		See KBRD_IRQ0_SEL	

Table 263: GPIO_IRQ4_IN_SEL_REG (0x50001408)

Bit	Mode	Symbol/Description	Reset
15:6	-	-	0x0
		Reserved	
3:0	R/W	KBRD_IRQ4_SEL	0x0

Bit	Mode	Symbol/Description	Reset
		See KBRD_IRQ0_SEL	

Table 264: GPIO_DEBOUNCE_REG (0x5000140C)

Bit	Mode	Symbol/Description	Reset	
11	R/W	DEB_ENABLE_KBRD	0x0	
		Enables the debounce counter for the KBRD interface		
10	R/W	DEB_ENABLE4	0x0	
		Enables the debounce counter for GPIO IRQ4		
9	R/W	DEB_ENABLE3	0x0	
		Enables the debounce counter for GPIO IRQ3		
8	R/W	DEB_ENABLE2	0x0	
		Enables the debounce counter for GPIO IRQ2		
7	R/W	DEB_ENABLE1	0x0	
		Enables the debounce counter for GPIO IRQ1		
6	R/W	DEB_ENABLE0	0x0	
		Enables the debounce counter for GPIO IRQ0		
5:0	R/W DEB_VALUE Keyboard debounce time if enabled. Generate KEYB_INT after specified time. Debounce time: N*1 ms. N =063		0x0	

Table 265: GPIO_RESET_IRQ_REG (0x5000140E)

Bit	Mode	Symbol/Description	Reset
15:6	-	-	0x0
		Reserved	
5	R0/W	RESET_KBRD_IRQ	0x0
		Writing 1 to this bit resets the KBRD IRQ. Reading returns 0.	
4	R0/W	RESET_GPIO4_IRQ	0x0
		Writing 1 to this bit resets the GPIO4 IRQ. Reading returns 0.	
3	R0/W	RESET_GPIO3_IRQ	0x0
		Writing 1 to this bit resets the GPIO3 IRQ. Reading returns 0.	
2	R0/W	RESET_GPIO2_IRQ	0x0
		Writing 1 to this bit resets the GPIO2 IRQ. Reading returns 0.	
1	R0/W	RESET_GPIO1_IRQ	0x0
		Writing 1 to this bit resets the GPIO1 IRQ. Reading returns 0.	
0	R0/W	RESET_GPIO0_IRQ	0x0
		Writing 1 to this bit resets the GPIO0 IRQ.	

Bit	Mode	Symbol/Description	Reset
		Reading returns 0.	

Table 266: GPIO_INT_LEVEL_CTRL_REG (0x50001410)

Bit	Mode	Symbol/Description	Reset
9	R/W	EDGE_LEVELn4	0x0
		See EDGE_LEVELn0, but for GPIO IRQ4	
8	R/W	EDGE_LEVELn3	0x0
		See EDGE_LEVELn0, but for GPIO IRQ3	
7	R/W	EDGE_LEVELn2	0x0
		See EDGE_LEVELn0, but for GPIO IRQ2	
6	R/W	EDGE_LEVELn1	0x0
		See EDGE_LEVELn0, but for GPIO IRQ1	
5	R/W	EDGE_LEVELn0	0x0
		0: Do not wait for key release after interrupt was reset for GPIO IRQ0, so a new interrupt can be initiated immediately	
		1: Wait for key release after interrupt was reset for IRQ0	
4	R/W	INPUT_LEVEL4	0x0
		See INPUT_LEVEL0, but for GPIO IRQ4	
3	R/W	INPUT_LEVEL3	0x0
		See INPUT_LEVEL0, but for GPIO IRQ3	
2	R/W	INPUT_LEVEL2	0x0
		See INPUT_LEVEL0, but for GPIO IRQ2	
1	R/W	INPUT_LEVEL1	0x0
		See INPUT_LEVEL0, but for GPIO IRQ1	
0	R/W	INPUT_LEVEL0	0x0
		0 = Selected input generates GPIO IRQ0 if that input is high	
		1 = Selected input generates GPIO IRQ0 if that input is low	

Table 267: KBRD_IRQ_IN_SEL0_REG (0x50001412)

Bit	Mode	Symbol/Description	Reset
11	R/W	KBRD_P11_EN	0x0
		Enable P0[11] for the keyboard interrupt	
10	R/W	KBRD_P10_EN	0x0
		Enable P0[10] for the keyboard interrupt	
9	R/W	KBRD_P09_EN	0x0
		Enable P0[9] for the keyboard interrupt	
8	R/W	KBRD_P08_EN	0x0
		Enable P0[8] for the keyboard interrupt	
7	R/W	KBRD_P07_EN	0x0
		Enable P0[7] for the keyboard interrupt	
6	R/W	KBRD_P06_EN	0x0

Bit	Mode	Symbol/Description	Reset
		Enable P0[6] for the keyboard interrupt	
5	R/W	KBRD_P05_EN	0x0
		Enable P0[5] for the keyboard interrupt	
4	R/W	KBRD_P04_EN	0x0
		Enable P0[4] for the keyboard interrupt	
3	R/W	KBRD_P03_EN	0x0
		Enable P0[3] for the keyboard interrupt	
2	R/W	KBRD_P02_EN	0x0
		Enable P0[2] for the keyboard interrupt	
1	R/W	KBRD_P01_EN	0x0
		Enable P0[1] for the keyboard interrupt	
0	R/W	KBRD_P00_EN	0x0
		Enable P0[0] for the keyboard interrupt	

Table 268: KBRD_CTRL_REG (0x50001414)

Bit	Mode	Symbol/Description	Reset
7	R/W	KBRD_REL	0x0
		0 = No interrupt on key release	
		1 = Interrupt also on key release (also debouncing if enabled)	
6	R/W	KBRD_LEVEL	0x0
		0 = Enabled input generates KBRD IRQ if that input is high	
		1 = Enabled input generates KBRD IRQ if that input is low	
5:0	R/W	KEY_REPEAT	0x0
		While key is pressed, automatically generate repeating	
		KEYB_INT after specified time unequal to 0.	
		Repeat time: N^*1 ms. $N = 163$, $N = 0$ disables the timer.	

32.11 Miscellaneous Registers

Table 269: Register map CRG_AON

Address	Register	Description
0x50000300	HWR_CTRL_REG	Hardware Reset control register
0x50000304	RESET_STAT_REG	Reset status register
0x50000308	RAM_LPMX_REG	
0x5000030c	PAD_LATCH_REG	Control the state retention of the GPIO ports
0x50000310	HIBERN_CTRL_REG	Hibernation control register
0x50000320	POWER_AON_CTRL_RE G	
0x50000324	GP_DATA_REG	

Table 270: HWR_CTRL_REG (0x50000300)

Bit	Mode	Symbol/Description	
0	R/W	DISABLE_HWR	0x0
		Disables the RST functionality on P00	

Table 271: RESET_STAT_REG (0x50000304)

Bit	Mode	Symbol/Description	Reset
3	R/W	WDOGRESET_STAT	0x1
		Indicates that a Watchdog has happened.	
		This bit is also set with a PowerOn Reset	
2	R/W	SWRESET_STAT	0x1
		Indicates that a SW Reset has been requested. The SW reset is requested by SYS_CTRL_REG[SW_RESET] or SCB->AIRCR inside the Cortex.	
		This bit is also set with a PowerOn Reset	
1	R/W	HWRESET_STAT	0x1
		Indicates that a HW Reset has happened This bit is also set with a PowerOn Reset	
0	R/W	PORESET_STAT	0x1
		Indicates that a PowerOn Reset has happened	

Table 272: RAM_LPMX_REG (0x50000308)

Bit	Mode	Symbol/Description	Reset
2:0 R/W RAMx_LPMX		RAMx_LPMX	0x7
		RAM[3:1] Transparent Light Sleep (TLS) Core Enable for System RAMs. Assert low to enable the TLS core feature, which will result in lower leakage current.	
		In case VDD is below 0.81 V, it is necessary to hold this pin high to maintain data retention.	

Table 273: PAD_LATCH_REG (0x5000030C)

Bit	Mode	Symbol/Description	Reset
0	PAD_LATCH_EN		0x1
		Controls the state retention of the pads.	
		0: latches are closed, pads retain their state.	
		1: latches are open, new control values have immediate effect	

Table 274: HIBERN_CTRL_REG (0x50000310)

Bit	Mode	Symbol/Description	
6:2	R/W	HIBERN_WKUP_MASK	
		Selects which pin to wake up from	
1	R/W HIBERN_WKUP_POLARITY		0x0
		Selects the polarity of the wakeup source. The polarity must be chosen such that the ANA_STATUS_REG[CLKLESS_WAKEUP_STAT] is "1". Any change on the	

Bit	Mode	Symbol/Description	
		selected GPIOs will make the CLKLESS_WAKEUP_STAT go to "0", and wakeup the system from hibernation.	
0	R/W HIBERNATION_ENABLE		0x0
		Enables the hibernation mode when sleeping 0: deep sleep mode, PD_SLP remains on	
		1: hibernation mode, PD_SLP goes off. REMAP_ADR0 needs to be set to the correct source to boot from before going to sleep.	

Table 275: POWER_AON_CTRL_REG (0x50000320)

Bit	Mode	Symbol/Description	Reset
14	R/W	-	0x0
		Reserved	
13:10	R/W	LDO_RET_TRIM	0x0
		VDD clamp level setting for hibernation mode	
9	R/W	CMP_VCONT_SLP_DISABLE	0x0
		Disable vcont comparator in SLP	
8:7	R/W	BOOST_MODE_FORCE	0x0
		0x:automatic selection of boost mode	
		11: force boost mode	
		10: force buck mode	
6	R/W	CHARGE_VBAT_DISABLE	0x0
		Do not charge vbat high in boost mode	
5	R/W	-	0x0
		Reserved	
4	R/W	-	0x0
		Reserved	
3	R/W	POR_VBAT_HIGH_RST_MASK	0x1
		Mask rst from por_vbat_high	
2	R/W	POR_VBAT_LOW_RST_MASK	0x0
		Mask rst from por_vbat_low	
1:0	R/W	VBAT_HL_CONNECT_RES_CTRL	0x0
		00: OFF	
		01: Forced ON	
		10: Active: automatic control, Sleep: forced ON	
		11: Automatic control	

Table 276: GP_DATA_REG (0x50000324)

Bit	Mode	Symbol/Description	Reset
7	7 R/W P03_P04_FILT_DIS		0x0
7 R/W		0: RC filtered input enabled for P0_3 and P0_4 (for example, when used for wake-up) 1: RC filtered input disabled for P0_3 and P0_4 (for example, when used for external clk or XTAL32k)	

Ultra-Low Power Bluetooth 5.1 SoC

Bit	Mode	Symbol/Description	Reset
6	R/W	FORCE_RCX_VDD	0x0
		0: RCX bias supply open (see FORCE_RCX_VREF)	
		1: RCX bias supply connected to VDD (use for sleep)	
5	R/W	FORCE_RCX_VREF	0x0
		0: RCX bias supply connected to clamp and VDD via 400k resistor (old situation)	
		1: RCX bias supply connected to vref_0v75_0 (use for calibration)	
4	R/W		0x0
		Reserved	
3:0	R/W	SW_GP_DATA	0x0

32.12 OTP Controller Registers

Table 277: Register map OTPC

Address	Register	Description
0x07f40000	OTPC_MODE_REG	Mode register
0x07f40004	OTPC_STAT_REG	Status register
0x07f40008	OTPC_PADDR_REG	The address of the word that will be programmed, when the PROG mode is used.
0x07f4000c	OTPC_PWORD_REG	The 32-bit word that will be programmed, when the PROG mode is used.
0x07f40010	OTPC_TIM1_REG	Various timing parameters of the OTP cell.
0x07f40014	OTPC_TIM2_REG	Various timing parameters of the OTP cell.
0x07f40018	OTPC_AHBADR_REG	AHB master start address
0x07f4001c	OTPC_CELADR_REG	OTP cell start address
0x07f40020	OTPC_NWORDS_REG	Number of words

Table 278: OTPC_MODE_REG (0x07F40000)

Bit	Mode	Symbol/Description	
31:8	-	-	0x0
		Reserved	
7:6	R/W	OTPC_MODE_PRG_SEL	0x0
		Defines the part of the OTP cell that is programmed by the controller during the PROG mode, for each program request that is applied.	
		0x0 : Both normal and redundancy arrays are programmed. This is the normal way of programming.	
		0x1 : Only the normal array is programmed.	
		0x2 : Only the redundancy array is programmed.	
		0x3 : Reserved	
		The value of this configuration field can be modified only when the controller is in an inactive mode (DSTBY or STBY). The setting will take effect when will be enabled again the PROG mode.	
5	R/W	OTPC_MODE_HT_MARG_EN	0x0
		Defines the temperature condition under which is performed a margin read. It affects only the initial margin read (RINI mode) and the programming verification margin read (PVFY).	
		0 : Regular temperature condition (less than 85°C)	
		1 : High temperature condition (85°C or more)	
		The value of this configuration field can be modified only when the controller is in an inactive mode (DSTBY or STBY). The selection will take effect at the next PVFY or RINI mode that will be enabled. The READ mode is not affected by the setting of this configuration bit.	
4	R/W	OTPC_MODE_USE_TST_ROW	0x0
		Selects the memory area of the OTP cell that will be used.	
		0 - Uses the main memory area of the OTP cell	
		1 - Uses the test row of the OTP cell	
		The value of this configuration field can be modified only when the controller is in an inactive mode (DSTBY or STBY). The selection will take effect at the next programming or reading mode that will be enabled.	

Bit	Mode	Symbol/Description	Reset
3	-	-	0x0
		Reserved	
2:0	R/W	OTPC_MODE_MODE	0x0
		Defines the mode of operation of the OTPC controller. The encoding of the modes is as follows:	
		0x0: DSTBY. The OTP memory is in deep standby mode (power supply ON and internal LDO OFF).	
		0x1: STBY. The OTP memory is powered (power supply ON and internal LDO ON, but is not selected).	
		0x2: READ. The OTP memory is in the normal read mode.	
		0x3: PROG. The OTP memory is in programming mode.	
		0x4: PVFY. The OTP memory is in programming verification mode (margin read after programming).	
		0x5: RINI. The OTP memory is in initial read mode (initial margin read).	
		0x6: AREAD. Copying of data from the OTP memory to a system RAM by using the internal DMA. See also the registers OTPC_AHBADR_REG, OTPC_CELADR_REG and OTPC_NWORDS_REG.	
		Whenever the OTPC_MODE_REG[MODE] is changing, the status bit OTPC_STAT_REG[OTPC_STAT_MRDY] gets the value zero. The new mode will be ready for use when the OTPC_STAT_MRDY become again 1. During the mode transition the OTPC_MODE_REG[MODE] become read only. Do not try to use or change any function of the controller until the OTPC_STAT_MRDY bit to become equal to 1.	
		The data transferring that is performed by using the AREAD mode is completed when OTPC_STAT_MRDY becomes again 1. The mode change automatically to DSTBY with the completion of the transfer.	

Table 279: OTPC_STAT_REG (0x07F40004)

Bit	Mode	Symbol/Description	Reset
31:3	-	-	0x0
		Reserved	
2	R	OTPC_STAT_MRDY	0x1
		Indicates the progress of the transition from a mode of operation to a new mode of operation.	
		0 : There is a transition in progress in a new mode of operation . Wait until the transition to be completed.	
		1 : The transition to the new mode of operation has been completed. The function that has been enabled by the new mode can be used. A new mode can be applied.	
		This status bit gets the value zero every time where the OTPC_MODE_REG[MODE] is changing. Do not try to use or change any function of the controller until this status bit to become equal to 1.	
1	R	OTPC_STAT_PBUF_EMPTY	0x1
		Indicates the status of the programming buffer (PBUF).	
		0 : The PBUF contains the address and the data of a programming request. The OTPC_PADDR_REG and the OTPC_PWORD_REG should not be written as long as this status bit is zero.	
		1 : The PBUF is empty and a new programming request can be registered in the PBUF by using the OTPC_PADDR_REG and the OTPC_PWORD_REG registers.	

Bit	Mode	Symbol/Description	
		This status bit gets the value zero every time where a programming is triggered by the OTPC_PADDR_REG (only if the PROG mode is active).	
0	R OTPC_STAT_PRDY		0x1
	Indicates the state of the programming process. 0: The controller is busy. A programming is in progress		
		1: The logic which performs programming is idle	

Table 280: OTPC_PADDR_REG (0x07F40008)

Bit	Mode	Symbol/Description	Reset
31:13	-	-	0x0
		Reserved	
12:0	2:0 R/W OTPC_PADDR		0x0
that kee mode. T (OTPC_		The OTPC_PADDR_REG and the OTPC_PWORD_REG consist the PBUF buffer that keeps the information that will be programmed in the OTP, by using the PROG mode. The PBUF holds the address (OTPC_PADDR_REG) and the data (OTPC_PWORD_REG) of each of the programming requests that are applied in the OTP memory.	
	the OTP memory. The OTPC_PADDR_REG refers to a word address. The OTPC_PADDR_REG to be writen after the OTP_PWORD_REG and only if the OTPC_STAT_REG[OTPC_STAT_PBUF_EMPTY] = 1. The register is read on as long the PBUF is not empty (OTPC_STAT_REG[OTPC_STAT_PBUF_EMF = 0). A writting to the OTPC_PADDR_REG triggers the controller to start the programming procedure (only if the PROG mode is active).		

Table 281: OTPC_PWORD_REG (0x07F4000C)

Bit	Mode	Symbol/Description	
31:0	R/W	OTPC_PWORD	0x0
		The OTPC_PADDR_REG and the OTPC_PWORD_REG consist the PBUF buffer that keeps the information that will be programmed in the OTP memory, by using the PROG mode. The PBUF holds the address (OTPC_PADDR_REG) and the data (OTPC_PWORD_REG) of each of the programming requests that are applied in the OTP memory.	
		The OTP_PWORD_REG must be written before the OTPC_PADDR_REG and only if OTPC_STAT_REG[OTPC_STAT_PBUF_EMPTY] = 1. The register is read only for as long the PBUF is not empty (OTPC_STAT_REG[OTPC_STAT_PBUF_EMPTY] = 0).	

Table 282: OTPC_TIM1_REG (0x07F40010)

Bit	Mode	Symbol/Description	Reset
31	-	-	0x0
		Reserved	
30:24	:24 R/W OTPC_TIM1_US_T_CSP		0x9
	The number of microseconds (minus one) that are required after the selection of the OTP memory, until to be ready for programming. It must be : - at least 10 µs		
		- no more than 100 μs	
23:20	R/W	OTPC_TIM1_US_T_CS 0x9	

Bit	Mode	Symbol/Description	Reset
		The number of microseconds (minus one) that are required after the selection of the OTP memory, until to be ready for any kind of read. It must be at least 10 µs.	
19:16	R/W	OTPC_TIM1_US_T_PL	
		The number of microseconds (minus one) that are required until to be enabled the LDO of the OTP. It must be at least 10 μ s.	
15	-	-	0x0
		Reserved	
14:12	R/W	OTPC_TIM1_CC_T_RD	0x0
	The number of hclk_c clock periods (minus one) that give a time interval at least higher than 60 ns. This timing parameter refers to the access time of the OTP memory.		
11:10	-	-	0x0
		Reserved	
9:8	R/W	OTPC_TIM1_CC_T_20NS	0x0
		The number of hclk_c clock periods (minus one) that give a time interval that is at least higher than 20 ns.	
7	-	-	0x0
		Reserved	
6:0	R/W	OTPC_TIM1_CC_T_1US	0xF
		The number of hclk_c clock periods (minus one) that give a time interval equal to 1 µs. This setting affects all the timing parameters that refer to microseconds, due to that defines the correspondence of a microsecond to a number of hclk_c clock cycles.	

Table 283: OTPC_TIM2_REG (0x07F40014)

Bit	Mode	Symbol/Description	Reset
31	R/W	OTPC_TIM2_US_ADD_CC_EN	0x1
		Adds an additional hclk_c clock cycle at all the time intervals that count in microseconds.	
		0 : The extra hclk_c clock cycle is not applied	
		1 : The extra hclk_c clock cycle is applied	
30:29	R/W	OTPC_TIM2_US_T_SAS	0x1
		The number of microseconds (minus one) that are required after the exit from the deep sleep standby mode and before to become ready to enter in an active mode (reading or programming). It must be at least 2 µs.	
28:24	R/W	OTPC_TIM2_US_T_PPH	0x4
		The number of microseconds (minus one) that are required after the last programming pulse and before to be disabled the programming mode in the OTP memory. It must be:	
		- at least 5 μs	
		- no more than 20 μs	
23:21	R/W	OTPC_TIM2_US_T_VDS	0x0
		The number of microseconds (minus one) that are required after the enabling of the power supply of the OTP memory and before to become ready for the enabling of the internal LDO. It must be at least 1 μ s.	
20:16	R/W	OTPC_TIM2_US_T_PPS 0x4	

Bit	Mode	Symbol/Description	Reset
		The number of microseconds (minus one) that are required after the enabling of the programming in the OTP memory and before to be applied the first programming pulse. It must be:	
		- at least 5 μs	
		- no more than 20 μs	
15	-	-	0x0
		Reserved	
14:8	R/W	OTPC_TIM2_US_T_PPR	0x4
		The number of microseconds (minus one) for recovery after a programming sequence. It must be :	
		- at least 5 μs	
		- no more than 100 μs	
7:5	R/W	OTPC_TIM2_US_T_PWI	0x0
		The number of microseconds (minus one) between two consecutive programming pulses. It must be :	
		- at least 1 μs	
		- no more than 5 μs	
4:0	R/W	OTPC_TIM2_US_T_PW	0x9
		The number of microseconds (minus one) that lasts the programming of each bit. It must be:	
		- at least 10 μs	
		- no more than 20 μs	

Table 284: OTPC_AHBADR_REG (0x07F40018)

Bit	Mode	Symbol/Description	
31:16	-	-	0x0
		Reserved	
15:2	R/W	R/W OTPC_AHBADR	
		It is the AHB address used by the AHB master interface of the controller (the bits [15:2]). The bits [1:0] of the address are considered always as equal to zero.	
		The value of the register remains unchanged, by the internal logic of the controller.	
1:0	-	-	
	Reserved		

Table 285: OTPC_CELADR_REG (0x07F4001C)

Bit	Mode	Symbol/Description	
31:13	-	-	
		Reserved	
12:0 R/W OTPC_CELADR		OTPC_CELADR	0x0
	Defines a word address inside the OTP cell that will be used during the AREAD mode and the OTP mirroring.		

Table 286: OTPC_NWORDS_REG (0x07F40020)

Bit	Mode	Symbol/Description	
31:13	-	-	
		Reserved	
12:0	R/W	OTPC_NWORDS	
	The number of words (minus one) that will be copied by the AREAD mode. During mirroring, this register reflects the amount of data that will be copied.		

32.13 Quadrature Decoder Registers

Table 287: Register map QDEC

Address	Register	Description
0x50000200	QDEC_CTRL_REG	Quad Decoder control register
0x50000202	QDEC_XCNT_REG	Counter value of the X Axis
0x50000204	QDEC_YCNT_REG	Counter value of the Y Axis
0x50000206	QDEC_CLOCKDIV_REG	Clock divider register
0x50000208	QDEC_CTRL2_REG	Quad Decoder port selection register
0x5000020a	QDEC_ZCNT_REG	Counter value of the Z Axis
0x5000020c	QDEC_EVENT_CNT_RE G	Event counter register

Table 288: QDEC_CTRL_REG (0x50000200)

Bit	Mode	Symbol/Description	Reset
10:3	R/W	QDEC_IRQ_THRES	0x2
		Defines the number of events on either counter (X or Y or Z) that need to be reached before an interrupt is generated. Events are equal to QDEC_IRQ_THRES+1.	
2	R/W	QDEC_IRQ_STATUS	0x0
		1 = Interrupt has occurred	
		0 = No interrupt pending	
		Write 1 clears the pending interrupt.	
1	R0/WC	QDEC_EVENT_CNT_CLR	0x0
		Writing 1 QDEC_EVENT_CNT_REG is cleared	
0	R/W	QDEC_IRQ_ENABLE	0x1
		0 = Interrupt is masked	
		1 = Interrupt is enabled	

Table 289: QDEC_XCNT_REG (0x50000202)

Bit	Mode	Symbol/Description	
15:0	R	QDEC_X_CNT	0x0
		Contains a signed value of the events. Zero when channel is disabled.	

Table 290: QDEC_YCNT_REG (0x50000204)

Bit	Mode	Symbol/Description	
15:0	R	QDEC_Y_CNT	0x0
		Contains a signed value of the events. Zero when channel is disabled	

Table 291: QDEC_CLOCKDIV_REG (0x50000206)

Bit	Mode	Symbol/Description	Reset
10	R/W	QDEC_PRESCALER_EN	
		0 = No prescaler enabled	
		1 = In Sleep and Active mode, quadrature clock is divided by 2	
9:0	R/W	QDEC_CLOCKDIV	0x3E7
		Contains the number of the input clock cycles minus one, that are required to generate one logic clock cycle.	
		Clock divider is bypassed when system runs at LP_CLK	

Table 292: QDEC_CTRL2_REG (0x50000208)

Bit	Mode	Symbol/Description	Reset
11	R/W	QDEC_CHZ_EVENT_MODE	0x1
		0 = Normal quadrature counting	
		1 = Counts rising and falling edge of both ports (if both ports change at the same time, counter increases by 1)	
10	R/W	QDEC_CHY_EVENT_MODE	0x1
		0 = Normal quadrature counting	
		1 = Counts rising and falling edge of both ports (if both ports change at the same time, counter increases by 1)	
9	R/W	QDEC_CHX_EVENT_MODE	0x1
		0 = Normal quadrature counting	
		1 = Counts rising and falling edge of both ports (if both ports change at the same time, counter increases by 1)	
8:6	R/W	QDEC_CHZ_PORT_SEL	3
		Defines which GPIOs are mapped on Channel Z	
		0: none	
		1: P0[2] -> CHZ_A, P0[5] -> CHZ_B	
		2: P0[1] -> CHZ_A, P0[4] -> CHZ_B	
		3: P0[3] -> CHZ_A, P0[10] -> CHZ_B	
		4: P0[6] -> CHZ_A, P0[7] -> CHZ_B	
		5: P0[8] -> CHZ_A, P0[9] -> CHZ_B	
		6: P0[0] -> CHZ_A, P0[11] -> CHZ_B	
		7: none	
5:3	R/W	QDEC_CHY_PORT_SEL	2
		Defines which GPIOs are mapped on Channel Y	
		0: none	
		1: P0[2] -> CHY_A, P0[5] -> CHY_B	
		2: P0[1] -> CHY_A, P0[4] -> CHY_B	
		3: P0[3] -> CHY_A, P0[10] -> CHY_B	

Bit	Mode	Symbol/Description	Reset
		4: P0[6] -> CHY_A, P0[7] -> CHY_B	
		5: P0[8] -> CHY_A, P0[9] -> CHY_B	
		6: P0[0] -> CHY_A, P0[11] -> CHY_B	
		7: none	
2:0	R/W	QDEC_CHX_PORT_SEL	1
		Defines which GPIOs are mapped on Channel X	
		0: none	
		1: P0[2] -> CHX_A, P0[5] -> CHX_B	
		2: P0[1] -> CHX_A, P0[4] -> CHX_B	
		3: P0[3] -> CHX_A, P0[10] -> CHX_B	
		4: P0[6] -> CHX_A, P0[7] -> CHX_B	
		5: P0[8] -> CHX_A, P0[9] -> CHX_B	
		6: P0[0] -> CHX_A, P0[11] -> CHX_B	
		7: none	

Table 293: QDEC_ZCNT_REG (0x5000020A)

Bit	Mode	Symbol/Description	
15:0	R	QDEC_Z_CNT	0
		Contains a signed value of the events. Zero when channel is disabled.	

Table 294: QDEC_EVENT_CNT_REG (0x5000020C)

Bit	Mode	Symbol/Description	Reset
7:0	R	QDEC_EVENT_CNT	0x0
		Gives the number of events at all channels.	

32.14 Real Time Clock Registers

Table 295: Register map RTC

Address	Register	Description
0x50004100	RTC_CONTROL_REG	RTC Control Register
0x50004104	RTC_HOUR_MODE_RE G	RTC Hour Mode Register
0x50004108	RTC_TIME_REG	RTC Time Register
0x5000410c	RTC_CALENDAR_REG	RTC Calendar Register
0x50004110	RTC_TIME_ALARM_RE G	RTC Time Alarm Register
0x50004114	RTC_CALENDAR_ALAR M_REG	RTC Calendar Alram Register
0x50004118	RTC_ALARM_ENABLE_ REG	RTC Alarm Enable Register
0x5000411c	RTC_EVENT_FLAGS_R EG	RTC Event Flags Register
0x50004120	RTC_INTERRUPT_ENAB LE_REG	RTC Interrupt Enable Register

Address	Register	Description
0x50004124	RTC_INTERRUPT_DISA BLE_REG	RTC Interrupt Disable Register
0x50004128	RTC_INTERRUPT_MAS K_REG	RTC Interrupt Mask Register
0x5000412c	RTC_STATUS_REG	RTC Status Register
0x50004130	RTC_KEEP_RTC_REG	RTC Keep RTC Register

Table 296: RTC_CONTROL_REG (0x50004100)

Bit	Mode	Symbol/Description	
1	R/W	RTC_CAL_DISABLE	0x1
		When this field is set high the RTC stops incrementing the calendar value.	
0	R/W	TC_TIME_DISABLE	
		When this field is set high the RTC stops incrementing the time value.	

Table 297: RTC_HOUR_MODE_REG (0x50004104)

Bit	Mode	Symbol/Description	Reset
0	R/W	RTC_HMS	0x0
		When this field is set high the RTC operates in 12-hour clock mode; otherwise, times are in 24-hour clock format.	

Table 298: RTC_TIME_REG (0x50004108)

Bit	Mode	Symbol/Description	Reset
31	R/W	RTC_TIME_CH	0x0
		The value in this register has altered since last read. Read and clear.	
30	R/W	RTC_TIME_PM	0x0
		In 12-hour clock mode, indicates PM when set.	
29:28	R/W	RTC_TIME_HR_T	0x0
		Hours tens. Represented in BCD digit (0-2).	
27:24	R/W	RTC_TIME_HR_U	0x0
		Hours units. Represented in BCD digit (0-9).	
23	-	-	0x0
		Reserved	
22:20	R/W	RTC_TIME_M_T	0x0
		Minutes tens. Represented in BCD digit (0-5).	
19:16	R/W	RTC_TIME_M_U	0x0
		Minutes units. Represented in BCD digit (0-9).	
15	-	-	0x0
		Reserved	
14:12	R/W	RTC_TIME_S_T	0x0
		Seconds tens. Represented in BCD digit (0-9).	
11:8	R/W	RTC_TIME_S_U	0x0

Bit	Mode	Symbol/Description	Reset
		Seconds units. Represented in BCD digit (0-9).	
7:4	R/W	RTC_TIME_H_T	0x0
		Hundredths of a second tens. Represented in BCD digit (0-9).	
3:0	R/W	RTC_TIME_H_U	0x0
		Hundredths of a second units. Represented in BCD digit (0-9).	

Table 299: RTC_CALENDAR_REG (0x5000410C)

Bit	Mode	Symbol/Description	Reset
31	R/W	RTC_CAL_CH	0x0
		The value in this register has altered since last read. Read and clear	
30	-	-	0x0
		Reserved	
29:28	R/W	RTC_CAL_C_T	0x2
		Century tens. Represented in BCD digit (1-2).	
27:24	R/W	RTC_CAL_C_U	0x0
		Century units. Represented in BCD digit (0-9).	
23:20	R/W	RTC_CAL_Y_T	0x0
		Year tens. Represented in BCD digit (0-9).	
19:16	R/W	RTC_CAL_Y_U	0x0
		Year units. Represented in BCD digit (0-9).	
15:14	-	-	0x0
		Reserved	
13:12	R/W	RTC_CAL_D_T	0x0
		Date tens. Represented in BCD digit (0-3).	
11:8	R/W	RTC_CAL_D_U	0x1
		Date units. Represented in BCD digit (0-9).	
7	R/W	RTC_CAL_M_T	0x0
		Month tens. Represented in BCD digit (0-1).	
6:3	R/W	RTC_CAL_M_U	0x1
		Month units. Represented in BCD digit (0-9).	
2:0	R/W	RTC_DAY	0x7
		Day of the week (arbitrary) units. Represented in BCD digit (0-7).	

Table 300: RTC_TIME_ALARM_REG (0x50004110)

Bit	Mode	Symbol/Description	Reset
31	-	-	0x0
		Reserved	
30	R/W	RTC_TIME_PM	0x0
		In 12-hour clock mode, indicates PM when set.	
29:28	R/W	RTC_TIME_HR_T	0x0

Bit	Mode	Symbol/Description	Reset
		Hours tens. Represented in BCD digit (0-2).	
27:24	R/W	RTC_TIME_HR_U	0x0
		Hours units. Represented in BCD digit (0-9).	
23	-		0x0
		Reserved	
22:20	R/W	RTC_TIME_M_T	0x0
		Minutes tens. Represented in BCD digit (0-5).	
19:16	R/W	RTC_TIME_M_U	0x0
		Minutes units. Represented in BCD digit (0-9).	
15	-		0x0
		Reserved	
14:12	R/W	RTC_TIME_S_T	0x0
		Seconds tens. Represented in BCD digit (0-9).	
11:8	R/W	RTC_TIME_S_U	0x0
		Seconds units. Represented in BCD digit (0-9).	
7:4	R/W	RTC_TIME_H_T	0x0
		Hundredths of a second tens. Represented in BCD digit (0-9).	
3:0	R/W	RTC_TIME_H_U	0x0
		Hundredths of a second units. Represented in BCD digit (0-9).	

Table 301: RTC_CALENDAR_ALARM_REG (0x50004114)

Bit	Mode	Symbol/Description	Reset
31:14	R/W		0x0
		Reserved	
13:12	R/W	RTC_CAL_D_T	0x0
		Date tens. Represented in BCD digit (0-3).	
11:8	R/W	RTC_CAL_D_U	0x0
		Date units. Represented in BCD digit (0-9).	
7	R/W	RTC_CAL_M_T	0x0
		Month tens. Represented in BCD digit (0-1).	
6:3	R/W	RTC_CAL_M_U	0x0
		Month units. Represented in BCD digit (0-9).	
2:0	-	-	0x0
		Reserved	

Table 302: RTC_ALARM_ENABLE_REG (0x50004118)

Bit	Mode	Symbol/Description	Reset
5	R/W	RTC_ALARM_MNTH_EN	0x0
		Alarm on month enable. Enable to trigger alarm when data specified in Calendar Alarm Register (M_T and M_U) has been reached.	
4	R/W	RTC_ALARM_DATE_EN	0x0

Bit	Mode	Symbol/Description	Reset
		Alarm on date enable. Enable to trigger alarm when data specified in Calendar Alarm Register (D_T and D_U) has been reached.	
3	R/W	RTC_ALARM_HOUR_EN	0x0
		Alarm on hour enable. Enable to trigger alarm when data specified in Time Alarm Register (PM, HR_T and HR_U) has been reached.	
2	R/W	RTC_ALARM_MIN_EN	0x0
		Alarm on minute enable. Enable to trigger alarm when data specified in Time Alarm Register (M_T and M_U) has been reached.	
1	R/W	RTC_ALARM_SEC_EN	0x0
		Alarm on second enable. Enable to trigger alarm when data specified in Time Alarm Register (S_T and S_U) has been reached.	
0	R/W	RTC_ALARM_HOS_EN	0x0
		Alarm on hundredths of a second enable. Enable to trigger alarm when data specified in Time Alarm Register (H_T and H_U) has been reached.	

Table 303: RTC_EVENT_FLAGS_REG (0x5000411C)

Bit	Mode	Symbol/Description	Reset
6	R	RTC_EVENT_ALRM	0x0
		Alarm event flag. Indicate that alarm event occurred since the last reset.	
5	R	RTC_EVENT_MNTH	0x0
		Month rolls over event flag. Indicate that month rolls over event occurred since the last reset.	
4	R	RTC_EVENT_DATE	0x0
		Date rolls over event flag. Indicate that date rolls over event occurred since the last reset.	
3	R	RTC_EVENT_HOUR	0x0
		Hour rolls over event flag. Indicate that hour rolls over event occurred since the last reset.	
2	R	RTC_EVENT_MIN	0x0
		Minute rolls over event flag. Indicate that minute rolls over event occurred since the last reset.	
1	R	RTC_EVENT_SEC	0x0
		Second rolls over event flag. Indicate that second rolls over event occurred since the last reset.	
0	R	RTC_EVENT_HOS	0x0
		Hundredths of a second event flag. Indicate that hundredths of a second rolls over event occurred since the last reset.	

Table 304: RTC_INTERRUPT_ENABLE_REG (0x50004120)

Bit	Mode	Symbol/Description	Reset
6	W	RTC_ALRM_INT_EN	0x0
		Interrupt on alarm enable. Enable to issue the interrupt when alarm event occurred.	
5	W	RTC_MNTH_INT_EN	0x0

Bit	Mode	Symbol/Description	Reset
		Interrupt on month enable. Enable to issue the interrupt when month event occurred.	
4	W	RTC_DATE_INT_EN	0x0
		Interrupt on date enable. Enable to issue the interrupt when date event occurred.	
3	W	RTC_HOUR_INT_EN	0x0
		Interrupt on hour enable. Enable to issue the interrupt when hour event occurred.	
2	W	RTC_MIN_INT_EN	0x0
		Interrupt on minute enable. Enable to issue the interrupt when minute event occurred.	
1	W	RTC_SEC_INT_EN	0x0
		Interrupt on second enable. Enable to issue the interrupt when second event occurred.	
0	W	RTC_HOS_INT_EN	0x0
		Interrupt on hundredths of a second enable. Enable to issue the interrupt when hundredths of a second event occurred.	

Table 305: RTC_INTERRUPT_DISABLE_REG (0x50004124)

Bit	Mode	Symbol/Description	Reset
6	W	RTC_ALRM_INT_DIS	0x0
		Interrupt on alarm disable. Disable to issue the interrupt when alarm event occurred.	
5	W	RTC_MNTH_INT_DIS	0x0
		Interrupt on month disable. Disable to issue the interrupt when month event occurred.	
4	W	RTC_DATE_INT_DIS	0x0
		Interrupt on date disable. Disable to issue the interrupt when date event occurred.	
3	W	RTC_HOUR_INT_DIS	0x0
		Interrupt on hour disable. Disable to issue the interrupt when hour event occurred.	
2	W	RTC_MIN_INT_DIS	0x0
		Interrupt on minute disable. Disable to issue the interrupt when minute event occurred.	
1	W	RTC_SEC_INT_DIS	0x0
		Interrupt on second disable. Disable to issue the interrupt when second event occurred.	
0	W	RTC_HOS_INT_DIS	0x0
		Interrupt on hundredths of a second disable. Disable to issue the interrupt when hundredths of a second event occurred.	

Table 306: RTC_INTERRUPT_MASK_REG (0x50004128)

Bit	Mode	Symbol/Description	Reset
6	R	RTC_ALRM_INT_MSK	0x1
		Mask alarm interrupt. It can be cleared (set) by setting corresponding bit (ALRM) in Interrupt Enable Register (Interrupt Disable Register).	
5	R	RTC_MNTH_INT_MSK	0x1

Bit	Mode	Symbol/Description	Reset
		Mask month interrupt. It can be cleared (set) by setting corresponding bit (MNTH) in Interrupt Enable Register (Interrupt Disable Register).	
4	R	RTC_DATE_INT_MSK	0x1
		Mask date interrupt. It can be cleared (set) by setting corresponding bit (DATE) in Interrupt Enable Register (Interrupt Disable Register).	
3	R	RTC_HOUR_INT_MSK	0x1
		Mask hour interrupt. It can be cleared (set) by setting corresponding bit (HOUR) in Interrupt Enable Register (Interrupt Disable Register).	
2	R	RTC_MIN_INT_MSK	0x1
		Mask minute interrupt. It can be cleared (set) by setting corresponding bit (MIN) in Interrupt Enable Register (Interrupt Disable Register).	
1	R	RTC_SEC_INT_MSK	0x1
		Mask second interrupt. It can be cleared (set) by setting corresponding bit (SEC) in Interrupt Enable Register (Interrupt Disable Register).	
0	R	RTC_HOS_INT_MSK	0x1
		Mask hundredths of a second interrupt. It can be cleared (set) by setting corresponding bit (HOS) in Interrupt Enable Register (Interrupt Disable Register).	

Table 307: RTC_STATUS_REG (0x5000412C)

Bit	Mode	Symbol/Description	Reset
3	R	RTC_VALID_CAL_ALM	0x1
		Valid Calendar Alarm. If cleared, then indicates that invalid entry occurred when writing to Calendar Alarm Register.	
2	R	RTC_VALID_TIME_ALM	0x1
		Valid Time Alarm. If cleared, then indicates that invalid entry occurred when writing to Time Alarm Register.	
1	R	RTC_VALID_CAL	0x1
		Valid Calendar. If cleared, then indicates that invalid entry occurred when writing to Calendar Register.	
0	R	RTC_VALID_TIME	0x1
		Valid Time. If cleared, then indicates that invalid entry occurred when writing to Time Register.	

Table 308: RTC_KEEP_RTC_REG (0x50004130)

Bit	Mode	Symbol/Description	Reset
0	R/W	RTC_KEEP	0x1
		Keep RTC. When high, the time and calendar registers and any other registers which directly affect or are affected by the time and calendar registers are NOT reset when software reset is applied. When low, the software reset resets every register except the keep RTC and control registers.	

32.15 SPI Interface Registers

Table 309: Register map SPI

Address	Register	Description
0x50001200	SPI_CTRL_REG	Spi control register
0x50001204	SPI_CONFIG_REG	Spi control register
0x50001208	SPI_CLOCK_REG	Spi clock register
0x5000120c	SPI_FIFO_CONFIG_REG	Spi fifo configuration register
0x50001210	SPI_IRQ_MASK_REG	Spi interrupt mask register
0x50001214	SPI_STATUS_REG	Spi status register
0x50001218	SPI_FIFO_STATUS_RE G	SPI RX/TX fifo status register
0x5000121c	SPI_FIFO_READ_REG	Spi RX fifo read register
0x50001220	SPI_FIFO_WRITE_REG	Spi TX fifo wtite register
0x50001224	SPI_CS_CONFIG_REG	Spi cs configuration register
0x50001228	SPI_FIFO_HIGH_REG	Spi TX/RX High 16bit word
0x5000122c	SPI_TXBUFFER_FORCE _L_REG	SPI TX buffer force low value
0x50001230	SPI_TXBUFFER_FORCE _H_REG	SPI TX buffer force high value

Table 310: SPI_CTRL_REG (0x50001200)

Bit	Mode	Symbol/Description	Reset
7	R/W	SPI_SWAP_BYTES	0x0
		0 = normal operation 1 = LSB and MSB are swaped in APB interface In case of 8-bit SPI interface, DMA/SPI can be configured in 16-bit mode to off load the bus. Enabling SPI_SWAP_BYTES bytes will read/write correctly	
6	R/W	SPI_CAPTURE_AT_NEXT_EDGE	0x0
		0 = SPI captures data at correct clock edge 1 = SPI captures data at next clock edge. (only for Master mode and high clock)	
5	R/W	SPI_FIFO_RESET	0x0
		0 = Fifo normal operation 1 = Fifo in reset state	
4	R/W	SPI_DMA_RX_EN	0x0
		Applicable only when SPI_RX_EN = 1 0 = No DMA request for RX 1 = DMA request when SPI_STATUS_RX_FULL = 1	
3	R/W	SPI_DMA_TX_EN	0x0
		Applicable only when SPI_TX_EN = 1 0 = No DMA request for TX 1 = DMA request when SPI_STATUS_TX_EMPTY = 1	

Bit	Mode	Symbol/Description	Reset
2	R/W	SPI_RX_EN	0x0
		0 = RX path is disabled 1 = RX path is enabled Note: if master clk async or spi mode = 1 or spi mode = 3 readonly is not supported	
1	R/W	SPI_TX_EN 0 = TX path is disabled 1 = TX path is enabled	0x0
0	R/W	SPI_EN 0 = SPI module is disable 1 = SPI module is enable	0x0

Table 311: SPI_CONFIG_REG (0x50001204)

Bit	Mode	Symbol/Description	Reset
7	R/W	SPI_SLAVE_EN	0x0
		0 = SPI module master mode	
		1 = SPI module slave mode	
6:2	R/W	SPI_WORD_LENGTH	0x0
		Define the spi word length = 1+ SPI_WORD_LENGTH (range 4 to 32)	
1:0	R/W	SPI_MODE	0x0
		Define the spi mode (CPOL, CPHA)	
		0 = new data on falling, capture on rising, clk low in idle state	
		1 = new data on rising, capture on falling, Clk low in idle state	
		2 = new data on rising, capture on falling, Clk high in idle state	
		3 = new data on falling, capture on rising Clk high in idle state	

Table 312: SPI_CLOCK_REG (0x50001208)

Bit	Mode	Symbol/Description	Reset
7	R/W		0x0
1	FX/VV	SPI_MASTER_CLK_MODE	UXU
		Should be always 1	
6:0	R/W	SPI_CLK_DIV	0x0
		Applicable only in master mode	
		Defines the SPI clock frequency in master only mode	
		SPI_CLK = module_clk / 2*(SPI_CLK_DIV+1) when SPI_CLK_DIV not 0x7F	
ı		if SPI_CLK_DIV=0x7F then SPI_CLK=module_clk	

Table 313: SPI_FIFO_CONFIG_REG (0x5000120C)

Bit	Mode	Symbol/Description	Reset
7:4	R/W	SPI_RX_TL	0x0

Bit	Mode	Symbol/Description	Reset
		Receive FIFO threshold level in bytes. Control the level of bytes in fifo that triggers the RX_FULL interrupt. IRQ is occurred when fifo level is more or equal to SPI_RX_TL+1. Fifo level is from 0 to 4	
3:0	R/W	SPI_TX_TL	0x0
		Transmit FIFO threshold level in bytes. Control the level of bytes in fifo that triggers the TX_EMPTY interrupt. IRQ is occurred when fifo level is less or equal to SPI_TX_TL. Fifo level is from 0 to 4	

Table 314: SPI_IRQ_MASK_REG (0x50001210)

Bit	Mode	Symbol/Description	Reset
1	R/W	SPI_IRQ_MASK_RX_FULL	0x0
		0 = FIFO RX full irq is masked	
		1 = FIFO RX full irq is enabled	
0	R/W	SPI_IRQ_MASK_TX_EMPTY	0x0
		0 = FIFO TX empty irq is masked	
		1 = FIFO TX empy irq is enabled	

Table 315: SPI_STATUS_REG (0x50001214)

Bit	Mode	Symbol/Description	Reset
1	R	SPI_STATUS_RX_FULL	0x0
		Auto clear 0 = RX fifo level is less than SPI_RX_TL+1 1 = RX fifo level is more or equal to SPI_RX_TL+1	
0	R	SPI_STATUS_TX_EMPTY Auto clear 0 = TX fifo level is larger than SPI_TX_TL 1 = TX fifo level is less or equal to SPI_TX_TL	0x1

Table 316: SPI_FIFO_STATUS_REG (0x50001218)

Bit	Mode	Symbol/Description	Reset
15	R	SPI_TRANSACTION_ACTIVE	0x0
		In master mode	
		0 = spi transaction is inactive	
		1 = spi transaction is active	
14	R	SPI_RX_FIFO_OVFL	0x0
		When 1, receive data is not written to fifo because fifo was full and interrupt is generated. It clears with SPI_CTRL_REG.SPI_FIFO_RESET	
13	R	SPI_STATUS_TX_FULL	0x0
		0 = TX fifo is not full	

Bit	Mode	Symbol/Description	Reset
		1 = TX fifo is full	
12	R	SPI_STATUS_RX_EMPTY	0x1
		0 = RX fifo is not empty 1 = RX fifo is empty	
11:6	R	SPI_TX_FIFO_LEVEL	0x0
		Gives the number of bytes in TX fifo	
5:0	R	SPI_RX_FIFO_LEVEL	0x0
		Gives the number of bytes in RX fifo	

Table 317: SPI_FIFO_READ_REG (0x5000121C)

Bit	Mode	Symbol/Description	Reset
15:0	R	SPI_FIFO_READ	0x0
		Read from RX fifo. Read access is permit only if SPI_STATUS_RX_EMPTY = 0. Returns the 16 LSb	

Table 318: SPI_FIFO_WRITE_REG (0x50001220)

Bit	Mode	Symbol/Description	
15:0	R0/W	SPI_FIFO_WRITE	0x0
		Write to TX fifo. Write access is permit only if SPI_STATUS_TX_FULL is 0	

Table 319: SPI_CS_CONFIG_REG (0x50001224)

Bit	Mode	Symbol/Description	Reset
2:0	R/W	SPI_CS_SELECT	0x0
		Control the cs output in master mode	
		0 = none slave device selected	
		1 = selected slave device connected to GPIO with FUNC_MODE=SPI_CS0	
		2 = selected slave device connected to GPIO with FUNC_MODE=SPI_CS1	
		4 = selected slave device connected to GPIO with FUNC_MODE=GPIO	

Table 320: SPI_FIFO_HIGH_REG (0x50001228)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	SPI_FIFO_HIGH	0x0
		RX/TX fifo data. 16 MSb when spi word is larger than 16 bits	
		This register has to be written before the SPI_FIFO_WRITE_REG	
		This register has to be read after the SPI_FIFO_READ_REG	

Table 321: SPI_TXBUFFER_FORCE_L_REG (0x5000122C)

Bit	Mode	Symbol/Description	Reset
15:0	W	SPI_TXBUFFER_FORCE_L	0x0
		Write directly the tx buffer (2 LSB). It must to be used only in slave mode	

Table 322: SPI_TXBUFFER_FORCE_H_REG (0x50001230)

Bit	Mode	Symbol/Description	Reset
15:0	W	SPI_TXBUFFER_FORCE_H	0x0
		Write directly the tx buffer (2 MSB). It must to be used only in slave mode.	
		This register has to be written before the SPI_FIFO_WRITE_REG	

32.16 Timer and Triple PWM Registers

Table 323: Register map Timer+3PWM

Address	Register	Description
0x50003400	TIMER0_CTRL_REG	Timer0 control register
0x50003402	TIMER0_ON_REG	Timer0 on control register
0x50003404	TIMER0_RELOAD_M_R EG	16 bits reload value for Timer0
0x50003406	TIMER0_RELOAD_N_RE G	16 bits reload value for Timer0
0x50003408	TRIPLE_PWM_FREQUE NCY	Frequency for PWM 2, 3, 4, 5, 6 and 7
0x5000340a	PWM2_START_CYCLE	Defines start Cycle for PWM2
0x5000340c	PWM3_START_CYCLE	Defines start Cycle for PWM3
0x5000340e	PWM4_START_CYCLE	Defines start Cycle for PWM4
0x50003410	PWM5_START_CYCLE	Defines start Cycle for PWM5
0x50003412	PWM6_START_CYCLE	Defines start Cycle for PWM6
0x50003414	PWM7_START_CYCLE	Defines start Cycle for PWM7
0x50003416	PWM2_END_CYCLE	Defines end Cycle for PWM2
0x50003418	PWM3_END_CYCLE	Defines end Cycle for PWM3
0x5000341a	PWM4_END_CYCLE	Defines end Cycle for PWM4
0x5000341c	PWM5_END_CYCLE	Defines end Cycle for PWM5
0x5000341e	PWM6_END_CYCLE	Defines end Cycle for PWM6
0x50003420	PWM7_END_CYCLE	Defines end Cycle for PWM7
0x50003422	TRIPLE_PWM_CTRL_RE	PWM 2, 3, 4, 5, 6, 7 Control

Table 324: TIMER0_CTRL_REG (0x50003400)

Bit	Mode	Symbol/Description	Reset
15:4	-		0x0
		Reserved	
3	R/W PWM_MODE		0x0
		0 = PWM signals are 1 during high time.	
		1 = PWM signals send out the (fast) clock divided by 2 during high time. So it is in the range of 1 to 8 MHz.	
2	R/W	TIM0_CLK_DIV	0x0
		1 = Timer0 uses selected clock frequency as is.	

Bit	Mode	Symbol/Description	Reset
		0 = Timer0 uses selected clock frequency divided by 10.	
		Note that this applies only to the ON-counter.	
1	R/W	TIM0_CLK_SEL	0x0
		1 = Timer0 uses 16, 8, 4, or 2 MHz (fast) clock frequency 0 = Timer0 uses LP clock	
0	R/W	TIM0_CTRL	0x0
		0 = Timer0 is off and in reset state	
		1 = Timer0 is running	

Table 325: TIMERO_ON_REG (0x50003402)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	TIM0_ON	0x0
		Timer0 On reload value.	
		If read the actual ON-counter value is returned.	

Table 326: TIMERO_RELOAD_M_REG (0x50003404)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	TIM0_M	0x0
		Timer0 "high" reload value.	
		If read, the actual T0-counter value is returned.	

Table 327: TIMERO_RELOAD_N_REG (0x50003406)

Bit	Mode	Symbol/Description	Reset
15:0	R/W	TIM0_N	0x0
		Timer0 "low" reload value.	
		If read, the actual T0-counter value is returned.	

Table 328: TRIPLE_PWM_FREQUENCY (0x50003408)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	PWM_FREQ	0x0
		Defines the frequency of PWM 2, 3, 4, 5, 6, and 7. PWM freq = module Frequency/(value+1)	
		Module frequency is LP_CLK when TRIPLE_PWM_CLK_SEL = 0, else is the sys_clk divided by TMR_DI.	

Table 329: PWM2_START_CYCLE (0x5000340A)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	START_CYCLE	0x0
		Defines the cycle in which the PWM becomes high. If start_cycle is larger than freq or end_cycle is equal to start_cycle, pwm out is always 0.	

Table 330: PWM3_START_CYCLE (0x5000340C)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	START_CYCLE	0x0
		Defines the cycle in which the PWM becomes high. If start_cycle is larger than freq or end_cycle is equal to start_cycle, pwm out is always 0.	

Table 331: PWM4_START_CYCLE (0x5000340E)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	START_CYCLE	0x0
		Defines the cycle in which the PWM becomes high. If start_cycle is larger than freq or end_cycle is equal to start_cycle, pwm out is always 0.	

Table 332: PWM5_START_CYCLE (0x50003410)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	START_CYCLE	0x0
		Defines the cycle in which the PWM becomes high. If start_cycle is larger than freq or end_cycle is equal to start_cycle, pwm out is always 0.	

Table 333: PWM6_START_CYCLE (0x50003412)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	START_CYCLE	0x0
		Defines the cycle in which the PWM becomes high. If start_cycle is larger than freq or end_cycle is equal to start_cycle, pwm out is always 0.	

Table 334: PWM7_START_CYCLE (0x50003414)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	START_CYCLE	0x0
		Defines the cycle in which the PWM becomes high. if start_cycle is larger than freq or end_cycle is equal to start_cycle, pwm out is always 0.	

Table 335: PWM2_END_CYCLE (0x50003416)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	END_CYCLE	0x0
		Defines the cycle in which the PWM becomes low. If end_cycle is larger than freq and start_cycle is not larger than freq, output is always 1.	

Table 336: PWM3_END_CYCLE (0x50003418)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	END_CYCLE	0x0
		Defines the cycle in which the PWM becomes low. If end_cycle is larger than freq and start_cycle is not larger than freq, output is always 1.	

Table 337: PWM4_END_CYCLE (0x5000341A)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	END_CYCLE	0x0
		Defines the cycle in which the PWM becomes low. If end_cycle is larger than freq and start_cycle is not larger than freq, output is always 1.	

Table 338: PWM5_END_CYCLE (0x5000341C)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	END_CYCLE	0x0
		Defines the cycle in which the PWM becomes low. If end_cycle is larger than freq and start_cycle is not larger than freq, output is always 1.	

Table 339: PWM6_END_CYCLE (0x5000341E)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	END_CYCLE	0x0
		Defines the cycle in which the PWM becomes low. If end_cycle is larger than freq and start_cycle is not larger than freq, output is always 1.	

Table 340: PWM7_END_CYCLE (0x50003420)

Bit	Mode	Symbol/Description	Reset
13:0	R/W	END_CYCLE	0x0
		Defines the cycle in which the PWM becomes low. If end_cycle is larger than freq and start_cycle is not larger than freq, output is always 1.	

Table 341: TRIPLE_PWM_CTRL_REG (0x50003422)

Bit	Mode	Symbol/Description	Reset
3	R/W	TRIPLE_PWM_CLK_SEL	0x0
		1 = Timer2 uses 16, 8, 4, or 2 MHz (fast) clock frequency 0 = Timer2 uses LP clock	
2	R/W	HW_PAUSE_EN	0x1
		1 = Hardware can pause PWM 2, 3, 4, 5, 6, 7	
1	R/W	SW_PAUSE_EN	0x0
		1 = PWM 2 3 4 5 6 7 are paused	
0	R/W	TRIPLE_PWM_ENABLE	0x0
		1 = Enable PWM 2 3 4 5 6 7	

32.17 Timer1 Registers

Table 342: Register map Timer1

Address	Register	Description
0x50004000	TIMER1_CTRL_REG	Timer1 control register
0x50004004	TIMER1_CAPTURE_RE G	Timer1 Capture control register
0x50004008	TIMER1_STATUS_REG	Timer1 counter value
0x5000400c	TIMER1_CAPCNT1_VAL UE_REG	Timer1 value for event on GPIO1
0x50004010	TIMER1_CAPCNT2_VAL UE_REG	Timer1 value for event on GPIO2
0x50004014	TIMER1_CLR_EVENT_R EG	Clear event register

Table 343: TIMER1_CTRL_REG (0x50004000)

Bit	Mode	Symbol/Description	Reset
16	R/W	TIMER1_CLK_EN	0x0
		0 = Timer1 clock is disabled	
		1 = Timer1 clock is enabled	
15	R/W	TIMER1_USE_SYS_CLK	0x0
		0 = Timer1 use the clock LP clock	
		1 = Timer1 use the system clock	
14	R/W	TIMER1_FREE_RUN_MODE_EN	0x0
		Applicable when timer counts up	
		1 = Timer1 goes to zero when it reaches the max value	
		0 = Timer1 goes to zero when it reaches the reload value	
13	R/W	TIMER1_IRQ_EN	0x0
		0 = Timer1 IRQ masked	
		1 = Timer1 IRQ unmasked	
12	R/W	TIMER1_COUNT_DOWN_EN	0x0
		0 = Timer1 counts up	
		1 = Timer1 counts down	
11	R/W	TIMER1_ENABLE	0x0
		0 = Timer1 disabled	
		1 = Timer1 enabled	
10:0	R/W	TIMER1_RELOAD	0x0
		Reload or max value in timer mode. Actual delay is the register value plus synchronization time (3 clock cycles)	

Table 344: TIMER1_CAPTURE_REG (0x50004004)

Bit	Mode	Symbol/Description	Reset
27	R/W	TIMER1_IN2_STAMP_TYPE	0x0
		0 = On each event store the counter value	
		1 = On each event store the RTC time stamp	

Bit	Mode	Symbol/Description	Reset
26:21	R/W	TIMER1_IN2_PERIOD_MAX	0x0
		Gives the number of periods +1 of IN2, in which module counts	
20	R/W	TIMER1_IN2_IRQ_EN	0x0
		1 = Interrupt is generated when capture is occurred or was counted TIMER1_IN2_PERIOD_MAX	
		0 = Interrupt is masked	
19	R/W	TIMER1_IN2_COUNT_EN	0x0
		0 = Capture mode 1 = Count mode	
18	R/W	TIMER1_IN2_EVENT_FALL_EN	0x0
		0 = Rising edge event 1 = Falling edge event It should be written when TIMER1 GPIO2 CONF = 0 to prevent false events	G.I.G
17:14	R/W	TIMER1_GPIO2_CONF	0x0
		0,13,14,15 = IN2 is not used 112 = Defines the P0 pin (011) module uses as IN2	
13	R/W	TIMER1 IN1 STAMP TYPE	0x0
		0 = On each event store the counter value 1 = On each event store the RTC time stamp	
12:7	R/W	TIMER1_IN1_PERIOD_MAX	0x0
		Gives the number of periods +1 of IN1, in which module counts	
6	R/W	TIMER1_IN1_IRQ_EN	0x0
		1 = Interrupt is generated when capture is occurred or was counted TIMER1_IN1_PERIOD_MAX	
		0 = Interrupt is masked	
5	R/W	TIMER1_IN1_COUNT_EN	0x0
		0 = Capture mode	
		1 = Count mode	
4	R/W	TIMER1_IN1_EVENT_FALL_EN	0x0
		0 = Rising edge event	
		1 = Falling edge event	
		It should be written when TIMER1_GPIO1_CONF = 0 to prevent false events	
3:0	R/W	TIMER1_GPIO1_CONF	0x0
		0,13,14,15 = IN1 is not used	
		112 = Defines the P0 pin (011) module uses as IN1	

Table 345: TIMER1_STATUS_REG (0x50004008)

Bit	Mode	Symbol/Description	Reset
15	R	TIMER1_IN2_OVRFLW	0x0
		1 = New IN2 event occurred while Interrupt was pending. TIMER1_CAPCNT2_VALUE_REG gives the time stamp of the first event.	
14	R	TIMER1_IN1_OVRFLW	0x0
		1 = New IN1 event occurred while Interrupt was pending.	

Bit	Mode	Symbol/Description	Reset
		TIMER1_CAPCNT1_VALUE_REG gives the time stamp of the first event.	
13	R	TIMER1_IN2_EVENT	0x0
		1 = Pending Capture 2 interrupt. It has to be clear writing 1 to TIMER1_CLR_IN2_EVENT	
12	R	TIMER1_IN1_EVENT	0x0
		1 = Pending Capture 1 interrupt. It has to be clear writing 1 to TIMER1_CLR_IN1_EVENT	
11	R	TIMER1_TIMER_EVENT	0x0
		1 = Pending Timer interrupt. it has to be clear writing 1 to TIMER1_CLR_TIMER_EVENT	
10:0	R	TIMER1_TIMER_VALUE	0x0
		Gives the current timer value	

Table 346: TIMER1_CAPCNT1_VALUE_REG (0x5000400C)

Bit	Mode	Symbol/Description	Reset
21:11	R	TIMER1_CAPCNT1_RTC_HIGH	0x0
		In Counter mode: Not used In Capture mode: Gives the RTC time stamp (high part) when an IN1 event was occurred	
10:0	R	TIMER1_CAPCNT1_VALUE	0x0
		In Counter mode: Gives the number of timer clock cycles minus 1 which was measured during TIMER1_IN1_PERIOD_MAX periods of IN1	
		In Capture mode (TIMER1_IN1_STAMP_TYPE = 0): Gives the Counter value when an IN1 event was occurred	
		In Capture mode (TIMER1_IN1_STAMP_TYPE = 1): Gives the RTC time stamp (low part) when an IN1 event was occurred	

Table 347: TIMER1_CAPCNT2_VALUE_REG (0x50004010)

Bit	Mode	Symbol/Description	Reset
21:11	R	TIMER1_CAPCNT2_RTC_HIGH	0x0
		In Counter mode: Not used In Capture mode Gives the RTC time stamp (high part) when an IN2 event was occurred	
10:0	R	TIMER1_CAPCNT2_VALUE	0x0
		In Counter mode: Gives the number of timer clock cycles minus 1 which was measured during TIMER1_IN2_PERIOD_MAX periods of IN2	
		In Capture mode (TIMER1_IN2_STAMP_TYPE = 0): Gives the Counter value when an IN2 event was occurred	
		In Capture mode (TIMER1_IN2_STAMP_TYPE = 1): Gives the RTC time stamp (low part) when an IN2 event was occurred	

Table 348: TIMER1_CLR_EVENT_REG (0x50004014)

Bit	Mode	Symbol/Description	Reset
2	R0/WC	TIMER1_CLR_IN2_EVENT	0x0
		Write 1 to clear the TIMER1_IN2_EVENT and TIMER1_IN2_OVRFLW	

Ultra-Low Power Bluetooth 5.1 SoC

Bit	Mode	Symbol/Description	Reset
1	R0/WC	TIMER1_CLR_IN1_EVENT	0x0
		Write 1 to clear the TIMER1_IN1_EVENT and TIMER1_IN1_OVRFLW	
0	R0/WC	TIMER1_CLR_TIMER_EVENT	0x0
		Write 1 to clear the TIMER1_TIMER_EVENT	

32.18 UART Interface Registers

Table 349: Register map UART

Address	Register	Description
0x50001000	UART_RBR_THR_DLL_ REG	Receive Buffer Register/Transmit Holding Register/Divisor Latch Low
0x50001004	UART_IER_DLH_REG	Interrupt Enable Register/Divisor Latch High
0x50001008	UART_IIR_FCR_REG	Interrupt Identification Register/FIFO Control Register
0x5000100c	UART_LCR_REG	Line Control Register
0x50001010	UART_MCR_REG	Modem Control Register
0x50001014	UART_LSR_REG	Line Status Register
0x50001018	UART_MSR_REG	Modem Status Register
0x5000101c	UART_SCR_REG	Scratchpad Register
0x50001030	UART_SRBR_STHR0_R EG	Shadow Receive/Transmit Buffer Register
0x50001034	UART_SRBR_STHR1_R EG	Shadow Receive/Transmit Buffer Register
0x50001038	UART_SRBR_STHR2_R EG	Shadow Receive/Transmit Buffer Register
0x5000103c	UART_SRBR_STHR3_R EG	Shadow Receive/Transmit Buffer Register
0x50001040	UART_SRBR_STHR4_R EG	Shadow Receive/Transmit Buffer Register
0x50001044	UART_SRBR_STHR5_R EG	Shadow Receive/Transmit Buffer Register
0x50001048	UART_SRBR_STHR6_R EG	Shadow Receive/Transmit Buffer Register
0x5000104c	UART_SRBR_STHR7_R EG	Shadow Receive/Transmit Buffer Register
0x50001050	UART_SRBR_STHR8_R EG	Shadow Receive/Transmit Buffer Register
0x50001054	UART_SRBR_STHR9_R EG	Shadow Receive/Transmit Buffer Register
0x50001058	UART_SRBR_STHR10_ REG	Shadow Receive/Transmit Buffer Register
0x5000105c	UART_SRBR_STHR11_ REG	Shadow Receive/Transmit Buffer Register
0x50001060	UART_SRBR_STHR12_ REG	Shadow Receive/Transmit Buffer Register
0x50001064	UART_SRBR_STHR13_ REG	Shadow Receive/Transmit Buffer Register
0x50001068	UART_SRBR_STHR14_ REG	Shadow Receive/Transmit Buffer Register
0x5000106c	UART_SRBR_STHR15_ REG	Shadow Receive/Transmit Buffer Register
0x50001070	UART_FAR_REG	FIFO Access Register
0x5000107c	UART_USR_REG	UART Status Register
0x50001080	UART_TFL_REG	Transmit FIFO Level

Address	Register	Description
0x50001084	UART_RFL_REG	Receive FIFO Level
0x50001088	UART_SRR_REG	Software Reset Register
0x5000108c	UART_SRTS_REG	Shadow Request to Send
0x50001090	UART_SBCR_REG	Shadow Break Control Register
0x50001094	UART_SDMAM_REG	Shadow DMA Mode
0x50001098	UART_SFE_REG	Shadow FIFO Enable
0x5000109c	UART_SRT_REG	Shadow RCVR Trigger
0x500010a0	UART_STET_REG	Shadow TX Empty Trigger
0x500010a4	UART_HTX_REG	Halt TX
0x500010a8	UART_DMASA_REG	DMA Software Acknowledge
0x500010c0	UART_DLF_REG	Divisor Latch Fraction Register
0x500010f8	UART_UCV_REG	Component Version
0x500010fa	UART_UCV_HIGH_REG	Component Version
0x500010fc	UART_CTR_REG	Component Type Register
0x500010fe	UART_CTR_HIGH_REG	Component Type Register
0x50001100	UART2_RBR_THR_DLL_ REG	Receive Buffer Register/Transmit Holding Register/Divisor Latch Low
0x50001104	UART2_IER_DLH_REG	Interrupt Enable Register/Divisor Latch High
0x50001108	UART2_IIR_FCR_REG	Interrupt Identification Register/FIFO Control Register
0x5000110c	UART2_LCR_REG	Line Control Register
0x50001110	UART2_MCR_REG	Modem Control Register
0x50001114	UART2_LSR_REG	Line Status Register
0x5000111c	UART2_SCR_REG	Scratchpad Register
0x50001130	UART2_SRBR_STHR0_ REG	Shadow Receive/Transmit Buffer Register
0x50001134	UART2_SRBR_STHR1_ REG	Shadow Receive/Transmit Buffer Register
0x50001138	UART2_SRBR_STHR2_ REG	Shadow Receive/Transmit Buffer Register
0x5000113c	UART2_SRBR_STHR3_ REG	Shadow Receive/Transmit Buffer Register
0x50001140	UART2_SRBR_STHR4_ REG	Shadow Receive/Transmit Buffer Register
0x50001144	UART2_SRBR_STHR5_ REG	Shadow Receive/Transmit Buffer Register
0x50001148	UART2_SRBR_STHR6_ REG	Shadow Receive/Transmit Buffer Register
0x5000114c	UART2_SRBR_STHR7_ REG	Shadow Receive/Transmit Buffer Register
0x50001150	UART2_SRBR_STHR8_ REG	Shadow Receive/Transmit Buffer Register
0x50001154	UART2_SRBR_STHR9_ REG	Shadow Receive/Transmit Buffer Register
0x50001158	UART2_SRBR_STHR10_ REG	Shadow Receive/Transmit Buffer Register

Address	Register	Description
0x5000115c	UART2_SRBR_STHR11_ REG	Shadow Receive/Transmit Buffer Register
0x50001160	UART2_SRBR_STHR12_ REG	Shadow Receive/Transmit Buffer Register
0x50001164	UART2_SRBR_STHR13_ REG	Shadow Receive/Transmit Buffer Register
0x50001168	UART2_SRBR_STHR14_ REG	Shadow Receive/Transmit Buffer Register
0x5000116c	UART2_SRBR_STHR15_ REG	Shadow Receive/Transmit Buffer Register
0x50001170	UART2_FAR_REG	FIFO Access Register
0x5000117c	UART2_USR_REG	UART Status Register
0x50001180	UART2_TFL_REG	Transmit FIFO Level
0x50001184	UART2_RFL_REG	Receive FIFO Level
0x50001188	UART2_SRR_REG	Software Reset Register
0x50001190	UART2_SBCR_REG	Shadow Break Control Register
0x50001194	UART2_SDMAM_REG	Shadow DMA Mode
0x50001198	UART2_SFE_REG	Shadow FIFO Enable
0x5000119c	UART2_SRT_REG	Shadow RCVR Trigger
0x500011a0	UART2_STET_REG	Shadow TX Empty Trigger
0x500011a4	UART2_HTX_REG	Halt TX
0x500011a8	UART2_DMASA_REG	DMA Software Acknowledge
0x500011c0	UART2_DLF_REG	Divisor Latch Fraction Register
0x500011f8	UART2_UCV_REG	Component Version
0x500011fa	UART2_UCV_HIGH_RE G	Component Version
0x500011fc	UART2_CTR_REG	Component Type Register
0x500011fe	UART2_CTR_HIGH_RE G	Component Type Register

Table 350: UART_RBR_THR_DLL_REG (0x50001000)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	RBR_THR_DLL	0x0
		Receive Buffer Register: (RBR). This register contains the data byte received on the serial input port (sin) in UART mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise, it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Transmit Holding Register: (THR)	

Bit	Mode	Symbol/Description	Reset
		This register contains data to be transmitted on the serial output port (sout) in UART mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, 16 number of characters of data may be written to the THR before the FIFO is full. Any attempt to write data when the FIFO is full results in the write data being lost.	
		Divisor Latch (Low): (DLL)	
		This register makes up the lower 8-bits of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may only be accessed when the DLAB bit (LCR[7]) is set. The output baud rate is equal to the serial clock (sclk) frequency divided by sixteen times the value of the baud rate divisor, as follows:	
		baud rate = (serial clock freq)/(16 * divisor)	
		Note that with the Divisor Latch Registers (DLL and DLH) set to zero, the baud clock is disabled and no serial communications occur. Also, when the Divisor Latch is set, at least eight clock cycles of the slowest UART clock should be allowed to pass before transmitting or receiving data.	
		For the Divisor Latch (High) bits, see the UART_IER_DLH_REG register.	

Table 351: UART_IER_DLH_REG (0x50001004)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7	R/W	PTIME_dlh7	0x0
		Interrupt Enable Register: PTIME, Programmable THRE Interrupt Mode Enable. This is used to enable/disable the generation of THRE Interrupt.	
		0 = Disabled	
		1 = Enabled	
		Divisor Latch (High): DLH7 , Bit 7 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set. See the UART_RBR_THR_DLL_REG register.	
6:4	R/W	dlh6_4	0x0
		Divisor Latch (High): DLH6 to DLH4 , Bits 6 to 4 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set, otherwise, this field is reserved. See the UART_RBR_THR_DLL_REG register.	
3	R/W	EDSSI_dlh3	0x0
		Interrupt Enable Register: EDSSI, Enable Modem Status Interrupt. This is used to enable/disable the generation of Modem Status Interrupt. This is the fourth highest priority interrupt.	
		0 = Disabled	
		1 = Enabled	
		Divisor Latch (High): DLH3 , Bit 3 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set. See the UART_RBR_THR_DLL_REG register.	
2	R/W	ELSI_dhl2	0x0
	1		

Bit	Mode	Symbol/Description	Reset
		Interrupt Enable Register: ELSI, Enable Receiver Line Status Interrupt. This is used to enable/disable the generation of Receiver Line Status Interrupt. This is the highest priority interrupt.	
		0 = Disabled	
		1 = Enabled	
		Divisor Latch (High): DLH2 , Bit 2 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set. See the UART_RBR_THR_DLL_REG register.	
1	R/W	ETBEI_dlh1	0x0
		Interrupt Enable Register: ETBEI, Enable Transmit Holding Register Empty Interrupt. This is used to enable/disable the generation of Transmitter Holding Register Empty Interrupt. This is the third highest priority interrupt.	
		0 = Disabled	
		1 = Enabled	
		Divisor Latch (High): DLH1 , Bit 1 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set. See the UART_RBR_THR_DLL_REG register.	
0	R/W	ERBFI_dlh0	0x0
		Interrupt Enable Register: ERBFI, Enable Received Data Available Interrupt. This is used to enable/disable the generation of Received Data Available Interrupt and the Character Timeout Interrupt (if in FIFO mode and FIFOs enabled). These are the second highest priority interrupts.	
		0 = Disabled	
		1 = Enabled	
		Divisor Latch (High): DLH0 , Bit 0 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set. See the UART_RBR_THR_DLL_REG register.	

Table 352: UART_IIR_FCR_REG (0x50001008)

Bit	Mode	Symbol/Description	Reset
7:6	R/W	UART_FIFOSE_RT	0x0
		On read	
		FIFOs Enabled (or FIFOSE): This is used to indicate whether the FIFOs are enabled or disabled.	
		00 = Disabled	
		11 = Enabled	
		On write	
		RCVR Trigger (or RT): This is used to select the trigger level in the receiver FIFO at which the Received Data Available Interrupt is generated. In auto flow control mode, it is used to determine when the rts_n signal is deasserted. It also determines when the dma_rx_req_n signal is asserted when in certain modes of operation. The following trigger levels are supported: 00 = 1 character in the FIFO 01 = FIFO 1/4 full	
		10 = FIFO 1/2 full	
		11 = FIFO 2 less than full	
5:4	R0/W	UART_TET	0x0

Bit	Mode	Symbol/Description	Reset
		On read	
		Reserved	
		On Write	
		TX Empty Trigger (or TET): This is used to select the empty threshold level at which the THRE Interrupts are generated when the mode is active. It also determines when the dma_tx_req_n signal is asserted when in certain modes of operation. The following trigger levels are supported: 00 = FIFO empty	
		01 = 2 characters in the FIFO	
		10 = FIFO 1/4 full	
		11 = FIFO 1/2 full	
3	R/W	UART_IID3_DMAM	0x0
		On Read (Bit3)	
		Interrupt ID (or IID): This indicates the highest priority pending interrupt which can be one of the following types:	
		0001 = No interrupt pending	
		0010 = THR empty	
		0100 = Received data available	
		0110 = Receiver line status	
		0111 = Busy detect	
		1100 = Character timeout	
		On Write	
		DMA Mode (or DMAM): This determines the DMA signalling mode used for the dma_tx_req_n and dma_rx_req_n output signals.	
		0 = Mode 0	
		1 = Mode 1	
2	R/W	UART_IID2_XFIFOR	0x0
		On Read (Bit2)	
		Interrupt ID (or IID): This indicates the highest priority pending interrupt which can be one of the following types:	
		0001 = No interrupt pending	
		0010 = THR empty	
		0100 = Received data available	
		0110 = Receiver line status	
		0111 = Busy detect	
		1100 = Character timeout	
		On Write	
		XMIT FIFO Reset (or XFIFOR): This resets the control portion of the transmit FIFO and treats the FIFO as empty. Note that this bit is "self-clearing" and it is not necessary to clear this bit.	
1	R/W	UART_IID1_RFIFOE	0x0
		On Read (Bit1)	
		Interrupt ID (or IID): This indicates the highest priority pending interrupt which can be one of the following types:	
		0001 = No interrupt pending	
		0010 = THR empty	
		0100 = Received data available	
		0110 = Receiver line status	
		0111 = Busy detect	

Bit	Mode	Symbol/Description	Reset
		1100 = Character timeout	
		On Write	
		RCVR FIFO Reset (or RFIFOR): This resets the control portion of the receive FIFO and treats the FIFO as empty. Note that this bit is "self-clearing" and it is not necessary to clear this bit.	
0	R/W	UART_IID0_FIFOE	0x1
		On Read (Bit0)	
		Interrupt ID (or IID): This indicates the highest priority pending interrupt which can be one of the following types:	
		0001 = No interrupt pending	
		0010 = THR empty	
		0100 = Received data available	
		0110 = Receiver line status	
		0111 = Busy detect	
		1100 = Character timeout	
		On Write	
		FIFO Enable (or FIFOE): This enables/disables the transmit (XMIT) and receive (RCVR) FIFOs. Whenever the value of this bit is changed both the XMIT and RCVR controller portion of FIFOs are reset.	

Table 353: **UART_LCR_REG** (0x5000100C)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7	R/W	UART_DLAB	0x0
		Divisor Latch Access Bit. Writeable only when UART is not busy (USR[0] is zero). This bit is used to enable reading and writing of the Divisor Latch register (DLL and DLH) to set the baud rate of the UART. This bit must be cleared after the initial baud rate setup to access other registers.	
6	R/W	UART_BC	0x0
		Break Control Bit. This is used to cause a break condition to be transmitted to the receiving device. If set to one, the serial output is forced to the spacing (logic 0) state. When not in Loopback mode, as determined by MCR[4], the sout line is forced low until the Break bit is cleared. If active (MCR[6] set to one) the sir_out_n line is continuously pulsed. When in Loopback mode, the break condition is internally looped back to the receiver and the sir_out_n line is forced low.	
5	-	- Reserved	0x0
4	R/W	UART_EPS Even Parity Select. Writeable only when UART is not busy (USR[0] is zero). This is used to select between even and odd parity, when parity is enabled (PEN set to one). If set to one, an even number of logic 1 s is transmitted or checked. If set to zero, an odd number of logic 1 s is transmitted or checked.	0x0
3	R/W	UART_PEN	0x0
		Parity Enable. Writeable only when UART is not busy (USR[0] is zero) This bit is used to enable and disable parity generation and detection in transmitted and received serial character respectively.	

Bit	Mode	Symbol/Description	Reset
		0 = Parity disabled	
		1 = Parity enabled	
2	R/W	UART_STOP	0x0
		Number of stop bits. Writeable only when UART is not busy (USR[0] is zero).	
		This is used to select the number of stop bits per character that the peripheral transmits and receives. If set to zero, one stop bit is transmitted in the serial data.	
		If set to one and the data bits are set to 5 (LCR[1:0] set to zero), one and a half stop bits is transmitted. Otherwise, two stop bits are transmitted. Note that regardless of the number of stop bits selected, the receiver checks only the first stop bit.	
		0 = 1 stop bit	
		1 = 1.5 stop bits when DLS (LCR[1:0]) is zero, else 2 stop bit	
1:0	R/W	UART_DLS	0x0
		Data Length Select. Writeable only when UART is not busy (USR[0] is zero). This is used to select the number of data bits per character that the peripheral transmits and receives. The number of bits that may be selected areas follows: 00 = 5 bits 01 = 6 bits 10 = 7 bits 11 = 8 bits	

Table 354: UART_MCR_REG (0x50001010)

Bit	Mode	Symbol/Description	Reset
15:7	-	-	0x0
		Reserved	
6	-	-	0x0
		Reserved	
5	R/W	UART_AFCE	0x0
		Auto Flow Control Enable.	
		When FIFOs are enabled and the Auto Flow Control Enable (AFCE) bit is set, Auto Flow Control features are enabled.	
		0 = Auto Flow Control Mode disabled	
		1 = Auto Flow Control Mode enabled	
4	R/W	UART_LB	0x0
		LoopBack Bit.	
		This is used to put the UART into a diagnostic mode for test purposes.	
		If operating in UART mode (SIR_MODE not active, MCR[6] set to zero), data on the sout line is held high, while serial data output is looped back to the sin line, internally. In this mode, all the interrupts are fully functional. Also, in Loopback mode, the modem control inputs (dsr_n, cts_n, ri_n, dcd_n) are disconnected and the modem control outputs (dtr_n, rts_n, out1_n, out2_n) are looped back to the inputs, internally.	
		If operating in Infrared mode (SIR_MODE active, MCR[6] set to one), data on the sir_out_n line is held low, while serial data output is inverted and looped back to the sir_in line.	
3	-	-	0x0
		Reserved	

Bit	Mode	Symbol/Description	Reset
2	-	-	0x0
		Reserved	
1	R/W	UART_RTS	0x0
		Request to Send.	
		This is used to directly control the Request to Send (rts_n) output. The Request To Send (rts_n) output is used to inform the modem or data set that the UART is ready to exchange data.	
		When Auto RTS Flow Control is not enabled (MCR[5] set to zero), the rts_n signal is set low by programming MCR[1] (RTS) to a high.In Auto Flow Control, AFCE_MODE == Enabled and active (MCR[5] set to one) and FIFOs enable (FCR[0] set to one), the rts_n output is controlled in the same way, but is also gated with the receiver FIFO threshold trigger (rts_n is inactive high when above the threshold). The rts_n signal is deasserted when MCR[1] is set low.	
		Note that in Loopback mode (MCR[4] set to one), the rts_n output is held inactive high while the value of this location is internally looped back to an input.	
0	-	-	0x0
		Reserved	

Table 355: UART_LSR_REG (0x50001014)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7	R	UART_RFE	0x0
		Receiver FIFO Error bit.	
		This bit is only relevant when FIFOs are enabled (FCR[0] set to one). This is used to indicate if there is at least one parity error, framing error, or break indication in the FIFO.	
		0 = No error in RX FIFO	
		1 = Error in RX FIFO	
		This bit is cleared when the LSR is read and the character with the error is at the top of the receiver FIFO and there are no subsequent errors in the FIFO.	
6	R	UART_TEMT	0x1
		Transmitter Empty bit.	
		If FIFOs enabled (FCR[0] set to one), this bit is set whenever the Transmitter Shift Register and the FIFO are both empty. If FIFOs are disabled, this bit is set whenever the Transmitter Holding Register(THR) and the Transmitter Shift Register are both empty.	
5	R	UART_THRE	0x1
		Transmit Holding Register Empty bit.	
		If THRE mode is disabled (IER[7] set to zero) and regardless of FIFOs being implemented/enabled or not, this bit indicates that the THR or TX FIFO is empty.	
		This bit is set whenever data is transferred from the THR or TX FIFO to the transmitter shift register and no new data has been written to the THR or TX FIFO. This also causes a THRE Interrupt to occur, if the THRE Interrupt is enabled. If both modes are active (IER[7] set to one and FCR[0] set to one respectively), the functionality is switched to indicate the transmitter FIFO is full, and no longer controls THRE interrupts, which are then controlled by the FCR[5:4] threshold setting.	
4	R	UART_BI	0x0

Bit	Mode	Symbol/Description	Reset
		Break Interrupt bit.	
		This is used to indicate the detection of a break sequence on the serial input data.	
		If in UART mode (SIR_MODE == Disabled), it is set whenever the serial input, sin, is held in a logic "0" state for longer than the sum of start time + data bits + parity + stop bits.	
		If in infrared mode (SIR_MODE == Enabled), it is set whenever the serial input, sir_in, is continuously pulsed to logic "0" for longer than the sum of start time + data bits + parity + stop bits. A break condition on serial input causes one and only one character, consisting of all zeros, to be received by the UART.	
		In FIFO mode, the character associated with the break condition is carried through the FIFO and is revealed when the character is at the top of the FIFO.	
		Reading the LSR clears the BI bit. In non-FIFO mode, the BI indication occurs immediately and persists until the LSR is read.	
3	R	UART_FE	0x0
		Framing Error bit.	
		This is used to indicate the occurrence of a framing error in the receiver. A framing error occurs when the receiver does not detect a valid STOP bit in the received data. In FIFO mode, because the framing error is associated with a character received, it	
		is revealed when the character with the framing error is at the top of the FIFO.	
		When a framing error occurs, the UART tries to resynchronize. It does this by assuming that the error was due to the start bit of the next character and then continues receiving the other bit, that is data, and/or parity and stop. It should be noted that the Framing Error (FE) bit (LSR[3]) is set if a break interrupt has occurred, as indicated by Break Interrupt (BI) bit (LSR[4]).	
		0 = No framing error	
		1 = Framing error	
		Reading the LSR clears the FE bit.	
2	R	UART_PE	0x0
		Parity Error bit.	
		This is used to indicate the occurrence of a parity error in the receiver if the Parity Enable (PEN) bit (LCR[3]) is set.	
		In the FIFO mode, because the parity error is associated with a character received, it is revealed when the character with the parity error arrives at the top of the FIFO.	
		It should be noted that the Parity Error (PE) bit (LSR[2]) is set if a break interrupt has occurred, as indicated by Break Interrupt (BI) bit (LSR[4]).	
		0 = No parity error	
		1 = Parity error	
		Reading the LSR clears the PE bit.	
1	R	UART_OE	0x0
		Overrun error bit.	
		This is used to indicate the occurrence of an overrun error.	
		This occurs if a new data character was received before the previous data was read.	
		In the non-FIFO mode, the OE bit is set when a new character arrives in the receiver before the previous character was read from the RBR. When this happens, the data in the RBR is overwritten. In the FIFO mode, an overrun error occurs when the FIFO is full and a new character arrives at the receiver. The data	
		in the FIFO is retained and the data in the receive shift register is lost.	
		0 = No overrun error	
		1 = Overrun error	
		Reading the LSR clears the OE bit.	

Bit	Mode	Symbol/Description	Reset
0	R	UART_DR	0x0
		Data Ready bit.	
		This is used to indicate that the receiver contains at least one character in the RBR or the receiver FIFO.	
		0 = No data ready	
		1 = Data ready	
		This bit is cleared when the RBR is read in non-FIFO mode, or when the receiver FIFO is empty, in FIFO mode.	

Table 356: UART_MSR_REG (0x50001018)

Bit	Mode	Symbol/Description	Reset
15:5	-	-	0x0
		Reserved	
4	R	UART_CTS	0x1
		Clear to Send.	
		This is used to indicate the current state of the modem control line cts_n. This bit is the complement of cts_n. When the Clear to Send input (cts_n) is asserted it is an indication that the modem or data set is ready to exchange data with the UART Ctrl.	
		0 = cts_n input is deasserted (logic 1)	
		1 = cts_n input is asserted (logic 0)	
		In Loopback mode (MCR[4] = 1), CTS is the same as MCR[1] (RTS).	
3:1	-	-	0x0
		Reserved	
0	-	-	0x0
		Reserved	

Table 357: **UART_SCR_REG** (0x5000101C)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	UART_SCRATCH_PAD	0x0
		This register is for programmers to use as a temporary storage space. It has no defined purpose in the UART Ctrl.	

Table 358: UART_SRBR_STHR0_REG (0x50001030)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register	

Bit	Mode	Symbol/Description	Reset
		(LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 359: UART_SRBR_STHR1_REG (0x50001034)

Mode	Symbol/Description	Reset
-	-	0x0
	Reserved	
R/W	SRBR_STHRx	0x0
	Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	
	-	R/W SRBR_STHRX Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write

Table 360: UART_SRBR_STHR2_REG (0x50001038)

Bit	Mode	Symbol/Description	Reset
15:8	-		0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0

Bit	Mode	Symbol/Description	Reset
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 361: UART_SRBR_STHR3_REG (0x5000103C)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 362: UART_SRBR_STHR4_REG (0x50001040)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 363: UART_SRBR_STHR5_REG (0x50001044)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined	

Bit	Mode	Symbol/Description	Reset
		by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 364: UART_SRBR_STHR6_REG (0x50001048)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
L		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 365: UART_SRBR_STHR7_REG (0x5000104C)

Bit	Mode	Symbol/Description	Reset
15:8	-		0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5])	

Bit	Mode	Symbol/Description	Reset
		is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 366: UART_SRBR_STHR8_REG (0x50001050)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 367: UART_SRBR_STHR9_REG (0x50001054)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	

Bit	Mode	Symbol/Description	Reset
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 368: UART_SRBR_STHR10_REG (0x50001058)

Bit	Mode	Symbol/Description	Reset
15:8	-		0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 369: UART_SRBR_STHR11_REG (0x5000105C)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must	

Bit	Mode	Symbol/Description	Reset
		be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 370: UART_SRBR_STHR12_REG (0x50001060)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 371: UART_SRBR_STHR13_REG (0x50001064)

Bit	Mode	Symbol/Description	Reset
15:8	-		0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0

Bit	Mode	Symbol/Description	Reset
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 372: UART_SRBR_STHR14_REG (0x50001068)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 373: UART_SRBR_STHR15_REG (0x5000106C)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 374: UART_FAR_REG (0x50001070)

Bit	Mode	Symbol/Description	Reset
0	R	UART_FAR	0x0
		Description: Writes have no effect when FIFO_ACCESS == No, always readable. This register is used to enable a FIFO access mode for testing, so that the receive FIFO can be written by the master and the transmit FIFO can be read by the master when FIFOs are implemented and enabled. When FIFOs are not implemented or not enabled it allows the RBR to be written by the master and the THR to be read by the master. 0 = FIFO access mode disabled 1 = FIFO access mode enabled Note, that when the FIFO access mode is enabled/disabled, the control portion of the receive FIFO and transmit FIFO is reset and the FIFO's are treated as empty.	

Table 375: UART_USR_REG (0x5000107C)

Bit	Mode	Symbol/Description	Reset
15:5	-	-	0x0
		Reserved	
4	R	UART_RFF	0x0
		Receive FIFO Full.	
		This is used to indicate that the receive FIFO is completely full.	
		0 = Receive FIFO not full	
		1 = Receive FIFO full	
		This bit is cleared when the RX FIFO is no longer full.	

Bit	Mode	Symbol/Description	Reset
3	R	UART_RFNE	0x0
		Receive FIFO Not Empty. This is used to indicate that the receive FIFO contains one or more entries. 0 = Receive FIFO is empty 1 = Receive FIFO is not empty This bit is cleared when the RX FIFO is empty.	
2	R	UART TFE	0x1
		Transmit FIFO Empty. This is used to indicate that the transmit FIFO is completely empty. 0 = Transmit FIFO is not empty 1 = Transmit FIFO is empty This bit is cleared when the TX FIFO is no longer empty.	
1	R	UART_TFNF	0x1
		Transmit FIFO Not Full. This is used to indicate that the transmit FIFO is not full. 0 = Transmit FIFO is full 1 = Transmit FIFO is not full This bit is cleared when the TX FIFO is full.	
0	R	UART_BUSY	0x0
		UART Busy. This indicates that a serial transfer is in progress, when cleared indicates that the DW_apb_uart is idle or inactive. 0 - DW_apb_uart is idle or inactive 1 - DW_apb_uart is busy (actively transferring data) Note that it is possible for the UART Busy bit to be cleared even though a new character may have been sent from another device. That is, if the DW_apb_uart has no data in the THR and RBR and there is no transmission in progress and a start bit of a new character has just reached the DW_apb_uart. This is due to the fact that a valid start is not seen until the middle of the bit period and this duration is dependent on the baud divisor that has been programmed. If a second system clock has been implemented (CLOCK_MODE == Enabled) the assertion of this bit is also delayed by several cycles of the slower clock.	

Table 376: UART_TFL_REG (0x50001080)

Bit	Mode	Symbol/Description	Reset
4:0	R	UART_TRANSMIT_FIFO_LEVEL	0x0
		Transmit FIFO Level.	
		This indicates the number of data entries in the transmit FIFO.	

Table 377: UART_RFL_REG (0x50001084)

Bit	Mode	Symbol/Description	Reset
4:0	R	UART_RECEIVE_FIFO_LEVEL	0x0
		Receive FIFO Level.	
		This is indicates the number of data entries in the receive FIFO.	

Table 378: UART_SRR_REG (0x50001088)

Bit	Mode	Symbol/Description	Reset
15:3	-	-	0x0
		Reserved	
2	W	UART_XFR	0x0
		XMIT FIFO Reset.	
		This is a shadow register for the XMIT FIFO Reset bit (FCR[2]). This can be used to remove the burden on software having to store previously written FCR values (which are pretty static) just to reset the transmit FIFO. This resets the control portion of the transmit FIFO and treats the FIFO as empty. Note that this bit is "self-clearing". It is not necessary to clear this bit.	
1	W	UART_RFR	0x0
		RCVR FIFO Reset.	
		This is a shadow register for the RCVR FIFO Reset bit (FCR[1]). This can be used to remove the burden on software having to store previously written FCR values (which are pretty static) just to reset the receive FIFO. This resets the control portion of the receive FIFO and treats the FIFO as empty.	
		Note that this bit is "self-clearing". It is not necessary to clear this bit.	
0	W	UART_UR	0x0
		UART Reset. This asynchronously resets the UART Ctrl and synchronously removes the reset assertion. For a two clock implementation both pclk and sclk domains are reset.	

Table 379: **UART_SRTS_REG** (0x5000108C)

Bit	Mode	Symbol/Description	Reset
15:1	-		0x0
		Reserved	
0	R/W	UART_SHADOW_REQUEST_TO_SEND	0x0
		Shadow Request to Send.	
		This is a shadow register for the RTS bit (MCR[1]), this can be used to remove the burden of having to perform a read-modify-write on the MCR. This is used to directly control the Request to Send (rts_n) output. The Request To Send (rts_n) output is used to inform the modem or data set that the UART Ctrl is ready to exchange data.	
		When Auto RTS Flow Control is not enabled (MCR[5] = 0), the rts_n signal is set low by programming MCR[1] (RTS) to a high.	
		In Auto Flow Control, AFCE_MODE == Enabled and active (MCR[5] = 1) and FIFOs enable (FCR[0] = 1), the rts_n output is controlled in the same way, but is also gated with the receiver FIFO threshold trigger (rts_n is inactive high when above the threshold).	
		Note that in Loopback mode (MCR[4] = 1), the rts_n output is held inactive-high while the value of this location is internally looped back to an input.	

Table 380: UART_SBCR_REG (0x50001090)

Bit	Mode	Symbol/Description	Reset
15:1	-		0x0
		Reserved	
0	R/W	UART_SHADOW_BREAK_CONTROL	0x0

Bit	Mode	Symbol/Description	Reset
		Shadow Break Control Bit.	
		This is a shadow register for the Break bit (LCR[6]), this can be used to remove the burden of having to perform a read modify write on the LCR. This is used to cause a break condition to be transmitted to the receiving device.	
		If set to one the serial output is forced to the spacing (logic 0) state. When not in Loopback Mode, as determined by MCR[4], the sout line is forced low until the Break bit is cleared.	
		If SIR_MODE active (MCR[6] = 1) the sir_out_n line is continuously pulsed. When in Loopback Mode, the break condition is internally looped back to the receiver.	

Table 381: UART_SDMAM_REG (0x50001094)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R/W	UART_SHADOW_DMA_MODE	0x0
		Shadow DMA Mode. This is a shadow register for the DMA mode bit (FCR[3]). This can be used to remove the burden of having to store the previously written value to the FCR in memory and having to mask this value so that only the DMA Mode bit gets updated. This determines the DMA signalling mode used for the dma_tx_req_n and dma_rx_req_n output signals. 0 = Mode 0 1 = Mode 1	

Table 382: UART_SFE_REG (0x50001098)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R/W	UART_SHADOW_FIFO_ENABLE	0x0
		Shadow FIFO Enable. This is a shadow register for the FIFO enable bit (FCR[0]). This can be used to remove the burden of having to store the previously written value to the FCR in memory and having to mask this value so that only the FIFO enable bit gets updated. This enables/disables the transmit (XMIT) and receive (RCVR) FIFOs. If this bit is set to zero (disabled) after being enabled then both the XMIT and RCVR controller portion of FIFOs are reset.	

Table 383: UART_SRT_REG (0x5000109C)

Bit	Mode	Symbol/Description	Reset
15:2	-	-	0x0
		Reserved	
1:0	R/W	UART_SHADOW_RCVR_TRIGGER	0x0
		Shadow RCVR Trigger. This is a shadow register for the RCVR trigger bits (FCR[7:6]). This can be used to remove the burden of having to store the previously written value to the FCR in memory and having to mask this value so that only the RCVR trigger bit gets updated.	

Bit	Mode	Symbol/Description	Reset
		This is used to select the trigger level in the receiver FIFO at which the Received Data Available Interrupt is generated. It also determines when the dma_rx_req_n signal is asserted when DMA Mode (FCR[3]) = 1. The following trigger levels are supported:	
		00 = 1 character in the FIFO	
		01 = FIFO ¼ full	
		10 = FIFO ½ full	
		11 = FIFO 2 less than full	

Table 384: UART_STET_REG (0x500010A0)

Bit	Mode	Symbol/Description	Reset
15:2	-	-	0x0
		Reserved	
1:0	R/W	UART_SHADOW_TX_EMPTY_TRIGGER	0x0
		Shadow TX Empty Trigger.	
		This is a shadow register for the TX empty trigger bits (FCR[5:4]). This can be used to remove the burden of having to store the previously written value to the FCR in memory and having to mask this value so that only the TX empty trigger bit gets updated.	
		This is used to select the empty threshold level at which the THRE Interrupts are generated when the mode is active. The following trigger levels are supported:	
		00 = FIFO empty	
		01 = 2 characters in the FIFO	
		10 = FIFO ¼ full	
		11 = FIFO ½ full	

Table 385: UART_HTX_REG (0x500010A4)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R/W	UART_HALT_TX	0x0
		This register is used to halt transmissions for testing, so that the transmit FIFO can be filled by the master when FIFOs are implemented and enabled.	
		0 = Halt TX disabled	
		1 = Halt TX enabled	
		Note, if FIFOs are implemented and not enabled, the setting of the halt TX register has no effect on operation.	

Table 386: UART_DMASA_REG (0x500010A8)

Bit	Mode	Symbol/Description	Reset
0	W	DMASA	0x0
		This register is used to perform DMA software acknowledge if a transfer needs to be terminated due to an error condition. For example, if the DMA disables the channel, then the DW_apb_uart should clear its request. This causes the TX request, TX single, RX request, and RX single signals to deassert. Note that this bit is "self-clearing" and it is not necessary to clear this bit.	

Table 387: UART_DLF_REG (0x500010C0)

Bit	Mode	Symbol/Description	Reset
3:0	R/W	UART_DLF	0x0
		The fractional value is added to integer value set by DLH, DLL. Fractional value is equal UART_DLF/16.	

Table 388: **UART_UCV_REG** (0x500010F8)

Bit	Mode	Symbol/Description	Reset
15:0	R	UCV	0x352A
		Component Version	

Table 389: UART_UCV_HIGH_REG (0x500010FA)

Bit	Mode	Symbol/Description	Reset
15:0	R	UCV	0x3331
		Component Version	

Table 390: UART_CTR_REG (0x500010FC)

Bit	Mode	Symbol/Description	Reset
15:0	R	CTR	0x110
		Component Type Register	

Table 391: UART_CTR_HIGH_REG (0x500010FE)

Bit	Mode	Symbol/Description	Reset
15:0	R	CTR	0x4457
		Component Type Register	

Table 392: UART2_RBR_THR_DLL_REG (0x50001100)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	RBR_THR_DLL	0x0
		Receive Buffer Register: (RBR).	
		This register contains the data byte received on the serial input port (sin) in UART mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise, it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Transmit Holding Register: (THR)	
		This register contains data to be transmitted on the serial output port (sout) in UART mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set,	

Bit	Mode	Symbol/Description	Reset
		writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, 16 number of characters of data may be written to the THR before the FIFO is full. Any attempt to write data when the FIFO is full results in the write data being lost.	
		Divisor Latch (Low): (DLL)	
		This register makes up the lower 8-bits of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may only be accessed when the DLAB bit (LCR[7]) is set. The output baud rate is equal to the serial clock (sclk) frequency divided by sixteen times the value of the baud rate divisor, as follows:	
		baud rate = (serial clock freq)/(16 * divisor)	
		Note that with the Divisor Latch Registers (DLL and DLH) set to zero, the baud clock is disabled and no serial communications occur. Also, when the Divisor Latch is set, at least eight clock cycles of the slowest UART clock should be allowed to pass before transmitting or receiving data.	
		For the Divisor Latch (High) bits, see the UART_IER_DLH_REG register.	

Table 393: UART2_IER_DLH_REG (0x50001104)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7	R/W	PTIME_dlh7	0x0
		Interrupt Enable Register: PTIME, Programmable THRE Interrupt Mode Enable. This is used to enable/disable the generation of THRE Interrupt. 0 = Disabled	
		1 = Enabled	
		Divisor Latch (High): DLH7 , Bit 7 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set. See the UART_RBR_THR_DLL_REG register.	
6:4	R/W	dlh6_4	0x0
		Divisor Latch (High): DLH6 to DLH4 , Bits 6 to 4 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set, otherwise, this field is reserved. See the UART_RBR_THR_DLL_REG register.	
3	R/W	EDSSI_dlh3	0x0
		Interrupt Enable Register: EDSSI, Enable Modem Status Interrupt. This is used to enable/disable the generation of Modem Status Interrupt. This is the fourth highest priority interrupt. 0 = Disabled 1 = Enabled	
		Divisor Latch (High): DLH3, Bit 3 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set. See the UART_RBR_THR_DLL_REG register.	
2	R/W	ELSI_dhl2	0x0
		Interrupt Enable Register: ELSI , Enable Receiver Line Status Interrupt. This is used to enable/disable the generation of Receiver Line Status Interrupt. This is the highest priority interrupt.	
		0 = Disabled	

Bit	Mode	Symbol/Description	Reset
		1 = Enabled	
		Divisor Latch (High): DLH2 , Bit 2 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set. See the UART_RBR_THR_DLL_REG register.	
1	R/W	ETBEI_dlh1	0x0
		Interrupt Enable Register: ETBEI, Enable Transmit Holding Register Empty Interrupt. This is used to enable/disable the generation of Transmitter Holding Register Empty Interrupt. This is the third highest priority interrupt. 0 = Disabled 1 = Enabled	
		Divisor Latch (High): DLH1 , Bit 1 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set. See the UART_RBR_THR_DLL_REG register.	
0	R/W	ERBFI_dlh0	0x0
		Interrupt Enable Register: ERBFI, Enable Received Data Available Interrupt. This is used to enable/disable the generation of Received Data Available Interrupt and the Character Timeout Interrupt (if in FIFO mode and FIFOs enabled). These are the second highest priority interrupts.	
		0 = Disabled	
		1 = Enabled	
		Divisor Latch (High): DLH0 , Bit 0 of the upper part of a 16-bit, read/write, Divisor Latch register that contains the baud rate divisor for the UART. This register may be accessed only when the DLAB bit (LCR[7]) is set. See the UART_RBR_THR_DLL_REG register.	

Table 394: UART2_IIR_FCR_REG (0x50001108)

Bit	Mode	Symbol/Description	Reset
7:6	R/W	UART_FIFOSE_RT	0x0
		On read	
		FIFOs Enabled (or FIFOSE): This is used to indicate whether the FIFOs are enabled or disabled.	
		00 = Disabled	
		11 = Enabled	
		On write	
		RCVR Trigger (or RT): This is used to select the trigger level in the receiver FIFO at which the Received Data Available Interrupt is generated. In auto flow control mode it is used to determine when the rts_n signal is deasserted. It also determines when the dma_rx_req_n signal is asserted when in certain modes of operation. The following trigger levels are supported:	
		00 = 1 character in the FIFO	
		01 = FIFO 1/4 full	
		10 = FIFO 1/2 full	
		11 = FIFO 2 less than full	
5:4	R0/W	UART_TET	0x0
		On read	
		Reserved	
		On Write	

Bit	Mode	Symbol/Description	Reset
		TX Empty Trigger (or TET): This is used to select the empty threshold level at which the THRE Interrupts are generated when the mode is active. It also determines when the dma_tx_req_n signal is asserted when in certain modes of operation. The following trigger levels are supported:	
		00 = FIFO empty	
		01 = 2 characters in the FIFO 10 = FIFO 1/4 full	
		11 = FIFO 1/2 full	
3	R/W	UART_IID3_DMAM	0x0
Ü	1000	On Read (Bit3)	OXO
		Interrupt ID (or IID): This indicates the highest priority pending interrupt which can be one of the following types:	
		0001 = No interrupt pending	
		0010 = THR empty	
		0100 = Received data available	
		0110 = Receiver line status	
		0111 = Busy detect	
		1100 = Character timeout	
		On Write	
		DMA Mode (or DMAM): This determines the DMA signalling mode used for the dma_tx_req_n and dma_rx_req_n output signals.	
		0 = Mode 0 1 = Mode 1	
	DAM		0,40
2	R/W	UART_IID2_XFIFOR	0x0
		On Read (Bit2) Interrupt ID (or IID): This indicates the highest priority pending interrupt which can be one of the following types:	
		0001 = No interrupt pending	
		0010 = THR empty	
		0100 = Received data available	
		0110 = Receiver line status	
		0111 = Busy detect	
		1100 = Character timeout	
		On Write	
		XMIT FIFO Reset (or XFIFOR): This resets the control portion of the transmit FIFO and treats the FIFO as empty. Note that this bit is "self-clearing" and it is not necessary to clear this bit.	
1	R/W	UART_IID1_RFIFOE	0x0
		On Read (Bit1)	
		Interrupt ID (or IID): This indicates the highest priority pending interrupt which can be one of the following types:	
		0001 = No interrupt pending	
		0010 = THR empty	
		0100 = Received data available	
		0110 = Receiver line status	
		0111 = Busy detect	
		1100 = Character timeout	
		On Write	

Bit	Mode	Symbol/Description	Reset
		RCVR FIFO Reset (or RFIFOR): This resets the control portion of the receive FIFO and treats the FIFO as empty. Note that this bit is "self-clearing" and it is not necessary to clear this bit.	
0	R/W	UART_IID0_FIFOE	0x1
		On Read (Bit0) Interrupt ID (or IID): This indicates the highest priority pending interrupt which can be one of the following types: 0001 = No interrupt pending 0010 = THR empty 0100 = Received data available 0110 = Receiver line status 0111 = Busy detect 1100 = Character timeout On Write FIFO Enable (or FIFOE): This enables/disables the transmit (XMIT) and receive (RCVR) FIFOs. Whenever the value of this bit is changed both the XMIT and RCVR controller portion of FIFOs are reset.	

Table 395: UART2_LCR_REG (0x5000110C)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7	R/W	UART_DLAB	0x0
		Divisor Latch Access Bit. Writeable only when UART is not busy (USR[0] is zero).	
		This bit is used to enable reading and writing of the Divisor Latch register (DLL and DLH) to set the baud rate of the UART.	
		This bit must be cleared after the initial baud rate setup to access other registers.	
6	R/W	UART_BC	0x0
		Break Control Bit.	
		This is used to cause a break condition to be transmitted to the receiving device. If set to one the serial output is forced to the spacing (logic 0) state. When not in Loopback mode, as determined by MCR[4], the sout line is forced low until the Break bit is cleared. If active (MCR[6] set to one) the sir_out_n line is continuously pulsed. When in Loopback mode, the break condition is internally looped back to the receiver and the sir_out_n line is forced low.	
5	-	-	0x0
		Reserved	
4	R/W	UART_EPS	0x0
		Even Parity Select. Writeable only when UART is not busy (USR[0] is zero).	
		This is used to select between even and odd parity, when parity is enabled (PEN set to one). If set to one, an even number of logic 1s is transmitted or checked. If set to zero, an odd number of logic 1s is transmitted or checked.	
3	R/W	UART_PEN	0x0
		Parity Enable. Writeable only when UART is not busy (USR[0] is zero)	
		This bit is used to enable and disable parity generation and detection in transmitted and received serial character respectively.	
		0 = parity disabled	
		1 = parity enabled	

Bit	Mode	Symbol/Description	Reset
2	R/W	UART_STOP	0x0
		Number of stop bits. Writeable only when UART is not busy (USR[0] is zero).	
		This is used to select the number of stop bits per character that the peripheral transmits and receives. If set to zero, one stop bit is transmitted in the serial data.	
		If set to one and the data bits are set to 5 (LCR[1:0] set to zero) one and a half stop bits is transmitted. Otherwise, two stop bits are transmitted. Note that regardless of the number of stop bits selected, the receiver checks only the first stop bit.	
		0 = 1 stop bit	
		1 = 1.5 stop bits when DLS (LCR[1:0]) is zero, else 2 stop bit	
1:0	R/W	UART_DLS	0x0
		Data Length Select. Writeable only when UART is not busy (USR[0] is zero).	
		This is used to select the number of data bits per character that the peripheral transmits and receives. The number of bits that may be selected areas follows:	
		00 = 5 bits	
		01 = 6 bits	
		10 = 7 bits	
		11 = 8 bits	

Table 396: UART2_MCR_REG (0x50001110)

Bit	Mode	Symbol/Description	Reset
15:5	-	-	0x0
		Reserved	
4	R/W	UART_LB	0x0
		LoopBack Bit.	
		This is used to put the UART into a diagnostic mode for test purposes.	
		If operating in UART mode (SIR_MODE not active, MCR[6] set to zero), data on the sout line is held high, while serial data output is looped back to the sin line, internally. In this mode, all the interrupts are fully functional. Also, in Loopback mode, the modem control inputs (dsr_n, cts_n, ri_n, dcd_n) are disconnected and the modem control outputs (dtr_n, rts_n, out1_n, out2_n) are looped back to the inputs, internally.	
		If operating in Infrared mode (SIR_MODE active, MCR[6] set to one), data on the sir_out_n line is held low, while serial data output is inverted and looped back to the sir_in line.	
3:0	-	-	0x0
		Reserved	

Table 397: UART2_LSR_REG (0x50001114)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7	R	UART_RFE	0x0
		Receiver FIFO Error bit.	
		This bit is only relevant when FIFOs are enabled (FCR[0] set to one). This is used to indicate if there is at least one parity error, framing error, or break indication in the FIFO.	

Bit	Mode	Symbol/Description	Reset
		0 = No error in RX FIFO	
		1 = Error in RX FIFO	
		This bit is cleared when the LSR is read and the character with the error is at the top of the receiver FIFO and there are no subsequent errors in the FIFO.	
6	R	UART_TEMT	0x1
		Transmitter Empty bit.	
		If FIFOs enabled (FCR[0] set to one), this bit is set whenever the Transmitter Shift Register and the FIFO are both empty. If FIFOs are disabled, this bit is set whenever the Transmitter Holding Register(THR) and the Transmitter Shift Register are both empty.	
5	R	UART_THRE	0x1
		Transmit Holding Register Empty bit.	
		If THRE mode is disabled (IER[7] set to zero) and regardless of FIFOs being implemented/enabled or not, this bit indicates that the THR or TX FIFO is empty.	
		This bit is set whenever data is transferred from the THR or TX FIFO to the transmitter shift register and no new data has been written to the THR or TX FIFO. This also causes a THRE Interrupt to occur, if the THRE Interrupt is enabled. If both modes are active (IER[7] set to one and FCR[0] set to one respectively), the functionality is switched to indicate the transmitter FIFO is full, and no longer controls THRE interrupts, which are then controlled by the FCR[5:4] threshold setting.	
4	R	UART_BI	0x0
		Break Interrupt bit.	
		This is used to indicate the detection of a break sequence on the serial input data.	
		If in UART mode (SIR_MODE == Disabled), it is set whenever the serial input, sin, is held in a logic "0" state for longer than the sum of start time + data bits + parity + stop bits.	
		If in infrared mode (SIR_MODE == Enabled), it is set whenever the serial input, sir_in, is continuously pulsed to logic "0" for longer than the sum of start time + data bits + parity + stop bits. A break condition on serial input causes one and only one character, consisting of all zeros, to be received by the UART.	
		In the FIFO mode, the character associated with the break condition is carried through the FIFO and is revealed when the character is at the top of the FIFO.	
		Reading the LSR clears the BI bit. In the non-FIFO mode, the BI indication occurs immediately and persists until the LSR is read.	
3	R	UART_FE	0x0
		Framing Error bit.	
		This is used to indicate the occurrence of a framing error in the receiver. A framing error occurs when the receiver does not detect a valid STOP bit in the received	
		data. In FIFO mode, because the framing error is associated with a character received, it is revealed when the character with the framing error is at the top of the FIFO.	
		When a framing error occurs, the UART tries to resynchronize. It does this by assuming that the error was due to the start bit of the next character and then continues receiving the other bit, that is data, and/or parity and stop. It should be noted that the Framing Error (FE) bit (LSR[3]) is set if a break interrupt has occurred, as indicated by Break Interrupt (BI) bit (LSR[4]).	
		0 = No framing error	
		1 = Framing error	
		Reading the LSR clears the FE bit.	
2	R	UART PE	0x0
		Parity Error bit.	

Bit	Mode	Symbol/Description	Reset
		This is used to indicate the occurrence of a parity error in the receiver if the Parity Enable (PEN) bit (LCR[3]) is set.	
		In the FIFO mode, because the parity error is associated with a character received, it is revealed when the character with the parity error arrives at the top of the FIFO.	
		It should be noted that the Parity Error (PE) bit (LSR[2]) is set if a break interrupt has occurred, as indicated by Break Interrupt (BI) bit (LSR[4]).	
		0 = No parity error	
		1 = Parity error	
		Reading the LSR clears the PE bit.	
1	R	UART_OE	0x0
		Overrun error bit.	
		This is used to indicate the occurrence of an overrun error.	
		This occurs if a new data character was received before the previous data was read.	
		In the non-FIFO mode, the OE bit is set when a new character arrives in the receiver before the previous character was read from the RBR. When this happens, the data in the RBR is overwritten. In the FIFO mode, an overrun error occurs when the FIFO is full and a new character arrives at the receiver. The data in the FIFO is retained and the data in the receive shift register is lost.	
		0 = No overrun error	
		1 = Overrun error	
		Reading the LSR clears the OE bit.	
0	R	UART_DR	0x0
		Data Ready bit.	
		This is used to indicate that the receiver contains at least one character in the RBR or the receiver FIFO.	
		0 = No data ready	
		1 = Data ready	
		This bit is cleared when the RBR is read in non-FIFO mode, or when the receiver FIFO is empty, in FIFO mode.	

Table 398: UART2_SCR_REG (0x5000111C)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	UART_SCRATCH_PAD	0x0
		This register is for programmers to use as a temporary storage space. It has no defined purpose in the UART Ctrl.	

Table 399: UART2_SRBR_STHR0_REG (0x50001130)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data	

Bit	Mode	Symbol/Description	Reset
		in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 400: UART2_SRBR_STHR1_REG (0x50001134)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 401: UART2_SRBR_STHR2_REG (0x50001138)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	

Bit	Mode	Symbol/Description	Reset
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 402: UART2_SRBR_STHR3_REG (0x5000113C)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 403: UART2_SRBR_STHR4_REG (0x50001140)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 404: UART2_SRBR_STHR5_REG (0x50001144)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined	

Bit	Mode	Symbol/Description	Reset
		by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 405: UART2_SRBR_STHR6_REG (0x50001148)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 406: UART2_SRBR_STHR7_REG (0x5000114C)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5])	

Bit	Mode	Symbol/Description	Reset
		is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 407: UART2_SRBR_STHR8_REG (0x50001150)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 408: UART2_SRBR_STHR9_REG (0x50001154)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	

Bit	Mode	Symbol/Description	Reset
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 409: UART2_SRBR_STHR10_REG (0x50001158)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 410: UART2_SRBR_STHR11_REG (0x5000115C)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must	

Bit	Mode	Symbol/Description	Reset
		be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 411: UART2_SRBR_STHR12_REG (0x50001160)

Bit	Mode	Symbol/Description	Reset
15:8	-		0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 412: UART2_SRBR_STHR13_REG (0x50001164)

Bit	Mode	Symbol/Description	Reset
15:8	-		0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0

Bit	Mode	Symbol/Description	Reset
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur.	
		Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 413: UART2_SRBR_STHR14_REG (0x50001168)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 414: UART2_SRBR_STHR15_REG (0x5000116C)

Bit	Mode	Symbol/Description	Reset
15:8	-	-	0x0
		Reserved	
7:0	R/W	SRBR_STHRx	0x0
		Shadow Receive Buffer Register x: This is a shadow register for the RBR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains the data byte received on the serial input port (sin) in UART mode or the serial infrared input (sir_in) in infrared mode. The data in this register is valid only if the Data Ready (DR) bit in the Line status Register (LSR) is set. If FIFOs are disabled (FCR[0] set to zero), the data in the RBR must be read before the next data arrives, otherwise it will be overwritten, resulting in an overrun error. If FIFOs are enabled (FCR[0] set to one), this register accesses the head of the receive FIFO. If the receive FIFO is full and this register is not read before the next data character arrives, then the data already in the FIFO will be preserved but any incoming data will be lost. An overrun error will also occur. Shadow Transmit Holding Register 0: This is a shadow register for the THR and has been allocated sixteen 32-bit locations so as to accommodate burst accesses from the master. This register contains data to be transmitted on the serial output port (sout) in UART mode or the serial infrared output (sir_out_n) in infrared mode. Data should only be written to the THR when the THR Empty (THRE) bit (LSR[5]) is set. If FIFOs are disabled (FCR[0] set to zero) and THRE is set, writing a single character to the THR clears the THRE. Any additional writes to the THR before the THRE is set again causes the THR data to be overwritten. If FIFOs are enabled (FCR[0] set to one) and THRE is set, x number of characters of data may be written to the THR before the FIFO is full. The number x (default=16) is determined by the value of FIFO Depth that you set during configuration. Any attempt to write data when the FIFO is full results in the write data being lost.	

Table 415: UART2_FAR_REG (0x50001170)

Bit	Mode	Symbol/Description	Reset
0	R	UART_FAR	0x0
		Description: Writes have no effect when FIFO_ACCESS == No, always readable. This register is use to enable a FIFO access mode for testing, so that the receive FIFO can be written by the master and the transmit FIFO can be read by the master when FIFOs are implemented and enabled. When FIFOs are not implemented or not enabled it allows the RBR to be written by the master and the THR to be read by the master. 0 = FIFO access mode disabled 1 = FIFO access mode enabled Note, that when the FIFO access mode is enabled/disabled, the control portion of the receive FIFO and transmit FIFO is reset and the FIFOs are treated as empty.	

Table 416: UART2_USR_REG (0x5000117C)

Bit	Mode	Symbol/Description	Reset
15:5	-	-	0x0
		Reserved	
4	R	UART_RFF	0x0
		Receive FIFO Full.	
		This is used to indicate that the receive FIFO is completely full.	
		0 = Receive FIFO not full	
		1 = Receive FIFO full	
		This bit is cleared when the RX FIFO is no longer full.	

Bit	Mode	Symbol/Description	Reset
3	R	UART_RFNE	0x0
		Receive FIFO Not Empty.	
		This is used to indicate that the receive FIFO contains one or more entries.	
		0 = Receive FIFO is empty	
		1 = Receive FIFO is not empty	
		This bit is cleared when the RX FIFO is empty.	
2	R	UART_TFE	0x1
		Transmit FIFO Empty.	
		This is used to indicate that the transmit FIFO is completely empty.	
		0 = Transmit FIFO is not empty	
		1 = Transmit FIFO is empty	
		This bit is cleared when the TX FIFO is no longer empty.	
1	R	UART_TFNF	0x1
		Transmit FIFO Not Full.	
		This is used to indicate that the transmit FIFO is not full.	
		0 = Transmit FIFO is full	
		1 = Transmit FIFO is not full	
		This bit is cleared when the TX FIFO is full.	
0	R	UART_BUSY	0x0
		UART Busy. This indicates that a serial transfer is in progress, when cleared indicates that the DW_apb_uart is idle or inactive. 0 - DW_apb_uart is idle or inactive 1 - DW_apb_uart is busy (actively transferring data) Note that it is possible for the UART Busy bit to be cleared even though a new character may have been sent from another device. That is, if the DW_apb_uart has no data in the THR and RBR and there is no transmission in progress and a start bit of a new character has just reached the DW_apb_uart. This is due to the fact that a valid start is not seen until the middle of the bit period and this duration is dependent on the baud divisor that has been programmed. If a second system clock has been implemented (CLOCK_MODE == Enabled) the assertion of this bit is also delayed by several cycles of the slower clock.	

Table 417: UART2_TFL_REG (0x50001180)

Bit	Mode	Symbol/Description	Reset
4:0	R	UART_TRANSMIT_FIFO_LEVEL	0x0
		Transmit FIFO Level.	
		This indicates the number of data entries in the transmit FIFO.	

Table 418: UART2_RFL_REG (0x50001184)

Bit	Mode	Symbol/Description	Reset
4:0	R	UART_RECEIVE_FIFO_LEVEL	0x0
		Receive FIFO Level.	
		This is indicates the number of data entries in the receive FIFO.	

Table 419: UART2_SRR_REG (0x50001188)

Bit	Mode	Symbol/Description	Reset
15:3	-	-	0x0

Bit	Mode	Symbol/Description	Reset
		Reserved	
2	W	UART_XFR	0x0
		XMIT FIFO Reset.	
		This is a shadow register for the XMIT FIFO Reset bit (FCR[2]). This can be used to remove the burden on software having to store previously written FCR values (which are pretty static) just to reset the transmit FIFO. This resets the control portion of the transmit FIFO and treats the FIFO as empty. Note that this bit is "self-clearing". It is not necessary to clear this bit.	
1	W	UART_RFR	0x0
		RCVR FIFO Reset.	
		This is a shadow register for the RCVR FIFO Reset bit (FCR[1]). This can be used to remove the burden on software having to store previously written FCR values (which are pretty static) just to reset the receive FIFO. This resets the control portion of the receive FIFO and treats the FIFO as empty.	
		Note that this bit is "self-clearing". It is not necessary to clear this bit.	
0	W	UART_UR	0x0
		UART Reset. This asynchronously resets the UART Ctrl and synchronously removes the reset assertion. For a two clock implementation both pclk and sclk domains are reset.	

Table 420: UART2_SBCR_REG (0x50001190)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R/W	UART_SHADOW_BREAK_CONTROL	0x0
		Shadow Break Control Bit.	
		This is a shadow register for the Break bit (LCR[6]), this can be used to remove the burden of having to perform a read modify write on the LCR. This is used to cause a break condition to be transmitted to the receiving device.	
		If set to one the serial output is forced to the spacing (logic 0) state. When not in Loopback Mode, as determined by MCR[4], the sout line is forced low until the Break bit is cleared.	
		If SIR_MODE active (MCR[6] = 1) the sir_out_n line is continuously pulsed. When in Loopback Mode, the break condition is internally looped back to the receiver.	

Table 421: UART2_SDMAM_REG (0x50001194)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R/W	UART_SHADOW_DMA_MODE	0x0
		Shadow DMA Mode. This is a shadow register for the DMA mode bit (FCR[3]). This can be used to remove the burden of having to store the previously written value to the FCR in memory and having to mask this value so that only the DMA Mode bit gets updated. This determines the DMA signalling mode used for the dma_tx_req_n and dma_rx_req_n output signals. 0 = Mode 0 1 = Mode 1	

Table 422: UART2_SFE_REG (0x50001198)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	0 R/W UART_SHADOW_FIFO_ENABLE		0x0
		Shadow FIFO Enable.	
		This is a shadow register for the FIFO enable bit (FCR[0]). This can be used to remove the burden of having to store the previously written value to the FCR in memory and having to mask this value so that only the FIFO enable bit gets updated. This enables/disables the transmit (XMIT) and receive (RCVR) FIFOs. If this bit is set to zero (disabled) after being enabled then both the XMIT and RCVR controller portion of FIFOs are reset.	

Table 423: UART2_SRT_REG (0x5000119C)

Bit	Mode	Symbol/Description	Reset
15:2	-	-	0x0
		Reserved	
1:0	R/W	UART_SHADOW_RCVR_TRIGGER	0x0
		Shadow RCVR Trigger.	
remove the burden of havin		This is a shadow register for the RCVR trigger bits (FCR[7:6]). This can be used to remove the burden of having to store the previously written value to the FCR in memory and having to mask this value so that only the RCVR trigger bit gets updated.	
	This is used to select the trigger level in the receiver FIFO at which the Receiv Data Available Interrupt is generated. It also determines when the dma_rx_req signal is asserted when DMA Mode (FCR[3]) = 1. The following trigger levels a supported:		
		00 = 1 character in the FIFO	
		01 = FIFO ¼ full	
		10 = FIFO ½ full	
		11 = FIFO 2 less than full	

Table 424: UART2_STET_REG (0x500011A0)

Bit	Mode	Symbol/Description	Reset
15:2	-		0x0
		Reserved	
1:0	R/W	UART_SHADOW_TX_EMPTY_TRIGGER	0x0
		Shadow TX Empty Trigger.	
		This is a shadow register for the TX empty trigger bits (FCR[5:4]). This can be used to remove the burden of having to store the previously written value to the FCR in memory and having to mask this value so that only the TX empty trigger bit gets updated.	
		This is used to select the empty threshold level at which the THRE Interrupts are generated when the mode is active. The following trigger levels are supported:	
		00 = FIFO empty	
		01 = 2 characters in the FIFO	
		10 = FIFO ¼ full	

Bit	Mode	Symbol/Description	Reset
		11 = FIFO ½ full	

Table 425: UART2_HTX_REG (0x500011A4)

Bit	Mode	Symbol/Description	Reset
15:1	-	-	0x0
		Reserved	
0	R/W	UART_HALT_TX	0x0
		This register is used to halt transmissions for testing, so that the transmit FIFO can be filled by the master when FIFOs are implemented and enabled.	
	0 = Halt TX disabled		
		1 = Halt TX enabled	
		Note, if FIFOs are implemented and not enabled, the setting of the halt TX register has no effect on operation.	

Table 426: UART2_DMASA_REG (0x500011A8)

Bit	Mode	Symbol/Description	
0 W		DMASA	0x0
	This register is used to perform DMA software acknowledge if a transfer needs to be terminated due to an error condition. For example, if the DMA disables the channel, then the DW_apb_uart should clear its request. This causes the TX request, TX single, RX request, and RX single signals to deassert. Note that this bit is "self-clearing" and it is not necessary to clear this bit.		

Table 427: UART2_DLF_REG (0x500011C0)

Bit	Mode	Symbol/Description	
3:0	R/W	UART_DLF	0x0
		The fractional value is added to integer value set by DLH, DLL. Fractional value is equal UART_DLF/16.	

Table 428: UART2_UCV_REG (0x500011F8)

Bit	Mode	Symbol/Description	Reset
15:0	R	UCV	0x352A
		Component Version	

Table 429: UART2_UCV_HIGH_REG (0x500011FA)

Bit	Mode	Symbol/Description	
15:0	R	UCV	0x3331
		Component Version	

Table 430: UART2_CTR_REG (0x500011FC)

Bit	Mode	Symbol/Description	
15:0	R	CTR	0x110
		Component Type Register	

Table 431: UART2_CTR_HIGH_REG (0x500011FE)

Bit	Mode	Symbol/Description	Reset
15:0	R	CTR	0x4457
		Component Type Register	

32.19 Chip Version Registers

Table 432: Register map Version

Address	Register	Description
0x50003200	CHIP_ID1_REG	Chip identification register 1.
0x50003204	CHIP_ID2_REG	Chip identification register 2.
0x50003208	CHIP_ID3_REG	Chip identification register 3.
0x5000320c	CHIP_ID4_REG	Chip identification register 4.

Table 433: CHIP_ID1_REG (0x50003200)

Bit	Mode	Symbol/Description	Reset
7:0	R	CHIP_ID1	0x32
		First character of device type "2632" in ASCII.	

Table 434: CHIP_ID2_REG (0x50003204)

Bit	Mode	Symbol/Description	Reset
7:0	R	CHIP_ID2	0x36
		Second character of device type "2632" in ASCII.	

Table 435: CHIP_ID3_REG (0x50003208)

Bit	Mode	Symbol/Description	Reset
7:0	R	CHIP_ID3	0x33
		Third character of device type "2632" in ASCII.	

Table 436: CHIP_ID4_REG (0x5000320C)

Bit	Mode	Symbol/Description	Reset
7:0	R	CHIP_ID4	0x32
		Fourth character of device type "2632" in ASCII.	

32.20 Wake-Up Registers

Table 437: Register map WKUP

Address	Register	Description
0x50000100	WKUP_CTRL_REG	Control register for the wakeup counter
0x50000102	WKUP_COMPARE_REG	Number of events before wakeup interrupt

Address	Register	Description
0x50000104	WKUP_IRQ_STATUS_R EG	Reset wakeup interrupt
0x50000106	WKUP_COUNTER_REG	Actual number of events of the wakeup counter
0x50000108	WKUP_SELECT_GPIO_ REG	Select which inputs from P0 port can trigger wkup counter
0x5000010a	WKUP2_SELECT_GPIO_ REG	Select which inputs from P1 port can trigger wkup counter
0x5000010c	WKUP_POL_GPIO_REG	Select the sensitivity polarity for each P0 input
0x5000010e	WKUP2_POL_GPIO_RE G	Select the sensitivity polarity for each P1 input

Table 438: WKUP_CTRL_REG (0x50000100)

Bit	Mode	Symbol/Description	Reset
8	R/W	WKUP2_ENABLE_IRQ	0x0
		0 = No interrupt will be generated	
		1 = If the event counter2 reaches the value set by WKUP_COMPARE_REG an IRQ will be generated	
7	R/W	WKUP_ENABLE_IRQ	0x0
		0 = No interrupt will be generated	
		1 = If the event counter reaches the value set by WKUP_COMPARE_REG an IRQ will be generated	
6	R/W	WKUP_SFT_KEYHIT	0x0
		0 = No effect	
		1 = Emulate key hit. The event counter and counter2 will increment by 1 (after debouncing if enabled). First make this bit 0 before any new key hit can be sensed.	
5:0	R/W	WKUP_DEB_VALUE	0x0
		Keyboard debounce time ($N*1$ ms with $N = 1$ to 63).	
		0x0: no debouncing	
		0x1 to 0x3F: 1 ms to 63 ms debounce time	

Table 439: WKUP_COMPARE_REG (0x50000102)

Bit	Mode	Symbol/Description	Reset
7:0	R/W	WKUP_COMPARE	0x0
		Defines the number of events -1 that have to be counted before the wake-up interrupt will be given. value 0 means one event.	

Table 440: WKUP_IRQ_STATUS_REG (0x50000104)

Bit	Mode	Symbol/Description	Reset
3	R0/W	WKUP2_CNTR_RST	0x0
		Writing 1 will reset the event2 counter	
2	R0/W	WKUP_CNTR_RST	0x0
		Writing 1 will reset the event counter	
1	R/W	WKUP2_IRQ_STATUS	0x0
		Gives 1 when there is a wkup2 pending IRQ. Writing 1 will reset the interrupt.	

Bit	Mode	Symbol/Description	Reset
0	R/W	WKUP_IRQ_STATUS	0x0
		Gives 1 when there is a wkup pending IRQ. Writing 1 will reset the interrupt.	

Table 441: WKUP_COUNTER_REG (0x50000106)

Bit	Mode	Symbol/Description	Reset
15:8	R	EVENT2_VALUE	0x0
		This value represents the number of events that have been counted so far. It will be reset by writting to the WKUP_CNTR_RST bit field of the WKUP_IRQ_STATUS_REG	
7:0	R	EVENT_VALUE	0x0
		This value represents the number of events that have been counted so far. It will be reset by writting to the WKUP_CNTR_RST bit field of the WKUP_IRQ_STATUS_REG.	

Table 442: WKUP_SELECT_GPIO_REG (0x50000108)

Bit	Mode	Symbol/Description	Reset
11:0	R/W	WKUP_SELECT_GPIO	0x0
		0 = Input P0x is not enabled for wake-up event counter 1 = Input P0x is enabled for wake-up event counter	

Table 443: WKUP2_SELECT_GPIO_REG (0x5000010A)

Bit	Mode	Symbol/Description	
11:0	R/W	WKUP2_SELECT_GPIO	0x0
0 = Input P0x is not enabled for wake-up event counter 1 = Input P0x is enabled for wake-up event counter			

Table 444: WKUP_POL_GPIO_REG (0x5000010C)

Bit	Mode	Symbol/Description	
11:0	R/W	WKUP_POL_GPIO	
	0 = The enabled input P0x increments the event counter if that input goes high 1 = The enabled input P0x increments the event counter if that input goes low		

Table 445: WKUP2_POL_GPIO_REG (0x5000010E)

Bit	Mode	Symbol/Description	
11:0	R/W	WKUP2_POL_GPIO	0x0
		0 = The enabled input P0x increments the event2 counter if that input goes high 1 = The enabled input P0x increments the event2 counter if that input goes low	

32.21 Watchdog Registers

Table 446: Register map WDOG

Address	Register	Description
0x50003100	WATCHDOG_REG	Watchdog timer register

Address	Register	Description
0x50003102	WATCHDOG_CTRL_RE G	Watchdog control register

Table 447: WATCHDOG_REG (0x50003100)

Bit	Mode	Symbol/Description		
15:9	R0/W	WDOG_WEN		
		0000.000 = Write enable for Watchdog timer Else Write disable. This filter prevents unintentional presetting the watchdog with a software run-away.		
8	R/W	WDOG_VAL_NEG	0x0	
		0 = Watchdog timer value is positive. 1 = Watchdog timer value is negative.		
7:0	R/W	WDOG_VAL	0xFF	
		Write: Watchdog timer reload value. Note that all bits 15-9 must be 0 to reload this register. Read: Actual Watchdog timer value. Decremented by 1 every 10.24 ms. Bit 8 indicates a negative counter value. 2, 1, 0, 1FF ₁₆ , 1FE ₁₆ , and so forth. An NMI or WDOG (SYS) reset is generated under the following conditions: If WATCHDOG_CTRL_REG[NMI_RST] = 0 then If WDOG_VAL = 0 -> NMI (Non Maskable Interrupt) if WDOG_VAL = 1F0 ₁₆ -> WDOG reset -> reload FF ₁₆ If WATCHDOG_CTRL_REG[NMI_RST] = 1 then if WDOG_VAL <= 0 -> WDOG reset -> reload FF ₁₆		

Table 448: WATCHDOG_CTRL_REG (0x50003102)

Bit	Mode	Symbol/Description	Reset
15:2	-	-	0x0
		Reserved	
1	R/W	-	0x0
		Reserved	
0	R/W	NMI_RST	0x0
		0 = Watchdog timer generates NMI at value 0, and WDOG (SYS) reset at <=-16. Timer can be frozen/resumed using SET_FREEZE_REG[FRZ_WDOG]/RESET_FREEZE_REG[FRZ_WDOG].	
		1 = Watchdog timer generates a WDOG (SYS) reset at value 0 and can not be frozen by software.Note that this bit can only be set to 1 by software and only be reset with a WDOG (SYS) reset or software reset.	
		The watchdog is always frozen when the Cortex-M0 is halted in DEBUG state.	

33. Ordering Information

Table 449: Ordering Information (Samples)

Part Number	Package	Size (mm)	Shipment Form	Pack Quantity
DA14531-00000FX2	FCGQFN24	2.2 × 3.0	Reel	100/1000
DA14531-00000OG2	WLCSP17	1.694 × 2.032	Reel	100/1000
DA14531-01000FX2	FCGQFN24	2.2 × 3.0	Reel	100/1000
DA14531-01000OG2	WLCSP17	1.694 × 2.032	Reel	100/1000

Table 450: Ordering Information (Production)

Part Number	Package	Size (mm)	Shipment Form	Pack Quantity
DA14531-00000FX2	FCGQFN24	2.2 × 3.0	Reel	4000
DA14531-00000OG2	WLCSP17	1.694 × 2.032	Reel	4000
DA14531-01000FX2	FCGQFN24	2.2 × 3.0	Reel	4000
DA14531-01000OG2	WLCSP17	1.694 × 2.032	Reel	4000

Part Number Legend:

DA14531-RRXXXYYZ

RR: chip revision number XXX: variant (000: No Flash)

YY: package code (FX: FCGQFN24, OG: WLCSP17)

Z: packing method (1: Tray, 2: Reel, A: Mini-Reel)

34. Package Information

34.1 Moisture Sensitivity Level (MSL)

The MSL is an indicator for the maximum allowable time period (floor life time) in which a moisture sensitive plastic device, once removed from the dry bag, can be exposed to an environment with a maximum temperature of 30°C and a maximum relative humidity of 60% relative humidity (RH.) before the solder reflow process.

WLCSP packages are qualified for MSL 1.

FCGQFN packages are qualified for MSL 1.

Table 451: MSL Classification

MSL Level	Floor Lifetime	Conditions
MSL 4	72 hours	30°C/60% RH
MSL 3	168 hours	30°C/60% RH
MSL 2A	4 weeks	30°C/60% RH
MSL 2	1 year	30°C/60% RH
MSL 1	Unlimited	30°C/85% RH

34.2 WLCSP Handling

Manual handling of WLCSP packages should be reduced to the absolute minimum. In cases where it is still necessary, a vacuum pick-up tool should be used. In extreme cases plastic tweezers could be used, but metal tweezers are not acceptable, since contact may easily damage the silicon chip.

Removal will cause damage to the solder balls and therefore a removed sample cannot be reused.

The WLCSP package has been coated to reduce exposure to ambient light, however WLCSP packages can remain sensitive to visible and infrared light. It is recommended to take precautions to properly shield the chip in the final product.

34.3 Soldering Information

Refer to the JEDEC standard J-STD-020 for relevant soldering information. This document can be downloaded from http://www.jedec.org.

34.4 Package Outline Drawings




Figure 85. WLCSP17 package outline drawing




Figure 86. FCGQFN24 package outline drawing

35. Revision History

Revision	Date	Description
3.8	July 10, 2025	Updated POD (Figure 86).
3.7	Apr 28, 2025	Converted into Renesas template.
3.6	Sep 26, 2022	Datasheet status: Final. Product status: Production.

Changelog:

- Added DA14531-01 variant (order codes, variant description)
- Fixed Figure 21 in v3.5
- Updated Table 31 in v3.5 Wake up from column in extended sleep
- Fixed typos in Section 4.2.3.2, the Extended Sleep and Deep Sleep Modes subsection

Changelog:

Changed VBAT HIGH supplies operating condition MAX value to 3.6 V (from 3.3 V)

3.4	Aug 30, 2021	Datasheet status: Final. Product status: Production
-----	--------------	---

Changelog:

- Updated Section 11.3 OTP Controller Programming, OTPC_MODE_REG[OTPC_MODE_MODE]=0x1 for STBY mode
- Updated Absolut Maximum Ratings table, Vesp_HBM_FCGQFN24 is reduced to 2.5 kV for RFIOp and RFIOm pins only

3.3	Mar 9, 2021	Datasheet status: Final. Product status: Production
-----	-------------	---

Changelog:

- Updated OTP programming range in Recommended Operating Conditions
- Removed duplicated register names in "Reset Signals and Registers" table
- Removed minimum 1.1 V for non OTP operation from front page
- Removed false link in OTP controller chapter

3.2	Oct 9, 2020	Datasheet status: Final. Product status: Production
-----	-------------	---

Changelog:

- Temperature Sensor specification parameter updated
- I2C Chapter: Features updated

-	•	
3.1	July 9, 2020	Datasheet status: Final. Product status: Production

Changelog:

- WLCSP17 and FCGQFN24 Package Outline Diagram updated
- V_{BAT_X}, GPADC, Temperature Sensor and XTAL32K specification parameters updated
- SPI Chapter: Features updated
- Buck, Boost and Bypass PMU figures updated

3.0 Mar 12, 2020 Datasheet status: Final.	3.0
---	-----

Changelog:

- Various updates in figures and text
- Electrical characteristics updates

2.1 Oct 17, 2019	Datasheet status: Preliminary.
------------------	--------------------------------

Changelog:

- Product status update and Datasheet status update
- VDD_Clamp recommended setting across temperature added

-	2.0 Oct 13, 2019 Datasheet status: Preliminary.	
---	---	--

Changelog:

Specifications

Revision	Date	Description		
1.5	June 3, 2019	Datasheet status: Target		
Changelog:				
1	 Ordering Information (Production): Pack Quantity Complies with Bluetooth LE 5.1 			
1.4	June 3, 2019	Datasheet status: Target		
PMU ProgrammTemperature SPMU: Buck, BoRCX programm	 BooterROM Sequence PMU Programming Temperature Sensor: routine for TS reading PMU: Buck, Boost, By-pass block diagram updated: SWs added, LDO_LOW_RET renamed to LDO_LOW RCX programming 			
1.3	Jan 25, 2019	Datasheet status: Target		
Changelog: Various Updates				
1.2	Oct 2, 2018	Datasheet status: Target		
Changelog: FCGQFN24 Package Outline updated				
1.1	Aug 30, 2018	Datasheet status: Target		

RoHS Compliance

June 29, 2018

1.0

Renesas Electronics' suppliers certify that its products are in compliance with the requirements of Directive 2011/65/EU of the European Parliament on the restriction of the use of certain hazardous substances in electrical and electronic equipment. RoHS certificates from our suppliers are available on request.

Datasheet status: Target

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01 Jan 2024)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu Koto-ku, Tokyo 135-0061, Japan www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us

© 2025 Renesas Electronics Corporation. All rights reserved.