

ISL70419SEH

Neutron Testing

TR038

Rev 0.00

October 12, 2016

Introduction

This report summarizes results of 1MeV equivalent neutron testing of the [ISL70419SEH](#) quad operational amplifier. The test was conducted in order to determine the sensitivity of the part to displacement damage (DD) caused by neutron or proton environments. Neutron fluences ranged from $2 \times 10^{12} \text{ n/cm}^2$ to $1 \times 10^{14} \text{ n/cm}^2$. This project was carried out in collaboration with Boeing (El Segundo, CA), whose support is gratefully acknowledged.

Related Literature

- For a full list of related documents please visit our website
 - [ISL70419SEH](#) product page

Part Description

The ISL70419SEH is a quad operational amplifier featuring a competitive combination of low noise vs power consumption. Low offset voltage, low input bias current, and low temperature drift makes the ISL70419SEH a good choice for applications requiring both high DC accuracy and AC performance. The combination of precision, low noise, low power, and a small footprint provides the user with outstanding value and flexibility relative to competitive parts. Applications include precision active filters, power supply controls, and industrial controls. The ISL70419SEH is offered in a 14 Ld hermetic ceramic flatpack. The device uses an industry standard pin configuration and operates across the extended temperature range from -55°C to $+125^\circ\text{C}$.

Specifications for radiation hardened QML devices are controlled by the Defense Logistics Agency Land and Maritime (DLA).

The ISL70419SRH is acceptance tested on a wafer-by-wafer basis to a total dose level of 300krad(Si) at high dose rate (50-300rad(Si)/s). The ISL70419SEH is acceptance tested to a total dose level of 300krad(Si) at high dose rate (50-300rad(Si)/s) and to 50krad(Si) at low dose rate ($<0.01\text{rad(Si)/s}$). The SMD rates both parts at 300krad(Si) at high dose rate (50-300rad(Si)/s) and at 50krad(Si) at low dose rate ($<0.01\text{rad(Si)/s}$).

TABLE 1. ISL70419SEH PIN ASSIGNMENTS

TERMINAL NUMBER	TERMINAL SYMBOL	TERMINAL NUMBER	TERMINAL SYMBOL
1	OUT_A	8	OUT_C
2	-IN_A	9	-IN_C
3	+IN_A	10	+IN_C
4	V+	11	V-
5	+IN_B	12	+IN_D
6	-IN_B	13	-IN_D
7	OUT_B	14	OUT_D

Test Description

Irradiation Facilities

1MeV equivalent neutron irradiation was performed at the White Sands Missile Range fast burst reactor (White Sands Missile Range, NM 88002). Dosimetry data can be furnished upon request. Parts were tested in an unbiased configuration with all leads shorted together in general accordance with TM1017 of MIL-STD-883. Samples exposed at the higher neutron levels required considerable 'cooldown' time before being shipped back to Intersil for electrical testing.

Test Fixturing

No formal irradiation test fixturing was involved. These DD tests are informally termed 'bag tests' as the samples are irradiated in an electrically inactive state with all leads shorted together.

Characterization Equipment and Procedures

Electrical testing was performed before and after irradiation using the Intersil Palm Bay, FL Automated Test Equipment (ATE). All electrical testing was performed at room temperature.

Experimental Matrix

The experimental matrix consisted of five samples irradiated at $2 \times 10^{12} \text{ n/cm}^2$, five irradiated at $1 \times 10^{13} \text{ n/cm}^2$, five irradiated at $3 \times 10^{13} \text{ n/cm}^2$, and five irradiated at $1 \times 10^{14} \text{ n/cm}^2$. Five control units were used. ISL70419SEHF/PROTO samples were drawn from fabrication lot X0H6DACA and were packaged in the standard 14 Ld ceramic production package. Samples were screened to the SMD limits over temperature before the start of neutron testing.

Results

The ISL70419SEH neutron testing results are reported in the balance of this report. It should be carefully realized when interpreting the data that each neutron irradiation was performed on a different five-unit sample; this is *not* total dose testing, where the damage is cumulative over a number of downpoints.

Attributes Data

TABLE 2. ISL70419SEH ATTRIBUTES DATA

PART	SERIAL	SAMPLE SIZE	FLUENCE, (n/cm ²)	PASS (Note 1)	FAIL	NOTES
ISL70419SEH	1-5	5	2x10 ¹²	5	0	All passed
ISL70419SEH	6-10	5	1x10 ¹³	5	0	All passed
ISL70419SEH	11-15	5	3x10 ¹³	5	0	All passed
ISL70419SEH	16-20	5	1x10 ¹⁴	0	5	All failed open-loop gain but were functional

NOTE:

1. "Pass" indicates a sample that passes all SMD limits.

Variables Data

The plots in [Figures 1](#) through [29](#) show data plots for key parameters before and after irradiation to each level. The reported parameters and their datasheet limits are shown in ["Appendix" on page 17](#). This appendix contains a considerable number of figures, but we chose to go into some detail for the critical input parameters, which are of great interest in any operational amplifier test. We plotted these channel-by-channel to determine if any channel sensitivity exists. Other parameters were plotted as averages of all four channels, an approach which does not work for critical parameters such as input offset voltage, which may show significant, uncorrelated variation. For these cases, we plotted each channel individually.

The plots show the population median of each parameter as a function of neutron irradiation as well as the population minimum and maximum. We chose to plot the median because of the small sample sizes (five per cell) involved. We also show the applicable post-total dose electrical limits as taken from the SMD. It should be noted that these limits are provided for *guidance only* as the ISL70419SEH is not specified or guaranteed for the neutron environment. Intersil does not design, qualify, or guarantee its parts for the DD environment, but has performed limited collaborative neutron testing for customer guidance.

Variables Data Plots




FIGURE 1. ISL70419SEH positive and negative supply current, sum of all four channels, as a function of 1MeV equivalent neutron irradiation at 2x10¹²n/cm², 1x10¹³n/cm², 3x10¹³n/cm², and 1x10¹⁴n/cm². The plot shows the population median, minimum, and maximum at each downpoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are 2.72mA maximum (ICC) and -2.72mA maximum (IEE).

Variables Data Plots (Continued)




FIGURE 2. ISL70419SEH input offset voltage, Channel A, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are $-110 \mu\text{V}$ to $110 \mu\text{V}$.




FIGURE 3. ISL70419SEH input offset voltage, Channel B, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are $-110 \mu\text{V}$ to $110 \mu\text{V}$.

Variables Data Plots (Continued)




FIGURE 4. ISL70419SEH input offset voltage, Channel C, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each downpoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are $-110 \mu\text{V}$ to $110 \mu\text{V}$.




FIGURE 5. ISL70419SEH input offset voltage, Channel D, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each downpoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are $-110 \mu\text{V}$ to $110 \mu\text{V}$.

Variables Data Plots (Continued)




FIGURE 6. ISL70419SEH positive input bias current, Channel A, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each downpoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -15nA to 15nA.




FIGURE 7. ISL70419SEH positive input bias current, Channel B, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each downpoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -15nA to 15nA.

Variables Data Plots (Continued)




FIGURE 8. ISL70419SEH positive input bias current, Channel C, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -15nA to 15nA.




FIGURE 9. ISL70419SEH positive input bias current, Channel D, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -15nA to 15nA.

Variables Data Plots (Continued)




FIGURE 10. ISL70419SEH negative input bias current, Channel A, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each downpoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -15nA to 15nA.




FIGURE 11. ISL70419SEH negative input bias current, Channel B, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each downpoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -15nA to 15nA.

Variables Data Plots (Continued)




FIGURE 12. ISL70419SEH negative input bias current, Channel C, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -15nA to 15nA.




FIGURE 13. ISL70419SEH negative input bias current, Channel D, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -15nA to 15nA.

Variables Data Plots (Continued)




FIGURE 14. ISL70419SEH input offset current, Channel A, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each downpoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -10nA to 10nA.




FIGURE 15. ISL70419SEH input offset current, Channel B, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each downpoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -10nA to 10nA.

Variables Data Plots (Continued)




FIGURE 16. ISL70419SEH input offset current, Channel C, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each dosepoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -10nA to 10nA.




FIGURE 17. ISL70419SEH input offset current, Channel D, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each dosepoint. Sample size for each cell was five. The post-total dose irradiation SMD limits are -10nA to 10nA.

Variables Data Plots (Continued)




FIGURE 18. ISL70419SEH output HIGH voltage, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is 13.2V minimum.




FIGURE 19. ISL70419SEH output LOW voltage, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is -13.2V maximum.

Variables Data Plots (Continued)




FIGURE 20. ISL70419SEH positive open-loop gain, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is 129.5dB minimum.




FIGURE 21. ISL70419SEH negative open-loop gain, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is 129.5dB minimum.

Variables Data Plots (Continued)




FIGURE 22. ISL70419SEH positive power supply rejection ratio, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each downpoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is 120dB minimum.




FIGURE 23. ISL70419SEH negative power supply rejection ratio, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each downpoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is 120dB minimum.

Variables Data Plots (Continued)




FIGURE 24. ISL70419SEH positive common-mode rejection ratio, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is 120dB minimum.




FIGURE 25. ISL70419SEH negative common-mode rejection ratio, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is 120dB minimum.

Variables Data Plots (Continued)




FIGURE 26. ISL70419SEH positive slew rate, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} n/cm^2$, $1 \times 10^{13} n/cm^2$, $3 \times 10^{13} n/cm^2$, and $1 \times 10^{14} n/cm^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is 0.2V/ μs minimum.




FIGURE 27. ISL70419SEH negative slew rate, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} n/cm^2$, $1 \times 10^{13} n/cm^2$, $3 \times 10^{13} n/cm^2$, and $1 \times 10^{14} n/cm^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is 0.2V/ μs minimum.

Variables Data Plots (Continued)




FIGURE 28. ISL70419SEH rise time, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is 625ns maximum.




FIGURE 29. ISL70419SEH fall time, average of all four channels, as a function of 1MeV equivalent neutron irradiation at $2 \times 10^{12} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, $3 \times 10^{13} \text{ n/cm}^2$, and $1 \times 10^{14} \text{ n/cm}^2$. The plot shows the population median, minimum, and maximum at each datapoint. Sample size for each cell was five. The post-total dose irradiation SMD limit is 700ns maximum.

Conclusion

This report summarizes results of 1MeV equivalent neutron testing of the ISL70419SEH quad operational amplifier. The test was conducted in order to determine the sensitivity of the part to displacement damage (DD) caused by neutron or proton environments in space. Neutron fluences ranged from $2 \times 10^{12} \text{ n/cm}^2$ to $1 \times 10^{14} \text{ n/cm}^2$. This test was carried out as part of a collaborative project with Boeing (El Segundo, CA), whose support is gratefully acknowledged.

In the figures, we plotted critical input parameters channel-by-channel to determine if any channel sensitivity exists. Other parameters were plotted as averages of all four channels.

The $2 \times 10^{11} \text{ n/cm}^2$, $1 \times 10^{13} \text{ n/cm}^2$, and $3 \times 10^{13} \text{ n/cm}^2$ samples met all SMD and datasheet specifications (Bin 1) after irradiation. All $1 \times 10^{14} \text{ n/cm}^2$ samples failed the open-loop gain parameter after irradiation, but remained functional.

Appendix

Reported Parameters

Reported parameters are shown below. The limits are taken from the applicable SMD and are provided for guidance only as the part is not designed or guaranteed for the neutron environment.

TABLE 3. REPORTED PARAMETERS

FIGURE	PARAMETER	LIMIT, LOW	LIMIT, HIGH	UNITS	NOTES
1	Supply current, positive	-	2.72	mA	Sum of four channels
	Supply current, negative	-2.72	-	mA	Sum of four channels
2	Input offset voltage	-110	110	μV	Channel A
3	Input offset voltage	-110	110	μV	Channel B
4	Input offset voltage	-110	110	μV	Channel C
5	Input offset voltage	-110	110	μV	Channel D
6	Positive input bias current	-15	15	nA	Channel A
7	Positive input bias current	-15	15	nA	Channel B
8	Positive input bias current	-15	15	nA	Channel C
9	Positive input bias current	-15	15	nA	Channel D
10	Negative input bias current	-15	15	nA	Channel A
11	Negative input bias current	-15	15	nA	Channel B
12	Negative input bias current	-15	15	nA	Channel C
13	Negative input bias current	-15	15	nA	Channel D
14	Input offset current	-10	10	nA	Channel A
15	Input offset current	-10	10	nA	Channel B
16	Input offset current	-10	10	nA	Channel C
17	Input offset current	-10	10	nA	Channel D
18	Output HIGH voltage	-	13.2	V	Average of four channels
19	Output LOW voltage	-13.2	-	V	Average of four channels
20	Positive open-loop gain	129.5	-	dB	Average of four channels
21	Negative open-loop gain	129.5	-	dB	Average of four channels
22	Positive power supply rejection ratio	120	-	dB	Average of four channels
23	Negative power supply rejection ratio	120	-	dB	Average of four channels
24	Positive common mode rejection ratio	120	-	dB	Average of four channels
25	Negative common mode rejection ratio	120	-	dB	Average of four channels
26	Positive slew rate	0.2	-	V/ μs	Average of four channels
27	Negative slew rate	0.2	-	V/ μs	Average of four channels
28	Rise time	-	625	ns	Average of four channels
29	Fall time	-	700	ns	Average of four channels

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
 4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
 6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
 7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
 9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
 11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.
1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited
9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH
Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852-2886-9022

Renesas Electronics Taiwan Co., Ltd.
13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

Renesas Electronics Singapore Pte. Ltd.
80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.
17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338