# Old Company Name in Catalogs and Other Documents

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <a href="http://www.renesas.com">http://www.renesas.com</a>

April 1<sup>st</sup>, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<a href="http://www.renesas.com">http://www.renesas.com</a>)

Send any inquiries to http://www.renesas.com/inquiry.



### Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights
  of third parties by or arising from the use of Renesas Electronics products or technical information described in this document.
  No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights
  of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



# PRFI IMINARY

Notice: This is not a final specification. Some parametric limits are subject to change.

R8C/34E Group, R8C/34F Group, R8C/34G Group, R8C/34H Group RENESAS MCU

REJ03B0246-0010 Rev.0.10 Apr 17, 2008

### 1. Overview

### 1.1 Features

The R8C/34E Group, R8C/34F Group, R8C/34G Group, and R8C/34H Group of single-chip MCUs incorporate the R8C/Tiny Series CPU core, employing sophisticated instructions for a high level of efficiency. With 1 Mbyte of address space, and it is capable of executing instructions at high speed. In addition, the CPU core boasts a multiplier for high-speed operation processing.

Power consumption is low, and the supported operating modes allow additional power control. These MCUs are designed to maximize EMI/EMS performance.

Integration of many peripheral functions, including multifunction timer and serial interface, reduces the number of system components.

The R8C/34E Group and R8C/34F Group have a single channel CAN module and are suitable for LAN systems in vehicles and for FA.

The R8C/34G Group and the R8C/34H Group do not have CAN modules.

The R8C/34E Group and the R8C/34G Group have data flash (1 KB  $\times$  4 blocks) with the background operation (BGO) function.

## 1.1.1 Applications

Automobiles and others

## 1.1.2 Specifications

Tables 1.1 and 1.2 outline the Specifications for R8C/34E Group, tables 1.3 and 1.4 outline the Specifications for R8C/34F Group, tables 1.5 and 1.6 outline the Specifications for R8C/34G Group, tables 1.7 and 1.8 outline the Specifications for R8C/34H Group.

Table 1.1 Specifications for R8C/34E Group (1)

Item	Function	Specification			
CPU	Central processing	R8C/Tiny series core			
	unit	Number of fundamental instructions: 89			
		Minimum instruction execution time:			
		50 ns (f(XIN) = 20 MHz, VCC = 2.7 to 5.5 V)			
		Multiplier: 16 bits × 16 bits → 32 bits			
		• Multiply-accumulate instruction: 16 bits × 16 bits + 32 bits → 32 bits			
		Operation mode: Single-chip mode (address space: 1 Mbyte)			
Memory	ROM, RAM, Data flash	Refer to Table 1.9 Product List for R8C/34E Group.			
Power Supply	Voltage detection	Power-on reset			
Voltage Detection	circuit	Voltage detection 3 (detection level of voltage detection 1 selectable)			
I/O Ports	Programmable I/O	Input-only: 1 pin			
	ports	CMOS I/O ports: 43, selectable pull-up resistor			
Clock	Clock generation	3 circuits: XIN clock oscillation circuit (with on-chip feedback resistor),			
	circuits	High-speed on-chip oscillator (with frequency adjustment function),			
		Low-speed on-chip oscillator			
		Oscillation stop detection: XIN clock oscillation stop detection function			
		• Frequency divider circuit: Dividing selectable 1, 2, 4, 8, and 16			
		Low power consumption modes:			
		Standard operating mode (high-speed clock, high-speed on-chip oscillator,			
		low-speed on-chip oscillator), wait mode, stop mode			
Interrupts		Interrupt Vectors: 69			
		• External: 9 sources (INT × 5 , key input × 4)			
		Priority levels: 7 levels			
Watchdog Time	er	• 15 bits × 1 (with prescaler)			
		Reset start selectable			
		Low-speed on-chip oscillator for watchdog timer selectable			
DTC (Data Tra	nsfer Controller)	• 1 channel			
		Activation sources: 31			
		Transfer modes: 2 (normal mode, repeat mode)			
Timer	Timer RA	8 bits (with 8-bit prescaler)			
		Timer mode (period timer), pulse output mode (output level inverted every			
		period), event counter mode, pulse width measurement mode, pulse period			
	Timer RB	measurement mode			
	Hiller RD	8 bits × 1 (with 8-bit prescaler) Timer mode (period timer), programmable waveform generation mode (PWM			
		output), programmable one-shot generation mode, programmable wait one-			
		shot generation mode			
	Timer RC	16 bits × 1 (with 4 capture/compare registers)			
		Timer mode (input capture function, output compare function), PWM mode			
		(output 3 pins), PWM2 mode (PWM output pin)			
	Timer RD	16 bits × 2 (with 4 capture/compare registers) Timer mode (input capture function, output compare function), PWM mode			
		(output 6 pins), reset synchronous PWM mode (output three-phase			
		waveforms (6 pins), sawtooth wave modulation), complementary PWM mode			
		(output three-phase waveforms (6 pins), triangular wave modulation), PWM3			
		mode (PWM output 2 pins with fixed period)			
	Timer RE	8 bits × 1			
		Output compare mode			

Specifications for R8C/34E Group (2) Table 1.2

Item	Function	Specification					
Serial	UART0, 1	Clock synchronous serial I/O/UART × 2 channel					
Interface	UART2	Clock synchronous serial I/O, UART, I <sup>2</sup> C mode (I <sup>2</sup> C-bus), IE mode (IE BUS <sup>(1)</sup> ), multiprocessor communication function					
Synchronous	Serial	1					
Communication	on Unit (SSU)						
LIN Module		Hardware LIN: 1 (timer RA, UART0)					
CAN module		One channel, 16 Mailboxes (conforms to the ISO 11898-1)					
A/D Converte	ſ	10-bit resolution × 12 channels, includes sample and hold function, with sweep mode					
Flash Memory	1	<ul> <li>Programming and erasure voltage: VCC = 2.7 to 5.5 V</li> </ul>					
		Programming and erasure endurance: 10,000 times (data flash)					
		1,000 times (program ROM)					
		Program security: ROM code protect, ID code check					
		Debug functions: On-chip debug, on-board flash rewrite function					
		Background operation (BGO) function (data flash)					
Operating Fre	quency/Supply	f(XIN) = 20 MHz (VCC = 2.7 to 5.5 V)					
Voltage							
Current consu	ımption	TBD (VCC = $5.0 \text{ V}$ , $f(XIN) = 20 \text{ MHz}$ )					
		TBD (VCC = 3.0 V, f(XIN) = 20 MHz)					
Operating Ambient Temperature		-40 to 85°C (J version)					
Darling		-40 to 125°C (K version) (2)					
Package		48-pin LQFP					
		Package code: PLQP0048KB-A (previous code: 48P6Q-A)					

- Notes:
   1. IE BUS is a trademark of NEC Electronics Corporation.
   2. Specify the K version if K version functions are to be used.

Table 1.3	Specifications fo	r R8C/34F Group (1)
Item	Function	Specification
CPU	Central processing	R8C/Tiny series core
	unit	Number of fundamental instructions: 89
		Minimum instruction execution time:
		50 ns (f(XIN) = 20 MHz, VCC = 2.7 to 5.5 V)
		Multiplier: 16 bits × 16 bits → 32 bits
		<ul> <li>Multiply-accumulate instruction: 16 bits × 16 bits + 32 bits → 32 bits</li> </ul>
		Operation mode: Single-chip mode (address space: 1 Mbyte)
Memory	ROM, RAM, Data	Refer to Table 1.10 Product List for R8C/34F Group.
,	flash	·
Power Supply	Voltage detection	Power-on reset
Voltage	circuit	Voltage detection 3 (detection level of voltage detection 1 selectable)
Detection		
I/O Ports	Programmable I/O	Input-only: 1 pin
	ports	CMOS I/O ports: 43, selectable pull-up resistor
Clock	Clock generation	3 circuits: XIN clock oscillation circuit (with on-chip feedback resistor),
	circuits	High-speed on-chip oscillator (with frequency adjustment function),
		Low-speed on-chip oscillator
		Oscillation stop detection: XIN clock oscillation stop detection function
		• Frequency divider circuit: Dividing selectable 1, 2, 4, 8, and 16
		Low power consumption modes:
		Standard operating mode (high-speed clock, high-speed on-chip oscillator,
		low-speed on-chip oscillator), wait mode, stop mode
Interrupts		• Interrupt Vectors: 69
		• External: 9 sources (INT × 5 , key input × 4)
		• Priority levels: 7 levels
Watchdog Tim	er	15 bits × 1 (with prescaler)
		Reset start selectable
		Low-speed on-chip oscillator for watchdog timer selectable
DTC (Data Tra	insfer Controller)	• 1 channel
2.0 (2010		Activation sources: 31
		Transfer modes: 2 (normal mode, repeat mode)
Timer	Timer RA	8 bits (with 8-bit prescaler)
		Timer mode (period timer), pulse output mode (output level inverted every
		period), event counter mode, pulse width measurement mode, pulse period
		measurement mode
	Timer RB	8 bits × 1 (with 8-bit prescaler)
		Timer mode (period timer), programmable waveform generation mode (PWM
		output), programmable one-shot generation mode, programmable wait one-
		shot generation mode
	Timer RC	16 bits × 1 (with 4 capture/compare registers)
		Timer mode (input capture function, output compare function), PWM mode
	T	(output 3 pins), PWM2 mode (PWM output pin)
	Timer RD	16 bits × 2 (with 4 capture/compare registers) Timer mode (input capture function, output compare function), PWM mode
		(output 6 pins), reset synchronous PWM mode (output three-phase
		waveforms (6 pins), sawtooth wave modulation), complementary PWM mode
		(output three-phase waveforms (6 pins), triangular wave modulation), PWM3 mode (PWM output 2 pins with fixed period)
	Timer RE	8 bits × 1
	IIIIlei KE	Output compare mode
	1	Output compare mode

Table 1.4 Specifications for R8C/34F Group (2)

Item	Function	Specification			
Serial	UART0, 1	Clock synchronous serial I/O/UART × 2 channel			
Interface	UART2	Clock synchronous serial I/O, UART, I <sup>2</sup> C mode (I <sup>2</sup> C-bus), IE mode (IE BUS <sup>(1)</sup> ), multiprocessor communication function			
Synchronous S	Serial	1			
Communication	n Unit (SSU)				
LIN Module		Hardware LIN: 1 (timer RA, UART0)			
CAN module		One channel, 16 Mailboxes (conforms to the ISO 11898-1)			
A/D Converter		10-bit resolution × 12 channels, includes sample and hold function, with sweep mode			
Flash Memory		<ul> <li>Programming and erasure voltage: VCC = 2.7 to 5.5 V</li> </ul>			
		Programming and erasure endurance: 100 times (program ROM)			
		Program security: ROM code protect, ID code check			
		Debug functions: On-chip debug, on-board flash rewrite function			
Operating Freq	uency/Supply	f(XIN) = 20 MHz (VCC = 2.7 to 5.5 V)			
Voltage	nntion	TDD (//CC = 5.0 \/ f/VIN\ = 20 MH=\			
Current consumption		TBD (VCC = 5.0 V, f(XIN) = 20 MHz) TBD (VCC = 3.0 V, f(XIN) = 20 MHz)			
Operating Ambient Temperature		-40 to 85°C (J version)			
		-40 to 125°C (K version) (2)			
Package		48-pin LQFP			
		Package code: PLQP0048KB-A (previous code: 48P6Q-A)			

- Notes:

  1. IE BUS is a trademark of NEC Electronics Corporation.

  2. Specify the K version if K version functions are to be used.

Table 1.5 Specifications for R8C/34G Group (1)

Table 1.5	Specifications to	1 K8C/34G Gloup (1)			
Item	Function	Specification			
CPU	Central processing	R8C/Tiny series core			
	unit	Number of fundamental instructions: 89			
		Minimum instruction execution time:			
		50 ns (f(XIN) = 20 MHz, VCC = 2.7 to 5.5 V)			
		Multiplier: 16 bits × 16 bits → 32 bits			
		<ul> <li>Multiply-accumulate instruction: 16 bits × 16 bits + 32 bits → 32 bits</li> </ul>			
		Operation mode: Single-chip mode (address space: 1 Mbyte)			
Memory	ROM, RAM, Data flash	Refer to Table 1.11 Product List for R8C/34G Group.			
Power Supply	Voltage detection	Power-on reset			
Voltage	circuit	Voltage detection 3 (detection level of voltage detection 1 selectable)			
Detection	Circuit	voltage detection 5 (detection level of voltage detection 1 selectable)			
I/O Ports	Programmable I/O	Input-only: 1 pin			
	ports	CMOS I/O ports: 43, selectable pull-up resistor			
Clock	Clock generation	3 circuits: XIN clock oscillation circuit (with on-chip feedback resistor),			
Olook	circuits	High-speed on-chip oscillator (with frequency adjustment function),			
	0000	Low-speed on-chip oscillator			
		Oscillation stop detection: XIN clock oscillation stop detection function			
		Frequency divider circuit: Dividing selectable 1, 2, 4, 8, and 16			
		• Low power consumption modes:			
		Standard operating mode (high-speed clock, high-speed on-chip oscillator,			
		low-speed on-chip oscillator), wait mode, stop mode			
Interrupts		Interrupt Vectors: 69			
interrupts		• External: 9 sources (INT × 5 , key input × 4)			
Watchdog Time	Or.	Priority levels: 7 levels  It bits × 1 (with prescaler)			
Watchdog Till	EI	• Reset start selectable			
DTO (Data Tar		Low-speed on-chip oscillator for watchdog timer selectable			
DIC (Data Tra	nsfer Controller)	• 1 channel			
		Activation sources: 31			
<del>-</del>	T= 54	Transfer modes: 2 (normal mode, repeat mode)			
Timer	Timer RA	8 bits (with 8-bit prescaler)			
		Timer mode (period timer), pulse output mode (output level inverted every			
		period), event counter mode, pulse width measurement mode, pulse period			
	Time on DD	measurement mode			
	Timer RB	8 bits × 1 (with 8-bit prescaler) Timer mode (period timer), programmable waveform generation mode (PWM			
		output), programmable one-shot generation mode, programmable wait one-			
		shot generation mode			
	Timer RC	16 bits × 1 (with 4 capture/compare registers)			
	Tilliel IXC	Timer mode (input capture function, output compare function), PWM mode			
		(output 3 pins), PWM2 mode (PWM output pin)			
	Timer RD	16 bits × 2 (with 4 capture/compare registers)			
		Timer mode (input capture function, output compare function), PWM mode			
		(output 6 pins), reset synchronous PWM mode (output three-phase			
		waveforms (6 pins), sawtooth wave modulation), complementary PWM mode			
		(output three-phase waveforms (6 pins), triangular wave modulation), PWM3			
		mode (PWM output 2 pins with fixed period)			
	Timer RE	8 bits × 1			
		Output compare mode			

Table 1.6 Specifications for R8C/34G Group (2)

Item	Function	Specification			
Serial	UART0, 1	Clock synchronous serial I/O/UART × 2 channel			
Interface	UART2	Clock synchronous serial I/O, UART, I <sup>2</sup> C mode (I <sup>2</sup> C-bus), IE mode (IE BUS <sup>(1)</sup> ), multiprocessor communication function			
Synchronous S	Serial	1			
Communicatio	n Unit (SSU)				
LIN Module		Hardware LIN: 1 (timer RA, UART0)			
A/D Converter		10-bit resolution × 12 channels, includes sample and hold function, with sweep mode			
Flash Memory		Programming and erasure voltage: VCC = 2.7 to 5.5 V			
		Programming and erasure endurance: 10,000 times (data flash)			
		1,000 times (program ROM)			
		Program security: ROM code protect, ID code check			
		Debug functions: On-chip debug, on-board flash rewrite function			
		Background operation (BGO) function (data flash)			
Operating Free	quency/Supply	f(XIN) = 20 MHz (VCC = 2.7 to 5.5 V)			
Voltage					
Current consumption		TBD (VCC = 5.0 V, f(XIN) = 20 MHz) TBD (VCC = 3.0 V, f(XIN) = 20 MHz)			
Operating Ambient Temperature		-40 to 85°C (J version)			
		-40 to 125°C (K version) (2)			
Package		48-pin LQFP			
		Package code: PLQP0048KB-A (previous code: 48P6Q-A)			

- Notes:
   1. IE BUS is a trademark of NEC Electronics Corporation.
   2. Specify the K version if K version functions are to be used.

Table 1.7 Specifications for R8C/34H Group (1)

Item	Function	Specification				
CPU	Central processing	R8C/Tiny series core				
	unit	Number of fundamental instructions: 89				
		Minimum instruction execution time:				
		50 ns (f(XIN) = 20 MHz, VCC = 2.7 to 5.5 V)				
		Multiplier: 16 bits × 16 bits → 32 bits				
		<ul> <li>Multiply-accumulate instruction: 16 bits × 16 bits + 32 bits → 32 bits</li> </ul>				
		Operation mode: Single-chip mode (address space: 1 Mbyte)				
Memory	ROM, RAM, Data flash	Refer to Table 1.12 Product List for R8C/34H Group.				
Power Supply	Voltage detection	Power-on reset				
Voltage Detection	circuit	Voltage detection 3 (detection level of voltage detection 1 selectable)				
I/O Ports	Programmable I/O	Input-only: 1 pin				
	ports	CMOS I/O ports: 43, selectable pull-up resistor				
Clock	Clock generation	3 circuits: XIN clock oscillation circuit (with on-chip feedback resistor),				
	circuits	High-speed on-chip oscillator (with frequency adjustment function), Low-speed on-chip oscillator				
		Oscillation stop detection: XIN clock oscillation stop detection function				
		• Frequency divider circuit: Dividing selectable 1, 2, 4, 8, and 16				
		Low power consumption modes:				
		Standard operating mode (high-speed clock, high-speed on-chip oscillator,				
		low-speed on-chip oscillator), wait mode, stop mode				
Interrupts	l .	Interrupt Vectors: 69				
-		• External: 9 sources (INT × 5 , key input × 4)				
		Priority levels: 7 levels				
Watchdog Tim	er	15 bits × 1 (with prescaler)				
		Reset start selectable				
		Low-speed on-chip oscillator for watchdog timer selectable				
DTC (Data Tra	nsfer Controller)	• 1 channel				
		Activation sources: 31				
		Transfer modes: 2 (normal mode, repeat mode)				
Timer	Timer RA	8 bits (with 8-bit prescaler)				
		Timer mode (period timer), pulse output mode (output level inverted every				
		period), event counter mode, pulse width measurement mode, pulse period				
		measurement mode				
	Timer RB	8 bits × 1 (with 8-bit prescaler)				
		Timer mode (period timer), programmable waveform generation mode (PWM				
		output), programmable one-shot generation mode, programmable wait one-				
	Times DC	shot generation mode				
	Timer RC	16 bits × 1 (with 4 capture/compare registers) Timer mode (input capture function, output compare function), PWM mode				
		(output 3 pins), PWM2 mode (PWM output pin)				
	Timer RD	16 bits × 2 (with 4 capture/compare registers)				
		Timer mode (input capture function, output compare function), PWM mode				
		(output 6 pins), reset synchronous PWM mode (output three-phase				
		waveforms (6 pins), sawtooth wave modulation), complementary PWM mode				
		(output three-phase waveforms (6 pins), triangular wave modulation), PWM3				
		mode (PWM output 2 pins with fixed period)				
	Timer RE	8 bits × 1				
		Output compare mode				

Table 1.8 Specifications for R8C/34H Group (2)

Item	Function	Specification				
Serial	UART0, 1	Clock synchronous serial I/O/UART × 2 channel				
Interface	UART2	Clock synchronous serial I/O, UART, I <sup>2</sup> C mode (I <sup>2</sup> C-bus), IE mode (IE BUS <sup>(1)</sup> ), multiprocessor communication function				
Synchronous S	Serial	1				
Communication	n Unit (SSU)					
LIN Module		Hardware LIN: 1 (timer RA, UART0)				
A/D Converter		10-bit resolution × 12 channels, includes sample and hold function, with sweep mode				
Flash Memory		<ul> <li>Programming and erasure voltage: VCC = 2.7 to 5.5 V</li> </ul>				
		Programming and erasure endurance: 100 times (program ROM)				
		Program security: ROM code protect, ID code check				
		Debug functions: On-chip debug, on-board flash rewrite function				
Operating Fred	quency/Supply	f(XIN) = 20 MHz (VCC = 2.7 to 5.5 V)				
Voltage						
Current consumption		TBD (VCC = 5.0 V, f(XIN) = 20 MHz) TBD (VCC = 3.0 V, f(XIN) = 20 MHz)				
Operating Ambient Temperature		-40 to 85°C (J version)				
		-40 to 125°C (K version) (2)				
Package		48-pin LQFP				
		Package code: PLQP0048KB-A (previous code: 48P6Q-A)				

- Notes:
   1. IE BUS is a trademark of NEC Electronics Corporation.
   2. Specify the K version if K version functions are to be used.

### 1.2 Product List

Table 1.9 lists Product List for R8C/34E Group, Table 1.10 lists Product List for R8C/34F Group, Table 1.11 lists Product List for R8C/34G Group, Table 1.12 lists Product List for R8C/34H Group.

Table 1.9 Product List for R8C/34E Group

Current of Apr. 2008

Part No.	ROM Capacity		RAM	Package Type	Remarks	
Fait No.	Program ROM	Data flash	Capacity	Fackage Type	Remarks	
R5F21346EJFP (D)	32 Kbytes	1 Kbyte × 4	2.5 Kbytes	PLQP0048KB-A	J version	
R5F21347EJFP (D)	48 Kbytes	1 Kbyte × 4	4 Kbytes	PLQP0048KB-A		
R5F21348EJFP (D)	64 Kbytes	1 Kbyte × 4	6 Kbytes	PLQP0048KB-A		
R5F2134AEJFP (P)	96 Kbytes	1 Kbyte × 4	8 Kbytes	PLQP0048KB-A		
R5F2134CEJFP (P)	128 Kbytes	1 Kbyte × 4	10 Kbytes	PLQP0048KB-A		
R5F21346EKFP (D)	32 Kbytes	1 Kbyte × 4	2.5 Kbytes	PLQP0048KB-A	K version	
R5F21347EKFP (D)	48 Kbytes	1 Kbyte × 4	4 Kbytes	PLQP0048KB-A		
R5F21348EKFP (D)	64 Kbytes	1 Kbyte × 4	6 Kbytes	PLQP0048KB-A		
R5F2134AEKFP (P)	96 Kbytes	1 Kbyte × 4	8 Kbytes	PLQP0048KB-A		
R5F2134CEKFP (P)	128 Kbytes	1 Kbyte × 4	10 Kbytes	PLQP0048KB-A		

(D): Under development

(P): Under planning




Figure 1.1 Part Number, Memory Size, and Package of R8C/34E Group

Table 1.10 Product List for R8C/34F Group

### Current of Apr. 2008

Part No.	ROM Capacity Program ROM	RAM Capacity	Package Type	Remarks
R5F21346FJFP (D)	32 Kbytes	2.5 Kbytes	PLQP0048KB-A	J version
R5F21347FJFP (D)	48 Kbytes	4 Kbytes	PLQP0048KB-A	
R5F21348FJFP (D)	64 Kbytes	6 Kbytes	PLQP0048KB-A	
R5F2134AFJFP (P)	96 Kbytes	8 Kbytes	PLQP0048KB-A	
R5F2134CFJFP (P)	128 Kbytes	10 Kbytes	PLQP0048KB-A	
R5F21346FKFP (D)	32 Kbytes	2.5 Kbytes	PLQP0048KB-A	K version
R5F21347FKFP (D)	48 Kbytes	4 Kbytes	PLQP0048KB-A	
R5F21348FKFP (D)	64 Kbytes	6 Kbytes	PLQP0048KB-A	
R5F2134AFKFP (P)	96 Kbytes	8 Kbytes	PLQP0048KB-A	
R5F2134CFKFP (P)	128 Kbytes	10 Kbytes	PLQP0048KB-A	

(D): Under development(P): Under planning




Figure 1.2 Part Number, Memory Size, and Package of R8C/34F Group

Table 1.11 Product List for R8C/34G Group

### Current of Apr. 2008

Part No.	ROM Capacity		RAM	Package Type	Remarks
Part No.	Program ROM	Data flash	Capacity	Package Type	Remarks
R5F21346GJFP (D)	32 Kbytes	1 Kbyte × 4	2.5 Kbytes	PLQP0048KB-A	J version
R5F21347GJFP (D)	48 Kbytes	1 Kbyte × 4	4 Kbytes	PLQP0048KB-A	
R5F21348GJFP (D)	64 Kbytes	1 Kbyte × 4	6 Kbytes	PLQP0048KB-A	
R5F2134AGJFP (P)	96 Kbytes	1 Kbyte × 4	8 Kbytes	PLQP0048KB-A	
R5F2134CGJFP (P)	128 Kbytes	1 Kbyte × 4	10 Kbytes	PLQP0048KB-A	
R5F21346GKFP (D)	32 Kbytes	1 Kbyte × 4	2.5 Kbytes	PLQP0048KB-A	K version
R5F21347GKFP (D)	48 Kbytes	1 Kbyte × 4	4 Kbytes	PLQP0048KB-A	
R5F21348GKFP (D)	64 Kbytes	1 Kbyte × 4	6 Kbytes	PLQP0048KB-A	
R5F2134AGKFP (P)	96 Kbytes	1 Kbyte × 4	8 Kbytes	PLQP0048KB-A	
R5F2134CGKFP (P)	128 Kbytes	1 Kbyte × 4	10 Kbytes	PLQP0048KB-A	

(D): Under development

(P): Under planning




Figure 1.3 Part Number, Memory Size, and Package of R8C/34G Group

Table 1.12 Product List for R8C/34H Group

### Current of Apr. 2008

Part No.	ROM Capacity Program ROM	RAM Capacity	Package Type	Remarks
R5F21346HJFP (D)	32 Kbytes	2.5 Kbytes	PLQP0048KB-A	J version
R5F21347HJFP (D)	48 Kbytes	4 Kbytes	PLQP0048KB-A	
R5F21348HJFP (D)	64 Kbytes	6 Kbytes	PLQP0048KB-A	
R5F2134AHJFP (P)	96 Kbytes	8 Kbytes	PLQP0048KB-A	
R5F2134CHJFP (P)	128 Kbytes	10 Kbytes	PLQP0048KB-A	
R5F21346HKFP (D)	32 Kbytes	2.5 Kbytes	PLQP0048KB-A	K version
R5F21347HKFP (D)	48 Kbytes	4 Kbytes	PLQP0048KB-A	
R5F21348HKFP (D)	64 Kbytes	6 Kbytes	PLQP0048KB-A	
R5F2134AHKFP (P)	96 Kbytes	8 Kbytes	PLQP0048KB-A	
R5F2134CHKFP (P)	128 Kbytes	10 Kbytes	PLQP0048KB-A	

(D): Under development(P): Under planning




Figure 1.4 Part Number, Memory Size, and Package of R8C/34H Group

## 1.3 Block Diagram

Figure 1.5 shows a Block Diagram.




Figure 1.5 Block Diagram

## 1.4 Pin Assignment

Figure 1.6 shows Pin Assignment (Top View). Tables 1.13 and 1.14 outlines the Pin Name Information by Pin Number.




Figure 1.6 Pin Assignment (Top View)

Table 1.13 Pin Name Information by Pin Number (1)

					I/O Pin Functions for o	of Peripheral Module	es	
Pin Number	Control Pin	Port	Interrupt	Timer	Serial Interface	Clock Synchronous Serial I/O with Chip Select	CAN Module <sup>(2)</sup>	A/D Converter Voltage Detection Circuit
1		P3_5			(CLK2) <sup>(1)</sup>	SSCK		
2		P3_3	ĪNT3		CTS2/RTS2	(SSI) <sup>(1)</sup> /SCS		
3		P3_4			(TXD2)/(SDA2)/ (RXD2)/(SCL2)	SSI/(SCS)(1)		
4	MODE							
5		P4_3						
6		P4_4						
7	RESET							
8	XOUT	P4_7						
9	VSS/AVSS							
10	XIN	P4_6						
11	VCC/AVCC							
12		P2_7		TRDIOD1				
13		P2_6		TRDIOC1				
14		P2_5		TRDIOB1				
15		P2_4		TRDIOA1				
16		P2_3		TRDIOD0				
17		P2_2		TRDIOC0				
18		P2_1		TRDIOB0				
19		P2_0		TRDIOA0/ TRDCLK				
20		P1_7	ĪNT1	(TRAIO) (1)				
21		P1_6			CLK0			
22		P1_5	ĪNT1 <sup>(1)</sup>	(TRAIO) (1)	RXD0			
23		P1_4		TRCCLK	TXD0			
24		P1_3	KI3	TRBO				AN11
25		P4_5	ĪNT0					ADTRG
26		P6_6	ĪNT2	TRCIOC	(TXD2)/(SDA2) (1)			

### Note:

- 1. This can be assigned to the pin in parentheses by a program.
- 2. Only for R8C/34E group and R8C/34F group.

					I/O Pin Functions for	or of Peripheral Modul	es	
Pin Number	Control Pin	Port	Interrupt	Timer	Serial Interface	Clock Synchronous Serial I/O with Chip Select	CAN Module <sup>(2)</sup>	A/D Converter Voltage Detection Circuit
27		P6_7	INT3 <sup>(1)</sup>	TRCIOD	(RXD2)/(SCL2) (1)			
28		P1_2	KI2	TRCIOB				AN10
29		P1_1	KI1	TRCIOA/ TRCTRG				AN9
30		P1_0	KI0					AN8
31		P3_1		(TRBO) (1)				
32		P3_0		(TRAO) (1)				
33		P6_5	ĪNT4		(CLK2) <sup>(1)</sup>			
34		P6_4						
35		P6_3						LVCMP2
36		P0_7						AN0
37		P0_6						AN1
38		P0_5						AN2
39		P0_4		TREO				AN3
40		P4_2						VREF
41		P6_0		(TREO) (1)				
42		P6_2					CRX0 <sup>(2)</sup>	
43		P6_1					CTX0 <sup>(2)</sup>	
44		P0_3						AN4
45		P0_2						AN5
46		P0_1						AN6
47		P0_0						AN7
48		P3_7		(TRAO) (1)	(TXD2)/(SDA2)/ (RXD2)/(SCL2) (1)	SSO		

### Note:

- 1. This can be assigned to the pin in parentheses by a program.
- 2. Only for R8C/34E group and R8C/34F group.

### 1.5 Pin Functions

Tables 1.15 and 1.16 list Pin Functions.

Table 1.15 Pin Functions (1)

Item	Pin Name	I/O Type	Description
Power supply input	VCC, VSS	_	Apply 2.7 V to 5.5 V to the VCC pin. Apply 0 V to the VSS pin.
Analog power supply input	AVCC, AVSS	_	Power supply for the A/D converter. Connect a capacitor between AVCC and AVSS.
Reset input	RESET	- 1	Input "L" on this pin resets the MCU.
MODE	MODE	I	Connect this pin to VCC via a resistor.
XIN clock input	XIN	I	These pins are provided for XIN clock generation circuit I/O. Connect a ceramic resonator or a crystal oscillator between
XIN clock output	XOUT	0	the XIN and XOUT pins <sup>(1)</sup> . To use an external clock, input it to the XIN pin and leave the XOUT pin open.
INT interrupt input	INT0 to INT4	I	INT interrupt input pins.
Key input interrupt	KI0 to KI3	I	Key input interrupt input pins
Timer RA	TRAIO	I/O	Timer RA I/O pin
	TRAO	0	Timer RA output pin
Timer RB	TRBO	0	Timer RB output pin
Timer RC	TRCCLK	I	External clock input pin
	TRCTRG	I	External trigger input pin
	TRCIOA, TRCIOB, TRCIOC, TRCIOD	I/O	Timer RC I/O pins
Timer RD	TRDIOA0, TRDIOA1, TRDIOB0, TRDIOB1, TRDIOC0, TRDIOC1, TRDIOD0, TRDIOD1	I/O	Timer RD I/O pins
	TRDCLK	I	External clock input pin
Timer RE	TREO	0	Divided clock output pin
Serial interface	CLK0, CLK1, CLK2	I/O	Transfer clock I/O pins
	RXD0, RXD2	I	Serial data input pins
	TXD0, TXD2	0	Serial data output pins
	CTS2	I	Transmission control input pin
	RTS2	0	Reception control output pin
	SCL2	I/O	I <sup>2</sup> C mode clock I/O pin
	SDA2	I/O	I <sup>2</sup> C mode data I/O pin
SSU	SSI	I/O	Data I/O pin
	SCS	I/O	Chip-select signal I/O pin
	SSCK	I/O	Clock I/O pin
	SSO	I/O	Data I/O pin

I: Input

O: Output

I/O: Input and output

Note:

1. Refer to the oscillator manufacturer for oscillation characteristics.

Table 1.16 Pin Functions (2)

Item	Pin Name	I/O Type	Description
CAN module	CRX0(2)	I	CAN data input pin
	CTX0(2)	0	CAN data output pin
Reference voltage input	VREF	I	Reference voltage input pin to A/D converter
A/D converter	AN0 to AN11	I	Analog input pins to A/D converter
	ADTRG	I	AD external trigger input pin
Voltage Detection Circuit	LVCMP2	I	Detection target voltage pin for voltage detection 2
I/O port	P0_0 to P0_7, P1_0 to P1_7, P2_0 to P2_7, P3_0 to P3_1, P3_3 to P3_5, P3_7, P4_3 to P4_7, P6_0 to P6_7	I/O	CMOS I/O ports. Each port has an I/O select direction register, allowing each pin in the port to be directed for input or output individually.  Any port set to input can be set to use a pull-up resistor or not by a program.
Input port	P4_2	I	Input-only ports

I: Input O: Output

I/O: Input and output

Note:

2. Only in the R8C/34E Group and the R8C/34F Group.

# 2. Central Processing Unit (CPU)

Figure 2.1 shows the CPU Registers. The CPU contains 13 registers. R0, R1, R2, R3, A0, A1, and FB configure a register bank. There are two sets of register bank.




Figure 2.1 CPU Registers

### 2.1 Data Registers (R0, R1, R2, and R3)

R0 is a 16-bit register for transfer, arithmetic, and logic operations. The same applies to R1 to R3. R0 can be split into high-order bits (R0H) and low-order bits (R0L) to be used separately as 8-bit data registers. R1H and R1L are analogous to R0H and R0L. R2 can be combined with R0 and used as a 32-bit data register (R2R0). R3R1 is analogous to R2R0.

#### 2.2 Address Registers (A0 and A1)

A0 is a 16-bit register for address register indirect addressing and address register relative addressing. It is also used for transfer, arithmetic, and logic operations. A1 is analogous to A0. A1 can be combined with A0 and as a 32bit address register (A1A0).

### 2.3 Frame Base Register (FB)

FB is a 16-bit register for FB relative addressing.

### 2.4 Interrupt Table Register (INTB)

INTB is a 20-bit register that indicates the start address of an interrupt vector table.

#### 2.5 **Program Counter (PC)**

PC is 20 bits wide and indicates the address of the next instruction to be executed.

#### 2.6 User Stack Pointer (USP) and Interrupt Stack Pointer (ISP)

The stack pointers (SP), USP, and ISP, are each 16 bits wide. The U flag of FLG is used to switch between USP and ISP.

### 2.7 Static Base Register (SB)

SB is a 16-bit register for SB relative addressing.

### 2.8 Flag Register (FLG)

FLG is an 11-bit register indicating the CPU state.

### 2.8.1 Carry Flag (C)

The C flag retains carry, borrow, or shift-out bits that have been generated by the arithmetic and logic unit.

#### 2.8.2 Debug Flag (D)

The D flag is for debugging only. Set it to 0.

#### 2.8.3 Zero Flag (Z)

The Z flag is set to 1 when an arithmetic operation results in 0; otherwise to 0.

#### 2.8.4 Sign Flag (S)

The S flag is set to 1 when an arithmetic operation results in a negative value; otherwise to 0.

#### 2.8.5 Register Bank Select Flag (B)

Register bank 0 is selected when the B flag is 0. Register bank 1 is selected when this flag is set to 1.

#### 2.8.6 Overflow Flag (O)

The O flag is set to 1 when an operation results in an overflow; otherwise to 0.

#### 2.8.7 Interrupt Enable Flag (I)

The I flag enables maskable interrupts.

Interrupt are disabled when the I flag is set to 0, and are enabled when the I flag is set to 1. The I flag is set to 0 when an interrupt request is acknowledged.

### 2.8.8 Stack Pointer Select Flag (U)

ISP is selected when the U flag is set to 0; USP is selected when the U flag is set to 1.

The U flag is set to 0 when a hardware interrupt request is acknowledged or the INT instruction of software interrupt numbers 0 to 31 is executed.

#### 2.8.9 **Processor Interrupt Priority Level (IPL)**

IPL is 3 bits wide and assigns processor interrupt priority levels from level 0 to level 7. If a requested interrupt has higher priority than IPL, the interrupt is enabled.

#### 2.8.10 Reserved Bit

If necessary, set to 0. When read, the content is undefined.

## 3. Memory

### 3.1 R8C/34E Group


Figure 3.1 is a Memory Map of R8C/34E Group. The R8C/34E Group has a 1-Mbyte address space from addresses 00000h to FFFFh. The internal ROM (program ROM) is allocated lower addresses, beginning with address 0FFFFh. For example, a 48-Kbyte internal ROM area is allocated addresses 04000h to 0FFFFh.

The fixed interrupt vector table is allocated addresses 0FFDCh to 0FFFFh. The starting address of each interrupt routine is stored here.

The internal ROM (data flash) is allocated addresses 03000h to 03FFFh.

The internal RAM is allocated higher addresses, beginning with address 00400h. For example, a 4-Kbyte internal RAM area is allocated addresses 00400h to 013FFh. The internal RAM is used not only for data storage but also as a stack area when a subroutine is called or when an interrupt request is acknowledged.

Special function registers (SFRs) are allocated addresses 00000h to 002FFh and 02C00h to 02FFFh (the SFR areas for the CAN, DTC, and other modules). Peripheral function control registers are allocated here. All unallocated spaces within the SFRs are reserved and cannot be accessed by users.



5		Internal ROM			Internal RAM		
Part Number	Size	Address 0YYYYh	Address ZZZZZh	Size	Address 0XXXXh		
R5F21346EJFP, R5F21346EKFP	32 Kbytes	08000h	_	2.5 Kbytes	00DFFh		
R5F21347EJFP, R5F21347EKFP	48 Kbytes	04000h	_	4 Kbytes	013FFh		
R5F21348EJFP, R5F21348EKFP	64 Kbytes	04000h	13FFFh	6 Kbytes	01BFFh		
R5F2134AEJFP, R5F2134AEKFP	96 Kbytes	04000h	1BFFFh	8 Kbytes	023FFh		
R5F2134CEJFP, R5F2134CEKFP	128 Kbytes	04000h	23FFFh	10 Kbytes	02BFFh		

Figure 3.1 Memory Map of R8C/34E Group


## R8C/34F Group

Figure 3.2 is a Memory Map of R8C/34F Group. The R8C/34F Group has a 1-Mbyte address space from addresses 00000h to FFFFFh. The internal ROM (program ROM) is allocated lower addresses, beginning with address 0FFFFh. For example, a 48-Kbyte internal ROM area is allocated addresses 04000h to 0FFFFh.

The fixed interrupt vector table is allocated addresses 0FFDCh to 0FFFFh. The starting address of each interrupt routine is stored here.

The internal RAM is allocated higher addresses, beginning with address 00400h. For example, a 4-Kbyte internal RAM area is allocated addresses 00400h to 013FFh. The internal RAM is used not only for data storage but also as a stack area when a subroutine is called or when an interrupt request is acknowledged.

Special function registers (SFRs) are allocated addresses 00000h to 002FFh and 02C00h to 02FFFh (the SFR areas for the CAN, DTC, and other modules). Peripheral function control registers are allocated here. All unallocated spaces within the SFRs are reserved and cannot be accessed by users.



Dard Namels on		Internal ROM			Internal RAM		
Part Number	Size	Address 0YYYYh	Address ZZZZZh	Size	Address 0XXXXh		
R5F21346FJFP, R5F21346FKFP	32 Kbytes	08000h	_	2.5 Kbytes	00DFFh		
R5F21347FJFP, R5F21347FKFP	48 Kbytes	04000h	_	4 Kbytes	013FFh		
R5F21348FJFP, R5F21348FKFP	64 Kbytes	04000h	13FFFh	6 Kbytes	01BFFh		
R5F2134AFJFP, R5F2134AFKFP	96 Kbytes	04000h	1BFFFh	8 Kbytes	023FFh		
R5F2134CFJFP, R5F2134CFKFP	128 Kbytes	04000h	23FFFh	10 Kbytes	02BFFh		

Figure 3.2 Memory Map of R8C/34F Group

### 3.3 **R8C/34G Group**

Figure 3.3 is a Memory Map of R8C/34G Group. The R8C/34G Group has a 1-Mbyte address space from addresses 00000h to FFFFh. The internal ROM (program ROM) is allocated lower addresses, beginning with address 0FFFFh. For example, a 48-Kbyte internal ROM area is allocated addresses 04000h to 0FFFFh.

The fixed interrupt vector table is allocated addresses 0FFDCh to 0FFFFh. The starting address of each interrupt routine is stored here.

The internal ROM (data flash) is allocated addresses 03000h to 03FFFh.

The internal RAM is allocated higher addresses, beginning with address 00400h. For example, a 4-Kbyte internal RAM area is allocated addresses 00400h to 013FFh. The internal RAM is used not only for data storage but also as a stack area when a subroutine is called or when an interrupt request is acknowledged.

Special function registers (SFRs) are allocated addresses 00000h to 002FFh and 02C00h to 02FFFh (the SFR areas for the DTC and other modules). Peripheral function control registers are allocated here. All unallocated spaces within the SFRs are reserved and cannot be accessed by users.




Figure 3.3 Memory Map of R8C/34G Group


### 3.4 R8C/34H Group

Figure 3.4 is a Memory Map of R8C/34H Group. The R8C/34H Group has a 1-Mbyte address space from addresses 00000h to FFFFh. The internal ROM (program ROM) is allocated lower addresses, beginning with address 0FFFFh. For example, a 48-Kbyte internal ROM area is allocated addresses 04000h to 0FFFFh.

The fixed interrupt vector table is allocated addresses 0FFDCh to 0FFFFh. The starting address of each interrupt routine is stored here.

The internal RAM is allocated higher addresses, beginning with address 00400h. For example, a 4-Kbyte internal RAM area is allocated addresses 00400h to 013FFh. The internal RAM is used not only for data storage but also as a stack area when a subroutine is called or when an interrupt request is acknowledged.

Special function registers (SFRs) are allocated addresses 00000h to 002FFh and 02C00h to 02FFFh (the SFR areas for the DTC and other modules). Peripheral function control registers are allocated here. All unallocated spaces within the SFRs are reserved and cannot be accessed by users.



04000h

23FFFh

10 Kbytes

02BFFh

Figure 3.4 Memory Map of R8C/34H Group

128 Kbytes

R5F2134CHJFP, R5F2134CHKFP

### **Special Function Registers (SFRs)** 4.

An SFR (special function register) is a control register for a peripheral function. Tables 4.1 to 4.17 list the special function registers.

Table 4.1 SFR Information (1) (1)

0000h 0001h 0002h 0003h 0004h 0005h			
0002h 0003h 0004h 0005h			
0003h 0004h 0005h			
0004h 0005h			
0005h			
	Processor Mode Register 0	PM0	00h
0000-	Processor Mode Register 1	PM1	00h
0006h	System Clock Control Register 0	CM0	00101000b
0007h	System Clock Control Register 1	CM1	00100000b
0008h	Module Standby Control Register	MSTCR	00h
0009h	System Clock Control Register 3	CM3	00h
000Ah	Protect Register	PRCR	00h
000Bh	Reset Source Determination Register	RSTFR	0XXX00XXb (2)
000Ch	Oscillation Stop Detection Register	OCD	00000100b
000Dh	Watchdog Timer Reset Register	WDTR	XXh
000Eh	Watchdog Timer Start Register	WDTS	XXh
000Fh	Watchdog Timer Control Register	WDTC	00111111b
0010h			
0011h			
0011h			
0012h			
0013h			
0014H	High-Speed On-Chip Oscillator Control Register 7	FRA7	When shipping
0015h	The speed on only obtained oblition register /	1100	**TIGH SHIPPING
0010H			-
0017H			
0019h			
0013h			
001An			
001Bh	Count Source Protection Mode Register	CSPR	00h
001011	Count Source Protection wode Register	CSFR	10000000b <sup>(3)</sup>
001Db			100000000000000000000000000000000000000
001Dh			
001Eh			
001Fh			
0020h			
0021h			
0022h	High Count On Chin Contillator Control Beninter C	- LEDAG	005
0023h	High-Speed On-Chip Oscillator Control Register 0	FRA0	00h
0024h	High-Speed On-Chip Oscillator Control Register 1	FRA1	When shipping
0025h	High-Speed On-Chip Oscillator Control Register 2	FRA2	00h
0026h	On-Chip Reference Voltage Control Register	OCVREFCR	00h
0027h			
0028h			
0029h	High-Speed On-Chip Oscillator Control Register 4	FRA4	When Shipping
002Ah	High-Speed On-Chip Oscillator Control Register 5	FRA5	When Shipping
002Bh	High-Speed On-Chip Oscillator Control Register 6	FRA6	When Shipping
002Ch			
002Dh			
002Eh			
002Fh	High-Speed On-Chip Oscillator Control Register 3	FRA3	When shipping
0030h	Voltage Monitor Circuit Control Register	CMPA	00h
0031h	Voltage Monitor Circuit Edge Select Register	VCAC	00h
0032h			
0033h	Voltage Detect Register 1	VCA1	00001000b
0034h	Voltage Detect Register 2	VCA2	00h <sup>(4)</sup>
			00100000b (5)
0035h			
0036h	Voltage Detection 1 Level Select Register	VD1LS	00000111b
0037h	<u> </u>		
	Voltage Monitor 0 Circuit Control Register	VW0C	1100X010b <sup>(4)</sup>
0038h I		1 *****	
0038h	I and the second		1100X011b (5)

- X: Undefined
  NOTES:

  1. The blank areas are reserved and cannot be accessed by users.
  2. The CWR bit in the RSTFR register is set to 0 after power-on and voltage monitor 0 reset. Software reset, watchdog timer reset, or oscillation
  - The CSPROINI bit in the OFS register is set to 0.
  - The LVDAS bit in the OFS register is set to 1.
  - The LVDAS bit in the OFS register is set to 0.

Table 4.2 SFR Information (2) (1)

	Register	Symbol	After reset
003Ah	Voltage Monitor 2 Circuit Control Register	VW2C	10000010b
003Bh			
003Ch			
003Dh			
003Eh			
003Fh			
0040h			
0041h	Flash Memory Ready Interrupt Control Register	FMRDYIC	XXXXX000b
0042h			
0043h			
0044h			
0045h			
0046h	INT4 Interrupt Control Register	INT4IC	XX00X000b
0047h	Timer RC Interrupt Control Register	TRCIC	XXXXX000b
0048h	Timer RD0 Interrupt Control Register	TRD0IC	XXXXX000b
0049h	Timer RD1 Interrupt Control Register	TRD1IC	XXXXX000b
004Ah	Timer RE Interrupt Control Register	TREIC	XXXXX000b
004Bh	UART2 Transmit Interrupt Control Register	S2TIC	XXXXX000b
004Ch	UART2 Receive Interrupt Control Register	S2RIC	XXXXX000b
004Dh	Key Input Interrupt Control Register	KUPIC	XXXXX000b
004DH 004Eh	A/D Conversion Interrupt Control Register	ADIC	XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX
004EII	SSU Interrupt Control Register	SSUIC	XXXXX000b
004FII	000 interrupt Control Negister	33010	^^^^
	LIADTO Transmit Interrupt Control Decistor	POTIC	VVVVVVV
0051h	UART0 Transmit Interrupt Control Register UART0 Receive Interrupt Control Register	SOTIC	XXXXX000b
0052h	OAKTU Receive Interrupt Control Register	SORIC	XXXXX000b
0053h			
0054h	INITE LA COLLEGE	1117010	V//20V/20Q
0055h	INT2 Interrupt Control Register	INT2IC	XX00X000b
0056h	Timer RA Interrupt Control Register	TRAIC	XXXXX000b
0057h			
0058h	Timer RB Interrupt Control Register	TRBIC	XXXXX000b
0059h	INT1 Interrupt Control Register	INT1IC	XX00X000b
005Ah	INT3 Interrupt Control Register	INT3IC	XX00X000b
005Bh			
005Ch			
005Dh	INT0 Interrupt Control Register	INT0IC	XX00X000b
005Eh	UART2 Bus Collision Detection Interrupt Control Register	U2BCNIC	XXXXX000b
005Fh			
0060h			
0061h			
0062h			
0063h			
0064h			
0065h			
0066h			
0067h			
0068h			
0069h 006Ah			
006An 006Bh			
	CANO Supposeful Reportion Intervent Control Desister	CORIC	VVVVVAAA
006Ch	CANO Successful Reception Interrupt Control Register		XXXXX000b
006Dh	CANO Successful Transmission Interrupt Control Register	COTIC	XXXXX000b
006Eh	CANO Receive FIFO Interrupt Control Register	COFRIC	XXXXX000b
000-	CANO Transmit FIFO Interrupt Control Register	COFTIC	XXXXX000b
006Fh		C0EIC	XXXXX000b
0070h	CAN0 Error Interrupt Control Register		
0070h 0071h	CAN0 Wake-up Interrupt Control Register	COWIC	XXXXX000b
0070h 0071h 0072h	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b
0070h 0071h 0072h 0073h	CAN0 Wake-up Interrupt Control Register	COWIC	
0070h 0071h 0072h 0073h 0074h	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b
0070h 0071h 0072h 0073h 0074h 0075h	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b
0070h 0071h 0072h 0073h 0074h 0075h 0076h	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b
0070h 0071h 0072h 0073h 0074h 0075h 0076h	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b
0070h 0071h 0072h 0073h 0074h 0075h 0076h	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b
0070h 0071h 0072h 0073h 0074h 0075h 0076h	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b
0070h 0071h 0072h 0073h 0074h 0075h 0076h 0077h	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b
0070h 0071h 0072h 0073h 0074h 0075h 0076h 0077h 0078h 0079h	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b
0070h 0071h 0072h 0073h 0074h 0075h 0076h 0077h 0078h 0079h 007Ah 007Bh	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b
0070h 0071h 0072h 0073h 0074h 0075h 0076h 0077h 0078h 0079h 007Ah 007Bh	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b
0070h 0071h 0072h 0073h 0074h 0075h 0076h 0077h 0078h 0079h 007Ah 007Bh	CAN0 Wake-up Interrupt Control Register  Voltage Monitor 1 Level Interrupt Control Register	C0WIC VCMP1IC	XXXXX000b

X : Undefined
NOTES:

1. The blank areas are reserved and cannot be accessed by users.

SFR Information (3) <sup>(1)</sup> Table 4.3

Address	Pogiator	Symbol	After reset
0080h	Register  DTC Activation Control Register	Symbol DTCTL	00h
	DTC Activation Control Register	DICIL	OUI
0081h			
0082h			
0083h			
0084h			
0085h			
0086h			
0087h			
0088h	DTC Activation Enable Register 0	DTCEN0	00h
0089h	DTC Activation Enable Register 1	DTCEN1	00h
008Ah	DTC Activation Enable Register 2	DTCEN2	00h
008Bh	DTC Activation Enable Register 3	DTCEN3	00h
008Ch	DTC Activation Enable Register 4	DTCEN4	00h
008Dh	DTC Activation Enable Register 5	DTCEN5	00h
008Eh	DTC Activation Enable Register 6	DTCEN6	00h
008Fh			
0090h			
0091h			
0092h			
0093h		+	<u> </u>
0094h			+
0094n			
0096h			
0097h			
0098h			
0099h			
009Ah			
009Bh			
009Ch			
009Dh			
009Eh			
009En			
	LIADTO Terroriti Desciente Designa	LIOMB	001
00A0h	UART0 Transmit/Receive Mode Register	U0MR	00h
00A1h	UART0 Bit Rate Register	U0BRG	XXh
00A2h	UART0 Transmit Buffer Register	U0TB	XXh
00A3h			XXh
00A4h	UART0 Transmit/Receive Control Register 0	U0C0	00001000b
00A5h	UART0 Transmit/Receive Control Register 1	U0C1	00000010b
00A6h	UART0 Receive Buffer Register	U0RB	XXh
00A7h	- Critical Cooking Damer Regions.	551.12	XXh
00A711	UART2 Transmit/Receive Mode Register	U2MR	00h
00A9h	UART2 Bit Rate Register	U2BRG	XXh
00AAh	UART2 Transmit Buffer Register	U2TB	XXh
00ABh			XXh
00ACh	UART2 Transmit/Receive Control Register 0	U2C0	00001000b
00ADh	UART2 Transmit/Receive Control Register 1	U2C1	00000010b
00AEh	UART2 Receive Buffer Register	U2RB	XXh
00AFh	<b>1</b>		XXh
00B0h	UART2 Digital Filter Function Select Register	URXDF	00h
00B1h	2 2.g.a aa coloot regiotol	010(8)	
00B1II			
00B3h			
00B4h			
00B5h			
00B6h			
00B7h			
00B8h			
00B9h			<u> </u>
00BAh			+
	LIART2 Special Mode Pegister F	U2SMR5	00h
UUDDP	UART2 Special Mode Register 5		
00BBh	HADTO Conside Made Desister 4		
00BCh	UART2 Special Mode Register 4	U2SMR4	00h
00BCh 00BDh	UART2 Special Mode Register 3	U2SMR3	000X0X0Xb
00BCh			

X: Undefined

Note:

1. The blank areas are reserved and cannot be accessed by users.

SFR Information (4) (1) Table 4.4

Address	Register	Symbol	After reset
00C0h	A/D Register 0	AD0	XXh
00C1h			000000XXb
	A/D Register 1	AD1	XXh
00C3h	-		000000XXb
	A/D Register 2	AD2	XXh
00C5h	ŭ		000000XXb
	A/D Register 3	AD3	XXh
00C7h	<del></del>		000000XXb
	A/D Register 4	AD4	XXh
00C9h	, 12 1 togistis. 1	1.5.	000000XXb
	A/D Register 5	AD5	XXh
00CBh	7 D Register 5	7.50	000000XXb
	A/D Register 6	AD6	XXh
00CDh	7 D Register 0	7.50	000000XXb
	A/D Register 7	AD7	XXh
00CFh	AD Register 1	ADI	000000XXb
00D0h			0000000000
00D0H			
00D2h			
00D3h	A/D Mada Daviston	101100	001-
00D4h	A/D Mode Register	ADMOD	00h
00D5h	A/D Input Select Register	ADINSEL	11000000b
00D6h	A/D Control Register 0	ADCON0	00h
	A/D Control Register 1	ADCON1	00h
00D8h			
00D9h			
00DAh			
00DBh			
00DCh			
00DDh			
00DEh			
00DFh			
	Port P0 Register	P0	XXh
	Port P1 Register	P1	XXh
00E2h	Port P0 Direction Register	PD0	00h
00E3h	Port P1 Direction Register	PD1	00h
	Port P2 Register	P2	XXh
	Port P3 Register	P3	XXh
	Port P2 Direction Register	PD2	00h
	Port P3 Direction Register	PD3	00h
	Port P4 Register	P4	XXh
00E9h	FOIL F4 Negister	F4	AAII
	Port D4 Direction Register	DD4	00b
	Port P4 Direction Register	PD4	00h
00EBh	Port D6 Pogistor	De	VVh
	Port P6 Register	P6	XXh
00EDh	D. ( DO D'. ( ) D. ( ) (	1000	0.01
	Port P6 Direction Register	PD6	00h
00EFh			
00F0h			
00F1h			
00F2h			
00F3h			
00F4h			
00F5h			
00F6h			
00F7h			
00F8h			
00F9h			
00FAh			
00FBh			
00FCh			
00FDh			+
00FEh			
		1	
00FFh			

X : Undefined
Note:

1. The blank areas are reserved and cannot be accessed by users.

4. Special Function Registers (SFRs)

Table 4.5 SFR Information (5) (1)

Address	Register	Symbol	After reset
0100h	Timer RA Control Register	TRACR	00h
0101h	Timer RA I/O Control Register	TRAIOC	00h
0102h	Timer RA Mode Register	TRAMR	00h
0103h	Timer RA Prescaler Register	TRAPRE	FFh
0104h	Timer RA Register	TRA	FFh
0105h	LIN0 Control Register 2	LIN0CR2	00h
0106h	LIN0 Control Register	LIN0CR	00h
0107h	LINO Status Register	LINOST	00h
0108h	Timer RB Control Register	TRBCR	00h
0100h	Timer RB One-Shot Control Register	TRBOCR	00h
	Timer RB I/O Control Register		
010Ah		TRBIOC	00h
010Bh	Timer RB Mode Register	TRBMR	00h
010Ch	Timer RB Prescaler Register	TRBPRE	FFh
010Dh	Timer RB Secondary Register	TRBSC	FFh
010Eh	Timer RB Primary Register	TRBPR	FFh
010Fh			
0110h			
0111h			
0112h		-	+
0112h			
0114h			
0115h			
0116h			
0117h			
0118h	Timer RE Counter Data Register	TRESEC	00h
0119h	Timer RE Compare Data Register	TREMIN	00h
011Ah	i i		
011Bh			
011Ch	Timer RE Control Register 1	TRECR1	00h
011Dh	Timer RE Control Register 2	TRECR2	00h
011Eh	Timer RE Count Source Select Register	TRECSR	00001000b
011Fh			
0120h	Timer RC Mode Register	TRCMR	01001000b
0121h	Timer RC Control Register 1	TRCCR1	00h
0122h	Timer RC Interrupt Enable Register	TRCIER	01110000b
0123h	Timer RC Status Register	TRCSR	01110000b
0124h	Timer RC I/O Control Register 0	TRCIOR0	10001000b
0125h	Timer RC I/O Control Register 1	TRCIOR1	10001000b
0126h	Timer RC Counter	TRC	00h
0120h	Timer No Counter	11.0	00h
	The BOO of the A	TROOPA	
0128h	Timer RC General Register A	TRCGRA	FFh
0129h			FFh
012Ah	Timer RC General Register B	TRCGRB	FFh
012Bh			FFh
012Ch	Timer RC General Register C	TRCGRC	FFh
012Dh			FFh
012Eh	Timer RC General Register D	TRCGRD	FFh
012Fh	1	1	FFh
0130h	Timer RC Control Register 2	TRCCR2	00011000b
0130h	Timer RC Digital Filter Function Select Register	TRCDF	00011000b
0132h	Timer RC Output Master Enable Register	TRCOER	01111111b
0133h	Timer RC Trigger Control Register	TRCADCR	00h
0134h			
0135h			
0136h	Timer RD Trigger Control Register	TRDADCR	00h
0137h	Timer RD Start Register	TRDSTR	11111100b
0138h	Timer RD Mode Register	TRDMR	00001110b
0139h	Timer RD PWM Mode Register	TRDPMR	10001000b
013Ah	Timer RD Function Control Register	TRDFCR	10001000b
013An	5	TRDOER1	
	Timer RD Output Master Enable Register 1		FFh
013Ch	Timer RD Output Master Enable Register 2	TRDOER2	01111111b
013Dh	Timer RD Output Control Register	TRDOCR	00h
040	Timer RD Digital Filter Function Select Register 0	TRDDF0	00h
013Eh 013Fh	Timor NE Bigitar Filter Function Coloct Register 6	TRDDF1	••

Note:

<sup>1.</sup> The blank areas are reserved and cannot be accessed by users.

Table 4.6 SFR Information (6) (1)

Address	Register	Symbol	After reset
0140h	Timer RD Control Register 0	TRDCR0	00h
0141h	Timer RD I/O Control Register A0	TRDIORA0	10001000b
0142h	Timer RD I/O Control Register C0	TRDIORC0	10001000b
0143h	Timer RD Status Register 0	TRDSR0	11100000b
0144h	Timer RD Interrupt Enable Register 0	TRDIER0	11100000b
0145h	Timer RD PWM Mode Output Level Control Register 0	TRDPOCR0	11111000b
0146h	Timer RD Counter 0	TRD0	00h
0147h			00h
0148h	Timer RD General Register A0	TRDGRA0	FFh
0149h	Times its contracting of the		FFh
014Ah	Timer RD General Register B0	TRDGRB0	FFh
014Bh	Time NE Contra Negleton Bo		FFh
014Ch	Timer RD General Register C0	TRDGRC0	FFh
014Dh	Timer ND General Negister 66	TRECKE	FFh
014Eh	Timer RD General Register D0	TRDGRD0	FFh
014Eh	Time ND General Negister Do	INDONDO	FFh
014111 0150h	Timer RD Control Register 1	TRDCR1	00h
0151h	Timer RD I/O Control Register A1	TRDIORA1	10001000b
0152h 0153h	Timer RD I/O Control Register C1	TRDIORC1 TRDSR1	10001000b
	Timer RD Status Register 1		11000000b
0154h	Timer RD Interrupt Enable Register 1	TRDIER1	11100000b
0155h	Timer RD PWM Mode Output Level Control Register 1	TRDPOCR1	11111000b
0156h	Timer RD Counter 1	TRD1	00h
0157h			00h
0158h	Timer RD General Register A1	TRDGRA1	FFh
0159h			FFh
015Ah	Timer RD General Register B1	TRDGRB1	FFh
015Bh			FFh
015Ch	Timer RD General Register C1	TRDGRC1	FFh
015Dh			FFh
015Eh	Timer RD General Register D1	TRDGRD1	FFh
015Fh			FFh
0160h			
0161h			
0162h			
0163h			
0164h			
0165h			
0166h			
0167h			
0168h			
0169h			
016Ah			
016Bh			
016Ch			
016Dh			<del>-  </del>
016Eh			
016Fh			
0170h			
0170H			
0171h			
0173h			
0174h			
0175h			
0176h			
0177h			
0178h			
0179h			
017Ah			
017Bh			
017Ch			
017Dh			
017Eh			
O I / LII			

X: Undefined

Note:

1. The blank areas are reserved and cannot be accessed by users.

SFR Information (7) (1) Table 4.7

Address	Register	Symbol	After reset
0180h	Timer RA Pin Select Register	TRASR	00h
0181h	Timer RB/RC Pin Select Register	TRBRCSR	00h
0182h	Timer RC Pin Select Register 0	TRCPSR0	00h
0183h	Timer RC Pin Select Register 1	TRCPSR1	00h
0184h	Timer RD Pin Select Register 0	TRDPSR0	00h
0185h	Timer RD Pin Select Register 1	TRDPSR1	00h
0186h	Timer Pin Select Register	TIMSR	00h
0187h	Timor Fin Colock Register		1
0188h	UART0 Pin Select Register	U0SR	00h
0189h	Office of the ocicot register	00010	0011
018Ah	UART2 Pin Select Register 0	U2SR0	00h
018Bh	UART2 Pin Select Register 1	U2SR1	00h
018Ch	SSU Pin Select Register	SSUIICSR	
	550 PIII Select Register	SSUIICSR	00h
018Dh		WITOD	
018Eh	INT Interrupt Input Pin Select Register	INTSR	00h
018Fh			
0190h			
0191h			
0192h		1	
0193h	SS Bit Counter Register	SSBR	11111000b
0194h	SS Transmit Data Register	SSTDR	FFh
0195h	1	1	FFh
0196h	SS Receive Data Register	SSRDR	FFh
0197h		1 - 2	FFh
0197h	SS Control Register H	SSCRH	00h
0199h	SS Control Register L	SSCRL	01111101b
0199h	SS Mode Register	SSMR	00011000b
019An	SS Enable Register	SSER	00011000b
019Ch	SS Status Register	SSSR	00h
019Dh	SS Mode Register 2	SSMR2	00h
019Eh			
019Fh			
01A0h			
01A1h			
01A2h			
01A3h			
01A4h			
01A5h			
01A6h			
01A7h			
01A8h			
01A9h			-
01A3H			
01ABh		1	
01ACh			ļ
01ADh		ļ	
01AEh			
01AFh			
01B0h			
01B1h		1	
01B2h	Flash Memory Status Register	FST	10000X00b
01B3h			
01B4h	Flash Memory Control Register 0	FMR0	00h
01B5h	Flash Memory Control Register 1	FMR1	00h
01B6h	Flash Memory Control Register 2	FMR2	00h
01B7h			
01B7H		1	<del> </del>
01B9h		-	
		1	
01BAh			ļ
01BBh		ļ	
01BCh			
01BDh			
01BEh			
01BFh			
		•	•

X : Undefined
NOTES:

1. The blank areas are reserved and cannot be accessed by users.

Table 4.8 SFR Information (8) (1)

Addrace			
Address	Register	Symbol	After reset
01C0h	Address Match Interrupt Register 0	RMAD0	XXh
01C1h		-	XXh
01C2h			0000XXXXb
01C3h	Address Match Interrupt Enable Register 0	AIER0	00h
01C4h	Address Match Interrupt Register 1	RMAD1	XXh
01C5h		1	XXh
010311			
01C6h			0000XXXXb
01C7h	Address Match Interrupt Enable Register 1	AIER1	00h
01C8h	· · · · · · · · · · · · · · · · · · ·		
01C9h			
01CAh			
01CBh			
01CCh			
01CDh			
01CEh			
01CFh		İ	
01D0h			
01D1h			
01D2h			
01D3h			+
01D4h			
01D5h			
01D6h			
01D0H			
01D8h			
01D9h			
01DAh			
01DBh			
01DCh			
01DDh			
01DEh			
01DFh			
01E0h	Pull-Up Control Register 0	PUR0	00h
01E1h	Pull-Up Control Register 1	PUR1	00h
	Pull-Op Control Register 1	FURI	0011
01E2h			
01E3h			
01E4h		İ	
01E5h			
01E6h			
01E7h			
01E7h 01E8h			
01E7h 01E8h 01E9h			
01E7h 01E8h			
01E7h 01E8h 01E9h 01EAh			
01E7h 01E8h 01E9h 01EAh 01EBh			
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh			
01E7h 01E8h 01E9h 01EAh 01EBh			
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh			
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh			
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01EFh			
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01EFh 01FOh			
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01EFh 01FOh			
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01EFh 01F7h 01F7h			
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01FFh 01FFh 01F70h 01F1h			
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01EFh 01F1h 01F1h 01F3h			
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01F7h 01F7h 01F7h 01F7h 01F7h 01F7h 01F7h			
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01F7h 01F7h 01F7h 01F7h 01F7h 01F7h 01F7h	Input Threshold Control Register 0	VITO	00h
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01F1h 01F1h 01F2h 01F3h 01F4h 01F5h	Input Threshold Control Register 0	VLT0	00h
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01FFh 01F7h 01F1h 01F2h 01F3h 01F4h 01F5h 01F5h	Input Threshold Control Register 0 Input Threshold Control Register 1	VLT0 VLT1	00h 00h
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01F0h 01F1h 01F3h 01F3h 01F4h 01F5h 01F6h 01F7h	Input Threshold Control Register 0 Input Threshold Control Register 1		
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01F0h 01F1h 01F3h 01F4h 01F5h 01F6h 01F7h	Input Threshold Control Register 0 Input Threshold Control Register 1		
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01EFh 01F1h 01F3h 01F3h 01F4h 01F5h 01F6h 01F7h 01F8h	Input Threshold Control Register 0 Input Threshold Control Register 1		
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01EFh 01F1h 01F7h 01F3h 01F4h 01F5h 01F6h 01F7h 01F8h 01F8h	Input Threshold Control Register 1	VLT1	00h
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01F7h 01F7h 01F7h 01F3h 01F6h 01F7h 01F7h 01F8h 01F7h 01F8h 01F7h 01F8h 01F9h	Input Threshold Control Register 1  External Input Enable Register 0	VLT1	00h
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01F7h	Input Threshold Control Register 1  External Input Enable Register 0	VLT1	00h
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01F1h 01F1h 01F2h 01F3h 01F3h 01F6h 01F7h 01F8h 01F8h 01F8h	Input Threshold Control Register 1  External Input Enable Register 0  External Input Enable Register 1	VLT1  INTEN INTEN1	00h 00h 00h
01E7h 01E8h 01E9h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01F7h 01F3h 01F3h 01F4h 01F5h 01F6h 01F7h 01F8h 01F9h 01F9h 01F9h	Input Threshold Control Register 1  External Input Enable Register 0  External Input Enable Register 1  INT Input Filter Select Register 0	INTEN INTEN INTEN1	00h 00h 00h 00h
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01F0h 01F1h 01F2h 01F3h 01F4h 01F5h 01F6h 01F7h 01F8h 01F9h 01FAh 01FBh 01FAh 01FBh	Input Threshold Control Register 1  External Input Enable Register 0  External Input Enable Register 1  INT Input Filter Select Register 0  INT Input Filter Select Register 1	INTEN INTEN INTF	00h 00h 00h 00h 00h
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01EFh 01F0h 01F1h 01F3h 01F3h 01F4h 01F5h 01F6h 01F7h 01F8h 01F9h 01FAh 01FBh 01FBh 01FBh 01FBh	Input Threshold Control Register 1  External Input Enable Register 0  External Input Enable Register 1  INT Input Filter Select Register 0	INTEN INTEN INTEN1	00h 00h 00h 00h
01E7h 01E8h 01E9h 01EAh 01EBh 01ECh 01EDh 01EEh 01F0h 01F1h 01F3h 01F3h 01F4h 01F5h 01F6h 01F7h 01F8h 01F9h 01F9h 01FAh 01FBh 01FAh 01FBh	Input Threshold Control Register 1  External Input Enable Register 0  External Input Enable Register 1  INT Input Filter Select Register 0  INT Input Filter Select Register 1	INTEN INTEN INTF	00h 00h 00h 00h 00h

X: Undefined

Note:

1. The blank areas are reserved and cannot be accessed by users.

Table 4.9 SFR Information (9) (1)

Address	Register	Symbol	After reset
2C00h	DTC Transfer Vector Area	Symbol	XXh
2C00II	DTC Transfer Vector Area		XXh
2C02h	DTC Transfer Vector Area		XXh
2C03h	DTC Transfer Vector Area		XXh
2C04h	DTC Transfer Vector Area		XXh
2C05h	DTC Transfer Vector Area		XXh
2C06h	DTC Transfer Vector Area		XXh
2C07h	DTC Transfer Vector Area		XXh
2C08h	DTC Transfer Vector Area		XXh
2C09h	DTC Transfer Vector Area		XXh
2C0Ah	DTC Transfer Vector Area DTC Transfer Vector Area		XXh
:	DTC Transfer Vector Area		XXh XXh
2C3Ah	DTC Transfer Vector Area		XXh
2C3Bh	DTC Transfer Vector Area		XXh
2C3Ch	DTC Transfer Vector Area		XXh
2C3Dh	DTC Transfer Vector Area		XXh
2C3Eh	DTC Transfer Vector Area		XXh
2C3Fh	DTC Transfer Vector Area		XXh
2C40h	DTC Control Data 0	DTCD0	XXh
2C41h			XXh
2C42h 2C43h			XXh XXh
2C43f1 2C44h			XXh
2C4411 2C45h			XXh
2C46h			XXh
2C47h			XXh
2C48h	DTC Control Data 1	DTCD1	XXh
2C49h			XXh
2C4Ah			XXh
2C4Bh			XXh
2C4Ch			XXh
2C4Dh			XXh
2C4Eh 2C4Fh			XXh XXh
2C50h	DTC Control Data 2	DTCD2	XXh
2C51h	510 control bata 2	B10B2	XXh
2C52h			XXh
2C53h			XXh
2C54h			XXh
2C55h			XXh
2C56h			XXh
2C57h	DTO 0 1 1D 1 0	DTODO	XXh
2C58h	DTC Control Data 3	DTCD3	XXh
2C59h 2C5Ah			XXh XXh
2C5Bh			XXh
2C5Ch			XXh
2C5Dh			XXh
2C5Eh			XXh
2C5Fh			XXh
2C60h	DTC Control Data 4	DTCD4	XXh
2C61h			XXh
2C62h			XXh
2C63h			XXh
2C64h 2C65h			XXh XXh
2C66h			XXh
2C67h			XXh
2C68h	DTC Control Data 5	DTCD5	XXh
2C69h			XXh
2C6Ah			XXh
2C6Bh			XXh
2C6Ch			XXh
2C6Dh			XXh
2C6Eh			XXh
2C6Fh			XXh

X : Undefined Note:

1. The blank areas are reserved and cannot be accessed by users.

**Table 4.10** SFR Information (10) (1)

A 1.1	, ,		A 6
Address	Register	Symbol	After reset
2C70h	DTC Control Data 6	DTCD6	XXh
2C71h			XXh
2C72h			XXh
2C73h			XXh
2C74h			XXh
2C75h			XXh
2C76h			XXh
2C77h			XXh
2C78h	DTC Control Data 7	DTCD7	XXh
2C79h			XXh
2C7Ah			XXh
2C7Bh			XXh
2C7Ch	1		XXh
2C7Dh	1		XXh
2C7Eh			XXh
2C7Fh	-		XXh
2C80h	DTC Control Data 0	DTCD8	
	DTC Control Data 8	DICDO	XXh
2C81h			XXh
2C82h			XXh
2C83h			XXh
2C84h			XXh
2C85h			XXh
2C86h			XXh
2C87h			XXh
2C88h	DTC Control Data 9	DTCD9	XXh
2C89h			XXh
2C8Ah			XXh
2C8Bh			XXh
2C8Ch			XXh
2C8Dh			XXh
2C8Eh			XXh
2C8Fh	-		XXh
2C90h	DTC Control Data 10	DTCD10	XXh
2C91h	DIC Control Data 10	DICDIO	XXh
2C92h			XXh
2C93h			XXh
2C94h			XXh
2C95h			XXh
2C96h			XXh
2C97h			XXh
2C98h	DTC Control Data 11	DTCD11	XXh
2C99h			XXh
2C9Ah			XXh
2C9Bh			XXh
2C9Ch			XXh
2C9Dh	1		XXh
2C9Eh	1		XXh
2C9Fh	1		XXh
2CA0h	DTC Control Data 12	DTCD12	XXh
2CA1h		1510512	XXh
2CA111	1		XXh
2CA2II	1		XXh
2CA3II	4		XXh
	4		
2CA5h	-		XXh
2CA6h	-		XXh
2CA7h	DT0 0 1 1 D 1 10		XXh
2CA8h	DTC Control Data 13	DTCD13	XXh
2CA9h			XXh
2CAAh			XXh
2CABh			XXh
2CACh			XXh
2CADh			XXh
2CAEh			XXh
2CAFh	1		XXh
V . Undefined		<u> </u>	-

X : Undefined
Note:

1. The blank areas are reserved and cannot be accessed by users.

**Table 4.11** SFR Information (11) (1)

Table 4.11	SFR information (11) (1)		
Address	Register	Symbol	After reset
2CB0h	DTC Control Data 14	DTCD14	XXh
2CB1h			XXh
2CB2h			XXh
2CB3h			XXh
2CB4h			XXh
2CB5h			XXh
2CB6h			XXh
2CB7h			XXh
	DTC Control Data 15	DTCD15	
2CB8h	DTC Control Data 15	פועסוע	XXh
2CB9h			XXh
2CBAh			XXh
2CBBh			XXh
2CBCh			XXh
2CBDh			XXh
2CBEh			XXh
2CBFh			XXh
2CC0h	DTC Control Data 16	DTCD16	XXh
2CC1h			XXh
2CC2h			XXh
2CC3h			XXh
2CC4h			XXh
2CC5h			XXh
2CC6h			XXh
2CC7h			XXh
	DTO Control Date 47	DTOD47	
2CC8h	DTC Control Data 17	DTCD17	XXh
2CC9h			XXh
2CCAh			XXh
2CCBh			XXh
2CCCh			XXh
2CCDh			XXh
2CCEh			XXh
2CCFh			XXh
2CD0h	DTC Control Data 18	DTCD18	XXh
2CD1h			XXh
2CD2h			XXh
2CD3h			XXh
2CD4h			XXh
2CD5h			XXh
2CD6h			XXh
2CD7h			XXh
	DTC Control Data 10	DTCD19	XXh
2CD8h	DTC Control Data 19	рісыя	
2CD9h			XXh
2CDAh			XXh
2CDBh			XXh
2CDCh			XXh
2CDDh			XXh
2CDEh			XXh
2CDFh			XXh
2CE0h	DTC Control Data 20	DTCD20	XXh
2CE1h			XXh
2CE2h			XXh
2CE3h			XXh
2CE4h			XXh
2CE5h			XXh
2CE6h			XXh
2CE7h			XXh
2CE8h	DTC Control Data 21	DTCD21	XXh
	DIO CONTO Data 21	DICDZI	
2CE9h			XXh
2CEAh			XXh
2CEBh			XXh
2CECh			XXh
2CEDh			XXh
2CEEh			XXh
2CEFh			XXh

X : Undefined
Note:

1. The blank areas are reserved and cannot be accessed by users.

SFR Information (12) (1) **Table 4.12** 

Address	Register	Symbol	After reset
2CF0h	DTC Control Data 22	DTCD22	XXh
2CF1h			XXh
2CF2h			XXh
2CF3h			XXh
2CF4h			XXh
2CF5h			XXh
2CF5f1			
2CF6h			XXh
2CF7h			XXh
2CF8h	DTC Control Data 23	DTCD23	XXh
2CF9h			XXh
2CFAh			XXh
2CFBh			XXh
2CFCh			XXh
2CFDh			XXh
2CFEh			XXh
2CFFh			XXh
2D00h			AAII
2D01h			
<u> </u>			
2E00h	CAN0 Mailbox 0 : Message ID	C0MB0	XXXX XXXXh
2E01h			<b> </b>
2E02h			
2E03h			<b> </b>
2E04h		1	
2E05h	CAN0 Mailbox 0 : Data length	1	XXh
2E06h	CANO Mailbox 0 : Data field	1	XXXX XXXX
2E07h	Of the mailbox o . Data field		
2E08h			XXXX XXXXh
2E09h			
2E0Ah			
2E0Bh			
2E0Ch			
2E0Dh			
2E0Eh	CAN0 Mailbox 0 : Time stamp		XXXXh
2E0Fh	,		
2E10h	CAN0 Mailbox 1 : Message ID	C0MB1	XXXX XXXXh
2E11h	O THO Malibox 1 : Moodago 15	COMBI	700007000011
2E12h			
2E13h			
2E14h			
2E15h	CAN0 Mailbox 1 : Data length		XXh
2E16h	CAN0 Mailbox 1 : Data field		XXXX XXXX
2E17h			XXXX XXXXh
2E18h			
2E19h			<b> </b>
2E1Ah			<b> </b>
2E1Bh			<b> </b>
2E1Ch			<b> </b>
2E1Dh			
	CANIO Maille and A. Timo a stance		VVVVI
2E1Eh	CAN0 Mailbox 1 : Time stamp		XXXXh
2E1Fh			
	CAN0 Mailbox 2 : Message ID	C0MB2	XXXX XXXXh
2E21h			
2E22h			<b> </b>
2E23h			<b> </b>
2E24h		1	
2E25h	CAN0 Mailbox 2 : Data length	1	XXh
2E26h	CANO Mailbox 2 : Data field	1	XXXX XXXX
2E27h	Of the mailbox 2 . Data field		
			XXXX XXXXh
2E28h			
2E29h			
2E2Ah			
2E2Bh			
2E2Ch			
2E2Dh			
2E2Eh	CAN0 Mailbox 2 : Time stamp	1	XXXXh
2E2Fh	p		
Y : Undefined		l	I.

X : Undefined
NOTES:

1. The blank areas are reserved and cannot be accessed by users.

**Table 4.13** SFR Information (13) (1)

Addrage	` ,		
Address	Register	Symbol	After reset
	CAN0 Mailbox 3 : Message ID	C0MB3	XXXX XXXXh
2E31h			
2E32h			
2E33h			
2E34h			
	CAN0 Mailbox 3 : Data length		XXh
2E36h	CANO Mailbox 3 : Data field		XXXX XXXX
2E37h	CANO IVIAIIDOX 3 . Data lieiu		
			XXXX XXXXh
2E38h			
2E39h			
2E3Ah			
2E3Bh			
2E3Ch			
2E3Dh			
2E3Eh	CAN0 Mailbox3 : Time stamp		XXXXh
2E3Fh	·		
	CAN0 Mailbox4 : Message ID	C0MB4	XXXX XXXXh
2E41h	- · · · · · · · · · · · · · · · · · · ·	332 .	
2E42h			
2E43h			
2E44h	OANOM 'II. A. D. I. L II.		200
2E45h	CAN0 Mailbox4 : Data length		XXh
	CAN0 Mailbox4 : Data field		XXXX XXXX
2E47h			XXXX XXXXh
2E48h			
2E49h			
2E4Ah			
2E4Bh			
2E4Ch			
2E4Dh			
	CANO Mailhayd - Time atoms		VVVVh
	CAN0 Mailbox4 : Time stamp		XXXXh
2E4Fh	0.110.11.11		2000/2000
	CAN0 Mailbox5 : Message ID	C0MB5	XXXX XXXXh
2E51h			
2E52h			
2E53h			
2E54h			
2E55h	CAN0 Mailbox5 : Data length		XXh
2E56h	CAN0 Mailbox5 : Data length CAN0 Mailbox5 : Data field		XXXX XXXX
2E57h	O II TO MAINDOND . Data licia		
			XXXX XXXXh
2E58h			
2E59h			
2E5Ah			
2E5Bh			
2E5Ch			
2E5Dh			
	CAN0 Mailbox5 : Time stamp		XXXXh
2E5Fh			1
	CAN0 Mailbox6 : Message ID	C0MB6	XXXX XXXXh
2E61h	ON WAINDONG . MICOGAGO ID	COMIDO	7000700011
2E62h			
2E63h			
2E64h			
2E65h	CAN0 Mailbox6 : Data length		XXh
	CAN0 Mailbox6 : Data field		XXXX XXXX
2E66h			XXXX XXXXh
2E66h			
2E66h 2E67h 2E68h			
2E66h 2E67h 2E68h 2E69h			
2E66h 2E67h 2E68h 2E69h 2E6Ah			
2E66h 2E67h 2E68h 2E69h 2E6Ah 2E6Bh			
2E66h 2E67h 2E68h 2E69h 2E6Ah 2E6Bh 2E6Ch			
2E66h 2E67h 2E68h 2E69h 2E6Ah 2E6Bh 2E6Ch 2E6Dh			
2E66h 2E67h 2E68h 2E69h 2E6Ah 2E6Bh 2E6Ch 2E6Dh	CAN0 Mailbox6 : Time stamp		XXXXh

X: Undefined
NOTES:

1. The blank areas are reserved and cannot be accessed by users.

**Table 4.14** SFR Information (14) (1)

Address	Register	Symbol	After reset
2E70h	CAN0 Mailbox7 : Message ID	C0MB7	XXXX XXXXh
2E71h	_		
2E72h			
	_		
2E73h			
2E74h			
2E75h	CAN0 Mailbox7 : Data length		XXh
2E76h	CAN0 Mailbox7 : Data field		XXXX XXXX
2E77h			XXXX XXXXh
2E78h	-		^^^
	_		
2E79h			
2E7Ah			
2E7Bh			
2E7Ch			
2E7Dh	-		
2E7Eh	CAN0 Mailbox7 : Time stamp		XXXXh
	CANO Malibox7 . Time stamp		^^^
2E7Fh			
2E80h	CAN0 Mailbox8 : Message ID	C0MB8	XXXX XXXXh
2E81h			
2E82h	7		
2E83h	†		
	<u> </u>		
2E84h			200
2E85h	CAN0 Mailbox8 : Data length		XXh
2E86h	CAN0 Mailbox8 : Data field		XXXX XXXX
2E87h			XXXX XXXXh
2E88h	†		7000700011
2E89h	+		
	4		
2E8Ah	_		
2E8Bh			
2E8Ch			
2E8Dh	7		
2E8Eh	CAN0 Mailbox8 : Time stamp		XXXXh
2E8Fh	- Orange Maliboxo . Time Stamp		AAAAII
			100000000
2E90h	CAN0 Mailbox9 : Message ID	C0MB9	XXXX XXXXh
2E91h			
2E92h			
2E93h	†		
2E94h	CAND Malle O. Balla Israella		NO.
2E95h	CAN0 Mailbox9 : Data length		XXh
2E96h	CAN0 Mailbox9 : Data field		XXXX XXXX
2E97h			XXXX XXXXh
2E98h	7		70001700011
2E99h	+		
	4		
2E9Ah	4		
2E9Bh			
2E9Ch			
2E9Dh			
2E9Eh	CAN0 Mailbox9 : Time stamp		XXXXh
2E9Fh	- Cristo Maliboxo . Tillio Starrip		700011
259511	CANIO MASSILLA AO AMARANA ID	2011210	1000/1000
2EA0h	CAN0 Mailbox10 : Message ID	C0MB10	XXXX XXXXh
2EA1h			
2EA2h			
2EA3h	1		
2EA4h			
	CANO Mailhay 10 + Data langth		VVb
2EA5h	CAN0 Mailbox10 : Data length		XXh
2EA6h	CAN0 Mailbox10 : Data field		XXXX XXXX
2EA7h			XXXX XXXXh
2EA8h	7		,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,
2EA9h	+		
	4		
2EAAh			
2EABh			
2EACh			
2EADh	†		
2EAEh	CAN0 Mailbox10 : Time stamp		XXXXh
	- CANO IVIAIIDOX TO . TITTLE STATILE		^^^1
2EAFh			
V . I lastafia			

X : Undefined
NOTES:

1. The blank areas are reserved and cannot be accessed by users.

**Table 4.15** SFR Information (15) (1)

A 1.1	Desire.	1 0 11	A 6
Address	Register	Symbol	After reset
2EB0h	CAN0 Mailbox11 : Message ID	C0MB11	XXXX XXXXh
2EB1h			
2EB2h			
2EB3h			
2EB4h			
2EB5h	CAN0 Mailbox11 : Data length		XXh
2EB6h	CAN0 Mailbox11 : Data field		XXXX XXXX
2EB7h	O'NO Wallbox 11 : Bata licia		
2EB8h	-		XXXX XXXXh
2EB9h			
2EBAh			
2EBBh			
2EBCh			
2EBDh			
2EBEh	CAN0 Mailbox11 : Time stamp		XXXXh
2EBFh			
2EC0h	CAN0 Mailbox12 : Message ID	C0MB12	XXXX XXXXh
2EC1h	· · · · · · · · · · · · · · · · · · ·		
2EC2h	1		
2EC3h	1		
2EC4h			
	CANO Mailhayd 2 - Data langth		VVb
2EC5h	CAN0 Mailbox12 : Data length		XXh
2EC6h	CAN0 Mailbox12 : Data field		XXXX XXXX
2EC7h			XXXX XXXXh
2EC8h			
2EC9h			
2ECAh			
2ECBh			
2ECCh			
2ECDh	1		
2ECEh	CAN0 Mailbox12 : Time stamp		XXXXh
2ECFh	OANO Mailbox 12. Hille Staffly		^^^
	CANO Mailhay 12 - Massaga ID	COMPAG	VVVV VVVVL
2ED0h	CAN0 Mailbox13 : Message ID	C0MB13	XXXX XXXXh
2ED1h			
2ED2h			
2ED3h			I
2ED4h			
2ED5h	CAN0 Mailbox13 : Data length		XXh
2ED6h	CAN0 Mailbox13 : Data length CAN0 Mailbox13 : Data field		XXXX XXXX
2ED7h			XXXX XXXXh
2ED8h	1		^^^^ ^^^
2ED9h	1		
	-		
2EDAh	-		
2EDBh			
2EDCh			
2EDDh			
2EDEh	CAN0 Mailbox13 : Time stamp		XXXXh
2EDFh			
2EE0h	CAN0 Mailbox14 : Message ID	C0MB14	XXXX XXXXh
2EE1h	· · · · · · · · · · · · · · · · · · ·		
2EE2h	1		
2EE3h	1		
		<del></del>	
2EE4h	CANO Mailbay 14 : Data longth		VVh
2EE5h	CANO Mailbox14: Data length		XXh
2EE6h	CAN0 Mailbox14 : Data field		XXXX XXXX
2EE7h			XXXX XXXXh
2EE8h			
2EE9h			
	7		
2EEAh			
2EEBh			
2EEBh 2EECh			
2EEBh 2EECh 2EEDh	CANO Mailhav14 : Time stamp		VVVVh
2EEBh 2EECh	CAN0 Mailbox14 : Time stamp		XXXXh

X : Undefined
NOTES:

1. The blank areas are reserved and cannot be accessed by users.

**Table 4.16** SFR Information (16) (1)

Address	Register	Symbol	After reset
2EF0h	CAN0 Mailbox15 : Message ID	COMB15	XXXX XXXXh
2EF1h	S. 1.15 Malibox 15 : Modolago 15	COMETO	7000700011
2EF2h	1	1	
2EF3h	1		
2EF4h		<del></del>	
2EF5h	CAN0 Mailbox15 : Data length	<del></del>	XXh
2EF6h	CANO Mailbox15 : Data field		XXXX XXXX
2EF7h	S. 1.15 Mailbox 15 . Bata Hold	1	XXXX XXXXh
2EF8h			****
2EF9h	4	1	
2EFAh	-		
2EFBh	-		
2EFCh	-		
2EFDh	-		
2EFEh	CAN0 Mailbox15 : Time stamp		XXXXh
2EFFh	CANO Malibox 13. Time Stamp		XXXXII
2F00h		<u> </u>	
2F01h			+
2F02h		<u> </u>	
2F03h			
2F04h			
2F04f1			+
2F05h			+
2F06f1			+
2F07h 2F08h			+
2F08h			+
2F09h 2F0Ah		<del></del>	+
			+
2F0Bh 2F0Ch		<del></del>	+
1			+
2F0Dh			+
2F0Eh			+
2F0Fh	CANO Mask Degister 0	COMICEO	VVVV VVVI
2F10h	CAN0 Mask Register 0	C0MKR0	XXXX XXXXh
2F11h			
2F12h	4	1	
2F13h	CANO Mark Desister 4	001//2/	LYANAY YARAH
2F14h	CAN0 Mask Register 1	C0MKR1	XXXX XXXXh
2F15h	4		
2F16h	4	1	
2F17h			1,000,000,000
2F18h	CAN0 Mask Register 2	C0MKR2	XXXX XXXXh
2F19h	1	1	
2F1Ah			
2F1Bh			1000/1000
2F1Ch	CAN0 Mask Register 3	C0MKR3	XXXX XXXXh
2F1Dh			
2F1Eh			
2F1Fh			
2F20h	CAN0 FIFO Received ID Compare Register 0	C0FIDCR0	XXXX XXXXh
2F21h			
2F22h			
2F23h			
2F24h	CAN0 FIFO Received ID Compare Register 1	C0FIDCR1	XXXX XXXXh
2F25h			
2F26h		1	
2F27h			
2F28h			
2F29h			
2F2Ah	CAN0 Mask Invalid Register	C0MKIVLR	XXXXh
2F2Bh			
2F2Ch			
2F2Dh			
2F2Eh	CAN0 Mailbox Interrupt Enable Register	COMIER	XXXXh
2F2Fh	1		
2F30h	CAN0 Message Control Register 0	C0MCTL0	00h
2F31h	CAN0 Message Control Register 1	C0MCTL1	00h
2F32h	CAN0 Message Control Register 2	C0MCTL2	00h
2F33h	CAN0 Message Control Register 3	C0MCTL3	00h
2F34h	CANO Message Control Register 4	C0MCTL4	00h
2F35h	CAN0 Message Control Register 5	C0MCTL5	00h
2F36h	CANO Message Control Register 6	C0MCTL6	00h
2F37h	CANO Message Control Register 7	COMCTL7	00h
2F38h	CANO Message Control Register 8	COMCTL8	00h
2F39h	CANO Message Control Register 9	COMCTL9	00h
2F39II	CANO Message Control Register 10	COMCTL9	00h
X : Undefined		COMOTETO	10011

X : Undefined

NOTES:

1. The blank areas are reserved and cannot be accessed by users.

SFR Information (17) <sup>(1)</sup> **Table 4.17** 

Address	Register	Symbol	After reset	
2F3Bh	CAN0 Message Control Register 11	C0MCTL11	00h	
2F3Ch	CAN0 Message Control Register 12	C0MCTL12	00h	
2F3Dh	CAN0 Message Control Register 13	C0MCTL13	00h	
2F3Eh	CAN0 Message Control Register 14	C0MCTL14	00h	
2F3Fh	CAN0 Message Control Register 15	C0MCTL15	00h	
2F40h	CAN0 Control Register	C0CTLR	0000 0101b	
2F41h			0000 0000b	
2F42h	CAN0 Status Register	COSTR	0000 0101b	
2F43h	1		0000 0000b	
2F44h	CAN0 Bit Configuration Register	C0BCR	00 0000h	
2F45h	1			
2F46h				
2F47h				
2F48h	CAN0 Receive FIFO Control Register	C0RFCR	1000 0000b	
2F49h	CAN0 Receive FIFO Pointer Control Register	C0RFPCR	XXh	
2F4Ah	CAN0 Transmit FIFO Control Register	C0TFCR	1000 0000b	
2F4Bh	CAN0 Transmit FIFO Pointer Control Register	C0TFPCR	XXh	
2F4Ch	CAN0 Error Interrupt Enable Register	C0EIER	00h	
2F4Dh	CAN0 Error Interrupt Factor Judge Register	C0EIFR	00h	
2F4Eh	CAN0 Reception Error Count Register	C0RECR	00h	
2F4Fh	CAN0 Transmission Error Count Register	C0TECR	00h	
2F50h	CAN0 Error Code Store Register	C0ECSR	00h	
2F51h	CAN0 Channel Search Support Register	C0CSSR	XXh	
2F52h	CANO Mailbox Search Status Register	COMSSR	1000 0000b	
2F53h	CAN0 Mailbox Search Mode Register	COMSMR	XXXX XX00b	
2F54h	CAN0 Time Stamp Register	COTSR	0000h	
2F55h				
2F56h	CAN0 Acceptance Filter Support Register	C0AFSR	XXXXh	
2F57h	1			
2F58h	CAN0 Test Control Register	C0TCR	00h	
:		1.0500	10110	
FFDBh	Option Function Select Register 2	OFS2	(Note 2)	
FFFFh	Option Function Select Register	IOFS	(Note 2)	
FFFFh	Option Function Select Register	OFS	(Note 2)	

X: Undefined


NOTES:

1. The blank areas are reserved and cannot be accessed by users.

2. This register cannot be changed by a program. Use a flash programmer to write to it.

# **Package Dimensions**

Diagrams showing the latest package dimensions and mounting information are available in the "Packages" section of the Renesas Technology website.



REVISION HISTORY	R8C/34E Group, R8C/34F Group, R8C/34G Group, R8C/34H Group
REVISION HISTORY	Shortsheet

Rev.	Date		Description
ixev.	Date	Page	Summary
0.10	Apr 17, 2008	_	First Edition issued

All trademarks and registered trademarks are the property of their respective owners.

Renesas Technology Corp. sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

- Renesas lechnology Corp. Sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan Notes:

  1. This document is provided for reference purposes only so that Renesas customers may select the appropriate Renesas products for their use. Renesas neither makes warrantes or representations with respect to the accuracy or completeness of the information in this document nor grants any license to any intellectual property girbs to any other rights of representations with respect to the information in this document in this document of the purpose of the respect to the information in this document in the product data, diagrams, charts, programs, algorithms, and application circuit examples.

  3. You should not use the products of the technology described in this document for the purpose of military use. When exporting the products or technology described herein, you should follow the applicable export control laws and regulations, and procedures required by such laws and regulations, and procedures required by such laws and regulations, and procedures required by such laws and regulations, and procedures required by such laws and regulations, and procedures required by such laws and regulations, and procedures required by such laws and regulations, and procedures required by such laws and regulations, and procedures required by such laws and regulations, and procedures required by such laws and regulations, and procedures required by such laws and regulations, and procedures required by such laws and regulations, and procedures required by such laws and regulations, and procedures required to change without any plan protein. Before purchasing or using any Renesas products listed in this document, in the such procedure in the procedure of the development of the development of the development of the procedure of the development of the development of the development of the development of the development of the development of the development of the development of the development of the de



## **RENESAS SALES OFFICES**

http://www.renesas.com

Refer to "http://www.renesas.com/en/network" for the latest and detailed information.

### Renesas Technology America, Inc.

450 Holger Way, San Jose, CA 95134-1368, U.S.A Tel: <1> (408) 382-7500, Fax: <1> (408) 382-7501

Renesas Technology Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.
Tel: <44> (1628) 585-100, Fax: <44> (1628) 585-900

Renesas Technology (Shanghai) Co., Ltd.
Unit 204, 205, AZIACenter, No.1233 Lujiazui Ring Rd, Pudong District, Shanghai, China 200120 Tel: <86> (21) 5877-1818, Fax: <86> (21) 6887-7858/7898

Renesas Technology Hong Kong Ltd.
7th Floor, North Tower, World Finance Centre, Harbour City, Canton Road, Tsimshatsui, Kowloon, Hong Kong Tel: <852> 2265-6688, Fax: <852> 2377-3473

**Renesas Technology Taiwan Co., Ltd.** 10th Floor, No.99, Fushing North Road, Taipei, Taiwan Tel: <886> (2) 2715-2888, Fax: <886> (2) 3518-3399

Renesas Technology Singapore Pte. Ltd.
1 Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632 Tel: <65> 6213-0200, Fax: <65> 6278-8001

Renesas Technology Korea Co., Ltd. Kukje Center Bldg. 18th Fl., 191, 2-ka, Hangang-ro, Yongsan-ku, Seoul 140-702, Korea Tel: <82> (2) 796-3115, Fax: <82> (2) 796-2145

Renesas Technology Malaysia Sdn. Bhd
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No.18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia Tel: <603> 7955-9390, Fax: <603> 7955-9510