


RX23E-B Group

Analog Front End Typical Characteristics

Overview

This document shows typical analog characteristics of 24-bit Δ - Σ A/D converter (DSAD), 16-bit D/A converter (DA) and analog front end (AFE) in RX23E-B.



Target device

RX23E-B

The analog characteristics in this document are the evaluation results of typical samples and are for reference.

Contents

1. RX23E-B Analog Front End Features	3
2. 24-bit Delta-Sigma A/D Converter	4
2.1 Noise histogram, Plot of Noise	4
2.2 RMS noise - Date rate	7
2.3 Effective resolution - Date rate	7
2.4 Noise table	8
2.5 Integral nonlinearity error	12
2.6 Integral nonlinearity error temperature drift	14
2.7 Offset error histogram	15
2.8 Offset error temperature drift	16
2.9 Offset error - Input common mode voltage	17
2.10 Gain error histogram	18
2.11 Gain error temperature drift	19
2.12 RMS noise - Input voltage	20
2.13 RMS noise Reference buffer dependence histogram	21
2.14 RMS noise - Reference differential input voltage	25
2.15 Analog input current	26
2.16 Noise histogram, Plot of Noise (High-Voltage Inputs)	27
2.17 RMS noise - Date rate (High-Voltage Inputs)	29
2.18 Effective resolution - Date rate (High-Voltage Inputs)	29
2.19 Noise table (High-Voltage Inputs)	30
2.20 Integral nonlinearity error (High-Voltage Inputs)	34
2.21 Analog input current (High-Voltage Inputs)	34
3. Voltage Reference	35
4. Temperature sensor	35
5. Excitation Current Source	36
6. External reference input	37
7. 16-Bit D/A Converter	38
8. Operating current	39







1. RX23E-B Analog Front End Features







- One 24-bit delta-sigma A/D converter
- A/D converter with up to 24-bit effective resolution (gain=1, output data rate=3.8SPS)
- High-precision programmable gain instrumentation amplifier
11nVRMS (gain=128, output data rate=3.8SPS)
- Rail-to-rail programmable gain instrumentation amplifier(gain=1 to 128)
- Programmable data rate : 3.8SPS to 125kSPS (fMOD=4MHz)
- Offset drift 4nV/°C (gain=64 to 128)
- Gain drift 1ppm/°C (gain=1 to 16 (PGA enable))
- Up to eight differential inputs, 16 single-ended inputs
- Four types of digital filters
 - Fourth-order sinc filter
 - Fourth-order sinc filter + fourth-order sinc filter
 - Fifth-order sinc filter
 - Fifth-order sinc filter + first-order sinc filter
- Simultaneous 50Hz/60Hz rejection (output data rate=10, 54SPS)
- Offset error and gain error calibration
- ± 10 -V input pins
- Delta-sigma A/D input disconnect detection assist
- Delta-sigma A/D reference voltage external input
- Voltage reference output voltage : 2.5V, temperature drift : 8ppm/°C ($T_a = -40$ to $+85^\circ\text{C}$),
output current: ± 10 mA
- Excitation current sources : Up to two
Output current : 50 μA to 1000 μA , current matching: $\pm 0.2\%$,
drift matching: 5 ppm/°C
- Bias voltage generator output voltage : $(\text{AVCC0} + \text{AVSS0})/2$
- Temperature sensor : Accuracy $\pm 5^\circ\text{C}$
- Low-side switch : 10 Ω on-resistance
- Low power-supply-voltage detectors
- Delta-sigma A/D input voltage fault detectors
- Delta-sigma A/D reference voltage fault detectors and disconnect detectors
- Excitation current source disconnect detectors
- High-voltage analog common input disconnect detector
- 16-bit D/A converter
 - One channel
 - DNL= ± 1 LSB, INL= ± 5 LSB (max, VREFH $\geq 4.5\text{V}$)





2. 24-bit Delta-Sigma A/D Converter

2.1 Noise histogram, Plot of Noise

AVCC0=5V, Ta=25°C, f_{MOD}=4MHz, V_{ID}=0V, External V_{REF}=2.5V, Reference buffer disabled









2.2 RMS noise - Date rate

AVCC0=5V, Ta=25°C, fMOD=4MHz, V_{ID}=0V, External VREF=2.5V, Reference buffer disabled



2.3 Effective resolution - Date rate

AVCC0=5V, Ta=25°C, fMOD=4MHz, V_{ID}=0V, External VREF=2.5V, Reference buffer disabled



2.4 Noise table

AVCC0=5V, Ta=25°C, fMOD=4MHz, V_{ID}=0V, Sinc⁵ filter or Sinc⁵+Sinc¹ filter, External VREF=2.5V, Reference buffer disabled

RMS noise[μVrms] (Peak-to-peak noise[μVpp])

Data rate [SPS]	OSR	Gain=1 (Bypass)	Gain=1 (BUF)	Gain=1 (PGA)	Gain=2	Gain=4	Gain=8	Gain=16	Gain=32	Gain=64	Gain=128
3.8	1048576	0.165 (1.00)	0.194 (1.34)	0.203 (1.34)	0.174 (1.17)	0.093 (0.67)	0.042 (0.33)	0.027 (0.19)	0.020 (0.15)	0.017 (0.13)	0.017 (0.13)
10.0	399872	0.243 (1.32)	0.268 (1.76)	0.284 (1.97)	0.234 (1.76)	0.121 (0.88)	0.067 (0.47)	0.040 (0.27)	0.030 (0.23)	0.027 (0.21)	0.027 (0.19)
50.1	79872	0.481 (3.29)	0.534 (3.84)	0.573 (3.84)	0.481 (3.71)	0.249 (1.79)	0.137 (1.10)	0.085 (0.62)	0.068 (0.47)	0.062 (0.46)	0.060 (0.44)
54	73728	0.502 (3.87)	0.561 (4.46)	0.597 (4.76)	0.500 (3.87)	0.263 (1.93)	0.141 (1.12)	0.089 (0.69)	0.070 (0.50)	0.064 (0.48)	0.062 (0.50)
60	66560	0.529 (3.95)	0.594 (3.95)	0.637 (4.61)	0.529 (3.95)	0.271 (2.14)	0.151 (1.11)	0.094 (0.72)	0.074 (0.55)	0.067 (0.51)	0.064 (0.48)
100	39936	0.663 (4.67)	0.732 (5.22)	0.788 (6.04)	0.675 (5.08)	0.348 (2.61)	0.191 (1.41)	0.120 (0.94)	0.094 (0.70)	0.087 (0.65)	0.084 (0.65)
977	4096	1.931 (14.1)	2.216 (15.9)	2.403 (18.7)	2.067 (15.5)	1.078 (8.33)	0.599 (4.50)	0.384 (2.89)	0.316 (2.51)	0.293 (2.22)	0.277 (2.06)
1953	2048	2.697 (20.1)	3.050 (23.1)	3.325 (27.6)	2.896 (22.9)	1.489 (10.7)	0.832 (6.59)	0.535 (4.00)	0.442 (3.27)	0.402 (2.89)	0.390 (2.98)
3906	1024	3.636 (27.9)	4.098 (31.8)	4.507 (31.6)	3.938 (30.7)	2.052 (15.4)	1.145 (8.83)	0.740 (5.53)	0.602 (4.63)	0.563 (4.03)	0.537 (4.26)
15625	256	5.226 (40.2)	5.936 (48.0)	6.801 (50.5)	5.927 (47.4)	3.170 (24.2)	1.791 (13.3)	1.154 (8.68)	0.988 (7.57)	0.921 (6.94)	0.884 (6.67)
17857	224	6.076 (45.4)	6.764 (48.9)	7.896 (59.1)	6.624 (47.8)	3.771 (28.9)	2.376 (17.4)	1.721 (12.8)	1.417 (11.3)	1.205 (9.54)	1.012 (7.93)
31250	128	8.214 (60.2)	8.876 (66.4)	10.65 (78.2)	9.046 (67.3)	5.059 (39.4)	3.158 (22.8)	2.311 (19.9)	1.936 (13.8)	1.661 (12.9)	1.399 (10.8)
41667	96	9.363 (67.5)	10.27 (78.1)	12.50 (95.7)	10.84 (83.0)	6.065 (45.2)	3.816 (28.4)	2.743 (20.7)	2.314 (16.7)	2.002 (15.5)	1.699 (13.5)
62500	64	11.76 (87.5)	13.09 (95.4)	16.36 (126)	14.50 (106)	8.139 (57.6)	4.996 (37.5)	3.531 (27.1)	3.071 (22.7)	2.638 (21.0)	2.364 (16.9)
125000	32	63.20 (468)	64.38 (472)	66.39 (495)	39.73 (320)	21.06 (156)	11.65 (88.4)	7.214 (58.2)	5.870 (48.2)	5.167 (40.5)	4.829 (39.9)

Effective resolution [Bits] (Noise-free resolution [Bits])

Data rate [SPS]	OSR	Gain=1 (Bypass)	Gain=1 (BUF)	Gain=1 (PGA)	Gain=2	Gain=4	Gain=8	Gain=16	Gain=32	Gain=64	Gain=128
3.8	1048576	24.0 (22.2)	24.0 (21.8)	24.0 (21.8)	23.8 (21.0)	23.7 (20.8)	23.8 (20.8)	23.4 (20.7)	22.9 (20.0)	22.1 (19.2)	21.2 (18.2)
10.0	399872	24.0 (21.9)	24.0 (21.4)	24.0 (21.3)	23.3 (20.4)	23.3 (20.4)	23.2 (20.4)	22.9 (20.1)	22.3 (19.4)	21.4 (18.5)	20.5 (17.7)
50.1	79872	23.3 (20.5)	23.2 (20.3)	23.1 (20.3)	22.3 (19.4)	22.3 (19.4)	22.1 (19.1)	21.8 (18.9)	21.1 (18.3)	20.3 (17.4)	19.3 (16.4)
54	73728	23.2 (20.3)	23.1 (20.1)	23.0 (20.0)	22.3 (19.3)	22.2 (19.3)	22.1 (19.1)	21.7 (18.8)	21.1 (18.2)	20.2 (17.3)	19.3 (16.3)
60	66560	23.2 (20.3)	23.0 (20.3)	22.9 (20.0)	22.2 (19.3)	22.1 (19.2)	22.0 (19.1)	21.7 (18.7)	21.0 (18.1)	20.1 (17.2)	19.2 (16.3)
100	39936	22.8 (20.0)	22.7 (19.9)	22.6 (19.7)	21.8 (18.9)	21.8 (18.9)	21.6 (18.8)	21.3 (18.3)	20.7 (17.8)	19.8 (16.9)	18.8 (15.9)
977	4096	21.3 (18.4)	21.1 (18.3)	21.0 (18.0)	20.2 (17.3)	20.1 (17.2)	20.0 (17.1)	19.6 (16.7)	18.9 (15.9)	18.0 (15.1)	17.1 (14.2)
1953	2048	20.8 (17.9)	20.6 (17.7)	20.5 (17.5)	19.7 (16.7)	19.7 (16.8)	19.5 (16.5)	19.2 (16.3)	18.4 (15.5)	17.6 (14.7)	16.6 (13.7)
3906	1024	20.4 (17.4)	20.2 (17.3)	20.1 (17.3)	19.3 (16.3)	19.2 (16.3)	19.1 (16.1)	18.7 (15.8)	18.0 (15.0)	17.1 (14.2)	16.1 (13.2)
15625	256	19.9 (16.9)	19.7 (16.7)	19.5 (16.6)	18.7 (15.7)	18.6 (15.7)	18.4 (15.5)	18.0 (15.1)	17.3 (14.3)	16.4 (13.6)	15.4 (12.5)
17857	224	19.7 (16.8)	19.5 (16.6)	19.3 (16.4)	18.5 (15.7)	18.3 (15.4)	18.0 (15.1)	17.5 (14.6)	16.8 (13.8)	16.0 (13.0)	15.2 (12.3)
31250	128	19.2 (16.3)	19.1 (16.2)	18.8 (16.0)	18.1 (15.2)	17.9 (14.8)	17.6 (14.7)	17.0 (13.9)	16.3 (13.5)	15.5 (12.6)	14.8 (11.8)
41667	96	19.0 (16.2)	18.9 (16.0)	18.6 (15.7)	17.8 (14.9)	17.7 (14.8)	17.3 (14.4)	16.8 (13.9)	16.0 (13.2)	15.3 (12.3)	14.5 (11.5)
62500	64	18.7 (15.8)	18.5 (15.7)	18.2 (15.3)	17.4 (14.5)	17.2 (14.4)	16.9 (14.0)	16.4 (13.5)	15.6 (12.8)	14.9 (11.9)	14.0 (11.2)
125000	32	16.3 (13.4)	16.2 (13.4)	16.2 (13.3)	15.9 (12.9)	15.9 (13.0)	15.7 (12.8)	15.4 (12.4)	14.7 (11.7)	13.9 (10.9)	13.0 (9.9)

AVCC0=5V, Ta=25°C, fMOD=4MHz, V_{ID}=0V, Sinc⁴ filter or Sinc⁴+Sinc⁴ filter, External VREF=2.5V, Reference buffer disabled

RMS noise[μVrms] (Peak-to-peak noise[μVpp])


Data rate [SPS]	OSR	Gain=1 (Bypass)	Gain=1 (BUF)	Gain=1 (PGA)	Gain=2	Gain=4	Gain=8	Gain=16	Gain=32	Gain=64	Gain=128
3.8	1048576	0.160 (0.50)	0.168 (1.00)	0.179 (1.00)	0.141 (0.92)	0.061 (0.42)	0.031 (0.23)	0.019 (0.14)	0.014 (0.10)	0.012 (0.09)	0.011 (0.09)
10.0	399872	0.192 (1.24)	0.252 (1.48)	0.236 (1.48)	0.177 (1.24)	0.094 (0.62)	0.047 (0.31)	0.030 (0.20)	0.022 (0.16)	0.019 (0.14)	0.018 (0.14)
50.1	79872	0.359 (2.43)	0.406 (2.73)	0.431 (3.03)	0.352 (2.58)	0.178 (1.29)	0.096 (0.72)	0.059 (0.42)	0.046 (0.34)	0.042 (0.30)	0.041 (0.31)
54	73728	0.346 (2.51)	0.390 (2.72)	0.421 (3.34)	0.352 (2.51)	0.182 (1.41)	0.098 (0.71)	0.062 (0.46)	0.048 (0.35)	0.044 (0.33)	0.042 (0.32)
60	66560	0.387 (2.52)	0.427 (3.15)	0.463 (3.15)	0.374 (2.67)	0.193 (1.34)	0.106 (0.75)	0.065 (0.47)	0.051 (0.37)	0.046 (0.34)	0.044 (0.33)
100	39936	0.470 (3.34)	0.523 (3.64)	0.572 (4.55)	0.469 (3.49)	0.242 (1.74)	0.133 (0.95)	0.083 (0.66)	0.065 (0.47)	0.059 (0.46)	0.057 (0.46)
977	4096	1.407 (10.9)	1.562 (12.9)	1.691 (12.4)	1.442 (11.1)	0.748 (5.90)	0.408 (3.10)	0.256 (1.98)	0.207 (1.54)	0.190 (1.40)	0.181 (1.43)
1953	2048	1.959 (15.9)	2.217 (16.7)	2.406 (17.2)	2.021 (17.0)	1.065 (7.99)	0.591 (4.56)	0.374 (3.00)	0.298 (2.12)	0.272 (2.09)	0.265 (2.06)
3906	1024	2.760 (21.4)	3.114 (22.9)	3.519 (27.1)	3.057 (22.1)	1.592 (11.6)	0.897 (6.78)	0.561 (4.19)	0.462 (3.92)	0.427 (3.18)	0.414 (3.21)
15625	256	5.579 (43.7)	6.185 (45.2)	7.339 (58.1)	6.490 (50.6)	3.422 (25.5)	1.930 (14.1)	1.250 (9.74)	1.070 (7.57)	1.001 (7.56)	0.971 (7.80)
17857	224	6.393 (46.8)	7.098 (52.2)	8.323 (63.1)	7.108 (52.0)	3.909 (30.1)	2.516 (19.5)	1.835 (13.9)	1.507 (11.7)	1.286 (9.67)	1.053 (7.86)
31250	128	8.509 (63.4)	9.342 (71.1)	11.25 (81.2)	9.657 (70.7)	5.429 (40.3)	3.435 (25.4)	2.502 (20.1)	2.084 (16.7)	1.778 (13.8)	1.511 (11.4)
41667	96	9.997 (80.7)	10.97 (81.7)	13.29 (98.6)	11.71 (85.9)	6.542 (49.6)	4.074 (30.6)	2.973 (23.3)	2.471 (18.7)	2.151 (16.2)	1.819 (14.0)
62500	64	14.59 (114)	15.73 (128)	19.50 (143)	16.09 (129)	8.891 (64.6)	5.504 (46.8)	3.850 (29.5)	3.277 (24.5)	2.968 (23.7)	2.613 (21.2)
125000	32	122.6 (851)	122.1 (904)	122.1 (909)	65.91 (489)	34.11 (264)	17.67 (126)	10.10 (72.7)	7.107 (53.2)	5.844 (44.9)	5.301 (40.1)

Effective resolution [Bits] (Noise-free resolution [Bits])

Data rate [SPS]	OSR	Gain=1 (Bypass)	Gain=1 (BUF)	Gain=1 (PGA)	Gain=2	Gain=4	Gain=8	Gain=16	Gain=32	Gain=64	Gain=128
3.8	1048576	24.0 (23.2)	24.0 (22.2)	24.0 (22.2)	24.0 (21.2)	24.0 (21.5)	24.0 (21.4)	23.9 (21.1)	23.4 (20.5)	22.6 (19.7)	22.7 (18.8)
10.0	399872	24.0 (21.9)	24.0 (21.7)	24.0 (21.7)	23.8 (20.9)	23.7 (20.9)	23.6 (20.9)	23.3 (20.6)	22.8 (19.9)	22.0 (19.1)	21.0 (18.1)
50.1	79872	23.7 (21.0)	23.6 (20.8)	23.5 (20.7)	22.8 (19.9)	22.7 (19.9)	22.6 (19.7)	22.3 (19.5)	21.7 (18.8)	20.8 (18.0)	19.9 (16.9)
54	73728	23.8 (20.9)	23.8 (20.8)	23.5 (20.5)	22.8 (19.9)	22.7 (19.8)	22.6 (19.8)	22.3 (19.4)	21.6 (18.8)	20.8 (17.9)	19.8 (16.9)
60	66560	23.6 (20.9)	23.5 (20.6)	23.4 (20.6)	22.7 (19.8)	22.6 (19.8)	22.5 (19.7)	22.2 (19.3)	21.5 (18.7)	20.7 (17.8)	19.8 (16.9)
100	39936	23.3 (20.5)	23.2 (20.4)	23.1 (20.1)	22.3 (19.5)	22.3 (19.5)	22.2 (19.3)	21.8 (18.8)	21.2 (18.3)	20.3 (17.4)	19.4 (16.4)
977	4096	21.8 (18.8)	21.6 (18.6)	21.5 (18.6)	20.7 (17.8)	20.7 (17.7)	20.5 (17.6)	20.2 (17.3)	19.5 (16.6)	18.7 (15.8)	17.7 (14.7)
1953	2048	21.3 (18.3)	21.1 (18.2)	21.0 (18.1)	20.2 (17.2)	20.2 (17.3)	20.0 (17.1)	19.7 (16.7)	19.0 (16.2)	18.1 (15.2)	17.2 (14.2)
3906	1024	20.8 (17.8)	20.6 (17.7)	20.4 (17.5)	19.6 (16.8)	19.6 (16.7)	19.4 (16.5)	19.1 (16.2)	18.4 (15.3)	17.5 (14.6)	16.5 (13.6)
15625	256	19.8 (16.8)	19.6 (16.8)	19.4 (16.4)	18.6 (15.6)	18.5 (15.6)	18.3 (15.4)	17.9 (15.0)	17.2 (14.3)	16.3 (13.3)	15.3 (12.3)
17857	224	19.6 (16.7)	19.4 (16.5)	19.2 (16.3)	18.4 (15.6)	18.3 (15.3)	17.9 (15.0)	17.4 (14.5)	16.7 (13.7)	15.9 (13.0)	15.2 (12.3)
31250	128	19.2 (16.3)	19.0 (16.1)	18.8 (15.9)	18.0 (15.1)	17.8 (14.9)	17.5 (14.6)	16.9 (13.9)	16.2 (13.2)	15.4 (12.5)	14.7 (11.7)
41667	96	18.9 (15.9)	18.8 (15.9)	18.5 (15.6)	17.7 (14.8)	17.5 (14.6)	17.2 (14.3)	16.7 (13.7)	15.9 (13.0)	15.1 (12.2)	14.4 (11.4)
62500	64	18.4 (15.4)	18.3 (15.3)	18.0 (15.1)	17.2 (14.2)	17.1 (14.2)	16.8 (13.7)	16.3 (13.4)	15.5 (12.6)	14.7 (11.7)	13.9 (10.8)
125000	32	15.3 (12.5)	15.3 (12.4)	15.3 (12.4)	15.2 (12.3)	15.2 (12.2)	15.1 (12.3)	14.9 (12.1)	14.4 (11.5)	13.7 (10.8)	12.8 (9.9)

2.5 Integral nonlinearity error (INL)







AVCC0=5V, Ta=25°C, f_{MOD}=4MHz, Sinc4 filter or Sinc4+Sinc4 filter, External V_{REF}=2.5V, Reference buffer disabled



Note 1. The evaluation results for total oversampling ratio=224 are typical characteristics for total oversampling ratio=32 to 224.




Note 2. The evaluation results for total oversampling ratio=256 are typical characteristics for total oversampling ratio=256 to 768.

Note 3. The evaluation results for total oversampling ratio=4096 are typical characteristics for total oversampling ratio=1024 to 1048576.



2.6 Integral nonlinearity error temperature drift

AVCC0=5V, f_{MOD} =4MHz, Sinc4 filter or Sinc4+Sinc4 filter, External V_{REF} =2.5V, Reference buffer disabled









Note 1. The evaluation results for total oversampling ratio=224 are typical characteristics for total oversampling ratio=32 to 224.





Note 2. The evaluation results for total oversampling ratio=256 are typical characteristics for total oversampling ratio=256 to 768.

Note 3. The evaluation results for total oversampling ratio=4096 are typical characteristics for total oversampling ratio=1024 to 1048576.

2.7 Offset error histogram


AVCC0=5V, $T_a=25^{\circ}\text{C}$, $f_{\text{MOD}}=4\text{MHz}$, $V_{\text{ID}}=0\text{V}$, Total oversampling ratio=4096, External $V_{\text{REF}}=2.5\text{V}$, Reference buffer disabled











2.8 Offset error temperature drift

AVCC0=5V, f_{MOD} =4MHz, V_{ID} =0V, Total oversampling ratio=4096, External V_{REF} =2.5V, Reference buffer disabled









2.9 Offset error - Input common mode voltage





AVCC0=5V, $T_a=25^{\circ}\text{C}$, $f_{\text{MOD}}=4\text{MHz}$, $V_{\text{ID}}=0\text{V}$, Total oversampling ratio=4096, External $V_{\text{REF}}=2.5\text{V}$, Reference buffer disabled



2.10 Gain error histogram


AVCC0=5V, Ta=25°C, f_{MOD}=4MHz, Total oversampling ratio=4096, External V_{REF}=2.5V, Reference buffer disabled











2.11 Gain error temperature drift

AVCC0=5V, Ta=25°C, f_{MOD}=4MHz, Total oversampling ratio=4096, External V_{REF}=2.5V, Reference buffer disabled







2.12 RMS noise - Input voltage





AVCC0=5V, Ta=25°C, fMOD=4MHz, Total oversampling ratio=4096, Sinc⁴+Sinc⁴ filter



2.13 RMS noise Reference buffer dependence histogram





AVCC0=5V, Ta=25°C, fMOD=4MHz, V_{ID}=0V, Total oversampling ratio=224, Sinc4+Sinc4 filter, External VREF=2.5V









Note: The evaluation results for total oversampling ratio=224 are typical characteristics for total oversampling ratio=32 to 224.

AVCC0=5V, Ta=25°C, fMOD=4MHz, VID=0V, Total oversampling ratio=4096, Sinc4+Sinc4 filter, External VREF=2.5V











Note: The evaluation results for total oversampling ratio=4096 are typical characteristics for total oversampling ratio=256 to 1048576.



2.14 RMS noise - Reference differential input voltage

AVCC0=5V, Ta=25°C, fMOD=4MHz, V_{ID}=0V, Sinc⁵ filter, Reference buffer disabled



2.15 Analog input current



AVCC0=5V, f_{MOD}=4MHz, Total oversampling ratio=4096





2.16 Noise histogram, Plot of Noise (High-Voltage Inputs)





AVCC0=5V, Ta=25°C, fMOD=4MHz, V_{ID}=0V, External VREF=2.5V, Reference buffer disabled

Gain=0.1(PGA disabled, BUF enabled),
f_{DR}=976.6 SPS, Sinc⁴+Sinc⁴ filter





Gain=0.1(PGA enabled, BUF enabled),
f_{DR}=976.6 SPS, Sinc⁴+Sinc⁴ filter







2.17 RMS noise - Date rate (High-Voltage Inputs)

AVCC0=5V, $T_a=25^\circ\text{C}$, $f_{\text{MOD}}=4\text{MHz}$, $V_{\text{ID}}=0\text{V}$, External VREF=2.5V, Reference buffer disabled



2.18 Effective resolution - Date rate (High-Voltage Inputs)

AVCC0=5V, $T_a=25^\circ\text{C}$, $f_{\text{MOD}}=4\text{MHz}$, $V_{\text{ID}}=0\text{V}$, External VREF=2.5V, Reference buffer disabled



2.19 Noise table (High-Voltage Inputs)

AVCC0=5V, Ta=25°C, fMOD=4MHz, V_{ID}=0V, Sinc⁵ filter or Sinc⁵+Sinc¹ filter, External VREF=2.5V, Reference buffer disabled

RMS noise[μVrms] (Peak-to-peak noise[μVpp])

Data rate [SPS]	OSR	Gain=0.1 (BUF)	Gain=0.1 (PGA)
3.8	1048576	2.656 (18.41)	2.791 (20.08)
10.0	399872	3.379 (24.13)	3.519 (24.13)
50.1	79872	6.349 (43.93)	6.763 (52.18)
54	73728	6.578 (50.57)	7.087 (47.59)
60	66560	7.099 (52.72)	7.519 (56.02)
100	39936	8.744 (63.15)	9.389 (68.66)
977	4096	25.69 (192.4)	29.47 (225.9)
1953	2048	35.69 (289.5)	40.31 (297.9)
3906	1024	47.88 (339.7)	55.15 (431.7)
15625	256	69.04 (513.7)	81.43 (622.5)
17857	224	77.43 (574.2)	103.7 (769.9)
31250	128	102.1 (801.6)	138.9 (1006)
41667	96	117.6 (914.9)	163.3 (1208)
62500	64	148.6 (1131)	208.7 (1504)
125000	32	648 (4767)	701 (5335)

Effective resolution [Bits] (Noise-free resolution [Bits])

Data rate [SPS]	OSR	Gain=0.1 (BUF)	Gain=0.1 (PGA)
3.8	1048576	24.0 (18.1)	24.0 (17.9)
10.0	399872	23.8 (17.7)	23.8 (17.7)
50.1	79872	22.9 (16.8)	22.8 (16.5)
54	73728	22.9 (16.6)	22.8 (16.7)
60	66560	22.7 (16.5)	22.7 (16.4)
100	39936	22.4 (16.3)	22.3 (16.2)
977	4096	20.9 (14.7)	20.7 (14.4)
1953	2048	20.4 (14.1)	20.2 (14.0)
3906	1024	20.0 (13.8)	19.8 (13.5)
15625	256	19.5 (13.2)	19.2 (13.0)
17857	224	19.3 (13.1)	18.9 (12.7)
31250	128	18.9 (12.6)	18.5 (12.3)
41667	96	18.7 (12.4)	18.2 (12.0)
62500	64	18.4 (12.1)	17.9 (11.7)
125000	32	16.2 (10.0)	16.1 (9.9)

AVCC0=5V, Ta=25°C, fMOD=4MHz, V_{ID}=0V, Sinc⁴ filter or Sinc⁴+Sinc⁴ filter, External VREF=2.5V, Reference buffer disabled

RMS noise[μVrms] (Peak-to-peak noise[μVpp])


Data rate [SPS]	OSR	Gain=0.1 (BUF)	Gain=0.1 (PGA)
3.8	1048576	2.285 (13.39)	2.173 (13.39)
10.0	399872	2.871 (19.78)	2.929 (17.31)
50.1	79872	4.815 (33.37)	5.029 (36.40)
54	73728	4.795 (35.52)	4.950 (35.52)
60	66560	5.151 (37.74)	5.404 (37.74)
100	39936	6.322 (48.54)	6.759 (48.54)
977	4096	18.29 (143.9)	19.53 (157.3)
1953	2048	25.45 (189.1)	27.80 (195.8)
3906	1024	36.36 (269.4)	40.47 (311.2)
15625	256	72.33 (547.2)	87.76 (676.0)
17857	224	81.57 (588.1)	110.7 (856.4)
31250	128	108.4 (809.9)	147.3 (1029)
41667	96	124.6 (909.7)	173.6 (1285)
62500	64	175.3 (1322)	233.3 (1760)
125000	32	1274 (8976)	1285 (9287)

Effective resolution [Bits] (Noise-free resolution [Bits])

Data rate [SPS]	OSR	Gain=0.1 (BUF)	Gain=0.1 (PGA)
3.8	1048576	24.0 (18.5)	24.0 (18.5)
10.0	399872	24.0 (17.9)	24.0 (18.1)
50.1	79872	23.3 (17.2)	23.2 (17.1)
54	73728	23.3 (17.1)	23.3 (17.1)
60	66560	23.2 (17.0)	23.1 (17.0)
100	39936	22.9 (16.7)	22.8 (16.7)
977	4096	21.4 (15.1)	21.3 (15.0)
1953	2048	20.9 (14.7)	20.8 (14.6)
3906	1024	20.4 (14.2)	20.2 (14.0)
15625	256	19.4 (13.2)	19.1 (12.9)
17857	224	19.2 (13.1)	18.8 (12.5)
31250	128	18.8 (12.6)	18.4 (12.2)
41667	96	18.6 (12.4)	18.1 (11.9)
62500	64	18.1 (11.9)	17.7 (11.5)
125000	32	15.3 (9.1)	15.2 (9.1)


2.20 Integral nonlinearity error (INL) (High-Voltage Inputs)

AVCC0=5V, Ta=25°C, f_{MOD}=4MHz, Total oversampling ratio=4096, External V_{REF}=2.5V, Reference buffer disabled







2.21 Analog input current (High-Voltage Inputs)

AVCC0=5V, Ta=25°C, f_{MOD}=4MHz, Total oversampling ratio=4096




3. Voltage Reference (VREF)

AVCC0=5V




4. Temperature Sensor

AVCC0=5V





5. Excitation Current Source

AVCC0=5V









6. External reference input

AVCC0=5V, External $V_{REF}=2.5V$





7. 16-Bit D/A Converter


AVCC0=5V




8. Operating current

24bit Delta-Sigma A/D Converter
PGA disabled, BUF disabled24bit Delta-Sigma A/D Converter
PGA enabled, BUF enabled


Analog input buffer




Voltage reference






Temperature sensor



Excitation current source





Revision History

Rev.	Date	Description	
		Page	Summary
1.00	Mar 29, 2024	—	First edition issued.

General Precautions in the Handling of Microprocessing Unit and Microcontroller Unit Products

The following usage notes are applicable to all Microprocessing unit and Microcontroller unit products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

1. Precaution against Electrostatic Discharge (ESD)

A strong electrical field, when exposed to a CMOS device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop the generation of static electricity as much as possible, and quickly dissipate it when it occurs. Environmental control must be adequate. When it is dry, a humidifier should be used. This is recommended to avoid using insulators that can easily build up static electricity.

Semiconductor devices must be stored and transported in an anti-static container, static shielding bag or conductive material. All test and measurement tools including work benches and floors must be grounded. The operator must also be grounded using a wrist strap. Semiconductor devices must not be touched with bare hands. Similar precautions must be taken for printed circuit boards with mounted semiconductor devices.

2. Processing at power-on

The state of the product is undefined at the time when power is supplied. The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the time when power is supplied. In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the time when power is supplied until the reset process is completed. In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the time when power is supplied until the power reaches the level at which resetting is specified.

3. Input of signal during power-off state

Do not input signals or an I/O pull-up power supply while the device is powered off. The current injection that results from input of such a signal or I/O pull-up power supply may cause malfunction and the abnormal current that passes in the device at this time may cause degradation of internal elements. Follow the guideline for input signal during power-off state as described in your product documentation.

4. Handling of unused pins

Handle unused pins in accordance with the directions given under handling of unused pins in the manual. The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of the LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible.

5. Clock signals

After applying a reset, only release the reset line after the operating clock signal becomes stable. When switching the clock signal during program execution, wait until the target clock signal is stabilized. When the clock signal is generated with an external resonator or from an external oscillator during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Additionally, when switching to a clock signal produced with an external resonator or by an external oscillator while program execution is in progress, wait until the target clock signal is stable.

6. Voltage application waveform at input pin

Waveform distortion due to input noise or a reflected wave may cause malfunction. If the input of the CMOS device stays in the area between V_{IL} (Max.) and V_{IH} (Min.) due to noise, for example, the device may malfunction. Take care to prevent chattering noise from entering the device when the input level is fixed, and also in the transition period when the input level passes through the area between V_{IL} (Max.) and V_{IH} (Min.).

7. Prohibition of access to reserved addresses

Access to reserved addresses is prohibited. The reserved addresses are provided for possible future expansion of functions. Do not access these addresses as the correct operation of the LSI is not guaranteed.

8. Differences between products

Before changing from one product to another, for example to a product with a different part number, confirm that the change will not lead to problems. The characteristics of a microprocessing unit or microcontroller unit products in the same group but having a different part number might differ in terms of internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.

7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 October 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan

www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:

www.renesas.com/contact/.