

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

H8/300L SLP Series

Static Driving of the LCD

Introduction

A four-digit number is displayed on an LCD panel using the segment-type LCD control circuit, LCD driver, and power supply circuit of the H8/38024 Series.

Target Device

H8/38024

Contents

1. Specifications	2
2. Description of Functions	2
3. Description of Operation	8
4. Description of Software	9
5. Flowchart.....	12
6. Program Listing	13

1. Specifications

1. Data values in RAM is displayed using the segment-type LCD control circuit, LCD driver, and power supply circuit of the H8/38024 Series.
2. Static driving of LCD is implemented using a single common signal and 32 segment signals.
3. An example of LCD module connection and LCD display for this sample task is shown in figure 1.1.




Figure 1.1 Example of LCD Display

2. Description of Functions

1. In this sample task, the LCD controller/driver is used for LCD display. The features of the LCD controller/driver are described below.
 - Display capacity
 - A. Duty cycle: Static
Internal driver: 32 segments
 - B. Duty cycle: 1/2
Internal driver: 32 segments
 - C. Duty cycle: 1/3
Internal driver: 32 segments
 - D. Duty cycle: 1/4
Internal driver: 32 segments
 - LCD RAM capacity: 16 bytes
 - LCD RAM is word-accessible.
 - Every unit of four segment output pins can be used individually as port pins.
 - The common output pins not used because of the specified duty cycle can be used for common double-buffering (parallel connection).
 - Display is possible in all operating modes other than standby mode.
 - Frame frequency can be selected from among 11 values.
 - A power supply split-resistance is built-in for supply of LCD drive power.
 - When not used, this LCD module alone can be placed in a standby state by the module standby mode.
 - A or B waveform can be selected by software.

2. Figure 2.1 is a block diagram of the LCD controller/driver used in this sample task.




Figure 2.1 Block Diagram of LCD Controller/Driver

3. Functions of the LCD controller/driver are described in table 2.1.

Table 2.1 LCD Controller/Driver Functions

Register/Pin	Function
LCD port control register (LPCR)	LPCR is an 8-bit readable/writable register which selects the duty cycle, the LCD driver, and pin functions. LPCR is initialized to H'00 upon a reset.
LCD control register (LCR)	LCR is an 8-bit readable/writable register which turns on and off the LCD drive power supply, controls display data, and selects the frame frequency. LCR is initialized to H'80 upon a reset.
LCD control register 2 (LCR2)	LCR2 is an 8-bit readable/writable register which controls switching between A and B waveforms. LCR2 is initialized to H'60 upon a reset.
Segment output pins (SEG ₃₂ to SEG ₁)	These are pins used for driving LCD segments; all these pins are multiplexed as port pins (setting is programmable).
Common output pins (COM ₄ to COM ₁)	These are LCD common driving output pins; under static or 1/2-duty cycle driving, they can be used in parallel.
LCD power supply pins (V ₁ , V ₂ , V ₃)	These pins are used when connecting an external bypass capacitor or when using an external power supply circuit.
LCD RAM	Display data is placed here. The relation between the LCD RAM and the display segments differs according to the duty cycle setting. Display is started in this way: after the registers necessary for display have been set, write data in the locations corresponding to the given duty cycle using the same instructions as those for writing to ordinary RAM, and then turn the display on. Word/byte access instructions can be used to set data in the LCD RAM.

4. In this sample task, a 4-digit 7-segment LCD is driven by static driving. Figure 2.2 is a diagram showing the correspondence between segment signals and segments of the 4-digit 7-segment LCD used in this sample task.




Figure 2.2 Correspondence between Segment Signals and Segments on the 4-Digit 7-Segment LCD Used in this Sample Task

5. Figure 2.3 shows the LCD RAM mapping under static driving.




Figure 2.3 LCD RAM Mapping under Static Driving

6. Figure 2.4 shows the relation between the display on the 4-digit 7-segment LCD used in this sample task and data set in the LCD RAM. The numeric characters "1234" is displayed on the 4-digit 7-segment LCD by setting the LCD RAM as shown in figure 2.4.




Figure 2.4 Relation between LCD Display and LCD RAM Settings

7. Figure 2.5 shows the relationship between SEG₁ to SEG₇ display on the 4-digit 7-segment LCD and the corresponding LCD RAM. As the figure 2.5 shows, when the LCD RAM bits for segments 0 to 7 are set to 1, the corresponding segments are lit; when cleared to 0, the corresponding segments are unlit.




Figure 2.5 Relationship between LCD Lit/Unlit States and LCD RAM Settings

Table 2.2 shows examples of display and data for display by SEG1 to SEG7 on the 4-digit 7-segment LCD.

Table 2.2 Example of Display Data

Symbol	Display	Address	Display Data							
			7	6	5	4	3	2	1	0
		H'F740	0	0	0	0	0	0	0	0
-		H'F740	0	0	0	0	0	0	0	1
0		H'F740	0	1	1	1	1	1	1	0
1		H'F740	0	1	0	0	1	0	0	0
2		H'F740	0	0	1	1	1	1	0	1
3		H'F740	0	1	1	0	1	1	0	1
4		H'F740	0	1	0	0	1	0	1	1
5		H'F740	0	1	1	0	0	1	1	1
6		H'F740	0	1	1	1	0	1	1	1
7		H'F740	0	1	0	0	1	1	1	0
8		H'F740	0	1	1	1	1	1	1	1
9		H'F740	0	1	1	0	1	1	1	1
A		H'F740	0	1	0	1	1	1	1	1
B		H'F740	0	0	1	1	0	0	1	1
C		H'F740	0	0	1	1	0	1	1	0
D		H'F740	0	1	1	1	1	0	0	1
E		H'F740	0	0	1	1	0	1	1	1
F		H'F740	0	0	0	1	0	1	1	1

9. Table 2.3 shows assignment of functions in this sample task.

Table 2.3 Function Assignment

Function	Assignment
LPCR	Selects duty cycle, LCD driver, and pin functions.
LCR	Turns LCD drive power supply on and off, controls display data, and selects frame frequency.
LCR2	Switches between A and B waveforms.
SEG ₃₁ to SEG ₂₅ SEG ₂₃ to SEG ₁₇ SEG ₁₅ to SEG ₉ SEG ₇ to SEG ₁	Used as segment driver pins.
COM ₁	Used as a common driver pin.
LCD RAM	Sets the LCD display data.

3. Description of Operation

1. Software settings for LCD display are described below.
 - A. Duty cycle selection
By setting DTS1 and DTS0, duty cycle can be selected from among "static", 1/2, 1/3, and 1/4.
 - B. Segment driver selection
SGS3 to SGS0 are used to select the segment drivers to be used.
 - C. Frame frequency selection
By setting CKS3 to CKS0, the frame frequency can be selected. The frame frequency should be selected according to the LCD panel specifications.
 - D. Selection of A or B waveforms
LCDAB can be used to select either the A or the B waveform for use as the LCD waveform.
2. Figure 3.1 shows the waveforms of segment drive signals, which illustrate the operation of this sample task.




Figure 3.1 Waveforms of Segment Drive Signals

4. Description of Software

4.1 Module

Table 4.1 shows the module in this sample task.

Table 4.1 Description of Modules

Module	Label	Function
Main routine	main	Initializes LCD RAM and LCD controller/driver, enables interrupts, and controls LCD display.

4.2 Arguments

In this sample task, no arguments are used.

4.3 Internal Registers

Table 4.2 shows the internal registers used in this sample task.

Table 4.2 Description of Internal Registers

Register	Function	Address	Setting
LPCR DTS1, DTS0	LCD Port Control Register (Duty Cycle Selection 1, 0) Selects a duty cycle from among "static", 1/2, 1/3, and 1/4 by the settings of DTS1 and DTS0 in combination. When DTS1 = 0 and DTS0 = 0, static drive is selected. When DTS1 = 0 and DTS0 = 1, 1/2 duty cycle is selected. When DTS1 = 1 and DTS0 = 0, 1/3 duty cycle is selected. When DTS1 = 1 and DTS0 = 1, 1/4 duty cycle is selected.	H'FFC0 Bit 7 Bit 6	DTS1 = 0 DTS0 = 0
LPCR CMX	LCD Port Control Register (Common Function Selection) Selects whether the same waveform is output from several pins in order to increase the common driving capacity when common pins are not used with the given duty cycle. If CMX = 0, the same waveform is not output from multiple common pins not used with that duty cycle. If CMX = 1, the same waveform is output from multiple common pins not used with that duty cycle.	H'FFC0 Bit 5	0

Register	Function	Address	Setting
LPCR	<p>SGS3 LCD Port Control Register (Segment Driver Selection)</p> <p>SGS2 Selects the segment driver to be used.</p> <p>SGS1 When SGX = 0, SGS3 = 0, SGS2 = 0, SGS1 = 0 and</p> <p>SGS0 SGS0 = 0, pins SEG₃₂ to SEG₁ function as ports.</p> <p>When SGX = 0, SGS3 = 0, SGS2 = 0, SGS1 = 0 and</p> <p>SGS0 = 1, pins SEG₃₂ to SEG₁ function as ports.</p> <p>When SGX = 0, SGS3 = 0, SGS2 = 0, SGS1 = 1 and</p> <p>SGS0 = *, pins SEG₃₂ to SEG₂₅ function as segment drivers and pins SEG₂₄ to SEG₁ function as ports.</p> <p>When SGX = 0, SGS3 = 0, SGS2 = 1, SGS1 = 0 and</p> <p>SGS0 = *, pins SEG₃₂ to SEG₁₇ function as segment drivers and pins SEG₁₆ to SEG₁ function as ports.</p> <p>When SGX = 0, SGS3 = 0, SGS2 = 1, SGS1 = 1 and</p> <p>SGS0 = *, pins SEG₃₂ to SEG₉ function as segment drivers and pins SEG₈ to SEG₁ function as ports.</p> <p>When SGX = 0, SGS3 = 1, SGS2 = *, SGS1 = * and</p> <p>SGS0 = *, pins SEG₃₂ to SEG₁ function as segment drivers.</p> <p>Note: * Don't care</p>	<p>H'FFC0</p> <p>Bit 3</p> <p>Bit 2</p> <p>Bit 1</p> <p>Bit 0</p>	<p>SGS3 = 1</p> <p>SGS2 = 0</p> <p>SGS1 = 0</p> <p>SGS0 = 0</p>
LCR	<p>PSW LCD Control Register (LCD Drive Power Supply On/Off Control)</p> <p>The LCD drive power supply can be turned off using this bit when LCD display is not used in power-down mode or when an external power supply is used. However, when the ACT bit is cleared to 0 or when in standby mode, the LCD drive power supply is always turned off regardless of setting of this bit.</p> <p>If PSW = 0, the LCD drive power supply is turned off.</p> <p>If PSW = 1, the LCD drive power supply is turned on.</p>	<p>H'FFC1</p> <p>Bit 6</p>	<p>1</p>
	<p>ACT LCD Control Register (Display Function Activate)</p> <p>Selects whether the LCD controller/driver is to be used or not. By clearing this bit to 0, LCD controller/driver operation is halted. In addition, regardless of the value of PSW, the LCD drive power supply is turned off.</p> <p>However, the register contents are retained.</p> <p>If ACT = 0, LCD controller/driver operation is halted.</p> <p>If ACT = 1, LCD controller/driver operates.</p>	<p>H'FFC1</p> <p>Bit 5</p>	<p>1</p>


Register	Function	Address	Setting	
LCR	DISP	LCD Control Register (Display Data Control)	H'FFC1	1
		DISP selects whether to display data in LCD RAM or display blank regardless of LCD RAM contents. If DISP = 0, blank is displayed If DISP = 1, LCD RAM data is displayed	Bit 4	
CKS3		LCD Control Register (Frame Frequency Select 3 to 0)	H'FFC1	CKS3 = 1
CKS2		Selects a clock to obtain a desired frame frequency.	Bit 3	CKS2 = 1
CKS1		When CKS3 = 0, CKS2 = *, CKS1 = 0 and CKS0 = 0,	Bit 2	CKS1 = 1
CKS0		ϕ_w is selected as operating clock When CKS3 = 0, CKS2 = *, CKS1 = 0 and CKS0 = 1, $\phi_w/2$ is selected as operating clock When CKS3 = 0, CKS2 = *, CKS1 = 1 and CKS0 = *, $\phi_w/4$ is selected as operating clock When CKS3 = 1, CKS2 = 0, CKS1 = 0 and CKS0 = 0, $\phi/2$ is selected as operating clock When CKS3 = 1, CKS2 = 0, CKS1 = 0 and CKS0 = 1, $\phi/4$ is selected as operating clock When CKS3 = 1, CKS2 = 0, CKS1 = 1 and CKS0 = 0, $\phi/8$ is selected as operating clock When CKS3 = 1, CKS2 = 0, CKS1 = 1 and CKS0 = 1, $\phi/16$ is selected as operating clock When CKS3 = 1, CKS2 = 1, CKS1 = 0 and CKS0 = 0, $\phi/32$ is selected as operating clock When CKS3 = 1, CKS2 = 1, CKS1 = 0 and CKS0 = 1, $\phi/64$ is selected as operating clock When CKS3 = 1, CKS2 = 1, CKS1 = 1 and CKS0 = 0, $\phi/128$ is selected as operating clock When CKS3 = 1, CKS2 = 1, CKS1 = 1 and CKS0 = 1, $\phi/256$ is selected as operating clock Note: * Don't care	Bit 1 Bit 0	CKS0 = 0
LCR2	LCDAB	LCD Control Register 2 (A Waveform/B Waveform Switching Control)	H'FFC2	0
		Selects whether the A or B waveform is to be used as the LCD drive waveform. If LCDAB = 0, the LCD is driven using the A waveform If LCDAB = 1, the LCD is driven using the B waveform	Bit 7	

4.4 Description of RAM

In this sample task, RAM is not used.

5. Flowchart

1. Main routine



6. Program Listing

INIT.SRC (Program listing)

```

.EXPORT  _INIT
.IMPORT  _main
;
.SECTION P, CODE
_INIT:
MOV.W   #H'FF80, R7
LDC.B   #B'10000000, CCR
JMP     @_main
;
.END

/*****
/*
/* H8/300L Super Low Power Series
/* -H8/38024 Series-
/* Application Note
/*
/* 'Liquid Crystal Display
/* -Static Drive, Internal Driver-'
/*
/* Function
/* : LCD Controller / Driver
/*
/* External Clock : 10MHz
/* Internal Clock : 5MHz
/* Sub Clock      : 32.768kHz
/*
*****/

#include <machine.h>

/*****
/* Symbol Definition
*****/
struct BIT {
    unsigned char  b7:1;    /* bit7 */
    unsigned char  b6:1;    /* bit6 */
    unsigned char  b5:1;    /* bit5 */
    unsigned char  b4:1;    /* bit4 */
    unsigned char  b3:1;    /* bit3 */
    unsigned char  b2:1;    /* bit2 */
    unsigned char  b1:1;    /* bit1 */
    unsigned char  b0:1;    /* bit0 */
};

#define  LPCR      *(volatile unsigned char *)0xFFC0    /* LCD Port Control Register */
#define  LCR       *(volatile unsigned char *)0xFFC1    /* LCD Control Register */
#define  LCR2      *(volatile unsigned char *)0xFFC2    /* LCD Control Register 2 */
#define  LCDRAM    (volatile unsigned char *)0xF740    /* LCD RAM */

/*****
/* Function define
*****/
extern void INIT ( void );    /* SP Set
void      main ( void );

```

```

/*****
/* Vector Address */
/*****
#pragma section V1 /* Vector Section Set */
void (*const VEC_TBL1[])(void) = {
    INIT /* 0x0000 Reset Vector */
};

#pragma section /* P */
/*****
/* Main Program */
/*****
void main ( void )
{
    int i;
    unsigned char *lcdram;

    set_imask_ccr(1); /* Interrupt Disable */

    lcdram = LCDRAM;
    for ( i = 0; i < 0x0F; i++ ){ /* Initialize LCD RAM */
        lcdram[i] = 0;
    }

    LPCR = 0x08; /* Static ,Select SEG32-SEG1 */
    LCR = 0xFE; /* LCD ON */
    LCR2 = 0x60;

    lcdram[0] = 0x48; /* "1" */
    lcdram[1] = 0x3d; /* "2" */
    lcdram[2] = 0x6d; /* "3" */
    lcdram[3] = 0x4b; /* "4" */

    set_imask_ccr(0); /* Interrupt Enable */

    while (1) {
        ;
    }
}

```

Link address specifications

Section Name	Address
CV1	H'0000
P	H'0100

Revision Record

Rev.	Date	Description	
		Page	Summary
1.00	Dec.19.03	—	First edition issued

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.
Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors.
Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.