

RAJ306101

General Purpose Motor Control IC

Rev.1.00 Oct 5, 2023

1 Description

The RAJ306101 is a general-purpose motor control IC for 3-phase brushless DC (BLDC) motor applications. RAJ306101 combines a smart gate driver and MCU (RX13T) in a single package. The smart gate driver includes three half-bridge gate drivers, a buck switching regulator and a charge pump for the gate drive voltage, two LDOs for the internal analog and logic circuitry and MCU, three accurate differential amplifiers, a BEMF sense amplifier, three general purpose comparators, and extensive protection functions.

The three half-bridge gate drivers are capable of driving up to three N-channel MOSFET bridges and support bridge voltages from 6V to 65V. Each gate driver supports up to 0.64A source and 1.28A sink peak drive current with adjustable drive strength control. Adaptive and adjustable dead-times are implemented to ensure robustness and flexibility. The active gate holding mechanism prevents miller effect induced cross-conduction and further enhances robustness.

Three accurate differential amplifiers with adjustable gain support ground-side shunt current sensing for each bridge. The device can also support both BLDC sensor/sensorless motor drive by the three general purpose comparators or a BEMF sense amplifier.

The protection functions include supply voltage OV/UV protection, buck regulator OV/UV/OC protection, charge pump UV protection, MOSFET VDS OC protection, current sense OC protection, MOSFET VGS fault, thermal warning, and thermal shutdown.

The smart gate driver can be configured to use SPI interface by the internal connection with MCU. All the parameters can be set through the SPI interface, and allows better monitoring. Fault conditions are reported on the nFAULT signal and each status bit in the Fault Status registers.

MCU supports H/W of the safe standard of IEC60730. The development tools of the RX13T Group are available.

2 Features

- · Operating power supply voltage:
 - VBRIDGE: 6V to 65V (78V abs max)
 - VM: 6V to 60V (65V abs max)
- Operating ambient temperature: -40°C to 105°C
- Supply current, VM current:
 - MCU, VDD current: 3.1mA (ICLK=32MHz)
 - Smart gate driver:
 Operating Mode: 2mA, Sleep Mode: 28µA
- 8mm×8mm 56 Ld QFN package (0.5mm pitch)

Smart gate driver function

- 3-Phase drive for BLDC application
 - Peak 0.64A/1.28A source/sink current with 16 adjustable drive strength through SPI interface
 - Adaptive and adjustable dead time
 - 3-phase HI/LI mode and 3-phase PWM mode
 - Input control signal configuration
- · Fully integrated power supply architecture
 - Two 5V LDOs allow for Sleep Mode low IQ
 - 500mA buck switching regulator for the gate drive voltage (5V to 15V adjustable)
 - 100mA adjustable output LDO for MCU supplies
- Three differential amplifiers with configurable gain for current sensing (5, 10, 20, 40V/V)
- BEMF sense amplifier for sensorless motor drive
- · Three comparators for hall sensor motor drive
- Extensive protection functions

MCU (RX13T) function

- CPU: 32bit CISC CPU
- Code flash: 128KB, Data flash: 4KB, RAM: 12KB
- SCI: 2 channels (SPI: 2ch, I²C: 2ch, UART: 2ch)
 1ch of SPI: common use with internal communication
- GPIO: 19 channels (I/O: 18ch, Input: 1ch)
- Up to 8 extended-function timers
 - 16-bit multi-function timer pulse unit 3 (6ch)
 - 16-bit compare match timers (2ch)
- Independent watchdog timer (15kHz oscillator)
- 12-bit resolution A/D converter input: 7ch
 - On-chip sample and hold circuit (3ch)
 - Programmable gain amplifier (3ch + 3ch)
 - Support 3 and 1 shunt current sense method

3 Applications

- Vacuum cleaners, Fans, Pumps, and Robotics
- · Power Tools and Garden Tools
- 1. Please refer to not only this datasheet but also "RAJ306101 User's Manual: Hardware (R18UZ0081EJ)" to understand this IC.
- 2. About detail specifications of RX13T, please see "RX13T Group User's Manual: Hardware (R01UH0822EJ)".
- 3. This product has some restrictions on function.

 Please check them on "CHAPTER2 MCU: RX13T" in "RAJ306101 User's Manual: Hardware (R18UZ0081EJ)".
- 4. About the electrical characteristics of RX13T, please substitute AVCC0/VCC condition to 3.135V<=AVCC0/VCC<=5.25V.



4 Overview

4.1 Typical Application Circuits




Figure 4.1-1 Simplified Block Diagram and Application – 3 Shunt Sensorless FOC Motor Drive

4.1 Typical Application Circuits (continued)




Figure 4.1-2 Simplified Block Diagram and Application – Sensorless Motor Drive by BEMF Sensing Comparator

4.1 Typical Application Circuits (continued)




Figure 4.1-3 Simplified Block Diagram and Application – Hall Sensor Motor Drive by Using 3 Comparators

4.1 Typical Application Circuits (continued)




Figure 4.1-4 Simplified Block Diagram and Application – 3 Shunt Sensorless FOC Motor Drive with 5V MCU Supply

4.2 Pin Configurations




Figure 4.2-1 Pin Configuration Diagram (Top View)

4.3 Pin Descriptions

Table 4.3-1 Pin Descriptions

	PIN	Alternate		I/O			
Number	Name	Function	level	type	Initial	Function	Note
1	AVDD_MCU	-	VDD	POWER	-	Positive power supply for RX13T analog circuits Connect to bypass capacitors between AVDD_MCU and AGND_MCU.	1
2	AGND_MCU	-	GND	GND	-	Ground for RX13T analog circuits	1
3	P11	MTIOC3A/ MTCLKA/POE8# IRQ1/CVREFC0	VDD	IN/OUT	IN	Digital input/output / Input/output for MTU3.TGRA / Input for the external clock / Input for request signals to place the MTU pins in the high impedance state / Interrupt request input / Analog reference voltage supply for comparator C	1
4	P10	MTCLKB/IRQ0	VDD	IN/OUT	IN	Digital input/output / Input for the external clock / Interrupt request input	1
5	VCL	-	VDD	-	-	Connect this pin to the GND_MCU1 pin via the 4.7 µF smoothing capacitor used to stabilize the internal power supply. Place the capacitor close to the pin.	1
6	MD	FINED	VDD	IN	IN	Input for setting the operating mode. The signal levels on this pin must not be changed during operation. / FINE interface pin.	1
7	RES#	-	VDD	IN	IN	Reset pin. This MCU enters the reset state when this signal goes low.	1
8	GND_MCU1	-	GND	GND	-	Ground for RX13T	1
9	P36	EXTAL	VDD	IN/OUT	IN	Digital input/output / An external clock can be input through the EXTAL pin.	1
10	VDD_MCU1	-	VDD	POWER	-	Positive power supply for RX13T Connect to bypass capacitors between VDD_MCU1 and GND_MCU1.	1
11	PE2	POE10#/ NMI/IRQ0	VDD	IN	IN	Digital input/output / Input for request signals to place the MTU pins in the high impedance state / Non-maskable interrupt request input / Interrupt request input	1
12	PD6	MTIOC0D/ CTS1#/RTS1#/ SS1#/IRQ5/ADST0	VDD	IN/OUT	IN	Digital input/output / Input/output for MTU0.TGRD / Input for SCI1 start control / Output for SCI1 start control / Chip-select input for SCI1 / Interrupt request input / Output for A/D conversion status	1
13	PD5	MTIOC0C/ RXD1/SMISO1/ SSCL1/IRQ3	VDD	IN/OUT	IN	Digital input/output / Input/output for MTU0.TGRC / Input for SCI1 received data / Input/output for SCI1 slave transmit datal / Input/output for the I2C clock / Interrupt request input	1
14	PD4	MTIOC0B/ SCK1/IRQ2	VDD	IN/OUT	IN	Digital input/output / Input/output for MTU0.TGRB / Input/output for SCI1 clock. / Interrupt request input	1
15	PD3	MTIOC0A/TXD1/ SMOSI1/SSDA1/	VDD	IN/OUT	IN	Digital input/output / Input/output for MTU0.TGRA / Output for SCI1 transmitted data / Input/output for SCI1 master transmit datal / Input/output for the I ² C data	1
16	PB7	MTIOC3C/MTCLKD/ RXD1/RXD5/ SMISO1/SMISO5/ SSCL1/SSCL5/IRQ5	VDD	IN/OUT	IN	Digital input/output / Input/output for MTU3.TGRC / Input for the external clock / Input for SCI1,5 received data / Input/output for SCI1,5 slave transmit datal / Input/output for SCI1,5 I ² C clock / Interrupt request input	1
17	PB6	MTIOC1B/MTIOC3A/ TXD1/TXD5/ SMOSI1/SMOSI5/ SSDA1/SSDA5	VDD	IN/OUT	IN	Digital input/output / Input/output for MTU1.TGRB / Input/output for MTU3.TGRA / Output for SCI1,5 transmitted data / Input/output for SCI1,5 master transmit datal / Input/output for SCI1,5 I ² C data	1
18	PB5	ADTRG0#	VDD	INOUT	IN	Digital input/output / Input for the external trigger signals that start the A/D conversion	1
19	PB4	POE8#/IRQ3	VDD	IN/OUT	IN	Digital input/output / Input for request signals to place the MTU pins in the high impedance state / Interrupt request input	1
20	PB3	MTIOC0A/SCK5/ CACREF	VDD	IN/OUT	IN	Digital input/output / Input/output for MTU0.TGRA / Input/output for SCI5 clock / Input for the clock frequency accuracy measurement circuit	1
21	PB0	MTIOC0D/MTIOC2A/ MTCLKB/nSMPL	VDD	IN/OUT	IN	Digital input/output / Input/output for MTU0.TGRD / Input/output for MTU2.TGRA / Input for the external clock / Sample and Hold control input for smart gate driver	1,2
22	PC	-	VCC5V	OUT	OUT	gm amplifier output for phase compensation of buck switching regulator.	
23	FB	-	VCC5V	IN	IN	Voltage feedback input of buck switching regulator (Ref.=0.8V).	
24	VM	-	VM	POWER	-	Power supply input. Connect bypass capacitors between VM and analog ground.	
25	SW1	-	VM	OUT	OUT	Switch node of buck switching regulator.	
26	VDRV	-	VDRV	POWER	-	Output of buck switching regulator, Low-side gate driver supply. Connect to bypass capacitors between VDRV and analog ground.	

Note1: RX13T terminal. Please refer to "RX13T Group User's Manual: Hardware" (R01UH0822EJ) about pin functions of RX13T.

Note2: When this pin is used as RX13T function pin, the S/H function of the differential amplifier in the smart gate driver is not available. Please set all of BEMF_SH, DA1_SH, DA2_SH, and DA3_SH bit in SNSCTL2 register of the smart gate driver to "0". Please refer to the control register information on section 6.7.15, Sense Block Control 2 register.



4.3 Pin Descriptions (continued)

Table 4.3-2 Pin Descriptions (continued)

	PIN	Alternate		I/O			
Number	Name	Function	level	type	Initial	Function	Note
27	CPL	-	VDRV	OUT	OUT	Charge pump low-side switch node. Connect a flying capacitor between CPH and CPL pins.	
28	СРН	-	VCP	OUT	OUT	Charge pump high-side switch node. Connect a flying capacitor between CPH and CPL pins.	
29	VCP	-	VCP	POWER	-	Charge pump output. Connect a bypass capacitor between VCP and VBRIDGE pins.	
30	VBRIDGE	-	VM	IN	IN	Charge pump output reference and high-side MOSFET drain sense Input. Connect a bypass capacitor between VBRIDGE pin and power ground.	
31	НОА	-	VCP	ОИТ	ОИТ	Phase A high-side gate driver output. Connect to the high-side MOSFET gate.	
32	HSA	-	VM	IN	IN	Phase A high-side source sense input. Connect to the high-side MOSFET source.	
33	LOA	-	VDRV	ОИТ	OUT	Phase A low-side gate driver output. Connect to the low-side MOSFET gate.	
34	HOB	-	VCP	ОИТ	OUT	Phase B high-side gate driver output. Connect to the high-side MOSFET gate.	
35	HSB	-	VM	IN	IN	Phase B high-side source sense input. Connect to the high-side MOSFET source.	
36	LOB	-	VDRV	ОИТ	ОИТ	Phase B low-side gate driver output. Connect to the low-side MOSFET gate.	
37	HOC	-	VCP	ОИТ	OUT	Phase C high-side gate driver output. Connect to the high-side MOSFET gate.	
38	HSC	-	VM	IN	IN	Phase C high-side source sense input. Connect to the high-side MOSFET source.	
39	LOC	-	VDRV	OUT	OUT	Phase C low-side gate driver output. Connect to the low-side MOSFET gate.	
40	PGND	-	GND	GND	-	Ground sense input of external power stage.	
41	DA1P	-	VDD	IN	IN	Positive input of differential amplifier 1.	
42	DA1N	-	VDD	IN	IN	Negative input of differential amplifier 1.	
43	DA2P	CMP2P	VDD	IN	IN	Positive input of differential amplifier 2 and positive input of comparator 2.	
44	DA2N	-	VDD	IN	IN	Negative input of differential amplifier 2.	
45	DA3P	CMP3P	VDD	IN	IN	Positive input of differential amplifier 3 and positive input of comparator 3.	
46	DA3N	CMP1P	VDD	IN	IN	Negative input of differential amplifier 3 and positive input of comparator 1.	
47	VDD	-	VDD	POWER	-	Internal series regulator output and power supply of output buffers. Connect to a bypass capacitor between VDD and AGND.	
48	AGND	-	GND	GND	-	Device analog ground.	
49	FBLDO	-	VCC5V	IN	IN	Voltage feedback input of internal series regulator (Ref.=1.2V).	
50	VCC5V	-	VCC5V	POWER	-	Internal series regulator output(5V). Connect to a bypass capacitor between VCC5V and AGND.	
51	VDD_MCU2	-	VDD	POWER	-	Positive power supply for RX13T	
52	P44	AN004/CMPC12/ DA3O	VDD	IN/OUT	IN	Digital input/output / A/D converter analog input / Comparator C1 analog input Output of differential amplifier 3	1,3
53	P43	AN003/CMPC02	VDD	IN/OUT	IN	Digital input/output / A/D converter analog input / Comparator C0 analog input	1
54	P42	AN002/CMPC20	VDD	IN/OUT	IN	Digital input/output / A/D converter analog input / Comparator C2 analog input	1
55	P41	AN001/CMPCC10	VDD	IN/OUT	IN	Digital input/output / A/D converter analog input / Comparator C1 analog input	1
56	P40	AN000/CMPC00	VDD	IN/OUT	IN	Digital input/output / A/D converter analog input / Comparator C0 analog input	1
-	EPAD (Thermal PAD)	-	GND	GND	-	Power ground for gate driver and charge pump. Must be connected to power ground.	
_	· · · · · · · · · · · · · · · · · · ·						

Note1: RX13T terminal. Please refer to "RX13T Group User's Manual: Hardware" (R01UH0822EJ) about pin functions of RX13T.

Note3: When this pin is used as RX13T function pin, please set MUX bits in SNSCTL5 register of the smart gate driver to "000b".

This pin has 330kΩ pulldown resistance. Please refer to the control register information on section 6.5.5, MUX1 output Control, and section 6.7.18, Sense Block Control 5 register.



5 Specifications

5.1 Absolute Maximum Ratings

Table 5.1-1 Absolute Maximum Ratings Note1

	ltem	Symbol	Minimum	Maximum	unit
VBRIDGE to GND Note2		VBRIDGEabs	-0.3	78	V
VM to GND Note2		VMabs	-0.3	65	V
Voltage difference between g	ground pins (AGND, PGND, EPAD)	DGNDabs	-0.3	0.3	V
VCP to GND, CPH to GND,	VCP to HSx, VCP to HOx (x=A,B,C)	VCPabs	-0.3	VBRIDGE + 15 Note3	V
CPL to GND		VCPLabs	-0.3	VDRV + 0.3	V
Continuous HOx (x=A,B,C) t	o GND	VHOxabs	-5	VCP + 0.5	V
Transient 200ns HOx (x=A,B	s,C) to GND	VHOxtran	-7	VCP + 0.5	V
HOx to HSx (x=A,B,C)		VGSHxabs	-0.3	15	V
Continuous HSx (x=A,B,C) to	GND	VHSxabs	-5	VBRIDGE + 5 Note4	V
Transient 200ns HSx (x=A,B	VHSxtran	-7	VBRIDGE + 7 Note4	V	
VDRV to AGND	VDRV to AGND		-0.3	17	V
Continuous LOx (x=A,B,C) to	GND	VLOabs	-1	VDRV + 0.5	V
SW1 to GND		VSWabs	-1	VM + 0.5	V
VCC5V to GND		VCCabs	-0.3	5.5	V
FB, PC, FBLDO to GND		VFBabs	-0.3	VCC5V + 0.3	V
DAzP (z=1,2,3) to GND, DAz	zN (z=1,2,3) to GND	VDAINabs	-1	VDD + 0.6	V
VDD, VDD_MCU1,2, AVDD_	MCU to GND	VDDabs	-0.3	5.5	V
Digital input voltage	P40 to P44	V _{DI1}	-0.3	AVDD_MCU + 0.3	V
	other than the above	V _{Dl2}	-0.3	VDD_MCU + 0.3	V
Analog input voltage	In case of AN000 to AN004 usage	VAI1	-0.3	AVDD_MCU + 0.3	V
Ambient temperature		TA	-40	105	°C
Junction temperature for sm	art gate driver (RAA306012)	TJ	-40	150	°C
Storage temperature		Tstg	-55	125	°C

Note1: Not subject to production test, specified at Ta=25°C by design

Note2: Power supply can be applied to VBRIDGE and VM pin independently.

Note3: VCP pin voltage with respect to HOx and HSx pins should be limited to 86V maximum.

This limits the maximum VCPabs, minimum VHOxabs, VHSxabs, and maximum VGSHxabs when VBRIDGE is greater than 66V. For example, when VBRIDGE=78V, VCPabs=84V, and VHOxabs=VHSxabs=-2V, VGSHxabs should be limited to (84V - 78V) = 6V. In this example, VDRV pin voltage is also limited to about 7V in consideration of the step-up voltage of the charge pump.

Note4: In case of VDRV<=7V, the maximum VHSxabs is limited to VBRIDGE + (VDRV-2V).

The maximum VHSxtran is also limited to VBRIDGE + VDRV.

Caution1: Product quality may suffer if the absolute maximum rating is exceeded even momentarily for any parameter

That is, the absolute maximum ratings are rated values at which the product is on the verge of suffering physical damage,
and therefore the product must be used under conditions that ensure that the absolute maximum ratings are not exceeded.

Caution2: To preclude malfunctions due to noise interference, insert capacitors with high frequency characteristics between the VDD_MCU1 and GND_MCU1 pins, between VDD_MCU2 and AGND pins, and between the AVDD_MCU and AGND_MCU pins. Place capacitors with values of about 0.1 µF as close as possible to every power supply pin and use the shortest and widest possible traces for the wiring. Connect the VCL pin to a GND_MCU1 pin via a 4.7µF capacitor. The capacitor must be placed close to the pin.

Caution3: Do not input signals to MCU ports while the MCU is not powered. The current injection that results from input of such a signal may cause malfunction and the abnormal current that passes in the MCU at this time may cause degradation of internal elements.

Remark1: Unless specified otherwise, the characteristics of alternate-function pins are same as those of the port pins.

Remark2: The GND pin of each block is the followings.

Gate driver block: EPAD, Charge pump: EPAD, Analog blocks: AGND, MCU: GND_MCU1, AGND_MCU, AGND

5.2 Thermal Information

Table 5.2-1 Thermal Information

Thermal resistance (Typical)	θ _{JA} [°C/W]	Ψ _{JT} [°C/W]
8mm x 8mm 56Ld QFN Package Note1,2	21.4	1.69

Note1: θ_{JA} is measured in free air with the component mounted on a high-effective thermal conductivity test board with "direct attach" features.

See TB379.

Note2: For Ψ_{JT} , the "case temp" location is the center of the exposed metal pad on the package underside.

5.3 Recommended Operating Conditions

Table 5.3-1 Recommended Operating Conditions

VBRIDGE to GND	VBRIDGEope	6	65	V	
VM to GND		VMope	6	60	V
VCC5V to GND		VCCope	4.75	5.25	V
VDRV to GND	VDRVope Note4	5	16	V	
VDD to GND		VDDope	3.135	5.25	V
VDD_MCU1,2, and	supplied from VCC5V	VMCUope1	4.75	5.25	V
AVDD_MCU to GND	supplied from VDD	VMCUope2	3.135	3.465	V
External load current (VD	D & VCC5V), Sleep Mode	Ivdd0	0	50 Note3	mA
External load current (VD	External load current (VDD & VCC5V), during start-up, LDO1=On			70 ^{Note3}	mA
External load current (VD	Ivdd1_1	0	90 Note3	mA	
Operating junction temper	rature	Tjope	-40	125	°C

Note3: Power dissipation and thermal limits must be observed.

External load current is defined as the total of VCC5V and VDD load current including MCU supply current.

Note4: VDRV voltage must be set so that VCC5V voltage doesn't deviate from the recommended operating condition.

5.4 Electrical Characteristics

Regarding the electrical characteristics of the function implemented in RX13T, please refer to "RX13T Group User's Manual: Hardware" (R01UH0822EJ).

Note: All specifications are for Ta=25°C, VM=48V unless otherwise noted.

		0 111		Rated level		Unit
Parameter	Symbol	Condition	MIN	TYP	MAX	Unit
Power supply (VM)	•					
VM Sleep Mode current	I∨MO	HOx/LOx=Low/Low, No load on VDD	-	28	44	μA
VM, VBRIDGE operating current (combined)	I∨м1	Operating Mode, HOx/LOx=Low/Low, excluding MCU supply current	-	2	-	mA
VDRV operating current	Ivdrv1	Operating Mode, HOx/LOx=Low/Low	-	3.8	-	mA
Sleep Mode entry time delay	tsleep	From internal EN trigger to Sleep Mode	-	0.55	0.85	ms
Wake-up time delay	twake	From internal EN trigger to All power rails ready, C2=2.2µF, C3=0.22µF	-	6.5	-	ms
Power supply (VCC5V)						
Output voltage	Vvcc0_1	VM=60V, Sleep Mode, load=0mA	-	5	-	V
	Vvcc0_2	VM=36V, Sleep Mode, load=10mA	-	5	-	V
	Vvcc0_3	VM=6V, Sleep Mode, load=50mA	4.75	5	-	V
	Vvcc1_1	VDRV=15V, Operating Mode, load=0.1mA	-	5	-	V
	Vvcc1_2	VDRV=12V, Operating Mode, load=40mA	4.85	5	5.15	V
	Vvcc1_3	VDRV=8V, Operating Mode, load=100mA	-	5	-	V
Current limit	Іьмтсс0_0	VM=6V, Sleep Mode	50	80	-	mA
	Іьмтсс0_1	VM=36V, during start-up, LDO1=On	80	130	-	mA
	Іьмтос1	VDRV=12V, Operating Mode	100	160	-	mA
Power supply (VDD)						
Output voltage Note2	Vvdd0_1	VM=60V, Sleep Mode, load=0mA	-	3.3	-	V
	Vvdd0_2	VM=36V, Sleep Mode, load=10mA	-	3.3	-	V
	Vvdd0_3	VM=6V, Sleep Mode, load=50mA	3.0	3.3	-	V
	VvDd1_1	VDRV=15V, Operating Mode, load=0.1mA	-	3.3	-	V
	VvDd1_2	VDRV=12V, Operating Mode, load=40mA	3.201	3.3	3.399	V
	VvDd1_3	VDRV=8V, Operating Mode, load=100mA	-	3.3	-	V
Current limit Note3	ILMTDD0	VM=6V, Sleep Mode	50	80	-	mA
	ILMTDD1_0	VM=36V, during start-up, LDO1=On	80	130	-	mA
	ILMTDD1_1	VDRV=12V, Operating Mode	100	160	-	mA

Note2: VDD specification does not apply when VDD LDO is not used by connecting FBLDO to VCC5V or VDD pin.

Note3: VDD current is limited by VCC5V current limit. These items are not tested.

5.4 Electrical Characteristics (continued)

Note: All specifications are for Ta=25°C, VM=48V unless otherwise noted.

_				Rated level		Lloit
Parameter	Symbol	Condition	MIN	TYP	MAX	Unit
Buck switching regulator (VDRV)						
Output voltage adjustment range Note1	Vdrv		5	-	15	V
Reference voltage	Vref_sr		0.776	0.8	0.824	V
gm amplifier gain	gm_sr		-	200	-	μ A /V
gm amplifier output capability	IgmSRC_SR		-	18	-	μΑ
	IgmSNK_SR		-	-18	-	μΑ
gm amplifier maximum output voltage	V _{gmH_SR}	FB=0V	-	3.95	-	V
gm amplifier minimum output voltage	VgmL_SR	FB=1V	-	0.02	-	V
Ramp offset voltage	Vramp_SR		-	870	-	mV
Oscillator frequency	fsw_sr		400	500	575	kHz
Soft-start time	tss_sr	Time to FB=0.8V	-	2.2	-	ms
Cycle-by-cycle current limit Note1	Ioc1_sr		-	1.2	-	А
Hiccup current limit threshold Note1	Ioc2_sr		-	1.4	-	А
Charge pump (VCP)						
Output voltage with respect to VBRIDGE	Vvcp_1	VM=60V, VDRV=12V, load=15mA	-	11	-	V
	Vvcp_2	VM=36V, VDRV=12V, load=15mA	-	11	-	V
	Vvcp_3	VM=6V, VDRV=6V, load=15mA	5.0	5.3	-	V
Oscillator frequency	fsw_cp		-	250	-	kHz
Maximum load current Note1	Iload_CP		28	-	-	mA
Gate driver block (HOx, LOx (x=A,B,C))						
High-side gate driver Output high voltage	Vgshh	Io=1mA, VDRV=12V, VM=HSx=24V, with respect to HSx	-	11.45	-	V
High-side gate driver Output low voltage	VGSHL	Io=-1mA, VDRV=12V, VM=HSx=24V, with respect to HSx	-	0.05	-	V
Low-side gate driver Output high voltage	Vgslh	Io=1mA, VDRV=12V, VM=HSx=24V, with respect to GND	-	11.95	1	٧
Low-side gate driver Output low voltage	VGSLL	Io=-1mA, VDRV=12V, VM=HSx=24V, with respect to GND	-	0.05	·	V
High-side gate clamp voltage Note1	VCLMP	Io=-1mA, with respect to HSx	16.0	17.2	18.4	V
Gate pulldown resistance	RPD		-	200	-	kΩ
Strong sink current Note1	ISNK_STG		-	1280	=	mA
Pullup source current	Isrc_pu		-	50	-	mA
Pulldown sink current	ISNK_PD		-	100	-	mA

5.4 Electrical Characteristics (continued)

Note: All specifications are for Ta=25°C, VM=48V unless otherwise noted.

		0 111		Rated level		
Parameter	Symbol	Condition	MIN	TYP	MAX	Unit
Gate driver block (HOx (x=A,B,C))						
High-side peak source current Note1	Isrcho	ISRC_HS[3:0]=0h	-	50	-	mA
	Isrch1	ISRC_HS[3:0]=1h	-	60	-	mA
	ISRCH2	ISRC_HS[3:0]=2h	-	70	-	mA
	Isrch3	ISRC_HS[3:0]=3h	-	80	-	mA
	IsrcH4	ISRC_HS[3:0]=4h	-	100	-	mA
	ISRCH5	ISRC_HS[3:0]=5h	-	120	-	mA
	Isrch6	ISRC_HS[3:0]=6h	-	140	-	mA
	ISRCH7	ISRC_HS[3:0]=7h	-	160	-	mA
	ISRCH8	ISRC_HS[3:0]=8h	-	200	-	mA
	IsrcH9	ISRC_HS[3:0]=9h	-	240	-	mA
	ISRCH10	ISRC_HS[3:0]=Ah	-	280	-	mA
	ISRCH11	ISRC_HS[3:0]=Bh	-	320	-	mA
	ISRCH12	ISRC_HS[3:0]=Ch	-	400	-	mA
	ISRCH13	ISRC_HS[3:0]=Dh	-	480	-	mA
	ISRCH14	ISRC_HS[3:0]=Eh	-	560	-	mA
	ISRCH15	ISRC_HS[3:0]=Fh	-	640	-	mA
High-side peak sink current Note1	Isnkho	ISRC_HS[3:0]=0h	-	100	-	mA
	IsnkH1	ISRC_HS[3:0]=1h	-	120	-	mA
	Isnkh2	ISRC_HS[3:0]=2h	-	140	-	mA
	Іѕикнз	ISRC_HS[3:0]=3h	-	160	-	mA
	ISNKH4	ISRC_HS[3:0]=4h	-	200	-	mA
	ISNKH5	ISRC_HS[3:0]=5h	-	240	-	mA
	IsnkH6	ISRC_HS[3:0]=6h	-	280	-	mA
	Isnkh7	ISRC_HS[3:0]=7h	-	320	-	mA
	ISNKH8	ISRC_HS[3:0]=8h	-	400	-	mA
	IsnkH9	ISRC_HS[3:0]=9h	-	480	-	mA
	ISNKH10	ISRC_HS[3:0]=Ah	-	560	-	mA
	ISNKH11	ISRC_HS[3:0]=Bh	-	640	-	mA
	ISNKH12	ISRC_HS[3:0]=Ch	-	800	-	mA
	ISNKH13	ISRC_HS[3:0]=Dh	-	960	-	mA
	ISNKH14	ISRC_HS[3:0]=Eh	-	1120	-	mA
	ISNKH15	ISRC_HS[3:0]=Fh	-	1280	-	mA

 $\label{thm:continuous} \textbf{Note1: This specification is not tested in production. Only functional test.}$

5.4 Electrical Characteristics (continued)

Note: All specifications are for Ta=25°C, VM=48V unless otherwise noted.

		0 111		Rated level		
Parameter	Symbol	Condition	MIN	TYP	MAX	Unit
Gate driver block (LOx (x=A,B,C))						
Low-side peak source current Note1	ISRCL0	ISRC_LS[3:0]=0h	-	50	-	mA
	ISRCL1	ISRC_LS[3:0]=1h	-	60	-	mA
	ISRCL2	ISRC_LS[3:0]=2h	-	70	-	mA
	ISRCL3	ISRC_LS[3:0]=3h	-	80	-	mA
	ISRCL4	ISRC_LS[3:0]=4h	-	100	-	mA
	ISRCL5	ISRC_LS[3:0]=5h	-	120	-	mA
	ISRCL6	ISRC_LS[3:0]=6h	-	140	-	mA
	ISRCL7	ISRC_LS[3:0]=7h	-	160	-	mA
	ISRCL8	ISRC_LS[3:0]=8h	-	200	-	mA
	ISRCL9	ISRC_LS[3:0]=9h	-	240	-	mA
	ISRCL10	ISRC_LS[3:0]=Ah	-	280	-	mA
	ISRCL11	ISRC_LS[3:0]=Bh	-	320	-	mA
	ISRCL12	ISRC_LS[3:0]=Ch	-	400	-	mA
	ISRCL13	ISRC_LS[3:0]=Dh	-	480	-	mA
	ISRCL14	ISRC_LS[3:0]=Eh	-	560	-	mA
	ISRCL15	ISRC_LS[3:0]=Fh	-	640	-	mA
Low-side peak sink current Note1	Isnklo	ISRC_LS[3:0]=0h	-	100	-	mA
	ISNKL1	ISRC_LS[3:0]=1h	-	120	-	mA
	ISNKL2	ISRC_LS[3:0]=2h	-	140	-	mA
	ISNKL3	ISRC_LS[3:0]=3h	-	160	-	mA
	ISNKL4	ISRC_LS[3:0]=4h	-	200	-	mA
	ISNKL5	ISRC_LS[3:0]=5h	-	240	-	mA
	ISNKL6	ISRC_LS[3:0]=6h	-	280	-	mA
	ISNKL7	ISRC_LS[3:0]=7h	-	320	-	mA
	ISNKL8	ISRC_LS[3:0]=8h	-	400	-	mA
	ISNKL9	ISRC_LS[3:0]=9h	-	480	-	mA
	ISNKL10	ISRC_LS[3:0]=Ah	-	560	-	mA
	İSNKL11	ISRC_LS[3:0]=Bh	-	640	-	mA
	ISNKL12	ISRC_LS[3:0]=Ch	-	800	-	mA
	ISNKL13	ISRC_LS[3:0]=Dh	-	960	-	mA
	İSNKL14	ISRC_LS[3:0]=Eh	-	1120	-	mA
	ISNKL15	ISRC_LS[3:0]=Fh	-	1280	-	mA

5.4 Electrical Characteristics (continued)

Note: All specifications are for Ta=25°C, VM=48V unless otherwise noted.

				Rated level		I be is
Parameter	Symbol	Condition	MIN	TYP	MAX	Unit
Gate driver block (HOx, LOx (x=A,B,C))	•			'		
Adaptive dead time VGs falling threshold Note1	V _{TH_} v _G s		-	1	-	V
Adaptive dead time VGs threshold hysteresis Note1	VHYS_VGS		-	2	-	٧
Gate drive dead time	tото	DEAD_TIME[1:0]=0h from VTH_VGS to other-side ON	-	50	-	ns
	tDT1	DEAD_TIME[1:0]=1h from VTH_VGS to other-side ON	-	100	-	ns
	tDT2	DEAD_TIME[1:0]=2h from VTH_VGS to other-side ON	-	200	-	ns
	tътз	DEAD_TIME[1:0]=3h from VTH_VGS to other-side ON	-	400	-	ns
Maximum gate transition time	tgтo	T_GT[1:0]=0h from Source/Sink start to Pullup/down start	-	500	-	ns
	tgT1	T_GT[1:0]=1h from Source/Sink start to Pullup/down start	-	1000	-	ns
	tgT2	T_GT[1:0]=2h from Source/Sink start to Pullup/down start	-	2000	-	ns
	tgтз	T_GT[1:0]=3h from Source/Sink start to Pullup/down start	-	4000	-	ns
Propagation delay Note1	tPROP	from PWM input trigger to HOx/LOx start	-	40	-	ns
Differential amplifier (DAzP, DAzN, DAzO	O (z=1,2,3))					
Common mode input voltage range	VIC_CSA	DAzP, DAzN pin	-0.5	-	2.8	V
Differential mode input voltage range	VID_CSA	DAzP - DAzN	-0.5	-	0.5	V
Input offset voltage	VIO_CSA	CAL_CONN=1	-5	-	5	mV
Output voltage linear range Note1	Vo_csa		0.4	-	VDD-0.4	V
Amplifier gain	GCSA0	DAz_GAIN[1:0]=0h	4.85	5	5.15	V/V
	GCSA1	DAz_GAIN[1:0]=1h	9.7	10	10.3	V/V
	GCSA2	DAz_GAIN[1:0]=2h	19.4	20	20.6	V/V
	GCSA3	DAz_GAIN[1:0]=3h	38.8	40	41.2	V/V
Settling time to +/-1% Note1	tset_csa0	DAz_GAIN[1:0]=0h	-	250	-	ns
	tset_csa1	DAz_GAIN[1:0]=1h	-	300	-	ns
	tset_csa2	DAz_GAIN[1:0]=2h	-	400	-	ns
	tset_csa3	DAz_GAIN[1:0]=3h	-	500	-	ns

5.4 Electrical Characteristics (continued)

Note: All specifications are for Ta=25°C, VM=48V unless otherwise noted.

_				Rated level		
Parameter	Symbol	Condition	MIN	TYP	MAX	Unit
BEMF sense amplifier (HSA, HSB, HSC, I	DA3O)				L	
Common mode input voltage range	VIC_EMF	HSA, HSB, HSC pin	-2.5	-	VM+2.5	V
Differential mode input voltage range0	VID_EMF0	HSA, HSB, HSC pin - VBRIDGE/2 BEMF_GAIN[1:0]=0h	-24	-	24	V
Differential mode input voltage range3	VID_EMF3	HSA, HSB, HSC pin - VBRIDGE/2 BEMF_GAIN[1:0]=3h	-1.2	-	1.2	V
Output offset voltage0	VIO_EMF0	DA3O pin with respect to VDD/2 BEMF_GAIN[1:0]=0h	-0.2	-	0.2	V
Output offset voltage3	VIO_EMF3	DA3O pin with respect to VDD/2 BEMF_GAIN[1:0]=3h	-0.3	-	0.3	V
Amplifier output voltage bias	VREF_EMF		-	VDD/2	-	V
BEMF sense amplifier gain	Gемғо	BEMF_GAIN[1:0]=0h	0.0475	0.05	0.0525	V/V
	GEMF1	BEMF_GAIN[1:0]=1h	0.095	0.1	0.105	V/V
	GEMF2	BEMF_GAIN[1:0]=2h	0.475	0.5	0.525	V/V
	G EMF3	BEMF_GAIN[1:0]=3h	0.95	1	1.05	V/V
Settling time to +/-1% Note1	tset_emf0	BEMF_GAIN[1:0]=0h	-	350	-	ns
	tset_emf1	BEMF_GAIN[1:0]=1h	-	400	-	ns
	tset_emf2	BEMF_GAIN[1:0]=2h	-	500	-	ns
	tset_emf3	BEMF_GAIN[1:0]=3h	-	1000	-	ns
Comparator (CMPzO (z=1,2,3))	·					
	VTH_CMP1	CMPz_VTH[3:0] =1h	0.173	0.206	0.221	V
	VTH_CMP2	CMPz_VTH[3:0] =2h	0.380	0.413	0.433	V
	VTH_CMP3	CMPz_VTH[3:0] =3h	0.589	0.619	0.650	V
Threshold voltage	VTH_CMP4	CMPz_VTH[3:0] =4h	0.784	0.825	0.866	V
for VDD=3.3V setting	VTH_CMP5	CMPz_VTH[3:0] =5h	0.980	1.031	1.083	V
	VTH_CMP6	CMPz_VTH[3:0] =6h	1.176	1.238	1.299	V
	VTH_CMP7	CMPz_VTH[3:0] =7h	1.372	1.444	1.516	V
	VTH_CMP8	CMPz_VTH[3:0] =8h	1.568	1.650	1.733	V
	VTH_CMP9	CMPz_VTH[3:0] =9h	1.763	1.856	1.949	V
	VTH_CMP10	CMPz_VTH[3:0] =Ah	1.959	2.063	2.166	V
	VTH_CMP11	CMPz_VTH[3:0] =Bh	2.155	2.269	2.382	V
	VTH_CMP12	CMPz_VTH[3:0] =Ch	2.351	2.475	2.599	V
	VTH_CMP13	CMPz_VTH[3:0] =Dh	2.547	2.681	2.815	V
	VTH_CMP14	CMPz_VTH[3:0] =Eh	2.743	2.888	3.032	V
	VTH_CMP15	CMPz_VTH[3:0] =Fh	2.939	3.094	3.248	V
Hysteresis	VHYS_CMP0	CMPz_HYS=0	-	+/-44	-	mV
	VHYS_CMP1	CMPz_HYS=1	-	0	-	mV
Comparator delay	tDLY_CMP		-	-	1	μs

5.4 Electrical Characteristics (continued)

Note: All specifications are for Ta=25°C, VM=48V unless otherwise noted.

Danamata	Oah al	O and all this are		Rated level		Lloit
Parameter	Symbol	Condition	MIN	TYP	MAX	Unit
Fault management						
VCC5V power-on-reset rising	VCCUVR		-	4.00	-	V
VCC5V power-on-reset falling	Vccuv		-	3.63	-	V
VM under voltage rising0	Vvmuvr0	VMUV_TH=0	5.2	5.5	5.8	V
VM under voltage falling0	Vvmuv0	VMUV_TH=0	5.0	5.3	5.6	V
VM under voltage rising1	Vvmuvr1	VMUV_TH=1	7.38	7.78	8.18	V
VM under voltage falling1	Vvmuv1	VMUV_TH=1	7.1	7.5	7.9	V
VM over voltage rising	Vvmov		-	63	-	V
VM over voltage falling	Vvmovr		-	60	-	V
VDRV under voltage fault rising	Vdrvuvr		4.2	4.4	4.6	V
VDRV under voltage fault falling	Vdrvuv		4.0	4.2	4.4	V
VDRV over voltage rising	Vdrvov	FB pin voltage	0.92	0.95	0.98	V
VDRV over voltage falling	Vdrvovr	FB pin voltage	0.80	0.825	0.85	V
VCP under voltage fault falling0	Vcpuv0	with respect to VBRIDGE, CPUV_TH=0	-	0.58*VDRV	-	V
VCP under voltage fault hysteresis0	Vcpuvhys0	CPUV_TH=0	-	0.07*VDRV	-	V
VCP under voltage fault falling1	Vcpuv1	with respect to VBRIDGE, CPUV_TH=1	-	0.8*VDRV	-	V
VCP under voltage fault hysteresis1	VCPUVHYS1	CPUV_TH=1	-	0.09*VDRV	=	V
Thermal warning threshold Note1	Twarn		-	140	-	°C
Thermal shutdown threshold Note1	Tsp		-	160	-	°C
Thermal hysteresis Note1	Thys		-	15	-	°C

5.4 Electrical Characteristics (continued)

Note: All specifications are for Ta=25°C, VM=48V unless otherwise noted.

Davometer	Cumbal	Condition	Rated level			Lloit
Parameter	Symbol	Condition	MIN	TYP	MAX	Unit
Fault management						
MOSFET VDs OCP threshold		VDS_TH[3:0]=0h	-	40	-	mV
		VDS_TH[3:0]=1h	-	60	-	mV
		VDS_TH[3:0]=2h	-	80	-	mV
		VDS_TH[3:0]=3h	-	120	-	mV
		VDS_TH[3:0]=4h	-	160	-	mV
		VDS_TH[3:0]=5h	-	200	-	mV
		VDS_TH[3:0]=6h	-	240	-	mV
	VDSOCP	VDS_TH[3:0]=7h	-	320	-	mV
		VDS_TH[3:0]=8h	-	400	-	mV
		VDS_TH[3:0]=9h	-	480	-	mV
		VDS_TH[3:0]=Ah	-	600	-	mV
		VDS_TH[3:0]=Bh	-	720	-	mV
		VDS_TH[3:0]=Ch	-	960	-	mV
		VDS_TH[3:0]=Dh	-	1200	-	mV
		VDS_TH[3:0]=Eh	-	1600	-	mV
		VDS_TH[3:0]=Fh	-	2000	-	mV
Shunt current sense OCP threshold		CSOCP_TH[2:0]=0h	37	51	65	mV
		CSOCP_TH[2:0]=1h	87	105	120	mV
		CSOCP_TH[2:0]=2h	131	157	175	mV
		CSOCP_TH[2:0]=3h	179	208	234	mV
	VCSOCP	CSOCP_TH[2:0]=4h	224	260	290	mV
		CSOCP_TH[2:0]=5h	456	516	572	mV
		CSOCP_TH[2:0]=6h	686	773	857	mV
		CSOCP_TH[2:0]=7h	917	1029	1140	mV
OCP	tDEG_OCP	DEG_TIME[1:0]=0h	1.10	1.57	2.04	μs
Deglitch time		DEG_TIME[1:0]=1h	1.67	2.38	3.09	μs
		DEG_TIME[1:0]=2h	2.44	3.49	4.54	μs
		DEG_TIME[1:0]=3h	4.01	5.73	7.45	μs
OCP	tretry_ocp	TRETRY_CSOCP, VDSOCP=0	-	4000	-	μs
Retry time		TRETRY_CSOCP, VDSOCP=1	-	70	-	μs

5.5 SPI Timing Specification for Smart Gate Driver

The communication between MCU and smart gate driver is executed by 4-wire serial peripheral interface. These signals have to keep the following specifications. Please construct the suitable F/W to get the certain communication.

Table 5.5-1 SPI timing specification

Item	Symbol Condition	Condition	Rated level			Unit
		Condition	MIN	TYP	MAX	Offit
Sleep mode to SPI interface ready	tready	VCC5V > Vccuvr, EN terminal from low to high	-	2	-	ms
SCLK period	tclk		500	-		ns
SCLK high time	tclkH		200	-	-	ns
SCLK low time	tclkl		200	-	-	ns
SDI input data setup time	tssdi		40	-	-	ns
SDI input data hold time	thsdi		60	-	-	ns
SDO output data delay time	tdSDO		-	-	120	ns
nSCS input setup time	tsnscs		200	-	-	ns
nSCS input hold time	tHnSCS		200	-	-	ns
nSCS high time before pulling low	tnscsH		1000	-	=	ns
Chip de-select off time	toffnscs		-	20	-	ns




Figure 5.5-1 SPI Timing Diagram

6 Smart Gate Driver Description

6.1 Power-On Sequence and Functional Modes

6.1.1 Power-On Sequence

Figure 6.1-1 shows the example of Power-On sequence. The mode of operation and nFAULT signal in the smart gate driver chip work according to EN signal from MCU (RX13T) and supply voltages including the output of the internal regulators. Refer to section 6.1.2, 6.1.3, and 6.2.




Figure 6.1-1 Power-On Sequence

6.1.2 Definitions of State of Different Modes

The smart gate driver contains four modes of operation:

Shutdown Mode:

This mode represents the state where VCC5V pin voltage is below the POR falling threshold (typical 3.63V). In this mode, most of internal functional blocks are disabled except for LDO1 and LDO3. LDO1 keeps powering the VCC5V rail until VM drops further below 1.2V. LDO3 is enabled in low power mode. Refer to section 6.3.3.

Sleep Mode:

The smart gate driver is in low-power Sleep Mode when VCC5V pin voltage is above the POR rising threshold (typical 4.0V) and EN is low. In this mode, the driver output is disabled and ignores any control input on HIx/LIx (x=A,B,C) selected from INz (z=1,2,3,4,5,6) signals. The power chain associated with the buck regulator (buck, charge pump, LDO2) is disabled. LDO1 and LDO3 are kept alive. LDO3 is enabled in low power mode. This minimizes the IC power consumption in Sleep Mode.

Operating Mode:

This mode represents the state when VCC5V pin voltage is above the POR rising threshold (typical 4.0V) and EN is pulled high. The smart gate driver is put into normal operation, high-efficiency buck regulator power chain (buck, charge pump, LDO2) and LDO3 are enabled in normal mode, and LDO1 is disabled. Driver output is enabled in response to control inputs on the Hlx/Llx (x=A,B,C) selected from INz (z=1,2,3,4,5,6) signals. No occurrence of any fault is required in this mode.

Fault Management Mode:

This mode represents the state after any fault occurs. The smart gate driver reacts to fault conditions (see section 6.2 for detailed responses) and reports the fault status to the MCU using the nFAULT terminal and through the SPI interface. In this mode, the functioning of blocks depends on the fault source and control settings.

6.1.3 Mode Transition

The mode transition conditions (A to J) are summarized in Table 6.1-1.




Figure 6.1-2 Mode Transition State Machine

6.1.3 Mode Transition (continued)

Table 6.1-1 Mode Transition Condition of State Machine

Transition	Exiting Mode	Entering Mode	Conditions	Actions
А	Shutdown	Sleep	VM rising, VCC5V > VCCUVR	Disable most of the function blocks except for 5V LDO1 and VDD LDO3 Note2. Entering Sleep Mode after device start-up delay.
В	Sleep	Operating	EN goes high and stays.	Enable all function blocks except for 5V LDO1. Entering Operating Mode after Wake-up time delay "twake".
С	Operating	Sleep	EN goes low and stays. Note1	Disable most of the function blocks except for 5V LDO1 and VDD LDO3 Note2. The control registers are reset. Entering Sleep Mode after Entry time delay "tsleep".
D	Sleep	Shutdown	VM falling, and VCC5V < Vccuv	Disable most of the function blocks except for 5V LDO1 and VDD LDO3 Note2. Entering Shutdown Mode after shutdown time delay.
E	Operating	Fault Management	Any fault condition occurs.	Respond based on fault management matrix.
F	Fault Management	Operating	Fault condition clears and operating recovers based on recovery action.	Enable all function blocks except for 5V LDO1. Entering Operating Mode after fault recovery delay.
G	Fault Management	Fault Management	Any other fault condition occurs.	Respond based on fault management matrix. Each function block disabling signal (active low) from multiple fault sources are ANDed together.
Н	Fault Management	Sleep	EN goes low and stays. Note1	Disable most of the function blocks except for 5V LDO1 and VDD LDO3 Note2. The control registers are reset. Entering Sleep Mode after fault recovery delay.
I	Fault Management	Shutdown	VCC5V < Vccuv	Disable most of the function blocks except for 5V LDO1 and VDD LDO3 Note2. The control registers are reset. Entering Shutdown Mode after shutdown time delay.
J	Operating	Shutdown	VCC5V < Vccuv	Disable most of the function blocks except for 5V LDO1 and VDD LDO3 Note2. The control registers are reset. Entering Shutdown Mode after shutdown time delay.

Note1: EN low pulse shorter than "tsleep" maximum (0.85ms) must NOT be input to avoid the unexpected behavior.

Note2: LDO3 enters a low-power mode when the EN terminal is pulled low.

6.2 Fault Management

The smart gate driver has the protect function against VM undervoltage, VM overvoltage, Charge pump undervoltage, MOSFET VDS overcurrent, Current sense overcurrent, MOSFET VGS fault, Thermal warning, Thermal shutdown, Buck regulator overcurrent, Buck regulator undervoltage, and Buck regulator overvoltage events. When a fault occurs, the individual fault bit is set high along with the global FAULT bit in FAULT status register. The FAULT bit is OR'ed with all the other individual status bits. The fault and recovery action of each function is shown in Table 6.2-1 and Table 6.2-2.



6.2 Fault Management (continued)

Table 6.2-1 Fault Management Matrix

Mode	Fault type	Condition	Configuration	Reports	Gate driver Input / Output	Regulator in Fault Management Mode	Recovery condition	Recovery action	
March Activation of March 2006 100		VCC5V < VCCUV (3.63V)	-	None	Blocked / Hi-Z pulldown		VCC5V > Vccuvr (4.0V)	Enter Sleep Mode	
1	VM undervoltage	VM < Vvmuv	DIS_VMUV=0b	nFAULT=Lo	Blocked / Hi-Z pulldown		VM > Vvmuvr	RA1	
Mathematical M	(VM_UV)	(5.3V or 7.5V)	DIS_VMUV=1b	Status bit=1b	Active	Keep state in original mode	(5.5V or 7.78V)	RA0	
March	VM overvoltage	VM - VANOV (62VA	DIS_VMOV=0b	nFAULT=Lo	Blocked / Hi-Z pulldown		VM - VAROUR (60VA	RA2	
Part	(VM_OV)	VIVI > VVIVIOV (63V)	DIS_VMOV=1b	Status bit=1b	Active	Keep state in original mode	VIVI < VVINOVR (60V)	RA0	
March	VCP undervoltage		DIS_VCPUV=0b		Blocked / Hi-Z pulldown	All reg. except LDO1 enable	VCP > VCPUV+ VCPUVHYS	RA3	
March Marc	(VCP_UV)	(0.58*VDRV)	DIS_VCPUV=1b	Status bit=1b	Active	Keep state in original mode	(0.58*VDRV +0.07*VDRV)	RA0	
Mode			VDSOCP_MODE=00b			All row overest I DO1 enable		RA4	
Mode Mode	VDS overcurrent	VDSX > VDSOCP	VDSOCP_MODE=01b		Depends on PDMODE	All reg. except LDO1 enable	Retry after tRETRY_OCP	RA5	
None None	(VDS_OCP)	(x=A,B,C)	VDSOCP_MODE=10b		Activo	Koon state in original mode		RA6	
Court state Court			VDSOCP_MODE=11b	None	Active	Keep state in original mode	None	No action is necessary.	
$ \frac{\text{CSOCP_MODE=01b}}{\text{CSOCP_MODE=10b}} = \frac{\text{CSOCP_MODE=10b}}{\text{Status bit=10}} = \frac{\text{PABLT=LO_CRatched)}}{\text{Status bit=10}} = \frac{\text{PABLT=LO_CRatched)}}{\text{Status bit=10}} = \frac{\text{PABLT=LO_CRatched)}}{\text{Active}} = \frac{\text{PABLT=LO_CRatched)}}{\text{None}} = \frac{\text{DAPS} \times \text{CSOCP}_{12.23}}{\text{None}} = \frac{\text{None}}{\text{None}} = \frac{\text{DAPS} \times \text{CSOCP}_{12.23}}{\text{None}} = \frac{\text{DAPS} \times \text{CSOCP}_{12.$	overcurrent DAZP > VCSOCP	CSOCP_MODE=00b		Depends on PDMODE			RA4		
$ \frac{(CS, OCP)}{CS, OCP)} = \frac{(CS, OCP)}{CS, OCP} = $		CSOCP_MODE=01b				Retry after tRETRY_OCP	RA5		
$ \frac{1}{MOSFT VOS fault} \\ 1$		CSOCP_MODE=10b					RA6		
$ \frac{\text{MOSFET Vos fault}}{\text{(VGS_FAULT)}} \\ \frac{\text{MOSFET_FIND}}{\text{VGS_STRUCK}} \\ \frac{\text{VGS_STRUCK}}{\text{IDS_VGSFLT=1D}} \\ \frac{\text{Status bit=1b}}{\text{None}} \\ \frac{\text{Status bit=1b}}{\text{None}} \\ \frac{\text{Active}}{\text{Active}} \\ \frac{\text{Keep state in original mode}}{\text{Keep state in original mode}} \\ \frac{\text{None}}{\text{None}} \\ \frac{\text{Status bit}}{\text{None}} \\ \frac{\text{Status bit}}{\text{Status bit}} \\ \frac{\text{TWARN_REP=0D}}{\text{TWARN_TEP=0D}} \\ \frac{\text{TWARN_REP=0D}}{\text{Status bit}}			CSOCP_MODE=11b	b None	, 50170	Keep state in original mode	None	No action is necessary.	
$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$	MOSFET Vos fault	Vocahuek - tor	DIS_VGSFLT=0b		Blocked / Hi-Z pulldown	All reg. except LDO1 enable		RA4	
Thermal shutdown (OTSD) $T_{J>TWARN (140^{\circ}C)}$ $T_{WARN_REP=1b}$	(VGS_FAULT)	VGS SIUCK > IG1	DIS_VGSFLT=1b	None	Active	Keep state in original mode	None	No action is necessary.	
TWARN_REP=1b	Thermal warning	Ti- Twany (140°C)	TWARN_REP=0b	only Status bit=1b	Activo	Keen state in original mode	Ti - Twacu Tuno (425°C)		
Thermal shutdown (OTSD) $T_j > TSD (160^{\circ}C)$ $T_j > TSD (160^{\circ}C$	(TWARN)	1] > 1 WARN (140 C)	TWARN_REP=1b		Active	Keep state in original mode	1) < 1 WARN - 1 HTS (125 C)		
DIS_OTSD=1b DIS_OTSD=1b DIS_STATUS brief b Active Keep state in original mode RA0	Thermal shutdown	Ti - Tep (160°C)	DIS_OTSD=0b	nFAULT=Lo	Blocked / Hi-Z pulldown		Ti a Ten Thive (145°C)	RA2	
$\frac{\text{Buck reg. overcurrent}}{\text{limit (SR_OC1)}} = \frac{\text{Buck reg. overcurrent}}{\text{limit (SR_OC1)}} = \frac{\text{Buck reg. overcurrent}}{\text{Imit (SR_OC21b)}} = \frac{\text{Bick reg. overcurrent}}{\text{Imit (SR_OC21b)}} = \frac{\text{Bick reg. overcurrent}}{\text{Imit (SR_OC21b)}} = \frac{\text{DiS_SROC=1b}}{\text{DiS_SROC=0b}} = \frac{\text{Bick reg. overcurrent}}{\text{DiS_SROC=1b}} = \frac{\text{Bicked/Hi-Z pulldown}}{\text{Bicked/Hi-Z pulldown}} = \frac{\text{Buck reg. soft-start done}}{\text{buck reg. hiccup mode}} = \frac{\text{Buck reg. soft-start done}}{\text{8. l. peak < IOC2_SR}} = \frac{\text{RA2}}{\text{RA3}} = \frac{\text{RA2}}{\text{RA3}} = \frac{\text{Bicked/Hi-Z pulldown}}{\text{Bicked/Hi-Z pulldown}} = \frac{\text{Buck reg. soft-start done}}{\text{buck reg. wio SR_OC}} = \frac{\text{Buck reg. soft-start done}}{\text{I. peak < IOC2_SR}} = \frac{\text{RA3}}{\text{RA4}} = \frac{\text{Bicked/Hi-Z pulldown}}{\text{Bicked/Hi-Z pulldown}} = \frac{\text{Buck reg. soft-start done}}{\text{buck reg. wio SR_OC}} = \frac{\text{Buck reg. soft-start done}}{\text{Buck reg. soft-start done}} = \frac{\text{RA4}}{\text{Active}} = \frac{\text{Bicked/Hi-Z pulldown}}{\text{Buck reg. hiccup mode}} = \frac{\text{Buck reg. soft-start done}}{\text{8. VDRV V VDRVUR (4.4V)}} = \frac{\text{RA2}}{\text{RA3}} = \frac{\text{Active}}{\text{Bicked/Hi-Z pulldown}} = \frac{\text{Buck reg. buck reg. soft-start done}}{\text{Buck reg. soft-start done}} = \frac{\text{Buck reg. soft-start done}}{\text{8. VDRV V VDRVUR (4.4V)}} = \frac{\text{RA2}}{\text{RA3}} = \frac{\text{Bucked/Hi-Z pulldown}}{\text{Bicked/Hi-Z pulldown}} = \frac{\text{Buck reg. buck reg. soft-start done}}{\text{Buck reg. soft-start done}} = \frac{\text{Buck reg. soft-start done}}{\text{8. VDRV V VDRVUR (4.4V)}} = \frac{\text{RA2}}{\text{RA3}} = \frac{\text{Bucked/Hi-Z pulldown}}{\text{Bicked/Hi-Z pulldown}} = \frac{\text{Bicked/Hi-Z pulldown}}{Bi$	(OTSD)	1) > 135 (166 0)	DIS_OTSD=1b	Status bit=1b	Active	Keep state in original mode	1) (135 - 1113 (145 6)	RA0	
DIS_SROC=1b DIS_SROC=1b DIS_SROC=0b DIS_SROC=0b DIS_SROC=0b DIS_SROC=0b DIS_SROC=1b DIS_SROC=0b DIS_SROC=1b	Buck reg. overcurrent	II pook > loc4 SB (4.2A)	DIS_SROC=0b	None	Activo		None	No action is possessory	
Buck reg. overcurrent protection (SR_OCP) Upack > ICC_SR (1.4A) DIS_SROC=1b DIS_SROC=1b DIS_SROC=1b DIS_SROC=1b DIS_SROC=1b DIS_SROC=1b DIS_SROC=1b DIS_VDRVUV=0b DIS_VDRVUV=0b DIS_VDRVUV=1b DIS_VDRVUV=1b DIS_VDRVUV=1b DIS_VDRVUV=1b DIS_VDRVUV=0b ThAULT=Lo Status bit=1b Blocked / Hi-z pulldown Active Rep state in original mode, buck reg. biccup mode & ULDO1, LDO3 enable, buck reg. biccup mode & VDRV > VDRVUN (4.4V) RA2 VDRV overvoltage (VDRV_DVV OPENUM (4.2V) VDRV overvoltage (VDRV_OPENUM (4.2V) FB > VDRVOV (0.95V) FB > VDRVOV (0.95V) The peak < ICC_SR RA0 Blocked / Hi-z pulldown Active Rep state in original mode & VDRV > VDRVUN (4.4V) RA0 Blocked / Hi-Z pulldown Charge pump, buck reg. Hi-Z FB < VDRVOVR (0.825V) FB < VDRVOVR (0.825V)	limit (SR_OC1)	ile peak > loci_sk (1.2A)		None	Active		Note	No action is necessary.	
DIS_SROC=1b DIS_SROC=1b Active Keep state in original mode, buck reg. w/o SR_OC IL peak < locz_sr RA0		II neak > 1002 SP (1.44)	DIS_SROC=0b		Blocked / Hi-Z pulldown			RA2	
VDRV undervoltage (VDRV_UV) VDRV < VDRVUV (4.2V) DIS_VDRVUV=1b FAULT=Lo Status bit=1b Blocked / Hi-2 pulldown buck reg. hiccup mode & VDRV > VDRVUVR (4.4V) RAQ VDRV overvoltage (VDRV_OV) DIS_VDRVUV=1b DIS_VDRVOV=0b Blocked / Hi-2 pulldown LDQ2_LDQ3 enable, charge pump, buck reg. Hi-2 RA3 FB > VDRVOV (0.95V) FB > VDRVOV (0.95V) FB < VDRVOVR (0.825V)	protection (SR_OCP)	pour > 1002_0R (1.4A)	eak > IOC2_SR (1.4A) Status bit=	Status bit=1b	Active		IL peak < loc2_sr	RA0	
DIS_VDRVUV=1b		VDRV < VppMM/// 2N	DIS_VDRVUV=0b		Blocked / Hi-z pulldown			RA2	
VDRV overvoltage (VDRV_OV) FB > VDRVOV (0.95V) FB > VDRVOV (0.95V) FB < VDRVOV (0.95V) FB < VDRVOV (0.95V) FB < VDRVOV (0.95V) FB < VDRVOV (0.95V) FB < VDRVOV (0.95V)	(VDRV_UV)	VDIX V \ VDRVUV (4.2V)	DIS_VDRVUV=1b	Status bit=1b	Active	Keep state in original mode	VDRV > VDRVUVR (4.4V)	RA0	
(VDRV_OV)		ER > V/pp//// /0.05\4	DIS_VDRVOV=0b		Blocked / Hi-Z pulldown		FB > \/np\/n\/p (0.925) \	RA3	
		. D > VDR.VOV (U.95V)	DIS_VDRVOV=1b	Status bit=1b	Active	Keep state in original mode	1 D < VDR VOVR (U.023V)	RA0	

6.2 Fault Management (continued)

Table 6.2-2 Fault Recovery Actions

	_	Release/Reset timing					
Recovery action	Case	Status register reset	nFAULT Device mode moves to Operating Mode		Gate driver Input / Output	Regulators soft-start	
RA0	Only report status	EN low pulse rising edge or CLR_FLT	Fault condition clears. Keep state in original mode				
RA1	VM_UV	EN low pulse rising edge or CLR_FLT	Fault condition clears.				
RA2	VM_OV, OTSD, SR_OCP, VDRV_UV	EN low pulse rising edge or CLR_FLT	Fault condition clears. EN low pulse rising edge or CLR_FLT			Fault condition clears.	
RA3	VCP_UV, VDRV_OV	EN low pulse rising edge or CLR_FLT	Fault condition clears. EN low pulse rising edge or CLR_FLT			Keep enable *Note1	
RA4	VDS_OCP, CS_OCP with OCP_MODE= 00b, or VGS_FAULT		EN low pulse rising edge or CLR_FLT Keep				
RA5	VDS_OCP, CS_OCP with OCP_MODE= 01b		Expiration of Keep of Retry delay time			Keep enable	
RA6	VDS_OCP, CS_OCP with OCP_MODE= 10b		oulse rising edge Keep state in CLR_FLT original mode				

Note1: Charge pump and buck regulator release Hi-Z after the recovery from $VDRV_OV$.

6.2.1 Fault Indicator nFAULT

The nFAULT terminal (open-drain configuration) is the fault indicator. It is pulled low if any of the fault conditions occur. It is pulled high when all the fault conditions are removed and all chip power rail start-ups are done. The nFAULT is latched only for MOSFET VDs overcurrent, Current sense overcurrent, and MOSFET VGs fault. Toggling the EN signal or setting CLR_FLT=1b in IC Control 1 register pulls the nFAULT high (if the fault is removed).

This signal notifies the MCU after any fault occurs, so the MCU can stop normal operation and enter the fault handling routine. It also informs the MCU when all fault conditions are removed and all necessary power rails are properly up, so the MCU can re-enter the normal operating routine.

6.2.2 Fault Condition Types

6.2.2.1 VCC5V Undervoltage (VCC_UV)

If the VCC5V pin voltage falls lower than the VCCUV threshold at any time, the smart gate driver enters Shutdown Mode, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs), and most of internal function blocks are disabled except for LDO1 and LDO3. Normal operation starts again (the smart gate driver enters Sleep Mode) when the VCC5V undervoltage condition is removed (VCCUVR).

6.2.2.2 VM Undervoltage (VM_UV)

If the input supply voltage on the VM pin falls lower than the VVMUV threshold at any time with DIS_VMUV=0b, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs), LDO1 and LDO3 are enabled, other regulators (buck, charge pump, LDO2) are disabled, and the nFAULT terminal is pulled low. The FAULT bit and VM UV bit are also latched high in the Fault Status registers.

The nFAULT terminal is released automatically and normal operation starts again (gate driver, buck, charge pump, LDO2, and LDO3 operation) when the VM undervoltage condition is removed (VVMUVR). The FAULT bit and VM_UV bit are reset after setting the CLR_FLT bit or an EN terminal low pulse.

This fault detection can be disabled by setting DIS_VMUV=1b in the Fault Control registers. If the VM undervoltage condition occurs with DIS_VMUV=1b, the device keeps state in original mode but the nFAULT terminal is pulled low until the VM undervoltage condition is removed (VVMUVR). The FAULT bit and VM_UV bit are set high in the Fault Status registers until cleared by the CLR FLT bit or an EN terminal low pulse.

6.2.2.3 VM Overvoltage (VM OV)

If the input supply voltage on the VM pin rises higher than the VvMoV threshold at any time with DIS_VMOV=0b, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs), LDO1 and LDO3 are enabled, other regulators (buck, charge pump, LDO2) are disabled, and the nFAULT terminal is pulled low. The FAULT bit and VM OV bit are also latched high in the Fault Status registers.

The nFAULT terminal is released automatically and normal operation starts again (buck, charge pump, LDO2, and LDO3 operation) when the VM overvoltage condition is removed (VVMOVR). The gate drivers are enabled and the FAULT bit and VM_OV bit are reset after setting the CLR_FLT bit or an EN terminal low pulse.

This fault detection can be disabled by setting DIS_VMOV=1b in the Fault Control registers. If the VM overvoltage condition occurs with DIS_VMOV=1b, the device keeps state in original mode but the nFAULT terminal is pulled low until the VM overvoltage condition is removed (VVMOVR). The FAULT bit and VM_OV bit are set high in the Fault Status registers until cleared by the CLR_FLT bit or an EN terminal low pulse.



6.2.2.4 VCP Undervoltage (VCP_UV)

If the charge pump voltage on the VCP pin falls lower than the VCPUV threshold at any time with DIS_VCPUV=0b, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs), the nFAULT terminal is pulled low, the buck regulator power chain (buck, charge pump, LDO2) and LDO3 keep enabled (LDO1 disabled). The FAULT bit and VCP_UV bit are also latched high in the Fault Status registers.

The nFAULT terminal is released automatically when the VCP undervoltage condition is removed (VCPUV + VCPUVHYS). The gate drivers are enabled and the FAULT bit and VCP_UV bit are reset after setting the CLR_FLT bit or an EN terminal low pulse.

This fault detection can be disabled by setting DIS_VCPUV=1b in the Fault Control registers. If the VCP undervoltage condition occurs with DIS_VCPUV=1b, the device keeps state in original mode but the nFAULT terminal is pulled low until the VCP undervoltage condition is removed (VCPUV + VCPUVHYS). The FAULT bit and VCP_UV bit are set high in the Fault Status registers until cleared by the CLR_FLT bit or an EN terminal low pulse.

6.2.2.5 MOSFET VDS Overcurrent (VDS_OCP)

A MOSFET VDs overcurrent is detected by monitoring the VDs voltage drop across the external MOSFET rDs(on). If the VDs voltage across an enabled MOSFET exceeds the VDSOCP threshold selected by the VDS_TH bits for longer than the tDEG_OCP deglitch time selected by the DEG_TIME bits, the smart gate driver judges VDS_OCP occurs and the fault actions are executed according to the VDSOCP_MODE bits in the Fault Control registers. The smart gate driver has following 4 different response modes for VDS_OCP fault action.

Note: For low-side VDs overcurrent, the voltage between HSx (x=A,B,C) and PGND is monitored, respectively. Therefore, this voltage includes the differential voltage across the shunt resistor.

Latch mode (VDSOCP_MODE=00b):

After a VDS_OCP in this mode, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs) or the outputs are pulled low according to the PDMODE bit, and the nFAULT terminal is pulled low. The FAULT bit, VDS_OCP bit, and corresponding VDSyx_OCP (y=H,L, x=A,B,C) bit are latched high in the Fault Status registers.

The nFAULT terminal is released, normal operation starts again, and the FAULT bit, VDS_OCP bit, and corresponding VDSyx_OCP (y=H,L, x=A,B,C) bit are reset after setting the CLR_FLT bit or an EN terminal low pulse.

Automatic Retry mode (VDSOCP_MODE=01b):

After a VDS_OCP in this mode, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs) or pulled low according to the PDMODE bit and the nFAULT terminal is pulled low. The FAULT bit, VDS_OCP bit, and corresponding VDSyx_OCP (y=H,L, x=A,B,C) bit are latched high in the Fault Status registers. The nFAULT terminal is released and normal operation starts again automatically after the tretry_ocp time passes. The FAULT bit, VDS_OCP bit, and corresponding VDSyx_OCP (y=H,L, x=A,B,C) bit keep latched until the retry starts.

Report Only mode (VDSOCP_MODE=10b):

No action takes place (the gate drivers keep active) after a VDS_OCP in this mode. The nFAULT terminal is pulled low and the FAULT, VDS_OCP, and corresponding VDSyx_OCP (y=H,L, x=A,B,C) bit are latched high in the Fault Status registers.

The controller handles the VDS_OCP appropriately by controlling INz (z=1,2,3,4,5,6) signals or EN signal. The nFAULT terminal is released and the FAULT bit, VDS_OCP bit, and corresponding VDSyx_OCP (y=H,L, x=A,B,C) bit are reset when the VDS_OCP condition is removed and the CLR_FLT bit or an EN terminal low pulse is set.

Disable mode (VDSOCP_MODE=11b):

No action and no report take place in this mode. The gate drivers keep active, the nFAULT terminal and the fault status bits keep state in original mode.



6.2.2.6 Current Sense Overcurrent (CS_OCP)

Current sense overcurrent is detected by monitoring the voltage drop across the external current sense resistor. If the differential voltage between DAzP and DAzN (z=1,2,3) exceeds the VCSOCP threshold selected by the CSOCP_TH bits for longer than the tDEG_OCP deglitch time selected by the DEG_TIME bits, the smart gate driver judges CS_OCP occurs and the fault actions are executed according to the CSOCP_MODE bits. The smart gate driver has following 4 different response modes for CS_OCP fault action. CSz_OCP (z=1,2,3) bits corresponding to each overcurrent can be disabled independently by setting DIS_CSzOCP (z=1,2,3) bits in the Fault Control registers to high. No action and no report take place in the case of DIS_CSzOCP (z=1,2,3)=1. If some differential amplifiers or DAzP, DAzN (z=1,2,3) pins are not used for shunt current sensing, corresponding DIS_CSzOCP (z=1,2,3) bits should be set to high.

Latch mode (CSOCP_MODE=00b):

After a CS_OCP in this mode, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs) or the outputs are pulled low according to the PDMODE bit and the nFAULT terminal is pulled low. The FAULT bit, CS_OCP bit, and corresponding CSz_OCP (z=1,2,3) bit are latched high in the Fault Status registers. The nFAULT terminal is released, normal operation starts again, and the FAULT bit, CS_OCP bit, and corresponding CSz_OCP (z=1,2,3) bit are reset after setting the CLR_FLT bit or an EN terminal low pulse.

Automatic Retry mode (CSOCP_MODE=01b):

After a CS_OCP in this mode, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs) or the outputs are pulled low according to the PDMODE bit and the nFAULT terminal is pulled low. The FAULT bit, CS_OCP bit, and corresponding CSz_OCP (z=1,2,3) bit are latched high in the Fault Status registers. The nFAULT terminal is released and normal operation starts again automatically after the tretry cocp time passes. The FAULT bit, CS_OCP bit, and corresponding CSz_OCP (z=1,2,3) bit keep latched until the retry starts.

Report Only mode (CSOCP_MODE=10b):

No action takes place (the gate drivers keep active) after a CS_OCP in this mode. The nFAULT terminal is pulled low and the FAULT bit, CS_OCP bit, and corresponding CSz_OCP (z=1,2,3) bit are latched high in the Fault Status registers.

The controller handles the CS_OCP appropriately by controlling INz (z=1,2,3,4,5,6) signals or EN signal. The nFAULT terminal is released and the FAULT bit, CS_OCP bit, and corresponding CSz_OCP (z=1,2,3) bit are reset when the CS_OCP condition is removed and the CLR_FLT bit or an EN terminal low pulse is set.

Disable mode (CSOCP_MODE=11b):

No action and no report take place in this mode. The gate drivers keep active, the nFAULT terminal and the fault status bits keep state in original mode.

6.2.2.7 MOSFET VGS Fault (VGS_FAULT)

MOSFET VGs fault is detected by monitoring the gate-source voltage VGs of the external MOSFET after the maximum gate transition time (tGT). If the VGs does not rise (over 3V typical) or drop (below 1V typical) by the abnormality of HOx, or LOx pins (shorted to other pins), or the inappropriate settings of ISRC_HS, ISRC_LS, and T_GT bits, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs) and the nFAULT terminal is pulled low. The FAULT bit, VGS_FAULT bit, and corresponding VGSyx_FAULT (y=H,L, x=A,B,C) bit are latched high in the Fault Status registers.

The nFAULT terminal is released, normal operation starts again, and the FAULT bit, VGS_FAULT bit, and VGSyx_FAULT (y=H,L, x=A,B,C) bit are reset after setting the CLR_FLT bit or an EN terminal low pulse. This fault detection can be disabled by setting DIS_VGSFLT=1b in the Fault Control registers. If the VGS_FAULT condition occurs with DIS_VGSFLT=1b, no action and no report take place. The gate drivers keep active, the nFAULT pin and the fault status bits keep state in original mode.



6.2.2.8 Thermal Warning (TWARN)

If the die temperature exceeds the trip point of the thermal warning temperature (Twarn), TWARN bit is set high in the Fault Status register. The device keeps state in original mode. When the die temperature falls lower than the recovery point of the thermal warning (Twarn – Thys), TWARN bit is cleared automatically. TWARN bit can be output to the nFAULT terminal by setting TWARN_REP=1b through the SPI interface.

6.2.2.9 Thermal Shutdown (OTSD)

If the die temperature exceeds the trip point of the thermal shutdown temperature (TsD) with DIS_OTSD=0b, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs), LDO1 and LDO3 are enabled, other regulators (buck, charge pump, LDO2) are disabled, and the nFAULT terminal is pulled low. The FAULT bit and OTSD bit are also latched high in the Fault Status registers.

The nFAULT terminal is released automatically and normal operation starts again (buck, charge pump, LDO2, and LDO3 operation) when the die temperature falls lower than the recovery point of the thermal shutdown (TsD – THYS). The gate drivers are enabled and the FAULT bit and OTSD bit are reset after setting the CLR FLT bit or an EN terminal low pulse.

The thermal shutdown can be disabled by setting DIS_OTSD=1b in the Fault Control registers. If the OTSD condition occurs with DIS_OTSD=1b, the device keeps state in original mode but the nFAULT terminal is pulled low until the OTSD condition is removed (TsD – THYS). The FAULT bit and OTSD bit are set high in the Fault Status registers until cleared by the CLR_FLT bit or an EN terminal low pulse. The controller handles the OTSD appropriately by controlling INz (z=1,2,3,4,5,6) signals or EN signal to avoid the high die temperature.

6.2.2.10 Buck Regulator Overcurrent Limiting (SR_OC1)

The overcurrent function of the buck regulator protects against any overload condition and output short at worst case by monitoring the current flowing through the high-side MOSFET. The device has two overcurrent function. The overcurrent function SR_OC1 limits the high-side MOSFET peak current cycle-by-cycle. No action and no report take place by SR_OC1 event except for the buck regulator. The gate drivers keep active, the nFAULT terminal and the fault status bits keep state in original mode.

6.2.2.11 Buck Regulator Overcurrent Protection (SR_OCP)

The second overcurrent function SR_OCP has the higher overcurrent threshold loc2_SR than loc1_SR. If the high-side MOSFET current reaches loc2_SR, the PWM shut off after two-cycle delay and the buck regulator enters Hiccup mode. In Hiccup mode, the PWM is disabled for a dummy cycle (63ms). After this dummy cycle, the true soft-start cycle is attempted again.

When SR_OCP occurs, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs), LDO1 and LDO3 are enabled, charge pump and LDO2 are disabled, and the nFAULT terminal is pulled low. The FAULT bit, SR_FAULT bit and SR_OCP bit are also latched high in the Fault Status registers.

The nFAULT terminal is released automatically when the overcurrent condition is removed (loc2_SR) and soft-start of power rails is done. The gate drivers are enabled and the FAULT bit, SR_FAULT bit and SR_OCP bit are reset after setting the CLR_FLT bit or an EN terminal low pulse.



6.2.2.12 Buck Regulator VDRV Undervoltage (VDRV_UV)

If the VDRV pin voltage of the buck regulator output falls lower than the VDRVUV threshold, the buck regulator enters Hiccup mode. The gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs), LDO1 and LDO3 are enabled, charge pump and LDO2 are disabled, and the nFAULT terminal is pulled low. The FAULT bit, SR_FAULT bit, and VDRV_UV bit are also latched high in the Fault Status registers. The nFAULT terminal is released automatically when the undervoltage condition is removed (VDRVUV) and soft-start of power rails is done. The gate drivers are enabled and the FAULT bit, SR_FAULT bit and VDRV_UV bit are reset after setting the CLR_FLT bit or an EN terminal low pulse.

6.2.2.13 Buck Regulator VDRV Overvoltage (VDRV_OV)

If the VDRV pin voltage of the buck regulator output rises higher than the VDRVOV threshold by FB pin voltage, the gate drivers are disabled (blocked inputs, Hi-Z pulldown outputs), LDO2 and LDO3 keep enable, charge pump and buck regulator stop switching until the fault condition is removed, and the nFAULT terminal is pulled low. The FAULT bit, SR_FAULT bit, and VDRV_OV bit are also latched high in the Fault Status registers.

The nFAULT terminal is released automatically and normal operation starts again (buck, charge pump) when the overvoltage condition is removed (VDRVOVR). The gate drivers are enabled and the FAULT bit, SR_FAULT bit and VDRV_OV bit are reset after setting the CLR_FLT bit or an EN terminal low pulse.

6.3 Power Architecture

6.3.1 Block Diagram and On/Off Table of Power Supply Blocks




Figure 6.3-1 Block Diagram of Power Supply Blocks

Table 6.3-1 On/Off Table of Power Supply Blocks

Mode	80mA 5V LDO1	100mA MCU LDO3	100mA 5V LDO2	Buck switching regulator	Charge pump	
Shutdown	On	On Note1	Off			
Sleep	On	On Note1	Off			
Operating	Off	On	On			
Fault Management	Reaction based on fault management matrix					

Note1: LDO3 enters a low-power mode when the EN terminal is pulled low.

6.3.2 VCC5V Supply

VCC5V supply consists of two LDOs and two analog switches for LDO output selection.

5V LDO1 for EN=Lo:

This LDO is a high voltage LDO fed from VM. It is enabled to generate VCC5V power upon device power-up (VCC5V reaches above rising POR) until the buck regulator soft-start is completed. Whenever LDO1 is enabled, ASW1 is also turned on.

Note: the bandgap reference used in LDO1 is untrimmed.

5V LDO2 for EN=Hi:

This LDO is a low voltage LDO fed from the buck regulator output. It supplies VCC5V in Operating Mode after the buck regulator soft-start is completed. ASW2 is on when LDO2 is used.

Note: the bandgap reference used in LDO2 is trimmed, to achieve better VCC5V accuracy in Operating Mode.

6.3.3 VDD Supply

VDD LDO is a low voltage LDO3 fed from VCC5V, designed to power the MCU and peripherals in applications as required. It has a dedicated feedback pin (FBLDO) that allows for fine adjustment of output voltage within the recommended operating condition. The internal reference is 1.2V. The output voltage is tightly regulated during normal Operating Mode. When the EN terminal is pulled low, LDO3 enters a low-power mode with not-so-tight regulation.

6.3.4 Low-side Gate Driver Supply (VDRV)

Low-side gate driver supply (VDRV) is generated by a 500mA buck switching regulator fed from VM. VDRV adjustable range is from 5V to 15V. The buck regulator integrates a 1.0Ω high voltage (65V) PMOS and the corresponding gate driver. It also integrates all the control circuitry and logic to achieve peak current mode control scheme. The freewheeling diode and inductor need to be placed externally. Regulator switching frequency is 500kHz, with two-level peak current limit at 1.2A (cycle-by-cycle current limit) and 1.4A (peak OCP threshold). Regulator output is monitored and protected from OV and UV conditions. Under medium or high load conditions, the regulator runs in continuous current mode (CCM). However, under light-load conditions, it can run in discontinuous current mode (DCM) due to the nature of asynchronous rectification. Moreover, in case of high VM low VDRV operation in light load, it can run in pulse skipping mode due to the minimum on-time limitation.





Figure 6.3-2 Buck Regulator Block Diagram

6.3.5 High-side Gate Driver Supply (VCP)

This high voltage charge pump is to generate a steady high-side gate driver supply rail at the level VBRIDGE+VDRV. The CPL pin switches between VDRV and EPAD (Ground) by complementary switches Q1 and Q2. The CPH pin switches between VBRIDGE and VCP (VBRIDGE+VDRV) by complementary switches Q3 and Q4. Q1 and Q4 are turned on and off at the same time, while Q2 and Q3 are turned on and off at the same time. In this way, during on-time of Q2 and Q3 (off-time of Q1 and Q4), the flying capacitor C3 across CPH and CPL gets charged by VBRIDGE. During on-time of Q1 and Q4 (off-time of Q2 and Q3), C2 gets charged up towards VBRIDGE+VDRV by VDRV. From its operation it can be seen that this charge pump always runs in full mode with minimal power dissipation. The complementary switches operate at 250kHz, which is 1/2 the internal oscillator frequency used by the buck regulator, and the duty cycle is 50%. The maximum loading target is 28mA. The charge pump output is monitored and undervoltage protection is implemented.

6.4 Gate Driver

6.4.1 Block Diagram



Note1: "x" in this figure stands for A,B, and C.

Figure 6.4-1 Block Diagram of Gate Driver

6.4.2 Gate Driver Control Modes

When the device is put into Operating Mode, the gate driver sets its output state based on the control signal present on HIx and LIx (x=A,B,C) signals which is selected from INz (z=1,2,3,4,5,6) signals according to HOx_SEL and LOx_SEL (x=A,B,C) bits in the Gate Driver Input Selection registers. Two gate driver control modes are available:

- 3-Phase HI/LI Mode
- 3-Phase PWM Mode

Detailed descriptions and logic truth tables are listed in the following 3-Phase HI/LI Mode and 3-Phase PWM Mode sections.

6.4.2.1 3-Phase HI/LI Mode

This mode is enabled when PWMMODE=0b in the IC Control 1 register. In this mode, HIx and LIx (x=A,B,C) inputs serve as control inputs for each individual driver output, logic active high. For each phase, the HIx (x=A,B,C) input signal controls the high-side gate driver output HOx (x=A,B,C) directly, while the LIx (x=A,B,C) input signal controls the low-side gate driver output LOx (x=A,B,C) directly. See Table 6.4-1.

Llx	Hlx	LOx	HOx - HSx	HSx
0	0	Low	Low	Hi-Z
0	1	Low	High	High
1	0	High	Low	Low
1	1	Low	Low	Hi-Z

Table 6.4-1 3-Phase HI/LI Mode Truth Table (x=A,B,C)

6.4.2.2 Three-Phase PWM Mode

This mode is enabled when PWMMODE=1b in the IC Control 1 register. In this mode, LIx (x=A,B,C) serves as the enable (logic high)/disable (logic low) of the driver output of each bridge. HIx (x=A,B,C) serves as control input for each bridge. See Table 6.4-2.

Llx	Hlx	LOx	HOx - HSx	HSx
0	0	Low	Low	Hi-Z
0	1	Low	Low	Hi-Z
1	0	High	Low	Low
1	1	Low	High	High

Table 6.4-2 3-Phase PWM Mode Truth Table (x=A,B,C)

6.4.3 Adjustable Slew-Rate

The gate driver architecture allows for the accurate setting of the gate drive source (ISRC) and sink current (ISNK). It is helpful to more accurately control and adjust the slew-rate of switch node voltage, which is beneficial for radiated emission optimization, controlling the reverse recovery of the body diode and avoiding CdV/dt induced cross-conduction. For all gate driver outputs, 16 levels of sourcing/sinking current can be supported by ISRC_HS or ISRC_LS bits through the SPI interface. The configurable range is from 50mA to 640mA for sourcing and 100mA to 1280mA for sinking.

Note: The driver sink current is automatically set to be double the source current.

The duration of driver peak source/sink current (maximum gate transition time (tgT)), can also be configured to ensure the MOSFET turns on fully. This maximum gate transition time (tgT) can be configured to four levels of options (500ns, 1000ns, 2000ns, 4000ns) by T_GT bits through the SPI interface.

6.4.4 Gate Driver Robustness Enhancement

Strong sinking current to avoid CdV/dt induced cross-conduction

Additionally, within the same bridge phase, whenever one of the gate drivers is during gate transition of turning on or turning off the corresponding external MOSFET, the complementary gate driver performs a strong sinking current (ISNK_STG) to avoid CdV/dt induced cross-conduction. The maximum duration of the strong sinking current is also equal to the maximum gate transition time (tgT).

Active pullup/pulldown current to hold gate state

After the maximum gate transition time (tgt), the driver actively imposes weaker current to hold the gate state. A pullup current (ISRC_PU) is sourced out of the driver to maintain a high output voltage, whereas a pulldown sinking current (ISNK_PD) is imposed to maintain nearly zero output voltage.

Adaptive dead time control plus configurable additional dead time

Adaptive dead time control is implemented by actively monitoring the gate of the MOSFET that is turning off first during the transition. The complementary MOSFET is allowed to start turning on only after it drops below the threshold (1V typical). In addition to adaptive dead time, you can add the extra dead time (tDT) by setting DEAD_TIME bits through SPI interface.

Note: The tGT value is defined as "maximum" gate transition time because in real applications, actual gate transition must be shorter than the tGT setting in order to properly drive the MOSFETs. Therefore, the duration of driver peak source/sink current can get terminated before reaching the full tGT duration. For example, during the turn off transition, after VGs drops below the adaptive dead time threshold, peak sink current and the complementary MOSFET gate strong sinking current are terminated, which is earlier than the elapse of tGT. For the turning-on transition, because there is no detection of VGs reaching enough high level for the MOSFET, peak source current and complementary MOSFET gate strong sinking current sustain a full tGT duration, assuming it is sufficiently long on time. Other instances involve the short on-time or off-time.

Adaptive dead time control disable function

Adaptive dead time control can be disabled by setting DIS_SADT=1b. In this case, the monitored result of the MOSFET gate voltage is ignored, and the complementary MOSFET is allowed to start turning on by the only the complementary HIx or LIx (x=A,B,C) input. After the complementary input changes to high, the extra dead time (tDT) is started to avoid the shoot through current of the gate driver. After finishing the extra dead time (tDT), the complementary MOSFET starts turning on. Refer to Figure 6.4-4.

Note: The inserted dead time should be shorter than the tgt setting in order to properly drive the MOSFETs. The duration of driver peak source/sink current is terminated after reaching the full tgt duration. Refer to Figure 6.4-5. And the inserted dead time must be longer than the MOSFET discharge time "tdchg" to avoid the shoot through current of the half-bridge MOSFET.



6.4.5 Gate Drive Timing Diagram in 3-Phase HI/LI Mode

Figure 6.4-2 shows the gate drive timing diagram if the HI/LI inserted dead time is relatively long (longer than maximum gate transition time (tgt) plus extra dead time (tgt) set). This case means:

- During high-side MOSFET turn-off/low-side MOSFET turn-on transition, if LIx (x=A,B,C) asserts high after the HOx-HSx (x=A,B,C) high-to-low transition time (tgt) and extra dead time (tgt) ends.
- During low-side MOSFET turn-off/high-side MOSFET turn-on transition, if HIx (x=A,B,C) asserts high after the LOx (x=A,B,C) high-to-low transition time (tgt) and extra dead time (tgt) ends.

Total effective dead time is adaptive dead time, plus extra dead time (tDT) selected by DEAD_TIME bits, plus additional dead time introduced by the HIx/LIx (x=A,B,C) signals.




Figure 6.4-2 Gate Drive Timing Diagram in 3-Phase HI/LI Mode if the HI/LI Inserted Dead Time is Relatively Long

6.4.5 Gate Drive Timing Diagram in 3-Phase HI/LI Mode (continued)

Figure 6.4-3 shows the gate drive timing diagram if the HIx/LIx (x=A,B,C) inserted dead time is relatively short (shorter than maximum gate transition time (tgT) plus extra dead time (tgT) set). This case means:

- During high-side MOSFET turn-off/low-side MOSFET turn-on transition, if LIx (x=A,B,C) asserts high before the HOx-HSx (x=A,B,C) high-to-low transition time (tGT) and extra dead time (tDT) ends.
- During low-side MOSFET turn-off/high-side MOSFET turn-on transition, if HIx (x=A,B,C) asserts high before the LOx (x=A,B,C) high-to-low transition time (tgt) and extra dead time (tbt) ends.

Total effective dead time is adaptive dead time, plus extra dead time (tDT) selected by DEAD_TIME bits.




Figure 6.4-3 Gate Drive Timing Diagram in 3-Phase HI/LI Mode if the HI/LI Inserted Dead Time is Relatively Short

6.4.6 Gate Drive Timing Diagram with DIS_SADT=1

Figure 6.4-4 shows the gate drive timing diagram with DIS_SADT=1b if the HIx/LIx (x=A,B,C) inserted dead time is shorter than maximum gate transition time (tgT). This case means:

- During high-side MOSFET turn-off/low-side MOSFET turn-on transition, if LIx (x=A,B,C) asserts high after the high-side MOSFET turns off and before the HOx-HSx (x=A,B,C) high-to-low transition time (tgT) ends.
- During low-side MOSFET turn-off/high-side MOSFET turn-on transition, if HIx (x=A,B,C) asserts high after the low-side MOSFET turns off and before the LOx (x=A,B,C) high-to-low transition time (tgt) ends.

Total effective dead time is a non-overlap time, plus extra dead time (tDT) selected by DEAD_TIME bits.




Figure 6.4-4 Gate Drive Timing Diagram with DIS_SADT=1 if the HI/LI Inserted Dead Time is Shorter than Gate Transition Time

6.4.6 Gate Drive Timing Diagram with DIS_SADT=1 (continued)

Figure 6.4-5 shows the gate drive timing diagram with DIS_SADT=1b if the HIx/LIx (x=A,B,C) inserted dead time is longer than maximum gate transition time (tgt). This case means:

- During high-side MOSFET turn-off/low-side MOSFET turn-on transition, if LIx (x=A,B,C) asserts high after the HOx-HSx (x=A,B,C) high-to-low transition time (tgT) ends.
- During low-side MOSFET turn-off/high-side MOSFET turn-on transition, if HIx (x=A,B,C) asserts high after the LOx (x=A,B,C) high-to-low transition time (tgT) ends.

Total effective dead time is a non-overlap time, plus extra dead time (tDT) selected by DEAD_TIME bits.




Figure 6.4-5 Gate Drive Timing Diagram with DIS_SADT=1 if the HI/LI Inserted Dead Time is Longer than Gate Transition Time

6.4.7 Gate Drive Timing Diagram in 3-Phase PWM Mode

Figure 6.4-6 shows the gate drive timing diagram when the gate driver control mode is 3-Phase PWM Mode. In this mode, the timing diagram is similar to 3-phase HI/LI Mode if the HIx/LIx (x=A,B,C) inserted dead time is zero.

Total effective dead time is adaptive dead time, plus extra dead time (tDT) selected by DEAD_TIME bits.




Figure 6.4-6 Gate Drive Timing Diagram in 3-Phase PWM Mode

6.5 **Sense Block**

6.5.1 Overview




Figure 6.5-1 Block Diagram of Sense Block

Oct 5, 2023

6.5.1 Overview (continued)

Figure 6.5-1 shows the block diagram of sense block. The smart gate driver comprises three differential programmable gain amplifiers, three general-purpose comparators, three current sense overcurrent comparators, a BEMF sense amplifier, and an analog multiplexer. The three differential amplifiers can separately support current sensing up to three phases by using low-side shunt resistors in the external halfbridges. The general-purpose comparator has 0V to VDD input common mode range. The inputs of generalpurpose comparators are DA2P, DA3P, and DA3N. The user can select these pins usage by changing the input signal only. The differential amplifiers and general-purpose comparators can be disabled individually by setting DAz EN in the IC Control registers or CMPz VTH (z=1,2,3) bits in the Sense Block Control registers to reduce the quiescent current. The current sense overcurrent comparator monitors the input of the differential amplifier continuously. The current sense overcurrent threshold VCSOCP is selectable through the CSOCP TH bits. Regarding BEMF (back electromotive force) sensing, two dedicated amplifiers form the BEMF sensing signal chain. The first differential amplifier outputs the voltage between high impedance phase and the virtual center tap. The high impedance phase is selected automatically at nSMPL falling edge, or selected by CMP1O/2O or CMP1O/3O inputs. The second programmable gain amplifier can adjust the output range suitably for the position detection by BEMF sensing. The output of BEMF sensing can be monitored through the analog multiplexer on DA3O/MUX1 pin. The analog multiplexer can output the VM voltage and die temperature by setting MUX bits in the Sense Block Control registers.

6.5.2 Differential Amplifiers for Current Sensing

The differential amplifier has the following functions.

Enable control:

Each differential amplifier can be disabled by DAz_EN (z=1,2,3)=0b according to the actual application.

Programmable gain:

The gain of differential amplifier is programmable by DAz_GAIN (z=1,2,3) bits. The gain settings are 5V/V, 10V/V, 20V/V, 40V/V.

Reference:

The output reference voltage of differential amplifier is 0.5*VDD.

Sample and hold (S/H) function:

When DAz_SH (z=1,2,3) bit is set "1", S/H function of the differential amplifier is enabled individually. Three differential amplifier outputs are sampled during nSMPL signal=L simultaneously. This function helps 3 shunt current sensing. Refer to Figure 6.5-2.

Note: The DA3O output is controlled by MUX[2:0] bits and BEMF_EN bit. When BEMF_EN bit is set to "1", S/H switch of the differential amplifier 3 keeps turn off to avoid the conflict with BEMF sense amplifier output. When BEMF_EN bit is set to "0", the output of the differential amplifier 3 can be monitored by MUX[2:0]=100b or 111b. Refer to section 6.5.5.


DC offset calibration:

DC offset calibration is automatically conducted upon device power up. It can also be initiated by setting CAL_DAz (z=1,2,3) bit in the Sense Block Control registers. When CAL_CONN bit is set to "0", it is done by turning off Sw1 and Sw2, turning on Sw3 and Sw4 (connecting differential amplifier inputs to GND), and setting gain depending on DAz_GAIN (z=1,2,3) bits, and then going through an auto-zero routine to minimize amplifier input offset. When CAL_CONN bit is set to "1", it is done by keeping Sw1 and Sw2 turn on (connecting differential amplifier inputs to the external shunt).

Note: If initiating calibration by CAL_DAz (z=1,2,3) bit, each amplifier can be calibrated individually. It takes approximately 288µs to finish calibration on each amplifier. Renesas recommends allowing 400µs per one amplifier for the calibration to complete in actual application. Although the calibration can be initiated by SPI interface even on the fly, Renesas recommends conducting the calibration when no MOSFETs are switching and with all driver output pulled low to avoid any impact of noise on calibration accuracy.



6.5.2 Differential Amplifiers for Current Sensing (continued)



Black line is the virtual signal which sampled DAzP (z=1,2,3) by nSMPL.

Figure 6.5-2 S/H Function of Current Sensing

6.5.3 BEMF Sense Amplifier

The BEMF sense amplifier has the following functions.

Enable control:

BEMF sense amplifier can be disabled by BEMF_EN=0b according to the actual application.

Programmable gain:

The gain of BEMF sense amplifier is programmable by BEMF_GAIN bits. The gain settings are 0.05V/V, 0.1V/V, 0.5V/V, 1.0V/V with DA3 GAIN=00b.

Reference:

The output reference voltage of BEMF sense amplifier is 0.5*VDD.

High impedance phase selection:

In typical trapezoidal BLDC operation, only 2-phase bridges are energized at a given time. The 3rd phase is in high impedance state (both high-side and low-side MOSFETs are turned off). By sensing the differential voltage between this high impedance phase and the virtual center tap, provides you the BEMF induced in this 3rd phase stator coil, which allows you to know/estimate the rotor position relative to this 3rd phase. This device has three methods for the high impedance phase selection according to the BEMF_PH bits. When BEMF_PH bits are set to 00xb, the 3rd phase is detected by checking the state of Hlx/Llx (x=A,B,C) signals in S/H control logic. The check timing is the falling edge of nSMPL signal. When BEMF_PH bits are set to 010b or 011b, the 3rd phase is selected according to CMP1O/2O or CMP1O/3O terminals. When BEMF_PH bits are set to 1xxb, the 3rd phase is selected according to BEMF_PH1,0 bits directly. These functions help to achieve the position sensorless trapezoidal BLDC operation without the additional external circuits. Refer to Figure 6.5-3 and section 6.7.15.

Sample and hold (S/H) function:

BEMF sense amplifier also has S/H function. S/H capacitance and amplifier are common use with the differential amplifier 3. S/H switch becomes active only when BEMF_EN bit is set to "1". The actual turning on timing of the S/H switch needs to occur after any possible transition is over. That requires to turn on after a reasonable delay relative to the Hlx/Llx (x=A,B,C) rising edge. The delay time is realized by waiting for LS_ON (or HS_ON if it's high-side turning on transition of HSx (x=A,B,C)) going high plus the configured gate driver transition time tGT. The actual turning off timing of the S/H switch aligns to the falling edge of the internal gate-off logic signal (which is issued shortly after Hlx/Llx (x=A,B,C) falling edge). This ensures the hold value is not affected by the off transition.

The turn on/off timing of the S/H switch is adjustable by nSMPL signal. The S/H switch keeps turn off during nSMPL=H. If any possible transition remains after the internal S/H delay time, the adjustment of turn on timing by nSMPL signal is necessary. Refer to Figure 6.5-4.

DC offset calibration:

DC offset calibration can be initiated by setting CAL_DA3/BEMF bit with BEMF_EN=1b. The calibration phase is selectable by the combination of CAL_BCONN bit and BEMF_PH bits in the Sense Block Control registers. The amplifier gain depends on BEMF_GAIN bits. The DC offset calibration goes through an auto-zero routine to minimize amplifier input offset.

Note: If initiating calibration by CAL_DA3/BEMF bit with BEMF_EN=1b, it takes approximately 288µs to finish calibration. Renesas recommends allowing 400µs for the calibration to complete in actual application. Although the calibration can be initiated by SPI interface even on the fly, the motor has to be stop condition to avoid BEMF voltage input.



6.5.3 BEMF Sense Amplifier (continued)




Figure 6.5-3 The Relation Between Typical Six Step Trapezoidal Drive and BEMF Detect Phase




Figure 6.5-4 S/H Timing During Commutation Period BF

6.5.4 Comparators

The general-purpose comparator has the following functions.

Enable control:

Each comparator can be disabled by setting CMPz_VTH (z=1,2,3) bits to 0000b according to the actual application.

Programmable threshold voltage and hysteresis:

The threshold voltage of general-purpose comparator is programmable by CMPz_VTH (z=1,2,3) bits individually. The threshold setting including the hysteresis voltage is following equation.

- Falling: VTH_CMP= VDD / 16 x CMPz VTH 44mV x (1 CMPz HYS)
- Rising: VTH_CMP= VDD / 16 x CMPz_VTH + 44mV x (1 CMPz_HYS)

Pin usage limitation:

The inputs of the general-purpose comparators are common use with the inputs of the differential amplifiers. When all of the differential amplifiers are used, the general-purpose comparators can be used for ONLY same inputs as the differential amplifiers.

6.5.5 MUX1 Output Control

DA3O/MUX1 pin has the analog multiplexer function. The following analog signals can be monitored depending on MUX bits in the Sense Block Control registers. After changing DA3O/MUX1 pin output or BEMF_EN bit, it is necessary to wait more than 4µs for the settling time of DA3O/MUX1 pin output.

- MUX=000b: GND (330kΩ pulldown)
- MUX=001b: VM monitor
- MUX=010b: Die temperature monitor
- MUX=011b: Differential amplifier reference voltage
- MUX=100b, BEMF_EN=0b: Differential amplifier 3 output with 10kΩ
- MUX=100b, BEMF EN=1b: BEMF sense amplifier output with 10kΩ
- MUX=101b: Differential amplifier 1 output
- MUX=110b: Differential amplifier 2 output
- MUX=111b, BEMF_EN=0b: Differential amplifier 3 output without 10kΩ
- MUX=111b, BEMF_EN=1b: BEMF sense amplifier output without 10kΩ




Figure 6.5-5 Block Diagram of Analog Multiplexer for DA3O/MUX1 Pin

6.5.6 VM Monitor

The output of VM attenuator can be monitored by setting 001b to MUX bits in SPI register. The relation between this monitored voltage (DA3O/MUX1 pin) and the VM voltage is shown in Figure 6.5-6.

The ratio of VM voltage and the monitored voltage (RVM) is 20.0 typical.




Figure 6.5-6 The Relation Between DA3O/MUX1 and VM Voltage

6.5.7 Junction Temperature Monitor

The junction temperature of the die can be monitored by setting 010b to MUX bits in SPI register.

The relation between this monitored voltage (DA3O/MUX1 pin) and the junction temperature is shown in Figure 6.5-7.

The junction temperature (Tj) is calculated by the following equation.

 $Tj [^{\circ}C] = 25[^{\circ}C] + (2.000 - MUX1 \text{ voltage}) [V] / 6.0 [mV/^{\circ}C]$

For example, in the case of ISENADIN=1.520[V]

 $Tj [^{\circ}C] = 25[^{\circ}C] + (2.000 - 1.520) [V] / 6.0 [mV/^{\circ}C] = 105[^{\circ}C]$




Figure 6.5-7 The Relation Between DA3O/MUX1 and the Junction Temperature

6.6 SPI Communication Format

The SPI block of the smart gate driver only works in slave mode. Figure 6.6-1 shows SPI communication format of both write and read mode. If the communication format is different from Figure 6.6-1, its communication becomes invalid.




Figure 6.6-1 SPI Communication Format

6.7 Control Register Map

Table 6-7 shows the control register map of the smart gate driver. The control registers are reset by entering Sleep or Shutdown Mode. Refer to section 6.1.3 Mode Transition.

Address	Register Name	Symbol	Access Type	Initial value	7	6	5	4	3	2	1	0
0x00	Fault Status 0	FLTSTS0	R	00h	FAULT	SR_FAULT	OV_UVLO	VDS_OCP	VGS_FAULT	CS_OCP	OTSD	TWARN
0x01	Fault Status 1	FLTSTS1	R	00h	VDRV_UV	VDRV_OV	SR_OCP	VCP_UV	VM_UV	VM_OV	N/A	N/A
0x02	Fault Status 2	FLTSTS2	R	00h	VDSHA_OCP	VDSLA_OCP	VGSHA_FAULT	VGSLA_FAULT	VDSHB_OCP	VDSLB_OCP	VGSHB_FAULT	VGSLB_FAULT
0x03	Fault Status 3	FLTSTS3	R	00h	VDSHC_OCP	VDSLC_OCP	VGSHC_FAULT	VGSLC_FAULT	N/A	CS1_OCP	CS2_OCP	CS3_OCP
0x04	Fault Control 1	FLTCTL1	R/W	00h	DIS_VDRVUV	DIS_VDRVOV	DIS_SROC	DIS_VCPUV	DIS_VMUV	DIS_VMOV	DIS_OTSD	TWARN_REP
0x05	Fault Control 2	FLTCTL2	R/W	07h	CSOCP_MODE1	CSOCP_MODE0	VDSOCP_MODE1	VDSOCP_MODE0	DIS_VGSFLT	DIS_CS10CP	DIS_CS2OCP	DIS_CS3OCP
0x06	IC Control 1	ICCTL1	R/W	35h	CLR_FLT	WRITE_LOCK2	WRITE_LOCK1	WRITE_LOCK0	PWMMODE	CSOCP_TH2	CSOCP_TH1	CSOCP_TH0
0x07	IC Control 2	ICCTL2	R/W	50h	DEAD_TIME1	DEAD_TIME0	T_GT1	T_GT0	BEMF_EN	DA1_EN	DA2_EN	DA3_EN
0x08	Gate Driver Control	GDCTL	R/W	FFh	ISRC_HS3	ISRC_HS2	ISRC_HS1	ISRC_HS0	ISRC_LS3	ISRC_LS2	ISRC_LS1	ISRC_LS0
0x09	Over Current Protection Control	OCPCTL	R/W	00h	VDS_TH3	VDS_TH2	VDS_TH1	VDS_TH0	TRETRY_CSOCP	TRETRY_VDSOCP	DEG_TIME1	DEG_TIME0
0x0A	Phase-A Gate Driver Input Selection	GDSELA	R/W	14h	CMP1_HYS	HOA_SEL2	HOA_SEL1	HOA_SEL0	VMUV_TH	LOA_SEL2	LOA_SEL1	LOA_SEL0
0x0B	Phase-B Gate Driver Input Selection	GDSELB	R/W	25h	CMP2_HYS	HOB_SEL2	HOB_SEL1	HOB_SEL0	PDMODE	LOB_SEL2	LOB_SEL1	LOB_SEL0
0x0C	Phase-C Gate Driver Input Selection	GDSELC	R/W	36h	CMP3_HYS	HOC_SEL2	HOC_SEL1	HOC_SEL0	CPUV_TH	LOC_SEL2	LOC_SEL1	LOC_SEL0
0x0D	Sense Block Control 1	SNSCTL1	R/W	AAh	BEMF_GAIN1	BEMF_GAIN0	DA1_GAIN1	DA1_GAIN0	DA2_GAIN1	DA2_GAIN0	DA3_GAIN1	DA3_GAIN0
0x0E	Sense Block Control 2	SNSCTL2	R/W	00h	CAL_BCONN	BEMF_PH2	BEMF_PH1	BEMF_PH0	BEMF_SH	DA1_SH	DA2_SH	DA3_SH
0x0F	Sense Block Control 3	SNSCTL3	R/W	88h	CMP1_VTH3	CMP1_VTH2	CMP1_VTH1	CMP1_VTH0	CMP2_VTH3	CMP2_VTH2	CMP2_VTH1	CMP2_VTH0
0x10	Sense Block Control 4	SNSCTL4	R/W	80h	CMP3_VTH3	CMP3_VTH2	CMP3_VTH1	CMP3_VTH0	CAL_CONN	CAL_DA1	CAL_DA2	CAL_DA3/BEMF
0x11	Sense Block Control 5	SNSCTL5	R/W	00h	DIS_SADT	RESERVED11_6	CTL6_UNLOCK	RESERVED11_4	RESERVED11_3	MUX2	MUX1	MUX0
0x12	Sense Block Control 6	SNSCTL6	R/W	40h	RESERVED12_7	BEMF_OFFSET	RESERVED12_5	RESERVED12_4	RESERVED12_3	RESERVED12_2	RESERVED12_1	GD_AOR

Table 6-7 Control Register Map

6.7.1 Fault Status 0 Register: FLTSTS0 (Address=0x00) [Default=0x00]

Figure 6.7-1 and Table 6.7-1 show the details of Fault Status 0 register.

Figure 6.7-1 Fault Status 0 Register FLTSTS0

7	6	5	4	3	2	1	0
FAULT	SR_FAULT	OV_UVLO	VDS_OCP	VGS_FAULT	CS_OCP	OTSD	TWARN
R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b

Table 6.7-1 Fault Status 0 Register FLTSTS0 Descriptions

Bit	Field	Туре	Default	Description
7	FAULT	R	0b	Logic OR of all Fault Status bits
6	SR_FAULT	R	0b	Logic OR of the Fault Status bits for buck switching regulator: VDRV_UV, VDRV_OV, SR_OCP
5	OV_UVLO	R	0b	Logic OR of the Fault Status bits for undervoltage and overvoltage: VCP_UV, VM_UV, VM_OV
4	VDS_OCP	R	0b	Logic OR of the Fault Status bits for Vbs overcurrent: VDSHx_OCP, VDSLx_OCP
3	VGS_FAULT	R	0b	Logic OR of the Fault Status bits for Ves fault: VGSHx_FAULT, VGSLx_FAULT
2	CS_OCP	R	0b	Logic OR of the Fault Status bits for current sense overcurrent: CS1_OCP, CS2_OCP, CS3_OCP
1	OTSD	R	0b	Indicator of thermal shutdown
0	TWARN	R	0b	Indicator of thermal warning

Note1: Fault status registers are reset by writing 1b to CLR_FLT, or recovery low pulse (>tsleep: 0.85ms) on EN pin.

6.7.2 Fault Status 1 Register: FLTSTS1 (Address=0x01) [Default=0x00]

Figure 6.7-2 and Table 6.7-2 show the details of Fault Status 1 register.

Figure 6.7-2 Fault Status 1 Register FLTSTS1

7	6	5	4	3	2	1	0
VDRV_UV	VDRV_OV	SR_OCP	VCP_UV	VM_UV	VM_OV	N/A	N/A
R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b

Table 6.7-2 Fault Status 1 Register FLTSTS1 Descriptions

Bit	Field	Туре	Default	Description			
7	VDRV_UV	R	0b	Indicator of VDRV undervoltage (VDRVUV)			
6	VDRV_OV	R	0b	Indicator of VDRV overvoltage (VDRVOV)			
5	SR_OCP	R	0b	Indicator of buck switching regulator overcurrent (loc2_sR)			
4	VCP_UV	R	0b	Indicator of VCP undervoltage (Vcpuv)			
3	VM_UV	R	0b	Indicator of VM undervoltage (VvMuv)			
2	VM_OV	R	0b	Indicator of VM overvoltage (Vvmov)			
1	N/A	R	0b	Not assigned			
0	N/A	R	0b	Not assigned			

 $Note 1: Fault \ status \ registers \ are \ reset \ by \ writing \ 1b \ to \ CLR_FLT, \ or \ recovery \ low \ pulse \ (>tsleep: 0.85ms) \ on \ EN \ pin.$

6.7.3 Fault Status 2 Register: FLTSTS2 (Address=0x02) [Default=0x00]

Figure 6.7-3 and Table 6.7-3 show the details of Fault Status 2 register.

Figure 6.7-3 Fault Status 2 Register FLTSTS2

7	6	5	4	3	2	1	0
VDSHA_OCP	VDSLA_OCP	VGSHA_FAULT	VGSLA_FAULT	VDSHB_OCP	VDSLB_OCP	VGSHB_FAULT	VGSLB_FAULT
R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b

Table 6.7-3 Fault Status 2 Register FLTSTS2 Descriptions

Bit	Field	Туре	Default	Description
7	VDSHA_OCP	R	0b	Indicator of Vps overcurrent on Phase-A high-side MOSFET
6	VDSLA_OCP	R	0b	Indicator of Vps overcurrent on Phase-A low-side MOSFET
5	VGSHA_FAULT	R	0b	Indicator of Ves fault on Phase-A high-side MOSFET
4	VGSLA_FAULT	R	0b	Indicator of Ves fault on Phase-A low-side MOSFET
3	VDSHB_OCP	R	0b	Indicator of Vps overcurrent on Phase-B high-side MOSFET
2	VDSLB_OCP	R	0b	Indicator of Vps overcurrent on Phase-B low-side MOSFET
1	VGSHB_FAULT	R	0b	Indicator of Ves fault on Phase-B high-side MOSFET
0	VGSLB_FAULT	R	0b	Indicator of Vos fault on Phase-B low-side MOSFET

 $Note 1: Fault \ status \ registers \ are \ reset \ by \ writing \ 1b \ to \ CLR_FLT, \ or \ recovery \ low \ pulse \ (>tsleep: 0.85ms) \ on \ EN \ pin.$

6.7.4 Fault Status 3 Register: FLTSTS3 (Address=0x03) [Default=0x00]

Figure 6.7-4 and Table 6.7-4 show the details of Fault Status 3 register.

Figure 6.7-4 Fault Status 3 Register FLTSTS3

7	6	5	4	3	2	1	0
VDSHC_OCP	VDSLC_OCP	VGSHC_FAULT	VGSLC_FAULT	N/A	CS1_OCP	CS2_OCP	CS3_OCP
R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b	R: 0b

Table 6.7-4 Fault Status 3 Register FLTSTS3 Descriptions

Bit	Field	Туре	Default	Description	
7	VDSHC_OCP	R	0b	Indicator of Vos overcurrent on Phase-C high-side MOSFET	
6	VDSLC_OCP	R	0b	Indicator of Vps overcurrent on Phase-C low-side MOSFET	
5	VGSHC_FAULT	R	0b	Indicator of Vss fault on Phase-C high-side MOSFET	
4	VGSLC_FAULT	R	0b	Indicator of Ves fault on Phase-C low-side MOSFET	
3	N/A	R	0b	Not assigned	
2	CS1_OCP	R	0b	Indicator of current sense overcurrent by DA1P, DA1N inputs	
1	CS2_OCP	R	0b	Indicator of current sense overcurrent by DA2P, DA2N inputs	
0	CS3_OCP	R	0b	Indicator of current sense overcurrent by DA3P, DA3N inputs	

 $Note 1: Fault \ status \ registers \ are \ reset \ by \ writing \ 1b \ to \ CLR_FLT, \ or \ recovery \ low \ pulse \ (>tsleep: 0.85ms) \ on \ EN \ pin.$

6.7.5 Fault Control 1 Register: FLTCTL1 (Address=0x04) [Default=0x00]

Figure 6.7-5 and Table 6.7-5 show the details of Fault Control 1 register.

Figure 6.7-5 Fault Control 1 Register FLTCTL1

7	6	5	4	3	2	1	0
DIS_VDRVUV	DIS_VDRVOV	DIS_SROC	DIS_VCPUV	DIS_VMUV	DIS_VMOV	DIS_OTSD	TWARN_REP
R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b

Table 6.7-5 Fault Control 1 Register FLTCTL1 Descriptions

Bit	Field	Туре	Default	Description
7	DIS_VDRVUV	R/W	0b	Write 1b to report status only for VDRV undervoltage (VDRVUV) detection
6	DIS_VDRVOV	R/W	0b	Write 1b to report status only for VDRV overvoltage (VDRVOV) detection
5	DIS_SROC	R/W	0b	Write 1b to report status only for buck switching regulator overcurrent (loc2_sR) protection
4	DIS_VCPUV	R/W	0b	Write 1b to report status only for VCP undervoltage (VcPuv) detection
3	DIS_VMUV	R/W	0b	Write 1b to report status only for VM undervoltage (V/MUV) detection
2	DIS_VMOV	R/W	0b	Write 1b to report status only for VM overvoltage fault (Vvmov) detection
1	DIS_OTSD	R/W	0b	Write 1b to report status only for thermal shutdown
0	TWARN_REP	R/W	0b	0b: Thermal warning is reported on only TWARN bit. 1b: Thermal warning is reported on nFAULT pin, FAULT bit and TWARN bit.

6.7.6 Fault Control 2 Register: FLTCTL2 (Address=0x05) [Default=0x07]

Figure 6.7-6 and Table 6.7-6 show the details of Fault Control 2 register.

Figure 6.7-6 Fault Control 2 Register FLTCTL2

7	6	5	4	3	2	1	0
CSOCP_MODE1	CSOCP_MODE0	VDSOCP_MODE1	VDSOCP_MODE0	DIS_VGSFLT	DIS_CS1OCP	DIS_CS2OCP	DIS_CS3OCP
R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 1b	R/W: 1b	R/W: 1b

Table 6.7-6 Fault Control 2 Register FLTCTL2 Descriptions

Bit	Field	Туре	Default	Description				
7	CSOCP_MODE1	R/W	0b	Response mode for current sense overcurrent 00b: Latch upon current sense overcurrent Note2				
6	CSOCP_MODE0	R/W	0b	O1b: Automatic retry upon current sense overcurrent 10b: Report on nFAULT pin, FAULT, CS_OCP and CS1/2/3_OCP bits only. No action takes place 11b: Disable. No report and no action takes place. Response mode for Vos overcurrent				
5	VDSOCP_MODE1	R/W	0b	Response mode for V _{DS} overcurrent 00b: Latch upon V _{DS} overcurrent Note2 01b: Automatic retry upon V _{DS} overcurrent				
4	VDSOCP_MODE0	R/W	0b	10b: Report on nFAULT pin, FAULT, VDS_OCP, VDSHx_OCP and VDSLx_OCP bits only. No action takes place. 11b: Disable, No report and no action takes place				
3	DIS_VGSFLT	R/W	0b	Write 1b to disable Vos fault detection				
2	DIS_CS1OCP	R/W	1b	Write 1b to disable current sense overcurrent by DA1P, DA1N inputs				
1	DIS_CS2OCP	R/W	1b	Write 1b to disable current sense overcurrent by DA2P, DA2N inputs				
0	DIS_CS3OCP	R/W	1b	Write 1b to disable current sense overcurrent by DA3P, DA3N inputs				

Note2: Latch is recovered by writing 1b to CLR_FLT, or recovery low pulse (>tsleep: 0.85ms) on EN pin.



6.7.7 IC Control 1 Register: ICCTL1 (Address=0x06) [Default=0x35]

Figure 6.7-7 and Table 6.7-7 show the details of IC Control1 register.

Figure 6.7-7 IC Control 1 Register ICCTL1

7	6	6 5		3	2	1	0
CLR_FLT	WRITE_LOCK2	WRITE_LOCK1	WRITE_LOCK0	PWMMODE	CSOCP_TH2	CSOCP_TH1	CSOCP_TH0
R/W: 0b	R/W: 0b	R/W: 1b	R/W: 1b	R/W: 0b	R/W: 1b	R/W: 0b	R/W: 1b

Table 6.7-7 IC Control 1 Register ICCTL1 Descriptions

Bit	Field	Туре	Default	Description
7	CLR_FLT	R/W	0b	Write 1b to clear the all flagged fault status bits. This bit is reset to 0b automatically.
6	WRITE_LOCK2	R/W	0b	Write 110b to ignore all further register write except WRITE LOCK[2:0].
5	WRITE_LOCK1	R/W	1b	Write 011b to unlock to allow register write.
4	WRITE_LOCK0	R/W	1b	Writing other values takes no effect.
3	PWMMODE	R/W	0b	0b: 3-Phase HI/LI mode, 1b: 3-Phase PWM mode
2	CSOCP_TH2	R/W	1b	Threshold voltage setting of current sense overcurrent by DAzP, DAzN (z=1,2,3) inputs
1	CSOCP_TH1	R/W	0b	000b: 51mV, 001b: 105mV, 010b: 157mV, 011b: 208mV,
0	CSOCP_TH0	R/W	1b	100b: 260mV, 101b: 516mV, 110b: 773mV, 111b: 1029mV

6.7.8 IC Control 2 Register: ICCTL2 (Address=0x07) [Default=0x50]

Figure 6.7-8 and Table 6.7-8 show the details of ICCTL2 register.

Figure 6.7-8 IC Control 2 Register ICCTL2

7	6	5	4	3	2	1	0
DEAD_TIME1	DEAD_TIME0	T_GT1	T_GT0	BEMF_EN	DA1_EN	DA2_EN	DA3_EN
R/W: 0b	R/W: 1b	R/W: 0b	R/W: 1b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b

Table 6.7-8 IC Control 2 Register ICCTL2 Descriptions

Bit	Field	Туре	Default	Description	
7	DEAD_TIME1	R/W	0b	Dead time from Vss voltage monitor output to start timing of another-side turn on	
6	DEAD_TIME0	R/W	1b	00b: 50ns, 01b: 100ns, 10b: 200ns, 11b: 400ns	
5	T_GT1	R/W	0b	Maximum gate transition time	
4	T_GT0	R/W	1b	00b: 500ns, 01b: 1000ns, 10b: 2000ns, 11b: 4000ns	
3	BEMF_EN	R/W	0b	Write 1b to enable BEMF sense amplifier.	
2	DA1_EN	R/W	0b	Write 1b to enable differential amplifier 1.	
1	DA2_EN	R/W	0b	Write 1b to enable differential amplifier 2.	
0	DA3_EN	R/W	0b	Write 1b to enable differential amplifier 3.	

6.7.9 Gate Drive Control Register: GDCTL (Address=0x08) [Default=0xFF]

Figure 6.7-9 and Table 6.7-9 show the details of Gate Drive Control register.

Figure 6.7-9 Gate Drive Control Register GDCTL

7	6	6 5		3	2	1	0
ISRC_HS3	ISRC_HS2	ISRC_HS1	ISRC_HS0	ISRC_LS3	ISRC_LS2	ISRC_LS1	ISRC_LS0
R/W: 1b	R/W: 1b	R/W: 1b	R/W: 1b	R/W: 1b	R/W: 1b	R/W: 1b	R/W: 1b

Table 6.7-9 Gate Drive Control Register GDCTL Descriptions

Bit	Field	Туре	Default	Description
7	ISRC_HS3	R/W	1b	High-side gate driver output source current. Sink current is 2*(source current).
6	ISRC_HS2	R/W	1b	0000b: 50mA, 0001b: 60mA, 0010b: 70mA, 0011b: 80mA, 0100b: 100mA, 0101b: 120mA, 0110b: 140mA, 0111b: 160mA,
5	ISRC_HS1	R/W	1b	1000b: 200mA, 1001b: 240mA, 1010b: 280mA, 1011b: 320mA,
4	ISRC_HS0	R/W	1b	1100b: 400mA, 1101b: 480mA, 1110b: 560mA, 1111b: 640mA
3	ISRC_LS3	R/W	1b	Low-side gate driver output source current. Sink current is 2*(source current).
2	ISRC_LS2	R/W	1b	0000b: 50mA, 0001b: 60mA, 0010b: 70mA, 0011b: 80mA, 0100b: 100mA, 0101b: 120mA, 0110b: 140mA, 0111b: 160mA.
1	ISRC_LS1	R/W	1b	1000b: 200mA, 1001b: 240mA, 1010b: 280mA, 1011b: 320mA,
0	ISRC_LS0	R/W	1b	1100b: 400mA, 1101b: 480mA, 1110b: 560mA, 1111b: 640mA

6.7.10 Overcurrent Protection Control Register: OCPCTL (Address=0x09) [Default=0x00]

Figure 6.7-10 and Table 6.7-10 show the details of OCP Control register.

Figure 6.7-10 Overcurrent Protection Control Register OCPCTL

7	6	5	4	3	2	1	0
VDS_TH3	VDS_TH2	VDS_TH1	VDS_TH0	TRETRY_CSOCP	TRETRY_VDSOCP	DEG_TIME1	DEG_TIME0
R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b

Table 6.7-10 Overcurrent Protection Control Register OCPCTL Descriptions

Bit	Field	Туре	Default	Description
7	VDS_TH3	R/W	0b	Threshold voltage setting of Vos overcurrent fault
6	VDS_TH2	R/W	0b	0000b: 40mV, 0001b: 60mV, 0010b: 80mV, 0011b: 120mV, 0100b: 160mV, 0101b: 200mV, 0110b: 240mV, 0111b: 320mV,
5	VDS_TH1	R/W	0b	1000b: 400mV, 1001b: 480mV, 1010b: 600mV, 1011b: 720mV,
4	VDS_TH0	R/W	0b	1100b: 960mV, 1101b: 1200mV, 1110b: 1600mV, 1111b: 2000mV
3	TRETRY_CSOCP	R/W	0b	Retry time for current sense overcurrent fault with CSOCP_MODE=01b, 0b: 4000µs, 1b: 70µs
2	TRETRY_VDSOCP	R/W	0b	Retry time for Vos overcurrent fault with VDSOCP_MODE=01b, 0b: 4000µs, 1b: 70µs
1	DEG_TIME1	R/W	0b	Deglitch time for both current sense and Vbs overcurrent fault
0	DEG_TIME0	R/W	0b	00b: 1.57μs, 01b: 2.38μs, 10b: 3.49μs, 11b: 5.73μs

6.7.11 Phase-A Gate Driver Input Selection Register: GDSELA (Address=0x0A) [Default=0x14]

Figure 6.7-11 and Table 6.7-11 show Phase-A Gate Driver Input Selection register.

Figure 6.7-11 Phase-A Gate Driver Input Selection Register GDSELA

7	6 5		4	3	2	1	0
CMP1_HYS	HOA_SEL2	HOA_SEL1	HOA_SEL0	VMUV_TH	LOA_SEL2	LOA_SEL1	LOA_SEL0
R/W: 0b	R/W: 0b	R/W: 0b	R/W: 1b	R/W: 0b	R/W: 1b	R/W: 0b	R/W: 0b

Table 6.7-11 Phase-A Gate Driver Input Selection Register GDSELA Descriptions

Bit	Field	Туре	Default	Description				
7	CMP1_HYS	R/W	0b	Comparator 1 hysteresis setting, 0b: +/-44mV, 1b: 0mV				
6	HOA_SEL2	R/W	0b	Nuna				
5	HOA_SEL1	R/W	0b	Input selection for Phase-A high-side gate driver Note3 000b: Lo fix, 001b: IN1, 010b: IN2, 011b: IN3, 100b: IN4, 101b: IN5, 110b: IN6, 111b: Hi-Z				
4	HOA_SEL0	R/W	1b	0000. 20 mg, 00 10. ma, 01 00. ma, 01 10. ma, 10 00. ma, 10 10. ma, 11 00. ma, 11 00. ma				
3	VMUV_TH	R/W	0b	VM under voltage threshold setting, 0b: 5.3V, 1b: 7.5V				
2	LOA_SEL2	R/W	1b	No. o				
1	LOA_SEL1	R/W	0b	Input selection for Phase-A low-side gate driver Note3 000b: Lo fix, 001b: IN1, 010b: IN2, 011b: IN3, 100b: IN4, 101b: IN5, 110b: IN6, 111b: Hi-Z				
0	LOA_SEL0	R/W	0b	0000. E0 114, 00 10. 1141, 01 00. 1142, 01 10. 1140, 1000. 1144, 10 10. 1140, 11 100. 1140, 11 10. 1142				

Note3: When HOx_SEL or LOx_SEL bits set to 111b, the source/sink current of gate driver becomes off (Hi-Z).

6.7.12 Phase-B Gate Driver Input Selection Register: GDSELB (Address=0x0B) [Default=0x25]

Figure 6.7-12 and Table 6.7-12 show Phase-B Gate Driver Input Selection register.

Figure 6.7-12 Phase-B Gate Driver Input Selection Register GDSELB

7	6	5	4	3	2	1	0
CMP2_HYS	HOB_SEL2	HOB_SEL1	HOB_SEL0	PDMODE	LOB_SEL2	LOB_SEL1	LOB_SEL0
R/W: 0b	R/W: 0b	R/W: 1b	R/W: 0b	R/W: 0b	R/W: 1b	R/W: 0b	R/W: 1b

Table 6.7-12 Phase-B Gate Driver Input Selection Register GDSELB Descriptions

Bit	Field	Туре	Default	Description				
7	CMP2_HYS	R/W	0b	Comparator 2 hysteresis setting, 0b: +/-44mV, 1b: 0mV				
6	HOB_SEL2	R/W	0b	land a latin for Dhang Dhinh aide mate drive Note3				
5	HOB_SEL1	R/W	1b	Input selection for Phase-B high-side gate driver Note3 000b: Lo fix, 001b: IN1, 010b: IN2, 011b: IN3, 100b: IN4, 101b: IN5, 110b: IN6, 111b: Hi-Z				
4	HOB_SEL0	R/W	0b	0000. E0 IIX, 0010. IIII, 0100. IIIE, 0110. III0, 1000. IIII, 1010. III0, 1100. III				
3	PDMODE	R/W	0b	Gate driver pulldown mode after VDS_OCP, CS_OCP, 0b: Hi-Z pulldown, 1b: driver output low				
2	LOB_SEL2	R/W	1b	No.				
1	LOB_SEL1	R/W	0b	Input selection for Phase-B low-side gate driver Note3 000b: Lo fix, 001b: IN1, 010b: IN2, 011b: IN3, 100b: IN4, 101b: IN5, 110b: IN6, 111b: Hi-Z				
0	LOB_SEL0	R/W	1b	0000. E0 117, 0010. 1141, 0100. 1142, 0110. 1140, 1000. 1144, 1010. 1140, 1100. 1140, 1110. 1142				

Note3: When HOx_SEL or LOx_SEL bits set to 111b, the source/sink current of gate driver becomes off (Hi-Z).



6.7.13 Phase-C Gate Driver Input Selection Register: GDSELC (Address=0x0C) [Default=0x36]

Figure 6.7-13 and Table 6.7-13 show Phase-C Gate Driver Input Selection register.

Figure 6.7-13 Phase-C Gate Driver Input Selection Register GDSELC

7	6	5	4	3	2	1	0
CMP3_HYS	HOC_SEL2	HOC_SEL1	HOC_SEL0	CPUV_TH	LOC_SEL2	LOC_SEL1	LOC_SEL0
R/W: 0b	R/W: 0b	R/W: 1b	R/W: 1b	R/W: 0b	R/W: 1b	R/W: 1b	R/W: 0b

Table 6.7-13 Phase-C Gate Driver Input Selection Register GDSELC Descriptions

Bit	Field	Туре	Default	Description				
7	CMP3_HYS	R/W	0b	Comparator 3 hysteresis setting, 0b: +/-44mV, 1b: 0mV				
6	HOC_SEL2	R/W	0b	Note3				
5	HOC_SEL1	R/W	1b	Input selection for Phase-C high-side gate driver Note3 000b: Lo fix, 001b: IN1, 010b: IN2, 011b: IN3, 100b: IN4, 101b: IN5, 110b: IN6, 111b: Hi-Z				
4	HOC_SEL0	R/W	1b	0000. E0 IIX, 00 ID. IIVI, 0 I 00. IIV2, 0 I ID. IIV0, 1000. IIV4, 10 ID. IIV0, 11 IO. IIV0, 11 ID. III 2				
3	CPUV_TH	R/W	0b	VCP under voltage threshold setting, 0b: 0.58*VDRV, 1b: 0.8*VDRV				
2	LOC_SEL2	R/W	1b	Notes				
1	LOC_SEL1	R/W	1b	Input selection for Phase-C low-side gate driver Note3 000b: Lo fix, 001b: IN1, 010b: IN2, 011b: IN3, 100b: IN4, 101b: IN5, 110b: IN6, 111b: Hi-Z				
0	LOC_SEL0	R/W	0b	0000. E0 115, 0010. 1141, 0100. 1142, 0110. 1140, 1000. 1144, 1010. 1140, 1100. 1140, 1110. 1112				

Note3: When HOx_SEL or LOx_SEL bits set to 111b, the source/sink current of gate driver becomes off (Hi-Z).

6.7.14 Sense Block Control 1 Register: SNSCTL1 (Address=0x0D) [Default=0xAA]

Figure 6.7-14 and Table 6.7-14 show Sense Block Control 1 register.

Figure 6.7-14 Sense Block Control 1 Register SNSCTL1

7	6	5	4	3	2	1	0
BEMF_GAIN1	BEMF_GAIN0	DA1_GAIN1	DA1_GAIN0	DA2_GAIN1	DA2_GAIN0	DA3_GAIN1	DA3_GAIN0
R/W: 1b	R/W: 0b	R/W: 1b	R/W: 0b	R/W: 1b	R/W: 0b	R/W: 1b	R/W: 0b

Table 6.7-14 Sense Block Control 1 Register SNSCTL1 Descriptions

Bit	Field	Туре	Default	Description	
7	BEMF_GAIN1	R/W	1b	Gain setting of BEMF sense amplifier with DA3_GAIN=00b	
6	BEMF_GAIN0	R/W	0b	00b: 0.05V/V, 01b: 0.1V/V, 10b: 0.5V/V, 11b: 1.0V/V	
5	DA1_GAIN1	R/W	1b	Gain setting of differential amplifier 1	
4	DA1_GAIN0	R/W	0b	00b: 5V/V, 01b: 10V/V, 10b: 20V/V, 11b: 40V/V	
3	DA2_GAIN1	R/W	1b	Gain setting of differential amplifier 2	
2	DA2_GAIN0	R/W	0b	00b: 5V/V, 01b: 10V/V, 10b: 20V/V, 11b: 40V/V	
1	DA3_GAIN1	R/W	1b	Gain setting of differential amplifier 3	
0	DA3_GAIN0	R/W	0b	00b: 5V/V, 01b: 10V/V, 10b: 20V/V, 11b: 40V/V	

6.7.15 Sense Block Control 2 Register: SNSCTL2 (Address=0x0E) [Default=0x00]

Figure 6.7-15 and Table 6.7-15 show Sense Block Control 2 register.

Figure 6.7-15 Sense Block Control 2 Register SNSCTL2

7	6	5	4	3	2	1	0
CAL_BCONN	BEMF_PH2	BEMF_PH1	BEMF_PH0	BEMF_SH	DA1_SH	DA2_SH	DA3_SH
R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b

Table 6.7-15 Sense Block Control 2 Register SNSCTL2 Descriptions

Bit	Field	Туре	Default	Description
7	CAL_BCONN	R/W	0b	Input selection of BEMF sense amplifier during BEMF offset calibration Ob: The amplifier inputs are connected to the reference voltage of BEMF sense amplifier (DAREF) 1b: The amplifier inputs are connected to the phase selected by BEMF_PH bits
6	BEMF_PH2	R/W	0b	Detect phase selection of BEMF sense amplifier Note4 00xb: Select automatically from the input signals of the gate driver at every nSMPL falling edge
5	BEMF_PH1	R/W	0b	010b: Select by CMP1O and CMP2O pins (CMP1O, CMP2O)= (0,0): No selection, (0,1): Phase-A, (1,0): Phase-B, (1,1): Phase-C 011b: Select by CMP1O and CMP3O pins
4	BEMF_PH0	R/W	0b	(CMP1O, CMP3O)= (0,0): No selection, (0,1): Phase-A, (1,0): Phase-B, (1,1): Phase-C 100b: No selection, 101b: Phase-A, 110b: Phase-B, 111b: Phase-C
3	BEMF_SH	R/W	0b	S/H control setting of BEMF sense amplifier Note4 0b: keep sampling, 1b: sampling during nSMPL signal=Lo & PWM ON after tGT
2	DA1_SH	R/W	0b	S/H control setting of differential amplifier 1 Note4 0b: keep sampling, 1b: sampling during nSMPL signal=Lo
1	DA2_SH	R/W	0b	S/H control setting of differential amplifier 2 Note4 0b: keep sampling, 1b: sampling during nSMPL signal=Lo
0	DA3_SH	R/W	0b	S/H control setting of differential amplifier 3 Note4 0b: keep sampling, 1b: sampling during nSMPL signal=Lo

Note4: Refer to the detail description of Differential Amplifiers for Current Sensing and BEMF sense amplifier

6.7.16 Sense Block Control 3 Register: SNSCTL3 (Address=0x0F) [Default=0x88]

Figure 6.7-16 and Table 6.7-16 show Sense Block Control 3 register.

Figure 6.7-16 Sense Block Control 3 Register SNSCTL3

7	6	5	4	3	2	1	0
CMP1_VTH3	CMP1_VTH2	CMP1_VTH1	CMP1_VTH0	CMP2_VTH3	CMP2_VTH2	CMP2_VTH1	CMP2_VTH0
R/W: 1b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 1b	R/W: 0b	R/W: 0b	R/W: 0b

Table 6.7-16 Sense Block Control 3 Register SNSCTL3 Descriptions

Bit	Field	Туре	Default	Description
7	CMP1_VTH3	R/W	1b	
6	CMP1_VTH2	R/W	0b	Threshold voltage setting of Comparator 1 0000b: Disable,
5	CMP1_VTH1	R/W	0b	0001b to 1111b: Threshold voltage = VDD /16 x CMP1 VTH
4	CMP1_VTH0	R/W	0b	
3	CMP2_VTH3	R/W	1b	
2	CMP2_VTH2	R/W	0b	Threshold voltage setting of Comparator 2 0000b: Disable,
1	CMP2_VTH1	R/W	0b	0001b to 1111b: Threshold voltage = VDD /16 x CMP2 VTH
0	CMP2_VTH0	R/W	0b	, -

6.7.17 Sense Block Control 4 Register: SNSCTL4 (Address=0x10) [Default=0x80]

Figure 6.7-17 and Table 6.7-17 show Sense Block Control 4 register.

Figure 6.7-17 Sense Block Control 4 Register SNSCTL4

7	6	5	4	3	2	1	0
CMP3_VTH3	CMP3_VTH2	CMP3_VTH1	CMP3_VTH0	CAL_CONN	CAL_DA1	CAL_DA2	CAL_DA3/BEMF
R/W: 1b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b

Table 6.7-17 Sense Block Control 4 Register SNSCTL4 Descriptions

Bit	Field	Туре	Default	Description		
7	CMP3_VTH3	R/W	1b			
6	CMP3_VTH2	R/W	0b	Threshold voltage setting of Comparator 3		
5	CMP3_VTH1	R/W	0b	0000b: Disable, 0001b to 1111b: Threshold voltage= VDD /16 x CMP3_VTH		
4	CMP3_VTH0	R/W	0b			
3	CAL_CONN	R/W	0b	Input selection of differential amplifier during DC offset calibration 0b: The amplifier inputs are connected to GND. 1b: The amplifier inputs are connected to the external shunt.		
2	CAL_DA1	R/W	0b	Write 1b to enable DC offset calibration for differential amplifier 1. This bit is automatically reset to 0 after calibration is done.		
1	CAL_DA2	R/W	0b	Write 1b to enable DC offset calibration for differential amplifier 2. This bit is automatically reset to 0 after calibration is done.		
0	CAL_DA3/BEMF	R/W	0b	Write 1b to this bit to enable DC offset calibration for differential amplifier 3 if BEMF sensing is disabled (BEMF_EN=0b). Write 1b to this bit to enable DC offset calibration for BEMF sensing amplifiers if BEMF sensing is enabled (BEMF_EN=1b). This bit automatically resets to 0 after calibration is done		

6.7.18 Sense Block Control 5 Register: SNSCTL5 (Address=0x11) [Default=0x00]

Figure 6.7-18 and Table 6.7-18 show Sense Block Control 5 register.

Figure 6.7-18 Sense Block Control 5 Register SNSCTL5

7	6	5	4	3	2	1	0
DIS_SADT	RESERVED11_6	CTL6_UNLOCK	RESERVED11_4	RESERVED11_3	MUX2	MUX1	MUX0
R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b	R/W: 0b

Table 6.7-18 Sense Block Control 5 Register SNSCTL5 Descriptions

Bit	Field	Туре	Default	Description		
7	DIS_SADT	R/W	0b	Write 1b to disable the adaptive dead time control function		
6	RESERVED11_6	R/W	0b	Reserved. The write value should be 0b.		
5	CTL6_UNLOCK	R/W	0b	Write 0b to ignore SNSCTL6 register write. Write 1b to unlock to allow SNSCTL6 register write.		
4	RESERVED11_4	R/W	0b	Reserved. The write value should be 0b.		
3	RESERVED11_3	R/W	0b	Reserved. The write value should be 0b.		
2	MUX2	R/W	0b	Output selection of DA3O/MUX1 pin 000b: GND (pulldown: 330kΩ)	In case of BEMF_EN=0b,	
1	MUX1	R/W	0b	010b: TEMP monitor 111b: Differential amplifier 3	100b: Differential amplifier 3 output w/ 10kΩ 111b: Differential amplifier 3 output w/o 10kΩ In case of BEMF EN=1b,	
0	MUX0	R/W	0b	101b: Differential amplifier 1 output 110b: Differential amplifier 2 output	100b: BEMF sense amplifier output w/ 10kΩ 111b: BEMF sense amplifier output w/o 10kΩ	

6.7.19 Sense Block Control 6 Register: SNSCTL6 (Address=0x12) [Default=0x40]

Figure 6.7-19 and Table 6.7-19 show Sense Block Control 6 Register. CTL6_UNLOCK=1b is necessary to allow SNSCTL6 register write. After writing SNSCTL6 register, CTL6_UNLOCK should be set to 0b.

Figure 6.7-19 Sense Block Control 6 Register SNSCTL6

7	6	5	4	3	2	1	0
RESERVED12_7	BEMF_OFFSET	RESERVED12_5	RESERVED12_4	RESERVED12_3	RESERVED12_2	RESERVED12_1	GD_AOR
R/W: 0b	R/W: 1b	R/W: 0b	R/W: 0b				

Table 6.7-19 Sense Block Control 6 Register SNSCTL6 Descriptions

Bit	Field	Туре	Default	Description
7	RESERVED12_7	R/W	0b	Reserved. The write value should be 0b.
6	BEMF_OFFSET	R/W	1b	Data selection of BEMF sense amplifier DC offset 0b: calibration data, 1b: trimming data by shipping test This bit automatically sets to 0 after DC offset calibration for BEMF sense amplifier is done.
5	RESERVED12_5	R/W	0b	Reserved. The write value should be 0b.
4	RESERVED12_4	R/W	0b	Reserved. The write value should be 0b.
3	RESERVED12_3	R/W	0b	Reserved. The write value should be 0b.
2	RESERVED12_2	R/W	0b	Reserved. The write value should be 0b.
1	RESERVED12_1	R/W	0b	Reserved. The write value should be 0b.
0	GD_AOR	R/W	0b	Write 1b to enable the active override mode of the gate driver logic.

7 MCU Description

7.1 Features

The integrated MCU is the RX13T with following features.

• 32-bit RX CPU core

- Max. operating frequency: 32MHz
- Capable of 50 DMIPS in operation at 32MHz
- Accumulator handles 64-bit results (for a single instruction) from 32-bit × 32-bit operations
- Multiplication and division unit handles 32-bit x 32-bit operations (multiplication instructions take one CPU clock cycle)
- Built-in FPU: 32-bit single-precision floating point (compliant to IEEE754)
- Fast interrupt
- CISC Harvard architecture with 5-stage pipeline
- Variable-length instructions, ultra-compact code
- On-chip debugging circuit

· Low power design and architecture

- Operation from 3.135V to 5.25V supply
- Three low power consumption modes

On-chip code flash memory, no wait states

- 128Kbyte capacities
- On-board or off-board user programming
- For instructions and operands

· On-chip data flash memory

- 4 Kbytes (1,000,000 program/erase cycles (typ.))
- BGO (Background operation)

· On-chip SRAM, no wait states

- 12 Kbytes of SRAM

• DMA

- DTC: Five transfer modes

Reset and supply management

- Seven types of reset, including the power-on reset (POR)
- Low voltage detection (LVD) with voltage settings

Clock functions

- External clock input frequency: Up to 2MHz
- PLL circuit input: 4MHz to 8MHz
- Low-speed on-chip oscillator: 4MHz
- High-speed on-chip oscillator: 32MHz ±1%
- IWDT-dedicated on-chip oscillator: 15kHz
- On-chip clock frequency accuracy measurement circuit (CAC)

· Independent watchdog timer

15kHz on-chip oscillator produces a dedicated clock signal to drive IWDT operation.

Useful functions for IEC60730 compliance

 Self-diagnostic and disconnection-detection assistance functions for the A/D converter, clock frequency accuracy measurement circuit, independent watchdog timer, RAM test assistance functions using the DOC, etc.



7.1 Features (continued)

• MPC

- Multiple locations are selectable for I/O pins of peripheral functions

• Up to 2 communication channels

- SCI with following useful functions (2 channels)
- Asynchronous mode, clock synchronous mode, smart card interface mode, simplified SPI, and simplified I2C

• Up to 8 extended-function timers

- 16-bit MTU3 (6 channels): 32MHz operation, input capture, output compare,
 3-phase complementary PWM x 1 channel-output,
 CPU-efficient complementary PWM, phase counting mode (1 channel)
- 16-bit compare match timers (2 channels)

• 12-bit A/D Converter: 7ch

- On-chip simultaneous sample and hold circuit (3ch: AN000 to AN002 + 3ch: AN004 to AN006) for 3 shunt method
- Double data register for 1shunt method
- Programmable Gain Amplifier (AN000 to AN002: x2, 2.5, 3.077, 5, 8, 10 + AN004 to AN006: x5, 10, 20, 40)
- A/D sampling time can be set for each channel of AN000 to AN006.
- AN000 to AN004 can be input from the external pin.
- Group scan priority control mode (3 levels)
- Self-diagnostic function and analog input disconnection detection assistance function (compliant to IEC60730)
- Comparator (3 + 3 channels)
- · Register write protection function can protect values in important registers against overwriting
- Up to 19 pins for general I/O ports
 - open drain, input pullup

For more details, refer to "RX13T Group User's Manual: Hardware (R01UH0822EJ)".



7.2 Resets

The following resets are implemented: RES# pin reset, power-on reset, voltage monitoring 0 reset, voltage monitoring 1 reset, voltage monitoring 2 reset, independent watchdog timer reset, and software reset. Table 7.2-1 lists the reset names and sources. For more details, refer to "RX13T Group User's Manual: Hardware (R01UH0822EJ)".

After MCU is reset, I/O port P70 connected to EN terminal for the smart gate driver internally functions as an input pin immediately. As the EN terminal has an internal pulldown resistance ($100k\Omega$), the smart gate driver also enters Sleep Mode. Refer to section 6.1.3 Mode Transition.

Reset name Source RES# pin reset Voltage input to the RES# pin is driven low Power-on reset VDD_MCU rises (voltage monitored: VPOR) Note1 Voltage monitoring 0 reset VDD_MCU falls (voltage monitored: Vdet0) Note1 Voltage monitoring 1 reset VDD_MCU falls (voltage monitored: Vdet1) Note1 Voltage monitoring 2 reset VDD_MCU falls (voltage monitored: Vdet2) Note1 Independent watchdog timer reset The independent watchdog timer underflows, or a refresh error occurs. Software reset Register setting for RX13T

Table 7.2-1 Reset Names and Sources

Note1: For the voltages to be monitored (VPOR, Vdet0, Vdet1, and Vdet2), see section 8, Voltage Detection Circuit (LVDAb) and section 32, Electrical Characteristics in "RX13T Group User's Manual: Hardware (R01UH0822EJ)".

7.3 Low Power Consumption

RX13T has several functions for reducing power consumption, by setting clock dividers, stopping modules, changing to low power consumption mode in normal operation, and changing to operating power control mode. Table 7.3-1 lists the specifications of low power consumption functions.

After a reset, this MCU returns to normal mode, but modules except the DTC, and RAM are stopped. This device can optimize the power consumption by these functions, the modes of the smart gate driver operation, and the enable control for each block in the smart gate driver. For details, refer to section 6.1 Power-On Sequence and Functional Modes.

Item	Specification
Clock divider functions	The frequency division ratio can be set independently for the system clock (ICLK), peripheral module clock (PCLKB), S12AD clock (PCLKD), and FlashIF clock (FCLK). Note1
Module stop function	Each peripheral module can be stopped independently by the module stop control register.
Function for transition to low power consumption mode	Transition to a low power consumption mode in which the CPU, peripheral modules, or oscillators are stopped is enabled.
Low power consumption modes	Sleep mode Deep sleep mode Software standby mode
Operating power control modes	Power consumption can be reduced in normal operation, sleep mode, and deep sleep mode by selecting an appropriate operating power control mode according to the operating frequency and operating voltage. Two operating power control modes are available High-speed operating mode Middle-speed operating mode

Table 7.3-1 Specifications of Low Power Consumption Functions

Note1: For details, refer to section 9, Clock Generation Circuit in "RX13T Group User's Manual: Hardware (R01UH0822EJ)".

7.4 I/O Ports

The I/O ports function as a general I/O port, an I/O pin of a peripheral module, or an input pin for an interrupt. Some of the pins are also configurable as an I/O pin of a peripheral module or an input pin for an interrupt. All pins function as input pins immediately after a reset, and pin functions are switched by register settings. The setting of each pin is specified by the registers for the corresponding I/O port and on-chip peripheral modules. Table 7.4-1 lists the specifications of I/O ports. The port settings for not only the external I/O pins but also the internal connection ports including unused pins according to Table 7.4-1 are also necessary. For more details, refer to section 5, I/O Registers and section 17, I/O Ports in "RX13T Group User's Manual: Hardware (R01UH0822EJ)".

Table 7.4-1 Specifications of I/O ports

Port symbol	I/O pins	Number of pins	Internal connect ports (Terminals of smart gate driver)	Note
PORT1	P10, P11	2	_	_
PORT2	-		P22 (CMP3O) P23 (CMP2O) P24 (CMP1O)	P22 to P24 port settings depend on the usage. P22 to P24 are available as the interrupt function through the comparator.
PORT3	P36	1	P37 (Unused)	Need to set P37 to output port.
PORT4	P40 to P44	5	P44 (DA3O) P45 (DA2O) P46 (DA1O) P47 (Unused)	P44 is common use with DA3O terminal for the differential amplifier. P45 and P46 are available as the ADC input through the PGA. Need to set P47 to output port.
PORT7	_	_	P70 (EN) P71 to P76 (IN6 to IN1)	P70 to P76 are used as an output port for the smart gate driver control.
PORT9	-	_	P93 (SCLK) P94 (nFAULT)	P93 is used as an output port for smart gate driver control. P94 is used as an input port for smart gate driver control.
PORTA		_	PA2 (nSCS) PA3 (Unused)	PA2 is used as an output port for smart gate driver control. Need to set PA3 to output port.
PORTB	PB0, PB3 to PB7	6	PB1 (SDO) PB2 (SDI)	PB0 is common use with nSMPL terminal for S/H function. PB1 is used as an output port for smart gate driver control. PB2 is used as an input port for smart gate driver control.
PORTD	PD3 to PD6	4	_	_
PORTE	PE2	1	_	_
	Total of pins	19		

7.5 Serial Communication Interface

RX13T has three independent serial communications interface (SCI) channels. The SCI consists of the SCIg module (SCI1 and SCI5) and the SCIh module (SCI12). SCI1 and SCI5 are available for this device. Table 7.5-1 lists the functions of SCI Channels. For more details, refer to section 23, Serial Communications Interface (SCIg, SCIh) in "RX13T Group User's Manual: Hardware (R01UH0822EJ)".

Table 7.5-1 Functions of SCI Channels

ltem	SCI1	SCI5 Note1	SCI12	RIIC	
Asynchronous mode	Available	Available Note2			
Clock synchronous mode	Available	Available Note2		Not available	
Smart card interface mode	Available	Available			
Simple I ² C mode	Available Note3	Available Note3	Not available		
Simple SPI mode	Available	Available Note4			
Extended serial mode	Not Available	Not Available			
MTU clock input	Available	Available			

Note1: SCI5 is common use in the external communication and SPI communication for the smart gate driver.

The SCI initialization according to the operating mode is necessary whenever the communication channel is changed. For details, refer to the section 23.3.6, 23.5.3, 23.7.4, and 23.8.5 in "RX13T Group User's Manual: Hardware (R01UH0822EJ)".

Note2: The hardware flow control by CTS5# and RTS5# pins is NOT available.

Note3: The simple I^2C mode is NOT available as the slave function.

Note4: The SPI multi master function and SPI slave function is NOT available.

When SCI5 is used as the SPI slave mode, it is necessary to use the clock synchronous mode in combination with the interrupt function.

8 External Circuit

The external circuit in the case of 3 shunt sensorless FOC is shown as Figure 8-1. The recommended value of each external component is shown in Table 8-1.




Figure 8-1 External Circuit Example - 3 Shunt Sensorless FOC

8 External Circuit (continued)

Table 8-1 The External Component List

Part No.	Recommended value	Ratings	Purpose	Notes
R1 to R3	Depend on application	Depend on application	Shunt resistance for current sense	
R4	48.7kΩ	-	Bleeder resistance for VDRV output voltage setting	1
R5	3.48kΩ	-	Bleeder resistance for VDRV output voltage setting	1
R6	60.4kΩ	-	Phase compensation resistance for the switching regulator	4
R7	160kΩ	-	Bleeder resistance for VDD output voltage setting	2
R8	91kΩ	-	Bleeder resistance for VDD output voltage setting	2
C1a	3x 4.7µF	100V	Bypass capacitance for VM terminal	5
C1b	0.1µF	100V	Bypass capacitance for VM terminal	5
C1c	4.7µF	100V	Bypass capacitance for VBRIDGE terminal	5
C1d	0.1µF	100V	Bypass capacitance for VBRIDGE terminal	5
C2	2.2µF	25V	Bypass capacitance for VCP terminal	3
C3	0.22µF	100V	Pumping capacitance for charge pump	3
C4	10µF	25V	Output capacitance for the switching regulator, VDRV terminal	4
C5	2200pF	10V	Phase compensation capacitance for the switching regulator	4
C6	DNP	10V	Phase compensation capacitance for the switching regulator	
C7	22µF	10V	Output capacitance for the linear regulator, VCC5V terminal	
C8	22µF	10V	Output capacitance for the linear regulator, VDD terminal	
C9	0.1µF	10V	Bypass capacitance for VDD_MCU2 terminal	
C10	0.1µF	10V	Bypass capacitance for AVDD_MCU terminal	
C11	0.1µF	10V	Bypass capacitance for VDD_MCU1 terminal	
C12	4.7µF	10V	Power supply stabilization for VCL terminal	
M1 to M6	Depend on application	Depend on application	Power MOSFET for the motor drive	
L1	22µH or 33µH	>2A	Coil for the switching regulator	
D1	0.6V	100V, >2A	Schottky rectifier diode for the switching regulator	

Please refer to "RAJ306101 User's Manual: Hardware (R18UZ0081EJ)" for the details to select the parts.

Note1: VDRV output voltage is 12V with these resistors.

Note2: VDD output voltage is 3.310V with these resistors.


Note3: Please consider the effective capacitance. The smaller C3 causes the larger voltage drop of VCP.

The smaller C2 causes the larger voltage ripple of VCP.

Note4: Please select the suitable value of R6 and C5 depending on C4 effective capacitance.

Note5: The suitable capacitance depends on the constraints of the application and characteristic.

9 Package Specification



Symbols	Dimension in Millimeters					
Syllibols	Min.	Тур.	Max.			
Α	=	=	0.80			
A1	0.00	-	0.05			
А3		0.203 REF.				
b	0.20	0.25	0.30			
D	-	8.00	=			
E	=	8.00	=			
е	-	0.50	-			
N		56				
L	0.35	0.40	0.45			
K	0.20	-	=			
D2	5.95	6.05	6.65			
E2	5.95	6.05	6.65			
aaa	0.15					
bbb	0.10					
ccc	0.10					
ddd	0.05					
eee	0.08					
fff	0.10					

10 Revision History

Revision	Date	Description	Object Page
1.00	5-Oct-23	Initial release.	• All

General Precautions in the Handling of Microprocessing Unit and Microcontroller Unit Products

The following usage notes are applicable to all Microprocessing unit and Microcontroller unit products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

1. Precaution against Electrostatic Discharge (ESD)

A strong electrical field, when exposed to a CMOS device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop the generation of static electricity as much as possible, and quickly dissipate it when it occurs. Environmental control must be adequate. When it is dry, a humidifier should be used. This is recommended to avoid using insulators that can easily build up static electricity. Semiconductor devices must be stored and transported in an anti-static container, static shielding bag or conductive material. All test and measurement tools including work benches and floors must be grounded. The operator must also be grounded using a wrist strap. Semiconductor devices must not be touched with bare hands. Similar precautions must be taken for printed circuit boards with mounted semiconductor devices.

2. Processing at power-on

The state of the product is undefined at the time when power is supplied. The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the time when power is supplied. In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the time when power is supplied until the reset process is completed. In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the time when power is supplied until the power reaches the level at which resetting is specified.

3. Input of signal during power-off state

Do not input signals or an I/O pull-up power supply while the device is powered off. The current injection that results from input of such a signal or I/O pull-up power supply may cause malfunction and the abnormal current that passes in the device at this time may cause degradation of internal elements. Follow the guideline for input signal during power-off state as described in your product documentation.

4. Handling of unused pins

Handle unused pins in accordance with the directions given under handling of unused pins in the manual. The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of the LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible.

Clock signals

After applying a reset, only release the reset line after the operating clock signal becomes stable. When switching the clock signal during program execution, wait until the target clock signal is stabilized. When the clock signal is generated with an external resonator or from an external oscillator during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Additionally, when switching to a clock signal produced with an external resonator or by an external oscillator while program execution is in progress, wait until the target clock signal is stable.

- 6. Voltage application waveform at input pin
 - Waveform distortion due to input noise or a reflected wave may cause malfunction. If the input of the CMOS device stays in the area between V_{IL} (Max.) and V_{IH} (Min.) due to noise, for example, the device may malfunction. Take care to prevent chattering noise from entering the device when the input level is fixed, and also in the transition period when the input level passes through the area between V_{IL} (Max.) and V_{IH} (Min.).
- 7. Prohibition of access to reserved addresses

Access to reserved addresses is prohibited. The reserved addresses are provided for possible future expansion of functions. Do not access these addresses as the correct operation of the LSI is not guaranteed.

8. Differences between products

Before changing from one product to another, for example to a product with a different part number, confirm that the change will not lead to problems. The characteristics of a microprocessing unit or microcontroller unit products in the same group but having a different part number might differ in terms of internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

Notice

- 1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
- 2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
- 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
- 5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
- 6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.

- 7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
- 8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
- 12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
- 13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 October 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit: www.renesas.com/contact/.