

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.

“Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.

“High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.

“Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

M62420SP/ FP/ AFP

2ch Electronic Volume with Tone by I²C Bus System

REJ03F0051-0100Z

Rev.1.0

Sep.17.2003

Description

M62420SP/FP/AFP is the tone and volume controller which is controlled by I²C bus. This IC can apply the broad application because of low noise and distortion.

M62420AFP changes the slave address from M62420FP.

Features

- TONE(Bass/Treble) control and 1 dB step volume control are enabled.
- Low noise and low distortion .
 $V_{NO} = 4.5 \mu V_{rms}$, $CTHD=0.1\%$ max
- Controlling by serial data in conformity to the I²C bus format .


Applications

- TV, Mini-Stereo, etc


Recommended Operating Condition

- Supply voltage range: 8.5 to 9.5 V (analog) 4.5 to 5.5 V (digital)
- Rated supply voltage: 9 V (analog) 5 V (digital)

System Block Diagram



Block diagram and Pin Configuration



Pin Description


Pin No.	Pin Name	I/O	Description
1	REF	I	Reference voltage terminal for analog
2	CH1 IN	I	Input terminal (ch1)
3	SIMIN1	I	Pin for capacitor of simulated inductor 1
4	SIMOUT 1	O	Pin for capacitor of simulated inductor 1
5	BASS1	I	Pin for capacitor of ch1-side bass setting
6	TRE1	I	Pin for capacitor of ch1-side treble setting
7	VOL OUT1	O	Output terminal (ch1)
8	DGND	I	Digital GND
9	SDA	I/O	I/O terminal of DATA I ² C bus format
10	SCL	I	Input terminal of CLOCK I ² C bus format
11	RESET	I	RESET terminal of built-in logic circuit
12	DVDD	I	VDD for digital circuit
13	AGND	I	GND for analog circuit
14	VOL OUT2	O	Output terminal (ch2)
15	TRE2	I	Pin for capacitor of ch2-side treble setting
16	BASS2	I	Pin for capacitor of ch2-side bass setting
17	SIMOUT2	O	Pin for capacitor of simulated inductor 2
18	SIMIN 2	I	Pin for capacitor of simulated inductor 2
19	CH2 IN	I	Input terminal (ch2)
20	AVDD	I	VCC for analog circuit

Absolute Maximum Ratings

(Ta = 25°C)

Symbol	Parameter	Condition	Limits	Unit
AVdd	Analog supply voltage		10.0	V
DVdd	Digital supply voltage		7.0	V
Pd	Power dissipation	Ta ≤ 25°C	750	mW
Kθ	Thermal Derating ratio	Ta > 25°C	7.5	mW / °C
Topr	Operating temperature		-20 to +75	°C
Tstg	Storage temperature		-40 to +125	°C

Thermal Derating Curves



Recommended Operating Condition

(Ta = 25°C unless otherwise noted)

Item	Symbol	Condition	MIN	TYP	MAX	Unit
Analog supply voltage	AVDD		8.5	9.0	9.5	V
Digital supply voltage	DVDD		4.5	5.0	5.5	V
H level input voltage (logic circuit)	VIH		0.7DVDD	—	VDD	V
H level input voltage (logic circuit)	VIL		0	—	0.3DVDD	V

Electrical Characteristics (DC)

(Ta = 25°C, AVDD = 9 V, DVDD = 5 V and tone, bassboost = 0 dB unless otherwise noted)

(1) Supply voltage

Item	Symbol	Conditions	Limit			Unit
			Min.	Typ.	Max.	
Analog supply current	Icc	AVdd = 9.0 V Measure terminal = 20 pin No signal input	—	10	20	mA
Digital supply current	Idd	DVdd = 5 V Measure terminal = 12 pin No signal input	—	0	2	μA

(2) I/O CHARACTERISTICS

Item	Symbol	Conditions	Limit			Unit
			Min.	Typ.	Max.	
Maximum input voltage	VIM	2,19 pin input, 7,14 pin output RL = 10 K, THD = 1%, f = 1 kHz ATT = -6dB	2.0	3.2	—	Vrms
Output voltage	Vodc	7 pin, 14 pin, no signal	4.35	4.5	4.65	V
Gain	Gv	Vin = 0dBm, FLAT, f = 1 kHz 2-7PIN 19-14PIN gain	-2	0	2	dB
Output noise voltage	Vono	JIS-A filter, no signal, Rg = 10 KΩ 7,14 pin	—	4.5	30	μVrms
Total harmonic distortion	THD	7 pin, 14 pin f=1kHz Vo = 0.5 Vrms, RL = 10KΩ LPF = 30 kHz	—	0.05	0.1	%
Channel separation	CT	RL = 10 K S:Vin = 1 Vrms, f=1kHz M:Rg = 10 kΩ, JIS-A filter	—	-100	-70	dB

(3) Tone Characteristics

Item	Symbol	Conditions	Limit			Unit
			Min.	Typ.	Max.	
Tone control gain (bass)	Gbassb	f = 100 Hz	9	12	15	dB
	Gbassc		-15	-12	-9	dB
Tone control gain (treble)	Gtrebb	f = 10 Hz	9	12	15	dB
	Gtrebc		-15	-12	-9	dB


(4) Volume Characteristics

Item	Symbol	Conditions	Limit			Unit
			Min.	Typ.	Max.	
Maximum attenuation	ATTmax	f = 1KHz, Vin = 0dBm	-108	-100	-80	dB
Minimum attenuation	ATTmin	2 pin to 7 pin 19 pin to 14pin gain JIS-A filter	-1.5	0	1.5	dB

Function Explanation

(1) Equivariation Circuit of Tone Control

The resonance circuit is able to construct by using built-in amplifier for simulated inductor. (Shows the constant as follow)



Center frequency

$$f_0 = 1 / 2\pi \sqrt{C1 \cdot C2 \cdot R1 \cdot R2} \text{ [Hz]}$$

$$Q = \sqrt{(C2 \cdot R2) / (C1 \cdot R1)}$$

(EX) BASS band (f=100Hz)
 R1=1.8KΩ , R2=136KΩ
 C1=0.47μF , C2=0.022μF

FIG1. The circuit used simulated inductor.


FIG1 is equal to FIG2.
 The following relation is concluded.

$$L = C2 \cdot R1 \cdot R2$$



FIG2. The equivalent circuit used L.

I²C BUS Input Data Format



(1) Slave address

M62420SP / FP

A6	A5	A4	A3	A2	A1	A0	R/W
1	0	0	0	0	0	0	0

M62420AFP

A6	A5	A4	A3	A2	A1	A0	R/W
1	0	0	0	0	0	1	0

(2) sub address

The following sub address is defined at this IC.

subA7	subA6	subA5	subA4	subA3	subA2	subA1	subA0
← empty slot →			MUTE mode	TREBLE level mode	BASS level mode	channel2 volume mode	channel1 volume mode
			1: ON 0: OFF	1: ON 0: OFF	1: ON 0: OFF	1: ON 0: OFF	1: ON 0: OFF

(3) -1: volume control

The volume control is enabled at following condition.

subA0 : $\begin{matrix} 0 \\ 1 \end{matrix}$, $\begin{matrix} 1 \\ 0 \end{matrix}$, $\begin{matrix} 1 \\ 1 \end{matrix}$ (either bit is 1)

subA2 : $\begin{matrix} 0 \\ 0 \end{matrix}$ (both bits are 0)

volume code

ATT	D4	D3	D2	D1	D0
0dB	H	H	H	H	H
2dB	H	H	H	H	L
4dB	H	H	H	L	H
6dB	H	H	H	L	L
8dB	H	H	L	H	H
10dB	H	H	L	H	L
12dB	H	H	L	L	H
14dB	H	H	L	L	L
16dB	H	L	H	H	H
18dB	H	L	H	H	L
20dB	H	L	H	L	H
22dB	H	L	H	L	L
24dB	H	L	L	H	H
26dB	H	L	L	H	L
28dB	H	L	L	L	H
30dB	H	L	L	L	L
32dB	L	H	H	H	H
34dB	L	H	H	H	L
36dB	L	H	H	L	H
38dB	L	H	H	L	L
40dB	L	H	L	H	H
42dB	L	H	L	H	L
46dB	L	H	L	L	H
50dB	L	H	L	L	L
54dB	L	L	H	H	H
58dB	L	L	H	H	L
62dB	L	L	H	L	H
66dB	L	L	H	L	L
70dB	L	L	L	H	H
74dB	L	L	L	H	L
78dB	L	L	L	L	H
∞dB	L	L	L	L	L

ATT	D6	D5
0dB	H	H
1dB	H	L
* 2dB	L	H
* 3dB	L	L

* 2dB,3dB setting is enabled at less than 42dB step.

(3) -2 : tone level control

The tone level controlling is enabled at following condition.

subA0 : 0
 subA1 : 0 (both bits are 0)

subA2 : 0 , 1 , 1
 subA3 : 1 , 0 , 1 (either bit is 1)

tone code

	BASS				TREBLE			
	D7	D6	D5	D4	D3	D2	D1	D0
12dB	L	H	H	L	L	H	H	L
10dB	L	H	L	H	L	H	L	H
8dB	L	H	L	L	L	H	L	L
6dB	L	L	H	H	L	L	H	H
4dB	L	L	H	L	L	L	H	L
2dB	L	L	L	H	L	L	L	H
0dB	L	L	L	L	L	L	L	L
-2dB	H	L	L	H	H	L	L	H
-4dB	H	L	H	L	H	L	H	L
-6dB	H	L	H	H	H	L	H	H
-8dB	H	H	L	L	H	H	L	L
-10dB	H	H	L	H	H	H	L	H
-12dB	H	H	H	L	H	H	H	L

non-used code

HHHH
 LHHH
 HLLL

(3) -3 : Mute mode


The mute mode is enabled at following condition.

subA0 : no definition
 subA1 : no definition

subA2 : no definition
 subA3 : no definition

subA4 : 1

DATA and CLOCK

**start**

This term is defined by SDA(in) falling edge at SCL H .

stop

This term is defined by SDA(in) rising edge at SCL H .

CAUTION

The SDA(IN) level never change at SCK=H
except start and stop .

data transmisson


The SDA(IN) is enabled at SCL rising edge and H .

acknowledge

Transmitter must send H during ninth clock pulse of SCL .


The case of finished receiving , the receiver replies L synchronized to falling edge of eighth pulse . And restart receiving the transmitted data synchronized to falling edge of ninth pulse .

BUS Line Timing Specification




Parameter	Symbol	MIN	MAX	Units
Min. input low voltage	V_{IL}	-0.5	1.5	V
Max. input high voltage	V_{IH}	3.0	5.5	V
SCL clock frequency	f_{SCL}	0	100	kHz
Time the bus must be free before a new transmission can start	t_{BUF}	4.7		μs
Hold time start condition. After this period the first clock pulse is generated	$t_{HD:STA}$	4.0		μs
The LOW period of the clock	t_{LOW}	4.7		μs
The HIGH period of the clock	t_{HIGH}	4.0		μs
Set up time for start condition (Only relevant for a repeated start condition)	$t_{SU:STA}$	4.7		μs
Hold time DATA	$t_{HD:DAT}$	0		μs
Set-up time DATA	$t_{SU:DAT}$	250		ns
Rise time of both SDA and SCL lines	t_{R}		1000	ns
Fall time of both SDA and SCL lines	t_{F}		300	ns
Set-up time for stop condition	$t_{SU:STO}$	4.0		μs


Level Diagram



Logic Circuit



Application Example









Package Dimensions

Plastic 20pin 300mil SOP

(MMP)

20P2N-A

EIAJ Package Code SOP20-P-300-1.27	JEDEC Code —	Weight(g) 0.26	Lead Material Cu Alloy
---------------------------------------	-----------------	-------------------	---------------------------



Recommended Mount Pad



Symbol	Dimension in Millimeters		
	Min	Nom	Max
A	—	—	2.1
A1	0	0.1	0.2
A2	—	1.8	—
b	0.35	0.4	0.5
c	0.18	0.2	0.25
D	12.5	12.6	12.7
E	5.2	5.3	5.4
e	—	1.27	—
HE	7.5	7.8	8.1
L	0.4	0.6	0.8
L1	—	1.25	—
Z	—	0.585	—
Z1	—	—	0.735
x	—	—	0.25
y	—	—	0.1
θ	0°	—	8°
b2	—	0.76	—
e1	—	7.62	—
l2	1.27	—	—

20P4B


(MMP)

Plastic 20pin 300mil SDIP

EIAJ Package Code SDIP20-P-300-1.78	JEDEC Code —	Weight(g) 1.0	Lead Material Alloy 42/Cu Alloy
--	-----------------	------------------	------------------------------------



Symbol	Dimension in Millimeters		
	Min	Nom	Max
A	—	—	4.5
A1	0.51	—	—
A2	—	3.3	—
b	0.38	0.48	0.58
b1	0.9	1.0	1.3
c	0.22	0.27	0.34
D	18.8	19.0	19.2
E	6.15	6.3	6.45
e	—	1.778	—
e1	—	7.62	—
L	3.0	—	—
theta	0°	—	15°



SEATING PLANE

Renesas Technology Corp. Sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.
Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
 2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
 3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors.
Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
 4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
 5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
 6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
 7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
 8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.
-



RENESAS SALES OFFICES

<http://www.renesas.com>

Renesas Technology America, Inc.
450 Holger Way, San Jose, CA 95134-1368, U.S.A
Tel: <1> (408) 382-7500 Fax: <1> (408) 382-7501

Renesas Technology Europe Limited.
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, United Kingdom
Tel: <44> (1628) 585 100, Fax: <44> (1628) 585 900

Renesas Technology Europe GmbH
Dornacher Str. 3, D-85622 Feldkirchen, Germany
Tel: <49> (89) 380 70 0, Fax: <49> (89) 929 30 11

Renesas Technology Hong Kong Ltd.
7/F., North Tower, World Finance Centre, Harbour City, Canton Road, Hong Kong
Tel: <852> 2265-6688, Fax: <852> 2375-6836

Renesas Technology Taiwan Co., Ltd.
FL 10, #99, Fu-Hsing N. Rd., Taipei, Taiwan
Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

Renesas Technology (Shanghai) Co., Ltd.
26/F., Ruijin Building, No.205 Maoming Road (S), Shanghai 200020, China
Tel: <86> (21) 6472-1001, Fax: <86> (21) 6415-2952

Renesas Technology Singapore Pte. Ltd.
1, Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: <65> 6213-0200, Fax: <65> 6278-8001