Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.

Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anticrime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majorityowned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



16

R8C/2G Group

Hardware Manual RENESAS MCU R8C FAMILY / R8C/2x SERIES

All information contained in these materials, including products and product specifications, represents information on the product at the time of publication and is subject to change by Renesas Electronics Corp. without notice. Please review the latest information published by Renesas Electronics Corp. through various means, including the Renesas Electronics Corp. website (http://www.renesas.com).

Renesas Electronics www.renesas.com

Rev.1.00 2008.04

Notes regarding these materials

- This document is provided for reference purposes only so that Renesas customers may select the appropriate Renesas products for their use. Renesas neither makes warranties or representations with respect to the accuracy or completeness of the information contained in this document nor grants any license to any intellectual property rights or any other rights of Renesas or any third party with respect to the information in this document.
- Renesas shall have no liability for damages or infringement of any intellectual property or other rights arising out of the use of any information in this document, including, but not limited to, product data, diagrams, charts, programs, algorithms, and application circuit examples.
 You should not use the products or the technology described in this document for the purpose of military
- 3. You should not use the products or the technology described in this document for the purpose of military applications such as the development of weapons of mass destruction or for the purpose of any other military use. When exporting the products or technology described herein, you should follow the applicable export control laws and regulations, and procedures required by such laws and regulations.
- 4. All information included in this document such as product data, diagrams, charts, programs, algorithms, and application circuit examples, is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas products listed in this document, please confirm the latest product information with a Renesas sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas such as that disclosed through our website. (http://www.renesas.com)
- 5. Renesas has used reasonable care in compiling the information included in this document, but Renesas assumes no liability whatsoever for any damages incurred as a result of errors or omissions in the information included in this document.
- 6. When using or otherwise relying on the information in this document, you should evaluate the information in light of the total system before deciding about the applicability of such information to the intended application. Renesas makes no representations, warranties or guaranties regarding the suitability of its products for any particular application and specifically disclaims any liability arising out of the application and use of the information in this document or Renesas products.
- 7. With the exception of products specified by Renesas as suitable for automobile applications, Renesas products are not designed, manufactured or tested for applications or otherwise in systems the failure or malfunction of which may cause a direct threat to human life or create a risk of human injury or which require especially high quality and reliability such as safety systems, or equipment or systems for transportation and traffic, healthcare, combustion control, aerospace and aeronautics, nuclear power, or undersea communication transmission. If you are considering the use of our products for such purposes, please contact a Renesas sales office beforehand. Renesas shall have no liability for damages arising out of the uses set forth above.
- 8. Notwithstanding the preceding paragraph, you should not use Renesas products for the purposes listed below: (1) artificial life support devices or systems
 - (2) surgical implantations
 - (3) healthcare intervention (e.g., excision, administration of medication, etc.)
 - (4) any other purposes that pose a direct threat to human life

Renesas shall have no liability for damages arising out of the uses set forth in the above and purchasers who elect to use Renesas products in any of the foregoing applications shall indemnify and hold harmless Renesas Technology Corp., its affiliated companies and their officers, directors, and employees against any and all damages arising out of such applications.

- 9. You should use the products described herein within the range specified by Renesas, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas shall have no liability for malfunctions or damages arising out of the use of Renesas products beyond such specified ranges.
- 10. Although Renesas endeavors to improve the quality and reliability of its products, IC products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Please be sure to implement safety measures to guard against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other applicable measures. Among others, since the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 11. In case Renesas products listed in this document are detached from the products to which the Renesas products are attached or affixed, the risk of accident such as swallowing by infants and small children is very high. You should implement safety measures so that Renesas products may not be easily detached from your products. Renesas shall have no liability for damages arising out of such detachment.
- 12. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written approval from Renesas.
- 13. Please contact a Renesas sales office if you have any questions regarding the information contained in this document, Renesas semiconductor products, or if you have any other inquiries.

General Precautions in the Handling of MPU/MCU Products

The following usage notes are applicable to all MPU/MCU products from Renesas. For detailed usage notes on the products covered by this manual, refer to the relevant sections of the manual. If the descriptions under General Precautions in the Handling of MPU/MCU Products and in the body of the manual differ from each other, the description in the body of the manual takes precedence.

1. Handling of Unused Pins

Handle unused pins in accord with the directions given under Handling of Unused Pins in the manual.

- The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible. Unused pins should be handled as described under Handling of Unused Pins in the manual.
- 2. Processing at Power-on

The state of the product is undefined at the moment when power is supplied.

- The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the moment when power is supplied.
 - In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the moment when power is supplied until the reset process is completed.

In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the moment when power is supplied until the power reaches the level at which resetting has been specified.

3. Prohibition of Access to Reserved Addresses

Access to reserved addresses is prohibited.

- The reserved addresses are provided for the possible future expansion of functions. Do
 not access these addresses; the correct operation of LSI is not guaranteed if they are
 accessed.
- 4. Clock Signals

After applying a reset, only release the reset line after the operating clock signal has become stable. When switching the clock signal during program execution, wait until the target clock signal has stabilized.

- When the clock signal is generated with an external resonator (or from an external oscillator) during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Moreover, when switching to a clock signal produced with an external resonator (or by an external oscillator) while program execution is in progress, wait until the target clock signal is stable.
- 5. Differences between Products

Before changing from one product to another, i.e. to one with a different part number, confirm that the change will not lead to problems.

— The characteristics of MPU/MCU in the same group but having different part numbers may differ because of the differences in internal memory capacity and layout pattern. When changing to products of different part numbers, implement a system-evaluation test for each of the products.

How to Use This Manual

1. Purpose and Target Readers

This manual is designed to provide the user with an understanding of the hardware functions and electrical characteristics of the MCU. It is intended for users designing application systems incorporating the MCU. A basic knowledge of electric circuits, logical circuits, and MCUs is necessary in order to use this manual. The manual comprises an overview of the product; descriptions of the CPU, system control functions, peripheral functions, and electrical characteristics; and usage notes.

Particular attention should be paid to the precautionary notes when using the manual. These notes occur within the body of the text, at the end of each section, and in the Usage Notes section.

The revision history summarizes the locations of revisions and additions. It does not list all revisions. Refer to the text of the manual for details.

The following documents apply to the R8C/2G Group. Make sure to refer to the latest versions of these documents. The newest versions of the documents listed may be obtained from the Renesas Technology Web site.

Document Type	Description	Document Title	Document No.
Datasheet	Hardware overview and electrical characteristics	R8C/2G Group	REJ03B0223
		Datasheet	
Hardware manual	Hardware specifications (pin assignments,	R8C/2G Group	This hardware
	memory maps, peripheral function	Hardware Manual	manual
	specifications, electrical characteristics, timing		
	charts) and operation description		
	Note: Refer to the application notes for details on		
	using peripheral functions.		
Software manual	Description of CPU instruction set	R8C/Tiny Series	REJ09B0001
		Software Manual	
Application note	Information on using peripheral functions and	Available from Renesas	
	application examples	Technology Web sit	e.
	Sample programs		
	Information on writing programs in assembly		
	language and C		
Renesas	Product specifications, updates on documents,		
technical update	etc.		

2. Notation of Numbers and Symbols

The notation conventions for register names, bit names, numbers, and symbols used in this manual are described below.

(1)	Register Names, Bit Names, and Pin Names Registers, bits, and pins are referred to in the text by symbols. The symbol is accompanied by the word "register," "bit," or "pin" to distinguish the three categories. Examples the PM03 bit in the PM0 register P3_5 pin, VCC pin	
(2)	Notation of Numbers The indication "b" is appended to numeric values given in binary format. However, nothing is appended to the values of single bits. The indication "h" is appended to numeric values given in hexadecimal format. Nothing is appended to numeric values given in decimal format. Examples Binary: 11b	

Hexadecimal: EFA0h Decimal: 1234

3. Register Notation

The symbols and terms used in register diagrams are described below.

	F	Symbol XXX	Address XXX	After Reset 00h	
	Bit Symbol	Bit Name		Function	RW
	XXX0	XXX bits	b1 b0 1 0: XXX 0 1: XXX		RW
	XXX1		1 0: Do not set. 1 1: XXX		RW
	(b2)	Nothing is assigned. When read, the conte	If necessary, set to ent is undefined.	0.	_
	(b3)	Reserved bits	Set to 0.		RW
 	XXX4	XXX bits	Function varies a mode.	ccording to the operating	RW
	XXX5				wo
	XXX6				RW
	XXX7	XXX bit	0: XXX 1: XXX		RO

*1

Blank: Set to 0 or 1 according to the application.0: Set to 0.1: Set to 1.

X: Nothing is assigned.

*2

RW: Read and write. RO: Read only. WO: Write only. -: Nothing is assigned.

*3

• Reserved bit

Reserved bit. Set to specified value.

*4

• Nothing is assigned

Nothing is assigned to the bit. As the bit may be used for future functions, if necessary, set to 0.

• Do not set to a value

Operation is not guaranteed when a value is set.

• Function varies according to the operating mode.

The function of the bit varies with the peripheral function mode. Refer to the register diagram for information on the individual modes.

4. List of Abbreviations and Acronyms

Abbreviation	Full Form	
ACIA	Asynchronous Communication Interface Adapter	
bps	bits per second	
CRC	Cyclic Redundancy Check	
DMA	Direct Memory Access	
DMAC	Direct Memory Access Controller	
GSM	Global System for Mobile Communications	
Hi-Z	High Impedance	
IEBus	Inter Equipment Bus	
I/O	Input / Output	
IrDA	Infrared Data Association	
LSB	Least Significant Bit	
MSB	Most Significant Bit	
NC	Non-Connect	
PLL	Phase Locked Loop	
PWM	Pulse Width Modulation	
SIM	Subscriber Identity Module	
UART	Universal Asynchronous Receiver / Transmitter	
VCO	Voltage Controlled Oscillator	

All trademarks and registered trademarks are the property of their respective owners.

Table of Contents

SFR F	ge Reference E	3 - 1
1.	Dverview	1
1.1	Features	
1.1		
1.1		
1.2	Product List	
1.3	Block Diagram	
1.4	Pin Assignment	
1.5	Pin Functions	
2.	Central Processing Unit (CPU)	8
2.1	Data Registers (R0, R1, R2, and R3)	9
2.2	Address Registers (A0 and A1)	
2.3	Frame Base Register (FB)	
2.4	Interrupt Table Register (INTB)	
2.5	Program Counter (PC)	
2.6	User Stack Pointer (USP) and Interrupt Stack Pointer (ISP)	
2.7	Static Base Register (SB)	9
2.8	Flag Register (FLG)	9
2.8	Carry Flag (C)	9
2.8	2 Debug Flag (D)	9
2.8	3 Zero Flag (Z)	9
2.8	4 Sign Flag (S)	9
2.8	5 Register Bank Select Flag (B)	9
2.8	5 Overflow Flag (O)	9
2.8	7 Interrupt Enable Flag (I)	. 10
2.8	Stack Pointer Select Flag (U)	. 10
2.8	Processor Interrupt Priority Level (IPL)	. 10
2.8	10 Reserved Bit	. 10
3.	lemory	. 11
4.	pecial Function Registers (SFRs)	. 12
5.	esets	. 24
5.1	Hardware Reset	. 27
5.1	When Power Supply is Stable	. 27
5.	2 Power On	. 27
5.2	Power-On Reset Function	. 29
5.3	Voltage Monitor 0 Reset	. 30
5.4	Voltage Monitor 1 Reset	. 30
5.5	Voltage Monitor 2 Reset	. 30
5.6	Watchdog Timer Reset	. 31
5.7	Software Reset	. 31
6.	oltage Detection Circuit	32
6.1	VCC Input Voltage	. 40
6.1	Monitoring Vdet0	. 40

6.1.2	Monitoring Vdet1	40
6.1.3	Monitoring Vdet2	40
6.2	Voltage Monitor 0 Reset	41
6.3	Voltage Monitor 1 Interrupt and Voltage Monitor 1 Reset	
6.4	Voltage Monitor 2 Interrupt and Voltage Monitor 2 Reset	44
7. Coi	nparator	46
7.1	Overview	
7.1	Register Description	
7.2	Monitoring Comparison Results	
7.3.1	Monitoring Comparison Results	
7.3.2	Monitoring Comparator 2	
7.4	Functional Description	
7.4.1	Comparator 1	
7.4.2	Comparator 2	
7.5	Comparator 1 and Comparator 2 Interrupts	
7.5.1	Non-Maskable Interrupts	
7.5.2	Maskable Interrupts	
7.6	Adjusting Internal Reference Voltage (Vref)	
8. I/O	Ports	65
8.1	Functions of I/O Ports	65
8.2	Effect on Peripheral Functions	66
8.3	Pins Other than Programmable I/O Ports	66
8.4	Port Setting	75
8.5	Unassigned Pin Handling	83
8.6	Notes on I/O Ports	84
8.6.1	Port P4_3, P4_4	84
0 Dre		05
	cessor Mode	
9.1	Processor Modes	85
10. Bus	5	96
10. Du	·	00
11. Clo	ck Generation Circuit	87
11.1	On-Chip Oscillator Clocks	96
11.1.1	Low-Speed On-Chip Oscillator Clock	
11.1.2	High-Speed On-Chip Oscillator Clock	96
11.2	XCIN Clock	
11.3	CPU Clock and Peripheral Function Clock	98
11.3.1	System Clock	
11.3.2	CPU Clock	
11.3.3	Peripheral Function Clock (f1, f2, f4, f8, and f32)	98
11.3.4	fOCO	
11.3.5	fOCO-F	
11.3.6	fOCO-S	
11.3.7	fC4 and fC32	98
11.4	Power Control	99
11.4.1	Standard Operating Mode	99

11.4.2	Wait Mode	101
11.4.3	Stop Mode	
11.5	Notes on Clock Generation Circuit	
11.5.1	Stop Mode	106
11.5.2	Wait Mode	106
11.5.3	Oscillation Circuit Constants	106
12. Pro	tection	107
13. Inte	rrupts	108
13.1	Interrupt Overview	
13.1.1	Types of Interrupts	
13.1.2	Software Interrupts	
13.1.3	Special Interrupts	
13.1.4	Peripheral Function Interrupt	110
13.1.5	Interrupts and Interrupt Vectors	111
13.1.6	Interrupt Control	
13.2	INT Interrupt	
13.2.1	$\overline{\text{INTi}}$ Interrupt (i = 0, 1, 2, 4)	
13.2.2	$\overline{\text{INTi}}$ Input Filter (i = 0, 1, 2, 4)	
13.3	Key Input Interrupt	
13.4	Address Match Interrupt	
13.5	Notes on Interrupts	
13.5.1	Reading Address 00000h	
13.5.2	SP Setting	
13.5.3	External Interrupt and Key Input Interrupt	
13.5.4	Changing Interrupt Sources	
13.5.5	Changing Interrupt Control Register Contents	131
14. ID (Code Areas	132
14.1	Overview	
14.2	Functions	
14.3	Notes on ID Code Areas	
14.3.1	Setting Example of ID Code Areas	133
15. Opt	ion Function Select Area	134
15.1	Overview	
15.2	OFS Register	
15.3	Notes on Option Function Select Area	
15.3.1	Setting Example of Option Function Select Area	136
16. Wat	tchdog Timer	137
16.1	Count Source Protection Mode Disabled	
16.2	Count Source Protection Mode Enabled	
17. Tim	ers	143
17.1	Timer RA	
17.1.1	Timer Mode	
17.1.2	Pulse Output Mode	

17.1.3	Event Counter Mode	152
17.1.4	Pulse Width Measurement Mode	154
17.1.5	Pulse Period Measurement Mode	157
17.1.6	Notes on Timer RA	160
17.2	Timer RB	161
17.2.1	Timer Mode	165
17.2.2	Programmable Waveform Generation Mode	168
17.2.3	Programmable One-shot Generation Mode	171
17.2.4	Programmable Wait One-Shot Generation Mode	175
17.2.5	Notes on Timer RB	178
17.3	Timer RE	182
17.3.1	Real-Time Clock Mode	183
17.3.2	Output Compare Mode	191
17.3.3	Notes on Timer RE	197
17.4	Timer RF	200
17.4.1	Input Capture Mode	205
17.4.2	Output Compare Mode	208
17.4.3	Notes on Timer RF	212
18. Ser	ial Interface	213
18.1	Clock Synchronous Serial I/O Mode	218
18.1.1	Polarity Select Function	221
18.1.2	LSB First/MSB First Select Function	
18.1.3	Continuous Receive Mode	222
18.2	Clock Asynchronous Serial I/O (UART) Mode	223
18.2.1	Bit Rate	227
18.3	Notes on Serial Interface	228
19. Hai	dware LIN	229
19.1	Features	229
19.2	Input/Output Pins	230
19.3	Register Configuration	231
19.4	Functional Description	233
19.4.1	Master Mode	
19.4.2	Slave Mode	236
19.4.3	Bus Collision Detection Function	240
19.4.4	Hardware LIN End Processing	
19.5	Interrupt Requests	
19.6	Notes on Hardware LIN	243
00 EI	ah Mamani	044
		244
20.1	Overview	
20.2	Memory Map	
20.3	Functions to Prevent Rewriting of Flash Memory	
20.3.1	ID Code Check Function	
20.3.2	ROM Code Protect Function	
20.4	CPU Rewrite Mode	
20.4.1	Register Description	
20.4.2	Status Check Procedure	254

20.4.3	EW0 Mode	
20.4.4	EW1 Mode	
20.5	Standard Serial I/O Mode	
20.5.1	ID Code Check Function	
20.6	Parallel I/O Mode	
20.6.1	ROM Code Protect Function	
20.7	Notes on Flash Memory	
20.7.1	CPU Rewrite Mode	
21. Red	ucing Power Consumption	
	Overview	
	Key Points and Processing Methods for Reducing Power Consumption	
21.2	Voltage Detection Circuit	
21.2.1	Ports	
21.2.2	Clocks	
21.2.3	Selecting Oscillation Drive Capacity	
21.2.4	Wait Mode, Stop Mode	
21.2.5	Stopping Peripheral Function Clocks	
21.2.0	Timers	
21.2.7	Reducing Internal Power Consumption	
21.2.8	Stopping Flash Memory	
21.2.9		
21.2.10	Low-Current-Consumption Read Mode	
22. Elec	trical Characteristics	275
23. Usa	ge Notes	292
23.1	Notes on I/O Ports	
23.1.1	Port P4_3, P4_4	
23.2	Notes on Clock Generation Circuit	
23.2.1	Stop Mode	
23.2.2	Wait Mode	
23.2.3	Oscillation Circuit Constants	
23.3	Notes on Interrupts	
23.3.1	Reading Address 00000h	
23.3.2	SP Setting	
23.3.3	External Interrupt and Key Input Interrupt	
23.3.4	Changing Interrupt Sources	
23.3.5	Changing Interrupt Control Register Contents	
23.4	Notes on ID Code Areas	
23.4.1	Setting Example of ID Code Areas	
23.5	Notes on Option Function Select Area	
23.5.1	Setting Example of Option Function Select Area	
	Notes on Timers	
23.6.1	Notes on Timer RA	
23.6.2	Notes on Timer RB	
23.6.3	Notes on Timer RE	
23.6.4	Notes on Timer RF	
	Notes on Serial Interface	
	Notes on Hardware LIN	

23.9 Notes on Flas	sh Memory	310
23.9.1 CPU Rew	rite Mode	310
	ise	
	a Bypass Capacitor between VCC and VSS Pins as a Countermeasure against Noise a	
23.10.2 Counterme	easures against Noise Error of Port Control Registers	312
24. Notes for On-Cl	hip Debugger	313
Appendix 1. Package	Dimensions	314
Appendix 2. Connection	on Examples with On-Chip Debugging Emulator	315
Appendix 3. Example	of Oscillation Evaluation Circuit	316

SFR Page Reference

Address	Pegister	Symbol	Page
0000h	Register	Symbol	Page
00001h			
0001h			
0002h			
	Drassager Made Degister 0	PM0	85
0004h	Processor Mode Register 0	-	
0005h	Processor Mode Register 1	PM1	85
0006h	System Clock Control Register 0	CM0	89
0007h	System Clock Control Register 1	CM1	90
0008h			
0009h			
000Ah	Protect Register	PRCR	107
000Bh			
000Ch	System Clock Select Register	OCD	91
000Dh	Watchdog Timer Reset Register	WDTR	139
000Eh	Watchdog Timer Start Register	WDTS	139
000Fh	Watchdog Timer Control Register	WDC	139
0010h	Address Match Interrupt Register 0	RMAD0	128
0011h			
0012h			
0013h	Address Match Interrupt Enable Register	AIER	128
0014h	Address Match Interrupt Register 1	RMAD1	128
0015h			-
0016h			
0017h			
0018h			
0019h			
001911 001Ah			
001An			
001Bh	Osunt Osuna Desta dian Mada Daviatan	0000	140
	Count Source Protection Mode Register	CSPR	140
001Dh			
001Eh			
001Fh			
0020h	High-Speed On-Chip Oscillator Control Register 0	HRA0	92
0021h	High-Speed On-Chip Oscillator Control Register 1	HRA1	92
0022h	High-Speed On-Chip Oscillator Control Register 2	HRA2	92
0023h			
0024h			
0025h			
0026h			
0027h			
0028h	Clock Prescaler Reset Flag	CPSRF	93
0029h	High-Speed On-Chip Oscillator Control Register 4	FRA4	93
002Ah			
002Bh	High-Speed On-Chip Oscillator Control Register 6	FRA6	93
002Ch	5 - Frite - Frite	-	
002Dh		-	
002Eh	BGR Trimming Auxiliary Register A	BGRTRMA	48
002Eh	BGR Trimming Auxiliary Register B	BGRTRMB	48
0030h		- 0	10
0030h	Voltage Detection Register 1	VCA1	35, 49
0031h	-	VCA1 VCA2	35, 49
	Voltage Detection Register 2	VUNZ	55, 48, 94
0033h			
0034h			
0035h		100440	07
0036h	Voltage Monitor 1 Circuit Control Register	VW1C	37, 50
0037h	Voltage Monitor 2 Circuit Control Register	VW2C	38, 51
0038h	Voltage Monitor 0 Circuit Control Register	VW0C	36
0039h			
003Ah			
	Voltage Detection Circuit External Input Control	VCAB	52
003Bh		1	1
	Register		
003Ch	Comparator Mode Register	ALCMR	52
003Ch 003Dh	Comparator Mode Register Voltage Monitor Circuit Edge Select Register	VCAC	39, 53
003Ch	Comparator Mode Register		

Address	Register	Symbol	Page
0040h			
0041h	Comparator 1 Interrupt Control Register	VCMP1IC	113
0042h	Comparator 2 Interrupt Control Register	VCMP2IC	113
0043h			
0044h			
0045h			
0046h			
0047h 0048h			
0040h			
0043h	Timer RE Interrupt Control Register	TREIC	113
004Bh	UART2 Transmit Interrupt Control Register	S2TIC	113
004Ch	UART2 Receive Interrupt Control Register	S2RIC	113
004Dh	Key Input Interrupt Control Register	KUPIC	113
004Eh			
004Fh			
0050h	Compare 1 Interrupt Control Register	CMP1IC	113
0051h	UART0 Transmit Interrupt Control Register	SOTIC	113
0052h	UART0 Receive Interrupt Control Register	SORIC	113
0053h			
0054h			
0055h	INT2 Interrupt Control Register	INT2IC	114
0056h	Timer RA Interrupt Control Register	TRAIC	113
0057h	i contra co	70010	
0058h	Timer RB Interrupt Control Register	TRBIC	113
0059h	INT1 Interrupt Control Register	INT1IC	114
005Ah	Timer DE Interrunt Control Degister	TREIC	110
005Bh 005Ch	Timer RF Interrupt Control Register Compare 0 Interrupt Control Register	TRFIC CMP0IC	113 113
005Dh	INT0 Interrupt Control Register	INTOIC	113
005Eh	INT4 Interrupt Control Register	INT4IC	114
005Eh	Capture Interrupt Control Register	CAPIC	114
0060h	Capture interrupt Control Register	OAHO	115
0061h			
0062h			
0063h			
0064h			
0065h			
0066h			
0067h			
0068h			
0069h			
006Ah			
006Bh			
006Ch			
006Dh			
006Eh 006Fh			+
006Fh 0070h			
0070h			
0071h			+
0072h			
0073h			-
0075h			1
0076h			
0077h			1
0078h			1
0079h			1
007Ah			
007Bh			İ
007Ch			
007Dh			
007Eh			
007Fh			

		•	·		1		
Address	Register	Symbol	Page	Address	Register	Symbol	Page
0080h				00C0h			
0081h				00C1h			
0082h				00C2h			
0083h				00C3h			
0084h				00C4h			
0085h				00C5h			
0086h				00C6h			
0087h				00C7h			
0088h				00C8h			
0089h				00C9h			
008Ah				00CAh			
008Bh				00CBh			
008Ch				00CCh			
008Dh				00CDh			
008Eh				00CEh			
008Fh				00CFh			
0090h				00D0h			
0091h		1		00D1h			1
0092h		<u> </u>		00D2h			
0093h			+	00D3h			
0094h	1		+	00D4h	1		
0095h		1		00D5h			
0096h		1	+	00D6h			
0090h		<u> </u>		00D0h			
009711 0098h		<u> </u>	+	00D7h 00D8h			
0090h				00D9h			
0099h				00D9h			
009An 009Bh				00DAn 00DBh			
009Bh				00DBh 00DCh			
009Ch				00DDh			
				00DDh 00DEh			
009Eh							
009Fh				00DFh			
00A0h	UART0 Transmit/Receive Mode Register	U0MR	215	00E0h	Port P0 Register	P0	72
00A1h	UARTO Bit Rate Register	U0BRG	215	00E1h	Port P1 Register	P1	72
	UART0 Transmit Buffer Register	U0TB	216	00E2h	Port P0 Direction Register	PD0	71
00A3h				00E3h	Port P1 Direction Register	PD1	71
00A4h	UART0 Transmit/Receive Control Register 0	U0C0	216	00E4h			
00A5h	UART0 Transmit/Receive Control Register 1	U0C1	217	00E5h	Port P3 Register	P3	72
00A6h	UART0 Receive Buffer Register	U0RB	217	00E6h			
00A7h				00E7h	Port P3 Direction Register	PD3	71
00A8h				00E8h	Port P4 Register	P4	72
00A9h				00E9h	I		
00AAh							
00ABh				00EAh	Port P4 Direction Register	PD4	71
00ACh				00EAh 00EBh	-		
00ADh				00EAh 00EBh 00ECh	Port P4 Direction Register Port P6 Register	PD4 P6	71
				00EAh 00EBh	-		
00AEh				00EAh 00EBh 00ECh 00EDh 00EEh	-		
00AEh 00AFh				00EAh 00EBh 00ECh 00EDh	Port P6 Register	P6	72
				00EAh 00EBh 00ECh 00EDh 00EEh	Port P6 Register	P6	72
00AFh				00EAh 00EBh 00ECh 00EDh 00EEh 00EFh	Port P6 Register	P6	72
00AFh 00B0h				00EAh 00EBh 00ECh 00EDh 00EEh 00EFh 00F0h	Port P6 Register	P6	72
00AFh 00B0h 00B1h				00EAh 00EBh 00ECh 00EDh 00EEh 00EFh 00F0h	Port P6 Register	P6	72
00AFh 00B0h 00B1h 00B2h				00EAh 00EBh 00ECh 00EDh 00EEh 00EFh 00F0h 00F1h 00F2h	Port P6 Register	P6	72
00AFh 00B0h 00B1h 00B2h 00B3h 00B4h				00EAh 00EBh 00ECh 00EDh 00EEh 00FFh 00F0h 00F1h 00F2h 00F3h	Port P6 Register	P6	72
00AFh 00B0h 00B1h 00B2h 00B3h 00B4h 00B5h				00EAh 00EBh 00ECh 00EDh 00EFh 00FFh 00F1h 00F2h 00F3h 00F3h	Port P6 Register Port P6 Direction Register	P6 PD6 PD6	72
00AFh 00B0h 00B1h 00B2h 00B3h 00B4h 00B5h 00B6h				00EAh 00EBh 00ECh 00EDh 00EEh 00FGh 00F0h 00F1h 00F3h 00F3h 00F3h 00F5h	Port P6 Register Port P6 Direction Register Port P6 Direction Register Pin Select Register 2	P6 PD6 PD6 PD6 PD7 PINSR2	72 71 71 73
00AFh 00B0h 00B1h 00B2h 00B3h 00B4h 00B5h 00B6h 00B6h				00EAh 00EBh 00ECh 00EDh 00EEh 00FCh 00F0h 00F1h 00F2h 00F3h 00F4h 00F5h 00F6h	Port P6 Register Port P6 Direction Register Port P6 Direction Register Pin Select Register 2 Pin Select Register 3	P6 PD6 PD6 PD6 PINSR2 PINSR2 PINSR3	72 71 71 73 73
00AFh 00B0h 00B1h 00B2h 00B3h 00B4h 00B5h 00B6h 00B6h 00B7h				00EAh 00EBh 00ECh 00EDh 00EEh 00FCh 00F1h 00F1h 00F2h 00F3h 00F4h 00F5h 00F6h 00F7h	Port P6 Register Port P6 Direction Register Port P6 Direction Register Pin Select Register 2 Pin Select Register 3 Port Mode Register	P6 PD6 PD6 PD6 PINSR2 PINSR2 PINSR3 PMR	72 71 71 73 73 73 74
00AFh 00B0h 00B1h 00B2h 00B3h 00B4h 00B5h 00B6h 00B7h 00B8h 00B9h				00EAh 00EBh 00ECh 00ECh 00EFh 00F0h 00F0h 00F0h 00F3h 00F3h 00F3h 00F5h 00F5h 00F7h 00F7h	Port P6 Register Port P6 Direction Register Port P6 Direction Register Pin Select Register 2 Pin Select Register 3 Port Mode Register External Input Enable Register	P6 PD6 PD6 PD6 PINSR2 PINSR2 PINSR3 PMR INTEN	72 71 73 73 73 74 121
00AFh 00B0h 00B1h 00B2h 00B3h 00B4h 00B5h 00B6h 00B7h 00B8h 00B9h				00EAh 00EBh 00ECh 00ECh 00EFh 00FFh 00F7h 00F7h 00F3h 00F4h 00F5h 00F6h 00F6h 00F7h 00F8h 00F9h	Port P6 Register Port P6 Direction Register Port P6 Direction Register Pin Select Register 2 Pin Select Register 3 Port Mode Register External Input Enable Register INT Input Filter Select Register	P6 PD6 PD6 PD6 PINSR2 PINSR2 PINSR3 PMR INTEN INTF	72 71 73 73 74 121 122
00AFh 00B0h 00B1h 00B2h 00B3h 00B4h 00B6h 00B6h 00B7h 00B8h 00B9h				00EAh 00EBh 00ECh 00ECh 00EFh 00FFh 00F7h 00F3h 00F3h 00F3h 00F6h 00F6h 00F6h 00F6h 00F7h 00F8h 00F9h 00F9h	Port P6 Register Port P6 Direction Register Port P6 Direction Register Pin Select Register 2 Pin Select Register 3 Port Mode Register External Input Enable Register INT Input Filter Select Register Key Input Enable Register	P6 PD6 PD6 PD6 PINSR2 PINSR3 PINSR3 PMR INTEN INTEN INTF KIEN	72 71 73 73 73 74 121 122 126
00AFh 00B0h 00B1h 00B2h 00B3h 00B4h 00B5h 00B6h 00B6h 00B8h 00B8h 00B8h 00B8h				00EAh 00EBh 00ECh 00ECh 00EFh 00FGh 00F1h 00F2h 00F3h 00F3h 00F4h 00F5h 00F6h 00F6h 00F7h 00F8h 00F9h 00FAh 00FBh	Port P6 Register Port P6 Direction Register Port P6 Direction Register Pin Select Register 2 Pin Select Register 3 Port Mode Register External Input Enable Register INT Input Filter Select Register Key Input Enable Register Pull-Up Control Register 0	P6 PD6 PD6 PD6 PINSR2 PINSR3 PINSR3 PMR INTEN INTEN INTF KIEN PUR0	72 71 73 73 73 74 121 122 126 74
00AFh 00B0h 00B1h 00B2h 00B3h 00B4h 00B5h 00B6h 00B7h 00B8h 00B8h 00BAh 00BBh 00BCh				00EAh 00EBh 00ECh 00EDh 00EFh 00FGh 00F1h 00F2h 00F3h 00F3h 00F3h 00F6h 00F6h 00F6h 00F8h 00F8h 00FAh 00FBh 00FCh	Port P6 Register Port P6 Direction Register Port P6 Direction Register Pin Select Register 2 Pin Select Register 3 Port Mode Register External Input Enable Register INT Input Filter Select Register Key Input Enable Register	P6 PD6 PD6 PD6 PINSR2 PINSR3 PINSR3 PMR INTEN INTEN INTF KIEN	72 71 73 73 73 74 121 122 126
00AFh 00B0h 00B1h 00B2h 00B3h 00B4h 00B5h 00B6h 00B6h 00B8h 00B8h 00B8h 00B8h				00EAh 00EBh 00ECh 00ECh 00EFh 00FGh 00F1h 00F2h 00F3h 00F3h 00F4h 00F5h 00F6h 00F6h 00F7h 00F8h 00F9h 00FAh 00FBh	Port P6 Register Port P6 Direction Register Port P6 Direction Register Pin Select Register 2 Pin Select Register 3 Port Mode Register External Input Enable Register INT Input Filter Select Register Key Input Enable Register Pull-Up Control Register 0	P6 PD6 PD6 PD6 PINSR2 PINSR3 PINSR3 PMR INTEN INTEN INTF KIEN PUR0	72 71 73 73 73 74 121 122 126 74

Address	Register	Symbol	Page
0100h	Timer RA Control Register	TRACR	146
0100h	Timer RA I/O Control Register	TRAIOC	146, 148, 151,
	-		153, 155, 158
0102h	Timer RA Mode Register	TRAMR	147
0103h	Timer RA Prescaler Register	TRAPRE	147
0104h	Timer RA Register	TRA	147
0105h			
0106h	LIN Control Register	LINCR	231
0107h	LIN Status Register	LINST	232
0108h	Timer RB Control Register	TRBCR	162
0109h	Timer RB One-Shot Control Register	TRBOCR	162
010Ah	Timer RB I/O Control Register	TRBIOC	163, 165, 169, 172, 176
010Bh	Timer RB Mode Register	TRBMR	163
010Ch	Timer RB Prescaler Register	TRBPRE	164
010Dh	Timer RB Secondary Register	TRBSC	164
010Eh	Timer RB Primary Register	TRBPR	164
010Fh			
0110h			
0111h			
0112h			
0113h			
0114h			
0115h			
0116h			
0117h			
0118h	Timer RE Second Data Register / Counter Data Register	TRESEC	185, 193
0119h	Timer RE Minute Data Register / Compare Data Register	TREMIN	185, 193
011Ah	Timer RE Hour Data Register	TREHR	186
011Bh	Timer RE Day of Week Data Register	TREWK	186
011Ch	Timer RE Control Register 1	TRECR1	187, 194
011Dh	Timer RE Control Register 2	TRECR2	188, 194
011Eh	Timer RE Count Source Select Register	TRECSR	189, 195
011Fh	Timer RE Real-Time Clock Precision Adjust Register	TREOPR	189
0120h			
0121h			
0122h			
0123h			
0123h 0124h			
0124h			
0124h 0125h			
0124h 0125h 0126h			
0124h 0125h 0126h 0127h			
0124h 0125h 0126h 0127h 0128h			
0124h 0125h 0126h 0127h 0128h 0129h			
0124h 0125h 0126h 0127h 0128h 0129h 012Ah			
0124h 0125h 0126h 0127h 0128h 0129h 012Ah 012Bh			
0124h 0125h 0126h 0127h 0128h 0129h 012Ah 012Bh 012Ch			

Address	Register	Symbol	Page
0130h			
0131h			
0132h			
0133h			
0134h			
0135h			
0136h			
0137h			
0138h			
0139h			
013Ah			
013Bh			
013Ch			
013Dh			
013Eh			
013Fh			
0140h			
0141h			
0142h			
0143h			
0144h			
0145h			
0146h			
0147h			
0148h			
0149h			
014Ah			
014Bh			
014Ch			
014Dh			
014Eh			
014Fh			
0150h			
0151h			
0152h			
0153h			
0154h			
0155h			
0156h			
0157h			
0158h		<u> </u>	
0159h			
015Ah			
015Ah			
015Ch			
015Dh			
015Eh			
015En			

NOTE:

Address	Register	Symbol	Page
0160h	UART2 Transmit/Receive Mode Register	U2MR	215
0161h	UART2 Bit Rate Register	U2BRG	215
0162h	UART2 Transmit Buffer Register	U2TB	216
0163h			
0164h	UART2 Transmit/Receive Control Register 0	U2C0	216
0165h	UART2 Transmit/Receive Control Register 1	U2C1	217
0166h	UART2 Receive Buffer Register	U2RB	217
0167h			
0168h			
0169h			
016Ah			
016Bh			
016Ch			
016Dh			
016Eh			
016Fh			
0170h			
0171h			
0172h			
0173h			
0174h			
0175h			
0176h			
0177h			
0178h			
0179h			
017Ah			
017Bh			
017Ch			
017Dh			
017Eh			
017Fh			
0180h			
0181h			
0182h			
0183h			
0184h			
0185h			
0186h			
0187h			
0188h			
0189h			
018Ah			
018Bh			
018Ch			
018Dh			
018Eh			
018Fh			
0190h			
0191h			
0192h			
0193h			
0194h			
0195h		1	
0196h			
0197h		1	
0198h		1	
0199h			
019Ah			1
019Bh			
019Ch		1	
019Dh		1	
019Eh			
		+	

Address	Register	Symbol	Page
01A0h		-	-
01A1h			
01A2h			
01A3h			
01A4h			
01A5h			
01A6h			
01A7h			
01A8h			
01A9h			
01AAh			
01ABh			
01ACh			
01ADh			
01AEh			
01AFh			
01B0h			
01B1h			
01B2h			
01B3h	Flash Memory Control Register 4	FMR4	253
01B4h			
01B5h	Flash Memory Control Register 1	FMR1	252
01B6h			
01B7h	Flash Memory Control Register 0	FMR0	249
01B8h			
01B9h			
01BAh			
01BBh			
01BCh			
01BDh			
01BEh			
01C0h			
01C1h			
01C2h			
01C3h			
01C4h 01C5h			
01C5h			
01C0h			
01C/h			
01C9h			
01CAh			
01CBh			
01CCh			
01CDh			
01CEh			
01CFh			
01D0h			
01D1h			
01D2h			-
01D3h			
01D4h			
01D5h			
01D6h			
01D7h			
01D8h			
01D9h			
01DAh			
01DBh			
01DCh			
01DDh			
01DEh			
01DFh			

Addiss	Desister	Cum-tI	Derr	A	Desister	Currels al	Derr
Address	Register	Symbol	Page	Address	Register	Symbol	Page
01E0h				0220h		L	1
01E1h				0221h			
01E2h				0222h		T	
01E3h				0223h			
01E4h				0224h			
01E5h				0225h		1	
01E6h				0226h			
01E7h				0227h		ł	ł
01E8h				0228h			l
01E9h				0229h			
01EAh				022Ah			
01EBh				022Bh			
01ECh				022Ch			
01EDh				022Dh			
01EEh				022Eh		1	
01EFh				022Fh		1	
01F0h				0230h		ł	
01F1h				0231h		ł	ł
						<u> </u>	
01F2h				0232h		ł	1
01F3h				0233h		 	l
01F4h				0234h		L	
01F5h				0235h			
01F6h				0236h			
01F7h				0237h			
01F8h				0238h		1	
01F9h				0239h			
01FAh				023Ah		1	
01FBh				023Bh		1	
01FCh				023Ch			
01FDh				023Dh			
01FEh				023Eh			
01FFh				023Fh			
0200h				0240h			
0201h				0241h			
0202h				0242h			
0203h				0243h			
0204h				0244h		1	
0205h				0245h			
0206h				0246h		ł	ł
0207h				0247h			l
0208h				0248h			
0209h				0249h			
020Ah				024Ah			
020Bh				024Bh			
020Ch				024Ch			
020Dh				024Dh		1	
020Eh				024Eh		<u> </u>	ł
020Eh				024Eh			
0201 h				0241 h		ł	
						ł	1
0211h				0251h		 	1
0212h				0252h		 	
0213h				0253h			
0214h				0254h			I
0215h				0255h			
0216h				0256h		1	
0217h				0257h		t	
0218h			<u> </u>	0258h		<u> </u>	1
0210h				0259h		ł	
						ł	1
021Ah				025Ah		 	
021Bh				025Bh		ļ	1
021Ch				025Ch			l
021Dh				025Dh			
021Eh				025Eh		1	
021Fh				025Fh		t	
· · · · · ·	1		1			ı	ı

Address	Register	Symbol	Page	Address	Perinter	Symbol	Page
0260h	Register	Symbol	гауе	02A0h	Register	Symbol	Faye
0200h				02A011			ł
0262h				02A1h			·
0263h				02A3h			·
0263h				02A3h 02A4h			<u>.</u>
							<u>.</u>
0265h				02A5h			
0266h				02A6h			
0267h				02A7h			ł
0268h				02A8h			ł
0269h				02A9h			
026Ah				02AAh			
026Bh				02ABh			
026Ch				02ACh			
026Dh				02ADh			
026Eh				02AEh			
026Fh				02AFh			
0270h				02B0h			
0271h			ļ	02B1h			
0272h		ļ		02B2h			
0273h		ļ		02B3h			
0274h		ļ		02B4h			
0275h				02B5h			
0276h				02B6h			ļ
0277h				02B7h			
0278h				02B8h			
0279h				02B9h			
027Ah				02BAh			
027Bh				02BBh			
027Ch				02BCh			
027Dh				02BDh			
027Eh				02BEh			
027Fh				02BFh			
0280h				02C0h			
0281h				02C1h			
0282h				02C2h			
0283h				02C3h			
0284h				02C4h			
0285h				02C5h			
0286h				02C6h			
0287h				02C7h			
0288h				02C8h			
0289h				02C9h			
028Ah				02CAh			t
028Bh		1		02CBh			ł
028Ch		1		02CCh			1
028Dh		1		02CDh			1
028Eh				02CEh			<u> </u>
028Fh				02CFh			<u> </u>
0290h	Timer RF Register	TRF	202	02D0h			<u> </u>
0291h	1			02D1h			<u> </u>
0292h				02D2h			
0293h				02D3h			
0294h				02D3h			
0294h 0295h	1	ł		02D4n			ł
0295h				02D5h			
02901 0297h				02D011			<u> </u>
0297h 0298h				02D7h 02D8h			
0298h	Timer RF Control Register 2	TRFCR2	203	02D8n 02D9h			<u> </u>
0299h 029Ah	Timer RF Control Register 2	TRFCR2	203	02D9h 02DAh			
029Ah 029Bh	Timer RF Control Register 0	TRFCR0	203	02DAh 02DBh			l
029Ch	Capture and Compare 0 Register	TRFM0	202	02DCh			
029Dh	Compare 1 Desister		000	02DDh			
029Eh	Compare 1 Register	TRFM1	202	02DEh			
029Fh				02DFh			<u> </u>

Address	Register	Symbol	Page
02E0h			
02E1h			
02E2h			
02E3h			
02E4h			
02E5h			
02E6h			
02E7h			
02E8h			
02E9h			
02EAh			
02EBh			
02ECh			
02EDh			
02EEh			
02EFh			
02F0h			
02F1h			
02F2h			
02F3h			
02F4h			
02F5h			
02F6h			
02F7h			
02F8h			
02F9h			
02FAh			
02FBh	Pin Select Register 4	PINSR4	39, 54, 73
02FCh			
02FDh	External Input Enable Register 2	INTEN2	122
02FEh	INT Input Filter Select Register 2	INTF2	123
02FFh	Timer RF Output Control Register	TRFOUT	204
FFFFh	Option Function Select Register	OFS	26, 135, 140, 247

NOTE: 1. The blank regions are reserved. Do not access locations in these regions.

R8C/2G Group RENESAS MCU

1. Overview

1.1 Features

The R8C/2G Group of single-chip MCUs incorporates the R8C/Tiny Series CPU core, employing sophisticated instructions for a high level of efficiency. With 1 Mbyte of address space, and it is capable of executing instructions at high speed. In addition, the CPU core boasts a multiplier for high-speed operation processing. Power consumption is low, and the supported operating modes allow additional power control. These MCUs also use an anti-noise configuration to reduce emissions of electromagnetic noise and are designed to withstand EMI. Integration of many peripheral functions, including multifunction timer and serial interface, reduces the number of system components.

1.1.1 Applications

Electric power meters, electronic household appliances, office equipment, audio equipment, consumer equipment, etc.

1.1.2 Specifications

Table 1.1 outlines the Specifications for R8C/2G Group.

Item	Function	Specification
CPU	Central processing	R8C/Tiny series core
-	unit	Number of fundamental instructions: 89
		Minimum instruction execution time:
		125 ns (System clock = 8 MHz, VCC = 2.7 to 5.5 V)
		250 ns (System clock = 4 MHz, VCC = 2.2 to 5.5 V)
		• Multiplier: 16 bits \times 16 bits \rightarrow 32 bits
		• Multiply-accumulate instruction: 16 bits × 16 bits + 32 bits \rightarrow 32 bits
		Operation mode: Single-chip mode (address space: 1 Mbyte)
Memory	ROM, RAM	Refer to Table 1.2 Product List for R8C/2G Group.
Power Supply	Voltage detection	Power-on reset
Voltage	circuit	Voltage detection 3
Detection		
Comparator		• 2 circuits (shared with voltage monitor 1 and voltage monitor 2)
		External reference voltage input is available
I/O Ports		Output-only: 1
		CMOS I/O ports: 27, selectable pull-up resistor
Clock	Clock generation	2 circuits: On-chip oscillator (high-speed, low-speed)
	circuits	(high-speed on-chip oscillator has a frequency adjustment function),
		XCIN clock oscillation circuit (32 kHz)
		• Frequency divider circuit: Dividing selectable 1, 2, 4, 8, and 16
		Low power consumption modes:
		Standard operating mode (low-speed clock, high-speed on-chip oscillator,
		low-speed on-chip oscillator), wait mode, stop mode
		Real-time clock (timer RE)
Interrupts		External: 5 sources, Internal: 17 sources, Software: 4 sources
Martin Law The		Priority levels: 7 levels
Watchdog Time		15 bits × 1 (with prescaler), reset start selectable
Timer	Timer RA	8 bits × 1 (with 8-bit prescaler)
		Timer mode (period timer), pulse output mode (output level inverted every
		period), event counter mode, pulse width measurement mode, pulse period
	Timer RB	measurement mode
		8 bits × 1 (with 8-bit prescaler) Timer mode (period timer), programmable waveform generation mode (PWM
		output), programmable one-shot generation mode, programmable wait one-
		shot generation mode
	Timer RE	8 bits × 1
		Real-time clock mode (count seconds, minutes, hours, days of week), output
		compare mode
	Timer RF	16 bits × 1 (with capture/compare register pin and compare register pin)
		Input capture mode, output compare mode
Serial	UART0, UART2	Clock synchronous serial I/O/UART × 2
Interface		
LIN Module		Hardware LIN: 1 (timer RA, UART0)
Flash Memory		 Programming and erasure voltage: VCC = 2.7 to 5.5 V
, ,		Programming and erasure endurance: 100 times
		Program security: ROM code protect, ID code check
		Debug functions: On-chip debug, on-board flash rewrite function
Operating Free	quency/Supply	System clock = 8 MHz (VCC = 2.7 to 5.5 V)
Voltage	• •	System clock = 4 MHz (VCC = 2.2 to 5.5 V)
Current consur	mption	5 mA (VCC = 5 V, system clock = 8 MHz)
		23 μ A (VCC = 3 V, wait mode (low-speed on-chip oscillator on))
		0.7 μ A (VCC = 3 V, stop mode, BGR trimming circuit disabled)
Operating Amb	pient Temperature	-20 to 85°C (N version)
	•	-40 to 85°C (D version) ⁽¹⁾
Package		32-pin LQFP
5-		Package code: PLQP0032GB-A (previous code: 32P6U-A)

Specifications for R8C/2G Group Table 1.1

NOTE: 1. Specify the D version if D version functions are to be used.

Table 1.2

Current of Apr. 2008

1.2 Product List

Product List for R8C/2G Group

Table 1.2 lists Product List for R8C/2G Group, Figure 1.1 shows a Part Number, Memory Size, and Package of R8C/2G Group.

Part No.	ROM Capacity	RAM Capacity	Package Type	Remarks
R5F212G4SNFP	16 Kbytes	512 bytes	PLQP0032GB-A	N version
R5F212G5SNFP	24 Kbytes	1 Kbytes	PLQP0032GB-A	
R5F212G6SNFP	32 Kbytes	1 Kbytes	PLQP0032GB-A	
R5F212G4SDFP	16 Kbytes	512 bytes	PLQP0032GB-A	D version
R5F212G5SDFP	24 Kbytes	1 Kbytes	PLQP0032GB-A	
R5F212G6SDFP	32 Kbytes	1 Kbytes	PLQP0032GB-A	



Figure 1.1 Part Number, Memory Size, and Package of R8C/2G Group

1.3 Block Diagram

Figure 1.2 shows a Block Diagram.



Figure 1.2 Block Diagram

1.4 Pin Assignment

Figure 1.3 shows Pin Assignment (Top View). Table 1.3 outlines the Pin Name Information by Pin Number.



Pin	Control Pin	Port	I/O Pin Functions for of Peripheral Modules						
Number		FUIL	Interrupt	Timer	Serial Interface	Comparator			
1		P3_5		TRFO12					
2		P3_7		(TRAO)/(TRFO11) ⁽¹⁾					
3	RESET								
4	XCOUT	(P4_4)							
5	VSS								
6	XCIN	(P4_3)							
7	VCC								
8	MODE								
9		P4_5	INT0						
10		P1_7	INT1	TRAIO					
11		P3_6	(INT1) ⁽¹⁾						
12		P3_1		TRBO					
13		P3_0		TRAO					
14		P3_2	INT2						
15		P1_6			CLK0	VCOUT2			
16		P1_5	(INT1) ⁽¹⁾	(TRAIO) ⁽¹⁾	RXD0				
17		P1_4			TXD0				
18		P1_3	KI3	(TRBO) ⁽¹⁾		VCOUT1			
19		P1_2	KI2	TRFO02		CVREF			
20		P6_5		(TREO) ⁽¹⁾	CLK2				
21		P1_1	KI1	TRFO01		VCMP2			
22		P1_0	KI0	TRFO00		VCMP1			
23		P3_3		TRFO10/TRFI					
24		P3_4		TRFO11					
25		P0_7	(KI0) ⁽¹⁾						
26		P0_6	INT4						
27		P0_5							
28		P0_4		(TREO) ⁽¹⁾					
29		P6_3			TXD2				
30		P6_0		TREO					
31		P6_6	(KI1) ⁽¹⁾						
32		P6_4	-		RXD2				
				1					

Table 1.3 Pin Name Information by Pin Number

NOTE:

1. Can be assigned to the pin in parentheses by a program.

1.5 **Pin Functions**

Table 1.4 lists Pin Functions.

Table 1.4 **Pin Functions**

Туре	Symbol	I/O Type	Description
Power supply input	VCC, VSS	_	Apply 2.2 V to 5.5 V to the VCC pin. Apply 0 V to the VSS pin.
Reset input	RESET	I	Input "L" on this pin resets the MCU.
MODE	MODE	I	Connect this pin to VCC via a resistor.
XCIN clock input	XCIN	Ι	These pins are provided for XCIN clock generation circuit I/O. Connect a crystal oscillator between the XCIN and XCOUT
XCIN clock output	XCOUT	0	pins. ⁽¹⁾ To use an external clock, input it to the XCIN pin and leave the XCOUT pin open.
INT interrupt input	INTO to INT2, INT4	I	INT interrupt input pins
Key input interrupt	KIO to KI3	I	Key input interrupt input pins
Timer RA	TRAIO	I/O	Timer RA I/O pin
	TRAO	0	Timer RA output pin
Timer RB	TRBO	0	Timer RB output pin
Timer RE	TREO	0	Divided clock output pin
Timer RF	TRFI	I	Timer RF input pin
	TRFO00 to TRFO02, TRFO10 to TRFO12	0	Timer RF output pins
Serial interface	CLK0, CLK2	I/O	Clock I/O pin
	RXD0, RXD2	I	Serial data input pin
	TXD0, TXD2	0	Serial data output pin
Comparator	VCMP1, VCMP2	I	Analog input pins to comparator
	CVREF	I	Reference voltage input pin to comparator
	VCOUT1, VCOUT2	0	Comparator output pins
I/O port	P0_4 to P0_7, P1_0 to P1_7, P3_0 to P3_7, P4_3, P4_5, P6_0, P6_3 to P6_6	I/O	CMOS I/O ports. Each port has an I/O select direction register, allowing each pin in the port to be directed for input or output individually. Any port set to input can be set to use a pull-up resistor or not by a program.
Output port	P4_4	0	Output-only port

I: Input I/O: Input and output O: Output

NOTE:

1. Refer to the oscillator manufacturer for oscillation characteristics.

2. Central Processing Unit (CPU)

Figure 2.1 shows the CPU Registers. The CPU contains 13 registers. R0, R1, R2, R3, A0, A1, and FB configure a register bank. There are two sets of register bank.



2.1 Data Registers (R0, R1, R2, and R3)

R0 is a 16-bit register for transfer, arithmetic, and logic operations. The same applies to R1 to R3. R0 can be split into high-order bits (R0H) and low-order bits (R0L) to be used separately as 8-bit data registers. R1H and R1L are analogous to R0H and R0L. R2 can be combined with R0 and used as a 32-bit data register (R2R0). R3R1 is analogous to R2R0.

2.2 Address Registers (A0 and A1)

A0 is a 16-bit register for address register indirect addressing and address register relative addressing. It is also used for transfer, arithmetic, and logic operations. A1 is analogous to A0. A1 can be combined with A0 to be used as a 32-bit address register (A1A0).

2.3 Frame Base Register (FB)

FB is a 16-bit register for FB relative addressing.

2.4 Interrupt Table Register (INTB)

INTB is a 20-bit register that indicates the start address of an interrupt vector table.

2.5 Program Counter (PC)

PC is 20 bits wide and indicates the address of the next instruction to be executed.

2.6 User Stack Pointer (USP) and Interrupt Stack Pointer (ISP)

The stack pointers (SP), USP, and ISP, are each 16 bits wide. The U flag of FLG is used to switch between USP and ISP.

2.7 Static Base Register (SB)

SB is a 16-bit register for SB relative addressing.

2.8 Flag Register (FLG)

FLG is an 11-bit register indicating the CPU state.

2.8.1 Carry Flag (C)

The C flag retains carry, borrow, or shift-out bits that have been generated by the arithmetic and logic unit.

2.8.2 Debug Flag (D)

The D flag is for debugging only. Set it to 0.

2.8.3 Zero Flag (Z)

The Z flag is set to 1 when an arithmetic operation results in 0; otherwise to 0.

2.8.4 Sign Flag (S)

The S flag is set to 1 when an arithmetic operation results in a negative value; otherwise to 0.

2.8.5 Register Bank Select Flag (B)

Register bank 0 is selected when the B flag is 0. Register bank 1 is selected when this flag is set to 1.

2.8.6 Overflow Flag (O)

The O flag is set to 1 when an operation results in an overflow; otherwise to 0.

2.8.7 Interrupt Enable Flag (I)

The I flag enables maskable interrupts.

Interrupt are disabled when the I flag is set to 0, and are enabled when the I flag is set to 1. The I flag is set to 0 when an interrupt request is acknowledged.

2.8.8 Stack Pointer Select Flag (U)

ISP is selected when the U flag is set to 0; USP is selected when the U flag is set to 1. The U flag is set to 0 when a hardware interrupt request is acknowledged or the INT instruction of software interrupt numbers 0 to 31 is executed.

2.8.9 Processor Interrupt Priority Level (IPL)

IPL is 3 bits wide and assigns processor interrupt priority levels from level 0 to level 7. If a requested interrupt has higher priority than IPL, the interrupt is enabled.

2.8.10 Reserved Bit

If necessary, set to 0. When read, the content is undefined.

3. Memory

3. Memory

Figure 3.1 is a Memory Map of R8C/2G Group. The R8C/2G group has 1 Mbyte of address space from addresses 00000h to FFFFFh.

The internal ROM is allocated lower addresses, beginning with address 0FFFFh. For example, a 16-Kbyte internal ROM area is allocated addresses 0C000h to 0FFFFh.

The fixed interrupt vector table is allocated addresses 0FFDCh to 0FFFFh. They store the starting address of each interrupt routine.

The internal RAM is allocated higher addresses beginning with address 00400h. For example, a 1-Kbyte internal RAM area is allocated addresses 00400h to 007FFh. The internal RAM is used not only for storing data but also for calling subroutines and as stacks when interrupt requests are acknowledged.

Special function registers (SFRs) are allocated addresses 00000h to 002FFh. The peripheral function control registers are allocated here. All addresses within the SFR, which have nothing allocated are reserved for future use and cannot be accessed by users.



Special Function Registers (SFRs) 4.

An SFR (special function register) is a control register for a peripheral function. Tables 4.1 to 4.12 list the special function registers.

Address	Register	Symbol	After reset
0000h			
0001h			
0002h			
0003h			
0004h	Processor Mode Register 0	PM0	00h
0005h	Processor Mode Register 1	PM1	00h
0006h	System Clock Control Register 0	CM0	01011000b
0007h	System Clock Control Register 1	CM1	00h
0008h			
0009h			
000Ah	Protect Register	PRCR	00h
000Bh			
000Ch	System Clock Select Register	OCD	00000100b
000Dh	Watchdog Timer Reset Register	WDTR	XXh
000Eh	Watchdog Timer Start Register	WDTS	XXh
000Eh	Watchdog Timer Control Register	WDC	00X11111b
0010h	Address Match Interrupt Register 0	RMAD0	00h
0011h			00h
0012h	4		00h
0013h	Address Match Interrupt Enable Register	AIER	00h
0014h	Address Match Interrupt Register 1	RMAD1	00h
0015h			00h
0016h			00h
0010h			0011
0018h			
0019h			
0013h			
001An			
001Ch	Count Source Protection Mode Register	CSPR	00h
001011		00110	1000000b(2)
001Dh			100000000(2)
001Dh 001Eh			
001Fh			0.01
0020h	High-Speed On-Chip Oscillator Control Register 0	HRA0 HRA1	00h Withon Obiensing
0021h	High-Speed On-Chip Oscillator Control Register 1		When Shipping
0022h	High-Speed On-Chip Oscillator Control Register 2	HRA2	00h
0023h			
0024h			
0025h			
0026h			
0027h	Clash Presseler Depet Flag	ODODE	0.0h
0028h	Clock Prescaler Reset Flag	CPSRF	00h
0029h	High-Speed On-Chip Oscillator Control Register 4	FRA4	When Shipping
002Ah		5540	
002Bh	High-Speed On-Chip Oscillator Control Register 6	FRA6	When Shipping
002Ch			
002Dh			
002Eh	BGR Trimming Auxiliary Register A	BGRTRMA	When Shipping
002Fh	BGR Trimming Auxiliary Register B	BGRTRMB	When Shipping

Table 4.1 SFR Information (1)⁽¹⁾

X: Undefined
NOTES:

The blank regions are reserved. Do not access locations in these regions.
The CSPROINI bit in the OFS register is set to 0.

Address	Register	Symbol	After reset
0030h			
0031h	Voltage Detection Register 1 ⁽²⁾	VCA1	00001000b
0032h	Voltage Detection Register 2 ⁽²⁾	VCA2	00h ⁽³⁾
			0010000b ⁽⁴⁾
0033h			
0034h			
0035h			
0036h	Voltage Monitor 1 Circuit Control Register ⁽⁵⁾	VW1C	00001010b
0037h	Voltage Monitor 2 Circuit Control Register ⁽⁵⁾	VW2C	00000010b
0038h	Voltage Monitor 0 Circuit Control Register ⁽²⁾	VW0C	1000X010b ⁽³⁾
			1100X011b ⁽⁴⁾
0039h			
003Ah			
003Bh	Voltage Detection Circuit External Input Control Register	VCAB	00h
003Ch	Comparator Mode Register	ALCMR	00h
003Dh	Voltage Monitor Circuit Edge Select Register	VCAC	00h
003Eh	BGR Control Register	BGRCR	00h
003Fh	BGR Trimming Register	BGRTRM	When Shipping
0040h			
0041h	Comparator 1 Interrupt Control Register	VCMP1IC	XXXXX000b
0042h	Comparator 2 Interrupt Control Register	VCMP2IC	XXXXX000b
0043h			
0044h			
0045h			
0046h			
0047h			
0048h			
0049h			
004Ah	Timer RE Interrupt Control Register	TREIC	XXXXX000b
004Bh	UART2 Transmit Interrupt Control Register	S2TIC	XXXXX000b
004Ch	UART2 Receive Interrupt Control Register	S2RIC	XXXXX000b
004Dh	Key Input Interrupt Control Register	KUPIC	XXXXX000b
004Eh			
004Fh			
0050h	Compare 1 Interrupt Control Register	CMP1IC	XXXXX000b
0051h	UART0 Transmit Interrupt Control Register	SOTIC	XXXXX000b
0052h	UART0 Receive Interrupt Control Register	SORIC	XXXXX000b
0053h			
0054h		INTOIO	N/VOOVOO01
0055h	INT2 Interrupt Control Register	INT2IC	XX00X000b
0056h	Timer RA Interrupt Control Register	TRAIC	XXXXX000b
0057h	Times DD Internet Control Deviator	TODIO	XXXXXXX000h
0058h 0059h	Timer RB Interrupt Control Register	TRBIC INT1IC	XXXXX000b XX00X000b
	INT1 Interrupt Control Register	INTTIC	4000×000×
005Ah 005Bh	Timer RF Interrupt Control Register	TRFIC	XXXXX000b
005BN	Compare 0 Interrupt Control Register	CMPOIC	XXXXX000b
005Dh	INTO Interrupt Control Register	INTOIC	XX00X000b
005Eh	INT4 Interrupt Control Register	INT6IC	XX00X000b
005Eh	Capture Interrupt Control Register	CAPIC	XXXXX000b
0060h			
0061h			
0062h			
0063h			
0064h			
0065h			
0066h			
0067h			
0068h			
0069h			
006Ah			
006Bh			
000011			
006Ch			
006Ch			

Table 4.2 SFR Information (2)⁽¹⁾

X: Undefined NOTES:

1.

The blank regions are reserved. Do not access locations in these regions. Software reset, watchdog timer reset, voltage monitor 1 reset, or voltage monitor 2 reset do not affect this register. The LVD0ON bit in the OFS register is set to 1 and hardware reset. Power-on reset, voltage monitor 0 reset, or the LVD0ON bit in the OFS register is set to 0 and hardware reset. Software reset, watchdog timer reset, voltage monitor 1 reset, or voltage monitor 2 reset do not affect b2 and b3. 2. 3. 4. 5.

Address	Register	Symbol	After reset
0070h			
0071h			
0072h			
0073h			
0074h			
0075h			
0076h			
0077h			
0078h			
0079h			
007Ah			
007Bh			
007Ch			
007Dh			
007Eh			
007Fh			
0080h			
0081h			
0082h		1	
0083h		1	
0084h		1	1
0085h		1	1
0086h			
0087h			
0088h			
0089h			
008Ah			
008Bh			
008Ch			
008Dh			
008Eh			
008Fh			
0090h			
0090h			
0091h			
0092h			
0093h 0094h			
0094h			
0095h			
0090h			
0097h 0098h			
0099h			
009Ah			
009Bh			
009Ch			
009Dh			
009Eh			
009Fh			0.01
00A0h	UARTO Transmit/Receive Mode Register	U0MR	00h
00A1h	UARTO Bit Rate Register	U0BRG	XXh
00A2h	UART0 Transmit Buffer Register	U0TB	XXh
00A3h			XXh
00A4h	UARTO Transmit/Receive Control Register 0	U0C0	00001000b
00A5h	UARTO Transmit/Receive Control Register 1	U0C1	00000010b
00A6h	UART0 Receive Buffer Register	U0RB	XXh
00A7h			XXh
00A8h			
00A9h			
00AAh			
00ABh			
00ACh			
00ADh			
00AEh			
00AFh			

Table 4.3	SFR Information (3) ⁽¹⁾	
-----------	------------------------------------	--
Address Register Symbol After res 0085h	ot	
---	----	
0061h		
0062n		
0068/h		
0084h		
0086h		
0086h		
0087h		
0088h		
0089h		
008Ah		
0008h		
008Ch		
008Bh		
008Eh		
008Fh		
0000h		
0002h		
00C2h		
00C3h		
00C4h		
00CSh		
00C6h		
00C7h		
00C8h		
00C9h 00C8h 00C8h 00C6h 00C7h 00C8h 00C7h 00C7h 0000h		
00CAh		
00CBh		
00CCh		
00CDh		
00CEh		
00CFh 00D0h 00D1h 00D3h 00D3h 00D3h 00D5h 00D6h 00D6h 00D7h 00D8h 00D8h 00D8h 00D8h 00DCh 00DCh 00DFh 00DFh 00DFh 00DFh 00DFh 00DFh 00DFh 00DFh 00DFh 00E1h Port P0 Register P0		
00D0h		
00D1h		
00D2h		
00D3h		
00D3h		
00D5h		
00D5h		
00D6h		
00D7h		
00D8h		
00D9h		
00DAh		
00DBh		
00DCh		
00DDh		
00DEh 00DFh 00E0h Port P0 Register P0 00h 00E1h Port P1 Register P1 00h 00E2h Port P0 Direction Register PD0 00h 00E3h Port P1 Direction Register PD1 00h 00E4h 00E5h Port P3 Register P3 00h 00E6h 00E7h Port P3 Direction Register PD3 00h 00E8h Port P4 Register P4 00h		
00DFh Pot P0 Register P0 00h 00E0h Port P0 Register P1 00h 00E1h Port P1 Register P1 00h 00E2h Port P0 Direction Register PD0 00h 00E3h Port P1 Direction Register PD1 00h 00E4h 00E5h Port P3 Register P3 00h 00E6h 00E7h Port P3 Direction Register PD3 00h 00E8h Port P4 Register P4 00h 00E9h		
O0E0h Port P0 Register P0 00h 00E1h Port P1 Register P1 00h 00E2h Port P0 Direction Register PD0 00h 00E3h Port P1 Direction Register PD1 00h 00E4h 00E5h Port P3 Register P3 00h 00E6h 00E7h Port P3 Direction Register PD3 00h 00E8h Port P4 Register P4 00h		
00E1h Port P1 Register P1 00h 00E2h Port P0 Direction Register PD0 00h 00E3h Port P1 Direction Register PD1 00h 00E4h 00E5h Port P3 Register P3 00h 00E6h 00E7h Port P3 Direction Register PD3 00h 00E8h Port P4 Register P4 00h		
00E2h Port P0 Direction Register PD0 00h 00E3h Port P1 Direction Register PD1 00h 00E4h 00E5h Port P3 Register P3 00h 00E6h 00E7h Port P3 Direction Register PD3 00h 00E8h Port P4 Register P4 00h 00E9h		
00E3h Port P1 Direction Register PD1 00h 00E4h		
00E4h Pott P3 Register P3 00h 00E6h P3 00h 00E 00E7h Port P3 Direction Register PD3 00h 00E8h Port P4 Register P4 00h 00E9h 00E 00E 00E		
O0E5h Port P3 Register P3 O0h O0E6h		
00E6h PD3 00h 00E7h Port P3 Direction Register PD3 00h 00E8h Port P4 Register P4 00h 00E9h		
00E7h Port P3 Direction Register PD3 00h 00E8h Port P4 Register P4 00h 00E9h		
00E8h Port P4 Register P4 00h 00E9h		
00E9h		
00EAh Port P4 Direction Register		
I UVEAN I POR PA DIRECTION REGISTER I PD4 I OOh		
00EBh		
00ECh Port P6 Register P6 00h		
00EDh		
00EEh Port P6 Direction Register PD6 00h		
00EFh		

SFR Information (4)⁽¹⁾ Table 4.4

Address	Register	Symbol	After reset
00F0h		Cymbol	
00F1h			
00F2h			
00F3h			
00F4h			
00F5h			
00F6h	Pin Select Register 2	PINSR2	00h
00F7h	Pin Select Register 3	PINSR3	00h
00F7h	Port Mode Register	PMR	
00F8h	External Input Enable Register	INTEN	00h 00h
	INT Input Filter Select Register		
00FAh		INTF	00h
00FBh	Key Input Enable Register	KIEN	00h
00FCh	Pull-Up Control Register 0	PUR0	00h
00FDh	Pull-Up Control Register 1	PUR1	00h
00FEh			
00FFh			
0100h	Timer RA Control Register	TRACR	00h
0101h	Timer RA I/O Control Register	TRAIOC	00h
0102h	Timer RA Mode Register	TRAMR	00h
0103h	Timer RA Prescaler Register	TRAPRE	FFh
0104h	Timer RA Register	TRA	FFh
0105h			
0106h	LIN Control Register	LINCR	00h
0107h	LIN Status Register	LINST	00h
0108h	Timer RB Control Register	TRBCR	00h
0109h	Timer RB One-Shot Control Register	TRBOCR	00h
010Ah	Timer RB I/O Control Register	TRBIOC	00h
010Bh	Timer RB Mode Register	TRBMR	00h
010Ch	Timer RB Prescaler Register	TRBPRE	FFh
010Dh	Timer RB Secondary Register	TRBSC	FFh
010Eh	Timer RB Primary Register	TRBPR	FFh
010Fh			
0110h			
0111h			
0112h			
0112h			
0113h			
0114n 0115h			
0116h			
0117h		TREAFO	
0118h	Timer RE Second Data Register / Counter Data Register	TRESEC	XXh
0119h	Timer RE Minute Data Register / Compare Data Register	TREMIN	XXh
011Ah	Timer RE Hour Data Register	TREHR	X0XXXXXb
011Bh	Timer RE Day of Week Data Register	TREWK	X0000XXXb
011Ch	Timer RE Control Register 1	TRECR1	XXX0X0X0b
011Dh	Timer RE Control Register 2	TRECR2	00XXXXXb
011Eh	Timer RE Count Source Select Register	TRECSR	00001000b
011Fh	Timer RE Real-Time Clock Precision Adjust Register	TREOPR	00h
0120h			
0121h			
0122h			
0123h			
0124h			
0125h			
0126h			
0127h			1
0128h			
0129h			
012Ah			
012Bh			
012Ch			
012Dh			
012Eh			
012Eh			
V12111			

SFR Information (5)⁽¹⁾ Table 4.5

Address	Register	Symbol	After reset
0130h			
0131h			
0132h			
0133h			
0134h			
0135h			
0136h			
0137h			
0138h			
0139h			
013Ah			
013Bh			
013Ch			
013Dh			
013Eh			
013Fh			
0140h			
0141h			
0142h			
0143h			
0143h			
014411 0145h			
0145n 0146h			
0147h			
0148h			
0149h			
014Ah			
014Bh			
014Ch			
014Dh			
014Eh			
014Fh			
0150h			
0151h			
0152h			
0153h			
0154h			
0155h			
0156h			
0157h			
0158h			
0159h			
015Ah			
015Bh			
015Bh			
015Dh			
015Eh			
015Fh			
0160h	UART2 Transmit/Receive Mode Register	U2MR	00h
0161h	UART2 Bit Rate Register	U2BRG	XXh
0162h	UART2 Transmit Buffer Register	U2TB	XXh
0163h			XXh
0164h	UART2 Transmit/Receive Control Register 0	U2C0	00001000b
0165h	UART2 Transmit/Receive Control Register 1	U2C1	00000010b
0166h	UART2 Receive Buffer Register	U2RB	XXh
0167h			XXh
0168h			
0169h		İ	1
016Ah		İ	1
016Bh			
016Ch			
016Dh			
016Eh			
016En			
		1	1

SFR Information (6)⁽¹⁾ Table 4.6

Address	Register	Symbol	After reset
0170h		-	
0171h			
0172h			
0173h			
0174h			
0175h			
0176h			
0177h 0178h			
0178h			
0179h			
017Bh			
017Ch			
017Dh			
017Eh			
017Fh			
0180h			
0181h			
0182h			
0183h			
0184h			
0185h			
0186h			
0187h			
0188h			
0189h 018Ah			
018An			
018Ch			
018Dh			
018Eh			
018Fh			
0190h			
0191h			
0192h			
0193h			
0194h			
0195h			
0196h			
0197h			
0198h			
0199h			
019Ah			
019Bh			
019Ch 019Dh			
019Dh 019Eh			
019Eh 019Fh			
019Fn			
01A0h			
01A2h			
01A3h			
01A4h			
01A5h			
01A6h			
01A7h			
01A8h			
01A9h			
01AAh			
01ABh			
01ACh			
01ADh			
01AEh			
01AFh			

SFR Information (7)⁽¹⁾ Table 4.7

Addroso	Pogistor	Symbol	After reset
Address 01B0h	Register	Symbol	Aiter reset
01B0h			
01B1h			
01B3h	Flash Memory Control Register 4	FMR4	0100000b
01B3h			0.000000
01B5h	Flash Memory Control Register 1	FMR1	100000Xb
01B6h			
01B7h	Flash Memory Control Register 0	FMR0	0000001b
01B8h			
01B9h			
01BAh			
01BBh			
01BCh			
01BDh			
01BEh			
01BFh			
01C0h			
01C1h			
01C2h 01C3h			
01C3h 01C4h			
01C4n			
01C6h			
01C7h			
01C8h			
01C9h			
01CAh			
01CBh			
01CCh			
01CDh			
01CEh			
01CFh			
01D0h			
01D1h			
01D2h			
01D3h			
01D4h 01D5h			
01D5h			
01D7h			
01D8h			
01D9h			
01DAh			
01DBh			
01DCh			
01DDh			
01DEh			
01DFh			
01E0h			
01E1h			
01E2h			
01E3h			
01E4h			
01E5h 01E6h			
01E6h			
01E7h			
01E9h			
01EAh			
01EBh			
01ECh			
01EDh			
01EEh			
01EFh			
A			

Address	Register	Symbol	After reset
01F0h	176912161	Symbol	AILEI TESEL
01F1h			
01F2h			
01F3h		<u> </u>	
01F4h		1	
01F5h		İ	
01F6h			
01F7h			
01F8h			
01F9h			
01FAh]
01FBh		ļ	ļI
01FCh 01FDh		ļ	<u> </u>]
01FDh 01FEh		<u> </u>	
01FEn 01FFh		ł	<u> </u>
0200h			
0200h		1	
0202h		1	
0203h			
0204h			
0205h			
0206h			
0207h			_
0208h			┟─────┨
0209h 020Ah			<u> </u>]
020Ah 020Bh		<u> </u>	
020Bh 020Ch		<u> </u>	├
020Ch			├
020Eh		t	<u> </u>
020Fh			
0210h			
0211h			
0212h			
0213h			_
0214h			<u> </u>
0215h 0216h		<u> </u>	├
0216h 0217h		l	┟─────┤
0217h 0218h			<u> </u>]
0218h		t	
021Ah		1	<u> </u>
021Bh			
021Ch			
021Dh			
021Eh			
021Fh			<u>_</u>
0220h		ļ	ļ]
0221h			<u> </u>
0222h 0223h		<u> </u>	├
0223h 0224h		l	┟─────┤
0224n 0225h			<u> </u>]
0226h		t	
0227h		1	<u> </u>
0228h			
0229h			
022Ah			
022Bh			
022Ch			
022Dh		ļ	ļl
022Eh		ļ	ļ]
022Fh		<u> </u>	<u> </u>
V·LIndofined			

SFR Information (9)⁽¹⁾ Table 4.9

Address	Register	Symbol	After reset
0230h	Register	Gymbol	Allei Teset
0231h			
0232h			
0233h			
0234h			
0235h			
0235h			
0230h			
0237h 0238h			
0230h			
023911 023Ah			
023An 023Bh			
02380			
023Ch 023Dh			
023DN			
023Eh			
023Fh			
0240h			
0241h			
0242h			
0243h			
0244h			
0245h			
0246h			
0247h			
0248h			
0249h			
024Ah			
024Bh			
024Ch			
024Dh			
024Eh			
024Fh			
0250h			
0251h			
0252h			
0253h			
0254h			
0255h			
0256h			
0257h			
0258h			
0259h			
025Ah			
025Bh			
025Ch			
025Dh			
025Eh			
025Fh			
0260h			
0261h			
0262h			
0263h			
0264h			
0265h			
0205h			
0267h			
0267h 0268h			<u> </u>
020011 0269h			
026Ah 026Bh			
026Ch			
026Dh			
026Eh			
026Fh			
V: Undofined			

SFR Information (10)⁽¹⁾ Table 4.10

Address	Register	Symbol	After reset
0270h	i tegistei	Gymbol	
0271h			
0272h			
0272h			
0274h			
0275h			
0275h			
0270h			
0277h 0278h			
0278h			
027911 027Ah			
027An 027Bh			
027Bh 027Ch			
027Dh			
027Eh			
027Fh			
0280h			
0281h			
0282h			
0283h			
0284h			
0285h			
0286h			
0287h			
0288h			
0289h			
028Ah			
028Bh			
028Ch			
028Dh			
028Eh			
028Fh			
0290h	Timer RF Register	TRF	00h
0291h			00h
0292h			
0293h			
0294h			
0295h			
0296h			
0297h			
0298h			
0299h	Timer RE Control Register 2	TRFCR2	00h
029Ah	Timer RF Control Register 2 Timer RF Control Register 0	TRFCR0	00h
029Bh	Timer RF Control Register 1	TRFCR1	00h
029Ch	Timer RF Control Register 1 Capture and Compare 0 Register	TRFM0	0000h ⁽²⁾
029Dh			FFFFh ⁽³⁾
023011	Compare 1 Register	TRFM1	FFFn®
029Eh	Compare i Register		
029Fh			FFh
02A0h			
02A1h			
02A2h			
02A3h			
02A4h			
02A5h			
02A6h			
02A7h			
02A8h			
02A9h			
02AAh			
02ABh			
02ACh			
02ADh		1	
02AEh		1	
02AFh			
<u></u>		1	1

SFR Information (11)⁽¹⁾ Table 4.11

X: Undefined NOTES:
1. The blank regions are reserved. Do not access locations in these regions.
2. After input capture mode.
3. After output compare mode.

Address	Register	Symbol	After reset
02B0h	i togistoi	Gymbol	
02B1h			
02B2h			
02B3h			
02B4h			
02B5h			
02B6h			
02B7h			
02B8h 02B9h			
02B9n 02BAh			
02BAn 02BBh			
02BCh			
02BDh			
02BEh			
02BFh			
02C0h			
02C1h			
02C2h			
02C3h			
02C4h			
02C5h			
02C6h			
02C7h 02C8h			
02C8h 02C9h			
02C3h			
02CBh			
02CCh			
02CDh			
02CEh			
02CFh			
02D0h			
02D1h			
02D2h			
02D3h			
02D4h 02D5h			
02D5h			
02D0h			
02D8h			
02D9h			
02DAh			
02DBh			
02DCh			
02DDh			
02DEh			
02DFh			
02E0h			
0055			
02EFh 02F0h			
02F0h 02F1h			
02F111 02F2h			
02F3h			
02F4h			
02F5h			
02F6h			
02F7h			
02F8h			
02F9h			
02FAh			
02FBh	Pin Select Register 4	PINSR4	00h
02FCh		NITENO	001
02FDh	External Input Enable Register 2	INTEN2	00h
02FEh 02FFh	INT Input Filter Select Register 2 Timer RF Output Control Register	INTF2 TRFOUT	00h 00h
UZFFII		INFUUI	0011
FFFFh	Option Function Select Register	OFS	(Note 2)
			(

SFR Information (12)⁽¹⁾ Table 4.12

X: Undefined

NOTES:
1. The blank regions are reserved. Do not access locations in these regions.
2. The OFS register cannot be changed by a program. Use a flash programmer to write to it.

5. Resets

The following resets are implemented: hardware reset, power-on reset, voltage monitor 0 reset, voltage monitor 1 reset, voltage monitor 2 reset, watchdog timer reset, and software reset.

Table 5.1 lists the Reset Names and Sources. Figure 5.1 lists the Block Diagram of Reset Circuit.

Table 5.1Reset Names and Sources

Reset Name	Source
Hardware reset	Input voltage of RESET pin is held "L"
Power-on reset	VCC rises
Voltage monitor 0 reset	VCC falls (monitor voltage: Vdet0)
Voltage monitor 1 reset	VCC falls (monitor voltage: Vdet1)
Voltage monitor 2 reset	VCC falls (monitor voltage: Vdet2)
Watchdog timer reset	Underflow of watchdog timer
Software reset	Write 1 to PM03 bit in PM0 register





5. Resets

Table 5.2 shows the Pin Functions while **RESET** Pin Level is "L", Figure 5.2 shows the CPU Register Status after Reset, Figure 5.3 shows the Reset Sequence, and Figure 5.4 shows the OFS Register.

Table 5.2 Pin Functions while RESET Pin Level is "L"

Pin Name	Pin Functions
P0_4 to P0_7	Input port
P1, P3	Input port
P4_3, P4_5	Input port
P4_4	Output port
P6_0, P6_3 to P6_6	Input port



Figure 5.2 CPU Register Status after Reset



•	Function Se	5			
	1 1	Symbol OFS	Address 0FFFFh	When Shipping FFh ⁽³⁾	
		Bit Symbol	Bit Name	Function	RW
		WDTON	Watchdog timer start select bit	0 : Starts w atchdog timer automatically after reset 1 : Watchdog timer is inactive after reset	RW
		(b1)	Reserved bit	Set to 1.	RW
		ROMCR	ROM code protect disabled bit	0 : ROM code protect disabled 1 : ROMCP1 enabled	RW
		ROMCP1	ROM code protect bit	0 : ROM code protect enabled 1 : ROM code protect disabled	RW
		(b4)	Reserved bit	Set to 1.	RW
		LVDOON	Voltage detection 0 circuit start bit ⁽²⁾	 0 : Voltage monitor 0 reset enabled after hardw are reset 1 : Voltage monitor 0 reset disabled after hardw are reset 	RW
		(b6)	Reserved bit	Set to 1.	RW
		CSPROINI	Count source protect mode after reset select bit	0 : Count source protect mode enabled after reset 1 : Count source protect mode disabled after reset	RW

1. The OFS register is on the flash memory. Write to the OFS register with a program. After writing is completed, do not write additions to the OFS register.

2. Setting the LVD0ON bit is only valid after a hardware reset. To use the power-on reset, set the LVD0ON bit to 0 (voltage monitor 0 reset enabled after hardware reset).

3. If the block including the OFS register is erased, FFh is set to the OFS register.



5.1 Hardware Reset

A reset is applied using the $\overline{\text{RESET}}$ pin. When an "L" signal is applied to the $\overline{\text{RESET}}$ pin while the supply voltage meets the recommended operating conditions, pins, CPU, and SFRs are all reset (refer to **Table 5.2 Pin Functions while RESET Pin Level is "L"**). When the input level applied to the RESET pin changes from "L" to "H", a program is executed beginning with the address indicated by the reset vector. After reset, the low-speed on-chip oscillator clock divided by 8 is automatically selected as the CPU clock.

Refer to 4. Special Function Registers (SFRs) for the state of the SFRs after reset.

The internal RAM is not reset. If the **RESET** pin is pulled "L" while writing to the internal RAM is in progress, the contents of internal RAM will be undefined.

Figure 5.5 shows an Example of Hardware Reset Circuit and Operation and Figure 5.6 shows an Example of Hardware Reset Circuit (Usage Example of External Supply Voltage Detection Circuit) and Operation.

5.1.1 When Power Supply is Stable

- (1) Apply "L" to the $\overline{\text{RESET}}$ pin.
- (2) Wait for $10 \mu s$.
- (3) Apply "H" to the $\overline{\text{RESET}}$ pin.

5.1.2 Power On

- (1) Apply "L" to the $\overline{\text{RESET}}$ pin.
- (2) Let the supply voltage increase until it meets the recommended operating conditions.
- (3) Wait for td(P-R) or more to allow the internal power supply to stabilize (refer to 22. Electrical Characteristics).
- (4) Wait for $10 \mu s$.
- (5) Apply "H" to the $\overline{\text{RESET}}$ pin.



Figure 5.5 Example of Hardware Reset Circuit and Operation



Figure 5.6 Example of Hardware Reset Circuit (Usage Example of External Supply Detection Circuit) and Operation

5.2 Power-On Reset Function

When the $\overline{\text{RESET}}$ pin is connected to the VCC pin via a pull-up resistor, and the VCC pin voltage level rises while the rise gradient is trth or more, the power-on reset function is enabled and the MCU resets its pins, CPU, and SFR. When a capacitor is connected to the $\overline{\text{RESET}}$ pin, too, always keep the voltage to the $\overline{\text{RESET}}$ pin 0.8VCC or more. When the input voltage to the VCC pin reaches the Vdet0 level or above, the low-speed on-chip oscillator clock starts counting. When the low-speed on-chip oscillator clock count reaches 32, the internal reset signal is held "H" and the MCU enters the reset sequence (refer to **Figure 5.3**). The low-speed on-chip oscillator clock divided by 8 is automatically selected as the CPU clock after reset.

Refer to **4. Special Function Registers (SFRs)** for the states of the SFR after power-on reset. The voltage monitor 0 reset is enabled after power-on reset.

Figure 5.7 shows an Example of Power-On Reset Circuit and Operation.



VCA2 register to 1.

Figure 5.7 Example of Power-On Reset Circuit and Operation

5.3 Voltage Monitor 0 Reset

A reset is applied using the on-chip voltage detection 0 circuit. The voltage detection 0 circuit monitors the input voltage to the VCC pin. The voltage to monitor is Vdet0.

When the input voltage to the VCC pin reaches the Vdet0 level or below, the pins, CPU, and SFR are reset.

When the input voltage to the VCC pin reaches the Vdet0 level or above, the low-speed on-chip oscillator clock start counting. When the low-speed on-chip oscillator clock count reaches 32, the internal reset signal is held "H" and the MCU enters the reset sequence (refer to **Figure 5.3**). The low-speed on-chip oscillator clock divided by 8 is automatically selected as the CPU clock after reset.

The LVD0ON bit in the OFS register can be used to enable or disable voltage monitor 0 reset after a hardware reset. Setting the LVD0ON bit is only valid after a hardware reset.

To use the power-on reset function, enable voltage monitor 0 reset by setting the LVD0ON bit in the OFS register to 0, the VW0C0 and VW0C6 bits in the VW0C register to 1 respectively, and the VCA25 bit in the VCA2 register to 1.

The LVD0ON bit cannot be changed by a program. To set the LVD0ON bit, write 0 (voltage monitor 0 reset enabled after hardware reset) or 1 (voltage monitor 0 reset disabled after hardware reset) to bit 5 of address 0FFFFh using a flash programmer.

Refer to Figure 5.4 OFS Register for details of the OFS register.

Refer to 4. Special Function Registers (SFRs) for the status of the SFR after voltage monitor 0 reset.

The internal RAM is not reset. When the input voltage to the VCC pin reaches the Vdet0 level or below while writing to the internal RAM is in progress, the contents of internal RAM are undefined.

Refer to 6. Voltage Detection Circuit for details of voltage monitor 0 reset.

5.4 Voltage Monitor 1 Reset

A reset is applied using the on-chip voltage detection 1 circuit. The voltage detection 1 circuit monitors the input voltage to the VCC pin. The voltage to monitor is Vdet1.

When the input voltage to the VCC pin reaches the Vdet1 level or below, the pins, CPU, and SFR are reset and a program is executed beginning with the address indicated by the reset vector. After reset, the low-speed on-chip oscillator clock divided by 8 is automatically selected as the CPU clock.

The voltage monitor 1 does not reset some portions of the SFR. Refer to **4. Special Function Registers (SFRs)** for details.

The internal RAM is not reset. When the input voltage to the VCC pin reaches the Vdet1 level or below while writing to the internal RAM is in progress, the contents of internal RAM are undefined.

Refer to 6. Voltage Detection Circuit for details of voltage monitor 1 reset.

5.5 Voltage Monitor 2 Reset

A reset is applied using the on-chip voltage detection 2 circuit. The voltage detection 2 circuit monitors the input voltage to the VCC pin. The voltage to monitor is Vdet2.

When the input voltage to the VCC pin reaches the Vdet2 level or below, the pins, CPU, and SFR are reset and the program beginning with the address indicated by the reset vector is executed. After reset, the low-speed on-chip oscillator clock divided by 8 is automatically selected as the CPU clock.

The voltage monitor 2 does not reset some SFRs. Refer to 4. Special Function Registers (SFRs) for details.

The internal RAM is not reset. When the input voltage to the VCC pin reaches the Vdet2 level or below while writing to the internal RAM is in progress, the contents of internal RAM are undefined.

Refer to 6. Voltage Detection Circuit for details of voltage monitor 2 reset.

5.6 Watchdog Timer Reset

When the PM12 bit in the PM1 register is set to 1 (reset when watchdog timer underflows), the MCU resets its pins, CPU, and SFR if the watchdog timer underflows. Then the program beginning with the address indicated by the reset vector is executed. After reset, the low-speed on-chip oscillator clock divided by 8 is automatically selected as the CPU clock.

The watchdog timer reset does not reset some SFRs. Refer to **4. Special Function Registers (SFRs)** for details. The internal RAM is not reset. When the watchdog timer underflows, the contents of internal RAM are undefined. Refer to **16. Watchdog Timer** for details of the watchdog timer.

5.7 Software Reset

When the PM03 bit in the PM0 register is set to 1 (MCU reset), the MCU resets its pins, CPU, and SFR. The program beginning with the address indicated by the reset vector is executed. After reset, the low-speed on-chip oscillator clock divided by 8 is automatically selected for the CPU clock.

The software reset does not reset some SFRs. Refer to **4. Special Function Registers (SFRs)** for details. The internal RAM is not reset.

6. Voltage Detection Circuit

The voltage detection circuit monitors the input voltage to the VCC pin. This circuit can be used to monitor the VCC input voltage by a program. Alternately, voltage monitor 0 reset, voltage monitor 1 interrupt, voltage monitor 1 reset, voltage monitor 2 interrupt, and voltage monitor 2 reset can also be used.

Note that voltage monitor 1 and voltage monitor 2 share the voltage detection circuit with comparator 1 and comparator 2. Either voltage monitor 1 and voltage monitor 2 or comparator 1 and comparator 2 can be selected. Table 6.1 lists the Specifications of Voltage Detection Circuit and Figures 6.1 to 6.4 show the Block Diagrams. Figures 6.5 to 6.10 show the Associated Registers.

	Item	Voltage Detection 0	Voltage Detection 1	Voltage Detection 2
VCC Monitor	Voltage to monitor	Vdet0	Vdet1	Vdet2
	Detection target	Whether passing through Vdet0 by falling	Passing through Vdet1 by rising or falling	Passing through Vdet2 by rising or falling
	Monitor	None	VW1C3 bit in VW1C register	VCA13 bit in VCA1 register
			Whether VCC is higher or lower than Vdet1	Whether VCC is higher or lower than Vdet2
Process	Reset	Voltage monitor 0 reset	Voltage monitor 1 reset	Voltage monitor 2 reset
When Voltage is Detected		Reset at Vdet0 > VCC; restart CPU operation at VCC > Vdet0	Reset at Vdet1 > VCC; restart CPU operation after a specified time	Reset at Vdet2 > VCC; restart CPU operation after a specified time
	Interrupt	None	Voltage monitor 1 interrupt	Voltage monitor 2 interrupt
			Interrupt request at both or either of Vdet1 > VCC and VCC > Vdet1	Interrupt request at both or either of Vdet2 > VCC and VCC > Vdet2
Digital Filter	Switch enabled/disabled	Available	Available	Available
	Sampling time	(Divide-by-n of fOCO-S) × 4	(Divide-by-n of fOCO-S) × 2	(Divide-by-n of fOCO-S) × 2
		n: 1, 2, 4, and 8	n: 1, 2, 4, and 8	n: 1, 2, 4, and 8

 Table 6.1
 Specifications of Voltage Detection Circuit



Figure 6.1 Block Diagram of Voltage Detection Circuit



Figure 6.2 Block Diagram of Voltage Monitor 0 Reset Generation Circuit



Figure 6.3 Block Diagram of Voltage Monitor 1 Interrupt/Reset Generation Circuit



Voltage I	De	etec	tio	n F	Register 1			
b7 b6 b5 b	04 b	<u> </u>		÷.				
0000	0	0	0	C	Symbol	Address	After Reset ⁽²⁾	
					VCA1	0031h	00001000b	
					Bit Symbol	Bit Name	Function	RW
					 (b2-b0)	Reserved bits	Set to 0.	RW
					VCA13	Voltage detection 2 signal monitor flag ⁽¹⁾	0 : VCC < Vdet2 1 : VCC ≥ Vdet2 or voltage detection 2 circuit disabled	RO
					 (b7-b4)	Reserved bits	Set to 0.	RW

NOTES:

- The VCA13 bit is enabled when the VCA27 bit in the VCA2 register is set to 1 (voltage detection 2 circuit enabled). The VCA13 bit is set to 1 (VCC ≥ Vdet 2) when the VCA27 bit in the VCA2 register is set to 0 (voltage detection 2 circuit disabled).
- 2. Softw are reset, w atchdog timer reset, voltage monitor 1 reset, and voltage monitor 2 reset do not affect this register.

Voltage Detection Register 2⁽¹⁾

b7	b6 b	5 b4 b	3 b2 b1	b0					
		0 0	000		Symbol	Address	After Reset ⁽⁵⁾		
							The LVD0ON bit in the OFS register is set to 1 and hardw are reset : Pow er-on reset, voltage monitor 0 reset or LVD0ON bit in the OFS register is	00h	
				VCA2	0032h	set to 0, and hardw are reset :	00100000	b	
					Bit Symbol	Bit Name	Function		RW
					VCA20	Internal pow er low consumption enable bit ⁽⁶⁾	0 : Low consumption disabled 1 : Low consumption enabled ⁽⁷⁾		RW
					 (b4-b1)	Reserved bits	Set to 0.		RW
					VCA25	Voltage detection 0 enable bit ⁽²⁾	0 : Voltage detection 0 circuit disabled 1 : Voltage detection 0 circuit enabled		RW
					VCA26	Voltage detection 1 enable bit ⁽³⁾	0 : Voltage detection 1 circuit disabled 1 : Voltage detection 1 circuit enabled		RW
					VCA27	Voltage detection 2 enable bit ⁽⁴⁾	0 : Voltage detection 2 circuit disabled 1 : Voltage detection 2 circuit enabled		RW

NOTES:

- 1. Set the PRC3 bit in the PRCR register to 1 (write enabled) before rewriting to the VCA2 register.
- To use the voltage monitor 0 reset, set the VCA25 bit to 1. After the VCA25 bit is set to 1 from 0, the voltage detection circuit waits for td(E-A) to elapse before starting operation.
- 3. To use the voltage monitor 1 interrupt/reset or the VW1C3 bit in the VW1C register, set the VCA26 bit to 1. After the VCA26 bit is set to 1 from 0, the voltage detection circuit waits for td(E-A) to elapse before starting operation.
- 4. To use the voltage monitor 2 interrupt/reset or the VCA13 bit in the VCA1 register, set the VCA27 bit to 1. After the VCA27 bit is set to 1 from 0, the voltage detection circuit waits for td(E-A) to elapse before starting operation.
- 5. Softw are reset, w atchdog timer reset, voltage monitor 1 reset, and voltage monitor 2 reset do not affect this register.
- 6. Use the VCA20 bit only when entering to wait mode. To set the VCA20 bit, follow the procedure show n in Figure 11.9 Handling Procedure of Internal Power Low Consumption Using VCA20 Bit.
- 7. When the VCA20 bit is set to 1 (low consumption enabled), do not set the CM10 bit in the CM1 register to 1 (stop mode).

Figure 6.5 Registers VCA1 and VCA2

r

	b3 b2 b1 b0	Symbol	Address	After Reset ⁽²⁾	
				The LVD0ON bit in the OFS register is set to 1 and hardw are reset : 1000X010 Pow er-on reset, voltage monitor 0 reset or LVD0ON bit in the OFS register is set	b
		VW0C	0038h	to 0, and hardware reset : 1100X011	b
		Bit Symbol	Bit Name	Function	RW
		VW0C0	Voltage monitor 0 reset enable bit ⁽³⁾	0 : Disable 1 : Enable	RW
		VW0C1	Voltage monitor 0 digital filter disable mode select bit	 0 : Digital filter enabled mode (digital filter circuit enabled) 1 : Digital filter disabled mode (digital filter circuit disabled) 	RW
		VW0C2	Reserved bit	Set to 0.	RW
		 (b3)	Reserved bit	When read, the content is undefined.	RO
		VW0F0	Sampling clock select bits	^{b5 b4} 0 0 : fOCO-S divided by 1 0 1 : fOCO-S divided by 2	RW
		VW0F1		1 0 : fOCO-S divided by 4 1 1 : fOCO-S divided by 8	RW
		VW0C6	Voltage monitor 0 circuit mode select bit	When the VW0C0 bit is set to 1 (voltage monitor 0 reset enabled), set to 1.	RW
		VW0C7	Voltage monitor 0 reset generation condition select bit ⁽⁴⁾	When the VW0C1 bit is set to 1 (digital filter disabled mode), set to 1.	RW
 The mon The Set 	value rema itor 2 reset VW0C0 bit the VW0C0	it in the PRCR ains unchange t is enabled w 0 bit to 0 (disa	bit ⁽⁴⁾ eregister to 1 (w rite enabled) ed after a softw are reset, w a hen the VCA25 bit in the VCA ble), w hen the VCA25 bit is s	before rew riting to the VW0C register. tchdog timer reset, voltage monitor 1 reset, and volta v2 register is set to 1 (voltage detection 0 circuit enat et to 0 (voltage detection 0 circuit disabled). w n in Table 6.2 Procedure for Setting Bits	ige

Figure 6.6 VW0C Register

Voltage Monitor 1 Circuit Control Register⁽¹⁾

0		5		
b7 b6 b5 b4 b3 b2 b1 b0				
	Symbol VW1C	Address 0036h	After Reset ⁽⁸⁾ 00001010b	
	Bit Symbol	Bit Name	Function	RW
	VW1C0	Voltage monitor 1 interrupt/reset enable bit ⁽⁶⁾	0 : Disable 1 : Enable	RW
	VW1C1	Voltage monitor 1 digital filter disable mode select bit ⁽²⁾	 0 : Digital filter enabled mode (digital filter circuit enabled) 1 : Digital filter disabled mode (digital filter circuit disabled) 	RW
	VW1C2	Voltage change detection flag ^(3, 4, 8)	0 : Not detected 1 : Vdet1 crossing detected	RW
	VW1C3	Voltage detection 1 signal monitor flag ^(3, 8)	0 : VCC < Vdet1 1 : VCC ≥ Vdet1 or voltage detection 1 circuit disabled	RO
	VW1F0	Sampling clock select bits	^{b5 b4} 0 0 : fOCO-S divided by 1 0 1 : fOCO-S divided by 2	RW
	VW1F1		1 0 : fOCO-S divided by 4 1 1 : fOCO-S divided by 8	RW
	VW1C6	Voltage monitor 1 circuit mode select bit ⁽⁵⁾	0 : Voltage monitor 1 interrupt mode 1 : Voltage monitor 1 reset mode	RW
	VW1C7	Voltage monitor 1 interrupt/reset generation condition select bit ^(7, 9)	0 : When VCC reaches Vdet1 or above 1 : When VCC reaches Vdet1 or below	RW

NOTES:

- Set the PRC3 bit in the PRCR register to 1 (w rite enabled) before rew riting to the VW1C register. When the VW1C register is rew ritten, the VW1C2 bit may be set to 1. Set the VW1C2 bit to 0 after rew riting the VW1C register.
- 2. To use the voltage monitor 1 interrupt to exit stop mode and to return again, write 0 to the VW1C1 bit before writing 1.
- 3. Bits VW1C2 and VW1C3 are enabled when the VCA26 bit in the VCA2 register is set to 1 (voltage detection 1 circuit enabled).
- 4. Set this bit to 0 by a program. When 0 is written by a program, it is set to 0 (and remains unchanged even if 1 is written to it).
- 5. The VW1C6 bit is enabled when the VW1C0 bit is set to 1 (voltage monitor 1 interrupt/reset enabled).
- The VW1C0 bit is enabled when the VCA26 bit in the VCA2 register is set to 1 (voltage detection 1 circuit enabled). Set the VW1C0 bit to 0 (disable) when the VCA26 bit is set to 0 (voltage detection 1 circuit disabled). To set VW1C0 bit to 1 (enable), follow the procedure show n in Table 6.3 Procedure for Setting Bits Associated with Voltage Monitor 1 Interrupt and Reset.
- 7. The VW1C7 bit is enabled when the VCAC1 bit in the VCAC register is set to 0 (one edge). Set the VW1C7 bit after setting the VCAC1 bit to 0.
- 8. Bits VW1C2 and VW1C3 remain unchanged after a softw are reset, w atchdog timer reset, voltage monitor 1 reset, or voltage monitor 2 reset.
- 9. When the VW1C6 bit is set to 1 (voltage monitor 1 reset mode), set the VW1C7 bit to 1 (when VCC reaches Vdet1 or below). (Do not set to 0.)

Figure 6.7 VW1C Register

Voltage Monitor 2 Circuit Control Register⁽¹⁾

b7 b6 b5 b	4 b3	3 b2	b1 b0	Symbol	Address	After Reset ⁽⁸⁾	
	Н	Η		VW2C	0037h	00000010b	
				Bit Symbol	Bit Name	Function	RW
L		VW2C0	Voltage monitor 2 interrupt/reset enable bit ⁽⁶⁾	0 : Disable 1 : Enable	RW		
				VW2C1	Voltage monitor 2 digital filter disable mode select bit ⁽²⁾	0 : Digital filter enabled mode (digital filter circuit enabled) 1 : Digital filter disabled mode (digital filter circuit disabled)	RW
		L		VW2C2	Voltage change detection flag ^(3, 4, 8)	0 : Not detected 1 : Vdet2 crossing detected	RW
				VW2C3	WDT detection flag ^(4, 8)	0 : Not detected 1 : Detected	RW
		VW2F0	Sampling clock select bits	b5 b4 0 0 : fOCO-S divided by 1 0 1 : fOCO-S divided by 2	RW		
				VW2F1		1 0 : fOCO-S divided by 4 1 1 : fOCO-S divided by 8	RW
				VW2C6	Voltage monitor 2 circuit mode select bit ⁽⁵⁾	0 : Voltage monitor 2 interrupt mode 1 : Voltage monitor 2 reset mode	RW
				VW2C7	Voltage monitor 2 interrupt/reset generation condition select bit ^(7, 9)	0 : When VCC reaches Vdet2 or above 1 : When VCC reaches Vdet2 or below	RW

NOTES:

- Set the PRC3 bit in the PRCR register to 1 (w rite enabled) before rew riting to the VW2C register. When the VW2C register is rew ritten, the VW2C2 bit may be set to 1. Set the VW2C2 bit to 0 after rew riting the VW2C register.
- 2. To use the voltage monitor 2 interrupt to exit stop mode and to return again, write 0 to the VW2C1 bit before writing 1.
- The VW2C2 bit is enabled when the VCA27 bit in the VCA2 register is set to 1 (voltage detection 2 circuit enabled).
- 4. Set this bit to 0 by a program. When 0 is written by a program, it is set to 0 (and remains unchanged even if 1 is written to it).
- 5. The VW2C6 bit is enabled when the VW2C0 bit is set to 1 (voltage monitor 2 interrupt/reset enabled).
- The VW2C0 bit is enabled when the VCA27 bit in the VCA2 register is set to 1 (voltage detection 2 circuit enabled). Set the VW2C0 bit to 0 (disable) when the VCA27 bit is set to 0 (voltage detection 2 circuit disabled). To set VW2C0 bit to 1 (enable), follow the procedure show n in Table 6.4 Procedure for Setting Bits Associated with Voltage Monitor 2 Interrupt and Reset.
- 7. The VW2C7 bit is enabled when the VCAC2 bit in the VCAC register is set to 0 (one edge). Set the VW2C7 bit after setting the VCAC2 bit to 0.
- 8. Bits VW2C2 and VW2C3 remain unchanged after a software reset, watchdog timer reset, voltage monitor 1 reset, or voltage monitor 2 reset.
- 9. When the VW2C6 bit is set to 1 (voltage monitor 2 reset mode), set the VW2C7 bit to 1 (when VCC reaches Vdet2 or below). (Do not set to 0.)











6.1 VCC Input Voltage

6.1.1 Monitoring Vdet0

Vdet0 cannot be monitored.

6.1.2 Monitoring Vdet1

Set the VCA26 bit in the VCA2 register to 1 (voltage detection 1 circuit enabled). After td(E-A) has elapsed (refer to **22. Electrical Characteristics**), Vdet1 can be monitored by the VW1C3 bit in the VW1C register.

6.1.3 Monitoring Vdet2

Set the VCA27 bit in the VCA2 register to 1 (voltage detection 2 circuit enabled). After td(E-A) has elapsed (refer to **22. Electrical Characteristics**), Vdet2 can be monitored by the VCA13 bit in the VCA1 register.

6.2 Voltage Monitor 0 Reset

Table 6.2 lists the Procedure for Setting Bits Associated with Voltage Monitor 0 Reset and Figure 6.11 shows an Example of Voltage Monitor 0 Reset Operation. To use the voltage monitor 0 reset to exit stop mode, set the VW0C1 bit in the VW0C register to 1 (digital filter disabled).

Step	When Using Digital Filter	When Not Using Digital Filter		
1	Set the VCA25 bit in the VCA2 register to 1	(voltage detection 0 circuit enabled)		
2	Wait for td(E-A)			
3	Select the sampling clock of the digital filter by the VW0F0 to VW0F1 bits in the VW0C register	Set the VW0C7 bit in the VW0C register to 1		
4(1)	Set the VW0C1 bit in the VW0C register to 0 (digital filter enabled)	Set the VW0C1 bit in the VW0C register to 1 (digital filter disabled)		
5(1)	Set the VW0C6 bit in the VW0C register to	1 (voltage monitor 0 reset mode)		
6	Set the VW0C2 bit in the VW0C register to	0		
7	Set the CM14 bit in the CM1 register to 0 (low-speed on-chip oscillator on)	-		
8	Wait for 4 cycles of the sampling clock of the digital filter	 – (No wait time required) 		
9	Set the VW0C0 bit in the VW0C register to 1 (voltage monitor 0 reset enabled)			

Table 6.2 Procedure for Setting Bits Associated with Voltage Monitor 0 Reset

NOTE:

1. When the VW0C0 bit is set to 0, steps 3, 4, and 5 can be executed simultaneously (with 1 instruction).



Figure 6.11 Example of Voltage Monitor 0 Reset Operation

6.3 Voltage Monitor 1 Interrupt and Voltage Monitor 1 Reset

Table 6.3 lists the Procedure for Setting Bits Associated with Voltage Monitor 1 Interrupt and Reset. Figure 6.12 shows an Example of Voltage Monitor 1 Interrupt and Voltage Monitor 1 Reset Operation. To use the voltage monitor 1 interrupt or voltage monitor 1 reset to exit stop mode, set the VW1C1 bit in the VW1C register to 1 (digital filter disabled).

			i vonago montor i m	ton apt and nooot	
	When Using Digital Filter When Not Using Digital			ng Digital Filter	
Step	Voltage Monitor 1	Voltage Monitor 1	Voltage Monitor 1	Voltage Monitor 1	
	Interrupt	Reset	Interrupt	Reset	
1	Set the COMPSEL bit	in the PINSR4 register	to 0 (voltage monitor 1	, voltage monitor 2)	
2	Set the VCA26 bit in the	ne VCA2 register to 1 (v	voltage detection 1 circ	uit enabled)	
3	Wait for td(E-A)				
	Select the sampling cl	•	Set the VW1C1 bit in t	he VW1C register to 1	
4	by the VW1F0 to VW1	F1 bits in the VW1C	(digital filter disabled)		
	register				
5(2)		he VW1C register to 0	-		
-	(digital filter enabled)				
	Select the timing of the		Select the timing of the interrupt and reset		
6	request by the VCAC1		request by the VCAC1 bit in the VCAC		
0	register and the VW10	C7 bit in the VW1C	register and the VW1C7 bit in the VW1C		
	register ⁽¹⁾		register ⁽¹⁾		
	Set the VW1C6 bit in	Set the VW1C6 bit in	Set the VW1C6 bit in	Set the VW1C6 bit in	
7	the VW1C register to	the VW1C register to	the VW1C register to	the VW1C register to	
1	0 (voltage monitor 1	1 (voltage monitor 1	0 (voltage monitor 1	1 (voltage monitor 1	
	interrupt mode)	reset mode)	interrupt mode)	reset mode)	
8	Set the VW1C2 bit in t	he VW1C register to 0	(Vdet1 crossing is not o	detected)	
9	Set the CM14 bit in the	e CM1 register to 0	-		
9	(low-speed on-chip os	cillator on)			
10	Wait for 2 cycles of the	e sampling clock of the	– (No wait time required)		
10	digital filter				
11	Set the VW1C0 bit in t	he VW1C register to 1	(voltage monitor 1 inter	rrupt/reset enabled)	
NOTES	·				

Table 6.3	Procedure for Setting Bits Associated	d with Voltage Monitor 1 Interrupt and Res	et
-----------	---------------------------------------	--	----

NOTES:

1. Set the VW1C7 bit to 1 (when VCC reaches Vdet1 or below) for the voltage monitor 1 reset.

2. When the VW1C0 bit is set to 0, steps 4 and 5 can be executed simultaneously (with 1 instruction).



Figure 6.12 Example of Voltage Monitor 1 Interrupt and Voltage Monitor 1 Reset Operation

6.4 Voltage Monitor 2 Interrupt and Voltage Monitor 2 Reset

Table 6.4 lists the Procedure for Setting Bits Associated with Voltage Monitor 2 Interrupt and Reset. Figure 6.13 shows an Example of Voltage Monitor 2 Interrupt and Voltage Monitor 2 Reset Operation. To use the voltage monitor 2 interrupt or voltage monitor 2 reset to exit stop mode, set the VW2C1 bit in the VW2C register to 1 (digital filter disabled).

		5	0		
	When Using	Digital Filter	When Not Usi	ng Digital Filter	
Step	Voltage Monitor 2	Voltage Monitor 2	Voltage Monitor 2	Voltage Monitor 2	
	Interrupt	Reset	Interrupt	Reset	
1	Set the COMPSEL bit	in the PINSR4 register	to 0 (voltage monitor 1	, voltage monitor 2)	
2	Set the VCA27 bit in the	ne VCA2 register to 1 (v	voltage detection 2 circ	uit enabled)	
3	Wait for td(E-A)				
4	Select the sampling clo by the VW2F0 to VW2 register	•	Set the VW2C1 bit in t (digital filter disabled)	he VW2C register to 1	
5(2)	Set the VW2C1 bit in the (digital filter enabled)	he VW2C register to 0	_		
6	Select the timing of the request by the VCAC2 register and the VW2C register ⁽¹⁾	bit in the VCAC	Select the timing of the interrupt and reset request by the VCAC2 bit in the VCAC register and the VW2C7 bit in the VW2C register ⁽¹⁾		
7	Set the VW2C6 bit in the VW2C register to 0 (voltage monitor 2 interrupt mode)	Set the VW2C6 bit in the VW2C register to 1 (voltage monitor 2 reset mode)	Set the VW2C6 bit in the VW2C register to 0 (voltage monitor 2 interrupt mode)	Set the VW2C6 bit in the VW2C register to 1 (voltage monitor 2 reset mode)	
8	Set the VW2C2 bit in t	he VW2C register to 0	(Vdet2 crossing is not o	detected)	
9	Set the CM14 bit in the CM1 register to 0 (low-speed on-chip oscillator on)		_		
10	Wait for 2 cycles of the digital filter	sampling clock of the	– (No wait time required)		
11			voltage monitor 2 inter		

NOTES:

1. Set the VW2C7 bit to 1 (when VCC reaches Vdet2 or below) for the voltage monitor 2 reset.

2. When the VW2C0 bit is set to 0, steps 4 and 5 can be executed simultaneously (with 1 instruction).



Figure 6.13 Example of Voltage Monitor 2 Interrupt and Voltage Monitor 2 Reset Operation

7. Comparator

The comparators compare a reference input voltage and an analog input voltage. Comparator 1 and comparator 2 are independent of each other. Note that comparator 1 and comparator 2 share the voltage detection circuit with voltage monitor 1 and voltage monitor 2. Either comparator 1 and comparator 2 or voltage monitor 1 and voltage monitor 2 can be selected to use the voltage detection circuit.

7.1 Overview

The comparison result of the reference input voltage and analog input voltage can be read by software. The result also can be output from the VCOUTi (i = 1 or 2) pin. An internal reference voltage or input voltage to the CVREF pin can be selected as the reference input voltage. The comparator 1 interrupt and comparator 2 interrupt also can be used.

Table 7.1 lists the Specifications of Comparator, Figure 7.1 shows the Block Diagram of Comparator, and Table 7.2 lists the Pin Configuration of Comparator.

	Item	Comparator 1	Comparator 2	
Analog input voltage		Input voltage to VCMP1 pin	Input voltage to VCMP2 pin	
Reference input voltage		Internal reference voltage or input voltage to CVREF pin		
Comparison target		Whether passing thorough reference input voltage by rising or falling		
Comparison result monitor		VW1C3 bit in VW1C register	VCA13 bit in VCA1 register	
		Whether higher or lower than reference input voltage		
Interrupt		Comparator 1 interrupt (non-makable or maskable selectable)	Comparator 2 interrupt (non-makable or maskable selectable)	
		Interrupt request at both or either of reference input voltage > input voltage to VCMP1 pin and input voltage to VCMP1 pin > reference input voltage	Interrupt request at both or either of reference input voltage > input voltage to VCMP2 pin and input voltage to VCMP2 pin > reference input voltage	
Digital Filter	Switch enabled/disabled	Available		
	Sampling time	(fOCO-S divided by n) × 2 n: 1, 2, 4, 8		
Compa	rison result output	Output from VCOUT1 pin (Whether the comparison result output is inverted or not can be selected)	Output from VCOUT2 pin (Whether the comparison result output is inverted or not can be selected)	

Table 7.1 Specifications of Comparator



Figure 7.1 Block Diagram of Comparator

Table 7.2 Pin Configuration of Comparator

Pin Name	I/O	Function
VCMP1	Input	Comparator 1 analog pin
VCOUT1	Output	Comparator 1 comparison result output pin
VCMP2	Input	Comparator 2 analog pin
VCOUT2	Output	Comparator 2 comparison result output pin
CVREF	Input	Comparator reference voltage pin

7.2 Register Description

Figures 7.2 to 7.11 show the registers associated with the comparator when comparator 1 or comparator 2 is selected.



Figure 7.2 Registers BGRTRMA and BGRTRMB

Voltage Detection	Register 1			
b7 b6 b5 b4 b3 b2 b1 b0 0 0 0 0 0 0 0 0	Symbol	Address	After Reset ⁽²⁾	
	VCA1	0031h	00001000b	
	Bit Symbol	Bit Name	Function	RW
	 (b2-b0)	Reserved bits	Set to 0.	RW
	VCA13	Comparator 2 signal monitor	flag ⁽¹⁾ 0: VCMP2 < reference voltage 1: VCMP2 ≥ reference voltage or comparator 2 circuit disabled	RO
	 (b7-b4)	Reserved bits	Set to 0.	RW
VCA13 bit is s 2 circuit disab	et to 1 (VCMF led).		A2 register is set to 1 (comparator 2 circuit enable the VCA27 bit in the VCA2 register is set to 0 (co nis register.	
Voltage Detection		-		
	Symbol	Address	After Reset ⁽²⁾ The LVD0ON bit in the OFS register is set to 1 and hardw are reset : 00h Pow er-on reset, voltage monitor 0 reset	
		0000	or the LVD0ON bit in the OFS register is set to 0, and hardw are reset : 00100	000h
	VCA2	0032h		
	Bit Symbol	Bit Name Internal pow er low	Function 0: Low consumption disabled	RW
	VCA20	consumption enable bit ⁽³⁾	1: Low consumption enabled ⁽⁷⁾	RW
	 (b4-b1)	Reserved bits	Set to 0.	RW
	VCA25	Voltage detection 0 enable bit ⁽⁴⁾	0: Voltage detection 0 circuit disabled 1: Voltage detection 0 circuit enabled	RW
	VCA26	Comparator 1 enable bit ⁽⁵⁾	0: Comparator 1 circuit disabled 1: Comparator 1 circuit enabled	RW
	VCA27	Comparator 2 enable bit ⁽⁶⁾	0: Comparator 2 circuit disabled 1: Comparator 2 circuit enabled	RW
 Software reset Use the VCA2 Figure 11.9 H To use the vol After the VCA operation. To use the con After the VCA To use the con After the VCA To use the con 	et and w atche 10 bit only w he landling Prod tage monitor (25 bit is set to mparator 1 inte 26 bit is set to mparator 2 inte	log timer reset do not affect the en the MCU enters w ait mode. Cedure of Internal Power L oreset, set the VCA25 bit to 1 or 1 from 0, the voltage detection errupt or the VW1C3 bit in the or 1 from 0, the comparator 1 comparator 1 compared to the VCA13 bit in the	To set the VCA20 bit, follow the procedure show Consumption Using VCA20 Bit .	ng peration.



0	04 b3 b2 b1 b0	Symbol VW1C	Address 0036h	After Reset ⁽²⁾ 00001010b	
		Bit Symbol	Bit Name	Function	R\
		VW1C0	Comparator 1 interrupt enable bit ⁽³⁾	0: Disable 1: Enable	R\
		VW1C1	Comparator 1 digital filter disable mode select bit ⁽⁴⁾	0: Digital filter enable mode (digital filter circuit enabled) 1: Digital filter disable mode (digital filter circuit disabled)	R\
		VW1C2	Comparator 1 interrupt flag ^(2, 5, 6)	[Source for setting this bit to 0] 0: Write 0 [Source for setting this bit to 0] 1: When interrupt request is generated	R\
		VW1C3	Comparator 1 signal monitor flag ^(2, 5)	0: VCMP1 < reference voltage 1: VCMP1 ≥ reference voltage or comparator 1 circuit disabled	R
		VW1F0	Sampling clock select bits	^{b5 b4} 0 0: fOCO-S divided by 1 0 1: fOCO-S divided by 2	RV
		VW1F1		1 0: fOCO-S divided by 4 1 1: fOCO-S divided by 8	RV
		VW1C6	Reserved bit	Set to 0.	RV
		VW1C7	Comparator 1 interrupt generation condition select bit ⁽⁷⁾	0: When VCMP1 reaches reference voltage or above 1: When VCMP1 reaches reference voltage or below	RV

VW1C register.

2. Bits VW1C2 and VW1C3 remain unchanged after a softw are reset or w atchdog timer reset.

3. The VW1C0 is enabled when the VCA26 bit in the VCA2 register is set to 1 (comparator 1 circuit enabled). When the VCA26 bit is set to 0 (comparator 1 circuit disabled), set the VW1C0 bit to 0 (disable). To set the VW1C0 bit to 1 (enable), follow the procedure show n in Table 7.3 Procedure for Setting Bits Associated with Comparator 1 Interrupt.

- 4. To use the comparator 1 interrupt to exit stop mode and to return again, write 1 to the VW1C1 bit after writing 0.
- 5. Bits VW1C2 and VW1C3 are enabled when the VCA26 bit in the VCA2 register is set to 1 (comparator 1 circuit enabled).

6. Set this bit to 0 by a program. When 0 is written by a program, it is set to 0 (and remains unchanged even if 1 is w ritten to it).

7. The VW1C7 bit is enabled when the VCAC1 bit in the VCAC register is set to 0 (one edge). Set the VW1C7 bit after setting the VCAC1 bit to 0.


b7 b6 b5 b4 b	b3 b2 b1 b0	Symbol VW2C	Address 0037h	After Reset ⁽²⁾ 00000010b	
		Bit Symbol	Bit Name	Function	RW
		VW2C0	Comparator 2 interrupt enable bit ⁽³⁾	0: Disable 1: Enable	RW
		VW2C1	Comparator 2 digital filter disable mode select bit ⁽⁴⁾	0: Digital filter enabled mode (digital filter circuit enabled) 1: Digital filter disabled mode (digital filter circuit disabled)	RW
		VW2C2	Comparator 2 interrupt flag ^(2, 5, 6)	[Source for setting this bit to 0] 0: Write 0 [Source for setting this bit to 0] 1: When interrupt request is generated	RW
		VW2C3	WDT detection flag ^(2, 6)	0: Not detected 1: Detected	RW
		VW2F0	Sampling clock select bits	^{b5 b4} 0 0: fOCO-S divided by 1 0 1: fOCO-S divided by 2	RW
		VW2F1		1 0: fOCO-S divided by 4 1 1: fOCO-S divided by 8	RW
		VW2C6	Reserved bit	Set to 0.	RW
		VW2C7	Comparator 2 interrupt generation condition select bit ⁽⁷⁾	 0: When VCMP2 reaches reference voltage or above 1: When VCMP2 reaches reference voltage or below 	RW

NOTES:

 Set the PRC3 bit in the PRCR register to 1 (w rite enabled) before rew riting the VW2C register. When the VW2C register is rew ritten, the VW2C2 bit may be set to 1. Set the VW2C2 bit to 0 after rew riting the VW2C register.

2. Bits VW2C2 and VW2C3 remain unchanged after a software reset or watchdog timer reset.

The VW2C0 bit is enabled when the VCA27 bit in the VCA2 register is set to 1 (comparator 2 circuit enabled). Set the VW2C0 bit to 0 (disable) when the VCA27 bit is set to 0 (comparator 2 circuit disabled). To set the VW2C0 bit to 1 (enable), follow the procedure show n in Table 7.4 Procedure for Setting Bits Associated with Comparator 2 Interrupt.

- 4. To use the comparator 2 interrupt to exit stop mode and to return again, write 1 to the VW2C1 bit after writing 0.
- 5. The VW2C2 is enabled when the VCA27 bit in the VCA2 register is set to 1 (comparator 2 circuit enabled).
- 6. Set this bit to 0 by a program. When 0 is written by a program, it is set to 0 (and remains unchanged even if 1 is written to it).
- 7. The VW2C7 bit is enabled when the VCAC2 bit in the VCAC register is set to 0 (one edge). Set the VW2C7 bit after setting the VCAC2 bit to 0.







b7 b6 b	5 b4 b3 b2 b1 b0) 7			
XX		Symbol	Address	After Reset	
		ALCMR	003Ch	00h	
		Bit Symbol	Bit Name	Function	RW
		LCM1POR	VCOUT1 output polarity select bit	 Non-inverted comparator 1 comparison result is output to VCOUT1 Inverted comparator 1 comparison result is output to VCOUT1 	RW
		LCM2POR	VCOUT2 output polarity select bit	0: Non-inverted comparator 2 comparison result is output to VCOUT21: Inverted comparator 2 comparison result is output to VCOUT2	RW
		CM10E	VCOUT1 output enable bit	0: Output disabled 1: Output enabled	RW
		CM2OE	VCOUT2 output enable bit	0: Output disabled 1: Output enabled	RW
		IRQ1SEL	Comparator 1 interrupt type select bit	0: Non-maskable interrupt 1: Maskable interrupt	RW
		IRQ2SEL	Comparator 2 interrupt type select bit	0: Non-maskable interrupt 1: Maskable interrupt	RW
\square		 (b7-b6)	Nothing is assigned. If necessar When read, the content is 0.	y, set to 0.	1-

Figure 7.7 ALCMR Register



7. Comparator







Figure 7.9 BGRCR Register



Figure 7.10 BGRTRM Register



Figure 7.11 PINSR4 Register

7.3 Monitoring Comparison Results

7.3.1 Monitoring Comparator 1

After the following settings are made, the comparison result of comparator 1 can be monitored by the VW1C3 bit in the VW1C register after td(E-A) has elapsed (refer to **22. Electrical Characteristics**).

- (1) Set the COMPSEL bit in the PINSR4 register is set to 1 (comparator 1, comparator 2).
- (2) Set the VCAB5 bit in the VCAB register to 1 (VCMP1 pin input voltage).
- (3) Set the VCA26 bit in the VCA2 register to 1 (comparator 1 circuit enabled).

7.3.2 Monitoring Comparator 2

After the following settings are made, the comparison result of comparator 2 can be monitored by the VCA13 bit in the VCA1 register after td(E-A) has elapsed (refer to **22. Electrical Characteristics**).

- (1) Set the COMPSEL bit in the PINSR4 register to 1 (comparator 1, comparator 2).
- (2) Set the VCAB6 bit in the VCAB register to 1 (VCMP2 pin input voltage).
- (3) Set the VCA27 bit in the VCA2 register to 1 (comparator 2 circuit enabled).

7.4 Functional Description

Comparator 1 and comparator 2 operate independently.

The comparison result of the reference input voltage and analog input voltage can be read by software. The result can also be output from the VCOUTi (i = 1 or 2) pin. An internal reference voltage or input voltage to the CVREF pin can be selected as the reference input voltage. The comparator 1 interrupt or the comparator 2 interrupt also can be used by selecting non-maskable or maskable for each interrupt.

7.4.1 Comparator 1

Table 7.3 lists the Procedure for Setting Bits Associated with Comparator 1 Interrupt, Figure 7.12 shows an Operating Example of Comparator 1 (When Digital Filter Enabled), and Figure 7.13 shows an Operating Example of Comparator 1 (When Digital Filter Disabled).

Table 7.3	Procedure for Setting Bits Associated with Comparator 1 Interrupt
-----------	---

Step	When Using Digital Filter	When Not Using Digital Filter				
1	Set the COMPSEL bit in the PINSR4 register to 1 (comparator 1, comparator 2)					
2	Set the VCAB5 bit in the VCAB register to 1 (VCMP1 pin input voltage)					
3	Set the VCA26 bit in the VCA2 register to	1 (comparator 1 circuit enabled)				
4	Wait for td(E-A)					
5	Select the interrupt type by the IRQ1SEL t	bit in the ALCMR register				
6	Select the sampling clock by bits VW1F0	Set the VW1C1 bit in the VW1C register to 1 (digital				
	and VW1F1 in the VW1C register	filter disabled)				
7(1)	Set the VW1C1 bit in the VW1C register	-				
	to 0 (digital filter enabled)					
8	Select the interrupt request timing by the VCAC1 bit in the VCAC register and the VW1C7 bit in					
	the VW1C register					
9	Set the VW1C2 bit in the VW1C register to 0					
10	Set the CM14 bit in the CM1 register to 0	_				
	(low-speed on-chip oscillator on)					
11	Wait for 2 cycles of the sampling clock of	 – (No wait time required) 				
	the digital filter.					
12	Set the VW1C0 bit in the VW1C register to	1 (comparator 1 interrupt enabled)				

NOTE:

1. When the VW1C0 bit is set to 0, steps 6 and 7 can be executed at the same time (with one instruction)



Figure 7.12 Operating Example of Comparator 1 (When Digital Filter Enabled)



7.4.2 Comparator 2

Table 7.4 lists the Procedure for Setting Bits Associated with Comparator 2 Interrupt, Figure 7.14 shows an Operating Example of Comparator 2 (When Digital Filter Enabled), and Figure 7.15 shows an Operating Example of Comparator 2 (When Digital Filter Disabled).

Table 7.4	Procedure for Setting Bits Associated with Comparator 2 Interrupt
-----------	---

Step	When Using Digital Filter	When Not Using Digital Filter				
1	Set the COMPSEL bit in the PINSR4 register to 1 (comparator 1, comparator 2)					
2	Set the VCAB6 bit in the VCAB register to 1 (VCMP2 pin input voltage)					
3	Set the VCA27 bit in the VCA2 register to 1 (comparator 2 circuit enabled)					
4	Wait for td(E-A)					
5	Select the interrupt type by the IRQ2SEL t	bit in the ALCMR register				
6	Select the sampling clock by bits VW2F0	Set the VW2C1 bit in the VW2C register to 1 (digital				
0	and VW2F1 in the VW2C register	filter disabled)				
7(1)	Set the VW2C1 bit in the VW2C register	-				
7	to 0 (digital filter enabled)					
8	Select the interrupt request timing by the VCAC2 bit in the VCAC register and the VW2C7 bit in					
0	the VW2C register					
9	Set the VW2C2 bit in the VW2C register to 0					
10	Set the CM14 bit in the CM1 register to 0	-				
10	(low-speed on-chip oscillator on)					
11	Wait for 2 cycles of the sampling clock of	 – (No wait time required) 				
11	the digital filter.					
12	Set the VW2C0 bit in the VW2C register to	o 1 (comparator 2 interrupt enabled)				

NOTE:

1. When the VW2C0 bit is set to 0, steps 6 and 7 can be executed at the same time (with one instruction).





Figure 7.15

7.5 Comparator 1 and Comparator 2 Interrupts

Two interrupt requests are generated, one each for comparator 1 and comparator 2. Non-maskable or maskable can be selected for each interrupt type. Refer to **13. Interrupts** for interrupts.

7.5.1 Non-Maskable Interrupts

When IRQiSEL (i = 1 or 2) bit in the ALCMR register is set to 0, the comparator i interrupt functions as a nonmaskable interrupt. When the selected interrupt request timing occurs, the VWiC2 bit in the VWiC register is set to 1. At this time, a non-maskable interrupt request for comparator i is generated.

7.5.2 Maskable Interrupts

When the IRQiSEL (i = 1 or 2) bit in the ALCMR register is set to 1, the comparator i interrupt functions as a maskable interrupt. The comparator i interrupt uses the single VCMPiIC register (bits IR and ILVL0 to ILVL2) and a single vector. When the selected interrupt request timing occurs, the VWiC2 bit in the VWiC register is set to 1. At this time, the IR bit in the VCMPiIC register is set to 1 (interrupt requested).

Refer to **13.1.6 Interrupt Control** for the VCMPiIC register and **13.1.5.2 Relocatable Vector Tables** for interrupt vectors.

7.6 Adjusting Internal Reference Voltage (Vref)

The level of the internal reference voltage (Vref) can be adjusted with the value of the BGRTRM register. The values for correcting the Vref are stored in registers BGRTRMA and BGRTRMB before shipping the MCU. The value of the BGRTRMA register is the same as that of the BGRTRM register after reset.

To use separate correction values to match the supply voltage ranges, transfer them from registers BGRTRMA and BGRTRMB to the BGRTRM register. Figure 7.16 shows the Procedure for Adjusting Internal Reference Voltage (Vref).

When the BGRCR0 bit in the BGRCR register to 1 (disabled), the internal reference voltage (Vref) adjustment circuit (BGR trimming circuit) is disabled and the value of the BGRTRM register is also disabled.

When the BGR trimming circuit is disabled, the accuracy of the internal reference voltage (Vref) is not guaranteed. Disable voltage detection circuits 0 to 2 and disable comparators 1 and 2 with the internal reference voltage selected. The high-speed on-chip oscillator should also be stopped as necessary because the precision of its oscillation frequency is not also guaranteed.



Figure 7.16 Procedure for Adjusting Internal Reference Voltage (Vref)



Determining Supply Voltage)

8. I/O Ports

There are 27 I/O ports P0_4 to P0_7, P1, P3, P4_3, P4_5, P6_0, P6_3 to P6_6.

When the XCIN clock oscillation circuit is not used, P4_3 can be used as an I/O port and P4_4 can be used as an output port.

Table 8.1 lists an Overview of I/O Ports.

Ports	I/O	Type of Output	I/O Setting	Internal Pull-Up Resister
P0_4 to P0_7, P1, P3	I/O	CMOS3 State	Set per bit	Set every 4 bits ⁽¹⁾
P4_3	I/O	CMOS3 State	Set per bit	Set every bit ⁽²⁾
P4_4	Output	CMOS3 State	Set per bit ⁽³⁾	None
P4_5	I/O	CMOS3 State	Set per bit	Set every bit ⁽²⁾
P6_0, P6_3	I/O	CMOS3 State	Set per bit	Set every 2 bits ⁽²⁾
P6_4 to P6_6	I/O	CMOS3 State	Set per bit	Set every 3 bits ⁽²⁾

Table 8.1 Overview of I/O Ports

NOTES:

- 1. In input mode, whether an internal pull-up resistor is connected or not can be selected by PUR0 register.
- 2. In input mode, whether an internal pull-up resistor is connected or not can be selected by PUR1 register.
- 3. Do not use port P4_4 as an input port (input mode).

8.1 Functions of I/O Ports

The PDi_j (j = 0 to 7) bit in the PDi (i = 0, 1, 3, 4, 6) register controls I/O of the ports P0_4 to P0_7, P1, P3, P4_3 to P4_5, P6_0, P6_3 to P6_6. The Pi register consists of a port latch to hold output data and a circuit to read pin states.

Figures 8.1 to 8.3 show the Configurations of I/O Ports. Table 8.2 lists the Functions of I/O Ports. Also, Figure 8.5 shows the PDi (i = 0, 1, 3, 4, or 6) Register. Figure 8.6 shows the Pi (i = 0, 1, 3, 4, or 6) Register, Figure 8.7 shows Registers PINSR2, PINSR3, and PINSR4, Figure 8.8 shows the PMR Register, Figure 8.9 shows Registers PUR0 and PUR1.

Operation When	Value of PDi_j B	it in PDi Register ⁽¹⁾
Accessing Pi Register	When PDi_j Bit is Set to 0 (Input Mode)	When PDi_j Bit is Set to 1 (Output Mode)
Reading	Read pin input level	Read the port latch
Writing	Write to the port latch	Write to the port latch. The value written to the port latch is output from the pin.

i = 0, 1, 3, 4, 6, j = 0 to 7

NOTE:

^{1.} Nothing is assigned to bits PD0_0 to PD0_3, PD4_0 to PD4_2, PD4_6, PD4_7, PD6_1, PD6_2, PD6_7.

8.2 Effect on Peripheral Functions

I/O ports function as I/O ports for peripheral functions (refer to **Table 1.3 Pin Name Information by Pin Number**).

Table 8.3 lists the Setting of PDi_j Bit when Functioning as I/O Ports for Peripheral Functions (i = 0, 1, 3, 4, 6, j = 0 to 7). Refer to the description of each function for information on how to set peripheral functions.

 Table 8.3
 Setting of PDi_j Bit when Functioning as I/O Ports for Peripheral Functions (i = 0, 1, 3, 4, 6, j = 0 to 7)

I/O of Peripheral Functions	PDi_j Bit Settings for Shared Pin Functions ⁽¹⁾
Input	Set this bit to 0 (input mode).
Output	This bit can be set to either 0 or 1 (output regardless of the port setting)

NOTE:

1. Nothing is assigned to bits PD0_0 to PD0_3, PD4_0 to PD4_2, PD4_6, PD4_7, PD6_1, PD6_2, PD6_7.

8.3 Pins Other than Programmable I/O Ports

Figure 8.4 shows the Configuration of I/O Pins.



Figure 8.1 Configuration of I/O Ports (1)













 Bits PD4_0 to PD4_2, PD4_6, and PD4_7 in the PD4 register are unavailable on this MCU. If it is necessary to set bits PD4_0 to PD4_2, PD4_6, and PD4_7, set to 0 (input mode). When read, the content is 0. To use port P4_4 as an output port, set the PD4_4 bit to 1 (output mode). Do not use port P4_4 as an input port.

Bits PD6_1, PD6_2, and PD6_7 in the PD6 register are unavailable on this MCU.
 If it is necessary to set bits PD6_1, PD6_2, and PD6_7, set to 0 (input mode). When read, the content is 0.





o7 b6 b5 b4 b3 b2 b1 b0	2			
	Symbol PINSR2	Address 00F6h	After Reset 00h	
	Bit Symbol	Bit Name	Function	RW
	(b3-b0)	Nothing is assigned. If necessa When read, the content is 0.	ry, set to 0.	_
	TRAOSEL	TRAO pin select bit	0 : P3_0 1 : P3_7	RW
	(b5)	Nothing is assigned. If necessa When read, the content is 0.		_
	TRBOSEL	TRBO pin select bit	0 : P3_1 1 : P1_3	RW
	(b7)	Nothing is assigned. If necessa When read, the content is 0.	ry, set to 0.	—
n Select Register	3			
57 b6 b5 b4 b3 b2 b1 b0	5			
	Symbol PINSR3	Address 00F7h	After Reset 00h	
	Bit Symbol	Bit Name	Function	RW
	 (b4-b0)	Nothing is assigned. If necessa When read, the content is 0.	-	_
	TREOSEL	1	: P6_0 : P0_4	RW
	 (b7-b6)	Nothing is assigned. If necessa When read, the content is 0.	ry, set to 0.	_
n Select Register	4			
0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	Symbol	Address	After Reset	
	PINSR4	02FBh	00h	
	Bit Symbol	Bit Name	Function	RW
	TRFOSEL	TRFO11 pin select bit	0 : P3_4 1 : P3_7	RW
	COMPSEL	Voltage monitor/comparator select bit	0 : Voltage monitor 1, voltage monitor 2 1 : Comparator 1, comparator 2	RW
	KIOSEL	KIO pin select bit	0 : P1_0 1 : P0_7	RW
		KIT pin select bit	0 : P1_1 1 : P6_6	RW
	KI1SEL			
	KI1SEL (b6-b4)	Reserved bits TREO pin select 2 bit	Set to 0. 0 : TREOSEL bit in PINSR3 register enabled	RW

Figure 8.7 Registers PINSR2, PINSR3, and PINSR4









8.4 Port Setting

Table 8.4 to Table 8.33 list the port setting.

Table 8.4 Port P0_4/(TREO)

Register	PD0	PINSR4	PINSR3	TRECR1	Function
Bit	PD0_4	TREOSEL2	TREOSEL	TOENA	runcion
Cotting	0	Other than 011b			Input port ⁽¹⁾
Setting value	1		Output port		
	Х	0	1	1	TREO output

X: 0 or 1

NOTE:

1. Pulled up by setting the PU01 bit in the PUR0 register to 1.

Table 8.5 Port P0_5

Register	PD0	Function
Bit	PD0_5	T unction
Setting	0	Input port ⁽¹⁾
value	1	Output port

NOTE:

1. Pulled up by setting the PU01 bit in the PUR0 register to 1.

Table 8.6 Port P0_6/INT4

Register	PD0	INTEN2	Function			
Bit	PD0_6	INT4EN	Function			
	0	0	Input port ⁽¹⁾			
Setting value	1	0	Output port			
value	0	1	INT4 input ⁽¹⁾			

NOTE:

1. Pulled up by setting the PU01 bit in the PUR0 register to 1.

Table 8.7 Port P0_7/(KI0)

Register	PD0	PINSR4	KIEN	Function	
Bit	PD0_7	KIOSEL	KI0EN	Function	
	0	Х	0	Input port ⁽¹⁾	
Setting value	1	Х	0	Output port	
value	0	1	1	KI0 input ⁽¹⁾	

X: 0 or 1 NOTE:

1. Pulled up by setting the PU01 bit in the PUR0 register to 1.

Register	PD1	TRFOUT	PINSR4	KIEN	VCAB	Function	
Bit	PD1_0	TRFOUT0	KIOSEL	KI0EN	VCAB5	Function	
	0	0	Х	0	0	Input port ⁽¹⁾	
	1	0	Х	0	0	Output port	
Setting value	Х	1	Х	0	0	TRFO00 output	
value	0	0	0	1	0	KI0 input ⁽¹⁾	
	0	0	Х	0	1	VCMP1 input ⁽¹⁾	

Table 8.8 Port P1_0/KI0/TRFO00/VCMP1

X: 0 or 1

NOTE:

1. Pulled up by setting the PU02 bit in the PUR0 register to 1.

Table 8.9 Port P1_1/KI1/TRF001/VCMP2

Register	PD1	TRFOUT	PINSR4	KIEN	VCAB	Function	
Bit	PD1_1	TRFOUT1	KI1SEL	KI1EN	VCAB6	T difetion	
	0	0	Х	0	0	Input port ⁽¹⁾ Output port	
	1	0	Х	0	0		
Setting value	Х	1	Х	0	0	TRFO01 output	
value	0	0	0	1	0	KI1 input ⁽¹⁾	
	0	0	Х	0	1	VCMP2 input ⁽¹⁾	

X: 0 or 1 NOTE:

1. Pulled up by setting the PU02 bit in the PUR0 register to 1.

Table 8.10 Port P1_2/KI2/TRFO02/CVREF

Register	PD1	TRFOUT	KIEN	VCAB	Function	
Bit	PD1_2	TRFOUT2	KI2EN	VCAB7	Function	
	0	0	0	0	Input port ⁽¹⁾	
	1	0	0	0	Output port	
Setting value	Х	1	0	0	TRFO02 output	
value	0	0	1	0	KI2 input ⁽¹⁾	
	0	0	0	1	CVREF input ⁽¹⁾	

X: 0 or 1 NOTE:

1. Pulled up by setting the PU02 bit in the PUR0 register to 1.

Register	PD1	Timer RB Setting	KIEN	ALCMR	Function
Bit	PD1_3	_	KI3EN	CM10E	Tunction
	0	Other than TRBO usage conditions	0	0	Input port ⁽¹⁾
0.111	1	Other than TRBO usage conditions	0	0	Output port
Setting value	0	Other than TRBO usage conditions	1	0	KI3 input ⁽¹⁾
X		Refer to Table 8.12 TRBO Pin Setting	0	0	TRBO output
	Х	Other than TRBO usage conditions	0	1	VCOUT1 output

Table 8.11 Port P1_3/KI3/VCOUT1/(TRBO)

X: 0 or 1 NOTE:

1. Pulled up by setting the PU02 bit in the PUR0 register to 1.

Table 8.12 TRBO Pin Setting

Register	PINSR2	TRBIOC	TRBMR		Function		
Bit	TRBOSEL	TOCNT ⁽¹⁾	TMOD1	TMOD0	Function		
	1	0	0	1	Programmable waveform generation mode		
	1	0	1	0	Programmable one-shot generation mode		
Setting	1	0	1	1	Programmable wait one-shot generation mode		
value	alue 1 1 0		1	P1_3 output port			
	Other than above			Other than TRBO usage conditions			

NOTE:

1. Set the TOCNT bit in the TRBIOC register to 0 in modes except for programmable waveform generation mode.

Table 8.13 Port P1_4/TXD0

Register	PD1		U0MR		Function		
Bit	PD1_4	SMD2	SMD1	SMD0	Function		
	0	0	0	0	Input port ⁽¹⁾		
	1	0	0	0	Output port		
Setting		0		1			
value	х		0	0	TXD0 output ⁽²⁾		
^	~	1		1			
			1	0			

X: 0 or 1

NOTES:

1. Pulled up by setting the PU03 bit in the PUR0 register to 1.

2. N-channel open-drain output by setting the NCH bit in the U0C0 register to 1.

Register	PD1	TR	AIOC		TRAMR		PMR	INTEN	Function
Bit	PD1_5	TIOSEL	TOPCR ⁽²⁾	TMOD2	TMOD1	TMOD0	INT1SEL	INT1EN	Function
		0	Х	Х	Х	Х			
	0	1	1	0	0	1	Х	0	Input port ⁽¹⁾
		1	0	0	0	0			
	1	0	Х	Х	Х	Х	x	0	Output port
		1	0	0	0	0	^	Ū	output port
Setting	0	0	Х	Х	Х	Х	v	0	RXD0 input ⁽¹⁾
value	0	1	0	Ot	her than 00	1b	X	0	
	0	1	0	0	0	0	0	1	$\overline{\mathbf{NT4}}$ is $\mathbf{nut}(1)$
	0	1	1	0	0	1	0	Ι	INT1 input ⁽¹⁾
	0	1	0	Other	than 000b,	, 001b	Х	Х	TRAIO input ⁽¹⁾
	0	1	0	Other	than 000b	,001b	0	1	TRAIO input/INT1 input ⁽¹⁾
	Х	1	0	0	0	1	Х	Х	TRAIO output

Table 8.14 Port P1_5/RXD0/(TRAIO)/(INT1)

X: 0 or 1 NOTES:

1. Pulled up by setting the PU03 bit in the PUR0 register to 1.

2. Set the TOPCR bit in the TRAIOC register to 0 in modes except for pulse output mode.

Table 8.15 Port P1_6/CLK0/VCOUT2

Register	PD1	ALCMR		U0	Function		
Bit	PD1_6	CM2OE	CKDIR	SMD2	SMD1	Function	
	0	0	0	(Other than 001	C	Input port ⁽¹⁾
	0	0	1	Х	Х	Х	
Setting	1	0	Х	(Other than 001	C	Output port
value	Х	0	0	0	0	1	CLK0 output
	0	0	1	X X X			CLK0 input ⁽¹⁾
	Х	1	Х	Х	Х	Х	VCOUT2 output

X: 0 or 1

NOTE:

1. Pulled up by setting the PU03 bit in the PUR0 register to 1.

Table 8.16 Port P1_7/TRAIO/INT1

Register	PD1	TRA	AIOC		TRAMR			INTEN	Function	
Bit	PD1_7	TIOSEL	TOPCR ⁽²⁾	TMOD2	TMOD1	TMOD0	INT1SEL	INT1EN	Function	
		1	Х	Х	Х	Х				
	0	0	1	0	0	1	Х	0	Input port ⁽¹⁾	
		0	0	0	0	0				
0.00	1	1	Х	Х	Х	Х	х	0	Output port	
Setting value	•	0	0	0	0	0	~			
value	0	0	0	0	0	0	0	1		
	0	0	1	0	0	1	U	Ι	INT1 input ⁽¹⁾	
	0	0	0	Other	than 000b,	001b	Х	Х	TRAIO input ⁽¹⁾	
	0	0	0	Other	than 000b,	001b	0	1	TRAIO input/INT1 input ⁽¹⁾	
	Х	0	0	0	0	1	Х	Х	TRAIO output	

X: 0 or 1 NOTES:

1. Pulled up by setting the PU03 bit in the PUR0 register to 1.

2. Set the TOPCR bit in the TRAIOC register to 0 in modes except for pulse output mode.

Table 8.17Port P3_0/TRAO

Register	PD3	PINSR2	TRAIOC	Function	
Bit	PD3_0	TRAOSEL	TOENA	FullCuoli	
Cotting	0	Х	0	Input port ⁽¹⁾	
Setting value	1	Х	0	Output port	
value	Х	0	1	TRAO output	

X: 0 or 1 NOTE:

1. Pulled up by setting the PU06 bit in the PUR0 register to 1.

Table 8.18 Port P3_1/TRBO

Register	PD3	Timer RB Setting	Function	
Bit	PD3_1	_	runcuon	
Cotting	0	Other than TRBO usage conditions	Input port ⁽¹⁾	
value	Setting 1 Other than TRBO usage conditions		Output port	
Value	X Refer to Table 8.19 TRBO Pin Setting		TRBO output	

X: 0 or 1 NOTE:

1. Pulled up by setting the PU06 bit in the PUR0 register to 1.

Table 8.19 TRBO Pin Setting

Register	PINSR2	TRBIOC	TRBMR		Function
Bit	TRBOSEL	TOCNT ⁽¹⁾	TMOD1	TMOD0	Function
	0	0	0	1	Programmable waveform generation mode
o. #:	0	0	1	0	Programmable one-shot generation mode
Setting value	0	0	1	1	Programmable wait one-shot generation mode
value	0	1	0	1	P3_1 output port
		Other that	an above		Other than TRBO usage conditions

NOTE:

1. Set the TOCNT bit in the TRBIOC register to 0 in modes except for programmable waveform generation mode.

Table 8.20 Port P3_2/INT2

Register	PD3	INTEN	Function	
Bit	PD3_2	INT2EN	Function	
0	0	0	Input port ⁽¹⁾	
Setting value	1	0	Output port	
value	0	1	INT2 input	

NOTE:

1. Pulled up by setting the PU06 bit in the PUR0 register to 1.

Table 8.21 Port P3_3/TRFO10/TRFI

Register	PD3	TRFOUT	Function	
Bit	PD3_3	TRFOUT3	Function	
	0	0	Input port ⁽¹⁾	
Setting	1	0	Output port	
value	Х	1	TRFO10 output	
	0	0	TRFI input ⁽¹⁾	

X: 0 or 1 NOTE:

1. Pulled up by setting the PU06 bit in the PUR0 register to 1.

Table 8.22Port P3_4/TRF011

Register	PD3	PINSR4	TRFOUT	Function	
Bit	PD3_4	TRFOSEL	TRFOUT4	Function	
Cotting	0	Х	0	Input port ⁽¹⁾	
Setting value	1	Х	0	Output port	
Value	Х	0	1	TRFO11 output	

X: 0 or 1 NOTE:

1. Pulled up by setting the PU07 bit in the PUR0 register to 1.

Table 8.23 Port P3_5/TRFO12

Register	PD3	TRFOUT	Function
Bit	PD3_5	TRFOUT5	
Catting	0	0	Input port ⁽¹⁾
Setting value	1	0	Output port
Value	Х	1	TRFO12 output

X: 0 or 1 NOTE:

1. Pulled up by setting the PU07 bit in the PUR0 register to 1.

Table 8.24 Port P3_6/(INT1)

Register	PD3	PMR	INTEN	Function	
Bit	PD3_6	INT1SEL	INT1EN	Function	
Catting	0	Х	0	Input port ⁽¹⁾	
Setting value	1	Х	0	Output port	
Value	0	1	1	INT1 input ⁽¹⁾	

X: 0 or 1 NOTE:

1. Pulled up by setting the PU07 bit in the PUR0 register to 1.

Table 8.25 Port P3_7/(TRAO)/(TRFO11)

Register	PD3	PINSR2	TRAIOC	PINSR4	TRFOUT	Function
Bit	PD3_7	TRAOSEL	TOENA	TRFOSEL	TRFOUT4	T uncuon
	0	Х	0	Х	0	Input port ⁽¹⁾
Setting	1	Х	0	Х	0	Output port
value	Х	1	1	Х	0	TRAO output
	Х	Х	0	1	1	TRFO11 output

X: 0 or 1

NOTE:

1. Pulled up by setting the PU07 bit in the PUR0 register to 1.

Table 8.26 Po	ort P4_3/(XCIN)
---------------	-----------------

Register	PD4	CM0	C	M1	Circuit specifications				
Bit	PD4_3	CM04	CM10	CM12	Oscillation buffer	Feedback resistor	Function		
	0	0	Х	Х	OFF	OFF	Input port ^(1, 2)		
	1	0	Х	Х	OFF	OFF	Output port ⁽²⁾		
	Х	1	0	0	ON	ON	XCIN clock oscillation (on-chip feedback resistor enabled)		
Setting value	Х	1	0	1	ON	OFF	XCIN clock oscillation (on-chip feedback resistor disabled)		
	х	1 1	1 1	1 1	1 1	0	OFF	ON	XCIN clock oscillation stop
	^		1	1	OFF	OFF	ACIN CLOCK OSCILLATION STOP		
х	1	0	0	ON	ON	External XCIN clock input			
	~		0	1	ON	OFF			

X: 0 or 1 NOTES:

1. Pulled up by setting the PU10 bit in the PUR1 register to 1.

2. Refer to 8.6.1 Port P4_3, P4_4.

Table 8.27 Port P4_4/(XCOUT)

Register	PD4	CM0	CM1		Circuit specifications		
Bit	PD4_4	CM04	CM10	CM12	Oscillation buffer	Feedback resistor	Function
	1	0	Х	Х	OFF	OFF	Output port ⁽¹⁾
	Х	1	0	0	ON	ON	XCIN clock oscillation (on-chip feedback resistor enabled)
Setting value	Х	1	0	1	ON	OFF	XCIN clock oscillation (on-chip feedback resistor disabled)
value	х	1 1	× 1 1	0	OFF	ON	XCIN clock oscillation stop
	~	1	1	1	OFF	OFF	ACIN CIOCK OSCIIIATION STOP
	х	1	0	0	ON	ON	External XCOUT clock output (inverted
	~	I	0	1	ON	OFF	output of XCIN clock)

X: 0 or 1

NOTE:

1. Refer to 8.6.1 Port P4_3, P4_4.

Table 8.28 Port P4_5/INT0

Register	PD4	INTEN	Function
Bit	PD4_5	INT0EN	Function
o #	0	0	Input port ⁽¹⁾
Setting value	1	0	Output port
value	0	1	INT0 input

NOTE:

1. Pulled up by setting the PU11 bit in the PUR1 register to 1.

Table 8.29Port P6_0/TREO

Register	PD6	PINSR4	PINSR3	TRECR1	Function
Bit	PD6_0	TREOSEL2	TREOSEL	TOENA	runction
Cotting	0			Input port ⁽¹⁾	
Setting value	1		Output port		
talde	Х	0	0	1	TREO output

X: 0 or 1 NOTE:

1. Pulled up by setting the PU14 bit in the PUR1 register to 1.

Table 8.30 Port P6_3/TXD2

Register	PD6	U2MR			Function
Bit	PD6_3	SMD2	SMD1	SMD0	Function
	0	0	0	0	Input port ⁽¹⁾
	1	0	0	0	Output port
Setting value	×	0	0	1	
				0	TYD2 = utput(2)
		1		1	TXD2 output ⁽²⁾
			1	0	

X: 0 or 1 NOTES:

Pulled up by setting the PU14 bit in the PUR1 register to 1.

N-channel open-drain output by setting the NCH bit in the U2C0 register to 1.

Table 8.31 Port P6_4/RXD2

Register	PD6	- Function	
Bit	PD6_4		
Catting	0	Input port ⁽¹⁾	
Setting value	1	Output port	
value	0	RXD2 input ⁽¹⁾	

NOTE:

1. Pulled up by setting the PU15 bit in the PUR1 register to 1.

Table 8.32Port P6_5/CLK2/(TREO)

Register	PD6	PINSR4	TRECR1	U2MR		Function		
Bit	PD6_5	TREOSEL2	TOENA	CKDIR	SMD2	SMD1	SMD0	runcuon
0		0 0		0	Other than 001b		loge the ent(1)	
	0	0 0	X	1	Х	Х	Х	Input port ⁽¹⁾
Setting	1	0	Х	Х	C	Other than 001	b	Output port
value	Х	0	Х	0	0	0	1	CLK2 output
	0	0	Х	1	Х	Х	Х	CLK2 input ⁽¹⁾
	Х	1	1	Х	Х	Х	Х	TREO output

X: 0 or 1

NOTE:

1. Pulled up by setting the PU15 bit in the PUR1 register to 1.

Table 8.33 Port P6_6/(KI1)

Register	PD6	PINSR4	INTEN	- Function	
Bit	PD6_6	KI1SEL	INT0EN	Function	
o	0	Х	0	Input port ⁽¹⁾	
Setting value	1	Х	0	Output port	
value	0	1	1	KI1 input ⁽¹⁾	

NOTE:

1. Pulled up by setting the PU15 bit in the PUR1 register to 1.

8.5 Unassigned Pin Handling

Table 8.34 lists Unassigned Pin Handling.

Table 8.34 Unassigned Pin Handling

Pin Name	Connection
Ports P0_4 to P0_7, P1, P3,	After setting to input mode, connect each pin to VSS via a resistor
P4_3 to P4_5, P6_0, P6_3 to P6_6	(pull-down) or connect each pin to VCC via a resistor (pull-up). ⁽²⁾
	 After setting to output mode, leave these pins open.^(1, 2)
RESET ⁽³⁾	Connect to VCC via a pull-up resistor ⁽²⁾

NOTES:

1. If these ports are set to output mode and left open, they remain in input mode until they are switched to output mode by a program. The voltage level of these pins may be undefined and the power current may increase while the ports remain in input mode.

The content of the direction registers may change due to noise or program runaway caused by noise. In order to enhance program reliability, the program should periodically repeat the setting of the direction registers.

- 2. Connect these unassigned pins to the MCU using the shortest wire length (2 cm or less) possible.
- 3. When the power-on reset function is in use.



Figure 8.10 Unassigned Pin Handling

8.6 Notes on I/O Ports

8.6.1 Port P4_3, P4_4

Ports P4_3 and P4_4 are also used as the XCIN function and the XCOUT function, respectively. During a reset period and after a reset release, these ports are set to the XCIN and XCOUT functions. Pins P4_3 and P4_4 can be switched to the port functions by setting the CM04 bit in the CM0 register to 0 (ports P4_3 and P4_4) by a program.

To use ports P4_3 and P4_4 as ports, note the following:

• Port P4_3

After a reset until the CM04 bit is set to 0 (ports P4_3 and P4_4) by a program, a typical 10 M Ω impedance is connected between the P4_3 pin and the MCU power supply or GND. If the XCIN is set to intermediate-level input or left floating, a shoot-through current flows into the oscillation driver.

• Port P4_4

Use port P4_4 as an output port by setting the PD4_4 bit in the PD4 register to 1 (output mode). After a reset until the CM04 bit is set to 0 (ports P4_3 and P4_4) by a program, the P4_4 pin may output an intermediate potential of about 2.0 V.

9. Processor Mode

9.1 Processor Modes

Single-chip mode can be selected as the processor mode.

Table 9.1 lists Features of Processor Mode. Figure 9.1 shows the PM0 Register and Figure 9.2 shows the PM1 Register.

Table 9.1 Features of Processor Mode

Processor Mode	Accessible Areas	Pins Assignable as I/O Port Pins
Single-chip mode	SFR, internal RAM, internal ROM	All pins are I/O ports or peripheral
		function I/O pins

Processor Mode Re	egister 0 ⁽¹⁾			
b7 b6 b5 b4 b3 b2 b1 b0	Symbol PM0	Address 0004h	After Reset 00h	
	Bit Symbol	Bit Name	Function	RW
	 (b2-b0)	Reserved bits	Set to 0.	RW
	PM03	Softw are reset bit	The MCU is reset when this bit is set to 1. When read, the content is 0.	RW
	 (b7-b4)	Nothing is assigned. If necessary, When read, the content is 0.	set to 0.	-





automatically set to 1.



10. Bus

The bus cycles differ when accessing ROM/RAM, and when accessing SFR.

Table 10.1 lists Bus Cycles by Access Space of the R8C/2G Group.

ROM/RAM and SFR are connected to the CPU by an 8-bit bus. When accessing in word (16-bit) units, these areas are accessed twice in 8-bit units.

Table 10.2 lists Access Units and Bus Operations.

Table 10.1	Bus Cycles by	/ Access Space	of the R8C/2G Group

Access Area	Bus Cycle
SFR	2 cycles of CPU clock
ROM/RAM	1 cycle of CPU clock

Table 10.2 Access Units and Bus Operations

Area	SFR	ROM, RAM
Even address Byte access	CPU clock	CPU Clock Address X Even X
	Data X Data X	Data X Data
Odd address Byte access	CPU Clock Address X Odd X Data X Data X	CPU clock Address X Odd X Data X Data
Even address Word access	CPU Clock	CPU Clock
	Address X Even X Even + 1 X	Address X Even X Even + 1 X
	Data X Data X Data X	Data
Odd address Word access		CPU Clock
	Address X Odd X Odd + 1 X	Address X Odd X Odd + 1 X
	Data X Data X Data X	Data X Data X Data X
11. Clock Generation Circuit

The clock generation circuit has:

- XCIN clock oscillation circuit
- Low-speed on-chip oscillator
- High-speed on-chip oscillator

Table 11.1 lists Specifications of Clock Generation Circuit. Figure 11.1 shows a Clock Generation Circuit. Figures 11.2 to 11.8 show clock associated registers. Figure 11.9 shows a Handling Procedure of Internal Power Low Consumption Using VCA20 Bit.

ltom	XCIN Clock Oscillation Circuit	On-Chip	Oscillator
Item		High-Speed On-Chip Oscillator	Low-Speed On-Chip Oscillator
Applications	CPU clock source Peripheral function clock source	CPU clock source Peripheral function clock source	CPU clock source Peripheral function clock source
Clock frequency	32.768 kHz	Approx. 8 MHz	Approx. 125 kHz
Connectable oscillator	Crystal oscillator	-	-
Oscillator connect pins	XCIN, XCOUT ⁽¹⁾	_(1)	_(1)
Oscillation stop, restart function	Usable	Usable	Usable
Oscillator status after reset	Oscillate	Stop	Oscillate
Others	 Externally generated clock can be input⁽²⁾ On-chip feedback resistor RfXCIN (connected/ not connected, selectable) 	_	_

Table 11.1 Specifications of Clock Generation Circuit

NOTES:

- 1. These pins can be used as P4_3 or P4_4 when using the on-chip oscillator clock as the CPU clock while the XCIN clock oscillation circuit is not used.
- 2. Set the CM04 bit in the CM0 register to 1 (XCIN-XCOUT pin) when an external clock is input.



Figure 11.1 Clock Generation Circuit

•	b3 b2 b1 b0	rol Registe	r 0 ⁽¹⁾		
0		Symbol CM0	Address 0006h	After Reset 01011000b	
		Bit Symbol	Bit Name	Function	RW
			lothing is assigned. If necessary, set to 0. Vhen read, the content is 0.		_
		(b1)	Reserved bit	Set to 0.	RW
		CM02	WAIT peripheral function clock stop bit	 0 : Peripheral function clock does not stop in w ait mode 1 : Peripheral function clock stops in w ait mode 	RW
		CM03	XCIN-XCOUT drive capacity select bit ⁽²⁾	0 : LOW 1 : HIGH	RW
		CM04	Port, XCIN-XCOUT switch bit ^(3, 4)	0 : Ports P4_3, P4_4 1 : XCIN-XCOUT pin	RW
		 (b5)	Nothing is assigned. If necessar When read, the content is 0.	y, set to 0.	_
		CM06	System clock division select bit $0^{(5)}$	0 : CM16, CM17 enabled 1 : Divide-by-8 mode	RW
		(b7)	Reserved bit	Set to 0.	RW

- 1. Set the PRC0 bit in the PRCR register to 1 (write enable) before rewriting the CM0 register.
- 2. When entering stop mode, the CM03 bit is set to 1 (HIGH). Rew rite the CM03 bit while the XCIN clock oscillation stabilizes.
- 3. P4_3 and P4_4 can be used as ports when the CM04 bit is set to 0 (ports P4_3 and P4_4). To use the XCIN clock, set the CM04 bit to 1 (XCIN-XCOUT pin). Also, set port P4_3 as input port without pull-up.
- 4. If the CM10 bit in the CM1 register is set to 1 (stop mode), when the CM04 bit is set to 1 (XCIN-XCOUT pin), the XCIN(P4_3) pin is set to the high-impedance state and the XCOUT (P4_4) pin is set to "H". When the CM04 bit is set to 0 (I/O ports P4_3 and P4_4), pins XCIN (P4_3) and XOUT (P4_4) retain the I/O status (status just before stop mode is entered).
- 5. When entering stop mode, the CM06 bit is set to 1 (divide-by-8 mode).

Figure 11.2 **CM0** Register

		Symbol	Address	After Reset	
		CM1	0007h	00h	
		Bit Symbol	Bit Name	Function	RV
		CM10	All clock stop control bit ^(2, 3, 4)	0 : Clock operates 1 : Stops all clocks (stop mode)	RV
		(b1)	Nothing is assigned. If necessary, se When read, the content is 0.	t to 0.	-
		CM12	XCIN-XCOUT on-chip feedback resistor select bit	0 : On-chip feedback resistor enabled 1 : On-chip feedback resistor disabled	RV
		(b3)	Nothing is assigned. If necessary, se When read, the content is 0.	t to 0.	-
╽╽╽└		CM14	Low -speed on-chip oscillation stop bit ^(4, 5, 6, 7)	0 : Low -speed on-chip oscillator on 1 : Low -speed on-chip oscillator off	RV
		(b5)	Nothing is assigned. If necessary, se When read, the content is 0.	t to 0.	-
		CM16	System clock division select bits 1 ⁽⁸⁾	^{b7 b6} 0 0 : No division mode 0 1 : Divide-by-2 mode	RV
		CM17		1 0 : Divide-by-4 mode 1 1 : Divide-by-16 mode	RV

- 3. If the CM10 bit is set to 1 (stop mode), when the CM04 bit in the CM0 register is set to 1 (XCIN-XCOUT pin), the XCIN(P4_3) pin is set to the high-impedance state and the XCOUT (P4_4) pin is set to "H". When the CM04 bit is set to 0 (I/O ports P4_3 and P4_4), pins XCIN (P4_3) and XOUT (P4_4) retain the I/O status (status just before stop mode is entered).
- 4. In count source protect mode enabled of w atchdog timer (refer to **16.2 Count Source Protection Mode Enabled**), the value remains unchanged even if bits CM10 and CM14 are set.
- 5. When the OCD2 bit in the OCD register is set to 0 (XCIN clock selected), the CM14 bit is set to 1 (low-speed on-chip oscillator off). When the OCD2 bit is set to 1 (on-chip oscillator clock selected), the CM14 bit is set to 0 (low-speed on-chip oscillator on). It remains unchanged even if 1 is written to it.
- 6. When using the voltage monitor 1 interrupt or voltage monitor 2 interrupt (when using the digital filter), set the CM14 bit to 0 (low-speed on-chip oscillator on).
- 7. In count source protect mode enabled, the CM14 bit is set to 0 (low-speed on-chip oscillator on). It remains unchanged even if 1 is w ritten to it.
- 8. When the CM06 bit in the CM0 register is set to 0 (bits CM16, CM17 enabled), bits CM16 to CM17 are enabled.

Figure 11.3 CM1 Register



oscillator clock selected).





- 2. Sw itching fOCO-fast mode 0 to fOCO-fast mode 2 multiplies the frequency by 0.5.
- 3. Set this bit not to exceed the maximum value of the system clock.

Figure 11.5 Registers HRA0, HRA1, and HRA2



Figure 11.6 CPSRF Register





b7 b6 b5		Register 2 ⁽¹)		
1 1 1 1	b4 b3 b2 b1 b0				
		Symbol	Address	After Reset ⁽⁵⁾ The LVD0ON bit in the OFS register is set to 1 and hardw are reset : 00h Pow er-on reset, voltage monitor 0 reset	
				or LVD0ON bit in the OFS register is	06
		VCA2 Bit Symbol	0032h Bit Name	set to 0, and hardw are reset : 0010000	RW
	L	VCA20	Internal pow er low consumption enable bit ⁽⁶⁾	0 : Low consumption disabled 1 : Low consumption enabled ⁽⁷⁾	RW
		 (b4-b1)	Reserved bits	Set to 0.	RW
		VCA25	Voltage detection 0 enable bit ⁽²⁾	0 : Voltage detection 0 circuit disabled 1 : Voltage detection 0 circuit enabled	RW
		VCA26	Voltage detection 1 enable bit ⁽³⁾	0 : Voltage detection 1 circuit disabled 1 : Voltage detection 1 circuit enabled	RW
		VCA27	Voltage detection 2 enable bit ⁽⁴⁾	0 : Voltage detection 2 circuit disabled 1 : Voltage detection 2 circuit enabled	RW
2. T A	Set the PRC3 To use the vo	ltage monitor () reset, set the VCA25 bit to 1	before rew riting to the VCA2 register. on circuit w aits for td(E-A) to elapse before starting	
3. T A	To use the vo	-		B bit in the VW1C register, set the VCA26 bit to 1. on circuit w aits for td(E-A) to elapse before starting	
A		-	•	bit in the VCA1 register, set the VCA27 bit to 1. on circuit waits for td(E-A) to elapse before starting	
	Softw are res egister.	et, w atchdog t	timer reset, voltage monitor 1	reset, and voltage monitor 2 reset do not affect this	
				et the VCA20 bit, follow the procedure show n in Fi nsumption Using VCA20 Bit.	gure
	When the VC mode).	A20 bit is set t	o 1 (low consumption enabled	d), do not set the CM10 bit in the CM1 register to 1 (s	top

Figure 11.8 VCA2 Register



The clocks generated by the clock generation circuits are described below.

11.1 On-Chip Oscillator Clocks

These clocks are supplied by the on-chip oscillators (high-speed on-chip oscillator and a low-speed on-chip oscillator). The on-chip oscillator clock is selected by the HRA01 bit in the HRA0 register.

11.1.1 Low-Speed On-Chip Oscillator Clock

The clock generated by the low-speed on-chip oscillator is used as the clock source for the CPU clock, peripheral function clock, fOCO, and fOCO-S.

After reset, the on-chip oscillator clock generated by the low-speed on-chip oscillator divided by 8 is selected as the CPU clock.

The frequency of the low-speed on-chip oscillator varies depending on the supply voltage and the operating ambient temperature. Application products must be designed with sufficient margin to allow for frequency changes.

11.1.2 High-Speed On-Chip Oscillator Clock

The clock generated by the high-speed on-chip oscillator is used as the clock source for the CPU clock, peripheral function clock, fOCO, and fOCO-F.

After reset, the on-chip oscillator clock generated by the high-speed on-chip oscillator stops. Oscillation is started by setting the HRA00 bit in the HRA0 register to 1 (high-speed on-chip oscillator on). The frequency can be adjusted by registers HRA1 and HRA2.

Furthermore, frequency correction data corresponding to the supply voltage ranges listed below is stored in registers FRA4 and FRA6. To use separate correction values to match these voltage ranges, transfer them from register FRA4 or FRA6 to the HRA1 register.

- FRA4 register: Stores data for frequency correction corresponding to VCC = 2.7 V to 5.5 V. (The value is the same as that of the HRA1 register after a reset.)
- FRA6 register: Stores data for frequency correction corresponding to VCC = 2.2 V to 5.5 V.

Since there are differences in the amount of frequency adjustment among the bits in the HRA1 register, make adjustments by changing the settings of individual bits. Adjust the HRA1 register so that the frequency of the high-speed on-chip oscillator clock does not exceed the maximum value of the system clock.

11.2 XCIN Clock

This clock is supplied by the XCIN clock oscillation circuit. This clock is used as the clock source for the CPU clock, peripheral function clock. The XCIN clock oscillation circuit is configured by connecting a resonator between the XCIN and XCOUT pins. The XCIN clock oscillation circuit includes an on-chip a feedback resistor, which is disconnected from the oscillation circuit in stop mode in order to reduce the amount of power consumed in the chip. The XCIN clock oscillation circuit may also be configured by feeding an externally generated clock to the XCIN pin.

Figure 11.10 shows Examples of XCIN Clock Connection Circuits.

During and after reset, the XCIN clock oscillates.

The XCIN clock starts oscillating when the CM04 bit in the CM0 register is set to 1 (XCIN-XCOUT pin).

To use the XCIN clock for the CPU clock source, set the OCD2 bit in the OCD register to 0 (selects XCIN clock) after the XCIN clock is oscillating stably.

This MCU has an on-chip feedback resistor and on-chip resistor disable/enable switching is possible by the CM12 bit in the CM1 register.

In stop mode, all clocks including the XCIN clock stop. Refer to 11.4 Power Control for details.



Figure 11.10 Examples of XCIN Clock Connection Circuits

11.3 CPU Clock and Peripheral Function Clock

There are a CPU clock to operate the CPU and a peripheral function clock to operate the peripheral functions. Refer to **Figure 11.1 Clock Generation Circuit**.

11.3.1 System Clock

The system clock is the clock source for the CPU and peripheral function clocks. Either the XCIN clock or the on-chip oscillator clock can be selected.

11.3.2 CPU Clock

The CPU clock is an operating clock for the CPU and watchdog timer.

The system clock can be divided by 1 (no division), 2, 4, 8, or 16 to produce the CPU clock. Use the CM06 bit in the CM0 register and bits CM16 to CM17 in the CM1 register to select the value of the division.

Use the XCIN clock while the XCIN clock oscillation stabilizes.

After reset, the low-speed on-chip oscillator clock divided by 8 provides the CPU clock.

When entering stop mode from high-speed clock mode, the CM06 bit is set to 1 (divide-by-8 mode).

11.3.3 Peripheral Function Clock (f1, f2, f4, f8, and f32)

The peripheral function clock is the operating clock for the peripheral functions.

The clock fi (i = 1, 2, 4, 8, and 32) is generated by the system clock divided by i. The clock fi is used for timers RA, RB, RE, and RF, and the serial interface.

When the WAIT instruction is executed after setting the CM02 bit in the CM0 register to 1 (peripheral function clock stops in wait mode), the clock fi stop.

11.3.4 fOCO

fOCO is an operating clock for the peripheral functions.

fOCO runs at the same frequency as the on-chip oscillator clock and can be used as the source for timer RA. When the WAIT instruction is executed, the clocks fOCO does not stop.

11.3.5 fOCO-F

fOCO-F is generated by the high-speed on-chip oscillator and supplied by setting the HRA00 bit to 1. When the WAIT instruction is executed, the clock fOCO-F does not stop.

11.3.6 fOCO-S

fOCO-S is an operating clock for the watchdog timer and voltage detection circuit. fOCO-S is supplied by setting the CM14 bit to 0 (low-speed on-chip oscillator on) and uses the clock generated by the low-speed on-chip oscillator. When the WAIT instruction is executed or in count source protect mode of the watchdog timer, fOCO-S does not stop.

11.3.7 fC4 and fC32

The clock fC4 is used for timer RE and the clock fC32 is used for timer RA, timer RF, and watchdog timer. Use fC4 and fC32 while the XCIN clock oscillation stabilizes.

11.4 Power Control

There are three power control modes. All modes other than wait mode and stop mode are referred to as standard operating mode.

11.4.1 Standard Operating Mode

Standard operating mode is further separated into three modes.

In standard operating mode, the CPU clock and the peripheral function clock are supplied to operate the CPU and the peripheral function clocks. Power consumption control is enabled by controlling the CPU clock frequency. The higher the CPU clock frequency, the more processing power increases. The lower the CPU clock frequency, the more power consumption decreases. When unnecessary oscillator circuits stop, power consumption is further reduced.

Before the clock sources for the CPU clock can be switched over, the new clock source needs to be oscillating and stable. If the new clock source is the XCIN clock, allow sufficient wait time in a program until oscillation is stabilized before exiting.

Modes		OCD Register	CM1 Reg	jister	CM0 R	egister	HRA0 F	Register
wodes		OCD2	CM17, CM16	CM14	CM06	CM04	HRA01	HRA00
High-speed on-chip	No division	1	00b	-	0	-	1	1
oscillator mode	Divide-by-2	1	01b	-	0	-	1	1
	Divide-by-4	1	10b	_	0	-	1	1
	Divide-by-8	1	-	_	1	-	1	1
	Divide-by-16	1	11b	-	0	-	1	1
Low-speed on-chip	No division	1	00b	0	0	-	0	-
oscillator mode	Divide-by-2	1	01b	0	0	-	0	-
	Divide-by-4	1	10b	0	0	-	0	-
	Divide-by-8	1	—	0	1	-	0	-
	Divide-by-16	1	11b	0	0	-	0	-
Low-speed clock	No division	0	00b	_	0	1	-	-
mode	Divide-by-2	0	01b	-	0	1	-	-
	Divide-by-4	0	10b	-	0	1	-	-
	Divide-by-8	0	—	-	1	1	-	-
	Divide-by-16	0	11b	_	0	1	_	_

Table 11.2 Settings and Modes of Clock Associated Bits

-: Can be 0 or 1, no change in outcome

11.4.1.1 High-Speed On-Chip Oscillator Mode

The high-speed on-chip oscillator is used as the on-chip oscillator clock when the HRA00 bit in the HRA0 register is set to 1 (high-speed on-chip oscillator on) and the HRA01 bit in the HRA0 register is set to 1. The on-chip oscillator divided by 1 (no division), 2, 4, 8, or 16 provides the CPU clock. Set the CM06 bit to 1 (divide-by-8 mode) when transiting to high-speed clock mode.

When the CM14 bit is set to 0 (low-speed on-chip oscillator on), fOCO-S can be used as the watchdog timer and voltage detection circuit.

11.4.1.2 Low-Speed On-Chip Oscillator Mode

If the CM14 bit in the CM1 register is set to 0 (low-speed on-chip oscillator on) or the HRA01 bit in the HRA0 register is set to 0, the low-speed on-chip oscillator provides the on-chip oscillator clock.

The on-chip oscillator clock divided by 1 (no division), 2, 4, 8 or 16 provides the CPU clock. The on-chip oscillator clock is also the clock source for the peripheral function clocks.

When the CM14 bit is set to 0 (low-speed on-chip oscillator on), fOCO-S can be used as the watchdog timer and voltage detection circuit.

In this mode, stopping the high-speed on-chip oscillator, and setting the FMR47 bit in the FMR4 register to 1 (flash memory low consumption current read mode enabled) enables low consumption operation.

To enter wait mode from low-speed on-chip oscillator mode, setting the VCA20 bit in the VCA2 register to 1 (internal power low consumption enabled) enables lower consumption current in wait mode.

Refer to 21. Reducing Power Consumption for how to reduce the power consumption.

11.4.1.3 Low-Speed Clock Mode

The XCIN clock divided by 1 (no division), 2, 4, 8, or 16 provides the CPU clock. Set the CM06 bit to 1 (divide by-8 mode) when transiting to high-speed on-chip oscillator mode, low-speed on-chip oscillator mode. If the CM14 bit is set to 0 (low-speed on-chip oscillator on) or the HRA00 bit in the HRA0 register is set to 1 (high speed on-chip oscillator on), fOCO can be used as timer RA.

When the CM14 bit is set to 0 (low-speed on-chip oscillator on), fOCO-S can be used as the watchdog timer and voltage detection circuit.

In this mode, stopping the high-speed on-chip oscillator, and setting the FMR47 bit in the FMR4 register to 1 (flash memory low consumption current read mode enabled) enables low consumption operation.

To enter wait mode from low-speed clock mode, setting the VCA20 bit in the VCA2 register to 1 (internal power low consumption enabled) enables lower consumption current in wait mode.

Refer to 21. Reducing Power Consumption for how to reduce the power consumption.

11.4.2 Wait Mode

Since the CPU clock stops in wait mode, the CPU, which operates using the CPU clock, and the watchdog timer, when count source protection mode is disabled, stop. The XCIN clock and on-chip oscillator clock do not stop and the peripheral functions using these clocks continue operating.

11.4.2.1 Peripheral Function Clock Stop Function

If the CM02 bit is set to 1 (peripheral function clock stops in wait mode), the f1, f2, f4, f8, and f32 clocks stop in wait mode. This reduces power consumption.

11.4.2.2 Entering Wait Mode

The MCU enters wait mode when the WAIT instruction is executed.

11.4.2.3 Pin Status in Wait Mode

The I/O port is the status before wait mode was entered is maintained.

11.4.2.4 Exiting Wait Mode

The MCU exits wait mode by a reset or a peripheral function interrupt.

The peripheral function interrupts are affected by the CM02 bit. When the CM02 bit is set to 0 (peripheral function clock does not stop in wait mode), all peripheral function interrupts can be used to exit wait mode. When the CM02 bit is set to 1 (peripheral function clock stops in wait mode), the peripheral functions using the peripheral function clock stop operating and the peripheral functions operated by external signals or on-chip oscillator clock can be used to exit wait mode.

Table 11.3 lists Interrupts to Exit Wait Mode and Usage Conditions.

Table 11.3 Interrupts to Exit Wait Mode and Usage Conditions

Interrupt	CM02 = 0	CM02 = 1
Serial interface interrupt	Usable when operating with	Usable when operating with external
	internal or external clock	clock
Key input interrupt	Usable	Usable
Timer RA interrupt	Usable in all modes	Can be used if there is no filter in
		event counter mode.
		Usable by selecting fOCO or fC32 as
		count source.
Timer RB interrupt	Usable in all modes	(Do not use)
Timer RE interrupt	Usable in all modes	Usable when operating in real time
		clock mode
Timer RF interrupt	Usable in all modes	(Do not use)
INTO, INT1, INT2, INT4 interrupt	Usable	Can be used if there is no filter
Voltage monitor 1 interrupt	Usable	Usable
Voltage monitor 2 interrupt	Usable	Usable

Figure 11.11 shows the Time from Wait Mode to Interrupt Routine Execution.

When using a peripheral function interrupt to exit wait mode, set up the following before executing the WAIT instruction.

- (1) Set the interrupt priority level in bits ILVL2 to ILVL0 in the interrupt control registers of the peripheral function interrupts to be used for exiting wait mode. Set bits ILVL2 to ILVL0 of the peripheral function interrupts that are not to be used for exiting wait mode to 000b (interrupt disabled).
- (2) Set the I flag to 1.
- (3) Operate the peripheral function to be used for exiting wait mode.

When exiting by a peripheral function interrupt, the time (number of cycles) between interrupt request generation and interrupt routine execution is determined by the settings of the FMSTP bit in the FMR0 register, as described in Figure 11.11.

The CPU clock, when exiting wait mode by a peripheral function interrupt, is the same clock as the CPU clock when the WAIT instruction is executed.

FMR0 RegisterTime until Flash MemoryFMSTP Bitis Activated (T1)		Time until CPU Clock is Supplied (T2)	1	for Interrupt uence (T3)	Remarks	
0 (flash memory operates) Period of system clock × 12 cycles + 30 μs (max.)		Period of CPU clock × 6 cycles	Period of CPU clock × 20 cycles		Following total time is the time from wait mode	
1 (flash memory stops)		Period of system clock × 12 cycles	Same as above	Sam	e as above	until an interrupt routine is executed.
		T1	, T2			Т3
Wait mode Flash memory activation sequence			CPU clock restart seq	uence	Interru	ot sequence
,		errupt request generated				

11.4.3 Stop Mode

Since the oscillator circuits stop in stop mode, the CPU clock and peripheral function clock stop and the CPU and peripheral functions that use these clocks stop operating. The least power required to operate the MCU is in stop mode. If the voltage applied to the VCC pin is VRAM or more, the contents of internal RAM is maintained.

The peripheral functions clocked by external signals continue operating. Table 11.4 lists Interrupts to Exit Stop Mode and Usage Conditions.

Table 11.4 Interrupts to Exit Stop Mode and Usage Conditions

Interrupt	Usage Conditions
Key input interrupt	-
INTO, INT1, INT2, INT4 interrupt	Can be used if there is no filter
Timer RA interrupt	When there is no filter and external pulse is counted in event counter mode
Serial interface interrupt	When external clock is selected
Voltage monitor 1 interrupt	Usable in digital filter disabled mode (VW1C1 bit in VW1C register is set to 1)
Voltage monitor 2 interrupt	Usable in digital filter disabled mode (VW2C1 bit in VW2C register is set to 1)

11.4.3.1 Entering Stop Mode

The MCU enters stop mode when the CM10 bit in the CM1 register is set to 1 (all clocks stop). At the same time, the CM06 bit in the CM0 register is set to 1 (divide-by-8 mode), the CM03 bit in the CM0 register is set to 1 (XCIN clock oscillator circuit drive capacity high).

11.4.3.2 Pin Status in Stop Mode

The status before wait mode was entered is maintained.

When the CM04 bit in the CM0 register is set to 1 (XCIN-XCOUT pin), the XCIN(P4_3) pin is set to the high-impedance state and the XCOUT (P4_4) pin is set to "H". When the CM04 bit is set to 0 (I/O ports P4_3 and P4_4), pins XCIN (P4_3) and XOUT (P4_4) retain the I/O status (status just before stop mode is entered).

11.4.3.3 Exiting Stop Mode

The MCU exits stop mode by a reset or peripheral function interrupt.

Figure 11.12 shows the Time from Stop Mode to Interrupt Routine Execution.

When using a peripheral function interrupt to exit stop mode, set up the following before setting the CM10 bit to 1.

- (1) Set the interrupt priority level in bits ILVL2 to ILVL0 of the peripheral function interrupts to be used for exiting stop mode. Set bits ILVL2 to ILVL0 of the peripheral function interrupts that are not to be used for exiting stop mode to 000b (interrupt disabled).
- (2) Set the I flag to 1.
- (3) Operates the peripheral function to be used for exiting stop mode.

When exiting by a peripheral function interrupt, the interrupt sequence is executed when an interrupt request is generated and the CPU clock supply is started.

If the clock used immediately before stop mode is a system clock and stop mode is exited by a peripheral function interrupt, the CPU clock becomes the previous system clock divided by 8.



Figure 11.12 Time from Stop Mode to Interrupt Routine Execution



Figure 11.13 shows the State Transitions in Power Control Mode.

Figure 11.13 State Transitions in Power Control Mode

11.5 Notes on Clock Generation Circuit

11.5.1 Stop Mode

When entering stop mode, set the FMR01 bit in the FMR0 register to 0 (CPU rewrite mode disabled) and the CM10 bit in the CM1 register to 1 (stop mode). An instruction queue pre-reads 4 bytes from the instruction which sets the CM10 bit to 1 (stop mode) and the program stops.

Insert at least 4 NOP instructions following the JMP.B instruction after the instruction which sets the CM10 bit to 1.

• Program example to enter stop mode

BCLR	1,FMR0	; CPU rewrite mode disabled
BSET	0,PRCR	; Protect disabled
FSET	Ι	; Enable interrupt
BSET	0,CM1	; Stop mode
JMP.B	LABEL_001	
LABEL_001 :		
NOP		
NOP		
NOP		
NOP		

11.5.2 Wait Mode

When entering wait mode, set the FMR01 bit in the FMR0 register to 0 (CPU rewrite mode disabled) and execute the WAIT instruction. An instruction queue pre-reads 4 bytes from the WAIT instruction and the program stops. Insert at least 4 NOP instructions after the WAIT instruction.

• Program example to execute the WAIT instruction

BCLR 1,FMR0 FSET I WAIT NOP NOP NOP NOP ; CPU rewrite mode disabled ; Enable interrupt ; Wait mode

11.5.3 Oscillation Circuit Constants

Ask the manufacturer of the oscillator to specify the best oscillation circuit constants for your system.

12. Protection

The protection function protects important registers from being easily overwritten when a program runs out of control. Figure 12.1 shows the PRCR Register. The registers protected by the PRCR register are listed below.

- Registers protected by PRC0 bit: Registers CM0, CM1, OCD, HRA0, HRA1, and HRA2
- Registers protected by PRC1 bit: Registers PM0 and PM1
- Registers protected by PRC2 bit: PD0 register
- Registers protected by PRC3 bit: Registers VCA2, VW0C, VW1C, VW2C, VCAB, BGRCR, and BGRTRM

b7 b6 b5 b4 b	-				
		Symbol PRCR	Address 000Ah	After Reset 00h	
		Bit Symbol	Bit Name	Function	RW
		PRC0	Protect bit 0	Writing to registers CM0, CM1, OCD, HRA0, HRA1, and HRA2 is enabled. 0 : Disables writing 1 : Enables w riting	RW
		PRC1	Protect bit 1	Writing to registers PM0 and PM1 is enabled. 0 : Disables writing 1 : Enables writing	RW
		PRC2	Protect bit 2	Writing to the PD0 register is enabled. 0 : Disables writing 1 : Enables writing ⁽¹⁾	RW
		PRC3	Protect bit 3	Writing to registers VCA2, VW0C, VW1C, VW2C, VCAB, BGRCR, and BGRTRM is enabled. 0 : Disables w riting 1 : Enables w riting	RW
		 (b5-b4)	Reserved bits	Set to 0.	RW
		— (b7-b6)	Nothing is assigned. If n When read, the content	•	—
NOTE:					

1. This PRC2 bit is set to 0 after writing 1 to this bit and executing a write to any address. Since the other bits are not set to 0, set them to 0 by a program.

Figure 12.1 PRCR Register

13. Interrupts

13. Interrupts

13.1 Interrupt Overview

13.1.1 Types of Interrupts

Figure 13.1 shows the Types of Interrupts.





- Maskable Interrupts: The interrupt enable flag (I flag) enables or disables these interrupts. The interrupt priority order can be changed based on the interrupt priority level.
 Non-Maskable Interrupts: The interrupt enable flag (I flag) does not enable or disable these interrupts.
 - The interrupt enable may does not enable of disable mese interrupts. The interrupt priority order cannot be changed based on interrupt priority level.

13.1.2 Software Interrupts

A software interrupt is generated when an instruction is executed. Software interrupts are non-maskable.

13.1.2.1 Undefined Instruction Interrupt

The undefined instruction interrupt is generated when the UND instruction is executed.

13.1.2.2 Overflow Interrupt

The overflow interrupt is generated when the O flag is set to 1 (arithmetic operation overflow) and the INTO instruction is executed. Instructions that set the O flag are: ABS, ADC, ADCF, ADD, CMP, DIV, DIVU, DIVX, NEG, RMPA, SBB, SHA, and SUB.

13.1.2.3 BRK Interrupt

A BRK interrupt is generated when the BRK instruction is executed.

13.1.2.4 INT Instruction Interrupt

An INT instruction interrupt is generated when the INT instruction is executed. The INT instruction can select software interrupt numbers 0 to 63. Software interrupt numbers 3 to 31 are assigned to the peripheral function interrupt. Therefore, the MCU executes the same interrupt routine when the INT instruction is executed as when a peripheral function interrupt is generated. For software interrupt numbers 0 to 31, the U flag is saved to the stack during instruction execution and the U flag is set to 0 (ISP selected) before the interrupt sequence is executed. The U flag is restored from the stack when returning from the interrupt routine. For software interrupt numbers 32 to 63, the U flag does not change state during instruction execution, and the selected SP is used.

13.1.3 Special Interrupts

Special interrupts are non-maskable. However, the comparator 1 and comparator 2 can select maskable interrupts, too.

13.1.3.1 Watchdog Timer Interrupt

The watchdog timer interrupt is generated by the watchdog timer. For details of the watchdog timer, refer to **16.** Watchdog Timer.

13.1.3.2 Voltage Monitor 1 Interrupt

The voltage monitor 1 interrupt is generated by the voltage monitor 1 circuit. For details of the voltage monitor 1 circuit, refer to **6. Voltage Detection Circuit**.

13.1.3.3 Voltage Monitor 2 Interrupt

The voltage monitor 2 interrupt is generated by the voltage monitor 2 circuit. For details of the voltage monitor 2, refer to **6. Voltage Detection Circuit**.

13.1.3.4 Comparator 1 Interrupt

The comparator 1 interrupt is generated by the comparator 1. The non-maskable interrupt or maskable interrupt can be selected. For details of the comparator 1 interrupt, refer to **7. Comparator**.

13.1.3.5 Comparator 2 Interrupt

The comparator 2 interrupt is generated by the comparator 2. The non-maskable interrupt or maskable interrupt can be selected. For details of the comparator 2 interrupt, refer to **7. Comparator**.

13.1.3.6 Single-Step Interrupt, and Address Break Interrupt

Do not use these interrupts. They are for use by development tools only.

13.1.3.7 Address Match Interrupt

The address match interrupt is generated immediately before executing an instruction that is stored at an address indicated by registers RMAD0 to RMAD1 when the AIER0 or AIER1 bit in the AIER register is set to 1 (address match interrupt enable). For details of the address match interrupt, refer to **13.4 Address Match Interrupt**.

13.1.4 Peripheral Function Interrupt

The peripheral function interrupt is generated by the internal peripheral function of the MCU and is a maskable interrupt. Refer to **Table 13.2 Relocatable Vector Tables** for sources of the peripheral function interrupt. For details of peripheral functions, refer to the descriptions of individual peripheral functions.

13.1.5 Interrupts and Interrupt Vectors

There are 4 bytes in each vector. Set the starting address of an interrupt routine in each interrupt vector. When an interrupt request is acknowledged, the CPU branches to the address set in the corresponding interrupt vector. Figure 13.2 shows an Interrupt Vector.

	MSB	LSB
Vector address (L)	Low address	
	Mid ad	ddress
	0000	High address
Vector address (H)	0000	0000

Figure 13.2	Interrupt Vector
-------------	------------------

13.1.5.1 Fixed Vector Tables

The fixed vector tables are allocated addresses 0FFDCh to 0FFFFh.

Table 13.1 lists the Fixed Vector Tables. The vector addresses (H) of fixed vectors are used by the ID code check function. For details, refer to **20.3 Functions to Prevent Rewriting of Flash Memory**.

Interrupt Source	Vector Addresses Address (L) to (H)	Remarks	Reference
Undefined instruction	0FFDCh to 0FFDFh	Interrupt on UND	R8C/Tiny Series Software
		instruction	Manual
Overflow	0FFE0h to 0FFE3h	Interrupt on INTO	
		instruction	
BRK instruction	0FFE4h to 0FFE7h	If the content of address	
		0FFE7h is FFh,	
		program execution	
		starts from the address	
		shown by the vector in	
		the relocatable vector	
		table.	
Address match	0FFE8h to 0FFEBh		13.4 Address Match
			Interrupt
Single step ⁽¹⁾	0FFECh to 0FFEFh		
Watchdog timer,	0FFF0h to 0FFF3h		16. Watchdog Timer
Voltage monitor 1,			6. Voltage Detection Circuit
Voltage monitor 2,			7. Comparator
Comparator 1,			
Comparator 2			
Address break ⁽¹⁾	0FFF4h to 0FFF7h		
(Reserved)	0FFF8h to 0FFFBh		
Reset	0FFFCh to 0FFFFh		5. Resets

Table 13.1 Fixed Vector Tables

NOTE:

1. Do not use these interrupts. They are for use by development tools only.

Relocatable Vector Tables 13.1.5.2

The relocatable vector tables occupy 256 bytes beginning from the starting address set in the INTB register. Table 13.2 lists the Relocatable Vector Tables.

Interrupt Source	Vector Addresses ⁽¹⁾ Address (L) to Address (H)	Software Interrupt Number	Interrupt Control Register	Reference
BRK instruction ⁽²⁾	+0 to +3(0000h to 0003h)	0	-	R8C/Tiny Series Software Manual
Comparator 1	+4 to +7(0004h to 0007h)	1	VCMP1IC	7. Comparator
Comparator 2	+8 to +11(0008h to 000Bh)	2	VCMP2IC	
(Reserved)		3 to 9	-	-
Timer RE	+40 to +43(0028h to 002Bh)	10	TREIC	17.3 Timer RE
UART2 transmit	+44 to +47(002Ch to 002Fh)	11	S2TIC	18. Serial Interface
UART2 receive	+48 to +51(0030h to 0033h)	12	S2RIC	
Key input	+52 to +55(0034h to 0037h)	13	KUPIC	13.3 Key Input Interrupt
(Reserved)		14	-	-
(Reserved)		15	-	-
Compare 1	+64 to +67(0040h to 0043h)	16	CMP1IC	17.4 Timer RF
UART0 transmit	+68 to +71(0044h to 0047h)	17	SOTIC	18. Serial Interface
UART0 receive	+72 to +75(0048h to 004Bh)	18	SORIC	
(Reserved)		19	-	-
(Reserved)		20	-	-
INT2	+84 to +87(0054h to 0057h)	21	INT2IC	13.2 INT Interrupt
Timer RA	+88 to +91(0058h to 005Bh)	22	TRAIC	17.1 Timer RA
(Reserved)		23	-	-
Timer RB	+96 to +99(0060h to 0063h)	24	TRBIC	17.2 Timer RB
INT1	+100 to +103(0064h to 0067h)	25	INT1IC	13.2 INT Interrupt
(Reserved)		26	-	
Timer RF	+108 to +111(006Ch to 006Fh)	27	TRFIC	17.4 Timer RF
Compare 0	+112 to +115(0070h to 0073h)	28	CMP0IC	
INT0	+116 to +119(0074h to 0077h)	29	INTOIC	13.2 INT Interrupt
INT4	+120 to +123(0078h to 007Bh)	30	INT4IC	
Capture	+124 to +127(007Ch to 007Fh)	31	CAPIC	17.4 Timer RF
Software interrupt ⁽²⁾	+128 to +131(0080h to 0083h) to +252 to +255(00FCh to 00FFh)	32 to 63	-	R8C/Tiny Series Software Manual

Table 13.2 **Relocatable Vector Tables**

NOTES:

These addresses are relative to those in the INTB register.
 The I flag does not disable these interrupts.

13.1.6 Interrupt Control

The following describes enabling and disabling the maskable interrupts and setting the priority for acknowledgement. The explanation does not apply to nonmaskable interrupts.

Use the I flag in the FLG register, IPL, and bits ILVL2 to ILVL0 in each interrupt control register to enable or disable maskable interrupts. Whether an interrupt is requested is indicated by the IR bit in each interrupt control register.

Figure 13.3 shows the Interrupt Control Register and Figure 13.4 shows the INTIIC Register (i=0, 1, 2, 4).





b6 b5 b4 b3 b2 b1 b0	Symbol INT2IC INT1IC INT0IC INT4IC	Address 0055h 0059h 005Dh 005Eh	After Reset XX00X000b XX00X000b XX00X000b XX00X000b	
	Bit Symbol	Bit Name	Function	R
	ILVL0	Interrupt priority level select bits	b2 b1 b0 0 0 0 : Level 0 (interrupt disable) 0 0 1 : Level 1	R
	ILVL1		0 1 0 : Level 2 0 1 1 : Level 3 1 0 0 : Level 4 1 0 1 : Level 5	R
	ILVL2	-	1 1 0 : Level 6 1 1 1 : Level 7	R
	IR	Interrupt request bit	0 : Requests no interrupt 1 : Requests interrupt	RW
	POL	Polarity switch bit ⁽⁴⁾	0 : Selects falling edge 1 : Selects rising edge ⁽³⁾	R
	 (b5)	Reserved bit	Set to 0.	R
	 (b7-b6)	Nothing is assigned. If necessary, When read, the content is undefine		-

2. Rew rite the interrupt control register when the interrupt request which is applicable for the register is not generated. Refer to 13.5.5 Changing Interrupt Control Register Contents.

3. If the INTIPL bit in registers INTEN and INTEN2 are set to 1 (both edges), set the POL bit to 0 (selects falling edge).

4. The IR bit may be set to 1 (requests interrupt) when the POL bit is rewritten. Refer to 13.5.4 Changing Interrupt Sources.



13.1.6.1 | Flag

The I flag enables or disables maskable interrupts. Setting the I flag to 1 (enabled) enables maskable interrupts. Setting the I flag to 0 (disabled) disables all maskable interrupts.

13.1.6.2 IR Bit

The IR bit is set to 1 (interrupt requested) when an interrupt request is generated. Then, when the interrupt request is acknowledged and the CPU branches to the corresponding interrupt vector, the IR bit is set to 0 (= interrupt not requested).

The IR bit can be set to 0 by a program. Do not write 1 to this bit.

13.1.6.3 ILVL2 to ILVL0 Bits and IPL

Interrupt priority levels can be set using bits ILVL2 to ILVL0.

Table 13.3 lists the Settings of Interrupt Priority Levels and Table 13.4 lists the Interrupt Priority Levels Enabled by IPL.

The following are conditions under which an interrupt is acknowledged:

- I flag = 1
- IR bit = 1
- Interrupt priority level > IPL

The I flag, IR bit, bits ILVL2 to ILVL0, and IPL are independent of each other. They do not affect one another.

Table 13.3Settings of Interrupt Priority
Levels

ILVL2 to ILVL0 Bits	Interrupt Priority Level	Priority Order
000b	Level 0 (interrupt disabled)	-
001b	Level 1	Low
010b	Level 2	
011b	Level 3	
100b	Level 4	
101b	Level 5	
110b	Level 6	V
111b	Level 7	High

Table 13.4 Interrupt Priority Levels Enabled by IPL

IPL	Enabled Interrupt Priority Levels
000b	Interrupt level 1 and above
001b	Interrupt level 2 and above
010b	Interrupt level 3 and above
011b	Interrupt level 4 and above
100b	Interrupt level 5 and above
101b	Interrupt level 6 and above
110b	Interrupt level 7 and above
111b	All maskable interrupts are disabled

13.1.6.4 Interrupt Sequence

An interrupt sequence is performed between an interrupt request acknowledgement and interrupt routine execution.

When an interrupt request is generated while an instruction is being executed, the CPU determines its interrupt priority level after the instruction is completed. The CPU starts the interrupt sequence from the following cycle. However, for the SMOVB, SMOVF, SSTR, or RMPA instructions, if an interrupt request is generated while the instruction is being executed, the MCU suspends the instruction to start the interrupt sequence. The interrupt sequence is performed as indicated below.

Figure 13.5 shows the Time Required for Executing Interrupt Sequence.

- (1) The CPU gets interrupt information (interrupt number and interrupt request level) by reading address 00000h. The IR bit for the corresponding interrupt is set to 0 (interrupt not requested).
- (2) The FLG register is saved to a temporary register⁽¹⁾ in the CPU immediately before entering the interrupt sequence.
- (3) The I, D and U flags in the FLG register are set as follows: The I flag is set to 0 (interrupts disabled). The D flag is set to 0 (single-step interrupt disabled). The U flag is set to 0 (ISP selected). However, the U flag does not change state if an INT instruction for software interrupt number 32 to 63 is executed.
- (4) The CPU's internal temporary register⁽¹⁾ is saved to the stack.
- (5) The PC is saved to the stack.
- (6) The interrupt priority level of the acknowledged interrupt is set in the IPL.
- (7) The starting address of the interrupt routine set in the interrupt vector is stored in the PC.

After the interrupt sequence is completed, instructions are executed from the starting address of the interrupt routine.

CPU Clock	
Address Bus	Address Undefined XSP-2 XSP-4 SP-3 XVEC VEC+1 VEC+2 PC
Data Bus	Interrupt Undefined VSP-2 SP-1 SP-4 SP-3 VeC VEC+1 VEC+2 Contents Contents Contents Contents Contents Contents Contents Contents Contents
RD	
WR	
	leterminate state depends on the instruction queue buffer. A read cycle occurs when the instruction queue buffer is o acknowledge instructions.

Figure 13.5 **Time Required for Executing Interrupt Sequence**

NOTE:

1. This register cannot be used by user.

13.1.6.5 Interrupt Response Time

Figure 13.6 shows the Interrupt Response Time. The interrupt response time is the period between an interrupt request generation and the execution of the first instruction in the interrupt routine. The interrupt response time includes the period between interrupt request generation and the completion of execution of the instruction (refer to (a) in **Figure 13.6**) and the period required to perform the interrupt sequence (20 cycles, refer to (b) in **Figure 13.6**).



Figure 13.6 Interrupt Response Time

13.1.6.6 IPL Change when Interrupt Request is Acknowledged

When an interrupt request of a maskable interrupt is acknowledged, the interrupt priority level of the acknowledged interrupt is set in the IPL.

When a software interrupt or special interrupt request is acknowledged, the level listed in Table 13.5 is set in the IPL.

Table 13.5 lists the IPL Value When Software or Special Interrupt Is Acknowledged.

 Table 13.5
 IPL Value When Software or Special Interrupt Is Acknowledged

Interrupt Source	Value Set in IPL
Watchdog timer, voltage monitor 1, voltage monitor 2,	7
comparator $1^{(1)}$, comparator $2^{(1)}$, address break	
Software, address match, single-step	Not changed

NOTE:

1. When non-maskable interrupts is selected.

13.1.6.7 Saving a Register

In the interrupt sequence, the FLG register and PC are saved to the stack.

After an extended 16 bits, 4 high-order bits in the PC and 4 high-order (IPL) and 8 low-order bits in the FLG register, are saved to the stack, the 16 low-order bits in the PC are saved.

Figure 13.7 shows the Stack State Before and After Acknowledgement of Interrupt Request.

The other necessary registers are saved by a program at the beginning of the interrupt routine. The PUSHM instruction can save several registers in the register bank being currently $used^{(1)}$ with a single instruction.

NOTE:

1. Selectable from registers R0, R1, R2, R3, A0, A1, SB, and FB.



Figure 13.7 Stack State Before and After Acknowledgement of Interrupt Request

The register saving operation, which is performed as part of the interrupt sequence, saved in 8 bits at a time in four steps.

Figure 13.8 shows the Register Saving Operation.



Figure 13.8 Register Saving Operation

13.1.6.8 **Returning from an Interrupt Routine**

When the REIT instruction is executed at the end of an interrupt routine, the FLG register and PC, which have been saved to the stack, are automatically restored. The program, that was running before the interrupt request was acknowledged, starts running again.

Restore registers saved by a program in an interrupt routine using the POPM instruction or others before executing the REIT instruction.

13.1.6.9 **Interrupt Priority**

If two or more interrupt requests are generated while a single instruction is being executed, the interrupt with the higher priority is acknowledged.

Set bits ILVL2 to ILVL0 to select the desired priority level for maskable interrupts (peripheral functions). However, if two or more maskable interrupts have the same priority level, their interrupt priority is resolved by hardware, and the higher priority interrupts acknowledged.

The priority levels of special interrupts, such as reset (reset has the highest priority) and watchdog timer, are set by hardware.

Figure 13.9 shows the Priority Levels of Hardware Interrupts.

The interrupt priority does not affect software interrupts. The MCU jumps to the interrupt routine when the instruction is executed.



Figure 13.9 **Priority Levels of Hardware Interrupts**

13.1.6.10 Interrupt Priority Judgement Circuit

The interrupt priority judgement circuit selects the highest priority interrupt, as shown in Figure 13.10.



Figure 13.10 Interrupt Priority Level Judgement Circuit

13.2 INT Interrupt

13.2.1 **INTi** Interrupt (i = 0, 1, 2, 4)

The \overline{INTi} interrupt is generated by an \overline{INTi} input. Table 13.6 lists the Pin Configuration of \overline{INT} Interrupt. When using the \overline{INTi} interrupt, the INTIEN bit in registers INTEN and INTEN2 are set to 1 (enable). The edge polarity is selected using the INTIPL bit in registers INTEN and INTEN2, and the POL bit in the INTIIC register.

Inputs can be passed through a digital filter with three different sampling clocks.

Figure 13.11 shows the INTEN Register. Figure 13.12 shows the INTF Register. Figure 13.13 shows the INTEN2 Register. Figure 13.14 shows the INTF2 Register.

Pin name	Input/Output	Function
INT0 (P4_5)	Input	INT0 interrupt input, Timer RB external trigger input
INT1 (P1_5, P1_7, or P3_6) ⁽¹⁾	Input	INT1 interrupt input
INT2 (P3_2)	Input	INT2 interrupt input
INT4 (P0_6)	Input	INT4 interrupt input

Table 13.6 Pin Configuration of INT Interrupt

NOTE:

1. The INT1 pin is selected by the INT1SEL bit in the PMR register and the TIOSEL bit in the TRAIOC register. Refer to **8. I/O Ports** for details.

Symbol INTEN	Address 00F9h	After Reset 00h	
Bit Symbol	Bit Name	Function	RV
INT0EN	INTO input enable bit	0 : Disable 1 : Enable	RV
INTOPL	INTO input polarity select bit ^(1, 2)	0 : One edge 1 : Both edges	RV
INT1EN	INT1 input enable bit	0 : Disable 1 : Enable	RV
INT1PL	INT1 input polarity select bit ^(1, 2)	0 : One edge 1 : Both edges	RV
INT2EN	INT2 input enable bit	0 : Disable 1 : Enable	RV
INT2PL	INT2 input polarity select bit ^(1, 2)	0 : One edge 1 : Both edges	RV
 (b7-b6)	Reserved bits	Set to 0.	RV

Figure 13.11 INTEN Register



Set to 0.





Reserved bits

(b7-b6)

2. The IR bit in the INT4IC register may be set to 1 (requests interrupt) when the INT4PL bit is rewritten. Refer to 13.5.4 Changing Interrupt Sources.



RW


Figure 13.14 INTF2 Register

13.2.2 **INTi** Input Filter (i = 0, 1, 2, 4)

The $\overline{\text{INTi}}$ input contains a digital filter. The sampling clock is selected by bits INTiF1 to INTiF0 in registers INTF and INTF2. The IR bit in the INTiIC register is set to 1 (interrupt requested) when the $\overline{\text{INTi}}$ level is sampled for every sampling clock and the sampled input level matches three times.

Figure 13.15 shows the Configuration of \overline{INTi} Input Filter. Figure 13.16 shows an Operating Example of \overline{INTi} Input Filter.



Figure 13.15 Configuration of INTi Input Filter



Figure 13.16 Operating Example of INTi Input Filter

13.3 Key Input Interrupt

A key input interrupt request is generated by one of the input edges of the $\overline{K10}$ to $\overline{K13}$ pins. Table 13.7 lists the Pin Configuration of Key Input Interrupt. The key input interrupt can be used as a key-on wake-up function to exit wait or stop mode.

The KIiEN (i = 0 to 3) bit in the KIEN register can select whether the pins are used as \overline{KIi} input. The KIiPL bit in the KIEN register can select the input polarity.

When inputting "L" to the $\overline{\text{KIi}}$ pin which sets the KIiPL bit to 0 (falling edge), the input of the other pins $\overline{\text{K10}}$ to $\overline{\text{K13}}$ is not detected as interrupts. Also, when inputting "H" to the $\overline{\text{KIi}}$ pin, which sets the KIiPL bit to 1 (rising edge), the input of the other pins $\overline{\text{K10}}$ to $\overline{\text{K13}}$ is not detected as interrupts.

Figure 13.17 shows a Block Diagram of Key Input Interrupt and Figure 13.18 shows the KIEN Register.

 Table 13.7
 Pin Configuration of Key Input Interrupt

Pin name	Input/Output	Function
KI0 (P0_7 or P1_0 ⁽¹⁾)	Input	KI0 input
KI1 (P1_1 or P6_6 ⁽²⁾)	Input	KI1 input
KI2 (P1_2)	Input	KI2 input
KI3 (P1_3)	Input	KI3 input

NOTES:

- 1. The KIO pin is selected by the KIOSEL bit in the PINSR4 register. Refer to **8. I/O Ports** for details.
- 2. The KI1 pin is selected by the KI1SEL bit in the PINSR4 register. Refer to **8. I/O Ports** for details.



Figure 13.17 Block Diagram of Key Input Interrupt

7 b6 b5	b4 b3 b2 b1 b0				
		Symbol	Address	After Reset	
		KIEN	00FBh	00h	
		Bit Symbol	Bit Name	Function	RW
		KIOEN	KI0 input enable bit	0 : Disable 1 : Enable	RW
		KIOPL	KI0 input polarity select bit	0 : Falling edge 1 : Rising edge	RW
	KI1EN	Kl1 input enable bit	0 : Disable 1 : Enable	RW	
		KI1PL	Kl1 input polarity select bit	0 : Falling edge 1 : Rising edge	RW
		KI2EN	Kl2 input enable bit	0 : Disable 1 : Enable	RW
	KI2PL	Kl2 input polarity select bit	0 : Falling edge 1 : Rising edge	RW	
		KI3EN	Kl3 input enable bit	0 : Disable 1 : Enable	RW
		- KI3PL	Kl3 input polarity select bit	0 : Falling edge 1 : Rising edge	RW

1. The IR bit in the KUPIC register may be set to 1 (requests interrupt) when the KIEN register is rew ritten. Refer to 13.5.4 Changing Interrupt Sources.

Figure 13.18 KIEN Register

13.4 Address Match Interrupt

An address match interrupt request is generated immediately before execution of the instruction at the address indicated by the RMADi register (i = 0 or 1). This interrupt is used as a break function by the debugger. When using the on-chip debugger, do not set an address match interrupt (registers of AIER, RMAD0, and RMAD1 and fixed vector tables) in a user system.

Set the starting address of any instruction in the RMADi register. Bits AIER0 and AIER1 in the AIER0 register can be used to select enable or disable of the interrupt. The I flag and IPL do not affect the address match interrupt. The value of the PC (refer to **13.1.6.7 Saving a Register** for the value of the PC) which is saved to the stack when an address match interrupt is acknowledged varies depending on the instruction at the address indicated by the RMADi register. (The appropriate return address is not saved on the stack.) When returning from the address match interrupt, return by one of the following means:

- Change the content of the stack and use the REIT instruction.
- Use an instruction such as POP to restore the stack as it was before the interrupt request was acknowledged. Then use a jump instruction.

Table 13.8 lists the Values of PC Saved to Stack when Address Match Interrupt is Acknowledged and Table 13.9 lists the Correspondence Between Address Match Interrupt Sources and Associated Registers. Figure 13.19 shows Registers AIER and RMAD0 to RMAD1.

Table 13.8	Values of PC Saved to Stack when Address Match Interrupt is Acknowledged
------------	--

Address Indicated by RMADi Register (i = 0 or 1)						PC Value Saved ⁽¹⁾
Instruction with 2-byte operation code ⁽²⁾						Address indicated by
 Instruction 	with 1-byte or	peration coo	e ⁽²⁾			RMADi register + 2
ADD.B:S	#IMM8,dest	SUB.B:S	#IMM8,dest	AND.B:S	#IMM8,dest	U U
OR.B:S	#IMM8,dest	MOV.B:S	#IMM8,dest	STZ	#IMM8,dest	
STNZ	#IMM8,dest	STZX	#IMM81,#IMM82,dest			
CMP.B:S	#IMM8,dest	PUSHM	src	POPM	dest	
JMPS	#IMM8	JSRS	#IMM8			
MOV.B:S #IMM,dest (however, dest = A0 or A1)						
Instructions	other than the	e above				Address indicated by
						RMADi register + 1

NOTES:

- 1. Refer to the **13.1.6.7 Saving a Register** for the PC value saved.
- 2. Operation code: Refer to the R8C/Tiny Series Software Manual (REJ09B0001).

Chapter 4. Instruction Code/Number of Cycles contains diagrams showing operation code below each syntax. Operation code is shown in the bold frame in the diagrams.

Table 13.9 Co	orrespondence Between	Address Match Interrup	ot Sources and Associated Registers
---------------	-----------------------	------------------------	-------------------------------------

Address Match Interrupt Source	Address Match Interrupt Enable Bit	Address Match Interrupt Register
Address match interrupt 0	AIER0	RMAD0
Address match interrupt 1	AIER1	RMAD1



Figure 13.19 Registers AIER and RMAD0 to RMAD1

13.5 Notes on Interrupts

13.5.1 Reading Address 00000h

Do not read address 00000h by a program. When a maskable interrupt request is acknowledged, the CPU reads interrupt information (interrupt number and interrupt request level) from 00000h in the interrupt sequence. At this time, the acknowledged interrupt IR bit is set to 0.

If address 00000h is read by a program, the IR bit for the interrupt which has the highest priority among the enabled interrupts is set to 0. This may cause the interrupt to be canceled, or an unexpected interrupt to be generated.

13.5.2 SP Setting

Set any value in the SP before an interrupt is acknowledged. The SP is set to 0000h after reset. Therefore, if an interrupt is acknowledged before setting a value in the SP, the program may run out of control.

13.5.3 External Interrupt and Key Input Interrupt

Either "L" level or an "H" level of width shown in the Electrical Characteristics is necessary for the signal input to pins $\overline{INT0}$, $\overline{INT1}$, $\overline{INT2}$, $\overline{INT4}$ and pins $\overline{K10}$ to $\overline{K13}$, regardless of the CPU clock. For details, refer to <u>Table 22.17</u> (VCC = 5V), Table 22.23 (VCC = 3V), and Table 22.29 (VCC = 2.2V) **External Interrupt INTi** (i = 0, 1, 2, 4) Input.

13.5.4 **Changing Interrupt Sources**

The IR bit in the interrupt control register may be set to 1 (interrupt requested) when the interrupt source changes. When using an interrupt, set the IR bit to 0 (no interrupt requested) after changing the interrupt source. In addition, changes of interrupt sources include all factors that change the interrupt sources assigned to individual software interrupt numbers, polarities, and timing. Therefore, if a mode change of a peripheral function involves interrupt sources, edge polarities, and timing, set the IR bit to 0 (no interrupt requested) after the change. Refer to the individual peripheral function for its related interrupts.

Figure 13.20 shows an Example of Procedure for Changing Interrupt Sources.



13.5.5 Changing Interrupt Control Register Contents

- (a) The contents of an interrupt control register can only be changed while no interrupt requests corresponding to that register are generated. If interrupt requests may be generated, disable interrupts before changing the interrupt control register contents.
- (b) When changing the contents of an interrupt control register after disabling interrupts, be careful to choose appropriate instructions.

Changing any bit other than IR bit

If an interrupt request corresponding to a register is generated while executing the instruction, the IR bit may not be set to 1 (interrupt requested), and the interrupt request may be ignored. If this causes a problem, use the following instructions to change the register: AND, OR, BCLR, BSET **Changing IR bit**

If the IR bit is set to 0 (interrupt not requested), it may not be set to 0 depending on the instruction used. Therefore, use the MOV instruction to set the IR bit to 0.

(c) When disabling interrupts using the I flag, set the I flag as shown in the sample programs below. Refer to (b) regarding changing the contents of interrupt control registers by the sample programs.

Sample programs 1 to 3 are for preventing the I flag from being set to 1 (interrupts enabled) before the interrupt control register is changed for reasons of the internal bus or the instruction queue buffer.

Example 1: Use NOP instructions to prevent I flag from being set to 1 before interrupt control register is changed

INT_SWITC	H1:	
FCLR	Ι	; Disable interrupts
AND.B	#00H,0056H	; Set TRAIC register to 00h
NOP		•
NOP		
FSET	Ι	; Enable interrupts

Example 2: Use dummy read to delay FSET instruction

INT_SWITCH2:

FCLR	Ι	; Disable interrupts
AND.B	#00H,0056H	; Set TRAIC register to 00h
MOV.W	MEM,R0	; <u>Dummy read</u>
FSET	Ι	; Enable interrupts

Example 3: Use POPC instruction to change I flag

INT_SWITC	H3:	
PUSHC	FLG	
FCLR	Ι	; Disable interrupts
AND.B	#00H,0056H	; Set TRAIC register to 00h
POPC	FLG	; Enable interrupts
		-

14. ID Code Areas

14.1 Overview

The ID code areas are used to implement a function that prevents the flash memory from being rewritten in standard serial I/O mode. This function prevents the flash memory from read, rewritten, or erased. The ID code areas are assigned to 0FFDFh, 0FFE3h, 0FFEBh, 0FFEFh, 0FFF3h, 0FFF7h, and 0FFFBh of the respective vector highest-order addresses of the fixed vector table. Figure 14.1 shows the ID Code Areas.



Figure 14.1 ID Code Areas

14.2 Functions

The ID code areas are used in standard serial I/O mode. Unless 3 bytes (addresses from 0FFFCh to 0FFFEh) of the reset vector are set to FFFFFFh, the ID codes stored in the ID code areas and the ID codes sent from the serial programmer or the on-chip debugging emulator are checked to see if they match. If the ID codes match, the commands sent from the serial programmer or the on-chip debugging emulator are acknowledged. If the ID codes do not match, the commands are not acknowledged. To use the serial programmer or the on-chip debugging simulator, first write predetermined ID codes to the ID code areas.

As the ID code areas are allocated in the flash memory (not in the SFRs), they cannot be rewritten by executing an instruction. Write appropriate values when creating a program.

14.3 Notes on ID Code Areas

14.3.1 Setting Example of ID Code Areas

As the ID code areas are allocated in the flash memory (not in the SFRs), they cannot be rewritten by executing an instruction. Write appropriate values when creating a program. The following shows a setting example.

• To set 55h in all of the ID code areas

.org 00FFDCH

.lword dummy (5500000h)	; UND
.lword dummy (5500000h)	; INTO
.lword dummy ; BREAK	
.lword dummy (5500000h)	; ADDRESS MATCH
.lword dummy (5500000h)	; SET SINGLE STEP
.lword dummy (5500000h)	; WDT
.lword dummy (5500000h)	; ADDRESS BREAK
.lword dummy (5500000h)	; RESERVE

(Programming formats vary depending on the compiler. Check the compiler manual.)

15. Option Function Select Area

15.1 Overview

The option function select area is used to select the MCU state after reset or the function to prevent rewriting in parallel I/O mode. The reset vector highest-order-address, 0FFFFh, is assigned as the option function select area. Figure 15.1 shows the Option Function Select Area.



Figure 15.1 Option Function Select Area

15.2 OFS Register

The OFS register is used to select the MCU state after reset or the function to prevent rewriting in parallel I/O mode. Figure 15.2 shows the OFS Register.

b7 b6	b5 b4 b3 b2 b1	<u> </u>			
$[]^1$		Symbol	Address	When Shipping	
		OFS	0FFFFh	FFh ⁽³⁾	
		Bit Symbol	Bit Name	Function	RW
			Watchdog timer start select bit	0 : Starts w atchdog timer automatically after reset1 : Watchdog timer is inactive after reset	RW
		(b1)	Reserved bit	Set to 1.	RW
		ROMCR	ROM code protect disabled bit	0 : ROM code protect disabled 1 : ROMCP1 enabled	RW
		ROMCP1	ROM code protect bit	0 : ROM code protect enabled 1 : ROM code protect disabled	RW
		(b4)	Reserved bit	Set to 1.	RW
		LVD0ON	Voltage detection 0 circuit start bit ⁽²⁾	 0 : Voltage monitor 0 reset enabled after hardw are reset 1 : Voltage monitor 0 reset disabled after hardw are reset 	RW
		(b6)	Reserved bit	Set to 1.	RW
		CSPROINI	Count source protect mode after reset select bit	0 : Count source protect mode enabled after reset 1 : Count source protect mode disabled after reset	RW

2. Setting the LVD0ON bit is only valid after a hardware reset. To use the pow er-on reset, set the LVD0ON bit to 0 (voltage monitor 0 reset enabled after hardware reset).

3. If the block including the OFS register is erased, FFh is set to the OFS register.

Figure 15.2 OFS Register

15.3 Notes on Option Function Select Area

15.3.1 Setting Example of Option Function Select Area

As the option function select area is allocated in the flash memory (not in the SFRs), they cannot be rewritten by executing an instruction. Write appropriate values when creating a program. The following shows a setting example.

• To set FFh in the OFS register .org 00FFFCH .lword reset | (0FF000000h) ; RESET (Programming formats vary depending on the compiler. Check the compiler manual.)

16. Watchdog Timer

The watchdog timer is a function that detects when a program is out of control. Use of the watchdog timer is recommended to improve the reliability of the system. The watchdog timer contains a 15-bit counter and allows selection of count source protection mode enable or disable.

Table 16.1 lists information on the Watchdog Timer Specifications.

Refer to **5.6 Watchdog Timer Reset** for details on the watchdog timer.

Figure 16.1 shows the Block Diagram of Watchdog Timer. Figure 16.2 shows the Registers WDTR, WDTS, and WDC. Figure 16.3 shows the Registers CSPR and OFS.

1					
Item	Count Source Protection		Count Source Protection		
nom	Mode Disabled		Mode Enabled		
Count source	CPU clock	XCIN clock divided by 32	Low-speed on-chip oscillator		
		(fC32)	clock		
Count operation	Decrement		•		
Count start condition	Either of the following ca	an be selected			
	After reset, count starts	automatically			
	Count starts by writing	to WDTS register			
Count stop condition	Stop mode, wait mode	Stop mode	None		
Reset condition of	• Reset				
watchdog timer	Write 00h to the WDTF	register before writing FFh			
-	Underflow				
Operation at the time	Watchdog timer interrupt or watchdog timer reset Watchdog timer reset				
of underflow					
Select functions		ler (when select the CPU clo	ock as the count source)		
	Selected by the WDC7 bit in the WDC register				
			ect fC32 as the count source)		
	3	to CVS1 in the CSPR regist	er		
	Count source protection mode				
	Whether count source protection mode is enabled or disabled after a reset can				
	be selected by the CSPROINI bit in the OFS register (flash memory). If count source protection mode is disabled after a reset, it can be enabled or disabled by				
	•	SPR register (program).	can be enabled of disabled by		
		atchdog timer after a reset			
	-	N bit in the OFS register (fla	ash memory)		
1					

Table 16.1 Watchdog Timer Specifications



Figure 16.1 Block Diagram of Watchdog Timer



Count Source Prote	ection Mode	e Register		
b7 b6 b5 b4 b3 b2 b1 b0	Symbol CSPR	Address 001Ch	After Reset ⁽¹⁾ 00h	
	Bit Symbol	Bit Name	Function	RW
	CVS0	Watchdog timer default value select bit ⁽²⁾	b1 b0 0 0 : 01FFh (512) 0 1 : 03FFh (1024)	RW
	CVS1		1 0 : 07FFh (2048) 1 1 : 0FFFh (4096)	RW
	CSS	Count source select bit ⁽³⁾	0 : CPU clock 1 : fC32	RW
		Nothing is assigned. If necessa	ry, set to 0.	
	(b6-b3)	When read, the content is 0.	-	
	CSPRO	Count source protection mode select bit ⁽⁴⁾	0 : Count source protection mode disabled 1 : Count source protection mode enabled	RW

NOTES:

- 1. When 0 is written to the CSPROINI bit in the OFS register, the value after reset is 1000000b.
- 2. When the CSS bit is set to 1 (fC32), Bits CVS0 to CVS1 are enabled.
- 3. When the CSPRO bit is set to 0 (count source protection mode disabled), the CSS bit is enabled.
- 4. Write 0 before writing 1 to set the CSPRO bit to 1.0 cannot be set by a program.

Option Function Select Register⁽¹⁾

7 b6 b5	5 b4 b	b3 b2 b1 b0	1			
1	1	1	Symbol	Address	When Shipping	
	П		OFS	0FFFFh	FFh ⁽³⁾	
	1 '		Bit Symbol	Bit Name	Function	RW
		L	WDTON	Watchdog timer start select bit	0 : Starts w atchdog timer automatically after reset 1 : Watchdog timer is inactive after reset	RW
		∟	(b1)	Reserved bit	Set to 1.	RW
			ROMCR	ROM code protect disabled bit	0 : ROM code protect disabled 1 : ROMCP1 enabled	RW
			ROMCP1	ROM code protect bit	0 : ROM code protect enabled 1 : ROM code protect disabled	RW
	ΙL		(b4)	Reserved bit	Set to 1.	RW
	<u> </u>		LV DOON	Voltage detection 0 circuit start bit ⁽²⁾	 0 : Voltage monitor 0 reset enabled after hardw are reset 1 : Voltage monitor 0 reset disabled after hardw are reset 	RW
\lfloor			(b6)	Reserved bit	Set to 1.	RW
			CSPROINI	Count source protect mode after reset select bit	0 : Count source protect mode enabled after reset 1 : Count source protect mode disabled after reset	RV

NOTES:

- 1. The OFS register is on the flash memory. Write to the OFS register with a program. After writing is completed, do not write additions to the OFS register.
- 2. Setting the LVD0ON bit is only valid after a hardw are reset. To use the pow er-on reset, set the LVD0ON bit to 0 (voltage monitor 0 reset enabled after hardw are reset).
- 3. If the block including the OFS register is erased, FFh is set to the OFS register.

Figure 16.3 Registers CSPR and OFS

16.1 Count Source Protection Mode Disabled

The count source of the watchdog timer is either the CPU clock or the XCIN clock divided by 32 (fC32) can be selected when count source protection mode is disabled. fC32 does not stop in wait mode, the watchdog timer to count continues.

Table 16.2 lists the Watchdog Timer Specifications (with Count Source Protection Mode Disabled).

Table 16.2 Watchdog Timer Specifications (with Count Source Protection Mode Disabled)

Item	Specifica	ation
Count source	CPU clock	XCIN clock divided by 32 (fC32)
Count operation	Decrement	
Period	$\frac{\text{Division ratio of prescaler (n)}}{\text{CPU clock}} \times \frac{\text{count value of watchdog}}{\text{timer (32768)}^{(1, 2)}}$	$\frac{32}{XCIN \ clock} \times \ count \ value \ of \ watchdog \ timer \ (m)^{(1)}$
	n: 16 or 128 (selected by WDC7 bit in WDC register) Example: When the CPU clock frequency is 8 MHz and prescaler divided by 16, the period is approximately 65.5 ms	m: 512, 1024, 2048 or 4096 (selected by bits CVS0 to CVS1 in the CSPR register) Example: When the XCIN clock frequency is 32.768 kHz and the count value by 512, the period is 0.5 s
Reset condition of watchdog timer	 Reset Write 00h to the WDTR register before writing FFI Underflow 	n
Count start condition	 The WDTON bit⁽³⁾ in the OFS register (0FFFFh) sel reset When the WDTON bit is set to 1 (watchdog timer The watchdog timer and prescaler stop after a rese is written to When the WDTON bit is set to 0 (watchdog timer The watchdog timer and prescaler start counting a timer to the watchdog timer a timer and prescaler start counting a timer a timer a timer a timer a timer a timer a timer a timer a timer a timer a timer a timer a timer a timer a timer a timer a timer a timer a timer a	is in stop state after reset) et and the count starts when the WDTS register starts automatically after exiting)
Count stop condition	Stop and wait modes (inherit the count from the held value after exiting modes)	Stop mode (inherit the count from the held value after exiting modes)
Operation at time of underflow	 When the PM12 bit in the PM1 register is set to 0 Watchdog timer interrupt When the PM12 bit in the PM1 register is set to 1 Watchdog timer reset (refer to 5.6 Watchdog Tin 	ner Reset)

NOTES:

- 1. The watchdog timer is reset when 00h is written to the WDTR register before FFh.
- 2. The prescaler is reset after the MCU is reset. Some errors in the period of the watchdog timer may be caused by the prescaler.
- 3. The WDTON bit cannot be changed by a program. To set the WDTON bit, write 0 to bit 0 of address 0FFFFh with a flash programmer.

16.2 Count Source Protection Mode Enabled

The count source of the watchdog timer is the low-speed on-chip oscillator clock when count source protection mode is enabled. If the CPU clock stops when a program is out of control, the clock can still be supplied to the watchdog timer.

Table 16.3 lists the Watchdog Timer Specifications (with Count Source Protection Mode Enabled).

Table 16.3	Watchdog Timer Specifications (with Count Source Protection Mode Enabled)
------------	---

Item	Specification
Count source	Low-speed on-chip oscillator clock
Count operation	Decrement
Period	<u>Count value of watchdog timer (4096)</u> Low-speed on-chip oscillator clock Example: Period is approximately 32.8 ms when the low-speed on- chip oscillator clock frequency is 125 kHz
Reset condition of watchdog timer	 Reset Write 00h to the WDTR register before writing FFh Underflow
Count start condition	 The WDTON bit⁽¹⁾ in the OFS register (0FFFFh) selects the operation of the watchdog timer after a reset. When the WDTON bit is set to 1 (watchdog timer is in stop state after reset) The watchdog timer and prescaler stop after a reset and the count starts when the WDTS register is written to When the WDTON bit is set to 0 (watchdog timer starts automatically after reset) The watchdog timer and prescaler start counting automatically after a reset
Count stop condition	None (The count does not stop in wait mode after the count starts. The MCU does not enter stop mode.)
Operation at time of underflow	Watchdog timer reset (refer to 5.6 Watchdog Timer Reset)
Registers, bits	 When setting the CSPPRO bit in the CSPR register to 1 (count source protection mode is enabled)⁽²⁾, the following are set automatically Set 0FFFh to the watchdog timer Set the CM14 bit in the CM1 register to 0 (low-speed on-chip oscillator on) Set the PM12 bit in the PM1 register to 1 (The watchdog timer is reset when watchdog timer underflows) The following conditions apply in count source protection mode Writing to the CM10 bit in the CM1 register is disabled (It remains unchanged even if it is set to 1. The MCU does not enter stop mode.) Writing to the CM14 bit in the CM1 register is disabled (It remains unchanged even if it is set to 1. The low-speed on-chip oscillator does not stop.)

NOTES:

- 1. The WDTON bit cannot be changed by a program. To set the WDTON bit, write 0 to bit 0 of address 0FFFFh with a flash programmer.
- 2. Even if 0 is written to the CSPROINI bit in the OFS register, the CSPRO bit is set to 1. The CSPROINI bit cannot be changed by a program. To set the CSPROINI bit, write 0 to bit 7 of address 0FFFFh with a flash programmer.

17. Timers

The MCU has two 8-bit timers with 8-bit prescalers, one 16-bit timer, and a timer with a 4-bit counter and an 8-bit counter. The two 8-bit timers with 8-bit prescalers are timer RA and timer RB. These timers contain a reload register to store the default value of the counter. The one 16-bit timer is timer RF and have input capture and output compare functions. The 4-bit and 8-bit counters are timer RE, and has an output compare function. All the timers operate independently.

Table 17.1 lists Functional Comparison of Timers.

	Item	Timer RA	Timer RB	Timer RE	Timer RF
Configuration		8-bit timer with 8-bit prescaler (with reload register)	8-bit timer with 8-bit prescaler (with reload register)	4-bit counter 8-bit counter	16-bit timer (with input capture and output compare)
Count		Decrement	Decrement	Increment	Increment
Count sources		• f1 • f2 • f8 • fOCO • fC32	• f1 • f2 • f8 • Timer RA underflow	• f4 • f8 • f32 • fC4	• f1 • f8 • f32
Function	Count of the internal count source	Timer mode	Timer mode	—	Output compare mode
	Count of the external count source	Event counter mode	_	—	—
	External pulse width/ period measurement	Pulse width measurement mode, pulse period measurement mode	_	—	Input capture mode
	PWM output	Pulse output mode ⁽¹⁾ , Event counter mode ⁽¹⁾	Programmable waveform generation mode	Output compare mode ⁽¹⁾	Output compare mode
	One-shot waveform output		Programmable one- shot generation mode, Programmable wait one-shot generation mode	—	_
	Timer	Timer mode (only fC32 count)	_	Real-time clock mode	—
Input pin		TRAIO	INT0	—	TRFI
Output pin		TRAO TRAIO	TRBO	TREO	TRFO00 to TRFO02, TRFO10 to TRFO12
Related interrupt		Timer RA interrupt, INT1 interrupt	Timer RB interrupt, INT0 interrupt	Timer RE interrupt	Timer RF interrupt, Compare 0 interrupt, Compare 1 interrupt, Capture interrupt
Timer stop)	Provided	Provided	Provided	Provided

Table 17.1	Functional Comparison of Timers
------------	---------------------------------

NOTE:

1. Rectangular waves are output in these modes. Since the waves are inverted at each overflow, the "H" and "L" level widths of the pulses are the same.

17.1 Timer RA

Timer RA is an 8-bit timer with an 8-bit prescaler.

The prescaler and timer each consist of a reload register and counter. The reload register and counter are allocated at the same address, and can be accessed when accessing registers TRAPRE and TRA (refer to **Tables 17.2 to 17.6 the Specifications of Each Mode**).

The count source for timer RA is the operating clock that regulates the timing of timer operations such as counting and reloading.

Figure 17.1 shows a Block Diagram of Timer RA. Figures 17.2 and 17.3 show the registers associated with timer RA.

Timer RA has the following five operating modes:

- Timer mode: The timer counts the internal count source.
- Pulse output mode: The timer counts the internal count source and outputs pulses of which polarity inverted by underflow of the timer.
- Event counter mode: The timer counts external pulses.
 - The timer measures the pulse width of an external pulse.
- Pulse width measurement mode:Pulse period measurement mode:

The timer measures the pulse period of an external pulse.



Figure 17.1 Block Diagram of Timer RA

(N)	X		Symbol	Address	After Reset	
	ТТТ	ΤT	TRACR	0100h	00h	
			Bit Symbol	Bit Name	Function	RV
			TSTART	Timer RA count start bit ⁽¹⁾	0 : Count stops 1 : Count starts	RW
			TCSTF	Timer RA count status flag ⁽¹⁾	0 : Count stops 1 : During count	RC
			TSTOP	Timer RA count forcible stop bit ⁽²⁾	When this bit is set to 1, the count is forcibly stopped. When read, its content is 0.	RW
			(b3)	Nothing is assigned. If necess When read, the content is 0.	ary, set to 0.	-
			TEDGF	Active edge judgment flag ^(3, 5)	0 : Active edge not received 1 : Active edge received (end of measurement period)	RV
			TUNDF	Timer RA underflow flag ^(3, 5)	0 : No underflow 1 : Underflow	RV
			 (b7-b6)	Nothing is assigned. If necess When read, the content is 0.	ary, set to 0.	- 1
2. V rd 3. E u 4. Ir	When th reset. Bits TED unchang n pulse register.	DGF and ged wh width	d TUNDF can nen 1 is w ritte measurement necessary to	o 1, bits TSTART and TCSTF and be set to 0 by w riting 0 to these en. t mode and pulse period measur	d registers TRAPRE and TRA are set to the value e bits by a program. How ever, their value remains rement mode, use the MOV instruction to set the T bits TEDGF and TUNDF, write 1 to them. er mode.	3
2. V rr 3. E u 4. Ir rr 5. S	When th reset. Bits TED unchang n pulse register. Set to 0	DGF and ged wirdth . If it is in time Contra	OP bit is set to d TUNDF can nen 1 is w ritte measurement necessary to	o 1, bits TSTART and TCSTF and be set to 0 by w riting 0 to these on. t mode and pulse period measur avoid changing the values of b	e bits by a program. How ever, their value remains rement mode, use the MOV instruction to set the T bits TEDGF and TUNDF, write 1 to them.	3
2. V rr 3. E u 4. Ir rr 5. S	When th reset. Bits TED unchang n pulse register. Set to 0	DGF and ged wirdth . If it is in time Contra	OP bit is set to d TUNDF can nen 1 is w ritte measurement necessary to r mode, pulse ol Register Symbol	b 1, bits TSTART and TCSTF and be set to 0 by writing 0 to these en. t mode and pulse period measur o avoid changing the values of b e output mode, and event counte Address	e bits by a program. How ever, their value remains rement mode, use the MOV instruction to set the T bits TEDGF and TUNDF, write 1 to them. er mode. After Reset	3
2. V rr 3. E u 4. Ir rr 5. S	When th reset. Bits TED unchang n pulse register. Set to 0	DGF and ged wirdth . If it is in time Contra	OP bit is set to d TUNDF can nen 1 is w ritte measurement necessary to r mode, pulse ol Register Symbol TRAIOC	Address 01, bits TSTART and TCSTF and be set to 0 by writing 0 to these en. t mode and pulse period measur o avoid changing the values of b o output mode, and event counte 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	e bits by a program. How ever, their value remains rement mode, use the MOV instruction to set the T bits TEDGF and TUNDF, write 1 to them. er mode. After Reset 00h	3 IRACR
2. V rr 3. E u 4. Ir rr 5. S	When th reset. Bits TED unchang n pulse register. Set to 0	DGF and ged wirdth . If it is in time Contra	OP bit is set to d TUNDF can nen 1 is w ritte measurement necessary to r mode, pulse ol Register Symbol	Address 010, bits TSTART and TCSTF and be set to 0 by writing 0 to these on. 1 mode and pulse period measure 1 avoid changing the values of b 2 output mode, and event counter 0 Address 0101h Bit Name	e bits by a program. How ever, their value remains rement mode, use the MOV instruction to set the T bits TEDGF and TUNDF, write 1 to them. er mode. After Reset	
2. V rr 3. E u 4. Ir rr 5. S	When th reset. Bits TED unchang n pulse register. Set to 0	DGF and ged wirdth . If it is in time Contra	OP bit is set to d TUNDF can nen 1 is writte measurement necessary to r mode, pulse ol Register Symbol TRAIOC Bit Symbol	Address 010, bits TSTART and TCSTF and be set to 0 by writing 0 to these on. 1 mode and pulse period measure 1 avoid changing the values of b 2 output mode, and event counter 0 Address 0101h Bit Name	e bits by a program. How ever, their value remains rement mode, use the MOV instruction to set the T bits TEDGF and TUNDF, write 1 to them. er mode. After Reset 00h Function	S IRACR
2. V rr 3. E u 4. Ir rr 5. S	When th reset. Bits TED unchang n pulse register. Set to 0	DGF and ged wirdth . If it is in time Contra	OP bit is set to d TUNDF can neen 1 is w ritte measurement necessary to r mode, pulse ol Register Symbol TRAIOC Bit Symbol TEDGSEL	Address 01, bits TSTART and TCSTF and be set to 0 by writing 0 to these on. The mode and pulse period measure of avoid changing the values of b output mode, and event counted Address 0101h Bit Name TRAIO polarity switch bit	e bits by a program. How ever, their value remains rement mode, use the MOV instruction to set the T bits TEDGF and TUNDF, write 1 to them. er mode. After Reset 00h Function	S IRACR RV RV
2. V rr 3. E u 4. Ir rr 5. S	When th reset. Bits TED unchang n pulse register. Set to 0	DGF and ged wirdth . If it is in time Contra	OP bit is set to d TUNDF can nen 1 is writte measurement necessary to r mode, pulse ol Register Symbol TRAIOC Bit Symbol TEDGSEL TOPCR	Address 010, bits TSTART and TCSTF and be set to 0 by writing 0 to these on. Trode and pulse period measure of avoid changing the values of b output mode, and event counted Address 0101h Bit Name TRAIO polarity sw itch bit TRAIO output control bit	e bits by a program. How ever, their value remains rement mode, use the MOV instruction to set the T bits TEDGF and TUNDF, write 1 to them. er mode. After Reset 00h Function	RV RV RV
2. V rr 3. E u 4. Ir rr 5. S	When th reset. Bits TED unchang n pulse register. Set to 0	DGF and ged wirdth . If it is in time Contra	OP bit is set to d TUNDF can nen 1 is writte measurement necessary to r mode, pulse ol Register Symbol TRAIOC Bit Symbol TEDGSEL TOPCR TOENA	Address 01, bits TSTART and TCSTF and be set to 0 by writing 0 to these on. to mode and pulse period measure avoid changing the values of b coutput mode, and event counter address 0101h Bit Name TRAIO polarity switch bit TRAIO output control bit TRAIO output enable bit	e bits by a program. How ever, their value remains rement mode, use the MOV instruction to set the T bits TEDGF and TUNDF, write 1 to them. er mode. After Reset 00h Function	3





Г

17.1.1 Timer Mode

In this mode, the timer counts an internally generated count source (refer to **Table 17.2 Timer Mode Specifications**).

Figure 17.4 shows TRAIOC Register in Timer Mode.

Table 17.2 Timer Mode Specification

Item	Specification
Count sources	f1, f2, f8, fOCO, fC32
Count operations	Decrement
	 When the timer underflows, the contents of the reload register are reloaded and the count is continued.
Divide ratio	1/(n+1)(m+1)
	n: Value set in TRAPRE register, m: Value set in TRA register
Count start condition	1 (count starts) is written to the TSTART bit in the TRACR register.
Count stop conditions	 0 (count stops) is written to the TSTART bit in the TRACR register.
	 1 (count forcibly stops) is written to the TSTOP bit in the TRACR register.
Interrupt request	When timer RA underflows [timer RA interrupt].
generation timing	
INT1/TRAIO pin	Programmable I/O port, or INT1 interrupt input
function	
TRAO pin function	Programmable I/O port
Read from timer	The count value can be read by reading registers TRA and TRAPRE.
Write to timer	 When registers TRAPRE and TRA are written while the count is stopped, values are written to both the reload register and counter. When registers TRAPRE and TRA are written during the count, values are written to the reload register and counter (refer to 17.1.1.1 Timer Write Control during Count Operation).

	b5 b4 b3 b2 b1 b0 0 0 0 0 0 0	Symbol	Address	After Reset	
ΤT		TRAIOC	0101h	00h	
		Bit Symbol	Bit Name	Function	RW
		TEDGSEL	TRAIO polarity switch bit	Set to 0 in timer mode.	RW
		TOPCR	TRAIO output control bit		RW
		TOENA	TRAO output enable bit		RW
		TIOSEL	INT1/TRAIO select bit	0 : INT1/TRAIO pin (P1_7) 1 : INT1/TRAIO pin (P1_5)	RW
		TIPF0	TRAIO input filter select bits	Set to 0 in timer mode.	RW
	L	TIPF1			
		 (b7-b6)	Nothing is assigned. If neces When read, the content is 0.	sary, set to 0.	_

Figure 17.4 TRAIOC Register in Timer Mode

17.1.1.1 Timer Write Control during Count Operation

Timer RA has a prescaler and a timer (which counts the prescaler underflows). The prescaler and timer each consist of a reload register and a counter. When writing to the prescaler or timer, values are written to both the reload register and counter.

However, values are transferred from the reload register to the counter of the prescaler in synchronization with the count source. In addition, values are transferred from the reload register to the counter of the timer in synchronization with prescaler underflows. Therefore, if the prescaler or timer is written to when count operation is in progress, the counter value is not updated immediately after the WRITE instruction is executed. Figure 17.5 shows an Operating Example of Timer RA when Counter Value is Rewritten during Count Operation.



17.1.2 Pulse Output Mode

In pulse output mode, the internally generated count source is counted, and a pulse with inverted polarity is output from the TRAIO pin each time the timer underflows (refer to **Table 17.3 Pulse Output Mode Specifications**).

Figure 17.6 shows TRAIOC Register in Pulse Output Mode.

Table 17.3	Pulse Output Mode Specifications
------------	----------------------------------

Item	Specification
Count sources	f1, f2, f8, fOCO, fC32
Count operations	 Decrement When the timer underflows, the contents in the reload register is reloaded and the count is continued.
Divide ratio	1/(n+1)(m+1) n: Value set in TRAPRE register, m: Value set in TRA register
Count start condition	1 (count starts) is written to the TSTART bit in the TRACR register.
Count stop conditions	 0 (count stops) is written to the TSTART bit in the TRACR register. 1 (count forcibly stops) is written to the TSTOP bit in the TRACR register.
Interrupt request generation timing	When timer RA underflows [timer RA interrupt].
INT1/TRAIO pin function	Pulse output, programmable output port, or INT1 interrupt ⁽¹⁾
TRAO pin function	Programmable I/O port or inverted output of TRAIO ⁽¹⁾
Read from timer	The count value can be read by reading registers TRA and TRAPRE.
Write to timer	 When registers TRAPRE and TRA are written while the count is stopped, values are written to both the reload register and counter. When registers TRAPRE and TRA are written during the count, values are written to the reload register and counter (refer to 17.1.1.1 Timer Write Control during Count Operation).
Select functions	 TRAIO output polarity switch function The TEDGSEL bit in the TRAIOC register selects the level at the start of pulse output.⁽¹⁾ TRAO output function Pulses inverted from the TRAIO output polarity can be output from the TRAO pin (selectable by the TOENA bit in the TRAIOC register). TRAO pin select function P3_0 or P3_7 is selected by the TRAOSEL bit in the PINSR2 register. Pulse output stop function <u>Output from the TRAIO pin is stopped by the TOPCR bit in the TRAIOC register.</u> INT1/TRAIO pin select function P1_7 or P1_5 is selected by the TIOSEL bit in the TRAIOC register.

NOTE:

1. The level of the output pulse becomes the level when the pulse output starts when the TRAMR register is written to.



Figure 17.6 TRAIOC Register in Pulse Output Mode

17.1.3 Event Counter Mode

In event counter mode, external signal inputs to the $\overline{INT1}/TRAIO$ pin are counted (refer to **Table 17.4 Event Counter Mode Specifications**).

Figure 17.7 shows TRAIOC Register in Event Counter Mode.

Table 17.4 Event Counter Mode Specification

Item	Specification
Count source	External signal which is input to TRAIO pin (active edge selectable by a program)
Count operations	• Decrement
	 When the timer underflows, the contents of the reload register are reloaded and the count is continued.
Divide ratio	1/(n+1)(m+1)
	n: setting value of TRAPRE register, m: setting value of TRA register
Count start condition	1 (count starts) is written to the TSTART bit in the TRACR register.
Count stop conditions	 0 (count stops) is written to the TSTART bit in the TRACR register.
	 1 (count forcibly stops) is written to the TSTOP bit in the TRACR register.
Interrupt request	 When timer RA underflows [timer RA interrupt].
generation timing	
INT1/TRAIO pin	Count source input (INT1 interrupt input)
function	
TRAO pin function	Programmable I/O port or pulse output ⁽¹⁾
Read from timer	The count value can be read by reading registers TRA and TRAPRE.
Write to timer	• When registers TRAPRE and TRA are written while the count is stopped, values
	are written to both the reload register and counter.
	• When registers TRAPRE and TRA are written during the count, values are
	written to the reload register and counter (refer to 17.1.1.1 Timer Write Control
Select functions	during Count Operation).
	• NT1 input polarity switch function
	The TEDGSEL bit in the TRAIOC register selects the active edge of the count source.
	Count source input pin select function
	P1 7 or P1 5 is selected by the TIOSEL bit in the TRAIOC register.
	• Pulse output function
	Pulses of inverted polarity can be output from the TRAO pin each time the timer
	underflows (selectable by the TOENA bit in the TRAIOC register). ⁽¹⁾
	TRAO pin select function
	P3_0 or P3_7 is selected by the TRAOSEL bit in the PINSR2 register.
	• Digital filter function
	Bits TIPF0 and TIPF1 in the TRAIOC register enable or disable the digital filter
	and select the sampling frequency.

NOTE:

1. The level of the output pulse becomes the level when the pulse output starts when the TRAMR register is written to.



Figure 17.7 TRAIOC Register in Event Counter Mode

17.1.4 Pulse Width Measurement Mode

In pulse width measurement mode, the pulse width of an external signal input to the INT1/TRAIO pin is measured (refer to **Table 17.5 Pulse Width Measurement Mode Specifications**).

Figure 17.8 shows TRAIOC Register in Pulse Width Measurement Mode and Figure 17.9 shows an Operating Example of Pulse Width Measurement Mode.

Table 17.5	Pulse Width Measurement Mode Specifications
------------	---

Item	Specification
Count sources	f1, f2, f8, fOCO, fC32
Count operations	Decrement
	• Continuously counts the selected signal only when measurement pulse is "H"
	level, or conversely only "L" level.
	• When the timer underflows, the contents of the reload register are reloaded
	and the count is continued.
Count start condition	1 (count starts) is written to the TSTART bit in the TRACR register.
Count stop conditions	• 0 (count stops) is written to the TSTART bit in the TRACR register.
	• 1 (count forcibly stops) is written to the TSTOP bit in the TRACR register.
Interrupt request	When timer RA underflows [timer RA interrupt].
generation timing	• Rising or falling of the TRAIO input (end of measurement period) [timer RA
	interrupt]
INT1/TRAIO pin function	Measured pulse input (INT1 interrupt input)
TRAO pin function	Programmable I/O port
Read from timer	The count value can be read by reading registers TRA and TRAPRE.
Write to timer	• When registers TRAPRE and TRA are written while the count is stopped,
	values are written to both the reload register and counter.
	• When registers TRAPRE and TRA are written during the count, values are
	written to the reload register and counter (refer to 17.1.1.1 Timer Write
	Control during Count Operation).
Select functions	Measurement level select
	• The TEDGSEL bit in the TRAIOC register selects the "H" or "L" level period.
	Measured pulse input pin select function
	P1_7 or P1_5 is selected by the TIOSEL bit in the TRAIOC register.
	• Digital filter function
	Bits TIPF0 and TIPF1 in the TRAIOC register enable or disable the digital
	filter and select the sampling frequency.



Figure 17.8 TRAIOC Register in Pulse Width Measurement Mode





17.1.5 Pulse Period Measurement Mode

In pulse period measurement mode, the pulse period of an external signal input to the INT1/TRAIO pin is measured (refer to **Table 17.6 Pulse Period Measurement Mode Specifications**).

Figure 17.10 shows TRAIOC Register in Pulse Period Measurement Mode and Figure 17.11 shows an Operating Example of Pulse Period Measurement Mode.

Item	Specification
Count sources	f1, f2, f8, fOCO, fC32
Count operations	 Decrement After the active edge of the measured pulse is input, the contents of the read- out buffer are retained at the first underflow of timer RA prescaler. Then timer RA reloads the contents in the reload register at the second underflow of timer RA prescaler and continues counting.
Count start condition	1 (count starts) is written to the TSTART bit in the TRACR register.
Count stop conditions	 0 (count stops) is written to TSTART bit in the TRACR register. 1 (count forcibly stops) is written to the TSTOP bit in the TRACR register.
Interrupt request generation timing	 When timer RA underflows or reloads [timer RA interrupt]. Rising or falling of the TRAIO input (end of measurement period) [timer RA interrupt]
INT1/TRAIO pin function	Measured pulse input ⁽¹⁾ (INT1 interrupt input)
TRAO pin function	Programmable I/O port
Read from timer	The count value can be read by reading registers TRA and TRAPRE.
Write to timer	 When registers TRAPRE and TRA are written while the count is stopped, values are written to both the reload register and counter. When registers TRAPRE and TRA are written during the count, values are written to the reload register and counter (refer to 17.1.1.1 Timer Write Control during Count Operation).
Select functions	 Measurement period select The TEDGSEL bit in the TRAIOC register selects the measurement period of the input pulse. Measured pulse input pin select function P1_7 or P1_5 is selected by the TIOSEL bit in the TRAIOC register. Digital filter function Bits TIPF0 and TIPF1 in the TRAIOC register enable or disable the digital filter and select the sampling frequency.

NOTE:

1. Input a pulse with a period longer than twice the timer RA prescaler period. Input a pulse with a longer "H" and "L" width than the timer RA prescaler period. If a pulse with a shorter period is input to the TRAIO pin, the input may be ignored.



Figure 17.10 TRAIOC Register in Pulse Period Measurement Mode


17.1.6 Notes on Timer RA

- Timer RA stops counting after a reset. Set the values in the timer RA and timer RA prescalers before the count starts.
- Even if the prescaler and timer RA are read out in 16-bit units, these registers are read 1 byte at a time by the MCU. Consequently, the timer value may be updated during the period when these two registers are being read.
- In pulse period measurement mode, bits TEDGF and TUNDF in the TRACR register can be set to 0 by writing 0 to these bits by a program. However, these bits remain unchanged if 1 is written. When using the READ-MODIFY-WRITE instruction for the TRACR register, the TEDGF or TUNDF bit may be set to 0 although these bits are set to 1 while the instruction is being executed. In this case, write 1 to the TEDGF or TUNDF bit which is not supposed to be set to 0 with the MOV instruction.
- When changing to pulse period measurement mode from another mode, the contents of bits TEDGF and TUNDF are undefined. Write 0 to bits TEDGF and TUNDF before the count starts.
- The TEDGF bit may be set to 1 by the first timer RA prescaler underflow generated after the count starts.
- When using the pulse period measurement mode, leave two or more periods of the timer RA prescaler immediately after the count starts, then set the TEDGF bit to 0.
- The TCSTF bit retains 0 (count stops) for 0 to 1 cycle of the count source after setting the TSTART bit to 1 (count starts) while the count is stopped.

During this time, do not access registers associated with timer $RA^{(1)}$ other than the TCSTF bit. Timer RA starts counting at the first valid edge of the count source after The TCSTF bit is set to 1 (during count). The TCSTF bit remains 1 for 0 to 1 cycle of the count source after setting the TSTART bit to 0 (count stops) while the count is in progress. Timer RA counting is stopped when the TCSTF bit is set to 0. During this time, do not access registers associated with timer $RA^{(1)}$ other than the TCSTF bit.

NOTE:

1. Registers associated with timer RA: TRACR, TRAIOC, TRAMR, TRAPRE, and TRA.

- When the TRAPRE register is continuously written during count operation (TCSTF bit is set to 1), allow three or more cycles of the count source clock for each write interval.
- When the TRA register is continuously written during count operation (TCSTF bit is set to 1), allow three or more cycles of the prescaler underflow for each write interval.

17.2 Timer RB

Timer RB is an 8-bit timer with an 8-bit prescaler.

The prescaler and timer each consist of a reload register and counter (refer to **Tables 17.7 to 17.10 the Specifications of Each Mode**).

Timer RB has timer RB primary and timer RB secondary as reload registers.

The count source for timer RB is the operating clock that regulates the timing of timer operations such as counting and reloading.

Figure 17.12 shows a Block Diagram of Timer RB. Figures 17.13 to 17.15 show the registers associated with timer RB.

Timer RB has four operation modes listed as follows:

• Timer mode:

The timer counts an internal count source (peripheral function clock or timer RA underflows). The timer outputs pulses of a given width successively.

- Programmable waveform generation mode:
- Programmable one-shot generation mode:

• Programmable wait one-shot generation mode:

The timer outputs a one-shot pulse. The timer outputs a delayed one-shot pulse.



Figure 17.12 Block Diagram of Timer RB



Figure 17.13 Registers TRBCR and TRBOCR

Bit Symbol Bit Name Function RM TOPL bit Function RM TOCNT Timer RB output switch bit RM NOSTG One-shot trigger control bit RM NOSEG One-shot trigger polarity RM Select bit RM RM - Nothing is assigned. If necessary, set to 0. - - (b7-b4) When read, the content is 0. - Finer RB Mode Register Symbol Address After Reset TMOD0 Bit Symbol Bit Name Function RM Mothing is assigned. If necessary, set to 0. 0 0: Timer mode 0 0: Timer mode RM TMOD0 Symbol Bit Name Function RM Timer RB operating mode 0 0: Timer mode 0 0: Timer mode NR TMOD1 Timer RB operating mode 0 0: Timer mode NR RM			Symbol	Address 010Ah	After Reset 00h	
TOPL Timer RB output level select bit Function varies depending on operating mode. RM TOCNT Timer RB output switch bit RM INOSEG One-shot trigger control bit RM INOSEG One-shot trigger polarity select bit RM INOSEG One-shot trigger polarity select bit RM INOSEG One-shot trigger polarity select bit RM INOSEG One-shot trigger polarity select bit RM INOSEG One-shot trigger polarity select bit RM INOSEG One-shot trigger polarity when read, the content is 0.						D\\/
IOPL bit IN TOCNT Timer RB output switch bit RM INOSTG One-shot trigger polarity RM INOSEG Symbol Address After Reset ITMER Bit Symbol Bit Name Function RM INODO Select bits 0 0 : Timer mode RM RM ITMOD1 Timer RB operating mode ot to 0 : Programmable one-shot generation mode RM ITMOD1 Timer RB count source 0 : When read, the content is 0. ITWRC Timer RB count source Sist 0 : f1 0 : f1 RM IO Timer RB count source Sist 0 : f1 0 : f1 RM IO Timer RB count source Sist 0 : f1 RM 0 : f1 RM IO Timer RB cou			ыс бульог			RVV
IOUNI INOSTG One-shot trigger control bit RM INOSTG One-shot trigger polarity select bit RM INOSEG One-shot trigger polarity select bit RM INOSEG One-shot trigger polarity select bit RM Immer RB Mode Register Immer RB Mode Register Immer RB Mode Register Immer RB operating mode Immer RB operating mode Immer RB operating mode Immer RB operating mode RM Immer RB operating mode Immer RB operating mode Immer RB operating mode Immer RB operating mode RM Immer RB operating mode Immer RB operating mode Immer RB operating mode Immer RB operating mode RM Immer RB operating mode Immer RB operating mode Immer RB operating mode RM RM Immer RB operating mode Immer RB operating mode Immer RB operating mode RM RM Immer RB operating mode Immer RB operating mode Immer RB operating mode RM RM Immer RB operating mode Immer RB operation mode Immer RB operation mode Immer RB operation mode RM Immer RB operation Immer RB count source Immer RB operation is 0. Immer RB operation is 0. Immer			TOPL	bit		RW
INOSIG			TOCNT	Timer RB output switch bit		RW
INUSES select bit RW			INOSTG	One-shot trigger control bit		RW
(b7-b4) When read, the content is 0. — Timer RB Mode Register b7 b6 b5 b4 b3 b2 b1 b0 Symbol Address After Reset DT b6 b5 b4 b3 b2 b1 b0 TRBMR 010Bh 00h RM Bit Symbol Bit Name Function RM TMOD0 Bit Name Function RM TMOD0 Timer RB operating mode b1 b0 0 0 : Timer mode RM TMOD1 Timer RB operating mode b1 b0 0 0 : Timer mode RM TMOD1 Timer RB operating mode b1 b0 RM RM TMOD1 Timer RB operating mode b1 b0 RM RM TMOD1 Timer RB write control bit(2) 0 : Write to reload register and counter RM TWRC Timer RB write control bit(2) 0 : Write to reload register and counter RM TCK0 Timer RB count source b5 b4 0 0 : f1 RM 1 : f2 RM 10 : Timer RA underflow T1 : f2 RM TCK0 Torking is assigned. If necessary, set to 0. — — — (b6) When read, the content is 0. —			INOSEG			RW
b7 b6 b5 b4 b3 b2 b1 b0 Symbol Address After Reset TRBMR 010Bh 00h Bit Symbol Bit Name Function RM TMOD0 select bits ⁽¹⁾ 0 0 : Timer mode 0 1 : Programmable waveform generation mode RM TMOD1 Timer RB operating mode 1 : Programmable waveform generation mode RM TMOD1 Timer RB operating mode 1 : Programmable wait one-shot generation mode RM - Nothing is assigned. If necessary, set to 0. - - (b2) When read, the content is 0. - - TWRC Timer RB count source 0 : Write to reload register and counter RM 1 : Write to reload register only RM 0 1 : f8 RM 1 : CK0 select bits ⁽¹⁾ 0 0 : f1 RM 0 1 : f8 1 0 : Timer RA underflow RM 1 : CK1 Timer RB count source - - (b6) When read, the content is 0. - - - Nothing is assigned. If necessary, set to 0. - - (b6) Timer RB count source 0 : Provides count source			 (b7-b4)		sary, set to 0.	_
Symbol Address After Reset TRBMR 010Bh 00h Bit Symbol Bit Name Function RM TMOD0 Bit Name Function RM TMOD0 Select bits ⁽¹⁾ 0 0 : Timer mode 0 0 : Timer mode RM TMOD1 Timer RB operating mode b1 to 0 0 : Timer mode RM TMOD1 Timer RB operating mode b1 to 0 0 : Timer mode RM TMOD1 Timer RB operating mode b1 to Programmable waveform generation mode RM TMOD1 Timer RB operating mode 1 : Programmable wait one-shot generation mode RM - Nothing is assigned. If necessary, set to 0. - - (b2) When read, the control bit ⁽²⁾ 0 : Write to reload register and counter RM TCK0 Timer RB count source 564 0 0 : f1 RM 0 1 : f8 1 0 : Timer RA underflow RM RM 1 : f2 RM 1 : f2 RM - Nothing is assigned. If necessary, set to 0. - - (b6) When read, the content is 0. - <td>imer RB N</td> <td>/lode Re</td> <td>gister</td> <td></td> <td></td> <td></td>	imer RB N	/lode Re	gister			
TRBMR 010Bh 00h Bit Symbol Bit Name Function RM TMOD0 Select bits ⁽¹⁾ 0 : Timer mode 0 : Timer mode RM TMOD1 TMOD1 Difference 0 : Timer mode RM TMOD1 TMOD1 Difference RM 0 : Timer mode RM TMOD1 TMOD1 Difference Difference RM RM TMOD1 TMOD1 Difference RM RM RM TMRC Timer RB write control bit ⁽²⁾ 0 : Write to reload register and counter RM TCK0 Timer RB count source Bible Bible RM 0 : f1 RM Difference TCK1 Timer RB count source Bible Difference RM Difference TCK1 Timer RB count source Difference Cites fit Cites fit Cites fit </td <td>b7 b6 b5 b4 b</td> <td>3 b2 b1 b0</td> <td></td> <td></td> <td></td> <td></td>	b7 b6 b5 b4 b	3 b2 b1 b0				
TRBMR 010Bh 00h Bit Symbol Bit Name Function RM TMOD0 Select bits ⁽¹⁾ 0 0 : Timer mode RM 0 1 : Programmable waveform generation mode 1 0 : Programmable one-shot generation mode RM TMOD1 TMOD1 1 : Programmable one-shot generation mode RM - Nothing is assigned. If necessary, set to 0. - - (b2) When read, the content is 0. - - TWRC Timer RB write control bit ⁽²⁾ 0 : Write to reload register and counter RM TCK0 Select bits ⁽¹⁾ 0 : Stb4 0 0 : f1 RM 0 : Timer RB count source Stb4 0 0 : f1 RM TCK1 TCK1 0 : Timer RA underflow RM 1 : f2 RM 1 : f2 RM - Nothing is assigned. If necessary, set to 0. - - (b6) When read, the content is 0. - - - TCKCUT Timer RB count source 0 : Provides count source - (b6) When read, the content is 0. - - - <		МП	Symbol	Address	After Reset	
Bit Symbol Bit Name Function RW Timer RB operating mode bit b0 0 0 : Timer mode RW TMOD0 select bits ⁽¹⁾ 0 0 : Timer mode RW TMOD1 Timer RB operating mode bit b0 0 0 : Timer mode RW TMOD1 Timer RB operating mode bit b0 0 0 : Timer mode RW TMOD1 Timer RB operating mode bit b0 0 0 : Timer mode RW TMOD1 Tool : Programmable waveform generation mode RW TMOD1 Timer RB write control bit ⁽²⁾ 0 : Write to reload register and counter RW TWRC Timer RB write control bit ⁽²⁾ 0 : Write to reload register only RW TCK0 Timer RB count source bit b4 0 0 : f1 RW TCK1 Timer RB count source bit b4 RW RW TCK1 Tool : f1 RW RW RW RW TCK0 Timer RB count source 0 : Provides count source - - (b6) When read, the content is 0. - - - - TCKCUT Timer RB count source			•			
Timer RB operating mode b1 b0 0 0 : Timer mode RM TMOD0 select bits ⁽¹⁾ 0 0 : Timer mode RM TMOD1 TMOD1 Programmable waveform generation mode RM TMOD1 TMOD1 Programmable waveform generation mode RM - Nothing is assigned. If necessary, set to 0. - - (b2) When read, the content is 0. - - TWRC Timer RB write control bit ⁽²⁾ 0 : Write to reload register and counter RM TCK0 Timer RB count source b5 b4 0 0 : f1 RM TCK1 TCK1 Timer RA underflow 1 : f2 RM - Nothing is assigned. If necessary, set to 0. - - (b6) When read, the content is 0. - - - Nothing is assigned. If necessary, set to 0. - - (b6) When read, the content is 0. - - TCKCUT Timer RB count source 0 : Provides count source - (b6) TCKCUT Timer RB count source 0 : Provides count source RM . .						RW
Image: Constraint of the select bits (1) 0 0 : Timer mode 0 0 : Timer mode RM Image: Constraint of the select bits (1) Image: Constraint of the select bits (1) 0 0 : Timer mode RM Image: Constraint of the select bits (1) Image: Conselect bits (1) Image: Const			Bit Cymioon			
Image: Constraint of the second se			TMODO			RW
Image: Description of the text of the text of t						
Image: Time of the content is 0. Image: Time of the content is 0. <td< td=""><td></td><td></td><td></td><td>-</td><td></td><td></td></td<>				-		
Involution Involution <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>						
(b2) When read, the content is 0.			TWOD1			RVV
(b2) When read, the content is 0.				Nothing is assigned. If neces	sary set to 0	
TWRC Timer RB w rite control bit ⁽²⁾ 0 : Write to reload register and counter RW 1 : Write to reload register only RW TCK0 Timer RB count source select bits ⁽¹⁾ b5 b4 RW TCK1 TCK1 0 : Timer RA underflow RW Nothing is assigned. If necessary, set to 0. (b6) When read, the content is 0. TCKCUT Timer RB count source cutoff bit ⁽¹⁾ 0 : Provides count source 1 : Cuts off count source RW NOTES: NOTES: RW RW RW			(b2)		Sary, set to 0.	—
Image: Notest of the content is 0. Image: Notest o			()		0 : Write to reload register and counter	
TCK0 Timer RB count source select bits ⁽¹⁾ b5 b4 0 0 : f1 0 1 : f8 1 0 : Timer RA underflow 1 1 : f2 RW - Nothing is assigned. If necessary, set to 0. (b6) - - TCKCUT Timer RB count source cutoff bit ⁽¹⁾ 0 : Provides count source 1 : Cuts off count source - NOTES: -			TWRC			RW
TCK0 select bits ⁽¹⁾ 0 0 : f1 RW TCK1 TCK1 0 : Timer RA underflow RW TCK1 TCK1 1 : f2 RW - Nothing is assigned. If necessary, set to 0. - (b6) When read, the content is 0. - TCKCUT Timer RB count source 0 : Provides count source RW 1 : Cuts off count source RW				Timor PR count course	• •	
Image: Construction 0 1 : f8 TCK1 1 0 : Timer RA underflow Image: Construction RW Image: Construction RW Image: Construction Image: Construction			TOKO			
TCK1 1 0 : Timer RA underflow RW - Nothing is assigned. If necessary, set to 0. - (b6) When read, the content is 0. - TCKCUT Timer RB count source 0 : Provides count source 1 : Cuts off count source RW			ICKU			RVV
TCK1 1 1 : f2 RW — Nothing is assigned. If necessary, set to 0. — (b6) When read, the content is 0. — TCKCUT Timer RB count source cutoff bit ⁽¹⁾ 0 : Provides count source 1 : Cuts off count source RW				-		
Interview Inter			TOUL			-
(b6) When read, the content is 0. — TCKCUT Timer RB count source cutoff bit ⁽¹⁾ 0 : Provides count source 1 : Cuts off count source RW			ICK1			RW
(b6) When read, the content is 0. — TCKCUT Timer RB count source cutoff bit ⁽¹⁾ 0 : Provides count source 1 : Cuts off count source RW						
TCKCUT Timer RB count source cutoff bit ⁽¹⁾ 0 : Provides count source 1 : Cuts off count source RW NOTES: RV			— (b6)		sary, set to U.	_
ICKCUI cutoff bit ⁽¹⁾ 1 : Cuts off count source RW NOTES: RW			(00)			
NOTES:			TCKCUT			RW
					1 : Cuts off count source	
 Change bits TMOD1 and TMOD0; TCK1 and TCK0; and TCKCUT when both the TSTART and TCSTF bits in the TRBCI 						
					KCUT when both the TSTART and TCSTF bits in the T	RBCF
register set to 0 (count stops).			O (accurate atom	c)		



	Symbol	Address	After Reset	
	TRBPRE	010Ch	FFh	
	Mode	Function	Setting Range	R١
	Timer mode	Counts an internal count source or timer RA underflow s	00h to FFh	R
	Programmable w aveform generation mode		00h to FFh	R
	Programmable one-shot generation mode		00h to FFh	R
	Programmable w ait one-shot generation mode		00h to FFh	R
NOTE:		set to 1, the TRBPRE register is set to FFh.		
	dary Register ^(3, 4)	Adrees	After Depet	
	Symbol TRBSC	Address 010Dh	After Reset FFh	
	Mode	Function	Setting Range	R
	— Timer mode	Disabled	00h to FFh	-
	Programmable w aveform generation mode	Counts timer RB prescaler underflow s ⁽¹⁾	00h to FFh	wo
	Programmable one-shot	Disabled	00h to FFh	
	generation mode			
	Programmable w ait one-shot generation mode of registers TRBPR and TRBSC a	Counts timer RB prescaler underflow s (one-shot width is counted) are reloaded to the counter alternately and coun		wc
 The values The count v When the T To w rite to Write th Write th Write th 	Programmable w ait one-shot generation mode of registers TRBPR and TRBSC a value can be read out by reading STOP bit in the TRBCR register is the TRBSC register, perform the f e value to the TRBSC register. e value to the TRBPR register. (If	(one-shot width is counted) are reloaded to the counter alternately and coun the TRBPR register even when the secondary p set to 1, the TRBSC register is set to FFh.	ted. beriod is being cou	
 The values The count v When the T To w rite to Write th Write th Write th 	Programmable w ait one-shot generation mode of registers TRBPR and TRBSC a value can be read out by reading of STOP bit in the TRBCR register is the TRBSC register, perform the f e value to the TRBSC register. e value to the TRBPR register. (If y Register ⁽²⁾	(one-shot width is counted) are reloaded to the counter alternately and coun the TRBPR register even when the secondary p set to 1, the TRBSC register is set to FFh. follow ing steps. the value does not change, write the same valu Address	ted. beriod is being cou ue second time.) After Reset	
 The values The count v When the T To w rite to Write th Write th Write th 	Programmable w ait one-shot generation mode of registers TRBPR and TRBSC a value can be read out by reading of STOP bit in the TRBCR register is the TRBSC register, perform the f e value to the TRBSC register. e value to the TRBPR register. (If y Register ⁽²⁾ Symbol TRBPR	(one-shot width is counted) are reloaded to the counter alternately and coun the TRBPR register even when the secondary p set to 1, the TRBSC register is set to FFh. follow ing steps. the value does not change, write the same valu Address 010Eh	ted. beriod is being cou ue second time.) After Reset FFh	nted
 The values The count v When the T To w rite to Write th Write th Write th 	Programmable w ait one-shot generation mode of registers TRBPR and TRBSC a value can be read out by reading of STOP bit in the TRBCR register is the TRBSC register, perform the f e value to the TRBSC register. e value to the TRBPR register. (If y Register ⁽²⁾	(one-shot width is counted) are reloaded to the counter alternately and coun the TRBPR register even when the secondary p set to 1, the TRBSC register is set to FFh. follow ing steps. the value does not change, write the same valu Address 010Eh Function	ted. beriod is being cou ue second time.) After Reset FFh Setting Range	nted
 The values The count v When the T To w rite to Write th Write th Write th 	Programmable w ait one-shot generation mode of registers TRBPR and TRBSC a value can be read out by reading of STOP bit in the TRBCR register is the TRBSC register, perform the f e value to the TRBSC register. e value to the TRBPR register. (If y Register ⁽²⁾ Symbol TRBPR Mode Timer mode	(one-shot width is counted) are reloaded to the counter alternately and coun the TRBPR register even when the secondary p set to 1, the TRBSC register is set to FFh. following steps. the value does not change, write the same valu Address 010Eh Function Counts timer RB prescaler underflow s	ted. beriod is being cou ue second time.) After Reset FFh Setting Range 00h to FFh	nted
 The values The count v When the T To w rite to Write th Write th Write th 	Programmable w ait one-shot generation mode of registers TRBPR and TRBSC a value can be read out by reading of STOP bit in the TRBCR register is the TRBSC register, perform the f e value to the TRBSC register. e value to the TRBPR register. (If y Register ⁽²⁾ Symbol TRBPR Mode Timer mode Programmable w aveform generation mode	(one-shot width is counted) are reloaded to the counter alternately and coun the TRBPR register even when the secondary p set to 1, the TRBSC register is set to FFh. follow ing steps. the value does not change, write the same valu Address 010Eh Function Counts timer RB prescaler underflow s ⁽¹⁾	ted. beriod is being cou ue second time.) After Reset FFh Setting Range 00h to FFh 00h to FFh	nted
 The values The count v When the T To w rite to Write th Write th Write th 	Programmable w ait one-shot generation mode of registers TRBPR and TRBSC a value can be read out by reading of STOP bit in the TRBCR register is the TRBSC register, perform the fe e value to the TRBSC register. e value to the TRBPR register. (If y Register ⁽²⁾ 	(one-shot width is counted) are reloaded to the counter alternately and counthe TRBPR register even when the secondary poset to 1, the TRBSC register is set to FFh. following steps. the value does not change, write the same value Address 010Eh Function Counts timer RB prescaler underflow s (one-shot width is counted)	ted. beriod is being cou ue second time.) After Reset FFh Setting Range 00h to FFh 00h to FFh 00h to FFh	R R R
 The values The count v When the T To w rite to Write th Write th Write th 	Programmable w ait one-shot generation mode of registers TRBPR and TRBSC a value can be read out by reading of STOP bit in the TRBCR register is the TRBSC register, perform the fe e value to the TRBSC register. e value to the TRBPR register. (If y Register ⁽²⁾ 	(one-shot width is counted) are reloaded to the counter alternately and coun the TRBPR register even when the secondary p set to 1, the TRBSC register is set to FFh. follow ing steps. the value does not change, write the same valu Address 010Eh Function Counts timer RB prescaler underflow s ⁽¹⁾ Counts timer RB prescaler underflow s	ted. beriod is being cou ue second time.) After Reset FFh Setting Range 00h to FFh 00h to FFh	

17.2.1 Timer Mode

In timer mode, a count source which is internally generated or timer RA underflows are counted (refer to **Table 17.7 Timer Mode Specifications**). Registers TRBOCR and TRBSC are not used in timer mode. Figure 17.16 shows TRBIOC Register in Timer Mode.

Item	Specification
Count sources	f1, f2, f8, timer RA underflow
Count operations	 Decrement When the timer underflows, it reloads the reload register contents before the count continues (when timer RB underflows, the contents of timer RB primary reload register is reloaded).
Divide ratio	1/(n+1)(m+1) n: setting value in TRBPRE register, m: setting value in TRBPR register
Count start condition	1 (count starts) is written to the TSTART bit in the TRBCR register.
Count stop conditions	 0 (count stops) is written to the TSTART bit in the TRBCR register. 1 (count forcibly stop) is written to the TSTOP bit in the TRBCR register.
Interrupt request generation timing	When timer RB underflows [timer RB interrupt].
TRBO pin function	Programmable I/O port
INT0 pin function	Programmable I/O port or INT0 interrupt input
Read from timer	The count value can be read out by reading registers TRBPR and TRBPRE.
Write to timer	 When registers TRBPRE and TRBPR are written while the count is stopped, values are written to both the reload register and counter. When registers TRBPRE and TRBPR are written to while count operation is in progress: If the TWRC bit in the TRBMR register is set to 0, the value is written to both the reload register and the counter. If the TWRC bit is set to 1, the value is written to the reload register only. (Refer to 17.2.1.1 Timer Write Control during Count Operation.)

Table 17.7 Timer Mode Specifications

Timer RB I/O Contro	ol Register			
	Symbol TRBIOC	Address 010Ah	After Reset 00h	
	Bit Symbol	Bit Name	Function	RW
	TOPL	Timer RB output level select bit	Set to 0 in timer mode.	RW
	TOCNT	Timer RB output switch bit		RW
	INOSTG	One-shot trigger control bit		RW
	INOSEG	One-shot trigger polarity select bit		RW
	 (b7-b4)	Nothing is assigned. If neces When read, the content is 0.	sary, set to 0.	-
		•		

Figure 17.16 TRBIOC Register in Timer Mode

17.2.1.1 Timer Write Control during Count Operation

Timer RB has a prescaler and a timer (which counts the prescaler underflows). The prescaler and timer each consist of a reload register and a counter. In timer mode, the TWRC bit in the TRBMR register can be used to select whether writing to the prescaler or timer during count operation is performed to both the reload register and counter or only to the reload register.

However, values are transferred from the reload register to the counter of the prescaler in synchronization with the count source. In addition, values are transferred from the reload register to the counter of the timer in synchronization with prescaler underflows. Therefore, even if the TWRC bit is set for writing to both the reload register and counter, the counter value is not updated immediately after the WRITE instruction is executed. In addition, if the TWRC bit is set for writing to the reload register only, the synchronization of the writing will be shifted if the prescaler value changes. Figure 17.17 shows an Operating Example of Timer RB when Counter Value is Rewritten during Count Operation.

When the TWRC bit is	set to 0 (write to reload register and co	ounter)				
	e TRBPRE register and 25h to egister by a program. I					
Count source						
	After writing, the reload n written with the first coun	egister is t source.				
Reloads register of timer RB prescaler	Previous value	N	lew value (01	h)	I	
Counter of	Reload with the second count source	Reload on underflow		•	\	
timer RB prescaler	06h X 05h X 04h X 01h X 00h	<u>`</u>	1h (00h (01h 00h	λ	
		After writing, the reloa written on the first und				
Reloads register of timer RB	Previous value	(New value (25h)	1	
			eload on the se	econd	\ 	
Counter of timer RB	03h	02h	25h	24h	Χ	
Set 01h to the	The IR bit re	mains unchanged until by a new value.	underflow			
	After writing, the reload re written with the first count					
Reloads register of timer RB prescaler	Previous value	New value				<u> </u>
Counter of timer RB prescaler	06h 🗙 05h 🔪 04h 🗙 03h 🗙 02h)	01h 00h 01	/\/\/\/\/	01h 00h writing, the reloa	01h 00h	01h
Reloads register of	Previous value	V	writte	n on the first und	ue (25h)	
timer RB		^				Reload on
					·	underflow
Counter of timer RB	03h	X	02h	01h	00h	25h
IR bit in TRBIC register	0				—	
		e	extending the di	ler values are up uration until time	r RB underflow.	
	er the following conditions. TCSTF in the TRBCR register are se	t to 1 (During cou	unt).			

Figure 17.17 Operating Example of Timer RB when Counter Value is Rewritten during Count Operation

17.2.2 Programmable Waveform Generation Mode

In programmable waveform generation mode, the signal output from the TRBO pin is inverted each time the counter underflows, while the values in registers TRBPR and TRBSC are counted alternately (refer to **Table 17.8 Programmable Waveform Generation Mode Specifications**). Counting starts by counting the setting value in the TRBPR register. The TRBOCR register is unused in this mode.

Figure 17.18 shows TRBIOC Register in Programmable Waveform Generation Mode. Figure 17.19 shows an Operating Example of Timer RB in Programmable Waveform Generation Mode.

Table 17.8	Programmable Waveform Generation Mode Specifications
------------	--

Item	Specification
Count sources	f1, f2, f8, timer RA underflow
Count operations	 Decrement When the timer underflows, it reloads the contents of the primary reload and secondary reload registers alternately before the count continues.
Width and period of output waveform	Primary period: (n+1)(m+1)/fi Secondary period: (n+1)(p+1)/fi Period: (n+1){(m+1)+(p+1)}/fi fi: Count source frequency n: Value set in TRBPRE register m: Value set in TRBPR register p: Value set in TRBSC register
Count start condition	1 (count start) is written to the TSTART bit in the TRBCR register.
Count stop conditions	 0 (count stop) is written to the TSTART bit in the TRBCR register. 1 (count forcibly stop) is written to the TSTOP bit in the TRBCR register.
Interrupt request generation timing	In half a cycle of the count source, after timer RB underflows during the secondary period (at the same time as the TRBO output change) [timer RB interrupt]
TRBO pin function	Programmable output port or pulse output
INT0 pin function	Programmable I/O port or INT0 interrupt input
Read from timer	The count value can be read out by reading registers TRBPR and TRBPRE. ⁽¹⁾
Write to timer	 When registers TRBPRE, TRBSC, and TRBPR are written while the count is stopped, values are written to both the reload register and counter. When registers TRBPRE, TRBSC, and TRBPR are written to during count operation, values are written to the reload registers only.⁽²⁾
Select functions	 Output level select function The TOPL bit in the TRBIOC register selects the output level during primary and secondary periods. TRBO pin output switch function Timer RB pulse output or P3_1 (P1_3) latch output is selected by the TOCNT bit in the TRBIOC register.⁽³⁾ TRBO pin select function P3_1 or P1_3 is selected by the TRBOSEL bit in the PINSR2 register.

NOTES:

1. Even when counting the secondary period, the TRBPR register may be read.

2. The set values are reflected in the waveform output beginning with the following primary period after writing to the TRBPR register.

- 3. The value written to the TOCNT bit is enabled by the following.
 - When counting starts.
 - When a timer RB interrupt request is generated. The contents after the TOCNT bit is changed are reflected from the output of the following primary period.







Figure 17.19 Operating Example of Timer RB in Programmable Waveform Generation Mode

17.2.3 Programmable One-shot Generation Mode

In programmable one-shot generation mode, a one-shot pulse is output from the TRBO pin by a program or an external trigger input (input to the INTO pin) (refer to **Table 17.9 Programmable One-Shot Generation Mode Specifications**). When a trigger is generated, the timer starts operating from the point only once for a given period equal to the set value in the TRBPR register. The TRBSC register is not used in this mode. Figure 17.20 shows TRBIOC Register in Programmable One-Shot Generation Mode. Figure 17.21 shows an Operating Example of Programmable One-Shot Generation Mode.

Table 17.9 Programmable One-Shot Generation Mode Specifi
--

Item	Specification
Count sources	f1, f2, f8, timer RA underflow
Count operations	 Decrement the setting value in the TRBPR register When the timer underflows, it reloads the contents of the reload register before the count completes and the TOSSTF bit is set to 0 (one-shot stops). When the count stops, the timer reloads the contents of the reload register before it stops.
One-shot pulse	(n+1)(m+1)/fi
output time	fi: Count source frequency, n: Setting value in TRBPRE register, m: Setting value in TRBPR register ⁽²⁾
Count start conditions	 The TSTART bit in the TRBCR register is set to 1 (count starts) and the next trigger is generated Set the TOSST bit in the TRBOCR register to 1 (one-shot starts) Input trigger to the INTO pin
Count stop conditions	 When reloading completes after timer RB underflows during primary period When the TOSSP bit in the TRBOCR register is set to 1 (one-shot stops) When the TSTART bit in the TRBCR register is set to 0 (stops counting) When the TSTOP bit in the TRBCR register is set to 1 (forcibly stops counting)
Interrupt request generation timing	In half a cycle of the count source, after the timer underflows (at the same time as the TRBO output ends) [timer RB interrupt]
TRBO pin function	Pulse output
INT0 pin functions	 When the INOSTG bit in the TRBIOC register is set to 0 (INTO one-shot trigger disabled): programmable I/O port or INTO interrupt input When the INOSTG bit in the TRBIOC register is set to 1 (INTO one-shot trigger enabled): external trigger (INTO interrupt input)
Read from timer	The count value can be read out by reading registers TRBPR and TRBPRE.
Write to timer	 When registers TRBPRE and TRBPR are written while the count is stopped, values are written to both the reload register and counter. When registers TRBPRE and TRBPR are written during the count, values are written to the reload register only (the data is transferred to the counter at the following reload).⁽¹⁾
Select functions	 Output level select function The TOPL bit in the TRBIOC register selects the output level of the one-shot pulse waveform. One-shot trigger select function Refer to 17.2.3.1 One-Shot Trigger Selection. TRBO pin select function P3_1 or P1_3 is selected by the TRBOSEL bit in the PINSR2 register.

NOTES:

1. The set value is reflected at the following one-shot pulse after writing to the TRBPR register.

2. Do not set both the TRBPRE and TRBPR registers to 00h.







Figure 17.21 Operating Example of Programmable One-Shot Generation Mode

17.2.3.1 One-Shot Trigger Selection

In programmable one-shot generation mode and programmable wait one-shot generation mode, operation starts when a one-shot trigger is generated while the TCSTF bit in the TRBCR register is set to 1 (count starts). A one-shot trigger can be generated by either of the following causes:

- 1 is written to the TOSST bit in the TRBOCR register by a program.
- Trigger input from the $\overline{INT0}$ pin.

When a one-shot trigger occurs, the TOSSTF bit in the TRBOCR register is set to 1 (one-shot operation in progress) after one or two cycles of the count source have elapsed. Then, in programmable one-shot generation mode, count operation begins and one-shot waveform output starts. (In programmable wait one-shot generation mode, count operation starts for the wait period.) If a one-shot trigger occurs while the TOSSTF bit is set to 1, no retriggering occurs.

To use trigger input from the $\overline{INT0}$ pin, input the trigger after making the following settings:

- Set the PD4_5 bit in the PD4 register to 0 (input port).
- Select the INTO digital filter with bits INTOF1 and INTOF0 in the INTF register.
- Select both edges or one edge with the INTOPL bit in INTEN register. If one edge is selected, further select falling or rising edge with the INOSEG bit in TRBIOC register.
- Set the INTOEN bit in the INTEN register to 0 (enabled).
- After completing the above, set the INOSTG bit in the TRBIOC register to 1 (INT pin one-shot trigger enabled).

Note the following points with regard to generating interrupt requests by trigger input from the INTO pin.

- Processing to handle the interrupts is required. Refer to 13. Interrupts, for details.
- If one edge is selected, use the POL bit in the INTOIC register to select falling or rising edge. (The INOSEG bit in the TRBIOC register does not affect INTO interrupts).
- If a one-shot trigger occurs while the TOSSTF bit is set to 1, timer RB operation is not affected, but the value of the IR bit in the INT0IC register changes.

17.2.4 Programmable Wait One-Shot Generation Mode

In programmable wait one-shot generation mode, a one-shot pulse is output from the TRBO pin by a program or an external trigger input (input to the $\overline{INT0}$ pin) (refer to **Table 17.10 Programmable Wait One-Shot Generation Mode Specifications**). When a trigger is generated from that point, the timer outputs a pulse only once for a given length of time equal to the setting value in the TRBSC register after waiting for a given length of time equal to the SPR register.

Figure 17.22 shows TRBIOC Register in Programmable Wait One-Shot Generation Mode. Figure 17.23 shows an Operating Example of Programmable Wait One-Shot Generation Mode.

Item	Specification
Count sources	f1, f2, f8, timer RA underflow
Count operations	 Decrement the timer RB primary setting value. When a count of the timer RB primary underflows, the timer reloads the contents of timer RB secondary before the count continues. When a count of the timer RB secondary underflows, the timer reloads the contents of timer RB primary before the count completes and the TOSSTF bit is set to 0 (one-shot stops). When the count stops, the timer reloads the contents of the reload register before it stops.
Wait time	(n+1)(m+1)/fi fi: Count source frequency n: Value set in the TRBPRE register, m Value set in the TRBPR register ⁽²⁾
One-shot pulse output time	(n+1)(p+1)/fi fi: Count source frequency n: Value set in the TRBPRE register, p: Value set in the TRBSC register
Count start conditions	 The TSTART bit in the TRBCR register is set to 1 (count starts) and the next trigger is generated. Set the TOSST bit in the TRBOCR register to 1 (one-shot starts). Input trigger to the INT0 pin
Count stop conditions	 When reloading completes after timer RB underflows during secondary period. When the TOSSP bit in the TRBOCR register is set to 1 (one-shot stops). When the TSTART bit in the TRBCR register is set to 0 (starts counting). When the TSTOP bit in the TRBCR register is set to 1 (forcibly stops counting).
Interrupt request generation timing	In half a cycle of the count source after timer RB underflows during secondary period (complete at the same time as waveform output from the TRBO pin) [timer RB interrupt].
TRBO pin function	Pulse output
INT0 pin functions	 When the INOSTG bit in the TRBIOC register is set to 0 (INT0 one-shot trigger disabled): programmable I/O port or INT0 interrupt input When the INOSTG bit in the TRBIOC register is set to 1 (INT0 one-shot trigger enabled): external trigger (INT0 interrupt input)
Read from timer	The count value can be read out by reading registers TRBPR and TRBPRE.
Write to timer	 When registers TRBPRE, TRBSC, and TRBPR are written while the count stops, values are written to both the reload register and counter. When registers TRBPRE, TRBSC, and TRBPR are written to during count operation, values are written to the reload registers only.⁽¹⁾
Select functions	 Output level select function The TOPL bit in the TRBIOC register selects the output level of the one-shot pulse waveform. One-shot trigger select function Refer to 17.2.3.1 One-Shot Trigger Selection. TRBO pin select function P3_1 or P1_3 is selected by the TRBOSEL bit in the PINSR2 register.

Table 17.10 Programmable Wait One-Shot Generation Mode Specifications

NOTES:

1. The set value is reflected at the following one-shot pulse after writing to registers TRBSC and TRBPR.

2. Do not set both the TRBPRE and TRBPR registers to 00h.







Figure 17.23 Operating Example of Programmable Wait One-Shot Generation Mode

17.2.5 Notes on Timer RB

- Timer RB stops counting after a reset. Set the values in the timer RB and timer RB prescalers before the count starts.
- Even if the prescaler and timer RB is read out in 16-bit units, these registers are read 1 byte at a time by the MCU. Consequently, the timer value may be updated during the period when these two registers are being read.
- In programmable one-shot generation mode and programmable wait one-shot generation mode, when setting the TSTART bit in the TRBCR register to 0, 0 (stops counting) or setting the TOSSP bit in the TRBOCR register to 1 (stops one-shot), the timer reloads the value of reload register and stops. Therefore, in programmable one-shot generation mode and programmable wait one-shot generation mode, read the timer count value before the timer stops.
- The TCSTF bit remains 0 (count stops) for 1 to 2 cycles of the count source after setting the TSTART bit to 1 (count starts) while the count is stopped.

During this time, do not access registers associated with timer $RB^{(1)}$ other than the TCSTF bit. Timer RB starts counting at the first valid edge of the count source after the TCSTF bit is set to 1 (during count). The TCSTF bit remains 1 for 1 to 2 cycles of the count source after setting the TSTART bit to 0 (count stops) while the count is in progress. Timer RB counting is stopped when the TCSTF bit is set to 0. During this time, do not access registers associated with timer $RB^{(1)}$ other than the TCSTF bit.

NOTE:

- 1. Registers associated with timer RB: TRBCR, TRBOCR, TRBIOC, TRBMR, TRBPRE, TRBSC, and TRBPR.
- If the TSTOP bit in the TRBCR register is set to 1 during timer operation, timer RB stops immediately.
- If 1 is written to the TOSST or TOSSP bit in the TRBOCR register, the value of the TOSSTF bit changes after one or two cycles of the count source have elapsed. If the TOSSP bit is written to 1 during the period between when the TOSST bit is written to 1 and when the TOSSTF bit is set to 1, the TOSSTF bit may be set to either 0 or 1 depending on the content state. Likewise, if the TOSSTF bit is written to 1 during the period between when the TOSSP bit is written to 1 and when the TOSSTF bit is set to 0, the TOSSTF bit may be set to either 0 or 1.

17.2.5.1 Timer mode

The following workaround should be performed in timer mode.

To write to registers TRBPRE and TRBPR during count operation (TCSTF bit is set to 1), note the following points:

- When the TRBPRE register is written continuously, allow three or more cycles of the count source for each write interval.
- When the TRBPR register is written continuously, allow three or more cycles of the prescaler underflow for each write interval.

17.2.5.2 Programmable waveform generation mode

The following three workarounds should be performed in programmable waveform generation mode.

- (1) To write to registers TRBPRE and TRBPR during count operation (TCSTF bit is set to 1), note the following points:
- When the TRBPRE register is written continuously, allow three or more cycles of the count source for each write interval.
- When the TRBPR register is written continuously, allow three or more cycles of the prescaler underflow for each write interval.
- (2) To change registers TRBPRE and TRBPR during count operation (TCSTF bit is set to 1), synchronize the TRBO output cycle using a timer RB interrupt, etc. This operation should be preformed only once in the same output cycle. Also, make sure that writing to the TRBPR register does not occur during period A shown in Figures 17.24 and 17.25.

The following shows the detailed workaround examples.

• Workaround example (a):

As shown in Figure 17.24, write to registers TRBSC and TRBPR in the timer RB interrupt routine. These write operations must be completed by the beginning of period A.



Figure 17.24 Workaround Example (a) When Timer RB interrupt is Used

• Workaround example (b):

As shown in Figure 17.25 detect the start of the primary period by the TRBO pin output level and write to registers TRBSC and TRBPR. These write operations must be completed by the beginning of period A. If the port register's bit value is read after the port direction register's bit corresponding to the TRBO pin is set to 0 (input mode), the read value indicates the TRBO pin output value.



Figure 17.25 Workaround Example (b) When TRBO Pin Output Value is Read

(3) To stop the timer counting in the primary period, use the TSTOP bit in the TRBCR register. In this case, registers TRBPRE and TRBPR are initialized and their values are set to the values after reset.

17.2.5.3 Programmable one-shot generation mode

The following two workarounds should be performed in programmable one-shot generation mode.

- (1) To write to registers TRBPRE and TRBPR during count operation (TCSTF bit is set to 1), note the following points:
- When the TRBPRE register is written continuously during count operation (TCSTF bit is set to 1), allow three or more cycles of the count source for each write interval.
- When the TRBPR register is written continuously during count operation (TCSTF bit is set to 1), allow three or more cycles of the prescaler underflow for each write interval.
- (2) Do not set both the TRBPRE and TRBPR registers to 00h.

17.2.5.4 Programmable wait one-shot generation mode

The following three workarounds should be performed in programmable wait one-shot generation mode.

- (1) To write to registers TRBPRE and TRBPR during count operation (TCSTF bit is set to 1), note the following points:
- When the TRBPRE register is written continuously, allow three or more cycles of the count source for each write interval.
- When the TRBPR register is written continuously, allow three or more cycles of the prescaler underflow for each write interval.
- (2) Do not set both the TRBPRE and TRBPR registers to 00h.
- (3) Set registers TRBSC and TRBPR using the following procedure.
 - (a) To use "INTO pin one-shot trigger enabled" as the count start condition Set the TRBSC register and then the TRBPR register. At this time, after writing to the TRBPR register, allow an interval of 0.5 or more cycles of the count source before trigger input from the INTO pin.
 - (b) To use "writing 1 to TOSST bit" as the start condition

Set the TRBSC register, the TRBPR register, and then TOSST bit. At this time, after writing to the TRBPR register, allow an interval of 0.5 or more cycles of the count source before writing to the TOSST bit.

17.3 Timer RE

Timer RE has the 4-bit counter and 8-bit counter. Timer RE has the following 2 modes:

- Real-time clock mode Generate 1-second signal from fC4 and count seconds, minutes, hours, and days of the week.
- Output compare mode Count a count source and detect compare matches.

The count source for timer RE is the operating clock that regulates the timing of timer operations.

17.3.1 Real-Time Clock Mode

In real-time clock mode, a 1-second signal is generated from fC4 using a divide-by-2 frequency divider, 4-bit counter, and 8-bit counter and used to count seconds, minutes, hours, and days of the week. Figure 17.26 shows a Block Diagram of Real-Time Clock Mode and Table 17.11 lists the Real-Time Clock Mode Specifications. Figures 17.27 to 17.31 and 17.33 to 17.35 show the Registers Associated with Real-Time Clock Mode. Table 17.12 lists the Interrupt Sources, Figure 17.32 shows the Definition of Time Representation and Figure 17.36 shows the Operating Example in Real-Time Clock Mode.



Figure 17.26 Block Diagram of Real-Time Clock Mode

Item	Specification
Count source	fC4
Count operation	Increment
Count start condition	1 (count starts) is written to TSTART bit in TRECR1 register
Count stop condition	0 (count stops) is written to TSTART bit in TRECR1 register
Interrupt request generation	Select any one of the following:
timing	Update second data
	Update minute data
	Update hour data
	Update day of week data
	 When day of week data is set to 000b (Sunday)
TREO pin function	Programmable I/O ports or output of f2, fC, f4, f8 or, 1Hz
Read from timer	When reading TRESEC, TREMIN, TREHR, or TREWK register, the count
	value can be read. The values read from registers TRESEC, TREMIN,
	and TREHR are represented by the BCD code.
Write to timer	When bits TSTART and TCSTF in the TRECR1 register are set to 0 (timer
	stops), the value can be written to registers TRESEC, TREMIN, TREHR,
	and TREWK. The values written to registers TRESEC, TREMIN, and
	TREHR are represented by the BCD codes.
Selectable functions	12-hour mode/24-hour mode switch function
	Counter precision adjustment function
	TREO pin select function
	P0_4, P6_0, or P6_5 is selected by the TREOSEL bit in the PINSR3 register and the TREOSEL2 bit in the PINSR4 register.

Table 17.11 Real-Time Clock Mode Specifications











Figure 17.29 TREHR Register in Real-Time Clock Mode



Figure 17.30 TREWK Register in Real-Time Clock Mode

b7 b6 b5	5 b4 b3 b2 b1 b0				
		Symbol	Address	After Reset	
ΤΤΤ		TRECR1	011Ch	XXX0X0X0b	
		Bit Symbol	Bit Name	Function	RW
		(b0)	Nothing is assigned. If necess When read, the content is 0.	sary, set to 0.	
		TCSTF	Timer RE count status flag	0 : Count stopped 1 : Counting	RO
		TOENA	TREO pin output enable bit	0 : Disable clock output 1 : Enable clock output	RW
		INT	Interrupt request timing bit	Set to 1 in real-time clock mode.	RW
		TRERST	Timer RE reset bit	 When setting this bit to 0, after setting it to 1, the follow ings will occur. Registers TRESEC, TREMIN, TREHR, TREWK, and TRECR2 are set to 00h. Bits TCSTF, INT, PM, H12_H24, and TSTART in the TRECR1 register are set to 0. The 8-bit counter is set to 00h and the 4-bit counter is set to 0h. 	RW
		РМ	A.m./p.m. bit	When the H12_H24 bit is set to 0 (12-hour mode)(1) 0 : a.m. 1 : p.m. When the H12_H24 bit is set to 1 (24-hour mode), its value is undefined.	RW
		H12_H24	Operating mode select bit	0 : 12-hour mode 1 : 24-hour mode	RW
		TSTART	Timer RE count start bit	0 : Count stops 1 : Count starts	RW

Figure 17.31 TRECR1 Register in Real-Time Clock Mode







Table 17.12	Interrupt Sources
-------------	-------------------

Factor	Interrupt Source	Interrupt Enable Bit
Periodic interrupt	Value in TREWK register is set to 000b (Sunday)	WKIE
triggered every week	(1-week period)	
Periodic interrupt	TREWK register is updated (1-day period)	DYIE
triggered every day		
Periodic interrupt	TREHR register is updated (1-hour period)	HRIE
triggered every hour		
Periodic interrupt	TREMIN register is updated (1-minute period)	MNIE
triggered every minute		
Periodic interrupt	TRESEC register is updated (1-second period)	SEIE
triggered every second		

b7 b6 b5	i b4 b3 b2 b1 b0				
Х	1000	Symbol	Address	After Reset	
		TRECSR	011Eh	00001000b	
		Bit Symbol	Bit Name	Function	RW
		RCS0	Count source select bits	Set to 00b in real-time clock mode.	RW
		RCS1			RW
		RCS2	4-bit counter select bit	Set to 0 in real-time clock mode.	RW
		RCS3	Real-time clock mode select bit	Set to 1 in real-time clock mode.	RW
		RCS4	Clock output select bits ⁽¹⁾	b6 b5 b4 0 0 0 : f2	RW
		RCS5		0 0 1 : fC 0 1 0 : f4	RW
	RCS6		0 1 1 : 1Hz 1 0 0 : f8 Other than above : Do not set.	RW	
		(b7)	Nothing is assigned. If necessary, When read, the content is 0.	set to 0.	<u> </u>

1. Write to bits RCS4 to RCS6 when the TOENA bit in the TRECR1 register is set to 0 (disable clock output).





When 00b or 11b is written to bits MINUS and PLUS, the 8-bit counter value is not added or subtracted.

Figure 17.35 TREOPR Register in Real-Time Clock Mode



Figure 17.36 Operating Example in Real-Time Clock Mode

17.3.2 Output Compare Mode

In output compare mode, the internal count source divided by 2 is counted using the 4-bit or 8-bit counter and compare value match is detected with the 8-bit counter. Figure 17.37 shows a Block Diagram of Output Compare Mode and Table 17.13 lists the Output Compare Mode Specifications. Figures 17.38 to 17.42 show the Registers Associated with Output Compare Mode, and Figure 17.43 shows the Operating Example in Output Compare Mode.



Figure 17.37 Block Diagram of Output Compare Mode

Item	Specification
Count sources	f4, f8, f32, fC4
Count operations	 Increment When the 8-bit counter content matches with the TREMIN register content, the value returns to 00h and count continues. The count value is held while count stops.
Count period	 When RCS2 = 0 (4-bit counter is not used) 1/fi x 2 x (n+1) When RCS2 = 1 (4-bit counter is used) 1/fi x 32 x (n+1) fi: Frequency of count source n: Setting value of TREMIN register
Count start condition	1 (count starts) is written to the TSTART bit in the TRECR1 register
Count stop condition	0 (count stops) is written to the TSTART bit in the TRECR1 register
Interrupt request generation timing	When the 8-bit counter content matches with the TREMIN register content
TREO pin function	Select any one of the following: • Programmable I/O ports • Output f2, fC, f4, or f8 • Compare output
Read from timer	When reading the TRESEC register, the 8-bit counter value can be read. When reading the TREMIN register, the compare value can be read.
Write to timer	Writing to the TRESEC register is disabled. When bits TSTART and TCSTF in the TRECR1 register are set to 0 (timer stops), writing to the TREMIN register is enabled.
Selectable functions	 Select use of 4-bit counter Compare output function Every time the 8-bit counter value matches the TREMIN register value, TREO output polarity is reversed. The TREO pin outputs "L" after reset is deasserted and the timer RE is reset by the TRERST bit in the TRECR1 register. Output level is held by setting the TSTART bit to 0 (count stops). TREO pin select function P0_4, P6_0, or P6_5 is selected by the TREOSEL bit in the PINSR3 register and the TREOSEL2 bit in the PINSR4 register.

Table 17.13	Output Compare Mode Specifications
-------------	------------------------------------



Figure 17.38 TRESEC Register in Output Compare Mode



17. Timers

Timer RE Control R	legister 1			
b7 b6 b5 b4 b3 b2 b1 b0	Symbol TRECR1 Bit Symbol (b0) TCSTF	Address 011Ch Bit Name Nothing is assigned. If necess When read, the content is 0. Timer RE count status flag	0 : Count stopped 1 : Counting	RW — RO
	TOENA INT	TREO pin output enable bit Interrupt request timing bit	0 : Disable clock output 1 : Enable clock output Set to 0 in output compare mode.	RW RW
	TRERST	Timer RE reset bit	 When setting this bit to 0, after setting it to 1, the follow ing will occur. Registers TRESEC, TREMIN, TREHR, TREWK, and TRECR2 are set to 00h. Bits TCSTF, INT, PM, H12_H24, and TSTART in the TRECR1 register are set to 0. The 8-bit counter is set to 00h and the 4-bit counter is set to 0h. 	RW
	PM	A.m./p.m. bit	Set to 0 in output compare mode.	RW
	H12_H24	Operating mode select bit		RW
L	TSTART	Timer RE count start bit	0 : Count stops 1 : Count starts	RW



h7 h6	3 b5 b4 b3 b2 b1 b0				
		Symbol TRECR2	Address 011Dh	After Reset 00XXXXXb	
		Bit Symbol	Bit Name	Function	RW
		SEIE	Periodic interrupt triggered every second enable bit	Set to 0 in output compare mode.	RW
		MNIE	Periodic interrupt triggered every minute enable bit		RW
		HRIE	Periodic interrupt triggered every hour enable bit	-	RW
		DYIE Periodic interrupt triggered day enable bit	Periodic interrupt triggered every day enable bit		RW
		WKIE	Periodic interrupt triggered every w eek enable bit		RW
		COMIE	Compare match interrupt enable bit	0 : Disable compare match interrupt 1 : Enable compare match interrupt	RW
		— (b7-b6)	Nothing is assigned. If necessary, se When read, the content is 0.	to 0.	_

Figure 17.41 TRECR2 Register in Output Compare Mode


1. Write to bits RCS0 to RCS1 when the TCSTF bit in the TRECR1 register is set to 0 (count stopped).

2. Write to bits RCS4 to RCS6 when the TOENA bit in the TRECR1 register is set to 0 (disable clock output).





Figure 17.43 Operating Example in Output Compare Mode

17.3.3 Notes on Timer RE

17.3.3.1 Starting and Stopping Count

Timer RE has the TSTART bit for instructing the count to start or stop, and the TCSTF bit, which indicates count start or stop. Bits TSTART and TCSTF are in the TRECR1 register.

Timer RE starts counting and the TCSTF bit is set to 1 (count starts) when the TSTART bit is set to 1 (count starts). It takes up to 2 cycles of the count source until the TCSTF bit is set to 1 after setting the TSTART bit to 1. During this time, do not access registers associated with timer $RE^{(1)}$ other than the TCSTF bit.

Also, timer RE stops counting when setting the TSTART bit to 0 (count stops) and the TCSTF bit is set to 0 (count stops). It takes the time for up to 2 cycles of the count source until the TCSTF bit is set to 0 after setting the TSTART bit to 0. During this time, do not access registers associated with timer RE other than the TCSTF bit.

NOTE:

1. Registers associated with timer RE: TRESEC, TREMIN, TREHR, TREWK, TRECR1, TRECR2, TRECSR, and TREOPR.

17.3.3.2 Register Setting

Write to the following registers or bits when timer RE is stopped.

- Registers TRESEC, TREMIN, TREHR, TREWK, and TRECR2
- Bits H12_H24, PM, and INT in TRECR1 register
- Bits RCS0 to RCS3 in TRECSR register

Timer RE is stopped when bits TSTART and TCSTF in the TRECR1 register are set to 0 (timer RE stopped).

Also, set all above-mentioned registers and bits (immediately before timer RE count starts) before setting the TRECR2 register.

Figure 17.44 shows a Setting Example in Real-Time Clock Mode.



Figure 17.44 Setting Example in Real-Time Clock Mode

17.3.3.3 Time Reading Procedure of Real-Time Clock Mode

In real-time clock mode, read registers TRESEC, TREMIN, TREHR, and TREWK when time data is updated and read the PM bit in the TRECR1 register when the BSY bit is set to 0 (not while data is updated). Also, when reading several registers, an incorrect time will be read if data is updated before another register is read after reading any register.

In order to prevent this, use the reading procedure shown below.

• Using an interrupt

Read necessary contents of registers TRESEC, TREMIN, TREHR, and TREWK and the PM bit in the TRECR1 register in the timer RE interrupt routine.

• Monitoring with a program 1

Monitor the IR bit in the TREIC register with a program and read necessary contents of registers TRESEC, TREMIN, TREHR, and TREWK and the PM bit in the TRECR1 register after the IR bit in the TREIC register is set to 1 (timer RE interrupt request generated).

• Monitoring with a program 2

- (1) Monitor the BSY bit.
- (2) Monitor until the BSY bit is set to 0 after the BSY bit is set to 1 (approximately 62.5 ms while the BSY bit is set to 1).
- (3) Read necessary contents of registers TRESEC, TREMIN, TREHR, and TREWK and the PM bit in the TRECR1 register after the BSY bit is set to 0.

• Using read results if they are the same value twice

- (1) Read necessary contents of registers TRESEC, TREMIN, TREHR, and TREWK and the PM bit in the TRECR1 register.
- (2) Read the same register as (1) and compare the contents.
- (3) Recognize as the correct value if the contents match. If the contents do not match, repeat until the read contents match with the previous contents.

Also, when reading several registers, read them as continuously as possible.

17.4 Timer RF

Timer RF is a 16-bit timer. The count source for timer RF is the operating clock that regulates the timing of timer operations. Figure 17.45 shows a Block Diagram of Timer RF. Figure 17.46 shows a Block Diagram of CMP Waveform Generation Unit. Figure 17.47 shows a Block Diagram of CMP Waveform Output Unit.

Timer RF has two modes: input capture mode and output compare mode. Figures 17.48 to 17.51 show the timer RF associated registers.



Figure 17.45 Block Diagram of Timer RF



Figure 17.46 Block Diagram of CMP Waveform Generation Unit



Figure 17.47 Block Diagram of CMP Waveform Output Unit



	Symbol	Address 0299h	After Reset	
	TRFCR2 Bit Symbol	Bit Name	00h Function	RW
	TRFC20	Timer RF capture input select bit	0 : TRFI pin input 1 : fC32	RW
	(b4-b1)	Nothing is assigned. If necessary, When read, the content is 0.	set to 0.	-
	 (b6-b5)	Reserved bits	Set to 0.	RW
	(b7)	Nothing is assigned. If necessary, When read, the content is 0.	set to 0.	-
	Symbol TRFCR0 Bit Symbol	Address 029Ah Bit Name	After Reset 00h Function	RW
limer RF Control I	Pagistar ()			
		Bit Name	Function	RW
	TSTART	Timer RF count start bit	0 : Count stops 1 : Count starts	RW
	ТСК0	Timer RF count source select bits ⁽¹⁾	b2 b1 0 0 : f1	RW
	TCK1		0 1 : f8 1 0 : f32 1 1 : Do not set.	RW
	TRFC03	Capture polarity select bits ⁽¹⁾	b4 b3 0 0 : Rising edge	RW
	TRFC04		0 1 : Falling edge 1 0 : Both edges 1 1 : Do not set.	RW
	TRFC05	CMP output select bit 0 w hen count stops	0 : TRFC06 bit disabled Holds output level before count stops 1 : TRFC06 bit enabled	RW
1 1	TRFC06	CMP output select bit 1 w hen count stops	0 : "L" output w hen count stops 1 : "H" output w hen count stops	RW
		Reserved bit	Set to 0.	RW



b7 b6 b5 b	v4 b3 b2 b1 b0				
		Symbol	Address	After Reset	
ТТТ		TRFCR1	029Bh	00h	
		Bit Symbol	Bit Name	Function	RW
		TIPF0	TRFI filter select bits ⁽¹⁾	b1 b0 0 0 : No filter	RW
		TIPF1		0 1 : Filter w ith f1 sampling 1 0 : Filter w ith f8 sampling 1 1 : Filter w ith f32 sampling	RW
		CCLR	TRF register count operation select bit ^(2, 3)	0 : Free-running operation 1 : Set TRF register to 0000h w hen compare 1 is matched.	RW
		TMOD	Timer RF operation mode select bit ⁽³⁾	0 : Input capture mode ^(2, 4) 1 : Output compare mode	RW
		TRFC14	Compare 0 output select bits ⁽²⁾	b5 b₄ CMP output w hen compare 0 is matched 0 0 : Unchanged 0 1 : Inverted 1 0 : "L"	RW
		TRFC15		10:L 11:"H"	
		TRFC16		 b7 b6 CMP output w hen compare 0 is matched 0 0 : Unchanged 0 1 : Inverted 	RW
		TRFC17		1 0 : "L" 1 1 : "H"	1.00

1. If filter enabled, when the same value from the TRFI pin is sampled three times continuously, the input is determined.

2. When the TMOD bit is set to 0 (input capture mode), set bits CCLR, and TRFC14 to TRFC17 to 0.

3. When the TSTART bit in the TRFCR0 register is set to 0 (count stops), rew rite bits CCLR and TMOD.

4. When the TMOD bit is set to 0 (input capture mode), set bits ILVL2 to ILVL0 in the CMP1IC register to 000b (level 0) and set the IR bit to 0 (no interrupt requested).

Figure 17.50 TRFCR1 Register

Timer RF Output Co	ontrol Regis	ster		
b7 b6 b5 b4 b3 b2 b1 b0				
	Symbol	Address	After Reset	
	TRFOUT	02FFh	00h	
	Bit Symbol	Bit Name	Function	RW
	TRFOUT0	TRFO00 output enable bit	0 : Output disabled	RW
	TRFOUT1	TRFO01 output enable bit	1 : Output enabled	RW
	TRFOUT2	TRFO02 output enable bit	1	RW
	TRFOUT3	TRFO10 output enable bit	1	RW
	TRFOUT4	TRFO11 output enable bit		RW
	TRFOUT5	TRFO12 output enable bit	1	RW
	TRFOUT6	TRFO00 to TRFO02 output invert bit	0 : Output not inverted 1 : Output inverted	RW
	TRFOUT7	TRFO10 to TRFO12 output invert bit]	RW

Figure 17.51 TRFOUT Register

17.4.1 Input Capture Mode

In input capture mode, the edge of the TRFI pin input signal or fC32 is used as a trigger to latch the timer value and the width or the period of external signal is measured. The TRFI input is equipped with a digital filter, and this prevents errors caused by noise or the like from occurring. Table 17.14 shows the Input Capture Mode Specifications. Figure 17.52 shows an Operating Example in Input Capture Mode.

Item	Specification
Count sources	f1, f8, f32
Count operations	 Increment Transfer the value in the TRF register to the TRFM0 register at the valid edge of the measured pulse.
Count period	1/fk × 65536 fk: Frequency of count source
Count start condition	The TSTART bit in the TRFCR0 register is set to 1 (count starts).
Count stop condition	The TSTART bit in the TRFCR0 register is set to 0 (count stops).
Interrupt request generation timing	 The valid edge of TRFI input or fC32 [capture interrupt] When timer RF overflows [timer RF interrupt]
TRFI pin function	Measured pulse input
TRFO00 to TRFO02, TRFO11 to TRFO12 pin functions	Programmable I/O port
Counter value reset timing	In the following cases, the value in the TRF register is set to 0000h. • When the TSTART bit in the TRFCR0 register is set to 0 (count stops).
Read from timer	 The count value can be read out by reading the TRF register. The count value at the measured pulse valid edge input can be read out by reading the TRFM0 register.
Write to timer	Write to the TRF and TRFM0 registers is disabled.
Select functions	 TRFI or fC32 polarity selected Selects the valid edge of the measured pulse. (Bits TRFC03 to TRFC04 in the TRFCR0 register.) Digital filter function The TRFI input is sampled, and when the sampled input level matches as three times, the level is determined. Selects the sampling clock of the digital filter. (Bits TIPF0 to TIPF1 in the TRFCR1 register.)

Table 17.14 Input Capture Mode Specifications



Figure 17.52 Operating Example in Input Capture Mode

17.4.1.1 Digital Filter

The TRFI input is sampled, and when the sampled input level matches three times, its level is determined. Select the digital filter function and sampling clock by the TRFCR1 register.



Figure 17.53 Block Diagram of Digital Filter

17.4.2 Output Compare Mode

In output compare mode, when the value of the TRF register matches the value of the TRFM0 (compare 0 match) or TRFM1 (compare 1 match) register, a user-set level is output mode from the output-compare output pin.

Table 17.15 shows the Output Compare Mode Specifications. Table 17.16 shows the Output in Output Compare Mode (Example of TRFO00 Pin). Figure 17.54 shows an Operating Example in Output Compare Mode. Figure 17.55 shows an Operating Example in Output Compare Mode ("L" and "H" Held Output in Count Stops).

Item	Specification			
Count sources	f1, f8, f32			
Count operations	Increment			
PWM waveform	PWM period: $1/fk \times (n + 1)$ "L" level width: $1/fk \times (n + 1)$ "H" level width: $1/fk \times (n - m)$ fk: Frequency of count source m: Value set in the TRFM0 register n: Value set in the TRFM1 register n + 1 It applies under the following conditions. • CMP output "H" when compare 0 is matched • CMP output "L" when compare 1 is matched • CMP output not inverted			
Count start condition	The TSTART bit in the TRFCR0 register is set to 1 (count starts).			
Count stop condition	The TSTART bit in the TRFCR0 register is set to 0 (count stops).			
Interrupt request generation timing	 When compare 0 match is generated [compare 0 interrupt] When compare 1 match is generated [compare 1 interrupt] When time RF overflows [timer RF interrupt]. 			
TRFO00 to TRFO12 pin functions	Programmable I/O port or output-compare output			
Counter value reset timing	 In the following cases, the value in the TRF register is set to 0000h. When the TSTART bit in the TRFCR0 register is set to 0 (count stops). The CCLR bit in the TRFCR1 register is set to 1 (the TRF register is set to 0000h at compare 1 match) in the compare 1 matches. 			
Read from timer	 The count value can be read out by reading the TRF register. The value in the compare register can be read out by reading registers TRFM0 and TRFM1. 			
Write to timer	Write to the TRF register is disabled			
Select functions	 Output-compare output pin selected Either 1 pin or multiple pins among TRFO00 to TRFO02, or TRFO10 to TRFO12 (bits TRFOUT0 to TRFOUT5 in the TRFOUT register). Output level at the compare match Selects "H", "L", inverted, or unchanged (bits TRFC14 to TRFC17 in the TRFCR1 register). Output level inverted Selects output level inverted or not inverted (bits TRFOUT6 to TRFOUT7 in the TRFOUT register). Output level at the count stops Selects "H", "L", or unchanged (bits TRFC05 to TRFC06 in the TRFCR0 register). Timing to set the TRF register to 0000h Overflow or compare 1 match in the TRFM1 register (the CCLR bit in the TRFCR1 register). TRFO11 pin select function P3_4 or P3_7 is selected by the TRFOSEL bit in the PINSR4 register. 			

Table 17.15 Output Compare Mode Specifications

	TRFO00 Output		Bit Setting Value						
TR			TRFCR0 Register			TRFOUT Register			
		TRFC06	TRFC05	TSTART	TRFOUT6	TRFOUT0	P1_0		
Counting	CMP output	Х	Х	1	0	1	1		
	Inverted output of	Х	Х	1	1	1	1		
	CMP output								
	"L" output	Х	Х	1	0	1	0		
	"H" output	Х	Х	1	1	1	0		
Count	Holds output level	Х	0	0	Х	1	1		
stops	before count stops								
	"L" output	0	1	0	Х	1	1		
	"H" output	1	1	0	Х	1	1		

Table 17.16 Output in Output Compare Mode (Example of TRFO00 Pin)

X: 0 or 1



Figure 17.54 Operating Example in Output Compare Mode



Figure 17.55 Operating Example in Output Compare Mode ("L" and "H" Held Output in Count Stops)

In output compare mode, the same PWM waveform is output from all of pins TRFO00 to TRFO02 and TRFO10 to TRFO12 during count operation. Note that the output waveform can be inverted for pins TRFO00 to TRFO02 or for pins TRFO10 to TRFO12. The output can also be fixed at "L" or "H" for individual pins for a given period.

The behavior when count operation stops can be selected from the following two options: the output level before the count stops is maintained, or output is fixed at "L" or "H".

The values in the compare i register can be read by reading the TRFMi (i = 0 or 1) register. Writing to the TRFMi register causes the values to be stored in the compare i register in the following timing:

- If the TSTART bit is set to 0 (count stops)
- Values are stored simultaneously with the write to the TRFMi register.
- If the TSTART bit is set to 1 (count starts) and the CCLR bit in the TRFCR1 register is set to 0 (free running) Values are stored when the TRF register (counter) overflows.
- If the TSTART bit is set to 1 and the CCLR bit is set to 1 (TRF register set to 0000h at compare 1 match) Values are stored when the compare 1 and TRF register (counter) values match.

17.4.3 Notes on Timer RF

• Access registers TRF, TRFM0, and TRFM1 in 16-bit units.

Example of reading timer RF: MOV.W 0290H,R0

0290H,R0 ; Read out timer RF

• In input capture mode, a capture interrupt request is generated by inputting an edge selected by bits TRFC03 and TRFC04 in the TRFCR0 register even when the TSTART bit in the TRFCR0 register is set to 0 (count stops).

18. Serial Interface

The serial interface consists of two channels (UART0 or UART2). Each UARTi (i = 0 or 2) has an exclusive timer to generate the transfer clock and operates independently.

Figure 18.1 shows a UARTi (i = 0 or 2) Block Diagram. Figure 18.2 shows a UARTi Transmit/Receive Unit. UARTi has two modes: clock synchronous serial I/O mode and clock asynchronous serial I/O mode (UART mode). Figures 18.3 to 18.5 show the Registers Associated with UARTi.



Figure 18.1 UARTi (i = 0 or 2) Block Diagram



Figure 18.2 UARTi Transmit/Receive Unit



Figure 18.3 Registers U0MR, U2MR and U0BRG, U2BRG



Figure 18.4 Registers U0TB, U2TB and U0C0, U2C0

UARTi Transm	nit/Re	ceive Contr	ol Register 1 (i = 0 or 2)		
b7 b6 b5 b4 b3 b2	b1 b0	Symbol U0C1 U2C1	Address 00A5h 0165h	After Reset 00000010b 00000010b	
		Bit Symbol	Bit Name	Function	RW
		TE	Transmit enable bit	0 : Disables transmission 1 : Enables transmission	RW
		TI	Transmit buffer empty flag	0 : Data in UiTB register 1 : No data in UiTB register	RO
		RE	Receive enable bit	0 : Disables reception 1 : Enables reception	RW
		RI	Receive complete flag ⁽¹⁾	0 : No data in UiRB register 1 : Data in UiRB register	RO
		UilRS	UARTi transmit interrupt cause select bit	0 : Transmission buffer empty (TI=1) 1 : Transmission completed (TXEPT=1)	RW
		UiRRM	UARTi continuous receive mode enable bit ⁽²⁾	0 : Disables continuous receive mode 1 : Enables continuous receive mode	RW
		 (b6)	Reserved bit	Set to 0.	RW
		(b7)	Nothing is assigned. If necessary, set to 0. When read, the content is 0.		

NOTES:

1. The RI bit is set to 0 w hen the higher byte of the UiRB register is read out.

2. Set the UIRRM bit to 0 (disables continuous receive mode) in UART mode.



NOTES:

1. Read out the UiRB register in 16-bit units.

2. Bits SUM, PER, FER, and OER are set to 0 (no error) when bits SMD2 to SMD0 in the UiMR register are set to 000b (serial interface disabled) or the RE bit in the UiC1 register is set to 0 (receive disabled). The SUM bit is set to 0 (no error) when bits PER, FER, and OER are set to 0 (no error). Bits PER and FER are set to 0 even when the higher byte of the UiRB register is read out.

Also, bits PER and FER are set to 0 w hen reading the high-order byte of the UiRB register.

Registers U0C1, U2C1 and U0RB, U2RB Figure 18.5

18.1 Clock Synchronous Serial I/O Mode

In clock synchronous serial I/O mode, data is transmitted and received using a transfer clock. Table 18.1 lists the Clock Synchronous Serial I/O Mode Specifications. Table 18.2 lists the Registers Used and Settings in Clock Synchronous Serial I/O Mode⁽¹⁾.

Item	Specification
Transfer data format	Transfer data length: 8 bits
Transfer clocks	 CKDIR bit in UiMR register is set to 0 (internal clock): fi/(2(n+1)) fi = f1, f8, f32 n = value set in UiBRG register: 00h to FFh The CKDIR bit is set to 1 (external clock): input from CLKi pin
Transmit start conditions	 Before transmission starts, the following requirements must be met⁽¹⁾ The TE bit in the UiC1 register is set to 1 (transmission enabled) The TI bit in the UiC1 register is set to 0 (data in the UiTB register)
Receive start conditions	 Before reception starts, the following requirements must be met⁽¹⁾ The RE bit in the UiC1 register is set to 1 (reception enabled) The TE bit in the UiC1 register is set to 1 (transmission enabled) The TI bit in the UiC1 register is set to 0 (data in the UiTB register)
Interrupt request generation timing	 When transmitting, one of the following conditions can be selected The UiIRS bit is set to 0 (transmit buffer empty): When transferring data from the UiTB register to UARTi transmit register (when transmission starts). The UiIRS bit is set to 1 (transmission completes): When completing data transmission from UARTi transmit register. When receiving
	When data transfer from the UARTi receive register to the UiRB register (when reception completes).
Error detection	 Overrun error⁽²⁾ This error occurs if the serial interface starts receiving the next data item before reading the UiRB register and receives the 7th bit of the next data.
Select functions	 CLK polarity selection Transfer data input/output can be selected to occur synchronously with the rising or the falling edge of the transfer clock. LSB first, MSB first selection Whether transmitting or receiving data begins with bit 0 or begins with bit 7 can be selected. Continuous receive mode selection Receive is enabled immediately by reading the UiRB register.

i = 0 or 2

NOTES:

- 1. If an external clock is selected, ensure that the external clock is "H" when the CKPOL bit in the UiC0 register is set to 0 (transmit data output at falling edge and receive data input at rising edge of transfer clock), and that the external clock is "L" when the CKPOL bit is set to 1 (transmit data output at rising edge and receive data input at falling edge of transfer clock).
- 2. If an overrun error occurs, the receive data (b0 to b8) of the UiRB register will be undefined. The IR bit in the SiRIC register remains unchanged.

Register	Bit	Function		
UiTB	0 to 7	Set data transmission		
UiRB	0 to 7	Data reception can be read		
	OER	Overrun error flag		
UiBRG	0 to 7	Set bit rate		
UiMR	SMD2 to SMD0	Set to 001b		
	CKDIR	Select the internal clock or external clock		
UiC0	CLK1 to CLK0	Select the count source in the UiBRG register		
	TXEPT	Transmit register empty flag		
	NCH	Select TXDi pin output mode		
	CKPOL	Select the transfer clock polarity		
	UFORM	Select the LSB first or MSB first		
UiC1	TE	Set this bit to 1 to enable transmission/reception		
	TI	Transmit buffer empty flag		
	RE	Set this bit to 1 to enable reception		
	RI	Reception complete flag		
	UilRS	Select the UARTi transmit interrupt source		
	UiRRM	Set this bit to 1 to use continuous receive mode		

Table 18.2	Registers Used and Settings in Clock Synchronous Serial I/O Mode ⁽¹⁾

i = 0 or 2

NOTE:

1. Set bits which are not in this table to 0 when writing to the above registers in clock synchronous serial I/O mode.

Table 18.3 lists the I/O Pin Functions in Clock Synchronous Serial I/O Mode. The TXDi pin outputs "H" level between the operating mode selection of UARTi (i = 0 or 2) and transfer start. (If the NCH bit is set to 1 (N-channel open-drain output), this pin is in a high-impedance state.)

Table 18.3	I/O Pin Functions in Clock Synchronous Serial I/O Mode
------------	--

r				
Pin Name	Function	Selection Method		
TXD0 (P1_4)	Output serial data	(Outputs dummy data when performing reception only)		
RXD0 (P1_5)	Input serial data	PD1_5 bit in PD1 register = 0		
		(P1_5 can be used as an input port when performing		
		transmission only)		
CLK0 (P1_6)	Output transfer clock	CKDIR bit in U0MR register = 0		
	Input transfer clock	CKDIR bit in U0MR register = 1		
		PD1_6 bit in PD1 register = 0		
TXD2 (P6_3)	Output serial data	(Outputs dummy data when performing reception only)		
RXD2 (P6_4)	Input serial data	PD6_4 bit in PD6 register = 0		
		(P6_4 can be used as an input port when performing		
		transmission only)		
CLK2 (P6_5)	Output transfer clock	CKDIR bit in U2MR register = 0		
	Input transfer clock	CKDIR bit in U2MR register = 1		
		PD6_5 bit in PD6 register = 0		



Figure 18.6 Transmit and Receive Timing Example in Clock Synchronous Serial I/O Mode

18.1.1 Polarity Select Function

Figure 18.7 shows the Transfer Clock Polarity. Use the CKPOL bit in the UiC0 (i = 0 or 2) register to select the transfer clock polarity.



Figure 18.7 Transfer Clock Polarity

18.1.2 LSB First/MSB First Select Function

Figure 18.8 shows the Transfer Format. Use the UFORM bit in the UiC0 (i = 0 or 2) register to select the transfer format.



18.1.3 Continuous Receive Mode

Continuous receive mode is selected by setting the UiRRM (i = 0 or 2) bit in the UiC1 register to 1 (enables continuous receive mode). In this mode, reading the UiRB register sets the TI bit in the UiC1 register to 0 (data in the UiTB register). When the UiRRM bit is set to 1, do not write dummy data to the UiTB register by a program.

18.2 Clock Asynchronous Serial I/O (UART) Mode

The UART mode allows data transmission and reception after setting the desired bit rate and transfer data format. Table 18.4 lists the UART Mode Specifications. Table 18.5 lists the Registers Used and Settings for UART Mode.

Item	Specification
Transfer data formats	 Character bit (transfer data): Selectable among 7, 8 or 9 bits Start bit: 1 bit
	Parity bit: Selectable among odd, even, or none
	Stop bit: Selectable among 1 or 2 bits
Transfer clocks	CKDIR bit in UiMR register is set to 0 (internal clock): fi/(16(n+1))
	$f_j = f_1, f_3, f_{32} n = value set in UiBRG register: 00h to FFh$
	• CKDIR bit is set to 1 (external clock): fEXT/(16(n+1))
	fEXT: Input from CLKi pin, n = value set in UiBRG register: 00h to FFh
Transmit start conditions	Before transmission starts, the following are required
	- TE bit in UiC1 register is set to 1 (transmission enabled)
	- TI bit in UiC1 register is set to 0 (data in UiTB register)
Receive start conditions	Before reception starts, the following are required
	- RE bit in UiC1 register is set to 1 (reception enabled)
	- Start bit detected
Interrupt request	• When transmitting, one of the following conditions can be selected
generation timing	- UiIRS bit is set to 0 (transmit buffer empty):
	When transferring data from the UiTB register to UARTi transmit register
	(when transmission starts).
	- UiIRS bit is set to 1 (transfer ends):
	When serial interfac.e completes transmitting data from the UARTi
	transmit register
	When receiving
	When transferring data from the UARTi receive register to UiRB register
	(when reception ends).
Error detection	• Overrun error ⁽¹⁾
	This error occurs if the serial interface starts receiving the next data item
	before reading the UiRB register and receive the bit preceding the final
	stop bit of the next data item.
	Framing error
	This error occurs when the set number of stop bits is not detected.
	Parity error
	This error occurs when parity is enabled, and the number of 1's in parity
	and character bits do not match the number of 1's set.
	• Error sum flag
	This flag is set is set to 1 when an overrun, framing, or parity error is
	generated.

Table 18.4	UART Mode Specifications
------------	--------------------------

i = 0 or 2

NOTE:

1. If an overrun error occurs, the receive data (b0 to b8) of the UiRB register will be undefined. The IR bit in the SiRIC register remains unchanged.

Register	Bit	Function		
UiTB	0 to 8	Set transmit data ⁽¹⁾		
UiRB	0 to 8	Receive data can be read ^(1, 2)		
	OER,FER,PER,SUM	Error flag		
UiBRG	0 to 7	Set a bit rate		
UiMR SMD2 to SMD0		Set to 100b when transfer data is 7 bits long Set to 101b when transfer data is 8 bits long Set to 110b when transfer data is 9 bits long		
	CKDIR	Select the internal clock or external clock		
	STPS	Select the stop bit		
	PRY, PRYE	Select whether parity is included and whether odd or even		
UiC0	CLK0, CLK1	Select the count source for the UiBRG register		
	TXEPT	Transmit register empty flag		
	NCH	Select TXDi pin output mode		
	CKPOL	Set to 0		
	UFORM	LSB first or MSB first can be selected when transfer data is 8 bits long. Set to 0 when transfer data is 7 or 9 bits long.		
UiC1	TE	Set to 1 to enable transmit		
	TI	Transmit buffer empty flag		
	RE	Set to 1 to enable receive		
	RI	Receive complete flag		
	UilRS	Select the source of UARTi transmit interrupt		
	UiRRM	Set to 0		

Table 18.5	Registers Used and Settings for UART Mode
------------	---

i = 0 or 2

NOTES:

- 1. The bits used for transmit/receive data are as follows: Bits 0 to 6 when transfer data is 7 bits long; bits 0 to 7 when transfer data is 8 bits long; bits 0 to 8 when transfer data is 9 bits long.
- 2. The following bits are undefined: Bits 7 and 8 when transfer data is 7 bits long; bit 8 when transfer data is 8 bits long.

Table 18.6 lists the I/O Pin Functions in UART Mode. After the UARTi (i = 0 or 2) operating mode is selected, the TXDi pin outputs "H" level. (If the NCH bit is set to 1 (N-channel open-drain output), this pin is in a high-impedance state) until transfer starts.)

Pin name	Function	Selection Method	
TXD0 (P1_4)	Output serial data	(Cannot be used as a port when performing reception only)	
RXD0 (P1_5)	Input serial data	PD1_5 bit in PD1 register = 0	
		(P1_5 can be used as an input port when performing	
		transmission only)	
CLK0 (P1_6)	Programmable I/O Port	CKDIR bit in U0MR register = 0	
	Input transfer clock	CKDIR bit in U0MR register = 1	
		PD1_6 bit in PD1 register = 0	
TXD2 (P6_3)	Output serial data	(Cannot be used as a port when performing reception only)	
RXD2 (P6_4)	Input serial data	PD6_4 bit in PD6 register = 0	
		(P6_4 can be used as an input port when performing	
		transmission only)	
CLK2 (P6_5)	Programmable I/O Port	CKDIR bit in U2MR register = 0	
Input transfer clock CKDIR bit in U2MR register = 1		CKDIR bit in U2MR register = 1	
		PD6_5 bit in PD6 register = 0	

Table 18.6 I/O Pin Functions in UART Mode



Figure 18.9 Transmit Timing in UART Mode



18.2.1 Bit Rate

In UART mode, the bit rate is the frequency divided by the UiBRG (i = 0 or 2) register.





Table 18.7	Bit Rate Setting Example in UART Mode (Internal Clock Selected)
------------	---

Bit Rate (bps)	BRG Count Source	System Clock = 8 MHz			
Bit Rate (bps)		UiBRG Setting Value	Actual Time (bps)	Error (%)	
1200	f8	51 (33h)	1201.92	0.16	
2400	f8	25 (19h)	2403.85	0.16	
4800	f8	12 (0Ch)	4807.69	0.16	
9600	f1	51 (33h)	9615.38	0.16	
14400	f1	34 (22h)	14285.71	-0.79	
19200	f1	25 (19h)	19230.77	0.16	
28800	f1	16 (10h)	29411.76	2.12	
31250	f1	15 (0Fh)	31250.00	0.00	
38400	f1	12 (0Ch)	38461.54	0.16	
51200	f1	9 (09h)	50000.00	-2.34	

18.3 Notes on Serial Interface

• When reading data from the UiRB (i = 0 or 2) register either in the clock synchronous serial I/O mode or in the clock asynchronous serial I/O mode. Ensure the data is read in 16-bit units. When the high-order byte of the UiRB register is read, bits PER and FER in the UiRB register and the RI bit in the UiC1 register are set to 0. To check receive errors, read the UiRB register and then use the read data.

Example (when reading receive buffer register): MOV.W 00A6H,R0 ; Read the U0RB register

• When writing data to the UiTB register in the clock asynchronous serial I/O mode with 9-bit transfer data length, write data to the high-order byte first then the low-order byte, in 8-bit units.

Example (when reading transmit buffer register):

MOV.B	#XXH,00A3H	; Write the high-order byte of U0TB register
MOV.B	#XXH,00A2H	; Write the low-order byte of U0TB register

19. Hardware LIN

The hardware LIN performs LIN communication in cooperation with timer RA and UARTO.

19.1 Features

The hardware LIN has the features listed below. Figure 19.1 shows a Block Diagram of Hardware LIN.

Master mode

- Generates Synch Break
- Detects bus collision

Slave mode

- Detects Synch Break
- Measures Synch Field
- Controls Synch Break and Synch Field signal inputs to UART0
- Detects bus collision

NOTE:

1. The WakeUp function is detected by INT1.





19.2 Input/Output Pins

The pin configuration of the hardware LIN is listed in Table 19.1.

Table 19.1 Pin Configuration

Name	Abbreviation	Input/Output	Function
Receive data input	RXD0	Input	Receive data input pin of the hardware LIN
Transmit data output	TXD0	Output	Transmit data output pin of the hardware LIN
Register Configuration 19.3

The hardware LIN contains the registers listed below. These registers are detailed in Figures 19.2 and 19.3.

- LIN Control Register (LINCR)
- LIN Status Register (LINST)

b7 b6	b5 b∕	b3 b2	b1 b0				
				Symbol	Address	After Reset	
TT	ТТ	TT	TT	LINCR	0106h	00h	
				Bit Symbol	Bit Name	Function	RW
				SFIE	Synch Field measurement- completed interrupt enable bit	 0: Disables Synch Field measurement- completed interrupt 1: Enables Synch Field measurement- completed interrupt 	RW
				SBIE	Synch Break detection interrupt enable bit	0 : Disables Synch Break detection interrupt 1 : Enables Synch Break detection interrupt	RW
		L		BCIE	Bus collision detection interrupt enable bit	0 : Disables bus collision detection interrupt 1 : Enables bus collision detection interrupt	RW
				RXDSF	RXD0 input status flag	0 : RXD0 input enabled 1 : RXD0 input disabled	RC
				LSTART	Synch Break detection start bit ⁽¹⁾	When this bit is set to 1, timer RA input is enabled and RXD0 input is disabled. When read, the content is 0.	RW
				SBE	RXD0 input unmasking timing select bit (effective only in slave mode)	 0 : Unmasked after Synch Break is detected 1 : Unmasked after Synch Field measurement is completed 	RW
				MST	LIN operation mode setting bit ⁽²⁾	 0 : Slave mode (Synch Break detection circuit actuated) 1 : Master mode (timer RA output OR'ed with TXD0) 	RW
				LINE	LIN operation start bit	0 : Causes LIN to stop 1 : Causes LIN to start operating ⁽³⁾	RW

1. After setting the LSTART bit, confirm that the RXDSF flag is set to 1 before Synch Break input starts.

2. Before changing LIN operation modes, temporarily stop the LIN operation (LINE bit = 0).

3. Inputs to timer RA and UART0 are prohibited immediately after this bit is set to 1. (Refer to Figure 19.5 Example of Header Field Transmission Flow chart (1) and Figure 19.9 Example of Header Field Reception Flow chart **(2)**.)





Figure 19.3 LINST Register

19.4 Functional Description

19.4.1 Master Mode

Figure 19.4 shows typical operation of the hardware LIN when transmitting a header field in master mode. Figures 19.5 and 19.6 show an Example of Header Field Transmission Flowchart. When transmitting a header field, the hardware LIN operates as described below.

- (1) When the TSTART bit in the TRACR register for timer RA is set by writing 1 in software, the hardware LIN outputs "L" level from the TXD0 pin for the period that is set in registers TRAPRE and TRA for timer RA.
- (2) When timer RA underflows upon reaching the terminal count, the hardware LIN reverses the output of the TXD0 pin and sets the SBDCT flag in the LINST register to 1. Furthermore, if the SBIE bit in the LINCR register is set to 1, it generates a timer RA interrupt.
- (3) The hardware LIN transmits 55h via UARTO.
- (4) The hardware LIN transmits an ID field via UART0 after it finishes sending 55h.
- (5) The hardware LIN performs communication for a response field after it finishes sending the ID field.



Figure 19.4 Typical Operation when Sending a Header Field





Rev.1.00 Apr 04, 2008 Page 235 of 318 **RENESAS** REJ09B0387-0100

19.4.2 Slave Mode

Figure 19.7 shows typical operation of the hardware LIN when receiving a header field in slave mode. Figure 19.8 through Figure 19.10 show an Example of Header Field Reception Flowchart.

When receiving a header field, the hardware LIN operates as described below.

- (1) Synch Break detection is enabled by writing 1 to the LSTART bit in the LINCR register of the hardware LIN.
- (2) When "L" level is input for a duration equal to or greater than the period set in timer RA, the hardware LIN detects it as Synch Break. At this time, the SBDCT flag in the LINST register is set to 1. Furthermore, if the SBIE bit in the LINCR register is set to 1, the hardware LIN generates a timer RA interrupt. Then it goes to Synch Field measurement.
- (3) The hardware LIN receives a Synch Field (55h). At this time, it measures the period of the start bit and bits 0 to 6 by using timer RA. In this case, it is possible to select whether to input the Synch Field signal to RXD0 of UART0 by setting the SBE bit in the LINCR register accordingly.
- (4) The hardware LIN sets the SFDCT flag in the LINST register to 1 when it finishes measuring the Synch Field. Furthermore, if the SFIE bit in the LINCR register is set to 1, it generates a timer RA interrupt.
- (5) After it finishes measuring the Synch Field, calculate a transfer rate from the count value of timer RA and set to UART0 and registers TRAPRE and TRA of timer RA again. Then it receives an ID field via UART0.
- (6) The hardware LIN performs communication for a response field after it finishes receiving the ID field.



Figure 19.7 Typical Operation when Receiving a Header Field





Figure 19.9 Example of Header Field Reception Flowchart (2)



19.4.3 Bus Collision Detection Function

The bus collision detection function can be used when UART0 is enabled for transmission (TE bit in the U0C1 register = 1).

Figure 19.11 shows the Typical Operation when a Bus Collision is Detected.



Figure 19.11 Typical Operation when a Bus Collision is Detected

19.4.4 Hardware LIN End Processing

Figure 19.12 shows an Example of Hardware LIN Communication Completion Flowchart. Use the following timing for hardware LIN end processing:

- If the hardware bus collision detection function is used Perform hardware LIN end processing after checksum transmission completes.
- If the bus collision detection function is not used Perform hardware LIN end processing after header field transmission and reception complete.



Figure 19.12 Example of Hardware LIN Communication Completion Flowchart

19.5 Interrupt Requests

There are four interrupt requests that are generated by the hardware LIN: Synch Break detection, Synch Break generation completed, Synch Field measurement completed, and bus collision detection. These interrupts are shared with timer RA.

Table 19.2 lists the Interrupt Requests of Hardware LIN.

Table 19.2 Interrupt Requests of Hardware LIN

Interrupt Request	Status Flag	Cause of Interrupt
Synch Break detection	SBDCT	Generated when timer RA has underflowed after measuring the "L" level duration of RXD0 input, or when a "L" level is input for a duration longer than the Synch Break period during communication.
Synch Break generation completed		Generated when "L" level output to TXD0 for the duration set by timer RA completes.
Synch Field measurement completed	SFDCT	Generated when measurement for 6 bits of the Synch Field by timer RA is completed.
Bus collision detection	BCDCT	Generated when the RXD0 input and TXD0 output values differed at data latch timing while UART0 is enabled for transmission.

19.6 Notes on Hardware LIN

For the time-out processing of the header and response fields, use another timer to measure the duration of time with a Synch Break detection interrupt as the starting point.

20. Flash Memory

20.1 Overview

Rewrite operations to the flash memory can be performed in three modes: CPU rewrite, standard serial I/O, and parallel I/O.

Table 20.1 lists the Flash Memory Performance (refer to **Table 1.1 Specifications for R8C/2G Group** for items not listed in **Table 20.1**).

Table 20.1 Flash Memory Performance

lt	tem	Specification
Flash memory operatir	ng mode	3 modes (CPU rewrite, standard serial I/O, and parallel I/O)
Division of erase block		Refer to Figure 20.1
Programming method		Byte unit
Erase method		Block erase
Programming and eras	ure control method	Program and erase control by software command
Protection method		Program ROM protection by FMR0 register
Number of commands		5 commands
Programming and erasure endurance ⁽¹⁾	Blocks 0 and 1 (program ROM)	100 times
Programming and eras	sure voltage	VCC = 2.7 to 5.5 V
ID code check function	1	Standard serial I/O mode supported
ROM code protect		Parallel I/O mode supported

NOTE:

1. Definition of programming and erasure endurance.

The programming and erasure endurance is defined on a per-block basis.

 Table 20.2
 Flash Memory Rewrite Modes

Flash Memory Rewrite Mode	CPU Rewrite Mode	Standard Serial I/O Mode	Parallel I/O Mode
Function	User ROM area is rewritten by executing software commands from the CPU.	User ROM area is rewritten by a dedicated serial programmer.	User ROM area is rewritten by a dedicated parallel programmer.
Areas which can be rewritten	User ROM area	User ROM area	User ROM area
Rewrite Program	User program	Standard boot program	-

20.2 Memory Map

The flash memory contains a user ROM area and a boot ROM area (reserved area).

Figure 20.1 shows the Flash Memory Block Diagram for R8C/2G Group.

The user ROM area contains program ROM.

The user ROM area is divided into several blocks. The user ROM area can be rewritten in CPU rewrite mode and standard serial I/O and parallel I/O modes.

The rewrite control program (standard boot program) for standard serial I/O mode is stored in the boot ROM area before shipment. The boot ROM area and the user ROM area share the same address, but have separate memory areas.



Figure 20.1 Flash Memory Block Diagram for R8C/2G Group

20.3 Functions to Prevent Rewriting of Flash Memory

Standard serial I/O mode has an ID code check function, and parallel I/O mode has a ROM code protect function to prevent the flash memory from being read or rewritten or erasure easily.

20.3.1 ID Code Check Function

The ID code check function is used in standard serial I/O mode. Unless 3 bytes (addresses from 0FFFCh to 0FFFEh) of the reset vector are set to FFFFFFh, the ID codes sent from the serial programmer or the on-chip debugging emulator and the 7-byte ID codes written in the flash memory are checked to see if they match. If the ID codes do not match, the commands sent from the serial programmer or the on-chip debugging emulator are not acknowledged. For details of the ID code check function, refer to **14. ID Code Areas**.

20.3.2 ROM Code Protect Function

The ROM protect function prevents the contents of the flash memory from being read, rewritten, or erased by means of the OFS register when parallel I/O mode is used.

Figure 20.2 shows the OFS Register. Refer to 15. Option Function Select Area for details of the OFS register.

The ROM code protect function is enabled by writing 0 to the ROMCP1 bit and 1 to the ROMCR bit. It disables reading or changing the contents of the on-chip flash memory.

Once ROM code protect is enabled, the content in the internal flash memory cannot be rewritten in parallel I/O mode. To disable ROM code protect, erase the block including the OFS register with CPU rewrite mode or standard serial I/O mode.

Option Function Se	lect Regist	er ⁽¹⁾		
b7 b6 b5 b4 b3 b2 b1 b0	Symbol	Address	When Shipping	
	OFS	0FFFFh	FFh ⁽³⁾	
	Bit Symbol	Bit Name	Function	RW
	WDTON	Watchdog timer start select bit	0 : Starts w atchdog timer automatically after reset1 : Watchdog timer is inactive after reset	RW
	(b1)	Reserved bit	Set to 1.	RW
	ROMCR	ROM code protect disabled bit	0 : ROM code protect disabled 1 : ROMCP1 enabled	RW
	ROMCP1	ROM code protect bit	0 : ROM code protect enabled 1 : ROM code protect disabled	RW
	(b4)	Reserved bit	Set to 1.	RW
	LVD00N	Voltage detection 0 circuit start bit ⁽²⁾	 0 : Voltage monitor 0 reset enabled after hardw are reset 1 : Voltage monitor 0 reset disabled after hardw are reset 	RW
	 (b6)	Reserved bit	Set to 1.	RW
	CSPROINI	Count source protect mode after reset select bit	0 : Count source protect mode enabled after reset 1 : Count source protect mode disabled after reset	RW

1. The OFS register is on the flash memory. Write to the OFS register with a program. After writing is completed, do not write additions to the OFS register.

2. Setting the LVD0ON bit is only valid after a hardware reset. To use the power-on reset, set the LVD0ON bit to 0 (voltage monitor 0 reset enabled after hardware reset).

3. If the block including the OFS register is erased, FFh is set to the OFS register.

Figure 20.2 OFS Register

20.4 CPU Rewrite Mode

In CPU rewrite mode, the user ROM area can be rewritten by executing software commands from the CPU. Therefore, the user ROM area can be rewritten directly while the MCU is mounted on a board without using a ROM programmer. Execute the software command only to blocks in the user ROM area. Table 20.3 lists the Differences between EW0 Mode and EW1 Mode.

Item	EW0 Mode	EW1 Mode
Operating mode	Single-chip mode	Single-chip mode
Areas in which a rewrite control program can be executed	RAM (Rewrite control program is executed after being transferred)	User ROM or RAM
Areas which can be rewritten	User ROM	User ROM However, blocks which contain a rewrite control program are excluded
Software command restrictions	None	 Program and block erase commands Cannot be run on any block which contains a rewrite control program Read status register command Cannot be executed
Modes after program or erase	Read status register mode	Read array mode
Modes after read status register	Read status register mode	Do not execute this command
CPU status during auto- write and auto-erase	Operating	Hold state (I/O ports hold state before the command is executed)
Flash memory status detection	 Read bits FMR00, FMR06, and FMR07 in the FMR0 register by a program Execute the read status register command and read bits SR7, SR5, and SR4 in the status register. 	Read bits FMR00, FMR06, and FMR07 in the FMR0 register by a program
CPU clock	5 MHz or below	No restriction (on clock frequency to be used)

Table 20.3 Differences between EW0 Mode and EW1 Mode

20.4.1 Register Description

The registers used in CPU rewrite mode are described.

20.4.1.1 FMR0 Register (FMR0)

Figure 20.3 shows the FMR0 Register.

7 b6 b5 b4 b3	b2 b1 b0				
0 0		Symbol	Address	After Reset	
		FMR0	01B7h	0000001b	
		Bit Symbol	Bit Name	Function	RW
		FMR00	RY/BY status flag	0 : Busy (w riting or erasing in progress) 1 : Ready	RC
		FMR01	CPU rew rite mode select bit ⁽¹⁾	0 : CPU rew rite mode disabled 1 : CPU rew rite mode enabled	RV
		FMR02	Blocks 0, 1 rew rite enable bit ^(2, 6)	0 : Disables rew rite 1 : Enables rew rite	RV
		FMSTP	Flash memory stop bit ^(3, 5)	0 : Enables flash memory operation 1 : Stops flash memory (enters low -pow er consumption state and flash memory is reset)	RW
		 (b5-b4)	Reserved bits	Set to 0.	RW
		FMR06	Program status flag ⁽⁴⁾	0 : Completed successfully 1 : Terminated by error	RC
		FMR07	Erase status flag ⁽⁴⁾	0 : Completed successfully 1 : Terminated by error	RC

NOTES:

- 1. To set this bit to 1, set it to 1 immediately after setting it first to 0. Do not generate an interrupt betw een setting the bit to 0 and setting it to 1. Enter read array mode and set this bit to 0.
- 2. Set this bit to 1 immediately after setting it first to 0 w hile the FMR01 bit is set to 1. Do not generate an interrupt betw een setting the bit to 0 and setting it to 1.
- 3. Set this bit by a program located in a space other than the flash memory.
- 4. This bit is set to 0 by executing the clear status command.
- 5. This bit is enabled when the FMR01 bit is set to 1 (CPU rew rite mode). When the FMR01 bit is set to 0, writing 1 to the FMSTP bit causes the FMSTP bit to be set to 1. The flash memory does not enter low -pow er consumption state nor is it reset.
- 6. When setting the FMR01 bit to 0 (CPU rew rite mode disabled), the FMR02 bit is set to 0 (disables rew rite).

Figure 20.3 FMR0 Register

• FMR00 Bit

This bit indicates the operating status of the flash memory. The bits value is 0 during programming, erasure, or erase-suspend mode; otherwise, it is 1.

• FMR01 Bit

The MCU is made ready to accept commands by setting the FMR01 bit to 1 (CPU rewrite mode).

• FMR02 Bit

Rewriting of blocks 0 and 1 does not accept program or block erase commands if the FMR02 bit is set to 0 (rewrite disabled).

Rewriting of blocks 0 and 1 is controlled by bits FMR15 and FMR16 if the FMR02 bit is set to 1 (rewrite enabled).

• FMSTP Bit

This bit is used to initialize the flash memory control circuits, and also to reduce the amount of current consumed by the flash memory. Access to the flash memory is disabled by setting the FMSTP bit to 1. Therefore, the FMSTP bit must be written to by a program transferred to the RAM. In the following cases, set the FMSTP bit to 1:

- When flash memory access resulted in an error while erasing or programming in EW0 mode (FMR00 bit not reset to 1 (ready))
- To provide lower consumption in low-speed on-chip oscillator mode and low-speed clock mode.

Note that when going to stop or wait mode while the CPU rewrite mode is disabled, the FMR0 register does not need to be set because the power for the flash memory is automatically turned off and is turned back on again after returning from stop or wait mode.

• FMR06 Bit

This is a read-only bit indicating the status of an auto-program operation. The bit is set to 1 when a program error occurs; otherwise, it is set to 0. For details, refer to the description in **Table 20.4 Errors and FMR0 Register Status**.

• FMR07 Bit

This is a read-only bit indicating the status of an auto-erase operation. The bit is set to 1 when an erase error occurs; otherwise, it is set to 0. Refer to **Table 20.4 Errors and FMR0 Register Status** for details.

FMR0 Regi	•	_	
Register	,	Error	Error Occurrence Condition
FMR07(SR5)	FMR06(SR4)		
1	1	Command sequence error	 When a command is not written correctly. When D0h or FFh is not written in the 2nd byte of the block erase command.⁽¹⁾ When the program command or block erase command is executed while rewriting is disabled by the FMR02 bit in the FMR0 register, or the FMR15 or FMR16 bit in the FMR1 register. When an address not allocated in flash memory is input during erase command input When attempting to erase the block for which rewriting is disabled during erase command input. When an address not allocated in flash memory is input during write command input. When an address not allocated in flash memory is input during write command input.
1	0	Erase error	 When the block erase command is executed but auto-erasure does not complete correctly
0	1	Program error	 When the program command is executed but not auto-programming does not complete.
0	0	Completed successfully	-

Errors and FMR0 Register Status Table 20.4

NOTE:

1. When FFh is written in the 2nd byte of the block erase command, the MCU enters read array mode, and the command code written in the 1st byte is disabled.

20.4.1.2 FMR1 Register (FMR1)

Figure 20.4 shows the FMR1 Register.

b7 b6	b5 b4 b3 b2 b1 b0	Symbol	Address	After Reset	
TT		FMR1	01B5h	100000Xb	
		Bit Symbol	Bit Name	Function	RW
		(b0)	Reserved bit	When read, the content is undefined.	RO
		- FMR11	EW1 mode select bit ^(1, 2)	0 : EW0 mode 1 : EW1 mode	RW
		 (b4-b2)	Reserved bits	Set to 0.	RW
		- FMR15	Block 0 rew rite disable bit ^(2,3)	0 : Enables rew rite 1 : Disables rew rite	RW
		- FMR16	Block 1 rew rite disable bit ^(2,3)	0 : Enables rew rite 1 : Disables rew rite	RW
		(b7)	Reserved bit	Set to 1.	RW

NOTES

- 1. To set this bit to 1, set it to 1 immediately after setting it first to 0 w hile the FMR01 bit is set to 1 (CPU rew rite mode enable). Do not generate an interrupt betw een setting the bit to 0 and setting it to 1.
- 2. This bit is set to 0 by setting the FMR01 bit in the FMR0 register to 0 (CPU rew rite mode disabled).
- 3. While the FMR01 bit is set to 1 (CPU rew rite mode enabled), bits FMR15 and FMR16 can be w ritten to. To set this bit to 0, set it to 0 immediately after setting it first to 1. To set this bit to 1, set it to 1.

Figure 20.4 **FMR1 Register**

• FMR11 Bit

Setting this bit to 1 (EW1 mode) places the MCU in EW1 mode.

• FMR15 Bit

When the FMR02 bit is set to 1 (rewrite enabled) and the FMR15 bit is set to 0 (rewrite enabled), block 0 accepts program and block erase commands.

• FMR16 Bit

When the FMR02 bit is set to 1 (rewrite enabled) and the FMR16 bit is set to 0 (rewrite enabled), block 1 accepts program and block erase commands.

20.4.1.3 FMR4 Register (FMR4)

Figure 20.5 shows the FMR4 Register.

b7 b6 b	5 b4 b3 b2 b1 b0	Symbol	Address	After Reset	
		FMR4	01B3h	0100000b	
		Bit Symbol	Bit Name	Function	RW
		 (b2-b0)	Reserved bits	Set to 0.	RW
		FMR43	Erase command flag	0 : Erase not executed 1 : Erase execution in progress	RO
		FMR44	Program command flag	0 : Program not executed 1 : Program execution in progress	RO
		(b5)	Nothing is assigned. If necess When read, the content is 0.	ary, set to 0.	_
		FMR46	Read status flag	0 : Disables reading 1 : Enables reading	RO
		FMR47	Low -current-consumption read mode enable bit ^(1, 2, 3)	0 : Disable 1 : Enable	RW

NOTES:

- 1. To set this bit to 1, set it to 1 immediately after setting it first to 0. Do not generate an interrupt betw een setting the bit to 0 and setting it to 1.
- 2. In high-speed on-chip oscillator mode, set the FMR47 bit to 0 (disabled).
- 3. Set the FMR01 bit to 0 (CPU rew rite mode disabled) in low -current-consumption read mode.

Figure 20.5 FMR4 Register

• FMR43 Bit

When the auto-erase operation starts, the FMR43 bit is set to 1 (erase execution in progress). When the auto-erase operation ends, the FMR43 bit is set to 0 (erase not executed).

• FMR44 Bit

When the auto-program operation starts, the FMR44 bit is set to 1 (program execution in progress). When the auto-program operation ends, the FMR44 bit is set to 0 (program not executed).

• FMR46 Bit

The FMR46 bit is set to 0 (reading disabled) during auto-program or auto-erase execution. Do not access the flash memory while this bit is set to 0.

• FMR47 Bit

Current consumption when reading the flash memory can be reduced by setting the FMR47 bit to 1 (enabled) in low-speed clock mode and low-speed on-chip oscillator mode. Refer to **21.2.10 Low-Current-Consumption Read Mode** for details of the handling procedure.

20.4.2 Status Check Procedure

When an error occurs, bits FMR06 to FMR07 in the FMR0 register are set to 1, indicating the occurrence of an error. Therefore, checking these status bits (full status check) can be used to determine the execution result. Figure 20.6 shows the Full Status Check and Handling Procedure for Individual Errors.



Figure 20.6 Full Status Check and Handling Procedure for Individual Errors

20.4.3 EW0 Mode

The MCU enters CPU rewrite mode and software commands can be acknowledged by setting the FMR01 bit in the FMR0 register to 1 (CPU rewrite mode enabled). In this case, since the FMR11 bit in the FMR1 register is set to 0, EW0 mode is selected.

Use software commands to control program and erase operations. The FMR0 register or the status register can be used to determine when program and erase operations complete. Figure 20.7 shows How to Set and Exit EW0 Mode.



Figure 20.7 How to Set and Exit EW0 Mode

20.4.3.1 Software Commands

There are five types of software commands:

- Read array
- Read status register
- Clear status register
- Program
- Block erase

Figure 20.8 shows Software Command Status Transition Diagram in EW0 Mode.



Figure 20.8 Software Command Status Transition Diagram in EW0 Mode

Read Array Command

The read array command reads the flash memory.

When FFh is written to an address in the user ROM area, the MCU enters read array mode. In this mode, the contents of the specified address can be read.

Read array mode continues until other commands are written. The MCU enters this mode after a reset is deasserted.

• Read Status Register Command

The read status register command is used to read the status register. Figure 20.9 shows Status Register. The status register indicates the operating status of the flash memory and whether an erase or program operation has completed normally or in error (refer to **Table 20.4 Errors and FMR0 Register Status**). When 70h is written to an address in the user ROM area, the MCU enters read status register mode. When the address in the user ROM area is read subsequently, the status register can be read.

The MCU remains in read status register mode until the next read array command is written.

The status of the status register can be determined by reading bits FMR00, FMR06, and FMR07 in the FMR0 register.



Figure 20.9 Status Register

Clear Status Register Command

The clear status register command sets the status register to 0.

When 50h is written to an address in the user ROM area, bits FMR07 and FMR06 in the FMR0 register and bits SR5 and SR4 in the status register are set to 00b.

Program Command

The program command writes data to the flash memory in 1-byte units.

When 40h is written and then data is written to the write address, an auto-program operation (data program and verify) starts.

The FMR00 bit in the FMR0 register can be used to determine whether auto-programming has completed. The FMR00 bit is set to 0 during auto-programming and set to 1 when auto-programming completes.

The FMR06 bit in the FMR0 register can be used to determine the result of auto-programming after it has been finished (refer to **20.4.2 Status Check Procedure**).

Do not write additions to the already programmed addresses.

Also, when the FMR02 bit in the FMR0 register is set to 0 (rewrite disabled), or the FMR02 bit is set to 1 (rewrite enabled) and the FMR15 bit in the FMR1 register is set to 1 (rewrite disabled), program commands targeting block 0 are not acknowledged. When the FMR 16 bit is set to 1 (rewrite disabled), program commands targeting block 1 are not acknowledged.

Figure 20.10 shows the Program Command in EW0 Mode.

In EW0 mode, the MCU enters read status register mode at the same time auto-programming starts and the status register can be read. In this case, the MCU remains in read status register mode until the next read array command is written.



Figure 20.10 Program Command in EW0 Mode

• Block Erase

When 20h is first written and then D0h is written to a given block address, an auto-erase operation (erase and verify) of the specified block starts.

The FMR00 bit in the FMR0 register can be used to determine whether auto-erasure has completed.

The FMR00 bit is set to 0 during auto-erasure and set to 1 when auto-erasure completes.

The FMR07 bit in the FMR0 register can be used to determine the result of auto-erasure after auto-erasure has completed (refer to **20.4.2 Status Check Procedure**).

Also, when the FMR02 bit in the FMR0 register is set to 0 (rewrite disabled), or the FMR02 bit is set to 1 (rewrite enabled) and the FMR15 bit in the FMR1 register is set to 1 (rewrite disabled), block erase commands targeting block 0 are not acknowledged. When the FMR16 bit is set to 1 (rewrite disabled), block erase commands targeting block 1 are not acknowledged.

In EW0 mode, the MCU enters read status register mode at the same time auto-erasure starts and the status register can be read. In this case, the MCU remains in read status register mode until the next read array command is written.

Figure 20.11 shows the Block Erase Command in EW0 Mode.

If the programming and erasure endurance is n (n = 100, 1000, or 10,000), each block can be erased n times. For example, if 1,024 1-byte writes are performed to block A, a 1-Kbyte block, and then the block is erased, the erase count stands at one. When performing 100 or more rewrites, the actual erase count can be reduced by executing programming operations in such a way that all blank areas are used before performing an erase operation. Avoid rewriting only particular blocks and try to average out the programming and erasure endurance of the blocks. It is also advisable to retain data on the erase count of each block and limit the number of erase operations to a certain number.



Figure 20.11 Block Erase Command in EW0 Mode

20.4.3.2 EW0 Mode Interrupts

In EW0 mode, maskable interrupts can be used by allocating a vector in RAM. Table 20.5 lists the EW0 Mode Interrupts. Refer to **20.7.1.3 Non-Maskable Interrupts** for details of the non-maskable interrupt.

Table 20.5 EW0 Mode Interrupts

Status	When Maskable Interrupt Request is Acknowledged
During auto-erasure	Interrupt handling is executed.
Auto-programming	

20.4.4 EW1 Mode

The MCU is switched to EW1 mode by setting the FMR11 bit to 1 (EW1 mode) after setting the FMR01 bit to 1 (CPU rewrite mode enabled).

The FMR0 register can be used to determine when program and erase operations complete. Figure 20.12 shows How to Set and Exit EW1 Mode.



Figure 20.12 How to Set and Exit EW1 Mode

20.4.4.1 Software Commands

There are four types of software commands:

- Read array
- Clear status register
- Program
- Block erase

Do not execute read status register command in EW1 mode. Figure 20.13 shows Software Command Status Transition Diagram in EW1 Mode.



Figure 20.13 Software Command Status Transition Diagram in EW1 Mode

Read Array Command The read array command reads the flash memory. When FFh is written to an address in the user ROM area, the MCU enters read array mode. In this mode, the contents of the specified address can be read. Read array mode continues until other commands are written. The MCU enters this mode after a reset is deasserted.
Clear Status Register Command The clear status register command sets the status register to 0.

The clear status register command sets the status register to 0. When 50h is written to an address in the user ROM area, bits FMR07 and FMR06 in the FMR0 register and bits SR5 and SR4 in the status register are set to 00b.

• Program Command

The program command writes data to the flash memory in 1-byte units.

When 40h is written and then data is written to the write address, an auto-program operation (data program and verify) starts.

The FMR00 bit in the FMR0 register can be used to determine whether auto-programming has completed. The FMR00 bit is set to 0 during auto-programming and set to 1 when auto-programming completes.

The FMR06 bit in the FMR0 register can be used to determine the result of auto-programming after it has been finished (refer to **20.4.2 Status Check Procedure**).

Do not write additions to the already programmed addresses.

Also, when the FMR02 bit in the FMR0 register is set to 0 (rewrite disabled), or the FMR02 bit is set to 1 (rewrite enabled) and the FMR15 bit in the FMR1 register is set to 1 (rewrite disabled), program commands targeting block 0 are not acknowledged. When the FMR 16 bit is set to 1 (rewrite disabled), program commands targeting block 1 are not acknowledged.

In EW1 mode, do not execute this command for any address which a rewrite control program is allocated.

Figure 20.14 shows the Program Command in EW1 Mode.



Figure 20.14 Program Command in EW1 Mode

• Block Erase

When 20h is first written and then D0h is written to a given block address, an auto-erase operation (erase and verify) of the specified block starts.

The FMR00 bit in the FMR0 register can be used to determine whether auto-erasure has completed.

The FMR00 bit is set to 0 during auto-erasure and set to 1 when auto-erasure completes.

The FMR07 bit in the FMR0 register can be used to determine the result of auto-erasure after auto-erasure has completed (refer to **20.4.2 Status Check Procedure**).

Also, when the FMR02 bit in the FMR0 register is set to 0 (rewrite disabled), or the FMR02 bit is set to 1 (rewrite enabled) and the FMR15 bit in the FMR1 register is set to 1 (rewrite disabled), block erase commands targeting block 0 are not acknowledged. When the FMR16 bit is set to 1 (rewrite disabled), block erase commands targeting block 1 are not acknowledged.

Do not execute this command for any address to which a rewrite control program is allocated.

Figure 20.15 shows the Block Erase Command in EW1 Mode.

If the programming and erasure endurance is n (n = 100, 1000, or 10,000), each block can be erased n times. For example, if 1,024 1-byte writes are performed to block A, a 1-Kbyte block, and then the block is erased, the erase count stands at one. When performing 100 or more rewrites, the actual erase count can be reduced by executing programming operations in such a way that all blank areas are used before performing an erase operation. Avoid rewriting only particular blocks and try to average out the programming and erasure endurance of the blocks.

It is also advisable to retain data on the erase count of each block and limit the number of erase operations to a certain number.



Figure 20.15 Block Erase Command in EW1 Mode

20.4.4.2 EW1 Mode Interrupts

In EW1 mode, maskable interrupts can be used.

Table 20.6 lists the EW1 Mode Interrupts. Refer to **20.7.1.3 Non-Maskable Interrupts** for details of the non-maskable interrupt.

Table 20.6EW1 Mode Interrupts

Status	When Maskable Interrupt Request is Acknowledged
During auto-erasure	Auto-erasure has priority and the interrupt request acknowledgement is put on standby. Interrupt handling is executed after auto-erasure completes.
During auto- programming	Auto-programming has priority and the interrupt request acknowledgement is put on standby. Interrupt handling is executed after auto-programming completes.

20.5 Standard Serial I/O Mode

In standard serial I/O mode, the user ROM area can be rewritten while the MCU is mounted on-board by using a serial programmer which is suitable for the MCU.

There are three types of standard serial I/O modes:

- Standard serial I/O mode 1Clock synchronous serial I/O used to connect with a serial programmer
- Standard serial I/O mode 2Clock asynchronous serial I/O used to connect with a serial programmer
- Standard serial I/O mode 3Special clock asynchronous serial I/O used to connect with a serial programmer

This MCU uses Standard serial I/O mode 3.

Refer to **Appendix 2. Connection Examples with On-Chip Debugging Emulator**. Contact the manufacturer of your serial programmer for details. Refer to the user's manual of your serial programmer for instructions on how to use it.

Table 20.7 lists the Pin Functions (Flash Memory Standard Serial I/O Mode 3), and Figure 20.16 shows an Example of Pin Processing in Standard Serial I/O Mode 3.

After processing the pins shown in Table 20.7 and rewriting the flash memory using the programmer, apply "H" to the MODE pin and reset the hardware to run a program in the flash memory in single-chip mode.

20.5.1 ID Code Check Function

The ID code check function determines whether the ID codes sent from the serial programmer and those written in the flash memory match.

Refer to 14. ID Code Areas for details of the ID code check.
Pin	Name	I/O	Description
VCC,VSS	Power input		Apply the voltage guaranteed for programming and erasure to the VCC pin and 0 V to the VSS pin.
			· · · ·
RESET	Reset input	I	Reset input pin.
P4_3/XCIN	P4_3 input/clock input	Ι	Connect crystal oscillator between pins XCIN and
			XCOUT when connecting external oscillator.
P4 4/XCOUT	P4 4 output/clock	0	To use P4_3 as an input port, input a "H" or "L" level
_	output		signal or leave the pin open.
			To use P4_4 as an output port, leave the pin open.
P0_4 to P0_7	Input port P0	Ι	Input a "H" or "L" level signal or leave the pin open.
P1_0 to P1_7	Input port P1	Ι	
P3_0 to P3_7	Input port P3	Ι	
P4_5	Input port P4	Ι	
P6_0, P6_3 to P6_6	Input port P6	Ι	
MODE	MODE	I/O	Serial data I/O pin. Connect to the flash programmer.

Table 20.7	Pin Functions	(Flash Memory	y Standard Serial I/O Mode 3)
------------	---------------	---------------	-------------------------------



Figure 20.16 Example of Pin Processing in Standard Serial I/O Mode 3

20.6 Parallel I/O Mode

Parallel I/O mode is used to input and output software commands, addresses and data necessary to control (read, program, and erase) the on-chip flash memory. Use a parallel programmer which supports this MCU. Contact the manufacturer of the parallel programmer for more information, and refer to the user's manual of the parallel programmer for details on how to use it.

ROM areas shown in Figure 20.1 can be rewritten in parallel I/O mode.

20.6.1 ROM Code Protect Function

The ROM code protect function disables the reading and rewriting of the flash memory. (Refer to **20.3.2 ROM Code Protect Function**.)

20.7 Notes on Flash Memory

20.7.1 CPU Rewrite Mode

20.7.1.1 Operating Speed

Before entering CPU rewrite mode (EW0 mode), select 5 MHz or below for the CPU clock using the CM06 bit in the CM0 register and bits CM16 to CM17 in the CM1 register. This does not apply to EW1 mode.

20.7.1.2 Prohibited Instructions

The following instructions cannot be used in EW0 mode because they reference data in the flash memory: UND, INTO, and BRK.

20.7.1.3 Non-Maskable Interrupts

• EW0 Mode

Once a watchdog timer, voltage monitor1, voltage monitor 2, comparator 1, or comparator 2 interrupt request is acknowledged, auto-erasure or auto-programming is forcibly stopped immediately and the flash memory is reset. Interrupt handling starts after a fixed period and the flash memory restarts.

As the block during auto-erasure or the address during auto-programming is forcibly stopped, the normal value may not be readable. Execute auto-erasure again and ensure it completes normally.

The watchdog timer does not stop during command operation, so that interrupt requests may be generated. Initialize the watchdog timer regularly.

Do not use the address match interrupt while a command is being executed because the vector of the address match interrupt is allocated in ROM.

Do not use a non-maskable interrupt while block 0 is being automatically erased because the fixed vector is allocated in block 0.

• EW1 Mode

Once a watchdog timer, voltage monitor1, voltage monitor 2, comparator 1, or comparator 2 interrupt request is acknowledged, auto-erasure or auto-programming is forcibly stopped immediately and the flash memory is reset. Interrupt handling starts after a fixed period and the flash memory restarts.

As the block during auto-erasure or the address during auto-programming is forcibly stopped, the normal value may not be readable. Execute auto-erasure again and ensure it completes normally.

The watchdog timer does not stop even during command operation, so that interrupt requests may be generated. Initialize the watchdog timer by using the erase-suspend function.

Do not use the address match interrupt while a command is being executed because the vector of the address match interrupt is allocated in ROM.

Do not use a non-maskable interrupt while block 0 is being automatically erased because the fixed vector is allocated in block 0.

20.7.1.4 How to Access

Write 0 before writing 1 when setting Bits FMR01, FMR02 in the FMR0 register, or FMR11 bit in the FMR1 register to 1. Do not generate an interrupt between writing 0 and 1.

20.7.1.5 Rewriting User ROM Area

In EW0 Mode, if the supply voltage drops while rewriting any block in which a rewrite control program is stored, it may not be possible to rewrite the flash memory because the rewrite control program cannot be rewritten correctly. In this case, use standard serial I/O mode.

20.7.1.6 Program

Do not write additions to the already programmed address.

20.7.1.7 Program and Erase Voltage for Flash Memory

To perform programming and erasure, use VCC = 2.7 V to 5.5 V as the supply voltage. Do not perform programming and erasure at less than 2.7 V.

21. Reducing Power Consumption

21.1 Overview

This chapter describes key points and processing methods for reducing power consumption.

21.2 Key Points and Processing Methods for Reducing Power Consumption

Key points for reducing power consumption are shown below. They should be referred to when designing a system or creating a program.

21.2.1 Voltage Detection Circuit

When voltage monitor 1 and comparator 1 are not used, set the VCA26 bit in the VCA2 register to 0 (voltage detection 1 circuit disabled). When voltage monitor 2 and comparator 2 are not used, set the VCA27 bit in the VCA2 register to 0 (voltage detection 2 circuit disabled).

If the power-on reset and voltage monitor 0 reset are not used, set the VCA25 bit in the VCA2 register to 0 (voltage detection 0 circuit disabled).

21.2.2 Ports

Even after the MCU enters wait mode or stop mode, the states of the I/O ports are retained. Current flows into the output ports in the active state, and shoot-through current flows into the input ports in the high-impedance state. Unnecessary ports should be set to input and fixed to a stable electric potential before the MCU enters wait mode or stop mode.

21.2.3 Clocks

Power consumption generally depends on the number of the operating clocks and their frequencies. The fewer the number of operating clocks or the lower their frequencies, the more power consumption decreases. Unnecessary clocks should be stopped accordingly.

Stopping low-speed on-chip oscillator oscillation: CM14 bit in CM1 register Stopping high-speed on-chip oscillator oscillation: HRA00 bit in HRA0 register

21.2.4 Selecting Oscillation Drive Capacity

Set the drive capacity of the XCIN clock oscillation circuit to "LOW". Confirm that the circuit oscillates stably while it is in the "LOW" state.

Selecting XCIN-XCOUT drive capacity: CM03 bit in CM0 register

21.2.5 Wait Mode, Stop Mode

Power consumption can be reduced in wait mode and stop mode. Refer to 11.4 Power Control for details.

21.2.6 Stopping Peripheral Function Clocks

If the peripheral function f1, f2, f4, f8, and f32 clocks are not necessary in wait mode, set the CM02 bit in the CM0 register to 1 (peripheral function clock stops in wait mode). This will stop the f1, f2, f4, f8, and f32 clocks in wait mode.

21.2.7 Timers

If timer RA is not used, set the TCKCUT bit in the TRAMR register to 1 (count source cutoff). If timer RB is not used, set the TCKCUT bit in the TRBMR register to 1 (count source cutoff).

21.2.8 Reducing Internal Power Consumption

When the MCU enters wait mode using low-speed clock mode or low-speed on-chip oscillator mode, internal power consumption can be reduced by using the VCA20 bit in the VCA2 register. Figure 21.1 shows the Handling Procedure of Internal Power Low Consumption Using VCA20 Bit. To enable internal power low consumption by the VCA20 bit, follow Figure 21.1 Handling Procedure of Internal Power Low Consumption Using VCA20 Bit.



21.2.9 Stopping Flash Memory

In low-speed on-chip oscillator mode and low-speed clock mode, power consumption can be further reduced by stopping the flash memory using the FMSTP bit in the FMR0 register.

Access to the flash memory is disabled by setting the FMSTP bit to 1 (flash memory stops). The FMSTP bit must be written to by a program transferred to RAM.

When the MUC enters stop mode or wait mode while CPU rewrite mode is disabled, the power for the flash memory is automatically turned off. It is turned back on again after the MCU exit stop mode or wait mode. This eliminates the need to set the FMR0 register.

Figure 21.2 shows the Handling Procedure Example of Low Power Consumption Using FMSTP Bit.



Figure 21.2 Handling Procedure Example of Low Power Consumption Using FMSTP Bit

21.2.10 Low-Current-Consumption Read Mode

In low-speed clock mode and low-speed on-chip oscillator mode, the current consumption when reading the flash memory can be reduced by setting the FMR47 bit in the FMR4 register to 1 (enabled). Figure 21.3 shows the Handling Procedure Example of Low-Current-Consumption Read Mode.



Figure 21.3 Handling Procedure Example of Low-Current-Consumption Read Mode

22. Electrical Characteristics

Table 22.1	Absolute	Maximum	Ratings
------------	----------	---------	---------

Symbol	Parameter	Condition	Rated Value	Unit
Vcc	Supply voltage		-0.3 to 6.5	V
VI	Input voltage		-0.3 to Vcc + 0.3	V
Vo	Output voltage		-0.3 to Vcc + 0.3	V
Pd	Power dissipation	Topr = 25°C	500	mW
Topr	Operating ambient temperature		-20 to 85 (N version) / -40 to 85 (D version)	°C
Tstg	Storage temperature		-65 to 150	°C

Table 22.2 Recommended Operating Conditions

Symbol	Derem	otor	Conditions		Standard		Unit
Symbol	,		Conditions	Min.	Тур.	Max.	Unit
Vcc	Supply voltage			2.2	-	5.5	V
Vss	Supply voltage			-	0	-	V
Vih	Input "H" voltage			0.8 Vcc	-	Vcc	V
VIL	Input "L" voltage			0	-	0.2 Vcc	V
IOH(sum)	Peak sum output "H" current	Sum of all pins IOH(peak)		-	-	-160	mA
IOH(sum)	Average sum output "H" current	Sum of all pins IOH(avg)		-	-	-80	mA
IOH(peak)	Peak output "H" current	All pins		-	-	-10	mA
IOH(avg)	Average output "H" current	All pins		-	-	-5	mA
IOL(sum)	Peak sum output "L" currents	Sum of all pins IOL(peak)		-	-	160	mA
IOL(sum)	Average sum output "L" currents	Sum of all pins IOL(avg)		-	_	80	mA
IOL(peak)	Peak output "L" currents	All pins		-	-	10	mA
IOL(avg)	Average output "L" current	All pins		-	-	5	mA
f(XCIN)	XCIN clock input oscillation	frequency	$2.2~V \leq Vcc \leq 5.5~V$	0	-	70	kHz
-	System clock	OCD2 = 0 XCIN clock selected	$2.2 \text{ V} \leq \text{Vcc} \leq 5.5 \text{ V}$	0	-	70	kHz
		OCD2 = 1 On-chip oscillator clock selected	HRA01 = 0 Low-speed on-chip oscillator selected	_	125	_	kHz
			$\begin{array}{l} \text{HRA01 = 1} \\ \text{High-speed on-chip} \\ \text{oscillator selected} \\ \text{2.7 V} \leq \text{Vcc} \leq 5.5 \text{ V} \end{array}$	-	-	8	MHz
			$\begin{array}{l} \text{HRA01 = 1} \\ \text{High-speed on-chip} \\ \text{oscillator selected} \\ \text{2.2 V} \leq \text{Vcc} \leq 5.5 \text{ V} \end{array}$	-	-	4	MHz

NOTES:

1. Vcc = 2.2 to 5.5 V at Topr = -20 to 85°C (N version) / -40 to 85°C (D version), unless otherwise specified.

2. The average output current indicates the average value of current measured during 100 ms.



Figure 22.1 Ports P0, P1, P3, P4, and P6 Timing Measurement Circuit

Symbol	Parameter	Conditions		Unit		
	Faranieter	Conditions	Min.	Тур.	Max.	Unit
-	Program/erase endurance ⁽²⁾		100 ⁽³⁾	-	-	times
-	Byte program time		-	50	400	μs
-	Block erase time		-	0.4	9	S
-	Program, erase voltage		2.7	-	5.5	V
-	Read voltage		2.2	-	5.5	V
-	Program, erase temperature		0	-	60	°C
-	Data hold time ⁽⁷⁾	Ambient temperature = 55°C	20	-	_	year

Table 22.3 Flash Memory (Program ROM) Electrical Characteristics

NOTES:

1. Vcc = 2.7 to 5.5 V at Topr = 0 to 60°C, unless otherwise specified.

Definition of programming/erasure endurance
 The programming and erasure endurance is defined on a per-block basis.
 If the programming and erasure endurance is n (n = 100 or 10,000), each block can be erased n times. For example, if 1,024
 1-byte writes are performed to block A, a 1 Kbyte block, and then the block is erased, the programming/erasure endurance still stands at one.

However, the same address must not be programmed more than once per erase operation (overwriting prohibited).

Endurance to guarantee all electrical characteristics after program and erase. (1 to Min. value can be guaranteed).
 In a system that executes multiple programming operations, the actual erasure count can be reduced by writing to sequential addresses in turn so that as much of the block as possible is used up before performing an erase operation. For example, when programming groups of 16 bytes, the effective number of rewrites can be minimized by programming up to 128 groups before erasing them all in one operation. It is also advisable to retain data on the erase count of each block and limit the number of erase operations to a certain number.

5. If an error occurs during block erase, attempt to execute the clear status register command, then execute the block erase command at least three times until the erase error does not occur.

6. Customers desiring program/erase failure rate information should contact their Renesas technical support representative.

7. The data hold time includes time that the power supply is off or the clock is not supplied.

Symbol	Parameter	Condition		Unit		
Symbol	Falameter	Condition	Min.	Тур.	Max.	Unit
Vdet0	Voltage detection level		2.2	2.3	2.4	V
_	Voltage detection circuit self power consumption	VCA25 = 1, Vcc = 5.0 V	_	0.9	-	μA
td(E-A)	Waiting time until voltage detection circuit operation starts ⁽²⁾		-	-	300	μS
Vccmin	MCU operating voltage minimum value		2.2	-	-	V

Table 22.4 Voltage Detection 0 Circuit Electrical Characteristics

NOTES:

1. The measurement condition is Vcc = 2.2 to 5.5 V and Topr = -20 to 85°C (N version) / -40 to 85°C (D version).

2. Necessary time until the voltage detection circuit operates when setting to 1 again after setting the VCA25 bit in the VCA2 register to 0.

Table 22.5 Voltage Detection 1 Circuit Electrical Characteristics

Symbol	Parameter	Condition		Unit		
Symbol		Condition	Min.	Тур.	Max.	Unit
Vdet1	Voltage detection level ⁽⁴⁾		2.70	2.85	3.00	V
-	Voltage monitor 1 interrupt request generation time ⁽²⁾		_	40	-	μs
-	Voltage detection circuit self power consumption	VCA26 = 1, Vcc = 5.0 V	-	0.6	-	μA
td(E-A)	Waiting time until voltage detection circuit operation starts ⁽³⁾		-	-	100	μS

NOTES:

- 1. The measurement condition is Vcc = 2.2 to 5.5 V and T_{opr} = -20 to 85°C (N version) / -40 to 85°C (D version).
- 2. Time until the voltage monitor 1 interrupt request is generated after the voltage passes Vdet1.
- 3. Necessary time until the voltage detection circuit operates when setting to 1 again after setting the VCA26 bit in the VCA2 register to 0.
- 4. This parameter shows the voltage detection level when the power supply drops. The voltage detection level when the power supply rises is higher than the voltage detection level when the power supply drops by approximately 0.1 V.

Table 22.6 Voltage Detection 2 Circuit Electrical Characteristics

Symbol	Parameter	Condition		Unit		
Symbol	Falameter	Condition	Min.	Тур.	Max.	Unit
Vdet2	Voltage detection level		3.3	3.6	3.9	V
-	Voltage monitor 2 interrupt request generation time ⁽²⁾		-	40	-	μS
-	Voltage detection circuit self power consumption	VCA27 = 1, Vcc = 5.0 V	-	0.6	-	μA
td(E-A)	Waiting time until voltage detection circuit operation starts ⁽³⁾		-	-	100	μS

NOTES:

1. The measurement condition is Vcc = 2.2 to 5.5 V and Topr = -20 to 85°C (N version) / -40 to 85°C (D version).

2. Time until the voltage monitor 2 interrupt request is generated after the voltage passes Vdet2.

3. Necessary time until the voltage detection circuit operates after setting to 1 again after setting the VCA27 bit in the VCA2 register to 0.

Symbol	Parameter	Condition		Unit		
	Falanielei	Condition	Min.	Тур.	Max.	Unit
Vpor1	Power-on reset valid voltage ⁽⁴⁾		-	-	0.1	V
Vpor2	Power-on reset or voltage monitor 0 reset valid voltage		0	-	Vdet0	V
trth	External power Vcc rise gradient ⁽²⁾		20	_	-	mV/msec

NOTES:

- 1. The measurement condition is Topr = -20 to 85°C (N version) / -40 to 85°C (D version), unless otherwise specified.
- 2. This condition (external power Vcc rise gradient) does not apply if Vcc \ge 1.0 V.
- 3. To use the power-on reset function, enable voltage monitor 0 reset by setting the LVD0ON bit in the OFS register to 0, the VW0C0 and VW0C6 bits in the VW0C register to 1 respectively, and the VCA25 bit in the VCA2 register to 1.
- 4. $t_{w(por1)}$ indicates the duration the external power Vcc must be held below the effective voltage (Vpor1) to enable a power on reset. When turning on the power for the first time, maintain $t_{w(por1)}$ for 30 s or more if $-20^{\circ}C \le T_{opr} \le 85^{\circ}C$, maintain $t_{w(por1)}$ for 3,000 s or more if $-40^{\circ}C \le T_{opr} < -20^{\circ}C$.



- 1. When using the voltage monitor 0 digital filter, ensure that the voltage is within the MCU operation voltage range (2.2 V or above) during the sampling time.
- The sampling clock can be selected. Refer to 6. Voltage Detection Circuit for details.
- 3. Vdet0 indicates the voltage detection level of the voltage detection 0 circuit. Refer to 6. Voltage Detection Circuit for details.

Figure 22.2 Reset Circuit Electrical Characteristics

Vcref External Vcin External range Vofs Input offs	Parameter	Condition		Unit		
	Farameter	Condition	Min.	Тур.	Max.	Unit
Vref	Internal reference voltage	Vcc = 2.2 V to 5.5 V, Topr = 25°C	1.15	1.25	1.35	V
		Vcc = 2.2 V to 5.5 V, Topr = -40 to 85°C	_	1.25	-	V
Vcref	External input reference voltage	Vcc = 2.2 V to 4.0 V	0.5	-	Vcc - 1.1	V
		Vcc = 4.0 V to 5.5 V	0.5	-	Vcc - 1.5	
Vcin	External comparison voltage input range		-0.3	-	Vcc + 0.3	V
Vofs	Input offset voltage		-	20	120	mV
Tcrsp	Response time		-	4	-	μS

Table 22.8	Comparator Electrical Characteristics
------------	---------------------------------------

NOTE:

1. The measurement condition is Topr = -20 to 85°C (N version) / -40 to 85°C (D version), unless otherwise specified.

Table 22.9 **High-speed On-Chip Oscillator Circuit Electrical Characteristics**

Symbol	Parameter	Condition	Standard			Unit
Symbol	Faranteter	Condition	Min.	Тур.	Max.	Unit
fOCO-F	High-speed on-chip oscillator frequency temperature • supply voltage dependence	$V_{CC} = 4.75 V \text{ to } 5.25 V$ Topr = 0 to $60^{\circ}C^{(2)}$	7.76	8	8.24	MHz
		$V_{CC} = 2.7 V \text{ to } 5.5 V$ $T_{opr} = -20 \text{ to } 85^{\circ}C^{(2)}$	7.68	8	8.32	MHz
		$V_{CC} = 2.7 V \text{ to } 5.5 V$ Topr = -40 to $85^{\circ}C^{(2)}$	7.44	8	8.32	MHz
		V_{CC} = 2.2 V to 5.5 V Topr = -20 to 85°C ⁽³⁾	7.04	8	8.96	MHz
		$V_{CC} = 2.2 \text{ V to } 5.5 \text{ V}$ $T_{opr} = -40 \text{ to } 85^{\circ}C^{(3)}$	6.8	8	9.2	MHz

NOTES:

1. The measurement condition is Topr = -20 to 85°C (N version) / -40 to 85°C (D version), unless otherwise specified.

2. These standard values show when the HRA1 register is set to the value before shipment and the HRA2 register is set to 00h.

3. These standard values show when the correction value in the FRA6 register is written into the HRA1 register.

Table 22.10 Low-speed On-Chip Oscillator Circuit Electrical Characteristics

Symbol	Parameter	Parameter Condition		Standard			
Symbol		Condition	Min.	Тур.	Max.	Unit	
fOCO-S	Low-speed on-chip oscillator frequency		30	125	250	kHz	
-	Oscillation stability time		-	10	100	μS	
-	Self power consumption at oscillation	Vcc = 5.0 V, Topr = 25°C	-	15	-	μA	

NOTE:

1. Vcc = 2.2 to 5.5 V, Topr = -20 to 85°C (N version) / -40 to 85°C (D version), unless otherwise specified.

Table 22.11 Power Supply Circuit Timing Characteristics

Symbol Parameter		Condition	Standard			Unit
Symbol	T arameter	Condition	Min.	Тур.	Max.	Onit
td(P-R)	Time for internal power supply stabilization during power-on ⁽²⁾		1	-	2000	μs
td(R-S)	STOP exit time ⁽³⁾		-	-	150	μs

NOTES:

The measurement condition is Vcc = 2.2 to 5.5 V and Topr = 25°C.
 Waiting time until the internal power supply generation circuit stabilizes during power-on.
 Time until system clock supply starts after the interrupt is acknowledged to exit stop mode.

Symbol	Dor	ameter	Condition	S	Standard		
Symbol			Min.	Тур.	Max.	Unit	
Vон	Output "H" voltage		Iон = –5 mA	Vcc - 2.0	-	Vcc	V
			Іон = –200 µА	Vcc - 0.5	-	Vcc	V
Vol	Output "L" voltage		IoL = 5 mA	-	-	2.0	V
			IoL = 200 μA	-	-	0.45	V
Vt+-Vt-	Hysteresis	INT0, INT1, INT2, INT4, KI0, KI1, KI2, KI3, RXD0, RXD2, CLK0, CLK2		0.1	0.5	_	V
		RESET		0.1	1.0	-	V
Ін	Input "H" current		VI = 5 V, Vcc = 5 V	-	-	5.0	μA
lı∟	Input "L" current		VI = 0 V, Vcc = 5 V	-	-	-5.0	μA
RPULLUP	Pull-up resistance		VI = 0 V, Vcc = 5 V	30	50	167	kΩ
Rfxcin	Feedback resistance	XCIN		-	18	-	MΩ
VRAM	RAM hold voltage		During stop mode	2.0	-	-	V

NOTE: 1. Vcc = 4.2 to 5.5 V at T_{opr} = -20 to 85°C (N version) / -40 to 85°C (D version), unless otherwise specified.

Symbol	Parameter		Condition		Standar	d	Uni
	. aramotor			Min.	Тур.	Max.	
lcc	Power supply current $(Vcc = 3.3 \text{ to } 5.5 \text{ V})$	High-speed on-chip oscillator mode	High-speed on-chip oscillator on = 8 MHz Low-speed on-chip oscillator on = 125 kHz No division	-	5	8	mA
Single-chip mode, output pins are open, other pins are Vss		High-speed on-chip oscillator on = 8 MHz Low-speed on-chip oscillator on = 125 kHz Divide-by-8	-	2	-	mA	
	Low-speed on-chip oscillator mode	High-speed on-chip oscillator off Low-speed on-chip oscillator on = 125 kHz Divide-by-8, FMR47 = 1	-	130	300	μA	
		Low-speed clock mode	High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) FMR47 = 1	-	130	300	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) Program operation on RAM Flash memory off, FMSTP = 1	_	30	_	μA
		Wait mode	High-speed on-chip oscillator off Low-speed on-chip oscillator on = 125 kHz While a WAIT instruction is executed Peripheral clock operation VCA27 = VCA26 = VCA25 = 0 VCA20 = 1	_	25	75	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator on = 125 kHz While a WAIT instruction is executed Peripheral clock off VCA27 = VCA26 = VCA25 = 0 VCA20 = 1	_	23	60	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (high drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit disabled (BGRCR0 = 1)	_	4	_	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit disabled (BGRCR0 = 1)	-	2.2	-	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (high drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit enabled (BGRCR0 = 0)	-	8	_	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit enabled (BGRCR0 = 0)	_	6	_	μA
		Stop mode	XCIN clock off, Topr = 25°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit disabled (BGRCR0 = 1)		0.8	3	μA
			XCIN clock off, Topr = 85°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit disabled (BGRCR0 = 1)	-	1.2	_	μA
			XCIN clock off, Topr = 25°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit enabled (BGRCR0 = 0)	_	5	8	μA
			XCIN clock off, Topr = 85°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit enabled (BGRCR0 = 0)	_	5.5	_	μA

Table 22.13Electrical Characteristics (2) [Vcc = 5 V]
(Topr = -20 to 85°C (N version) / -40 to 85°C (D version), unless otherwise specified.)

Timing Requirements (Unless Otherwise Specified: Vcc = 5 V, Vss = 0 V at Topr = 25°C) [Vcc = 5 V]

Table 22.14 XCIN Input

	Parameter		Standard	
	Farameter	Min.	Max.	Unit
tc(XCIN)	XCIN input cycle time	14	-	μS
twh(xcin)	XCIN input "H" width	7	-	μS
twl(xcin)	XCIN input "L" width	7	-	μS



Figure 22.3 XCIN Input Timing Diagram when Vcc = 5 V

Table 22.15 TRAIO Input

Symbol	Parameter		Standard	
			Max.	Unit
tc(TRAIO)	TRAIO input cycle time	100	-	ns
twh(traio)	TRAIO input "H" width	40	-	ns
twl(traio)	TRAIO input "L" width	40	-	ns



Figure 22.4 TRAIO Input Timing Diagram when Vcc = 5 V

Table 22.16	Serial Interface
-------------	------------------

Symbol	Parameter	Star	Standard		
tc(CK) (tw(CKH) (tw(CKL) (Falanetei	Min.	Max.	Unit	
tc(CK)	CLKi input cycle time	200	-	ns	
tw(скн)	CLKi input "H" width	100	-	ns	
tw(CKL)	CLKi input "L" width	100	-	ns	
td(C-Q)	TXDi output delay time	-	50	ns	
th(C-Q)	TXDi hold time	0	-	ns	
tsu(D-C)	RXDi input setup time	50	-	ns	
th(C-D)	RXDi input hold time	90	-	ns	

i = 0 or 2



Figure 22.5 Serial Interface Timing Diagram when Vcc = 5 V

Table 22.17 External Interrupt INTi (i = 0, 1, 2, 4) Input

Symbol	Parameter		Standard		
			Max.	Unit	
tw(INH)	INTi input "H" width	250(1)	-	ns	
tw(INL)	INTi input "L" width	250 ⁽²⁾	-	ns	

NOTES:

1. When selecting the digital filter by the INTi input filter select bit, use an INTi input HIGH width of either (1/digital filter clock frequency × 3) or the minimum value of standard, whichever is greater.

2. When selecting the digital filter by the INTi input filter select bit, use an INTi input LOW width of either (1/digital filter clock frequency × 3) or the minimum value of standard, whichever is greater.



Figure 22.6 External Interrupt INTi Input Timing Diagram when Vcc = 5 V

Sumbol	Der	Parameter	Condition	Standard			Unit
Symbol	Parameter		Condition	Min.	Тур.	Max.	Unit
Vон	Output "H" voltage		Іон = –1 mA	Vcc - 0.5	-	Vcc	V
Vol	Output "L" voltage		IoL = 1 mA	-	-	0.5	V
Vt+-Vt-	Hysteresis	INT0, INT1, INT2, INT4, KI0, KI1, KI2, KI3, RXD0, RXD2, CLK0, CLK2		0.1	0.3	_	V
		RESET		0.1	0.4	-	V
Ін	Input "H" current		VI = 3 V, Vcc = 3 V	-	I	4.0	μA
lı∟	Input "L" current		VI = 0 V, Vcc = 3 V	-	-	-4.0	μA
Rpullup	Pull-up resistance		VI = 0 V, Vcc = 3 V	66	160	500	kΩ
Rfxcin	Feedback resistance	XCIN		-	18	_	MΩ
VRAM	RAM hold voltage		During stop mode	1.8	I	-	V

Table 22.18 Electrical Characteristics (3) [Vcc = 3 V]

NOTE: 1. Vcc =2.7 to 3.3 V at T_{opr} = -20 to 85°C (N version) / -40 to 85°C (D version), unless otherwise specified.

Symbol	Parameter		Condition	9	Standar	d	Uni
5,				Min.	Тур.	Max.	
Icc	Power supply current $(Vcc = 2.7 \text{ to } 3.3 \text{ V})$	High-speed on-chip oscillator mode	High-speed on-chip oscillator on = 8 MHz Low-speed on-chip oscillator on = 125 kHz No division	-	5	-	mA
	Single-chip mode, output pins are open, other pins are Vss		High-speed on-chip oscillator on = 8 MHz Low-speed on-chip oscillator on = 125 kHz Divide-by-8	-	2	-	mA
		Low-speed on-chip oscillator mode	High-speed on-chip oscillator off Low-speed on-chip oscillator on = 125 kHz Divide-by-8, FMR47 = 1	-	130	300	μA
		Low-speed clock mode	High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) FMR47 = 1	-	130	300	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) Program operation on RAM Flash memory off, FMSTP = 1	_	30	_	μA
		Wait mode	High-speed on-chip oscillator off Low-speed on-chip oscillator on = 125 kHz While a WAIT instruction is executed Peripheral clock operation VCA27 = VCA26 = VCA25 = 0 VCA20 = 1	_	25	70	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator on = 125 kHz While a WAIT instruction is executed Peripheral clock off VCA27 = VCA26 = VCA25 = 0 VCA20 = 1	_	23	55	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (high drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit disabled (BGRCR0 = 1)	_	3.8	-	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit disabled (BGRCR0 = 1)	_	2	_	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (high drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit enabled (BGRCR0 = 0)	-	8	-	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit enabled (BGRCR0 = 0)	_	6	_	μA
		Stop mode	XCIN clock off, Topr = 25°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit disabled (BGRCR0 = 1)	_	0.7	3	μA
			XCIN clock off, Topr = 85°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit disabled (BGRCR0 = 1)	_	1.1	_	μA
			XCIN clock off, Topr = 25°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit enabled (BGRCR0 = 0)	_	5	7	μA
			XCIN clock off, Topr = 85°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit enabled (BGRCR0 = 0)	_	5.5	_	μA

Table 22.19Electrical Characteristics (4) [Vcc = 3 V]
(Topr = -20 to 85°C (N version) / -40 to 85°C (D version), unless otherwise specified.)

Timing requirements (Unless Otherwise Specified: Vcc = 3 V, Vss = 0 V at Topr = 25°C) [Vcc = 3 V]

Table 22.20 XCIN Input

Symbol	Parameter		Standard		
Symbol			Max.	Unit	
tc(XCIN)	XCIN input cycle time	14	-	μS	
twh(xcin)	XCIN input "H" width		-	μS	
twl(xcin)	XCIN input "L" width	7	-	μS	





Table 22.21 TRAIO Input

Symbol	Parameter		Standard		
			Max.	Unit	
tc(TRAIO)	TRAIO input cycle time	300	-	ns	
twh(traio)	TRAIO input "H" width	120	-	ns	
twl(traio)	TRAIO input "L" width	120	-	ns	



Figure 22.8 TRAIO Input Timing Diagram when Vcc = 3 V

Table 22.22	Serial	Interface
-------------	--------	-----------

Symbol	Parameter		Standard		
			Max.	Unit	
tc(CK)	CLKi input cycle time	300	-	ns	
tw(скн)	CLKi input "H" width	150	-	ns	
tW(CKL)	CLKi Input "L" width	150	-	ns	
td(C-Q)	TXDi output delay time	-	80	ns	
th(C-Q)	TXDi hold time	0	-	ns	
tsu(D-C)	RXDi input setup time	70	-	ns	
t h(C-D)	RXDi input hold time	90	-	ns	

i = 0 or 2





Table 22.23External Interrupt INTi (i = 0, 1, 2, 4) Input

Symbol	Parameter		Standard		
			Max.	Unit	
tw(INH)	INTi input "H" width	380 ⁽¹⁾	-	ns	
tw(INL)	INTi input "L" width	380(2)	_	ns	

NOTES:

1. When selecting the digital filter by the INTi input filter select bit, use an INTi input HIGH width of either (1/digital filter clock frequency × 3) or the minimum value of standard, whichever is greater.

2. When selecting the digital filter by the INTi input filter select bit, use an INTi input LOW width of either (1/digital filter clock frequency × 3) or the minimum value of standard, whichever is greater.



Figure 22.10 External Interrupt INTi Input Timing Diagram when Vcc = 3 V

Sumbol	Dor	Parameter	Condition	Standard			Unit
Symbol	Parameter		Condition	Min.	Тур.	Max.	Unit
Vон	Output "H" voltage		Іон = –1 mA	Vcc - 0.5	-	Vcc	V
Vol	Output "L" voltage		IOL = 1 mA	-	-	0.5	V
Vt+-Vt-	Hysteresis	INT0, INT1, INT2, INT4, KI0, KI1, KI2, KI3, RXD0, RXD2, CLK0, CLK2		0.05	0.3	-	V
		RESET		0.05	0.15	-	V
Ін	Input "H" current		VI = 2.2 V	-	-	4.0	μA
lı∟	Input "L" current		VI = 0 V	-	-	-4.0	μA
Rpullup	Pull-up resistance		VI = 0 V	100	200	600	kΩ
Rfxcin	Feedback resistance	XCIN		-	35	-	MΩ
VRAM	RAM hold voltage		During stop mode	1.8	-	_	V

Table 22.24	Electrical Characteristics (5) [Vcc = 2.2 V]

NOTE: 1. Vcc = 2.2 V at T_{opr} = -20 to 85°C (N version) / -40 to 85°C (D version), unless otherwise specified.

Symbol	Parameter		Condition		Standar	d	Uni
Symbol			Condition	Min.	Тур.	Max.	
Icc	Power supply current $(Vcc = 2.2 \text{ to } 2.7 \text{ V})$	High-speed on-chip oscillator mode	High-speed on-chip oscillator on = 4 MHz Low-speed on-chip oscillator on = 125 kHz No division	-	3.5	-	mA
	Single-chip mode, output pins are open, other pins are Vss		High-speed on-chip oscillator on = 4 MHz Low-speed on-chip oscillator on = 125 kHz Divide-by-8	-	1.5	-	mA
		Low-speed on-chip oscillator mode	High-speed on-chip oscillator off Low-speed on-chip oscillator on = 125 kHz Divide-by-8, FMR47 = 1	-	100	230	μA
		Low-speed clock mode	High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) FMR47 = 1	-	100	230	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) Program operation on RAM Flash memory off, FMSTP = 1	_	25	_	μΑ
		Wait mode	High-speed on-chip oscillator off Low-speed on-chip oscillator on = 125 kHz While a WAIT instruction is executed Peripheral clock operation VCA27 = VCA26 = VCA25 = 0 VCA20 = 1	_	22	60	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator on = 125 kHz While a WAIT instruction is executed Peripheral clock off VCA27 = VCA26 = VCA25 = 0 VCA20 = 1	_	20	55	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (high drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit disabled (BGRCR0 = 1)	_	3	_	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit disabled (BGRCR0 = 1)	-	1.8	_	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (high drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit enabled (BGRCR0 = 0)	-	7	-	μA
			High-speed on-chip oscillator off Low-speed on-chip oscillator off XCIN clock oscillator on = 32 kHz (low drive) While a WAIT instruction is executed VCA27 = VCA26 = VCA25 = 0 VCA20 = 1 BGR trimming circuit enabled (BGRCR0 = 0)	-	6	_	μA
		Stop mode	XCIN clock off, Topr = 25°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit disabled (BGRCR0 = 1)	_	0.7	3	μA
			XCIN clock off, Topr = 85°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit disabled (BGRCR0 = 1)	-	1.1	-	μA
			XCIN clock off, Topr = 25°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit enabled (BGRCR0 = 0)	-	5	7	μA
			XCIN clock off, Topr = 85°C High-speed on-chip oscillator off Low-speed on-chip oscillator off CM10 = 1 Peripheral clock off VCA27 = VCA26 = VCA25 = 0 BGR trimming circuit enabled (BGRCR0 = 0)	-	5.5	_	μA

Table 22.25Electrical Characteristics (6) [Vcc = 2.2 V]
(Topr = -20 to 85°C (N version) / -40 to 85°C (D version), unless otherwise specified.)

Timing requirements (Unless Otherwise Specified: Vcc = 2.2 V, Vss = 0 V at Topr = 25°C) [Vcc = 2.2 V]

Table 22.26 XCIN Input

Symbol	Parameter		Standard		
			Max.	Unit	
tc(XCIN)	XCIN input cycle time	14	-	μS	
twh(xcin)	XCIN input "H" width	7	-	μS	
twl(xcin)	XCIN input "L" width	7	-	μS	





Table 22.27 TRAIO Input

Symbol	Parameter		Standard		
			Max.	Unit	
tc(TRAIO)	TRAIO input cycle time	500	-	ns	
twh(traio)	TRAIO input "H" width	200	-	ns	
twl(traio)	TRAIO input "L" width	200	-	ns	



Figure 22.12 TRAIO Input Timing Diagram when Vcc = 2.2 V

Table 22.28 Serial	Interface
--------------------	-----------

Symbol	Parameter	Standard		Unit
		Min.	Max.	Unit
tc(CK)	CLKi input cycle time	800	-	ns
tw(скн)	CLKi input "H" width	400	-	ns
tW(CKL)	CLKi input "L" width	400	-	ns
td(C-Q)	TXDi output delay time	-	200	ns
th(C-Q)	TXDi hold time	0	-	ns
tsu(D-C)	RXDi input setup time	150	-	ns
th(C-D)	RXDi input hold time	90	-	ns

i = 0 or 2





Table 22.29 External Interrupt INTi (i = 0, 1, 2, 4) Input

Symbol	Parameter	Standard		Unit
		Min.	Max.	Unit
tw(INH)	INTi input "H" width	1000(1)	-	ns
tw(INL)	INTi input "L" width	1000(2)	I	ns

NOTES:

1. When selecting the digital filter by the INTi input filter select bit, use an INTi input HIGH width of either (1/digital filter clock frequency × 3) or the minimum value of standard, whichever is greater.

When selecting the digital filter by the INTi input filter select bit, use an INTi input LOW width of either (1/digital filter clock frequency × 3) or the minimum value of standard, whichever is greater.



Figure 22.14 External Interrupt INTi Input Timing Diagram when Vcc = 2.2 V

23. Usage Notes

23.1 Notes on I/O Ports

23.1.1 Port P4_3, P4_4

Ports P4_3 and P4_4 are also used as the XCIN function and the XCOUT function, respectively. During a reset period and after a reset release, these ports are set to the XCIN and XCOUT functions. Pins P4_3 and P4_4 can be switched to the port functions by setting the CM04 bit in the CM0 register to 0 (ports P4_3 and P4_4) by a program.

To use ports P4_3 and P4_4 as ports, note the following:

• Port P4_3

After a reset until the CM04 bit is set to 0 (ports P4_3 and P4_4) by a program, a typical 10 M Ω impedance is connected between the P4_3 pin and the MCU power supply or GND. If the XCIN is set to intermediate-level input or left floating, a shoot-through current flows into the oscillation driver.

• Port P4_4

Use port P4_4 as an output port by setting the PD4_4 bit in the PD4 register to 1 (output mode). After a reset until the CM04 bit is set to 0 (ports P4_3 and P4_4) by a program, the P4_4 pin may output an intermediate potential of about 2.0 V.

23.2 Notes on Clock Generation Circuit

23.2.1 Stop Mode

When entering stop mode, set the FMR01 bit in the FMR0 register to 0 (CPU rewrite mode disabled) and the CM10 bit in the CM1 register to 1 (stop mode). An instruction queue pre-reads 4 bytes from the instruction which sets the CM10 bit to 1 (stop mode) and the program stops.

Insert at least 4 NOP instructions following the JMP.B instruction after the instruction which sets the CM10 bit to 1.

• Program example to enter stop mode

BCLR	1,FMR0	; CPU rewrite mode disabled
BSET	0,PRCR	; Protect disabled
FSET	Ι	; Enable interrupt
BSET	0,CM1	; Stop mode
JMP.B	LABEL_001	
LABEL_001 :		
NOP		
NOP		
NOP		
NOP		

23.2.2 Wait Mode

When entering wait mode, set the FMR01 bit in the FMR0 register to 0 (CPU rewrite mode disabled) and execute the WAIT instruction. An instruction queue pre-reads 4 bytes from the WAIT instruction and the program stops. Insert at least 4 NOP instructions after the WAIT instruction.

• Program example to execute the WAIT instruction

BCLR 1,FMR0 FSET I WAIT NOP NOP NOP NOP ; CPU rewrite mode disabled ; Enable interrupt ; Wait mode

23.2.3 Oscillation Circuit Constants

Ask the manufacturer of the oscillator to specify the best oscillation circuit constants for your system.

23.3 Notes on Interrupts

23.3.1 Reading Address 00000h

Do not read address 00000h by a program. When a maskable interrupt request is acknowledged, the CPU reads interrupt information (interrupt number and interrupt request level) from 00000h in the interrupt sequence. At this time, the acknowledged interrupt IR bit is set to 0.

If address 00000h is read by a program, the IR bit for the interrupt which has the highest priority among the enabled interrupts is set to 0. This may cause the interrupt to be canceled, or an unexpected interrupt to be generated.

23.3.2 SP Setting

Set any value in the SP before an interrupt is acknowledged. The SP is set to 0000h after reset. Therefore, if an interrupt is acknowledged before setting a value in the SP, the program may run out of control.

23.3.3 External Interrupt and Key Input Interrupt

Either "L" level or an "H" level of width shown in the Electrical Characteristics is necessary for the signal input to pins $\overline{INT0}$, $\overline{INT1}$, $\overline{INT2}$, $\overline{INT4}$ and pins $\overline{K10}$ to $\overline{K13}$, regardless of the CPU clock. For details, refer to <u>Table 22.17</u> (VCC = 5V), Table 22.23 (VCC = 3V), and Table 22.29 (VCC = 2.2V) **External Interrupt INTi** (i = 0, 1, 2, 4) Input.

23.3.4 **Changing Interrupt Sources**

The IR bit in the interrupt control register may be set to 1 (interrupt requested) when the interrupt source changes. When using an interrupt, set the IR bit to 0 (no interrupt requested) after changing the interrupt source. In addition, changes of interrupt sources include all factors that change the interrupt sources assigned to individual software interrupt numbers, polarities, and timing. Therefore, if a mode change of a peripheral function involves interrupt sources, edge polarities, and timing, set the IR bit to 0 (no interrupt requested) after the change. Refer to the individual peripheral function for its related interrupts.

Figure 23.1 shows an Example of Procedure for Changing Interrupt Sources.



23.3.5 Changing Interrupt Control Register Contents

- (a) The contents of an interrupt control register can only be changed while no interrupt requests corresponding to that register are generated. If interrupt requests may be generated, disable interrupts before changing the interrupt control register contents.
- (b) When changing the contents of an interrupt control register after disabling interrupts, be careful to choose appropriate instructions.

Changing any bit other than IR bit

If an interrupt request corresponding to a register is generated while executing the instruction, the IR bit may not be set to 1 (interrupt requested), and the interrupt request may be ignored. If this causes a problem, use the following instructions to change the register: AND, OR, BCLR, BSET **Changing IR bit**

If the IR bit is set to 0 (interrupt not requested), it may not be set to 0 depending on the instruction used. Therefore, use the MOV instruction to set the IR bit to 0.

(c) When disabling interrupts using the I flag, set the I flag as shown in the sample programs below. Refer to (b) regarding changing the contents of interrupt control registers by the sample programs.

Sample programs 1 to 3 are for preventing the I flag from being set to 1 (interrupts enabled) before the interrupt control register is changed for reasons of the internal bus or the instruction queue buffer.

Example 1: Use NOP instructions to prevent I flag from being set to 1 before interrupt control register is changed

INT_SWITC	H1:	
FCLR	Ι	; Disable interrupts
AND.B	#00H,0056H	; Set TRAIC register to 00h
NOP		•
NOP		
FSET	Ι	; Enable interrupts

Example 2: Use dummy read to delay FSET instruction

INT_SWITCH2:

FCLR	Ι	; Disable interrupts
AND.B	#00H,0056H	; Set TRAIC register to 00h
MOV.W	MEM,R0	; <u>Dummy read</u>
FSET	Ι	; Enable interrupts

Example 3: Use POPC instruction to change I flag

INT_SWITC	H3:	
PUSHC	FLG	
FCLR	Ι	; Disable interrupts
AND.B	#00H,0056H	; Set TRAIC register to 00h
POPC	FLG	; Enable interrupts
		-

23.4 Notes on ID Code Areas

23.4.1 Setting Example of ID Code Areas

As the ID code areas are allocated in the flash memory (not in the SFRs), they cannot be rewritten by executing an instruction. Write appropriate values when creating a program. The following shows a setting example.

• To set 55h in all of the ID code areas

.org 00FFDCH

.lword dummy (5500000h)	; UND
.lword dummy (5500000h)	; INTO
.lword dummy ; BREAK	
.lword dummy (5500000h)	; ADDRESS MATCH
.lword dummy (5500000h)	; SET SINGLE STEP
.lword dummy (5500000h)	; WDT
.lword dummy (5500000h)	; ADDRESS BREAK
.lword dummy (5500000h)	; RESERVE

(Programming formats vary depending on the compiler. Check the compiler manual.)

23.5 Notes on Option Function Select Area

23.5.1 Setting Example of Option Function Select Area

As the option function select area is allocated in the flash memory (not in the SFRs), they cannot be rewritten by executing an instruction. Write appropriate values when creating a program. The following shows a setting example.

• To set FFh in the OFS register .org 00FFFCH .lword reset | (0FF000000h) ; RESET (Programming formats vary depending on the compiler. Check the compiler manual.)

23.6 Notes on Timers

23.6.1 Notes on Timer RA

- Timer RA stops counting after a reset. Set the values in the timer RA and timer RA prescalers before the count starts.
- Even if the prescaler and timer RA are read out in 16-bit units, these registers are read 1 byte at a time by the MCU. Consequently, the timer value may be updated during the period when these two registers are being read.
- In pulse period measurement mode, bits TEDGF and TUNDF in the TRACR register can be set to 0 by writing 0 to these bits by a program. However, these bits remain unchanged if 1 is written. When using the READ-MODIFY-WRITE instruction for the TRACR register, the TEDGF or TUNDF bit may be set to 0 although these bits are set to 1 while the instruction is being executed. In this case, write 1 to the TEDGF or TUNDF bit which is not supposed to be set to 0 with the MOV instruction.
- When changing to pulse period measurement mode from another mode, the contents of bits TEDGF and TUNDF are undefined. Write 0 to bits TEDGF and TUNDF before the count starts.
- The TEDGF bit may be set to 1 by the first timer RA prescaler underflow generated after the count starts.
- When using the pulse period measurement mode, leave two or more periods of the timer RA prescaler immediately after the count starts, then set the TEDGF bit to 0.
- The TCSTF bit retains 0 (count stops) for 0 to 1 cycle of the count source after setting the TSTART bit to 1 (count starts) while the count is stopped.

During this time, do not access registers associated with timer $RA^{(1)}$ other than the TCSTF bit. Timer RA starts counting at the first valid edge of the count source after The TCSTF bit is set to 1 (during count). The TCSTF bit remains 1 for 0 to 1 cycle of the count source after setting the TSTART bit to 0 (count stops) while the count is in progress. Timer RA counting is stopped when the TCSTF bit is set to 0. During this time, do not access registers associated with timer $RA^{(1)}$ other than the TCSTF bit.

NOTE:

1. Registers associated with timer RA: TRACR, TRAIOC, TRAMR, TRAPRE, and TRA.

- When the TRAPRE register is continuously written during count operation (TCSTF bit is set to 1), allow three or more cycles of the count source clock for each write interval.
- When the TRA register is continuously written during count operation (TCSTF bit is set to 1), allow three or more cycles of the prescaler underflow for each write interval.

23.6.2 Notes on Timer RB

- Timer RB stops counting after a reset. Set the values in the timer RB and timer RB prescalers before the count starts.
- Even if the prescaler and timer RB is read out in 16-bit units, these registers are read 1 byte at a time by the MCU. Consequently, the timer value may be updated during the period when these two registers are being read.
- In programmable one-shot generation mode and programmable wait one-shot generation mode, when setting the TSTART bit in the TRBCR register to 0, 0 (stops counting) or setting the TOSSP bit in the TRBOCR register to 1 (stops one-shot), the timer reloads the value of reload register and stops. Therefore, in programmable one-shot generation mode and programmable wait one-shot generation mode, read the timer count value before the timer stops.
- The TCSTF bit remains 0 (count stops) for 1 to 2 cycles of the count source after setting the TSTART bit to 1 (count starts) while the count is stopped.

During this time, do not access registers associated with timer $RB^{(1)}$ other than the TCSTF bit. Timer RB starts counting at the first valid edge of the count source after the TCSTF bit is set to 1 (during count). The TCSTF bit remains 1 for 1 to 2 cycles of the count source after setting the TSTART bit to 0 (count stops) while the count is in progress. Timer RB counting is stopped when the TCSTF bit is set to 0. During this time, do not access registers associated with timer $RB^{(1)}$ other than the TCSTF bit.

NOTE:

- 1. Registers associated with timer RB: TRBCR, TRBOCR, TRBIOC, TRBMR, TRBPRE, TRBSC, and TRBPR.
- If the TSTOP bit in the TRBCR register is set to 1 during timer operation, timer RB stops immediately.
- If 1 is written to the TOSST or TOSSP bit in the TRBOCR register, the value of the TOSSTF bit changes after one or two cycles of the count source have elapsed. If the TOSSP bit is written to 1 during the period between when the TOSST bit is written to 1 and when the TOSSTF bit is set to 1, the TOSSTF bit may be set to either 0 or 1 depending on the content state. Likewise, if the TOSSTF bit is written to 1 during the period between when the TOSSP bit is written to 1 and when the TOSSTF bit is set to 0, the TOSSTF bit may be set to either 0 or 1.

23.6.2.1 Timer mode

The following workaround should be performed in timer mode.

To write to registers TRBPRE and TRBPR during count operation (TCSTF bit is set to 1), note the following points:

- When the TRBPRE register is written continuously, allow three or more cycles of the count source for each write interval.
- When the TRBPR register is written continuously, allow three or more cycles of the prescaler underflow for each write interval.

23.6.2.2 Programmable waveform generation mode

The following three workarounds should be performed in programmable waveform generation mode.

- (1) To write to registers TRBPRE and TRBPR during count operation (TCSTF bit is set to 1), note the following points:
- When the TRBPRE register is written continuously, allow three or more cycles of the count source for each write interval.
- When the TRBPR register is written continuously, allow three or more cycles of the prescaler underflow for each write interval.
- (2) To change registers TRBPRE and TRBPR during count operation (TCSTF bit is set to 1), synchronize the TRBO output cycle using a timer RB interrupt, etc. This operation should be preformed only once in the same output cycle. Also, make sure that writing to the TRBPR register does not occur during period A shown in Figures 23.2 and 23.3.

The following shows the detailed workaround examples.

• Workaround example (a):

As shown in Figure 23.2, write to registers TRBSC and TRBPR in the timer RB interrupt routine. These write operations must be completed by the beginning of period A.



Figure 23.2 Workaround Example (a) When Timer RB interrupt is Used

• Workaround example (b):

As shown in Figure 23.3 detect the start of the primary period by the TRBO pin output level and write to registers TRBSC and TRBPR. These write operations must be completed by the beginning of period A. If the port register's bit value is read after the port direction register's bit corresponding to the TRBO pin is set to 0 (input mode), the read value indicates the TRBO pin output value.



Figure 23.3 Workaround Example (b) When TRBO Pin Output Value is Read

(3) To stop the timer counting in the primary period, use the TSTOP bit in the TRBCR register. In this case, registers TRBPRE and TRBPR are initialized and their values are set to the values after reset.

23.6.2.3 Programmable one-shot generation mode

The following two workarounds should be performed in programmable one-shot generation mode.

- (1) To write to registers TRBPRE and TRBPR during count operation (TCSTF bit is set to 1), note the following points:
- When the TRBPRE register is written continuously during count operation (TCSTF bit is set to 1), allow three or more cycles of the count source for each write interval.
- When the TRBPR register is written continuously during count operation (TCSTF bit is set to 1), allow three or more cycles of the prescaler underflow for each write interval.
- (2) Do not set both the TRBPRE and TRBPR registers to 00h.
23.6.2.4 Programmable wait one-shot generation mode

The following three workarounds should be performed in programmable wait one-shot generation mode.

- (1) To write to registers TRBPRE and TRBPR during count operation (TCSTF bit is set to 1), note the following points:
- When the TRBPRE register is written continuously, allow three or more cycles of the count source for each write interval.
- When the TRBPR register is written continuously, allow three or more cycles of the prescaler underflow for each write interval.
- (2) Do not set both the TRBPRE and TRBPR registers to 00h.
- (3) Set registers TRBSC and TRBPR using the following procedure.
 - (a) To use "INTO pin one-shot trigger enabled" as the count start condition Set the TRBSC register and then the TRBPR register. At this time, after writing to the TRBPR register, allow an interval of 0.5 or more cycles of the count source before trigger input from the INTO pin.
 - (b) To use "writing 1 to TOSST bit" as the start condition

Set the TRBSC register, the TRBPR register, and then TOSST bit. At this time, after writing to the TRBPR register, allow an interval of 0.5 or more cycles of the count source before writing to the TOSST bit.

23.6.3 Notes on Timer RE

23.6.3.1 Starting and Stopping Count

Timer RE has the TSTART bit for instructing the count to start or stop, and the TCSTF bit, which indicates count start or stop. Bits TSTART and TCSTF are in the TRECR1 register.

Timer RE starts counting and the TCSTF bit is set to 1 (count starts) when the TSTART bit is set to 1 (count starts). It takes up to 2 cycles of the count source until the TCSTF bit is set to 1 after setting the TSTART bit to 1. During this time, do not access registers associated with timer $RE^{(1)}$ other than the TCSTF bit.

Also, timer RE stops counting when setting the TSTART bit to 0 (count stops) and the TCSTF bit is set to 0 (count stops). It takes the time for up to 2 cycles of the count source until the TCSTF bit is set to 0 after setting the TSTART bit to 0. During this time, do not access registers associated with timer RE other than the TCSTF bit.

NOTE:

1. Registers associated with timer RE: TRESEC, TREMIN, TREHR, TREWK, TRECR1, TRECR2, TRECSR, and TREOPR.

23.6.3.2 Register Setting

Write to the following registers or bits when timer RE is stopped.

- Registers TRESEC, TREMIN, TREHR, TREWK, and TRECR2
- Bits H12_H24, PM, and INT in TRECR1 register
- Bits RCS0 to RCS3 in TRECSR register

Timer RE is stopped when bits TSTART and TCSTF in the TRECR1 register are set to 0 (timer RE stopped).

Also, set all above-mentioned registers and bits (immediately before timer RE count starts) before setting the TRECR2 register.

Figure 23.4 shows a Setting Example in Real-Time Clock Mode.



23.6.3.3 Time Reading Procedure of Real-Time Clock Mode

In real-time clock mode, read registers TRESEC, TREMIN, TREHR, and TREWK when time data is updated and read the PM bit in the TRECR1 register when the BSY bit is set to 0 (not while data is updated). Also, when reading several registers, an incorrect time will be read if data is updated before another register is read after reading any register.

In order to prevent this, use the reading procedure shown below.

• Using an interrupt

Read necessary contents of registers TRESEC, TREMIN, TREHR, and TREWK and the PM bit in the TRECR1 register in the timer RE interrupt routine.

• Monitoring with a program 1

Monitor the IR bit in the TREIC register with a program and read necessary contents of registers TRESEC, TREMIN, TREHR, and TREWK and the PM bit in the TRECR1 register after the IR bit in the TREIC register is set to 1 (timer RE interrupt request generated).

• Monitoring with a program 2

- (1) Monitor the BSY bit.
- (2) Monitor until the BSY bit is set to 0 after the BSY bit is set to 1 (approximately 62.5 ms while the BSY bit is set to 1).
- (3) Read necessary contents of registers TRESEC, TREMIN, TREHR, and TREWK and the PM bit in the TRECR1 register after the BSY bit is set to 0.

• Using read results if they are the same value twice

- (1) Read necessary contents of registers TRESEC, TREMIN, TREHR, and TREWK and the PM bit in the TRECR1 register.
- (2) Read the same register as (1) and compare the contents.
- (3) Recognize as the correct value if the contents match. If the contents do not match, repeat until the read contents match with the previous contents.

Also, when reading several registers, read them as continuously as possible.

23.6.4 Notes on Timer RF

• Access registers TRF, TRFM0, and TRFM1 in 16-bit units.

Example of reading timer RF:

MOV.W 0290H,R0 ; Read out timer RF

• In input capture mode, a capture interrupt request is generated by inputting an edge selected by bits TRFC03 and TRFC04 in the TRFCR0 register even when the TSTART bit in the TRFCR0 register is set to 0 (count stops).

23.7 Notes on Serial Interface

• When reading data from the UiRB (i = 0 or 2) register either in the clock synchronous serial I/O mode or in the clock asynchronous serial I/O mode. Ensure the data is read in 16-bit units. When the high-order byte of the UiRB register is read, bits PER and FER in the UiRB register and the RI bit in the UiC1 register are set to 0. To check receive errors, read the UiRB register and then use the read data.

Example (when reading receive buffer register): MOV.W 00A6H,R0 ; Read the U0RB register

• When writing data to the UiTB register in the clock asynchronous serial I/O mode with 9-bit transfer data length, write data to the high-order byte first then the low-order byte, in 8-bit units.

Example (when reading transmit buffer register):

1 1	0	e
MOV.B	#XXH,00A3H	; Write the high-order byte of U0TB register
MOV.B	#XXH,00A2H	; Write the low-order byte of U0TB register

23.8 Notes on Hardware LIN

For the time-out processing of the header and response fields, use another timer to measure the duration of time with a Synch Break detection interrupt as the starting point.

23.9 Notes on Flash Memory

23.9.1 CPU Rewrite Mode

23.9.1.1 Operating Speed

Before entering CPU rewrite mode (EW0 mode), select 5 MHz or below for the CPU clock using the CM06 bit in the CM0 register and bits CM16 to CM17 in the CM1 register. This does not apply to EW1 mode.

23.9.1.2 Prohibited Instructions

The following instructions cannot be used in EW0 mode because they reference data in the flash memory: UND, INTO, and BRK.

23.9.1.3 Non-Maskable Interrupts

• EW0 Mode

Once a watchdog timer, voltage monitor1, voltage monitor 2, comparator 1, or comparator 2 interrupt request is acknowledged, auto-erasure or auto-programming is forcibly stopped immediately and the flash memory is reset. Interrupt handling starts after a fixed period and the flash memory restarts.

As the block during auto-erasure or the address during auto-programming is forcibly stopped, the normal value may not be readable. Execute auto-erasure again and ensure it completes normally.

The watchdog timer does not stop during command operation, so that interrupt requests may be generated. Initialize the watchdog timer regularly.

Do not use the address match interrupt while a command is being executed because the vector of the address match interrupt is allocated in ROM.

Do not use a non-maskable interrupt while block 0 is being automatically erased because the fixed vector is allocated in block 0.

• EW1 Mode

Once a watchdog timer, voltage monitor1, voltage monitor 2, comparator 1, or comparator 2 interrupt request is acknowledged, auto-erasure or auto-programming is forcibly stopped immediately and the flash memory is reset. Interrupt handling starts after a fixed period and the flash memory restarts.

As the block during auto-erasure or the address during auto-programming is forcibly stopped, the normal value may not be readable. Execute auto-erasure again and ensure it completes normally.

The watchdog timer does not stop even during command operation, so that interrupt requests may be generated. Initialize the watchdog timer by using the erase-suspend function.

Do not use the address match interrupt while a command is being executed because the vector of the address match interrupt is allocated in ROM.

Do not use a non-maskable interrupt while block 0 is being automatically erased because the fixed vector is allocated in block 0.

23.9.1.4 How to Access

Write 0 before writing 1 when setting Bits FMR01, FMR02 in the FMR0 register, or FMR11 bit in the FMR1 register to 1. Do not generate an interrupt between writing 0 and 1.

23.9.1.5 Rewriting User ROM Area

In EW0 Mode, if the supply voltage drops while rewriting any block in which a rewrite control program is stored, it may not be possible to rewrite the flash memory because the rewrite control program cannot be rewritten correctly. In this case, use standard serial I/O mode.

23.9.1.6 Program

Do not write additions to the already programmed address.

23.9.1.7 Program and Erase Voltage for Flash Memory

To perform programming and erasure, use VCC = 2.7 V to 5.5 V as the supply voltage. Do not perform programming and erasure at less than 2.7 V.

23.10 Notes on Noise

23.10.1 Inserting a Bypass Capacitor between VCC and VSS Pins as a Countermeasure against Noise and Latch-up

Connect a bypass capacitor (at least 0.1 μ F) using the shortest and thickest write possible.

23.10.2 Countermeasures against Noise Error of Port Control Registers

During rigorous noise testing or the like, external noise (mainly power supply system noise) can exceed the capacity of the MCU's internal noise control circuitry. In such cases the contents of the port related registers may be changed.

As a firmware countermeasure, it is recommended that the port registers, port direction registers, and pull-up control registers be reset periodically. However, examine the control processing fully before introducing the reset routine as conflicts may be created between the reset routine and interrupt routines.

24. Notes for On-Chip Debugger

When using the on-chip debugger to develop and debug programs for the R8C/2G Group take note of the following.

- (1) Some of the user flash memory and RAM areas are used by the on-ship debugger. These areas cannot be accessed by the user.
 - Refer to the on-chip debugger manual for which areas are used.
- (2) Do not set the address match interrupt (registers AIER, RMAD0, and RMAD1 and fixed vector tables) in a user system.
- (3) Do not use the BRK instruction in a user system.
- (4) Debugging is available under the condition of supply voltage VCC = 2.7 to 5.5 V. Debugging with the on-chip debugger under less than 2.7 V is not allowed.

Connecting and using the on-chip debugger has some special restrictions. Refer to the on-chip debugger manual for details.

Appendix 1. Package Dimensions

Diagrams showing the latest package dimensions and mounting information are available in the "Packages" section of the Renesas Technology website.



Appendix 2. Connection Examples with On-Chip Debugging Emulator

Appendix Figure 2.1 shows a Connection Example with E8 Emulator (R0E000080KCE00).



Appendix Figure 2.1 Connection Example with E8 Emulator (R0E000080KCE00)

Appendix 3. Example of Oscillation Evaluation Circuit

Appendix Figure 3.1 shows an Example of Oscillation Evaluation Circuit.



Appendix Figure 3.1 **Example of Oscillation Evaluation Circuit**

Index

[A] AIER
[B] BGRCR 53 BGRTRM 54 BGRTRMA 48 BGRTRMB 48
[C] CAPIC
[F] FMR0 249 FMR1 252 FMR4 253 FRA4 93 FRA6 93
[H] HRA0
[1] INTOIC 114 INT1IC 114 INT2IC 114 INT2IC 114 INT4IC 114 INTEN 121 INTEN2 122 INTF 122 INTF2 123
[K] KIEN
[L] LINCR
[O] OCD
[P] PDi (i = 0, 1, 3, 4, or 6)

PM0	
PM1	
PMR	74
PRCR	
PUR0	
PUR1	74

[R]

RMAD0	
RMAD1	

[S]

SORIC	113
SOTIC	113
S2RIC	113
S2TIC	113

[T]

[']	
TRA	
TRACR	
TRAIC	
TRAIOC	146, 148, 151, 153, 155, 158
TRAMR	
TRAPRE	
TRBCR	
TRBIC	
TRBIOC	
TRBMR	
TRBOCR	
TRBPR	
TRBPRE	
TRBSC	
TRECR1	
TRECR2	
TRECSR	
TREHR	
TREIC	
TREMIN	
TREOPR	
TRESEC	
TREWK	
TRF	
TRFCR0	
TRFCR1	
TRFCR2	
TRFIC	
TRFM0	
TRFM1	
TRFOUT	

[U]

U0BRG	
U0C0	
U0C1	
UOMR	
UORB	
UOTB	
U2BRG	
U2C0	
U2C1	
U2MR	
U2RB	
U2TB	

[V]	
VCA1	35, 49
VCA2	35, 49, 94
VCAB	
VCAC	39, 53
VCMP1IC	113
VCMP2IC	
VW0C	
VW1C	
VW2C	

[W]	
WDC	139
WDTR	139
WDTS	139

REVISION HISTORY	
------------------	--

Rev.	Date		Description
		Page	Summary
0.01	Mar 30, 2007	_	First Edition issued
0.10	Jul 20, 2007		"RENESAS TECHNICAL UPDATE" reflected: TN-16C-A164A/E, TN-16C-A167A/E
		_	Register/bit symbols revised: "CM1POR" \rightarrow "LCM1POR", "CM2POR" \rightarrow "LCM2POR", "ACMR" \rightarrow "ALCMR"
		2	Table 1.1: Clock; "Real-time clock (timer RE)" added
		5	Figure 1.3 "P4_4/(XCOUT) ⁽¹⁾ " → "P4_4/XCOUT", "P4_3/(XCIN) ⁽¹⁾ " → "P4_3/XCIN"
		6	Table 1.3 "(XCOUT) ⁽¹⁾ " \rightarrow "XCOUT", "(XCIN) ⁽¹⁾ " \rightarrow "XCIN"
		13, 36	Table 4.2, Figure 6.6: 0038h After reset; "0000X010b" \rightarrow "1000X010b", "0100X011b" \rightarrow "1100X011b"
		25	Figure 5.3 revised
		26, 130, 135, 242	Figure 5.4, Figure 15.2, Figure 16.3, Figure 20.2: OFS Register; NOTE1 revised
		83	Figure 11.1 revised
		139	Table 17.1: Timer RE; "• fC32" deleted
		144	Figure 17.5 revised
		156	17.2 "The reload register same address" added
		159	Figure 17.15 "Programmable one-shot mode" \rightarrow "Programmable one-shot generation mode"
		162	Figure 17.17 revised
		173	NOTE: "TRBIOC" added
		229	Figure 19.5 revised
		230	Figure 19.6 revised
		231	Figure 19.7: SFDCT flag in the LINST register; "Set bythe B1CLR bit in the LINST register" → "Set bythe B0CLR bit in the LINST register"
		233	Figure 19.9 revised
		236	Figure 19.12 revised
		268	Figure 20.23: Title is revised
		270	Figure 20.24: Title is revised
		276	Figure 21.2 NOTE4 deleted
		282	Table 22.9 Parameter: "High-speed on-chip oscillator temperature supply voltage dependence" \rightarrow "High-speed on-chip oscillator frequency temperature • supply voltage dependence"
		317	Appendix Figure 2.1 revised
0.20	Nov 12, 2007	2	Table 1.1 I/O Ports: "• Output-only: 1" added "• CMOS I/O ports: 28" → "• CMOS I/O ports: 27"
		4	Figure 1.2 revised

REVISION HISTORY

Devi	Dete		Description
Rev.	Date	Page	Summary
0.20	Nov 12, 2007	5	Figure 1.3 revised
		6	Table 1.3 Pin Number: 4, 6, 20 revised
		7	Table 1.4 I/O port: "P4_3 to P4_5" \rightarrow "P4_3, P4_5"
			Output port added
		12	Table 4.1 0006h "01001000b" → "01011000b"
		16	Table 4.5 0118h to 011Dh: After reset revised 011Fh "Timer RE Real-Time Clock Precision Adjust Register" added
		45	Figure 6.13 revised
		61	 8. "There are 28 I/O ports oscillation circuit is not used." → "There are 27 I/O ports used as an output port." Table 8.1 revised, NOTE3 added
		65	Figure 8.3 revised
		67	Figure 8.5 NOTE3 "To use port P4_4 as an input port." added
		69	Figure 8.7 b7 revised
		70	Figure 8.9 PUR1: b1 revised
		71	Table 8.4 revised
		77	Table 8.26 NOTE2 added, Table 8.27 revised
		78	Table 8.29, Table 8.32 revised
		80	8.6 added
		83	Table 11.1 Oscillator status after reset: XCIN Clock Oscillation Circuit "Stop" \rightarrow "Oscillate"
		85	Figure 11.2 revised
		93	11.2 "During and after reset, the XCIN clock stops." → "During and after reset, the XCIN clock oscillates."
		141	Figure 17.1 "TSTART" \rightarrow "TCSTF"
		179	Figure 17.26 revised
		180	Table 17.11 Select function revised
		181	Figure 17.27, Figure 17.28 After Reset "00h" \rightarrow "Undefined"
		182	Figure 17.29 After Reset "00h" \rightarrow "X0XXXXXb" Figure 17.30 After Reset "00h" \rightarrow "X0000XXXb"
		183	Figure 17.31 After Reset "00h" \rightarrow "XXX0X0X0b"
		184	Figure 17.33 After Reset "00h" \rightarrow "00XXXXXb"
		185	Figure 17.35 added
		187	Figure 17.37 revised
		188	Table 17.13 Select functions: Specification revised
		189	Figure 17.38, Figure 17.39 After Reset "00h" \rightarrow "Undefined"
		190	Figure 17.40 After Reset "00h" \rightarrow "XXX0X0X0b"
			Figure 17.41 After Reset "00h" \rightarrow "00XXXXXb"
		193	17.3.3.1 NOTE revised

REVISION HISTORY

D	Date	Description				
Rev.		Page Summary				
0.20	Nov 12, 2007	194	Figure 17.44 revised			
		200	Figure 17.50 NOTE4 added			
		234	Figure 19.9 revised			
		279	Table 22.2 NOTE2 revised			
		309	Figure 23.4 revised			
1.00	Apr 04, 2008	All pages	"Under development" deleted			
		2	Table 1.1 revised			
		3	Table 1.2 "(D): Under development" deleted			
		11	Figure 3.1 "Expanded area" deleted			
		12	Table 4.1 "002Eh" "002Fh" revised			
		13	Table 4.2 "003Eh" "003Fh" revised			
		24	Figure 5.1 NOTE1 added			
		25	Table 5.2 revised			
		38, 51	Figure 6.8, Figure 7.5; "7. The VW2C7 1." \rightarrow "7. The VW2C7 0."			
		48	Figure 7.2 added			
		53, 54	Figure 7.9, Figure 7.10 added			
		63, 64	7.6, Figure 7.16, Figure 7.17 added			
		107	12, Figure 12.1; "BGRCR, and BGRTRM" added			
		144	Table 17.1 Timer RF "Capture interrupt" added			
		161	Figure 17.12 "TSTRAT" \rightarrow "TSTART"			
		171	Table 17.9 "TRBP pin function" \rightarrow "TRBO pin function"			
		235	Figure 19.6 "Three to five" \rightarrow "One to two"			
		238	Figure 19.9 revised			
		244	Table 20.1 "Suspend function" deleted			
		248	20.4 "The flash module (EW1 mode)." deleted Table 20.3 " to erase-suspend" " to program-suspend" deleted			
		250	 FMR00 Bit "(including suspend periods)" deleted 			
		251	Table 20.4 "FRM0 Register" \rightarrow "FMR0 Register"			
		253	Figure 20.5 revised • FMR40 Bit, • FMR41 Bit, • FMR42 Bit, • FMR43 Bit, • FMR44 Bit, • FMR46 Bit; deleted			
		256	Figure 20.8 revised			
		258	• Program Command; revised Old Figure 20.11 deleted			
		259	• Block Erase; revised Old Figure 20.13, Old 20.4.3.2, Old Figure 20.14, Old Figure 20.15; deleted			
		262	Figure 20.13 revised			
		263	Program Command; revised Old Figure 20.19 deleted			

REVISION HISTORY

Rev.	Date	Description		
		Page	Summary	
1.00	Apr 04, 2008	264	• Block Erase; revised Old Figure 20.21, Old 20.4.4.2, Old Figure 20.22, Old Figure 20.23; deleted	
		265	Table 20.6 revised	
		267	Table 20.7 "P4_4 input/clock output" \rightarrow "P4_4 output/clock output"	
		270	Old 20.7.1.7, Old 20.7.1.8 deleted	
		276	Table 22.3 revised Figure 22.2 deleted	
		279	Table 22.8, Table 22.11 revised Table 22.9 revised, NOTE3 added	
		281	Table 22.13 revised	
		285	Table 22.19 revised	
		289	Table 22.25 revised	
		311	Old 23.9.1.7, Old 23.9.1.8 deleted	

R8C/2G Group Hardware Manual

Publication Date	e:		Mar 30, 2007 Apr 04, 2008	
		ales Strategic Planning Div. enesas Technology Corp.		

 $\ensuremath{\mathbb{C}}$ 2008. Renesas Technology Corp., All rights reserved. Printed in Japan

R8C/2G Group Hardware Manual



Renesas Electronics Corporation 1753, Shimonumabe, Nakahara-ku, Kawasaki-shi, Kanagawa 211-8668 Japan