

μPD166029T1J

INTELLIGENT POWER DEVICE

R07DS1163EJ0200 Rev.2.00 May 22, 2015

1. Overview

1.1 Description

Family:

μPD166029T1J is part of 2nd Generation Intelligent Power Devices (IPD). They are N-channel high-side switches with charge pump, voltage controlled input, diagnostic feedback with proportional load current sense and embedded protection function. Family includes up to 14 devices depending on on-state resistance, package and channel number combination.

Scalability:

Variety of on-state resistance combined with standardized package on pin-out give user high flexibility for unit design depending on target load.

Robustness:

Because of advanced protection method, 2nd Generation Intelligent Power Devices achieve high robustness against long term and repetitive short circuit condition.

1.2 Features

- Built-in charge pump
- 3.3V compatible logic interface
- Low standby current
- Short circuit protection
 - Shutdown by over current detection
 - Power limitation protection by over load detection (Power limitation: current limitation with delta Tch control)
 - Absolute Tch over temperature protection
- Built-in diagnostic function
 - Proportional load current sensing
 - Defined fault signal in case of abnormal load condition
 - Loss of ground protection
- Under voltage lock out
- Active clamp operation at inductive load switch off
- AEC Qualified
- · RoHS compliant

1.3 Application

- Light bulb switching from 5W to 10W
- Switching of all types of 14V DC grounded loads, such as LED, inductor, resistor and capacitor
- Power supply switch, fail-safe switch of 14V DC grounded system

Note: The information contained in this document is the one that was obtained when the document was issued, and may be subject to change.


2. Ordering Information

| Part No. | Nick name | Lead plating | Packing | Package |
|--------------------|-----------|---------------|------------------|--------------------|
| UPD166029T1J-E1-AY | NHD070B | Pure Matte Sn | Tape 1500 p/reel | 12-pin Power HSSOP |
| UPD166029T1J-E2-AY | NHD070B | Pure Matte Sn | Tape 1500 p/reel | 12-pin Power HSSOP |

Note: Part No. and Nick name are tentative and might change at anytime without notice.

MSL: 1, profile acc. J-STD-20C


2.1 Nick name




3. Specification

3.1 Block Diagram

3.1.1 Nch High-side Dual Device




Voltage and Current Definition



3.2 Pin Configuration

3.2.1 12-pin Power HSSOP Pin Configuration

| Pin No. | Terminal Name |
|---------|---------------|
| | |
| 1 | GND |
| 2 | IN1 |
| 3 | IS1 |
| 4 | IS2 |
| 5 | IN2 |
| 6 | VCC |
| 7 | SEN |
| 8 | OUT2 |
| 9 | OUT2 |
| 10 | OUT1 |
| 11 | OUT1 |
| 12 | VCC |
| Tab | VCC |



Pin function

| Terminal Name | Pin function | Recommended connection |
|---------------|---|--|
| GND | Ground connection | Connected to GND through a 100 Ω resistor or a diode for reverse current protection |
| | | Refer chapter 6. |
| INn | Input signal for channel n (n=1 to 2) | Connected to MCU port through 2k-50K serial resistor. |
| ISn | Current sense and Diagnosis output signal | Connected to GND through a 0.67K-5K resistor. |
| | channel n (n=1 to 2) | Not connect if this pin is not used. |
| SEN | Sense enable input | Connected to MCU port through 2k-50K serial resistor. Not connect if this pin is not used. |
| OUTn | Protected high-side power output channel n (n=1 to 2) | Connected to load with small 50-100nF capacitor in parallel |
| VCC | Positive power supply for logic supply as well as output power supply | Connected to battery voltage with small 100nF capacitor in parallel |
| N.C. | Non connection | Left open |

3.3 Absolute Maximum Ratings

Ta=25°C, unless other specified

| Parameter | Symbol | Rating | Unit | Test Condition | | | |
|---|-----------------------|--------------|------|---|--|--|--|
| Vcc Voltage | Vcc | 28 | V | | | | |
| Vcc Voltage at reverse | -Vcc | -16 | V | RL=7.7 Ω , t<2min, | | | |
| battery condition | | | | RIN= $2k\Omega$, RSEN= $2k\Omega$,RIS= $1k\Omega$, RGND= 100Ω | | | |
| GND Reverse current at reverse battery condition | I _{GND(Rev)} | 200 | mA | RL=7.7Ω, t<2min | | | |
| Vcc voltage under Load Dump condition | Vload dump | 42 | V | RI=1 Ω , RL=7.7 Ω , RIS=1k Ω , RIN=2k Ω , RSEN=2k Ω , RGND=100 Ω , td=400ms | | | |
| Load Current | IL | Self limited | Α | , | | | |
| Total power dissipation for whole device (DC) | P _D | 1.85 | W | Ta=85degreeC, Device on 50mm×50mm×1.5mm epoxy PCB FR4 with 6 cm² of 70 μm copper area | | | |
| Voltage at IN pin | Vin | -2 ~ 16 | V | DC RIN=2kΩ | | | |
| | | -16 | | At reverse battery condition, t<2min, RIN=2kΩ, RSEN=2kΩ | | | |
| IN pin current | I _{IN} | 10 | mA | DC | | | |
| Voltage at IS pin | Vis | VCC | V | DC RIS=1kΩ | | | |
| | | -16 | V | At reverse battery condition, t<2min, RL=7.7 Ω , RIS=1k Ω | | | |
| IS Reverse current at reverse battery condition | I _{IS(Rev)} | -30 | mA | At reverse battery condition, t<2min, RL=7.7Ω | | | |
| Voltage at SEN pin | Vsen | -2 ~ 16 | V | DC RSEN=2kΩ | | | |
| | | -16 | | At reverse battery condition, t<2min RIN= $2k\Omega$, RSEN= $2k\Omega$ | | | |
| SEN pin current | Isen | 10 | mA | DC | | | |
| Channel Temperature | Tch | -40 to +150 | °C | | | | |
| Storage Temperature | Tstg | -55 to +150 | °C | | | | |
| ESD susceptibility | V _{ESD} | 2000 | V | HBM AEC-Q100-002 std. All pin R=1.5kΩ, C=100pF | | | |
| | | 4000 | | IEC61000-4-2 std. R=330Ω, C=150pF, 100nF at VCC and OUT | | | |
| | | 200 | V | MM AEC-Q100-003 std. R=0Ω, C=200pF | | | |
| Inductive load switch-off energy dissipation single pulse | EAS | 15 | mJ | VCC=13.5V, Tch,start<150°C, RL=7.7Ω | | | |
| Inductive load switch-off energy dissipation repetitive pulse | EAR | 13 | mJ | VCC=13.5V, Tch,start=85°C, RL=7.7Ω | | | |

3.4 Thermal Characteristics

| Parameter | Symbol | Min | Тур | Max | Unit | Test Condition |
|-------------------------|-----------|-----|-----|-----|------|---|
| Thermal characteristics | Rth(ch-a) | | 35 | | °C/W | According to JEDEC JESD51-2, -5, -7 on FR4 2s2p board |
| | Rth(ch-c) | | 1.3 | | °C/W | All channel |

3.5 Electrical Characteristics

Operation function

Tch=-40 to 150°C, Vcc=7 to 18V, unless otherwise specified

| Parameter | Symbol | Min | Тур | Max | Unit | Test Con | dition |
|--|----------------------|-----|-----|-----|------|---|-----------------------------------|
| Operating Voltage | Vcc | 4.5 | | 28 | V | V _{IN} =4.5V | |
| | | | | | | RL=7.7Ω | |
| Operating current per channel | I _{GND} | | 2.2 | 4 | mA | V _{IN} =4.5V | |
| Output Leakage current per channel | I _{L(off)} | | | 0.5 | μА | Tch=25°C | VCC=13.5V, VIN=0V, VSEN=0V, |
| | | | | 3 | | Tch=-40~125°C | VIS=0V, VOUT=0V, VGND=0V |
| Standby current | ICC(off) | | | 0.5 | μА | Tch=25°C | VCC=13.5V, VIN=0V, VSEN=0V, |
| | | | | 2 | | Tch=-40~85°C | VIS=0V, VOUT=0V, VGND=0V |
| On-state resistance per | Ron | | 70 | | mΩ | Tch=25°C, IL=1.8A | |
| channel | | | | 180 | | Tch=150°C, IL=1.8A | |
| Low level IN pin voltage | VIL | | | 0.8 | V | | |
| High level IN pin voltage | VIH | 2.5 | | | V | | |
| Low level IN pin current | lıL | 2 | | 25 | μΑ | VIN=0.8V | |
| High level IN pin current | Iн | 2 | | 25 | μΑ | VIN=2.5V | |
| Clamping IN pin voltage 1) | Vzin | 5 | 6 | | V | | |
| Low level SEN pin voltage | V _{SENL} | | | 0.8 | V | | |
| High level SEN pin voltage | V _{SENH} | 2.5 | | | V | | |
| Low level SEN pin current | ISENL | 2 | | 25 | μА | VSEN=0.8V | |
| High level SEN pin current | ISENH | 2 | | 25 | μА | VSEN=2.5V | |
| Clamping SEN pin voltage ¹⁾ | Vzsen | 5 | 6 | | V | | |
| Under voltage shutdown | V _{CC(Uv)} | | | 4.5 | V | | |
| Under voltage restart | V _{CC(Cpr)} | | | 5.0 | V | | |
| Turn on time | ton | | | 200 | μS | VCC=13.5V, RL=7.7Ω | |
| Turn on delay time | td(on) | | | 100 | μS | | |
| Turn off time | toff | | | 200 | μS | | |
| Turn off delay time | td(off) | | | 150 | μS | | |
| Slew rate on | dV/dton | | | 1.5 | V/μs | | |
| Slew rate off | -dV/dtoff | | | 1.5 | V/μs | | |
| Switching drift ¹⁾ | ton-toff | -50 | | +50 | μS | Vcc = 9 to 18V drift from Tch=-40 to 150°C drift fi ton; Vout=Vcc-1.5V afte | om Tch=25°C |
| Turn on energy loss 1) | Eon | | 0.1 | 0.2 | mJ | VCC=13.5V,Tch=25°C, | RL=7.7Ω |
| Turn off energy loss 1) | Eoff | | 0.1 | 0.2 | mJ | | |
| Driving capability 1) | Dr(capa) | 450 | | | mΩ | Tch=25°C, VCC=8~16V | |
| | | 550 | | | | Tch=105°C, VCC=8~16 | V |

¹⁾ not subjected production test, guaranteed by design

Protection function

Tch=-40 to 150°C, Vcc=7 to 18V, unless otherwise specified

| Parameter | Symbol | Min | Тур | Max | Unit | Test Condition | |
|--|------------------|-----|-----|-----|------|----------------------------------|--|
| Over current detection current | IL(SC) | 13 | 22 | | Α | VCC=13.5V, Von=8V, Tch=25°C | |
| Current limitation under power limitation toggling | IL(CL) | | 11 | | Α | VCC=13.5V | |
| Current limitation under absolute thermal toggling | IL(TT) | | 5 | | Α | VCC=13.5V | |
| Current limitation trigger threshold during turn-on | Von(CL1) | | 2.0 | | V | VCC=13.5V | |
| Current limitation trigger threshold during on-state | Von(CL2) | | 0.8 | | V | VCC=13.5V | |
| Absolute thermal shutdown temperature | aTth | 150 | | | °C | | |
| Thermal hysteresis for absolute thermal toggling | aTth,hys | | 20 | | °C | | |
| Power limitation thermal shutdown temperature | dTth | | 60 | | °C | | |
| Power limitation restart temperature | dTth,rest art | | 30 | | °C | | |
| Output clamp at inductive load switch off | Von,clam p | 30 | | 40 | V | VCC=13.5V, IL=40mA, Tch=25°C | |
| Output current while GND disconnection | IL(GND) | | | 1 | mA | IIN=0A, ISEN=0A, IGND=0A, IIS=0A | |
| Output voltage drop at reverse battery condition | Vds(rev) | | | 0.9 | V | Tch=25°C VCC=-13.5V, | |
| Teverse battery condition | | | | 0.7 | | Tch=150°C RL=7.7Ω | |

Diagnosis function

Tch=-40 to 150°C, Vcc=7 to 18V, VIN=4.5V, VSEN=4.5V, unless otherwise specified

| Parameter | Symbol | Min | Тур | Max | Unit | Test Condition |
|--|------------|------|------|------|------|---------------------------------------|
| Current sense ratio | KILIS | 1120 | 1400 | 1680 | | IL=1.0A |
| | | 980 | 1400 | 1820 | | IL=0.2A |
| Current sense drift depend on temperature | dKILIS | -15 | | 15 | % | VCC=13.5V, Tch,start=25°C, RL=7.7Ω |
| Sense current offset current | lis,offset | | | 2 | μА | IL<10mA |
| Sense current leakage current | lis,dis | | | 1 | μА | VIN=0V, VSEN=0V |
| Sense current under fault | lis,fault | 3 | | 9.5 | mA | VCC=13.5V, RIS=0.67kΩ |
| condition | | 3.5 | | 9 | | VCC=13.5V, RIS=1kΩ |
| | | 3.5 | | 5.5 | | VCC=13.5V, RIS=2kΩ |
| Minimum output current for current sense output | IL(CSE) | 10 | | 45 | mA | IIS>5μA |
| Open load detection threshold at off-state | VOUT(OL) | 2.0 | | 5.0 | V | VIN=0V, Tch=-40~105°C |
| OUT terminal current at Open load condition | IOUT(OL) | -1.0 | | | μА | VIN =0V |
| Open load detection delay after input negative slope | tdop | | 300 | | μS | VIN=4.5V to 0V, VOUT>VOUT(OL) |

Diagnosis function

Tch=-40 to 150°C, Vcc=7 to 18V, VIN=4.5V, VSEN=4.5V, unless otherwise specified


| Parameter | Symbol | Min | Тур | Max | Unit | Test Condition |
|---|--------------|-----|-----|-----|------|--|
| Sense current settling time after input signal positive slope | tsis(on) | | | 250 | μS | VCC=13.5V, VIN=0V to 4.5V, IL/IIS=KILIS, RL=7.7 Ω |
| Sense current settling time after input signal negative slope ¹⁾ | tsis(off) | | | 10 | μS | VIN=4.5V to 0V |
| Sense current settling time after sense enable during on-state ¹⁾ | tssen(on) | | | 20 | μs | VSEN=0V to 4.5V, RL=7.7Ω |
| Sense current settling time after sense disable during on-state ¹⁾ | tssen(off) | | | 20 | μS | VSEN=4.5V to 0V, RL=7.7Ω |
| Sense current settling time during on-state 1) | tsis(LC) | | | 20 | μS | RL=7.7 Ω to 3.85 Ω |
| Fault signal delay after over current detection 1) | tdsc(fault) | | | 10 | μS | VIN=0V to 4.5V, IL=IL(SC) |
| Fault signal delay after power limitation valid 1) | tdpl(fault) | | | 10 | μS | Von>Von(CL1) |
| Fault signal delay after power limitation invalid 1) | tdpl(off) | | | 30 | μS | Von <von(cl1)< td=""></von(cl1)<> |
| Fault signal delay after absolute thermal shutdown | tdot(fault) | | | 10 | μS | IIS→IIS,fault |
| Fault signal delay after open load detection at off-state 1) | tdop(fault) | | | 10 | μS | VIN=0V, VOUT>VOUT(OL) |
| Fault signal delay after input negative slope 1) | tdoff(fault) | | | 10 | μS | VIN=4.5V to 0V |

¹⁾ not subjected production test, guaranteed by design

3.6 Feature Description


3.6.1 Driving Circuit

The high-side output is turned on, if the input pin is over VIH. The high-side output is turned off, if the input pin is open or the input pin is below VIL. Threshold is designed between VIH min and VIL max with hysteresis. IN terminal is pulled down with constant current source.




Switching a resistive load

Switching lamps




Switching an inductive load



The dynamic clamp circuit works only when the inductive load is switched off. When the inductive load is switched off, the voltage of OUT falls below 0V. The gate voltage of SW1 is then nearly equal to GND. Next, the voltage at the source of SW1 (= gate of output MOS) falls below the GND voltage.


SW1 is turned on, and the clamp diode is connected to the gate of the output MOS, activating the dynamic clamp circuit.

When the over-voltage is applied to VCC, the gate voltage and source voltage of SW1 are both nearly equal to GND. SW1 is not turned on, the clamp diode is not connected to the gate of the output MOS, and the dynamic clamp circuit is not activated.




3.6.2 Device behavior at over voltage condition

In case of supply voltage greater than Vload dump, logic part is clamped by ZD_{AZ} (35V min). And current through of logic part is limited by external ground resistor. In addition, the power transistor switches off in order to protect the load from over voltage. Permanent supply voltage than V_{load} dump must not be applied to VCC.



3.6.3 Device behavior at low voltage condition

If the voltage supply (V_{CC}) goes down under $V_{CC}(Uv)$, the device outputs shuts down. If voltage supply (V_{CC}) increase over $V_{CC}(Cpr)$, the device outputs turns back on automatically. The device keeps off state after under voltage shutdown. The IS output is cleared during off-state.



3.6.4 Loss of Ground protection

In case of complete loss of the device ground connection, but connected load ground, the device securely changes to off if VIN was initially greater than VIH state or keeps off state if VIN was initially lower than VIL state.

In case of device loss of ground, IN and SEN terminal will/could/ might be at VCC voltage.

3.6.5 Short circuit protection

Turn-on in an over load condition including short circuit condition

The device shuts down automatically when condition (a) is detected. The sense pin output Iis,fault. Shutdown is latched until the next reset via input pin. The device shuts down automatically when condition (b) is detected. The device restarts automatically when device cooling to dTch,restart. The output current is limited by output power MOSFET saturation current. The device shuts down automatically when condition (c) is detected and restarts automatically in absolute thermal toggling mode. The sense pin output Iis,fault during power limitation mode or thermal toggling mode. In case of device shutdown by (c) detection but also (b) condition, the output current is limited by IL(CL).

- (a) IL > IL(SC)
- (b) deltaTch > dTth
- (c) Tch > aTth

Over load condition including short circuit condition during on-state

The device runs automatically into power limitation mode when condition (a) is detected once after Von < Von(CL2). The device shuts down automatically when condition (b) is detected. The device restarts automatically in power limitation mode. The device shuts down automatically when condition (c) is detected and restarts automatically in absolute thermal toggling mode. The sense pin output Iis, fault during power limitation mode or thermal toggling mode.

- (a) Von > Von(CL2)
- (b) deltaTch > dTth
- (c) Tch > aTth

Power limitation control

Current limitation control with IL(CL) when auto restart from deltaTch protection.

During the current limitation operation and Von>Von(CL1), the sense pin outputs Iis,fault. Even auto restart from delta Tch protection, if Von<Von(CL2) depends on short circuit impedance condition, the device does not operate as current limitation with IL(CL). In this case, the sense pin output sense current at on-state, Iis,fault at off-state during toggling operation with power limitation mode.

Absolute thermal toggling

Current limitation control with IL(TT) when auto restart from absolute Tch protection.

During the current limitation operation and Von>Von(CL1), the sense pin outputs Iis, fault. Even auto restart from absolute Tch protection, if Von<Von(CL2) depends on short circuit impedance condition, the device does not operate as current limitation with IL(TT). In this case, the sense pin output sense current at on-state, Iis, fault at off-state during toggling operation with thermal toggling mode.

delta Tch


Junction temperature differences between thermal sensor of power area and thermal sensor of control area.

3.6.6 Device behavior at reverse current conduction during on-state


During on-state(VIN>VIH) the device might shut down automatically when Vout>Vcc+0.3V is detected.

And the sense pin outputs Iis, fault if the device shuts down.

If restart is required, please reset via input pin when detect the Iis.fault.




State transition diagram



IL(lim) initial value is power MOSFET saturation current.


Turn-on in an over load condition including short circuit condition

(a) IL > IL(SC)




Turn-on in an over load condition including short circuit condition

(b) deltaTch > dTth




Turn-on in an over load condition including short circuit condition

(c) Tch > aTth




An over load condition which is include a short circuit condition during on-state

(a) Von > Von(CL) with weak short condition




An over load condition including short circuit condition during on-state

(a) Von > Von(CL) with dead condition




An over load condition including short circuit condition during on-state

(b) deltaTch > dTth



An over load condition including short circuit condition during on-state


(c) Tch > aTth



3.6.7 Device behavior at small load current conduction

The device has a function which controls Ron in order to improve KILIS accuracy at small load current conduction.

Von (VCC-OUT) is proportionate to IL under normal conditions. Under IL<IL(NL) condition, Ron is controlled to increase to be Von=Von(NL)=30mV(typ).



3.6.8 Diagnostic signal


Truth table


| | SEN | Input | Output | Diagnostic output ²⁾ |
|----------------------|-----|-------|-----------------|---|
| Normal Operation | Н | H VCC | | IIS = IL/KILIS |
| Normal Operation | | L | L 1) | < 1μA (lis,dis) |
| Shutdown by over | | Н | L 1) | lis,fault 3) |
| current detection | | L | L 1) | < 1μA (lis,dis) |
| | | | \ (QLIT 6) | IIS = IL/KILIS in case of Von <von(cl1)< td=""></von(cl1)<> |
| Power limitation | | Н | VOUT 6) | lis,fault 4) in case of Von>Von(CL1) |
| 1 ower minitation | | | L 1) | lis,fault 4) |
| | | L | L ¹⁾ | < 1µA (lis,dis) |
| | | | VOUT 6) | IIS = IL/KILIS in case of Von <von(cl1)< td=""></von(cl1)<> |
| Thormal togaling | | Н | VO01 % | lis,fault 5) in case of Von>Von(CL1) |
| Thermal toggling | | | L 1) | lis, fault 5) |
| | | L | L ¹⁾ | < 1µA (lis,dis) |
| Short circuit to VCC | | Н | VCC | < 2μA (lis,offset) |
| Short circuit to VCC | | L | VOUT 7) | lis,fault in case of VOUT>VOUT(OL) |
| Open Load | | Н | VCC | < 2μA (lis,offset) |
| Open Load | | L | VOUT 7) | lis,fault in case of VOUT>VOUT(OL) |
| X 8) | L | X 8) | X 8) | < 1µA (lis,dis) |

- 1) In case of OUT terminal is connected to GND via load.
- 2) In case of IS terminal is connected to GND via resister.
- 3) IS terminal keeps Iis, fault as long as input signal activate after the over current detection.
- 4) IS terminal keeps Iis, fault during power limitation if Von>Von(CL1).
- 5) IS terminal keeps Iis, fault during thermal toggling if Von>Von(CL1)..
- 6) VOUT depends on the short circuit condition
- 7) VOUT depends on the ratio of VCC-OUT-GND resistive component.
- 8) Don't care

Current sense output


The device output analog feedback current proportional to output current from IS pin. In the case of much higher current than nominal load current, current sense output is saturated. In the case of much lower current than nominal load current, current sense output is above $5\mu A$ if output current is above IL(CSE) max, current sense output is below $2\mu A$, IIS,offset max, if output current is below IL(CSE) min.







Sense current under fault condition

The device output IIS, fault, constant current, from IS pin under fault condition such as after over current detection, during power limitation and during thermal toggling. IIS, fault is specified with RIS=1k Ω condition. IIS, fault is attenuated depends on VCC-VIS voltage. Operation point as IIS, fault output is also depends on RIS condition. For example, In the case of RIS=1k Ω , IIS, fault could be 3.5mA to 9mA, VCC-VIS could be 4.5V to 10V, VIS could be 9V to 3.5V if VCC=13.5V. In the case of RIS is higher than 1k Ω , Operation point as IIS, fault is lower than specified value but VIS should be higher than RIS=1k Ω condition.







Sense current settling time




Fault signal delay time at over current detection




Fault signal delay time at power limitation



Fault signal delay time at Thermal toggling



Fault signal delay time at open load detection





3.6.9 Nominal load

| Product | Nominal load | | |
|---------|--------------|--|--|
| NHD070B | 7.7Ω | | |

3.6.10 Driving Capability


Driving Capability is specified as load impedance. Over current detection characteristics is designed above Driving Capability characteristics. If estimated load impedance which comes from peak inrush current is lower than Driving Capability characteristics, this means, the device does not detect inrush current as over current and does not shutdown the output. Depend on the conditions, Power Limitation function may work during inrush current. If estimated load impedance which comes from peak inrush current is lower than Driving Capability characteristics, Power limitation disappear within 30ms. This parameter does not mean that the device can drive the resistive load up to Driving Capability characteristics.






3.6.11 Measurement condition

Switching waveform of OUT terminal




3.7 Package drawing


12-pin Power HSSOP




3.8 Taping information





3.9 Marking information





4. Typical characteristics















































































5. Thermal characteristics

TRANSIENT THERMAL RESISTANCE vs. PULSE WIDTH



6. Application example in principle



RIN, RSEN, RAN values are in range of 2k to $50k\Omega$ depending microcontroller while R_L value is typically $4k\Omega$.

If necessary to raise HBM tolerated dose, adding resister between OUT terminal and Ground is effective. Resister's value is typically $100k\Omega$


GND Network recommendation

In case of V_loaddump < 35V

Vbat VCC GND

External diode is recommended in order to prevent reverse current toward control logic part at reverse battery condition.

In case of $35V < V_loaddump < 42V$



External diode and resistor are recommended in order to prevent reverse current toward control logic part at reverse battery condition and limit the current through ZD_{AZ} at load dump condition. 100Ω is recommended as RGND.

Note: If other component is installed to prevent reverse current at reverse battery condition, diode is not required in GND Network.

Note: Approx. $1k\Omega$ additional resistor in parallel with the diode is recommended if Vf vaule of the diode is high.

Revision History

$\mu PD166029T1J \ Datasheet$

| | | | Description | | | |
|------|--------------|------|---|--|--|--|
| Rev. | Date | Page | Summary | | | |
| 1.00 | Mar 27, 2014 | 1-38 | 1st issue | | | |
| 2.00 | May 22, 2015 | 15 | "Device behavior at reverse current conduction during on-state" is added. | | | |
| | | 24 | "Device behavior at small load current conduction" is added. | | | |

Notice

- 1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information
- 2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product
- 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc
 - Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics.
- 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
- 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics
- 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics



SALES OFFICES

Renesas Electronics Corporation

http://www.renesas.com

Refer to "http://www.renesas.com/" for the latest and detailed information

Renesas Electronics America Inc. 2801 Scott Boulevard Santa Clara, CA 95050-2549, U.S.A. Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited 9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3 Tel: +1-905-237-2004

Renesas Electronics Europe Limited Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100191, P.R.China Tel: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, P. R. China 200333
Tel: 486-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2865-6688, Fax: +852 2886-9022

Renesas Electronics Taiwan Co., Ltd. 13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd. 80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949 TE: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia Tei: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HALII Stage, Indiranagar, Bangalore, India Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd. 12F., 234 Teheran-ro, Gangnam-Gu, Seoul, 135-080, Korea Tel: +82-2-558-3737, Fax: +82-2-558-5141

© 2015 Renesas Electronics Corporation. All rights reserved.